

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332335-840

Luminaire Tested: **S123RDIP-S1000D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332335-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D365U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5156.2 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332335-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332335-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74
1	104	99	96	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	57	54
3	87	77	70	64	82	74	67	62	67	62	58	61	57	53	56	52	49	46
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43	40
5	74	62	53	47	70	59	52	46	54	48	43	50	44	40	45	41	38	35
6	68	56	47	41	64	53	46	40	49	43	38	45	40	36	41	37	33	31
7	63	51	42	37	60	49	41	36	45	38	34	41	36	32	38	33	30	28
8	59	46	38	33	56	44	37	32	41	35	30	38	32	29	35	30	27	25
9	55	42	35	30	52	41	34	29	38	32	27	35	30	26	32	28	24	23
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	30	26	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332335-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	3.1
10°-20°	442.8	8.6
20°-30°	637.6	12.4
30°-40°	718.2	13.9
40°-50°	687.1	13.3
50°-60°	562.6	10.9
60°-70°	379.6	7.4
70°-80°	191.0	3.7
80°-90°	51.9	1.0
90°-100°	98.1	1.9
100°-110°	277.8	5.4
110°-120°	273.3	5.3
120°-130°	218.0	4.2
130°-140°	171.9	3.3
140°-150°	128.3	2.5
150°-160°	89.4	1.7
160°-170°	52.5	1.0
170°-180°	17.1	0.3
0°-30°	1239.5	24.0
0°-40°	1957.7	38.0
0°-60°	3207.4	62.2
0°-90°	3829.9	74.3
90°-120°	649.2	12.6
90°-150°	1167.3	22.6
90°-180°	1326.0	25.7
0°-180°	5156.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	1	4	9	10	10	4
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	219	481	552	72
125°	102	120	205	371	435	90
135°	119	142	202	306	353	92
145°	136	156	199	251	276	85
155°	154	167	193	219	229	71
165°	169	174	185	196	199	48
175°	176	176	177	180	180	17
180°	176	176	176	176	176	



TEST NUMBER: P332335-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.6	24.0	21.4	19.0	16.5	15.2	15.5	15.7	15.9	16.1	15.8
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.8	6.8	7.9	8.9	8.6
92.5°	4.4	6.6	9.6	12.3	15.3	20.6	30.0	45.3	60.4	54.8	41.4
95°	12.1	13.2	17.2	23.2	32.5	46.4	76.7	129.9	188.4	211.7	171.7
97.5°	20.7	21.0	24.1	29.4	38.6	53.6	82.6	142.5	240.1	328.0	350.8
100°	26.5	26.8	29.3	34.2	42.8	56.8	81.7	134.5	228.4	338.0	408.3
102.5°	32.4	33.0	35.2	40.0	47.7	60.5	82.9	127.6	211.3	319.4	411.1
105°	41.4	42.5	44.6	48.9	55.6	66.8	86.0	122.8	190.3	286.9	389.3
107.5°	51.0	52.0	54.1	58.3	64.6	74.9	91.9	122.4	176.8	258.2	351.2
110°	57.8	58.9	60.7	64.6	70.7	80.7	96.7	123.8	171.7	242.0	327.3



TEST NUMBER: P332335-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.1	65.1	67.0	70.9	77.0	86.6	101.6	126.7	168.7	231.1	306.4
115°	73.1	74.6	76.7	80.3	86.3	96.0	109.6	131.3	167.7	219.4	281.2
117.5°	82.2	83.8	85.6	89.0	95.7	104.6	118.1	137.4	168.3	212.6	266.0
120°	88.5	89.6	91.4	94.9	101.7	110.6	123.5	142.0	169.6	209.4	258.0
122.5°	93.9	95.0	96.7	100.7	107.1	116.6	129.2	146.3	171.5	207.5	251.5
125°	101.7	102.4	104.5	108.5	115.2	124.9	137.4	153.1	174.5	204.8	243.1
127.5°	107.7	108.7	111.4	115.3	122.8	132.5	144.5	158.6	177.9	203.6	235.6
130°	111.4	112.4	115.6	119.9	127.4	137.0	148.9	162.4	180.3	202.7	231.6
132.5°	114.2	115.5	119.1	124.2	131.7	141.1	152.5	165.8	182.0	202.4	227.9
135°	119.2	120.6	124.5	129.9	137.4	147.0	158.0	170.3	184.5	202.0	223.1
137.5°	123.9	125.4	129.3	134.9	142.4	151.3	162.0	173.5	186.2	201.2	218.8
140°	127.0	128.9	132.4	138.1	145.2	154.2	164.5	175.2	187.3	201.0	216.2
142.5°	130.5	132.0	135.8	141.0	148.1	156.4	166.5	176.9	188.2	200.4	214.0
145°	135.9	137.0	140.3	145.6	151.7	159.9	169.2	178.7	188.7	199.4	210.9
147.5°	141.6	142.2	145.3	150.0	155.8	162.8	171.3	180.0	188.7	198.1	207.9
150°	145.2	145.6	148.5	153.1	158.0	164.5	172.7	180.3	188.7	197.0	205.9
152.5°	149.0	149.1	151.9	155.9	160.4	166.5	173.6	180.8	187.9	195.6	203.6
155°	154.5	154.5	156.6	160.3	164.2	169.2	175.2	181.0	187.0	193.1	200.2
157.5°	159.0	159.3	161.0	164.1	167.4	171.3	176.1	181.3	185.8	190.9	196.3
160°	162.4	162.4	163.8	166.6	169.2	172.7	177.0	181.3	185.2	189.1	193.8
162.5°	164.9	164.9	166.1	168.3	170.6	173.6	177.3	181.0	184.1	187.4	191.2
165°	168.7	168.4	169.2	171.0	172.4	174.9	177.7	180.3	182.4	184.9	187.7
167.5°	171.7	171.3	171.7	173.0	174.0	175.6	177.6	179.7	180.7	182.3	184.4
170°	173.4	172.7	173.1	174.1	174.9	175.6	177.3	178.7	179.6	180.6	182.4
172.5°	174.6	174.1	174.2	175.0	175.4	175.8	177.3	178.5	178.6	179.2	180.4
175°	175.9	175.6	175.2	175.9	175.9	176.3	177.0	177.7	177.3	177.3	178.0
177.5°	176.6	176.3	176.0	176.3	176.3	176.3	176.6	177.1	176.6	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P332335-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	15.6	15.5	15.2	15.1	14.8	14.6	14.4	14.1
90°	8.9	9.3	9.6	10.3	10.0	10.3	10.7	10.3
92.5°	30.1	23.8	21.0	19.2	18.6	17.5	17.9	17.2
95°	128.5	87.1	68.2	55.3	48.6	45.3	42.8	41.4
97.5°	320.2	256.5	210.5	167.8	141.5	125.4	115.7	112.7
100°	420.7	391.8	350.1	299.4	263.4	237.3	223.4	223.8
102.5°	454.1	453.2	428.9	396.8	368.7	348.1	336.5	328.2
105°	463.9	499.6	506.3	497.2	480.7	467.2	455.8	453.9
107.5°	435.8	493.7	525.0	537.8	538.1	533.4	529.6	526.3
110°	409.0	474.6	519.6	544.6	554.6	557.4	556.7	556.0



TEST NUMBER: P332335-840

CATALOG NUMBER: S123RDIP-S1000D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.4	449.5	499.9	532.0	550.3	559.2	561.9	562.0
115°	347.2	409.3	461.8	500.7	527.5	543.1	550.3	552.1
117.5°	321.7	375.4	422.4	461.9	489.9	507.9	518.1	520.5
120°	308.3	356.5	399.3	435.4	463.5	483.5	492.1	494.2
122.5°	297.8	341.3	381.0	414.5	439.6	457.6	467.0	469.7
125°	283.7	322.7	356.9	385.5	408.3	423.9	432.9	435.4
127.5°	271.5	306.1	337.0	363.0	383.3	396.8	404.9	407.1
130°	263.7	295.9	324.8	349.0	367.9	380.8	388.3	391.1
132.5°	256.6	286.1	313.1	336.2	354.0	366.8	373.4	375.5
135°	246.9	272.3	295.5	315.8	333.4	344.1	350.4	352.9
137.5°	238.1	258.9	278.9	296.6	311.2	322.1	327.5	329.2
140°	233.1	251.3	268.3	283.7	297.3	307.3	313.0	312.7
142.5°	228.2	243.8	258.6	272.0	283.6	292.5	297.5	297.2
145°	222.4	234.1	245.5	255.9	264.8	272.3	275.2	275.9
147.5°	217.5	226.9	236.1	243.5	250.2	255.3	258.0	258.3
150°	214.1	222.4	229.8	236.6	242.0	245.9	248.0	248.0
152.5°	211.0	218.0	224.7	230.4	234.5	238.1	239.4	239.4
155°	206.3	212.0	217.3	221.6	224.8	227.7	228.4	228.7
157.5°	201.3	206.0	210.2	213.6	216.3	218.4	219.0	218.9
160°	198.4	202.4	205.9	208.4	210.9	213.1	213.1	212.7
162.5°	195.0	198.3	201.7	203.9	205.5	207.3	207.3	207.0
165°	190.6	192.7	195.2	197.0	198.4	199.9	199.4	199.4
167.5°	186.7	188.3	189.8	191.1	191.7	192.7	192.4	192.4
170°	184.1	185.2	186.6	187.3	187.7	188.4	188.0	188.0
172.5°	181.9	182.7	183.8	184.2	184.3	185.0	184.4	184.1
175°	178.7	179.2	179.9	179.9	179.9	180.3	179.9	179.6
177.5°	176.8	177.1	177.4	177.4	177.1	177.4	176.8	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)