

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332347-840

Luminaire Tested: **S123RDIP-S1000D805U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332347-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U840-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6765.9 lumens  
Efficiency: N/A  
Efficacy: 124.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332347-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332347-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	92	88	93	89	86	83	77	74	72	66	64	62	56	54	53	48
2	91	84	78	73	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	76	66	58	52	71	62	55	49	54	48	44	46	42	39	40	36	34	31
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	36	32	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	29	36	31	26	32	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	22	25	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332347-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.1	2.4
10°-20°	442.8	6.5
20°-30°	637.6	9.4
30°-40°	718.2	10.6
40°-50°	687.1	10.2
50°-60°	562.6	8.3
60°-70°	379.6	5.6
70°-80°	191.0	2.8
80°-90°	53.5	0.8
90°-100°	217.1	3.2
100°-110°	614.6	9.1
110°-120°	604.6	8.9
120°-130°	482.3	7.1
130°-140°	380.2	5.6
140°-150°	283.8	4.2
150°-160°	197.8	2.9
160°-170°	116.2	1.7
170°-180°	37.8	0.6
0°-30°	1239.5	18.3
0°-40°	1957.7	28.9
0°-60°	3207.4	47.4
0°-90°	3831.6	56.6
90°-120°	1436.3	21.2
90°-150°	2582.6	38.2
90°-180°	2934.0	43.4
0°-180°	6765.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	2	10	20	22	23	5
95°	27	87	468	137	92	29
105°	92	135	635	1110	1004	97
115°	162	202	486	1065	1221	160
125°	225	266	453	821	963	200
135°	264	315	447	676	781	204
145°	301	345	441	555	610	189
155°	342	369	427	486	506	157
165°	373	384	409	434	441	105
175°	389	390	392	398	397	37
180°	390	390	390	390	390	



TEST NUMBER: P332347-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.7	24.3	21.9	19.8	17.4	16.4	16.9	17.3	17.8	18.3	17.9
90°	1.6	3.1	4.7	7.1	8.7	10.3	12.6	15.0	17.4	19.7	19.0
92.5°	9.8	14.5	21.2	27.4	33.9	45.6	66.3	100.3	133.6	121.4	91.6
95°	26.9	29.2	37.9	51.3	71.8	102.6	169.8	287.4	416.9	468.2	379.8
97.5°	45.7	46.6	53.4	65.0	85.2	118.6	182.7	315.4	531.2	725.6	776.3
100°	58.5	59.2	64.7	75.8	94.7	125.5	180.8	297.6	505.3	747.7	903.2
102.5°	71.7	73.1	78.0	88.5	105.5	133.7	183.3	282.5	467.4	706.6	909.6
105°	91.6	93.9	98.7	108.2	123.2	147.6	190.3	271.6	420.8	634.8	861.4
107.5°	112.7	115.1	119.7	129.0	143.1	165.8	203.2	270.8	391.1	571.3	777.1
110°	127.9	130.3	134.2	142.9	156.3	178.4	214.0	274.0	379.8	535.3	724.0



TEST NUMBER: P332347-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	141.8	144.2	148.1	156.8	170.3	191.7	224.7	280.2	373.4	511.3	677.9
115°	161.9	165.0	169.8	177.6	191.1	212.4	242.4	290.5	371.1	485.5	622.2
117.5°	181.9	185.5	189.5	196.7	211.8	231.5	261.2	304.2	372.5	470.4	588.5
120°	195.8	198.1	202.1	210.1	225.0	244.8	273.2	314.3	375.1	463.4	570.9
122.5°	207.8	210.2	214.1	222.7	237.0	258.0	285.8	323.7	379.4	459.1	556.3
125°	225.0	226.6	231.4	240.0	255.0	276.3	304.0	338.7	386.1	453.2	537.7
127.5°	238.1	240.4	246.3	255.2	271.8	293.1	319.7	351.0	393.6	450.4	521.3
130°	246.3	248.7	255.8	265.3	281.9	303.2	329.2	359.2	398.7	448.5	512.4
132.5°	252.7	255.7	263.4	274.8	291.3	312.0	337.4	366.8	402.5	447.8	504.2
135°	263.7	266.9	275.6	287.4	304.0	325.3	349.7	376.6	408.2	446.9	493.4
137.5°	274.1	277.4	286.0	298.6	315.0	334.8	358.3	383.8	412.0	445.1	484.1
140°	281.0	285.0	293.0	305.6	321.3	341.0	364.0	387.7	414.5	444.5	478.5
142.5°	288.6	292.0	300.5	311.8	327.7	346.1	368.4	391.4	416.4	443.2	473.4
145°	300.8	303.2	310.3	322.1	335.6	353.8	374.3	395.6	417.7	441.3	466.7
147.5°	313.2	314.6	321.5	331.7	344.7	360.2	379.0	398.1	417.7	438.4	460.0
150°	321.3	322.1	328.4	338.7	349.7	364.0	382.1	398.7	417.7	435.9	455.6
152.5°	329.5	329.7	336.0	345.1	354.8	368.4	384.1	400.0	415.8	432.6	450.5
155°	341.8	341.8	346.6	354.5	363.1	374.3	387.7	400.3	413.7	427.2	442.9
157.5°	351.6	352.2	356.1	363.0	370.4	379.0	389.7	401.1	411.0	422.2	434.4
160°	359.2	359.2	362.4	368.7	374.3	382.1	391.6	401.1	409.8	418.5	428.7
162.5°	365.0	365.0	367.5	372.5	377.4	384.1	392.2	400.4	407.3	414.7	423.0
165°	373.4	372.6	374.3	378.2	381.3	386.9	393.1	398.7	403.4	409.0	415.3
167.5°	379.9	379.0	379.8	382.7	385.0	388.5	393.0	397.5	399.7	403.3	407.9
170°	383.7	382.1	382.9	385.3	386.9	388.5	392.4	395.6	397.2	399.5	403.4
172.5°	386.3	385.3	385.5	387.2	388.1	389.1	392.4	395.0	395.3	396.4	399.0
175°	389.2	388.5	387.7	389.2	389.2	390.0	391.6	393.1	392.4	392.4	393.9
177.5°	390.6	390.0	389.4	390.0	390.0	390.0	390.6	391.9	390.6	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332347-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	17.8	17.7	17.6	17.7	17.3	17.2	17.1	16.7
90°	19.7	20.5	21.3	22.9	22.1	22.9	23.7	22.9
92.5°	66.4	52.7	46.6	42.5	41.1	38.7	39.5	38.1
95°	284.3	192.7	150.8	122.4	107.3	100.3	94.7	91.6
97.5°	708.5	567.5	465.6	371.2	313.0	277.4	256.1	249.3
100°	930.9	866.9	774.6	662.4	582.7	525.0	494.2	495.0
102.5°	1004.7	1002.7	948.9	877.8	815.8	770.1	744.4	726.2
105°	1026.4	1105.3	1120.3	1099.8	1063.5	1033.5	1008.2	1004.3
107.5°	964.2	1092.4	1161.5	1189.6	1190.3	1180.2	1171.6	1164.4
110°	904.8	1050.1	1149.5	1204.9	1226.9	1233.2	1231.6	1230.1





TEST NUMBER: P332347-840

CATALOG NUMBER: S123RDIP-S1000D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	846.1	994.5	1106.0	1177.0	1217.5	1237.1	1243.0	1243.3
115°	768.2	905.5	1021.7	1107.7	1166.9	1201.6	1217.5	1221.4
117.5°	711.9	830.4	934.6	1022.0	1083.7	1123.5	1146.2	1151.7
120°	682.2	788.7	883.5	963.2	1025.6	1069.9	1088.7	1093.5
122.5°	658.8	755.3	843.0	917.2	972.5	1012.3	1033.2	1039.2
125°	627.6	713.8	789.5	852.7	903.2	938.0	957.7	963.2
127.5°	600.6	677.2	745.7	803.1	848.1	877.8	895.6	900.7
130°	583.5	654.5	718.5	772.1	814.1	842.4	859.0	865.4
132.5°	567.6	633.1	692.6	743.8	783.0	811.5	826.2	830.6
135°	546.3	602.4	653.7	698.7	737.4	761.1	775.3	780.8
137.5°	526.9	572.9	617.1	656.1	688.6	712.7	724.7	728.3
140°	515.5	555.8	593.7	627.6	657.7	679.7	692.5	691.7
142.5°	504.8	539.4	572.3	601.8	627.3	646.9	658.3	657.5
145°	491.9	518.0	543.2	566.1	585.8	602.4	608.7	610.3
147.5°	481.3	502.0	522.4	538.7	553.6	564.8	570.9	571.5
150°	473.7	491.9	508.5	523.4	535.3	544.0	548.8	548.8
152.5°	466.8	482.4	497.1	509.6	518.9	526.9	529.8	529.8
155°	456.4	469.0	480.8	490.3	497.4	503.7	505.3	506.0
157.5°	445.2	455.9	465.0	472.4	478.6	483.3	484.6	484.4
160°	439.0	447.7	455.6	461.1	466.7	471.3	471.3	470.6
162.5°	431.4	438.8	446.1	451.0	454.6	458.7	458.7	458.0
165°	421.6	426.4	431.9	435.9	439.0	442.1	441.3	441.3
167.5°	413.0	416.7	419.9	422.7	424.1	426.4	425.6	425.6
170°	407.4	409.8	412.9	414.5	415.3	416.9	416.1	416.1
172.5°	402.3	404.0	406.6	407.6	407.7	409.3	407.9	407.3
175°	395.6	396.4	397.9	397.9	397.9	398.7	397.9	397.2
177.5°	391.3	391.9	392.5	392.5	391.9	392.5	391.3	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0

(END OF REPORT)