

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332379-840

Luminaire Tested: **S123RDIP-S1165D1025U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332379-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8175.8 lumens  
Efficiency: N/A  
Efficacy: 122.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	92	84	79	74	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	67	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	30	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	28	25	22	20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	24	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19957	19957	19957	19957
5°	23791	20042	17650	20042
10°	29704	19928	15946	19928
15°	34867	19724	14540	19724
20°	38913	19420	13347	19420
25°	38292	19099	12613	19099
30°	27524	18804	11857	18804
35°	18378	18419	11369	18419
40°	13540	17956	10863	17956
45°	11357	17145	10368	17145
50°	10021	16083	9676	16083
55°	8788	14865	8728	14865
60°	7828	13702	7995	13702
65°	6872	12455	7440	12455
70°	5397	11339	6795	11339
75°	4754	9902	6209	9902
80°	4135	8412	6106	8412
85°	3335	6756	6472	6756



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.3	2.2
10°-20°	569.6	7.0
20°-30°	894.9	10.9
30°-40°	933.7	11.4
40°-50°	799.0	9.8
50°-60°	609.0	7.4
60°-70°	390.4	4.8
70°-80°	187.8	2.3
80°-90°	53.5	0.7
90°-100°	83.6	1.0
100°-110°	250.2	3.1
110°-120°	425.6	5.2
120°-130°	559.8	6.8
130°-140°	629.2	7.7
140°-150°	618.5	7.6
150°-160°	520.7	6.4
160°-170°	346.6	4.2
170°-180°	121.4	1.5
0°-30°	1646.9	20.1
0°-40°	2580.6	31.6
0°-60°	3988.6	48.8
0°-90°	4620.3	56.5
90°-120°	759.4	9.3
90°-150°	2566.9	31.4
90°-180°	3555.0	43.5
0°-180°	8175.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1854	1854	1854	1854	1854	
5°	2202	1855	1634	1855	2202	227
15°	3129	1770	1305	1770	3129	887
25°	3224	1608	1062	1608	3224	1386
35°	1399	1402	865	1402	1399	917
45°	746	1126	681	1126	746	587
55°	468	792	465	792	468	423
65°	270	489	292	489	270	265
75°	114	238	149	238	114	123
85°	27	55	52	55	27	32
90°	30	1	30	1	30	16
95°	79	60	79	60	79	81
105°	240	227	240	227	240	255
115°	429	428	429	428	429	425
125°	620	627	620	627	620	554
135°	812	814	812	814	812	625
145°	987	987	987	987	987	616
155°	1128	1130	1128	1130	1128	519
165°	1227	1231	1227	1231	1227	346
175°	1275	1280	1275	1280	1275	121
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1974.8	1977.3	1969.0	1967.8	1958.2	1955.7	1955.7	1942.4	1934.1	1923.4	1917.0
5°	2201.8	2214.5	2208.2	2193.8	2170.0	2164.4	2149.4	2125.6	2098.6	2065.3	2049.4
7.5°	2485.3	2502.6	2496.0	2473.9	2448.9	2428.8	2386.2	2346.7	2291.3	2242.7	2201.1
10°	2717.7	2699.5	2685.1	2663.7	2640.7	2603.4	2559.0	2497.8	2427.2	2371.7	2309.8
12.5°	2891.6	2888.7	2870.5	2848.5	2816.0	2780.6	2725.9	2651.5	2569.4	2489.1	2418.3
15°	3128.9	3133.6	3121.7	3098.7	3052.6	2989.9	2907.4	2876.5	2759.0	2671.7	2584.3
17.5°	3293.0	3292.1	3290.4	3258.5	3211.6	3166.9	3090.4	3009.0	2902.7	2779.7	2662.0
20°	3397.1	3389.2	3390.8	3355.1	3320.1	3268.5	3193.9	3075.6	2988.4	2846.3	2724.8
22.5°	3394.6	3393.0	3399.0	3386.8	3361.4	3321.8	3263.2	3163.3	3051.9	2908.5	2771.9
25°	3224.1	3217.7	3255.1	3265.4	3305.9	3313.0	3295.5	3240.8	3135.2	2987.6	2818.5
27.5°	2698.4	2694.8	2764.1	2850.7	2960.6	3046.0	3128.6	3168.4	3135.2	3029.5	2860.1
30°	2214.5	2289.1	2324.0	2449.4	2589.1	2755.8	2901.8	3040.7	3074.8	3028.9	2889.9
32.5°	1838.6	1903.7	1932.9	2040.5	2170.7	2365.9	2585.0	2781.7	2920.6	2955.8	2872.2
35°	1398.6	1399.4	1466.0	1513.6	1634.3	1835.1	2047.8	2311.3	2573.2	2771.7	2792.3
37.5°	1116.0	1119.9	1160.2	1207.7	1298.2	1404.4	1591.7	1810.8	2113.3	2418.0	2596.6
40°	963.6	970.7	1000.9	1047.7	1112.8	1193.0	1339.0	1545.4	1797.8	2136.7	2413.7
42.5°	865.8	877.4	892.9	929.0	969.3	1044.4	1162.5	1321.9	1551.5	1871.9	2191.5
45°	746.1	752.5	764.4	781.0	817.5	869.9	949.3	1056.4	1247.0	1504.9	1824.7
47.5°	658.1	654.8	667.3	680.9	705.2	740.8	794.1	881.5	1017.4	1224.4	1495.7
50°	598.4	597.6	606.4	616.7	639.7	665.9	709.6	775.5	883.4	1054.9	1303.3
52.5°	542.6	545.6	551.8	564.6	581.3	602.5	641.7	689.1	781.8	929.8	1136.9
55°	468.3	470.7	479.4	486.6	498.5	519.9	544.5	584.2	647.7	750.8	921.5
57.5°	405.5	404.3	412.7	414.4	428.0	445.5	464.4	495.2	541.3	618.0	733.0
60°	363.6	361.1	368.3	373.9	381.0	395.3	411.1	441.3	477.9	534.2	632.6
62.5°	325.4	324.3	329.5	335.1	341.0	354.0	367.3	390.5	419.4	466.9	544.9
65°	269.8	272.3	274.6	277.0	280.1	288.1	300.8	316.7	336.6	369.9	426.3
67.5°	212.1	214.5	215.3	220.2	227.0	232.0	239.7	253.9	267.6	295.8	327.8
70°	171.5	170.7	171.5	173.8	182.6	191.3	201.6	212.0	220.7	240.4	267.5
72.5°	147.3	145.9	147.9	148.5	152.7	155.1	161.6	171.3	182.6	196.0	215.4
75°	114.3	114.3	114.3	114.3	117.4	119.1	121.5	123.8	127.7	134.1	148.5
77.5°	84.4	84.6	85.7	86.5	87.2	88.1	89.6	91.9	93.3	96.6	102.9
80°	66.7	67.5	66.7	67.5	67.5	69.1	69.9	72.2	73.0	77.0	79.4
82.5°	50.2	49.7	50.2	51.0	51.0	52.5	52.7	54.4	54.6	56.7	59.1
85°	27.0	25.4	27.0	26.2	27.8	26.2	27.0	28.6	28.6	29.4	32.5
87.5°	12.4	13.5	12.2	12.7	12.7	13.1	13.0	12.8	13.9	13.1	13.1
90°	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0	25.0	24.2	21.3
92.5°	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2	39.4	38.7	37.1
95°	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3	75.5	74.6	72.8
97.5°	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8	117.8	116.7	115.4
100°	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6	148.9	148.1	147.0
102.5°	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0	184.3	183.7	182.2
105°	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9	237.9	237.9	235.9
107.5°	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2	294.5	293.8	293.0
110°	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5	332.5	331.6	331.2



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7	370.6	369.5	369.5
115°	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9	429.7	429.4	429.9
117.5°	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6	488.7	488.7	489.3
120°	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8	528.0	528.3	529.4
122.5°	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3	567.9	568.6	569.2
125°	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2	627.1	628.0	628.4
127.5°	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4	685.6	686.9	687.4
130°	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0	723.9	724.8	725.5
132.5°	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5	761.6	762.7	763.2
135°	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8	817.7	818.5	818.8
137.5°	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7	872.6	873.5	873.0
140°	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8	908.1	908.3	908.1
142.5°	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7	941.9	942.1	941.7
145°	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5	991.7	991.9	991.3
147.5°	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5	1067.5	1067.5	1067.1
152.5°	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1	1093.7	1093.4	1093.1
155°	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9	1132.0	1131.0	1130.8
157.5°	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2	1165.3	1164.3	1164.2
160°	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7	1185.6	1184.5	1184.5
162.5°	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1	1205.0	1203.9	1203.7
165°	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5	1229.1	1227.8	1227.8
167.5°	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6	1247.4
170°	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1	1258.1
172.5°	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7	1268.3	1266.9	1266.9
175°	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9	1277.6	1276.2	1276.2
177.5°	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0	1281.9	1280.8	1280.8
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1914.5	1912.6	1903.7	1893.5	1880.2	1871.3	1864.3	1860.5	1849.1	1835.1	1825.5
5°	2032.8	2008.9	1983.5	1952.6	1924.0	1894.6	1876.3	1854.9	1828.8	1799.4	1778.8
7.5°	2159.4	2112.7	2062.4	2010.5	1959.2	1913.2	1872.6	1837.8	1796.0	1753.9	1724.4
10°	2256.5	2188.3	2117.7	2045.4	1979.5	1917.6	1870.0	1823.2	1773.2	1724.7	1688.3
12.5°	2344.8	2254.9	2173.5	2084.8	2000.5	1926.5	1857.9	1802.8	1742.7	1691.1	1649.5
15°	2456.6	2364.5	2266.0	2131.1	2019.2	1925.6	1842.2	1770.0	1697.0	1633.5	1593.0
17.5°	2561.0	2422.5	2290.2	2177.7	2032.3	1915.2	1813.5	1727.2	1647.0	1579.6	1529.8
20°	2604.2	2470.0	2326.4	2182.7	2039.8	1908.9	1790.6	1695.4	1612.0	1535.8	1489.9
22.5°	2630.2	2478.3	2327.0	2172.6	2020.8	1884.8	1767.8	1663.0	1572.7	1500.3	1443.5
25°	2660.6	2479.6	2312.9	2160.5	2005.7	1858.2	1719.2	1608.1	1510.5	1433.5	1373.1
27.5°	2680.6	2467.7	2270.7	2101.3	1944.3	1797.3	1670.0	1552.2	1453.2	1371.7	1307.0
30°	2684.3	2458.1	2238.3	2055.0	1895.4	1760.5	1625.6	1512.9	1408.1	1321.5	1261.2
32.5°	2689.5	2434.7	2194.4	1999.7	1836.3	1702.7	1580.4	1472.8	1365.5	1280.3	1218.7
35°	2668.5	2421.7	2128.0	1904.1	1740.6	1611.2	1501.0	1401.7	1296.2	1213.6	1150.9
37.5°	2578.3	2370.1	2059.1	1796.5	1625.6	1505.7	1415.8	1329.3	1232.5	1143.5	1084.4
40°	2487.5	2319.3	2005.7	1731.1	1552.6	1429.5	1348.6	1277.9	1184.3	1100.9	1037.4
42.5°	2352.3	2250.1	1954.9	1662.5	1470.0	1351.4	1283.1	1216.9	1134.7	1050.1	990.4
45°	2104.2	2117.7	1851.0	1553.3	1355.6	1236.6	1172.4	1126.3	1053.3	983.4	922.3
47.5°	1793.0	1919.2	1728.9	1436.9	1235.2	1123.5	1067.2	1027.0	977.9	909.3	853.5
50°	1589.8	1770.0	1631.1	1358.9	1159.6	1048.5	992.9	960.4	917.6	863.5	810.4
52.5°	1402.5	1596.0	1513.0	1271.8	1077.7	976.1	921.8	895.0	861.0	810.2	762.1
55°	1143.8	1339.8	1320.8	1140.5	954.8	863.5	822.3	792.1	769.1	731.0	693.0
57.5°	925.1	1111.1	1120.8	994.5	846.6	756.4	720.8	698.1	683.1	654.4	619.1
60°	787.4	958.1	991.4	896.2	769.1	689.7	654.8	636.5	624.7	601.7	574.6
62.5°	673.1	818.3	856.1	787.5	694.8	620.6	593.2	575.6	567.5	547.6	523.8
65°	515.1	635.8	672.3	634.2	585.7	526.2	504.0	489.0	481.8	470.7	453.2
67.5°	387.4	475.2	515.3	488.5	471.0	433.3	419.2	411.1	404.8	397.2	382.5
70°	311.1	376.2	417.5	410.3	396.1	376.2	365.9	360.3	354.0	347.7	335.0
72.5°	250.1	295.0	333.7	337.3	325.6	321.6	312.6	310.2	306.4	298.7	291.8
75°	165.9	196.8	223.8	234.2	238.9	242.9	238.9	238.1	237.3	231.0	227.0
77.5°	108.8	125.4	142.4	160.1	167.4	172.9	174.1	177.0	174.9	171.6	169.7
80°	83.3	87.4	99.2	114.3	126.2	131.0	134.1	135.7	134.9	134.1	131.0
82.5°	60.5	63.8	69.4	80.0	90.0	98.0	99.9	99.6	101.3	101.8	99.2
85°	32.5	33.3	34.9	36.6	42.1	50.8	53.2	54.7	56.4	56.4	51.6
87.5°	13.8	12.6	13.3	12.8	14.2	14.4	17.8	20.5	21.6	19.5	20.0
90°	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0	3.2	5.5	7.8
92.5°	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4	26.0	27.5	29.0
95°	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5	61.0	62.6	64.2
97.5°	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6	106.8	108.0	109.2
100°	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1	138.5	139.8	141.1
102.5°	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4	174.2	175.0	175.8
105°	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8	227.2	227.7	228.1
107.5°	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9	289.2	289.4	289.7
110°	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6	328.1	328.5	328.9





TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9	368.2	368.5	368.7
115°	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4	429.1	429.8	430.4
117.5°	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3	489.8	490.2	490.7
120°	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3	528.6	529.9	531.3
122.5°	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7	567.7	568.7	569.7
125°	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0	627.7	628.3	629.0
127.5°	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7	684.1	685.5	686.9
130°	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7	721.5	723.4	725.1
132.5°	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9	758.6	760.4	762.2
135°	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5	814.9	816.2	817.5
137.5°	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0	867.1	868.2	869.3
140°	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2	903.3	904.4	905.5
142.5°	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2	936.3	937.6	938.7
145°	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8	987.3	987.7	988.3
147.5°	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1	1032.9	1033.7	1034.5
150°	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5	1064.0	1064.4	1064.8
152.5°	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3	1089.9	1090.6	1091.2
155°	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7	1164.5	1164.2	1163.9
160°	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5	1186.0	1185.6	1185.2
162.5°	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9	1205.2	1204.6	1204.0
165°	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8	1230.1	1229.5	1228.8
167.5°	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8	1249.9	1249.0	1248.1
170°	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1	1261.2	1260.3	1259.4
172.5°	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9	1270.1	1269.2	1268.3
175°	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2	1279.3	1278.4	1277.6
177.5°	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0	1283.3	1282.6	1281.9
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1822.4	1814.1	1808.5	1795.7	1787.5	1778.6	1769.7	1775.4	1774.7	1774.1	1774.1
5°	1761.3	1743.0	1726.4	1705.0	1691.4	1674.8	1662.0	1660.4	1663.7	1652.5	1646.2
7.5°	1700.6	1675.7	1652.0	1628.4	1603.4	1583.4	1570.7	1564.9	1556.8	1549.9	1542.9
10°	1658.1	1628.7	1605.7	1576.3	1549.3	1525.5	1510.5	1500.2	1494.6	1489.0	1478.7
12.5°	1614.3	1585.6	1556.2	1523.0	1497.3	1469.7	1458.3	1446.8	1436.1	1430.0	1415.8
15°	1550.1	1512.9	1481.9	1446.9	1418.4	1391.4	1375.5	1352.5	1349.3	1341.4	1327.1
17.5°	1485.8	1445.3	1402.7	1376.7	1344.5	1316.5	1292.3	1284.5	1261.8	1253.2	1240.9
20°	1435.0	1397.8	1365.2	1331.1	1284.2	1258.1	1239.0	1228.7	1210.4	1199.3	1191.3
22.5°	1391.2	1353.3	1315.7	1275.9	1237.3	1207.9	1194.0	1177.9	1167.9	1152.4	1143.8
25°	1328.7	1287.4	1242.1	1199.3	1171.5	1149.3	1127.1	1112.8	1098.5	1091.4	1075.5
27.5°	1256.0	1212.8	1170.5	1138.0	1103.9	1082.0	1061.9	1049.1	1032.0	1020.0	1011.2
30°	1216.0	1165.2	1128.6	1099.3	1055.6	1035.0	1020.0	1004.1	991.4	978.7	970.0
32.5°	1169.6	1123.3	1088.6	1052.3	1018.9	996.2	976.7	962.8	952.0	939.9	931.2
35°	1096.9	1058.0	1022.3	985.8	961.2	938.2	915.1	903.2	892.9	881.8	873.9
37.5°	1031.2	994.8	960.9	926.2	895.8	877.1	858.5	849.4	835.5	828.0	819.9
40°	990.6	954.8	918.4	885.0	853.2	839.0	822.3	808.8	796.1	790.5	781.8
42.5°	946.1	910.4	879.6	843.7	817.7	798.3	782.9	768.2	758.6	750.5	745.6
45°	880.2	848.5	818.3	782.6	758.0	741.3	723.9	710.3	701.7	696.1	687.3
47.5°	816.3	784.6	753.9	722.8	698.9	679.9	662.5	653.1	641.5	634.7	628.7
50°	769.9	741.3	708.8	680.2	656.4	637.3	623.1	611.2	600.9	592.1	588.1
52.5°	727.4	696.9	668.8	642.1	617.0	595.4	582.4	569.9	562.1	552.1	547.5
55°	657.2	627.8	604.0	577.8	553.2	534.9	519.1	508.0	500.1	489.0	482.6
57.5°	591.3	565.0	536.5	513.8	488.5	473.0	459.9	444.8	435.2	426.4	420.2
60°	546.8	516.7	492.1	470.7	448.5	428.6	416.7	404.8	394.5	385.8	380.2
62.5°	500.5	474.1	450.8	427.5	407.2	389.9	376.1	366.1	357.0	351.4	345.9
65°	429.4	408.8	385.0	365.9	346.9	334.2	323.1	314.3	308.0	304.0	299.2
67.5°	364.0	344.0	323.2	304.5	291.8	282.1	274.8	267.3	264.2	259.0	255.9
70°	321.4	300.8	282.6	268.3	255.6	248.4	243.7	238.1	234.9	228.6	225.4
72.5°	275.1	260.1	247.0	235.3	225.1	218.6	212.6	205.7	200.7	193.7	190.5
75°	216.7	203.2	192.9	184.9	178.5	169.9	161.2	154.0	151.6	149.3	148.5
77.5°	160.5	151.9	144.4	137.7	129.9	123.5	121.6	120.0	119.6	118.3	118.3
80°	126.2	118.3	112.7	104.7	100.0	100.0	100.0	98.5	99.2	99.2	99.2
82.5°	93.8	86.5	83.5	80.7	79.7	80.3	80.3	80.7	80.2	81.4	80.8
85°	48.4	49.2	50.8	50.0	50.8	50.8	52.4	51.6	52.4	50.8	52.4
87.5°	19.8	22.2	23.4	24.6	25.9	25.8	26.6	26.8	27.6	27.8	27.9
90°	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0	26.9	27.8	28.5
92.5°	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2	40.9	41.6	41.8
95°	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3	77.3	78.2	78.7
97.5°	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8	119.9	120.9	121.3
100°	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6	150.2	150.9	151.5
102.5°	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0	185.7	186.3	186.6
105°	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9	237.9	237.9	238.1
107.5°	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2	295.9	296.6	296.8
110°	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5	334.4	335.3	335.5



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7	372.7	373.9	374.4
115°	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9	430.1	430.3	430.3
117.5°	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6	488.6	488.6	488.2
120°	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8	527.6	527.4	526.9
122.5°	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3	566.8	566.2	565.6
125°	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2	625.3	624.4	623.5
127.5°	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4	683.2	681.9	680.8
130°	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0	722.1	721.2	719.9
132.5°	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5	759.5	758.4	757.3
135°	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8	815.9	815.0	814.3
137.5°	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7	870.8	869.8	868.9
140°	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8	907.6	907.4	906.5
142.5°	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7	941.5	941.2	940.5
145°	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5	991.3	991.0	990.5
147.5°	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5	1067.5	1067.5	1066.8
152.5°	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1	1094.4	1094.8	1094.4
155°	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9	1133.8	1134.6	1134.3
157.5°	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2	1167.1	1168.1	1167.9
160°	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7	1187.8	1188.9	1189.0
162.5°	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1	1207.2	1208.3	1208.1
165°	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5	1231.8	1233.1	1233.0
167.5°	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1
170°	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4
172.5°	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7	1271.1	1272.4	1272.4
175°	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9	1280.2	1281.6	1281.4
177.5°	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0	1284.0	1285.2	1285.1
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1766.6	1765.8	1766.6	1763.9	1766.6	1765.8	1766.6	1774.1	1774.1	1774.7	1775.4
5°	1643.8	1643.1	1640.6	1633.5	1640.6	1643.1	1643.8	1646.2	1652.5	1663.7	1660.4
7.5°	1536.6	1535.5	1528.5	1528.7	1528.5	1535.5	1536.6	1542.9	1549.9	1556.8	1564.9
10°	1473.2	1473.9	1464.4	1458.9	1464.4	1473.9	1473.2	1478.7	1489.0	1494.6	1500.2
12.5°	1411.6	1408.0	1400.3	1394.1	1400.3	1408.0	1411.6	1415.8	1430.0	1436.1	1446.8
15°	1330.3	1322.3	1303.3	1304.8	1303.3	1322.3	1330.3	1327.1	1341.4	1349.3	1352.5
17.5°	1234.6	1228.7	1228.4	1217.3	1228.4	1228.7	1234.6	1240.9	1253.2	1261.8	1284.5
20°	1178.7	1174.7	1176.3	1165.2	1176.3	1174.7	1178.7	1191.3	1199.3	1210.4	1228.7
22.5°	1134.9	1130.8	1124.2	1120.7	1124.2	1130.8	1134.9	1143.8	1152.4	1167.9	1177.9
25°	1070.8	1064.4	1058.0	1062.0	1058.0	1064.4	1070.8	1075.5	1091.4	1098.5	1112.8
27.5°	1006.6	1001.9	995.5	994.7	995.5	1001.9	1006.6	1011.2	1020.0	1032.0	1049.1
30°	965.9	961.2	958.1	954.0	958.1	961.2	965.9	970.0	978.7	991.4	1004.1
32.5°	924.7	923.7	918.1	917.3	918.1	923.7	924.7	931.2	939.9	952.0	962.8
35°	870.7	866.0	864.3	865.2	864.3	866.0	870.7	873.9	881.8	892.9	903.2
37.5°	819.4	813.0	810.2	807.4	810.2	813.0	819.4	819.9	828.0	835.5	849.4
40°	782.6	776.3	774.7	773.1	774.7	776.3	782.6	781.8	790.5	796.1	808.8
42.5°	741.3	738.8	737.8	735.0	737.8	738.8	741.3	745.6	750.5	758.6	768.2
45°	685.0	684.2	679.4	681.1	679.4	684.2	685.0	687.3	696.1	701.7	710.3
47.5°	625.6	622.1	618.7	621.0	618.7	622.1	625.6	628.7	634.7	641.5	653.1
50°	585.0	583.4	576.2	577.8	576.2	583.4	585.0	588.1	592.1	600.9	611.2
52.5°	544.3	538.3	535.6	534.6	535.6	538.3	544.3	547.5	552.1	562.1	569.9
55°	477.1	469.9	466.7	465.1	466.7	469.9	477.1	482.6	489.0	500.1	508.0
57.5°	411.0	409.1	406.6	408.3	406.6	409.1	411.0	420.2	426.4	435.2	444.8
60°	372.2	372.2	372.2	371.4	372.2	372.2	372.2	380.2	385.8	394.5	404.8
62.5°	342.4	340.5	339.9	341.0	339.9	340.5	342.4	345.9	351.4	357.0	366.1
65°	296.9	296.1	292.9	292.1	292.9	296.1	296.9	299.2	304.0	308.0	314.3
67.5°	253.9	251.0	250.0	248.9	250.0	251.0	253.9	255.9	259.0	264.2	267.3
70°	221.5	219.8	215.1	215.9	215.1	219.8	221.5	225.4	228.6	234.9	238.1
72.5°	186.5	184.9	184.0	182.9	184.0	184.9	186.5	190.5	193.7	200.7	205.7
75°	147.6	146.8	146.0	149.3	146.0	146.8	147.6	148.5	149.3	151.6	154.0
77.5°	118.3	118.3	118.8	117.4	118.8	118.3	118.3	118.3	118.3	119.6	120.0
80°	99.2	99.2	98.5	98.5	98.5	99.2	99.2	99.2	99.2	99.2	98.5
82.5°	79.6	80.2	80.7	79.4	80.7	80.2	79.6	80.8	81.4	80.2	80.7
85°	52.4	51.6	53.2	52.4	53.2	51.6	52.4	52.4	50.8	52.4	51.6
87.5°	29.3	28.1	28.2	28.9	28.2	28.1	29.3	27.9	27.8	27.6	26.8
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0
92.5°	41.5	41.3	41.0	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2
95°	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3
97.5°	121.3	121.2	121.1	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8
100°	151.9	152.3	152.8	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6
102.5°	186.5	186.4	186.4	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0
105°	238.5	239.0	239.4	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9
107.5°	296.6	296.3	296.0	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2
110°	335.0	334.6	334.2	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	374.3	374.2	374.1	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7
115°	430.1	429.9	429.7	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9
117.5°	487.6	487.0	486.4	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6
120°	526.5	526.1	525.6	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8
122.5°	565.0	564.3	563.7	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3
125°	622.7	621.8	620.9	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2
127.5°	679.7	678.6	677.6	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4
130°	718.4	716.8	715.3	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0
132.5°	756.1	754.9	753.7	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5
135°	813.9	813.3	812.9	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8
137.5°	868.1	867.2	866.4	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7
140°	904.9	903.3	901.8	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8
142.5°	939.3	938.1	936.9	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7
145°	989.6	988.7	987.7	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5
147.5°	1036.5	1035.1	1033.8	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5
150°	1065.5	1064.2	1062.8	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5
152.5°	1093.2	1092.1	1090.9	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1
155°	1132.8	1131.1	1129.5	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9
157.5°	1166.7	1165.4	1164.2	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2
160°	1188.2	1187.3	1186.4	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7
162.5°	1206.7	1205.3	1203.9	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1
165°	1231.5	1229.9	1228.4	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5
167.5°	1251.7	1250.3	1249.0	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3
170°	1262.7	1261.2	1259.6	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2
172.5°	1270.8	1269.3	1267.7	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7
175°	1279.9	1278.3	1276.8	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9
177.5°	1283.8	1282.5	1281.3	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1769.7	1778.6	1787.5	1795.7	1808.5	1814.1	1822.4	1825.5	1835.1	1849.1	1860.5
5°	1662.0	1674.8	1691.4	1705.0	1726.4	1743.0	1761.3	1778.8	1799.4	1828.8	1854.9
7.5°	1570.7	1583.4	1603.4	1628.4	1652.0	1675.7	1700.6	1724.4	1753.9	1796.0	1837.8
10°	1510.5	1525.5	1549.3	1576.3	1605.7	1628.7	1658.1	1688.3	1724.7	1773.2	1823.2
12.5°	1458.3	1469.7	1497.3	1523.0	1556.2	1585.6	1614.3	1649.5	1691.1	1742.7	1802.8
15°	1375.5	1391.4	1418.4	1446.9	1481.9	1512.9	1550.1	1593.0	1633.5	1697.0	1770.0
17.5°	1292.3	1316.5	1344.5	1376.7	1402.7	1445.3	1485.8	1529.8	1579.6	1647.0	1727.2
20°	1239.0	1258.1	1284.2	1331.1	1365.2	1397.8	1435.0	1489.9	1535.8	1612.0	1695.4
22.5°	1194.0	1207.9	1237.3	1275.9	1315.7	1353.3	1391.2	1443.5	1500.3	1572.7	1663.0
25°	1127.1	1149.3	1171.5	1199.3	1242.1	1287.4	1328.7	1373.1	1433.5	1510.5	1608.1
27.5°	1061.9	1082.0	1103.9	1138.0	1170.5	1212.8	1256.0	1307.0	1371.7	1453.2	1552.2
30°	1020.0	1035.0	1055.6	1099.3	1128.6	1165.2	1216.0	1261.2	1321.5	1408.1	1512.9
32.5°	976.7	996.2	1018.9	1052.3	1088.6	1123.3	1169.6	1218.7	1280.3	1365.5	1472.8
35°	915.1	938.2	961.2	985.8	1022.3	1058.0	1096.9	1150.9	1213.6	1296.2	1401.7
37.5°	858.5	877.1	895.8	926.2	960.9	994.8	1031.2	1084.4	1143.5	1232.5	1329.3
40°	822.3	839.0	853.2	885.0	918.4	954.8	990.6	1037.4	1100.9	1184.3	1277.9
42.5°	782.9	798.3	817.7	843.7	879.6	910.4	946.1	990.4	1050.1	1134.7	1216.9
45°	723.9	741.3	758.0	782.6	818.3	848.5	880.2	922.3	983.4	1053.3	1126.3
47.5°	662.5	679.9	698.9	722.8	753.9	784.6	816.3	853.5	909.3	977.9	1027.0
50°	623.1	637.3	656.4	680.2	708.8	741.3	769.9	810.4	863.5	917.6	960.4
52.5°	582.4	595.4	617.0	642.1	668.8	696.9	727.4	762.1	810.2	861.0	895.0
55°	519.1	534.9	553.2	577.8	604.0	627.8	657.2	693.0	731.0	769.1	792.1
57.5°	459.9	473.0	488.5	513.8	536.5	565.0	591.3	619.1	654.4	683.1	698.1
60°	416.7	428.6	448.5	470.7	492.1	516.7	546.8	574.6	601.7	624.7	636.5
62.5°	376.1	389.9	407.2	427.5	450.8	474.1	500.5	523.8	547.6	567.5	575.6
65°	323.1	334.2	346.9	365.9	385.0	408.8	429.4	453.2	470.7	481.8	489.0
67.5°	274.8	282.1	291.8	304.5	323.2	344.0	364.0	382.5	397.2	404.8	411.1
70°	243.7	248.4	255.6	268.3	282.6	300.8	321.4	335.0	347.7	354.0	360.3
72.5°	212.6	218.6	225.1	235.3	247.0	260.1	275.1	291.8	298.7	306.4	310.2
75°	161.2	169.9	178.5	184.9	192.9	203.2	216.7	227.0	231.0	237.3	238.1
77.5°	121.6	123.5	129.9	137.7	144.4	151.9	160.5	169.7	171.6	174.9	177.0
80°	100.0	100.0	100.0	104.7	112.7	118.3	126.2	131.0	134.1	134.9	135.7
82.5°	80.3	80.3	79.7	80.7	83.5	86.5	93.8	99.2	101.8	101.3	99.6
85°	52.4	50.8	50.8	50.0	50.8	49.2	48.4	51.6	56.4	56.4	54.7
87.5°	26.6	25.8	25.9	24.6	23.4	22.2	19.8	20.0	19.5	21.6	20.5
90°	25.0	24.2	21.3	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0
92.5°	39.4	38.7	37.1	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4
95°	75.5	74.6	72.8	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5
97.5°	117.8	116.7	115.4	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6
100°	148.9	148.1	147.0	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1
102.5°	184.3	183.7	182.2	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4
105°	237.9	237.9	235.9	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8
107.5°	294.5	293.8	293.0	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9
110°	332.5	331.6	331.2	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	370.6	369.5	369.5	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9
115°	429.7	429.4	429.9	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4
117.5°	488.7	488.7	489.3	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3
120°	528.0	528.3	529.4	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3
122.5°	567.9	568.6	569.2	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7
125°	627.1	628.0	628.4	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0
127.5°	685.6	686.9	687.4	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7
130°	723.9	724.8	725.5	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7
132.5°	761.6	762.7	763.2	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9
135°	817.7	818.5	818.8	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5
137.5°	872.6	873.5	873.0	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0
140°	908.1	908.3	908.1	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2
142.5°	941.9	942.1	941.7	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2
145°	991.7	991.9	991.3	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8
147.5°	1038.5	1038.5	1037.8	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1
150°	1067.5	1067.5	1067.1	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5
152.5°	1093.7	1093.4	1093.1	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3
155°	1132.0	1131.0	1130.8	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1165.3	1164.3	1164.2	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7
160°	1185.6	1184.5	1184.5	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5
162.5°	1205.0	1203.9	1203.7	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9
165°	1229.1	1227.8	1227.8	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8
167.5°	1249.0	1247.6	1247.4	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8
170°	1259.6	1258.1	1258.1	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1
172.5°	1268.3	1266.9	1266.9	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9
175°	1277.6	1276.2	1276.2	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2
177.5°	1281.9	1280.8	1280.8	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1864.3	1871.3	1880.2	1893.5	1903.7	1912.6	1914.5	1917.0	1923.4	1934.1	1942.4
5°	1876.3	1894.6	1924.0	1952.6	1983.5	2008.9	2032.8	2049.4	2065.3	2098.6	2125.6
7.5°	1872.6	1913.2	1959.2	2010.5	2062.4	2112.7	2159.4	2201.1	2242.7	2291.3	2346.7
10°	1870.0	1917.6	1979.5	2045.4	2117.7	2188.3	2256.5	2309.8	2371.7	2427.2	2497.8
12.5°	1857.9	1926.5	2000.5	2084.8	2173.5	2254.9	2344.8	2418.3	2489.1	2569.4	2651.5
15°	1842.2	1925.6	2019.2	2131.1	2266.0	2364.5	2456.6	2584.3	2671.7	2759.0	2876.5
17.5°	1813.5	1915.2	2032.3	2177.7	2290.2	2422.5	2561.0	2662.0	2779.7	2902.7	3009.0
20°	1790.6	1908.9	2039.8	2182.7	2326.4	2470.0	2604.2	2724.8	2846.3	2988.4	3075.6
22.5°	1767.8	1884.8	2020.8	2172.6	2327.0	2478.3	2630.2	2771.9	2908.5	3051.9	3163.3
25°	1719.2	1858.2	2005.7	2160.5	2312.9	2479.6	2660.6	2818.5	2987.6	3135.2	3240.8
27.5°	1670.0	1797.3	1944.3	2101.3	2270.7	2467.7	2680.6	2860.1	3029.5	3135.2	3168.4
30°	1625.6	1760.5	1895.4	2055.0	2238.3	2458.1	2684.3	2889.9	3028.9	3074.8	3040.7
32.5°	1580.4	1702.7	1836.3	1999.7	2194.4	2434.7	2689.5	2872.2	2955.8	2920.6	2781.7
35°	1501.0	1611.2	1740.6	1904.1	2128.0	2421.7	2668.5	2792.3	2771.7	2573.2	2311.3
37.5°	1415.8	1505.7	1625.6	1796.5	2059.1	2370.1	2578.3	2596.6	2418.0	2113.3	1810.8
40°	1348.6	1429.5	1552.6	1731.1	2005.7	2319.3	2487.5	2413.7	2136.7	1797.8	1545.4
42.5°	1283.1	1351.4	1470.0	1662.5	1954.9	2250.1	2352.3	2191.5	1871.9	1551.5	1321.9
45°	1172.4	1236.6	1355.6	1553.3	1851.0	2117.7	2104.2	1824.7	1504.9	1247.0	1056.4
47.5°	1067.2	1123.5	1235.2	1436.9	1728.9	1919.2	1793.0	1495.7	1224.4	1017.4	881.5
50°	992.9	1048.5	1159.6	1358.9	1631.1	1770.0	1589.8	1303.3	1054.9	883.4	775.5
52.5°	921.8	976.1	1077.7	1271.8	1513.0	1596.0	1402.5	1136.9	929.8	781.8	689.1
55°	822.3	863.5	954.8	1140.5	1320.8	1339.8	1143.8	921.5	750.8	647.7	584.2
57.5°	720.8	756.4	846.6	994.5	1120.8	1111.1	925.1	733.0	618.0	541.3	495.2
60°	654.8	689.7	769.1	896.2	991.4	958.1	787.4	632.6	534.2	477.9	441.3
62.5°	593.2	620.6	694.8	787.5	856.1	818.3	673.1	544.9	466.9	419.4	390.5
65°	504.0	526.2	585.7	634.2	672.3	635.8	515.1	426.3	369.9	336.6	316.7
67.5°	419.2	433.3	471.0	488.5	515.3	475.2	387.4	327.8	295.8	267.6	253.9
70°	365.9	376.2	396.1	410.3	417.5	376.2	311.1	267.5	240.4	220.7	212.0
72.5°	312.6	321.6	325.6	337.3	333.7	295.0	250.1	215.4	196.0	182.6	171.3
75°	238.9	242.9	238.9	234.2	223.8	196.8	165.9	148.5	134.1	127.7	123.8
77.5°	174.1	172.9	167.4	160.1	142.4	125.4	108.8	102.9	96.6	93.3	91.9
80°	134.1	131.0	126.2	114.3	99.2	87.4	83.3	79.4	77.0	73.0	72.2
82.5°	99.9	98.0	90.0	80.0	69.4	63.8	60.5	59.1	56.7	54.6	54.4
85°	53.2	50.8	42.1	36.6	34.9	33.3	32.5	32.5	29.4	28.6	28.6
87.5°	17.8	14.4	14.2	12.8	13.3	12.6	13.8	13.1	13.1	13.9	12.8
90°	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0
92.5°	26.0	27.5	29.0	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2
95°	61.0	62.6	64.2	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3
97.5°	106.8	108.0	109.2	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8
100°	138.5	139.8	141.1	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6
102.5°	174.2	175.0	175.8	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0
105°	227.2	227.7	228.1	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9
107.5°	289.2	289.4	289.7	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2
110°	328.1	328.5	328.9	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5





TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	368.2	368.5	368.7	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7
115°	429.1	429.8	430.4	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9
117.5°	489.8	490.2	490.7	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6
120°	528.6	529.9	531.3	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8
122.5°	567.7	568.7	569.7	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3
125°	627.7	628.3	629.0	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2
127.5°	684.1	685.5	686.9	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4
130°	721.5	723.4	725.1	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0
132.5°	758.6	760.4	762.2	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5
135°	814.9	816.2	817.5	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8
137.5°	867.1	868.2	869.3	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7
140°	903.3	904.4	905.5	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8
142.5°	936.3	937.6	938.7	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7
145°	987.3	987.7	988.3	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5
147.5°	1032.9	1033.7	1034.5	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5
150°	1064.0	1064.4	1064.8	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5
152.5°	1089.9	1090.6	1091.2	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1
155°	1130.0	1130.0	1130.0	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9
157.5°	1164.5	1164.2	1163.9	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2
160°	1186.0	1185.6	1185.2	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7
162.5°	1205.2	1204.6	1204.0	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1
165°	1230.1	1229.5	1228.8	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5
167.5°	1249.9	1249.0	1248.1	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3
170°	1261.2	1260.3	1259.4	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2
172.5°	1270.1	1269.2	1268.3	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7
175°	1279.3	1278.4	1277.6	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9
177.5°	1283.3	1282.6	1281.9	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1955.7	1955.7	1958.2	1967.8	1969.0	1977.3	1974.8
5°	2149.4	2164.4	2170.0	2193.8	2208.2	2214.5	2201.8
7.5°	2386.2	2428.8	2448.9	2473.9	2496.0	2502.6	2485.3
10°	2559.0	2603.4	2640.7	2663.7	2685.1	2699.5	2717.7
12.5°	2725.9	2780.6	2816.0	2848.5	2870.5	2888.7	2891.6
15°	2907.4	2989.9	3052.6	3098.7	3121.7	3133.6	3128.9
17.5°	3090.4	3166.9	3211.6	3258.5	3290.4	3292.1	3293.0
20°	3193.9	3268.5	3320.1	3355.1	3390.8	3389.2	3397.1
22.5°	3263.2	3321.8	3361.4	3386.8	3399.0	3393.0	3394.6
25°	3295.5	3313.0	3305.9	3265.4	3255.1	3217.7	3224.1
27.5°	3128.6	3046.0	2960.6	2850.7	2764.1	2694.8	2698.4
30°	2901.8	2755.8	2589.1	2449.4	2324.0	2289.1	2214.5
32.5°	2585.0	2365.9	2170.7	2040.5	1932.9	1903.7	1838.6
35°	2047.8	1835.1	1634.3	1513.6	1466.0	1399.4	1398.6
37.5°	1591.7	1404.4	1298.2	1207.7	1160.2	1119.9	1116.0
40°	1339.0	1193.0	1112.8	1047.7	1000.9	970.7	963.6
42.5°	1162.5	1044.4	969.3	929.0	892.9	877.4	865.8
45°	949.3	869.9	817.5	781.0	764.4	752.5	746.1
47.5°	794.1	740.8	705.2	680.9	667.3	654.8	658.1
50°	709.6	665.9	639.7	616.7	606.4	597.6	598.4
52.5°	641.7	602.5	581.3	564.6	551.8	545.6	542.6
55°	544.5	519.9	498.5	486.6	479.4	470.7	468.3
57.5°	464.4	445.5	428.0	414.4	412.7	404.3	405.5
60°	411.1	395.3	381.0	373.9	368.3	361.1	363.6
62.5°	367.3	354.0	341.0	335.1	329.5	324.3	325.4
65°	300.8	288.1	280.1	277.0	274.6	272.3	269.8
67.5°	239.7	232.0	227.0	220.2	215.3	214.5	212.1
70°	201.6	191.3	182.6	173.8	171.5	170.7	171.5
72.5°	161.6	155.1	152.7	148.5	147.9	145.9	147.3
75°	121.5	119.1	117.4	114.3	114.3	114.3	114.3
77.5°	89.6	88.1	87.2	86.5	85.7	84.6	84.4
80°	69.9	69.1	67.5	67.5	66.7	67.5	66.7
82.5°	52.7	52.5	51.0	51.0	50.2	49.7	50.2
85°	27.0	26.2	27.8	26.2	27.0	25.4	27.0
87.5°	13.0	13.1	12.7	12.7	12.2	13.5	12.4
90°	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	40.9	41.6	41.8	41.5	41.3	41.0	40.7
95°	77.3	78.2	78.7	78.7	78.7	78.7	78.7
97.5°	119.9	120.9	121.3	121.3	121.2	121.1	121.0
100°	150.2	150.9	151.5	151.9	152.3	152.8	153.2
102.5°	185.7	186.3	186.6	186.5	186.4	186.4	186.3
105°	237.9	237.9	238.1	238.5	239.0	239.4	239.9
107.5°	295.9	296.6	296.8	296.6	296.3	296.0	295.8
110°	334.4	335.3	335.5	335.0	334.6	334.2	333.7



TEST NUMBER: P332379-840

CATALOG NUMBER: S123RDIP-S1165D1025U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	372.7	373.9	374.4	374.3	374.2	374.1	374.0
115°	430.1	430.3	430.3	430.1	429.9	429.7	429.4
117.5°	488.6	488.6	488.2	487.6	487.0	486.4	485.6
120°	527.6	527.4	526.9	526.5	526.1	525.6	525.2
122.5°	566.8	566.2	565.6	565.0	564.3	563.7	563.1
125°	625.3	624.4	623.5	622.7	621.8	620.9	620.0
127.5°	683.2	681.9	680.8	679.7	678.6	677.6	676.6
130°	722.1	721.2	719.9	718.4	716.8	715.3	713.7
132.5°	759.5	758.4	757.3	756.1	754.9	753.7	752.5
135°	815.9	815.0	814.3	813.9	813.3	812.9	812.5
137.5°	870.8	869.8	868.9	868.1	867.2	866.4	865.6
140°	907.6	907.4	906.5	904.9	903.3	901.8	900.2
142.5°	941.5	941.2	940.5	939.3	938.1	936.9	935.6
145°	991.3	991.0	990.5	989.6	988.7	987.7	986.8
147.5°	1038.5	1038.5	1037.8	1036.5	1035.1	1033.8	1032.5
150°	1067.5	1067.5	1066.8	1065.5	1064.2	1062.8	1061.5
152.5°	1094.4	1094.8	1094.4	1093.2	1092.1	1090.9	1089.7
155°	1133.8	1134.6	1134.3	1132.8	1131.1	1129.5	1128.0
157.5°	1167.1	1168.1	1167.9	1166.7	1165.4	1164.2	1162.9
160°	1187.8	1188.9	1189.0	1188.2	1187.3	1186.4	1185.5
162.5°	1207.2	1208.3	1208.1	1206.7	1205.3	1203.9	1202.4
165°	1231.8	1233.1	1233.0	1231.5	1229.9	1228.4	1226.8
167.5°	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6
170°	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1
172.5°	1271.1	1272.4	1272.4	1270.8	1269.3	1267.7	1266.1
175°	1280.2	1281.6	1281.4	1279.9	1278.3	1276.8	1275.2
177.5°	1284.0	1285.2	1285.1	1283.8	1282.5	1281.3	1280.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2

(END OF REPORT)