

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332363-840

Luminaire Tested: **S123RDIP-S1165D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332363-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5887.8 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332363-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332363-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	92	99	95	92	88	86	84	81	78	76	74	71	69	68	64
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58	55
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47
4	80	69	61	55	76	66	59	53	60	55	50	55	50	47	51	47	43	41
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	42	38	35
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34	31
7	63	51	43	37	60	49	41	36	45	39	34	41	36	32	38	34	30	28
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	35	30	52	41	34	29	38	32	27	35	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332363-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	3.1
10°-20°	511.4	8.7
20°-30°	736.4	12.5
30°-40°	829.4	14.1
40°-50°	793.5	13.5
50°-60°	649.8	11.0
60°-70°	438.4	7.4
70°-80°	220.6	3.7
80°-90°	59.7	1.0
90°-100°	17.5	0.3
100°-110°	83.2	1.4
110°-120°	199.9	3.4
120°-130°	254.6	4.3
130°-140°	272.0	4.6
140°-150°	254.4	4.3
150°-160°	205.2	3.5
160°-170°	132.4	2.2
170°-180°	45.6	0.8
0°-30°	1431.6	24.3
0°-40°	2261.0	38.4
0°-60°	3704.3	62.9
0°-90°	4423.0	75.1
90°-120°	300.6	5.1
90°-150°	1081.5	18.4
90°-180°	1465.0	24.9
0°-180°	5887.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	0	4	9	10	11	5
95°	22	8	11	13	14	27
105°	106	108	78	18	16	113
115°	199	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	269
145°	404	406	407	408	408	253
155°	445	444	445	446	444	205
165°	469	468	468	470	468	133
175°	480	479	479	481	479	46
180°	480	480	480	480	480	



TEST NUMBER: P332363-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.6	27.6	24.6	21.7	18.8	17.4	17.6	17.8	18.0	18.2	18.0
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	6.7	6.5	6.2	6.0	5.8	6.1	6.8	7.6	8.4	9.1	9.6
95°	21.8	18.5	15.2	12.0	8.8	7.6	8.5	9.3	10.2	11.1	11.6
97.5°	43.7	42.3	40.8	39.4	37.9	34.3	28.6	22.9	17.2	11.5	12.1
100°	60.3	61.9	63.5	65.0	66.7	61.3	48.9	36.6	24.1	11.8	12.4
102.5°	79.2	80.3	81.4	82.6	83.7	77.6	64.0	50.5	37.0	23.5	21.5
105°	106.3	107.2	108.1	109.0	109.9	106.7	99.6	92.4	85.3	78.2	64.1
107.5°	135.0	135.7	136.4	137.1	137.8	138.8	139.9	141.0	142.1	143.2	132.9
110°	154.2	154.8	155.4	156.0	156.7	157.4	158.3	159.2	160.1	161.0	158.3



TEST NUMBER: P332363-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.4	173.0	173.6	174.1	174.7	175.4	176.3	177.2	178.0	178.9	178.9
115°	199.4	200.0	200.5	200.9	201.4	202.0	202.7	203.4	204.1	204.8	205.6
117.5°	225.7	226.3	226.8	227.4	228.0	228.5	228.8	229.2	229.6	229.9	230.6
120°	242.0	242.7	243.4	244.1	244.8	245.3	245.5	245.8	246.0	246.2	246.9
122.5°	258.5	259.1	259.6	260.2	260.8	261.3	261.6	261.9	262.2	262.5	263.0
125°	281.2	281.9	282.5	283.1	283.8	284.2	284.6	284.9	285.2	285.5	285.7
127.5°	303.2	303.9	304.5	305.1	305.7	306.2	306.6	307.0	307.4	307.7	308.0
130°	316.9	317.5	318.1	318.8	319.4	319.9	320.2	320.5	320.8	321.1	321.4
132.5°	330.0	330.6	331.3	331.9	332.5	333.0	333.3	333.6	333.8	334.1	334.4
135°	350.1	350.5	351.0	351.5	351.9	352.3	352.6	353.0	353.4	353.7	353.9
137.5°	367.2	367.8	368.4	369.0	369.6	370.0	370.2	370.3	370.5	370.7	371.1
140°	378.6	379.1	379.6	380.0	380.5	380.9	381.1	381.3	381.6	381.8	382.1
142.5°	389.2	389.7	390.1	390.6	391.1	391.4	391.7	391.9	392.1	392.4	392.6
145°	403.9	404.6	405.1	405.7	406.2	406.6	406.7	406.9	407.0	407.2	407.4
147.5°	417.9	418.3	418.6	419.0	419.3	419.6	419.8	419.9	420.1	420.2	420.4
150°	426.5	426.7	426.9	427.2	427.4	427.6	427.8	427.9	428.1	428.2	428.4
152.5°	434.1	434.2	434.3	434.4	434.5	434.7	434.7	434.8	434.9	435.0	435.4
155°	445.0	444.8	444.6	444.5	444.3	444.3	444.4	444.4	444.5	444.6	445.0
157.5°	453.4	453.4	453.4	453.3	453.3	453.3	453.2	453.1	453.0	453.0	453.4
160°	458.6	458.5	458.4	458.3	458.3	458.2	458.1	458.0	458.0	457.9	458.3
162.5°	463.4	463.2	463.0	462.8	462.6	462.4	462.3	462.3	462.2	462.1	462.6
165°	469.3	469.0	468.8	468.6	468.3	468.2	468.1	468.0	467.9	467.9	468.5
167.5°	473.8	473.5	473.2	472.9	472.5	472.4	472.4	472.4	472.4	472.4	473.0
170°	476.4	476.1	475.7	475.4	475.1	474.9	474.9	474.9	474.9	474.9	475.6
172.5°	478.1	477.8	477.4	477.0	476.6	476.5	476.5	476.6	476.7	476.7	477.4
175°	480.3	479.9	479.5	479.2	478.8	478.6	478.7	478.8	478.8	478.9	479.5
177.5°	480.9	480.6	480.3	480.0	479.6	479.5	479.6	479.6	479.7	479.8	480.3
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332363-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	17.8	17.6	17.4	17.1	16.9	16.6	16.4	16.2
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.2	10.7	11.2	11.5	11.5	11.6	11.7	11.8
95°	12.2	12.7	13.3	13.5	13.5	13.5	13.5	13.5
97.5°	12.7	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.6	14.7	14.8	14.9	14.9
102.5°	19.6	17.6	15.7	14.7	14.8	14.9	15.1	15.2
105°	50.1	36.1	22.0	15.0	15.2	15.3	15.6	15.7
107.5°	122.7	112.4	102.1	91.6	81.1	70.5	59.9	49.3
110°	155.7	153.1	150.5	143.5	132.2	120.8	109.5	98.2



TEST NUMBER: P332363-840

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	179.0	179.0	179.2	177.9	175.5	173.2	170.8	168.3
115°	206.4	207.2	208.0	208.5	208.8	209.2	209.5	209.8
117.5°	231.3	231.9	232.5	232.9	232.9	233.0	233.1	233.1
120°	247.5	248.1	248.7	249.1	249.1	249.1	249.1	249.1
122.5°	263.4	263.9	264.3	264.5	264.6	264.7	264.7	264.8
125°	285.8	286.0	286.1	286.3	286.4	286.6	286.8	286.9
127.5°	308.2	308.5	308.8	308.8	308.6	308.5	308.3	308.2
130°	321.8	322.1	322.4	322.6	322.3	322.2	322.0	321.8
132.5°	334.7	335.0	335.3	335.4	335.1	334.9	334.7	334.5
135°	354.2	354.4	354.6	354.6	354.4	354.2	353.9	353.7
137.5°	371.4	371.8	372.2	372.3	372.1	372.0	371.8	371.7
140°	382.4	382.7	383.1	383.1	383.0	382.8	382.7	382.5
142.5°	392.9	393.1	393.4	393.4	393.2	392.9	392.7	392.5
145°	407.5	407.7	407.8	407.9	407.9	407.9	407.9	407.9
147.5°	420.5	420.7	420.9	420.8	420.4	420.0	419.7	419.3
150°	428.6	428.7	428.9	428.8	428.6	428.4	428.1	427.9
152.5°	435.7	436.0	436.3	436.2	435.9	435.5	435.0	434.7
155°	445.5	445.9	446.3	446.2	445.8	445.2	444.7	444.2
157.5°	453.9	454.4	454.9	454.8	454.2	453.6	452.9	452.3
160°	458.8	459.3	459.8	459.7	459.2	458.6	458.1	457.5
162.5°	463.2	463.7	464.2	464.3	463.8	463.3	462.8	462.3
165°	469.1	469.8	470.4	470.4	469.9	469.3	468.8	468.2
167.5°	473.6	474.3	474.9	474.9	474.3	473.6	473.0	472.4
170°	476.3	476.9	477.5	477.5	476.9	476.3	475.6	474.9
172.5°	478.0	478.6	479.2	479.2	478.5	477.8	477.1	476.4
175°	480.0	480.6	481.1	481.1	480.5	479.8	479.2	478.6
177.5°	480.8	481.3	481.8	481.7	481.1	480.5	479.8	479.2
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

(END OF REPORT)