

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831962

Luminaire Tested: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831962  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D365U840-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6345.1 lumens  
Efficiency: N/A  
Efficacy: 121.6 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 52.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79				
1	106	102	98	95	101	97	94	91	89	87	85	82	80	78	75	74	72	69				
2	97	90	84	80	93	87	81	77	80	76	72	74	70	68	68	65	63	60				
3	90	81	74	68	86	78	71	66	72	67	63	66	62	59	61	58	55	53				
4	83	73	65	59	79	70	63	58	65	59	55	60	56	52	56	52	49	47				
5	77	66	58	52	74	64	56	51	59	53	49	55	50	46	51	47	44	42				
6	72	60	52	47	69	58	51	46	54	48	44	51	46	42	47	43	40	37				
7	67	55	47	42	64	53	46	41	50	44	39	47	42	38	44	39	36	34				
8	63	51	43	38	60	49	42	37	46	40	36	43	38	34	41	36	33	31				
9	59	47	40	35	56	46	39	34	43	37	33	40	35	32	38	34	30	29				
10	55	44	37	32	53	42	36	31	40	34	30	38	33	29	36	31	28	26				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	40739	40739	40739	40739	40739
5°	48372	46830	40995	33140	30767
10°	43827	47566	40791	26552	22778
15°	30175	40783	40360	21702	18018
20°	20992	31400	39550	18299	15837
25°	15997	23931	38371	16264	14596
30°	13926	19132	36896	15101	13520
35°	12786	16139	34807	14121	12540
40°	11665	14412	32073	13159	11643
45°	10535	13181	29125	12248	10749
50°	9562	12161	25648	11355	9640
55°	8649	11168	22308	10483	8270
60°	7750	10155	19375	9522	7817
65°	7154	9011	16677	8558	7391
70°	5813	7789	14552	7742	6008
75°	5099	6197	12327	6421	5290
80°	4618	5244	10098	5387	5002
85°	4211	4594	7669	4891	4594

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 30731 cd/sqm



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	345.0	5.4
10°-20°	798.3	12.6
20°-30°	915.9	14.4
30°-40°	902.8	14.2
40°-50°	796.1	12.5
50°-60°	612.5	9.7
60°-70°	402.7	6.3
70°-80°	195.6	3.1
80°-90°	50.3	0.8
90°-100°	95.7	1.5
100°-110°	280.1	4.4
110°-120°	273.5	4.3
120°-130°	217.8	3.4
130°-140°	171.9	2.7
140°-150°	128.2	2.0
150°-160°	89.4	1.4
160°-170°	52.5	0.8
170°-180°	17.1	0.3
0°-30°	2059.1	32.5
0°-40°	2961.9	46.7
0°-60°	4370.5	68.9
0°-90°	5019.0	79.1
90°-120°	649.2	10.2
90°-150°	1167.1	18.4
90°-180°	1326.0	20.9
0°-180°	6345.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3785	3785	3785	3785	3785	
5°	4477	4334	3794	3067	2848	409
15°	2708	3660	3622	1948	1617	764
25°	1347	2015	3231	1369	1229	636
35°	973	1228	2649	1075	954	607
45°	692	866	1913	805	706	537
55°	461	595	1189	559	441	413
65°	281	354	655	336	290	275
75°	123	149	296	154	127	132
85°	34	37	62	40	37	36
90°	10	9	1	9	10	8
95°	41	212	12	212	41	67
105°	454	287	41	287	454	453
115°	552	220	73	220	552	538
125°	435	205	102	205	435	394
135°	353	202	119	202	353	274
145°	276	200	136	200	276	175
155°	229	193	154	193	229	107
165°	200	185	169	185	200	57
175°	180	177	176	177	180	17
180°	176	176	176	176	176	



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4194.4	4181.2	4168.0	4164.2	4160.3	4147.9	4135.5	4107.5	4079.6	4050.9	4022.2
5°	4476.8	4478.4	4479.9	4476.1	4472.2	4455.9	4439.6	4405.5	4371.3	4334.1	4296.8
7.5°	4389.9	4414.8	4439.6	4444.3	4448.9	4461.3	4473.7	4466.0	4458.2	4444.3	4430.3
10°	4009.8	4008.2	4006.7	4034.6	4062.5	4145.5	4228.6	4271.2	4313.9	4351.9	4389.9
12.5°	3389.1	3391.4	3393.7	3485.3	3576.8	3655.2	3733.5	3842.2	3950.8	4067.9	4185.1
15°	2707.8	2745.8	2783.9	2865.3	2946.8	3064.7	3182.7	3328.5	3474.4	3659.8	3845.3
17.5°	2223.7	2240.0	2256.3	2334.6	2413.0	2524.7	2636.4	2801.7	2967.0	3205.9	3444.9
20°	1832.6	1847.4	1862.1	1918.8	1975.4	2082.5	2189.5	2347.0	2504.5	2741.2	2977.8
22.5°	1530.0	1558.7	1587.5	1625.5	1663.5	1741.1	1818.7	1979.3	2139.9	2355.6	2571.3
25°	1346.9	1360.1	1373.3	1405.9	1438.5	1513.0	1587.5	1693.8	1800.0	2015.0	2229.9
27.5°	1222.8	1226.7	1230.5	1254.6	1278.7	1326.8	1374.9	1473.4	1571.9	1748.8	1925.7
30°	1120.4	1127.4	1134.3	1153.0	1171.6	1206.5	1241.4	1311.2	1381.1	1539.3	1697.6
32.5°	1041.2	1045.1	1049.0	1064.5	1080.0	1105.6	1131.2	1186.3	1241.4	1362.4	1483.5
35°	973.0	973.7	974.5	986.1	997.8	1022.6	1047.4	1093.2	1139.0	1228.2	1317.4
37.5°	895.4	900.8	906.2	914.8	923.3	945.0	966.7	1004.0	1041.2	1114.9	1188.7
40°	830.2	834.8	839.5	849.6	859.7	876.7	893.8	928.0	962.1	1025.7	1089.3
42.5°	765.0	768.1	771.2	781.3	791.4	812.3	833.3	860.5	887.6	940.4	993.1
45°	692.1	699.8	707.6	718.5	729.3	747.2	765.0	793.0	820.9	865.9	910.9
47.5°	631.6	635.4	639.3	648.6	657.9	679.7	701.4	726.2	751.1	793.0	834.8
50°	571.0	572.6	574.2	582.7	591.2	610.6	630.0	658.7	687.4	726.2	765.0
52.5°	513.6	517.5	521.4	529.9	538.5	551.7	564.8	594.3	623.8	661.8	699.8
55°	460.9	463.2	465.5	471.7	477.9	493.5	509.0	534.6	560.2	595.1	630.0
57.5°	411.2	414.3	417.4	422.1	426.7	440.7	454.7	477.2	499.7	534.6	569.5
60°	360.0	363.9	367.8	373.2	378.6	389.5	400.4	420.5	440.7	471.7	502.8
62.5°	322.8	323.5	324.3	329.0	333.6	341.4	349.1	365.4	381.7	412.8	443.8
65°	280.9	283.2	285.5	287.9	290.2	296.4	302.6	316.6	330.5	353.8	377.1
67.5°	237.4	239.7	242.1	246.0	249.8	255.3	260.7	270.0	279.3	301.0	322.8
70°	184.7	184.7	184.7	190.9	197.1	206.4	215.7	222.7	229.7	247.5	265.4
72.5°	150.5	151.3	152.1	152.8	153.6	159.1	164.5	176.1	187.8	198.6	209.5
75°	122.6	123.4	124.1	124.9	125.7	127.2	128.8	132.7	136.6	149.0	161.4
77.5°	97.8	98.5	99.3	100.1	100.9	102.4	104.0	105.5	107.1	111.7	116.4
80°	74.5	75.3	76.0	76.8	77.6	78.4	79.1	80.7	82.2	84.6	86.9
82.5°	54.3	54.3	54.3	54.3	54.3	55.9	57.4	57.4	57.4	59.0	60.5
85°	34.1	34.1	34.1	34.9	35.7	35.7	35.7	36.5	37.2	37.2	37.2
87.5°	15.5	14.7	14.0	14.7	15.5	15.5	15.5	16.3	17.1	17.1	17.1
90°	10.3	10.7	10.3	10.0	10.3	9.6	9.3	8.9	8.6	8.9	7.9
92.5°	18.9	19.6	19.3	20.7	21.4	23.9	27.5	35.3	49.6	66.4	73.5
95°	41.4	42.8	45.3	48.5	55.3	68.2	87.1	128.5	171.7	211.6	188.4
97.5°	84.9	88.9	97.4	111.0	134.9	175.6	222.7	295.1	336.5	325.5	243.0
100°	223.8	223.4	237.3	263.4	299.4	350.1	391.8	420.7	408.3	338.0	228.4
102.5°	354.4	364.7	375.8	395.1	421.1	448.6	468.6	462.5	411.8	314.8	207.0
105°	453.9	455.7	467.1	480.7	497.1	506.4	499.6	463.9	389.3	286.9	190.2
107.5°	518.9	522.8	527.4	533.9	536.0	526.4	498.5	442.5	357.2	262.3	178.1
110°	556.0	556.7	557.4	554.6	544.6	519.6	474.6	409.0	327.2	242.0	171.7



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	563.5	563.1	559.6	549.2	528.9	495.0	443.2	375.8	301.2	228.4	168.1
115°	552.1	550.3	543.2	527.4	500.7	461.8	409.3	347.2	281.2	219.5	167.7
117.5°	527.1	524.6	513.9	496.4	468.6	428.2	380.1	325.1	268.0	213.4	168.1
120°	494.3	492.1	483.6	463.6	435.4	399.3	356.5	308.3	258.0	209.5	169.5
122.5°	463.6	460.7	451.1	433.6	409.3	376.5	337.6	295.1	249.8	207.0	172.0
125°	435.4	432.9	424.0	408.3	385.4	356.9	322.6	283.7	243.0	204.8	174.5
127.5°	411.1	409.0	400.8	387.2	366.5	340.1	308.7	273.4	236.6	203.8	177.4
130°	391.1	388.3	380.8	367.9	349.0	324.7	295.8	263.7	231.6	202.7	180.2
132.5°	371.5	369.7	363.3	350.4	333.0	310.1	283.7	254.8	227.0	202.3	182.4
135°	352.9	350.4	344.0	333.3	315.8	295.5	272.3	247.0	223.0	202.0	184.5
137.5°	333.3	331.2	325.8	314.8	299.8	281.6	260.9	239.5	219.5	201.3	185.9
140°	312.6	313.0	307.3	297.3	283.7	268.4	251.2	233.0	216.3	200.9	187.4
142.5°	293.3	293.7	288.7	280.1	269.1	256.2	242.0	227.0	213.4	200.2	188.4
145°	275.9	275.1	272.3	264.8	255.9	245.5	234.1	222.3	210.9	199.5	188.8
147.5°	260.9	260.5	257.7	252.3	245.2	237.7	228.0	218.4	208.4	198.4	188.8
150°	248.0	248.0	245.9	242.0	236.6	229.8	222.3	214.1	205.9	197.0	188.8
152.5°	237.3	237.3	236.2	232.7	228.8	223.4	217.0	210.2	203.1	195.2	187.7
155°	228.8	228.4	227.7	224.8	221.6	217.3	212.0	206.3	200.2	193.1	187.0
157.5°	220.5	220.5	219.8	217.7	214.8	211.3	207.0	202.0	197.0	191.3	185.9
160°	212.7	213.0	213.0	210.9	208.4	205.9	202.3	198.4	193.8	189.1	185.2
162.5°	205.6	205.9	205.9	204.1	202.7	200.6	197.3	194.1	190.6	187.0	183.8
165°	199.5	199.5	199.8	198.4	197.0	195.2	192.7	190.6	187.7	184.9	182.4
167.5°	193.4	193.4	193.8	192.7	192.0	190.6	189.1	187.4	184.9	182.7	180.9
170°	188.1	188.1	188.4	187.7	187.4	186.6	185.2	184.1	182.4	180.6	179.5
172.5°	183.1	183.4	184.1	183.4	183.4	183.1	182.0	181.3	179.9	178.8	178.4
175°	179.5	179.9	180.2	179.9	179.9	179.9	179.1	178.8	178.1	177.4	177.4
177.5°	177.0	177.0	177.7	177.4	177.7	177.7	177.4	177.0	176.6	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4018.3	4014.4	3977.2	3939.9	3903.5	3867.0	3839.8	3812.7	3766.9	3721.1	3692.4
5°	4267.4	4237.9	4178.9	4119.9	4031.5	3943.0	3868.5	3794.1	3699.4	3604.7	3525.6
7.5°	4406.2	4382.2	4310.8	4239.4	4122.3	4005.1	3888.7	3772.3	3632.7	3493.0	3373.5
10°	4410.1	4430.3	4371.3	4312.4	4180.5	4048.6	3890.3	3732.0	3544.2	3356.5	3202.1
12.5°	4272.0	4358.9	4346.5	4334.1	4199.8	4065.6	3873.2	3680.8	3450.3	3219.9	3026.7
15°	4013.6	4182.0	4231.7	4281.3	4170.4	4059.4	3840.6	3621.8	3351.0	3080.3	2858.3
17.5°	3680.8	3916.7	4047.8	4178.9	4098.2	4017.5	3777.8	3538.0	3233.1	2928.2	2686.9
20°	3286.6	3595.4	3801.0	4006.7	3977.2	3947.7	3700.2	3452.7	3123.7	2794.7	2533.3
22.5°	2897.1	3223.0	3507.0	3791.0	3821.2	3851.5	3601.6	3351.8	2991.8	2631.8	2365.7
25°	2561.2	2892.5	3230.8	3569.1	3637.3	3705.6	3468.2	3230.8	2857.6	2484.4	2219.8
27.5°	2240.7	2555.8	2928.2	3300.6	3424.7	3548.9	3331.6	3114.4	2725.7	2337.0	2073.2
30°	1979.3	2260.9	2641.1	3021.3	3194.3	3367.3	3167.9	2968.5	2582.9	2197.3	1938.9
32.5°	1735.6	1987.8	2369.5	2751.3	2952.2	3153.2	2980.9	2808.7	2437.8	2066.9	1811.7
35°	1543.2	1769.0	2125.1	2481.3	2706.3	2931.3	2790.1	2648.9	2286.5	1924.2	1682.9
37.5°	1378.0	1567.3	1901.7	2236.1	2475.1	2714.0	2596.1	2478.2	2137.6	1796.9	1568.8
40°	1241.4	1393.5	1704.6	2015.7	2250.1	2484.4	2383.5	2282.6	1977.7	1672.8	1459.4
42.5°	1124.3	1255.4	1534.7	1814.0	2028.9	2243.9	2177.1	2110.4	1834.2	1558.0	1360.1
45°	1021.1	1131.2	1377.2	1623.1	1821.0	2018.8	1966.1	1913.3	1675.1	1436.9	1255.4
47.5°	929.5	1024.2	1243.7	1463.3	1641.0	1818.7	1769.8	1720.9	1523.8	1326.8	1161.5
50°	845.7	926.4	1109.5	1292.6	1452.5	1612.3	1571.9	1531.6	1368.7	1205.7	1063.0
52.5°	766.6	833.3	997.8	1162.3	1291.1	1419.9	1388.8	1357.8	1232.1	1106.4	976.8
55°	691.3	752.6	891.5	1030.4	1140.5	1250.7	1219.7	1188.7	1090.9	993.1	879.1
57.5°	623.0	676.6	789.1	901.6	989.2	1076.9	1062.2	1047.4	966.0	884.5	790.6
60°	550.9	599.0	696.0	793.0	863.6	934.2	917.1	900.0	841.8	783.6	702.9
62.5°	486.5	529.2	606.7	684.3	741.7	799.2	786.7	774.3	730.1	685.9	619.2
65°	419.0	460.9	523.7	586.6	631.6	676.6	665.7	654.8	621.5	588.1	534.6
67.5°	357.7	392.6	446.9	501.2	531.5	561.7	555.5	549.3	523.7	498.1	456.2
70°	295.6	325.9	370.9	415.9	436.8	457.8	460.1	462.4	439.1	415.9	384.8
72.5°	233.5	257.6	299.5	341.4	357.7	374.0	373.2	372.4	358.5	344.5	316.6
75°	179.2	197.1	229.7	262.2	276.2	290.2	293.3	296.4	283.2	270.0	254.5
77.5°	128.8	141.2	166.0	190.9	206.4	221.9	223.5	225.0	218.8	212.6	197.8
80°	90.8	94.7	110.2	125.7	142.0	158.3	160.6	162.9	156.7	150.5	141.2
82.5°	62.8	65.2	70.6	76.0	89.2	102.4	105.5	108.6	105.5	102.4	92.3
85°	38.0	38.8	41.1	43.4	49.7	55.9	59.0	62.1	60.5	59.0	53.5
87.5°	17.1	17.1	17.8	18.6	20.2	21.7	25.6	29.5	27.2	24.8	22.5
90°	6.8	5.7	4.6	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	55.0	36.0	24.6	18.2	14.6	11.4	7.9	5.4	7.9	11.4	14.6
95°	129.9	76.7	46.4	32.5	23.2	17.1	13.2	12.1	13.2	17.1	23.2
97.5°	144.5	82.8	52.8	37.5	28.2	22.8	19.6	19.3	19.6	22.8	28.2
100°	134.5	81.7	56.7	42.8	34.3	29.3	26.8	26.4	26.8	29.3	34.3
102.5°	126.0	83.2	61.4	48.9	41.4	36.8	34.6	33.9	34.6	36.8	41.4
105°	122.8	86.0	66.7	55.7	48.9	44.6	42.5	41.4	42.5	44.6	48.9
107.5°	122.0	90.6	73.5	63.2	56.7	52.5	50.3	49.2	50.3	52.5	56.7
110°	123.8	96.7	80.7	70.7	64.6	60.7	58.9	57.8	58.9	60.7	64.6





TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	127.4	102.8	88.1	78.5	72.4	68.5	66.7	65.7	66.7	68.5	72.4
115°	131.3	109.6	96.0	86.4	80.3	76.7	74.6	73.2	74.6	76.7	80.3
117.5°	136.3	116.7	103.1	94.2	87.4	84.2	82.4	80.7	82.4	84.2	87.4
120°	142.0	123.5	110.6	101.7	94.9	91.4	89.6	88.5	89.6	91.4	94.9
122.5°	147.4	130.6	118.1	108.5	102.1	98.1	96.4	95.3	96.4	98.1	102.1
125°	153.1	137.4	124.9	115.3	108.5	104.6	102.4	101.7	102.4	104.6	108.5
127.5°	157.7	143.5	131.3	121.7	114.2	110.3	107.8	106.7	107.8	110.3	114.2
130°	162.4	148.8	137.0	127.4	119.9	115.6	112.4	111.3	112.4	115.6	119.9
132.5°	166.7	153.5	142.0	132.8	125.3	119.9	116.3	114.9	116.3	119.9	125.3
135°	170.2	158.1	147.0	137.4	129.9	124.5	120.6	119.2	120.6	124.5	129.9
137.5°	173.1	161.3	150.6	141.7	134.2	128.5	124.5	123.1	124.5	128.5	134.2
140°	175.2	164.5	154.2	145.2	138.1	132.4	128.8	127.0	128.8	132.4	138.1
142.5°	177.4	167.0	157.0	148.8	141.7	136.7	132.8	131.3	132.8	136.7	141.7
145°	178.8	169.2	159.9	151.7	145.6	140.2	137.0	136.0	137.0	140.2	145.6
147.5°	179.9	170.9	162.4	155.2	149.2	144.5	141.3	140.6	141.3	144.5	149.2
150°	180.2	172.7	164.5	158.1	153.1	148.5	145.6	145.2	145.6	148.5	153.1
152.5°	180.9	173.8	167.0	160.9	156.7	152.7	149.9	149.9	149.9	152.7	156.7
155°	180.9	175.2	169.2	164.2	160.2	156.7	154.5	154.5	154.5	156.7	160.2
157.5°	181.3	175.9	170.9	167.0	163.4	160.2	158.4	158.1	158.4	160.2	163.4
160°	181.3	177.0	172.7	169.2	166.7	163.8	162.4	162.4	162.4	163.8	166.7
162.5°	180.9	177.4	173.8	170.9	168.8	166.7	165.6	165.6	165.6	166.7	168.8
165°	180.2	177.7	174.9	172.4	170.9	169.2	168.4	168.8	168.4	169.2	170.9
167.5°	179.9	177.7	175.6	173.8	172.7	171.3	170.9	171.3	170.9	171.3	172.7
170°	178.8	177.4	175.6	174.9	174.2	173.1	172.7	173.4	172.7	173.1	174.2
172.5°	178.4	177.4	175.9	175.6	175.2	174.5	174.5	174.9	174.5	174.5	175.2
175°	177.7	177.0	176.3	175.9	175.9	175.2	175.6	175.9	175.6	175.2	175.9
177.5°	177.4	176.6	176.3	176.3	176.3	175.9	176.3	176.6	176.3	175.9	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	3663.7	3619.5	3575.3	3543.5	3511.6	3472.1	3432.5	3431.0	3429.4	3399.9	3370.4
5°	3446.5	3369.7	3292.8	3217.6	3142.3	3067.1	2991.8	2974.7	2957.7	2932.1	2906.5
7.5°	3254.0	3131.5	3008.9	2912.7	2816.5	2741.2	2665.9	2614.7	2563.5	2523.9	2484.4
10°	3047.7	2895.6	2743.5	2627.1	2510.8	2429.3	2347.8	2288.9	2229.9	2202.0	2174.0
12.5°	2833.5	2668.3	2503.0	2388.9	2274.9	2177.1	2079.4	2025.8	1972.3	1933.5	1894.7
15°	2636.4	2458.8	2281.1	2160.1	2039.0	1947.5	1855.9	1802.4	1748.8	1710.0	1671.2
17.5°	2445.6	2266.4	2087.1	1964.5	1841.9	1758.9	1675.9	1623.9	1571.9	1547.9	1523.8
20°	2271.8	2091.0	1910.2	1794.6	1679.0	1597.5	1516.1	1488.1	1460.2	1437.7	1415.2
22.5°	2099.5	1925.7	1751.9	1641.0	1530.0	1471.1	1412.1	1389.6	1367.1	1350.0	1333.0
25°	1955.2	1782.2	1609.2	1512.2	1415.2	1369.4	1323.7	1308.9	1294.2	1277.1	1260.0
27.5°	1809.4	1644.9	1480.4	1402.8	1325.2	1288.0	1250.7	1232.1	1213.5	1199.5	1185.5
30°	1680.6	1528.5	1376.4	1312.0	1247.6	1215.0	1182.4	1162.3	1142.1	1128.9	1115.7
32.5°	1556.4	1421.4	1286.4	1231.3	1176.2	1144.4	1112.6	1093.2	1073.8	1058.3	1042.8
35°	1441.6	1324.4	1207.3	1156.8	1106.4	1074.6	1042.8	1023.4	1004.0	988.5	973.0
37.5°	1340.7	1234.4	1128.1	1080.8	1033.5	1005.5	977.6	957.4	937.3	921.0	904.7
40°	1246.1	1152.2	1058.3	1012.5	966.7	936.5	906.2	888.4	870.5	855.8	841.1
42.5°	1162.3	1076.1	990.0	945.0	900.0	871.3	842.6	821.7	800.7	792.2	783.6
45°	1073.8	997.8	921.7	878.3	834.8	804.6	774.3	756.5	738.6	730.9	723.1
47.5°	996.2	925.6	855.0	812.3	769.7	742.5	715.4	701.4	687.4	676.6	665.7
50°	920.2	851.9	783.6	742.5	701.4	678.1	654.8	637.8	620.7	612.9	605.2
52.5°	847.3	785.2	723.1	681.2	639.3	616.8	594.3	579.6	564.8	548.5	532.3
55°	765.0	710.7	656.4	619.2	581.9	558.6	535.4	518.3	501.2	484.2	467.1
57.5°	696.7	643.2	589.7	556.3	522.9	500.4	477.9	459.3	440.7	426.7	412.8
60°	622.3	575.7	529.2	496.6	464.0	442.3	420.5	402.7	384.8	377.9	370.9
62.5°	552.4	509.0	465.5	436.8	408.1	387.2	366.2	354.6	342.9	338.3	333.6
65°	481.0	443.8	406.6	380.2	353.8	336.0	318.1	312.7	307.2	303.4	299.5
67.5°	414.3	382.5	350.7	327.4	304.1	291.7	279.3	273.1	266.9	262.2	257.6
70°	353.8	325.9	297.9	277.8	257.6	246.0	234.3	228.9	223.5	214.9	206.4
72.5°	288.6	266.9	245.2	229.7	214.1	204.1	194.0	183.1	172.2	164.5	156.7
75°	239.0	217.2	195.5	180.8	166.0	154.4	142.8	138.9	135.0	132.7	130.3
77.5°	183.1	164.5	145.9	134.2	122.6	117.2	111.7	109.4	107.1	106.3	105.5
80°	131.9	116.4	100.9	94.7	88.5	86.9	85.3	83.8	82.2	81.5	80.7
82.5°	82.2	74.5	66.7	65.2	63.6	62.8	62.1	61.3	60.5	59.7	59.0
85°	48.1	45.0	41.9	41.1	40.3	39.6	38.8	38.8	38.8	38.8	38.8
87.5°	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	19.4	18.6
90°	3.9	4.6	5.7	6.8	7.9	8.9	8.6	8.9	9.3	9.6	10.3
92.5°	18.2	24.6	36.0	55.0	73.5	66.4	49.6	35.3	27.5	23.9	21.4
95°	32.5	46.4	76.7	129.9	188.4	211.6	171.7	128.5	87.1	68.2	55.3
97.5°	37.5	52.8	82.8	144.5	243.0	325.5	336.5	295.1	222.7	175.6	134.9
100°	42.8	56.7	81.7	134.5	228.4	338.0	408.3	420.7	391.8	350.1	299.4
102.5°	48.9	61.4	83.2	126.0	207.0	314.8	411.8	462.5	468.6	448.6	421.1
105°	55.7	66.7	86.0	122.8	190.2	286.9	389.3	463.9	499.6	506.4	497.1
107.5°	63.2	73.5	90.6	122.0	178.1	262.3	357.2	442.5	498.5	526.4	536.0
110°	70.7	80.7	96.7	123.8	171.7	242.0	327.2	409.0	474.6	519.6	544.6



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	78.5	88.1	102.8	127.4	168.1	228.4	301.2	375.8	443.2	495.0	528.9
115°	86.4	96.0	109.6	131.3	167.7	219.5	281.2	347.2	409.3	461.8	500.7
117.5°	94.2	103.1	116.7	136.3	168.1	213.4	268.0	325.1	380.1	428.2	468.6
120°	101.7	110.6	123.5	142.0	169.5	209.5	258.0	308.3	356.5	399.3	435.4
122.5°	108.5	118.1	130.6	147.4	172.0	207.0	249.8	295.1	337.6	376.5	409.3
125°	115.3	124.9	137.4	153.1	174.5	204.8	243.0	283.7	322.6	356.9	385.4
127.5°	121.7	131.3	143.5	157.7	177.4	203.8	236.6	273.4	308.7	340.1	366.5
130°	127.4	137.0	148.8	162.4	180.2	202.7	231.6	263.7	295.8	324.7	349.0
132.5°	132.8	142.0	153.5	166.7	182.4	202.3	227.0	254.8	283.7	310.1	333.0
135°	137.4	147.0	158.1	170.2	184.5	202.0	223.0	247.0	272.3	295.5	315.8
137.5°	141.7	150.6	161.3	173.1	185.9	201.3	219.5	239.5	260.9	281.6	299.8
140°	145.2	154.2	164.5	175.2	187.4	200.9	216.3	233.0	251.2	268.4	283.7
142.5°	148.8	157.0	167.0	177.4	188.4	200.2	213.4	227.0	242.0	256.2	269.1
145°	151.7	159.9	169.2	178.8	188.8	199.5	210.9	222.3	234.1	245.5	255.9
147.5°	155.2	162.4	170.9	179.9	188.8	198.4	208.4	218.4	228.0	237.7	245.2
150°	158.1	164.5	172.7	180.2	188.8	197.0	205.9	214.1	222.3	229.8	236.6
152.5°	160.9	167.0	173.8	180.9	187.7	195.2	203.1	210.2	217.0	223.4	228.8
155°	164.2	169.2	175.2	180.9	187.0	193.1	200.2	206.3	212.0	217.3	221.6
157.5°	167.0	170.9	175.9	181.3	185.9	191.3	197.0	202.0	207.0	211.3	214.8
160°	169.2	172.7	177.0	181.3	185.2	189.1	193.8	198.4	202.3	205.9	208.4
162.5°	170.9	173.8	177.4	180.9	183.8	187.0	190.6	194.1	197.3	200.6	202.7
165°	172.4	174.9	177.7	180.2	182.4	184.9	187.7	190.6	192.7	195.2	197.0
167.5°	173.8	175.6	177.7	179.9	180.9	182.7	184.9	187.4	189.1	190.6	192.0
170°	174.9	175.6	177.4	178.8	179.5	180.6	182.4	184.1	185.2	186.6	187.4
172.5°	175.6	175.9	177.4	178.4	178.4	178.8	179.9	181.3	182.0	183.1	183.4
175°	175.9	176.3	177.0	177.7	177.4	177.4	178.1	178.8	179.1	179.9	179.9
177.5°	176.3	176.3	176.6	177.4	176.6	176.3	176.6	177.0	177.4	177.7	177.7
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3784.8	3784.8	3784.8	3784.8
2.5°	3362.7	3354.9	3351.8	3348.7
5°	2882.4	2858.3	2852.9	2847.5
7.5°	2474.3	2464.2	2430.8	2397.5
10°	2143.0	2112.0	2098.0	2084.0
12.5°	1866.0	1837.3	1832.6	1828.0
15°	1651.1	1630.9	1623.9	1616.9
17.5°	1509.9	1495.9	1487.4	1478.8
20°	1405.1	1395.0	1388.8	1382.6
22.5°	1325.2	1317.4	1312.8	1308.1
25°	1248.4	1236.8	1232.9	1229.0
27.5°	1175.5	1165.4	1161.5	1157.6
30°	1107.2	1098.6	1093.2	1087.8
32.5°	1032.7	1022.6	1019.5	1016.4
35°	966.7	960.5	957.4	954.3
37.5°	896.9	889.2	884.5	879.9
40°	837.2	833.3	831.0	828.6
42.5°	776.7	769.7	768.9	768.1
45°	716.1	709.2	707.6	706.1
47.5°	659.5	653.3	652.5	651.7
50°	596.7	588.1	581.9	575.7
52.5°	524.5	516.7	511.3	505.9
55°	458.5	450.0	445.4	440.7
57.5°	408.9	405.0	402.7	400.4
60°	368.5	366.2	364.7	363.1
62.5°	331.3	329.0	329.0	329.0
65°	297.2	294.8	292.5	290.2
67.5°	252.9	248.3	247.5	246.7
70°	199.4	192.4	191.6	190.9
72.5°	156.0	155.2	153.6	152.1
75°	128.8	127.2	127.2	127.2
77.5°	104.0	102.4	102.4	102.4
80°	79.9	79.1	79.9	80.7
82.5°	59.0	59.0	58.2	57.4
85°	38.0	37.2	37.2	37.2
87.5°	18.6	18.6	18.6	18.6
90°	10.0	10.3	10.7	10.3
92.5°	20.7	19.3	19.6	18.9
95°	48.5	45.3	42.8	41.4
97.5°	111.0	97.4	88.9	84.9
100°	263.4	237.3	223.4	223.8
102.5°	395.1	375.8	364.7	354.4
105°	480.7	467.1	455.7	453.9
107.5°	533.9	527.4	522.8	518.9
110°	554.6	557.4	556.7	556.0



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	549.2	559.6	563.1	563.5
115°	527.4	543.2	550.3	552.1
117.5°	496.4	513.9	524.6	527.1
120°	463.6	483.6	492.1	494.3
122.5°	433.6	451.1	460.7	463.6
125°	408.3	424.0	432.9	435.4
127.5°	387.2	400.8	409.0	411.1
130°	367.9	380.8	388.3	391.1
132.5°	350.4	363.3	369.7	371.5
135°	333.3	344.0	350.4	352.9
137.5°	314.8	325.8	331.2	333.3
140°	297.3	307.3	313.0	312.6
142.5°	280.1	288.7	293.7	293.3
145°	264.8	272.3	275.1	275.9
147.5°	252.3	257.7	260.5	260.9
150°	242.0	245.9	248.0	248.0
152.5°	232.7	236.2	237.3	237.3
155°	224.8	227.7	228.4	228.8
157.5°	217.7	219.8	220.5	220.5
160°	210.9	213.0	213.0	212.7
162.5°	204.1	205.9	205.9	205.6
165°	198.4	199.8	199.5	199.5
167.5°	192.7	193.8	193.4	193.4
170°	187.7	188.4	188.1	188.1
172.5°	183.4	184.1	183.4	183.1
175°	179.9	180.2	179.9	179.5
177.5°	177.4	177.7	177.0	177.0
180°	176.3	176.3	176.3	176.3



TEST NUMBER: P831962

CATALOG NUMBER: S123RDIP-S1165D365U840-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.04	17.14	16.71	17.81	18.60	20.70	21.80	21.37	22.48	23.27
	3H	17.28	18.26	17.96	18.95	19.77	22.22	23.20	22.90	23.89	24.71
	4H	17.67	18.59	18.38	19.29	20.13	22.72	23.64	23.43	24.34	25.18
	6H	17.97	18.82	18.68	19.53	20.38	23.05	23.90	23.76	24.61	25.46
	8H	18.06	18.87	18.79	19.60	20.45	23.13	23.94	23.86	24.67	25.52
	12H	18.12	18.89	18.85	19.61	20.49	23.17	23.94	23.90	24.66	25.54
4H	2H	16.79	17.71	17.50	18.41	19.25	20.73	21.65	21.43	22.35	23.19
	3H	18.18	18.95	18.90	19.69	20.54	22.41	23.17	23.13	23.91	24.76
	4H	18.65	19.34	19.38	20.08	20.96	23.02	23.72	23.76	24.46	25.34
	6H	19.03	19.63	19.78	20.39	21.29	23.48	24.07	24.23	24.84	25.73
	8H	19.16	19.72	19.92	20.48	21.38	23.61	24.17	24.37	24.93	25.83
	12H	19.25	19.74	20.02	20.53	21.44	23.68	24.18	24.46	24.97	25.88
8H	4H	18.98	19.54	19.74	20.30	21.20	23.01	23.57	23.77	24.33	25.23
	6H	19.45	19.91	20.24	20.72	21.62	23.51	23.97	24.30	24.78	25.68
	8H	19.65	20.05	20.45	20.86	21.78	23.70	24.11	24.50	24.91	25.84
	12H	19.80	20.16	20.60	20.95	21.93	23.83	24.19	24.63	24.98	25.96
12H	4H	19.00	19.50	19.78	20.29	21.20	22.97	23.47	23.75	24.26	25.16
	6H	19.51	19.92	20.31	20.73	21.65	23.49	23.90	24.29	24.70	25.62
	8H	19.74	20.10	20.54	20.89	21.88	23.69	24.05	24.49	24.85	25.83