

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832455

Luminaire Tested: S123RDP-S1165D935-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-2019  
 Report Number: P832455  
 Test Lab: INNOVATION CENTER  
 Issue Date: 05/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: NEO-RAY  
 Catalog Number: S123RDP-S1165D935-4F0-1E-UDD-G  
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE  
 DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 4278.3 lumens  
 Efficiency: N/A  
 Efficacy: 101.4 lumens/watt  
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
 CIE Type: Direct


Input Watts (W): 42.2  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

### Luminous Intensity Polar Plot



TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89			87		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78			76		
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69			67		
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61			59		
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54			53		
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49			47		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45			43		
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41			39		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38			36		
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35			33		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	34733	34733	34733	34733	34733
5°	41242	39927	34952	28254	26231
10°	37366	40555	34777	22638	19420
15°	25727	34771	34410	18503	15363
20°	17898	26771	33719	15601	13503
25°	13639	20403	32714	13867	12444
30°	11872	16312	31457	12875	11527
35°	10900	13761	29676	12039	10692
40°	9946	12288	27347	11219	9927
45°	8983	11237	24832	10443	9164
50°	8153	10369	21867	9682	8219
55°	7373	9522	19018	8938	7051
60°	6607	8658	16518	8118	6665
65°	6100	7682	14220	7294	6301
70°	4954	6641	12409	6600	5120
75°	4346	5282	10509	5473	4512
80°	3936	4469	8610	4593	4265
85°	3594	3927	6533	4162	3927

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 26201 cd/sqm

TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	294.1	6.9
10°-20°	680.6	15.9
20°-30°	780.9	18.3
30°-40°	769.7	18.0
40°-50°	678.8	15.9
50°-60°	522.2	12.2
60°-70°	343.3	8.0
70°-80°	166.7	3.9
80°-90°	42.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1755.6	41.0
0°-40°	2525.3	59.0
0°-60°	3726.2	87.1
0°-90°	4278.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4278.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3227	3227	3227	3227	3227	
5°	3817	3695	3235	2615	2428	349
15°	2309	3120	3088	1660	1379	652
25°	1148	1718	2754	1168	1048	542
35°	830	1047	2258	916	814	517
45°	590	738	1631	686	602	458
55°	393	507	1013	476	376	352
65°	240	302	558	286	247	235
75°	104	127	253	132	108	112
85°	29	32	53	34	32	33
90°	0	0	0	0	0	

TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3576.1	3564.9	3553.6	3550.3	3547.0	3536.4	3525.8	3502.0	3478.2	3453.7	3429.3
5°	3816.9	3818.2	3819.5	3816.2	3812.9	3799.0	3785.1	3756.0	3726.9	3695.2	3663.4
7.5°	3742.8	3764.0	3785.1	3789.1	3793.1	3803.7	3814.2	3807.6	3801.0	3789.1	3777.2
10°	3418.7	3417.3	3416.0	3439.8	3463.6	3534.4	3605.2	3641.6	3678.0	3710.4	3742.8
12.5°	2889.5	2891.4	2893.4	2971.5	3049.5	3116.4	3183.2	3275.8	3368.4	3468.3	3568.2
15°	2308.7	2341.1	2373.5	2442.9	2512.4	2613.0	2713.5	2837.9	2962.2	3120.3	3278.4
17.5°	1895.9	1909.8	1923.7	1990.5	2057.3	2152.5	2247.8	2388.7	2529.6	2733.3	2937.1
20°	1562.5	1575.0	1587.6	1635.9	1684.2	1775.5	1866.8	2001.1	2135.3	2337.1	2538.9
22.5°	1304.5	1329.0	1353.4	1385.9	1418.3	1484.4	1550.6	1687.5	1824.4	2008.3	2192.2
25°	1148.4	1159.6	1170.9	1198.6	1226.4	1289.9	1353.4	1444.1	1534.7	1717.9	1901.2
27.5°	1042.5	1045.8	1049.1	1069.7	1090.2	1131.2	1172.2	1256.2	1340.2	1491.0	1641.9
30°	955.2	961.2	967.1	983.0	998.9	1028.6	1058.4	1117.9	1177.5	1312.4	1447.4
32.5°	887.7	891.0	894.4	907.6	920.8	942.6	964.5	1011.4	1058.4	1161.6	1264.8
35°	829.5	830.2	830.9	840.8	850.7	871.9	893.0	932.1	971.1	1047.2	1123.2
37.5°	763.4	768.0	772.6	779.9	787.2	805.7	824.2	856.0	887.7	950.6	1013.4
40°	707.8	711.8	715.8	724.3	732.9	747.5	762.1	791.2	820.3	874.5	928.8
42.5°	652.2	654.9	657.5	666.1	674.7	692.6	710.5	733.6	756.8	801.7	846.7
45°	590.1	596.7	603.3	612.6	621.8	637.0	652.2	676.1	699.9	738.2	776.6
47.5°	538.5	541.8	545.1	553.0	561.0	579.5	598.0	619.2	640.3	676.1	711.8
50°	486.9	488.2	489.5	496.8	504.1	520.6	537.1	561.6	586.1	619.2	652.2
52.5°	437.9	441.2	444.5	451.8	459.1	470.3	481.6	506.7	531.9	564.3	596.7
55°	392.9	394.9	396.9	402.2	407.5	420.7	433.9	455.8	477.6	507.4	537.1
57.5°	350.6	353.2	355.9	359.9	363.8	375.7	387.6	406.8	426.0	455.8	485.5
60°	306.9	310.2	313.6	318.2	322.8	332.1	341.3	358.5	375.7	402.2	428.7
62.5°	275.2	275.8	276.5	280.5	284.4	291.1	297.7	311.6	325.5	351.9	378.4
65°	239.5	241.4	243.4	245.4	247.4	252.7	258.0	269.9	281.8	301.6	321.5
67.5°	202.4	204.4	206.4	209.7	213.0	217.6	222.3	230.2	238.1	256.7	275.2
70°	157.4	157.4	157.4	162.7	168.0	176.0	183.9	189.9	195.8	211.0	226.2
72.5°	128.3	129.0	129.7	130.3	131.0	135.6	140.2	150.2	160.1	169.3	178.6
75°	104.5	105.2	105.8	106.5	107.2	108.5	109.8	113.1	116.4	127.0	137.6
77.5°	83.3	84.0	84.7	85.3	86.0	87.3	88.6	90.0	91.3	95.3	99.2
80°	63.5	64.2	64.8	65.5	66.2	66.8	67.5	68.8	70.1	72.1	74.1
82.5°	46.3	46.3	46.3	46.3	46.3	47.6	49.0	49.0	49.0	50.3	51.6
85°	29.1	29.1	29.1	29.8	30.4	30.4	30.4	31.1	31.8	31.8	31.8
87.5°	13.2	12.6	11.9	12.6	13.2	13.2	13.2	13.9	14.6	14.6	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3425.9	3422.6	3390.9	3359.1	3328.0	3296.9	3273.8	3250.6	3211.6	3172.6	3148.1
5°	3638.3	3613.1	3562.9	3512.6	3437.2	3361.8	3298.3	3234.8	3154.1	3073.4	3005.9
7.5°	3756.7	3736.2	3675.3	3614.5	3514.6	3414.7	3315.5	3216.2	3097.2	2978.1	2876.2
10°	3760.0	3777.2	3726.9	3676.7	3564.2	3451.7	3316.8	3181.8	3021.8	2861.7	2730.0
12.5°	3642.3	3716.3	3705.8	3695.2	3580.7	3466.3	3302.2	3138.2	2941.7	2745.3	2580.5
15°	3422.0	3565.5	3607.9	3650.2	3555.6	3461.0	3274.5	3087.9	2857.0	2626.2	2437.0
17.5°	3138.2	3339.3	3451.1	3562.9	3494.1	3425.3	3220.9	3016.5	2756.5	2496.5	2290.8
20°	2802.1	3065.4	3240.7	3416.0	3390.9	3365.7	3154.7	2943.7	2663.2	2382.7	2159.8
22.5°	2470.1	2747.9	2990.0	3232.1	3257.9	3283.7	3070.7	2857.7	2550.8	2243.8	2016.9
25°	2183.6	2466.1	2754.5	3042.9	3101.1	3159.4	2956.9	2754.5	2436.3	2118.1	1892.6
27.5°	1910.4	2179.0	2496.5	2814.0	2919.9	3025.7	2840.5	2655.3	2323.9	1992.5	1767.5
30°	1687.5	1927.6	2251.8	2575.9	2723.4	2870.9	2700.9	2530.9	2202.2	1873.4	1653.1
32.5°	1479.8	1694.8	2020.2	2345.7	2517.0	2688.4	2541.5	2394.7	2078.5	1762.3	1544.6
35°	1315.7	1508.2	1811.9	2115.5	2307.3	2499.2	2378.8	2258.4	1949.5	1640.5	1434.8
37.5°	1174.8	1336.2	1621.4	1906.5	2110.2	2314.0	2213.4	2112.9	1822.5	1532.0	1337.6
40°	1058.4	1188.1	1453.3	1718.6	1918.4	2118.1	2032.1	1946.2	1686.2	1426.2	1244.3
42.5°	958.5	1070.3	1308.5	1546.6	1729.8	1913.1	1856.2	1799.3	1563.8	1328.3	1159.6
45°	870.5	964.5	1174.2	1383.9	1552.6	1721.2	1676.3	1631.3	1428.2	1225.1	1070.3
47.5°	792.5	873.2	1060.4	1247.6	1399.1	1550.6	1508.9	1467.2	1299.2	1131.2	990.3
50°	721.0	789.8	946.0	1102.1	1238.3	1374.6	1340.2	1305.8	1166.9	1028.0	906.3
52.5°	653.6	710.5	850.7	990.9	1100.7	1210.6	1184.1	1157.6	1050.5	943.3	832.8
55°	589.4	641.7	760.1	878.5	972.4	1066.3	1039.9	1013.4	930.1	846.7	749.5
57.5°	531.2	576.8	672.8	768.7	843.4	918.2	905.6	893.0	823.6	754.1	674.1
60°	469.7	510.7	593.4	676.1	736.3	796.5	781.9	767.3	717.7	668.1	599.3
62.5°	414.8	451.1	517.3	583.4	632.4	681.4	670.8	660.2	622.5	584.8	527.9
65°	357.2	392.9	446.5	500.1	538.5	576.8	567.6	558.3	529.9	501.4	455.8
67.5°	305.0	334.7	381.0	427.3	453.1	478.9	473.6	468.3	446.5	424.7	389.0
70°	252.0	277.8	316.2	354.6	372.4	390.3	392.3	394.3	374.4	354.6	328.1
72.5°	199.1	219.6	255.3	291.1	305.0	318.8	318.2	317.5	305.6	293.7	269.9
75°	152.8	168.0	195.8	223.6	235.5	247.4	250.0	252.7	241.4	230.2	217.0
77.5°	109.8	120.4	141.6	162.7	176.0	189.2	190.5	191.8	186.5	181.3	168.7
80°	77.4	80.7	93.9	107.2	121.1	134.9	136.9	138.9	133.6	128.3	120.4
82.5°	53.6	55.6	60.2	64.8	76.1	87.3	90.0	92.6	90.0	87.3	78.7
85°	32.4	33.1	35.1	37.0	42.3	47.6	50.3	52.9	51.6	50.3	45.6
87.5°	14.6	14.6	15.2	15.9	17.2	18.5	21.8	25.1	23.2	21.2	19.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3123.6	3085.9	3048.2	3021.1	2994.0	2960.2	2926.5	2925.2	2923.9	2898.7	2873.6
5°	2938.4	2872.9	2807.4	2743.3	2679.1	2614.9	2550.8	2536.2	2521.7	2499.8	2478.0
7.5°	2774.4	2669.8	2565.3	2483.3	2401.3	2337.1	2272.9	2229.3	2185.6	2151.9	2118.1
10°	2598.4	2468.7	2339.1	2239.9	2140.6	2071.2	2001.7	1951.4	1901.2	1877.4	1853.5
12.5°	2415.8	2274.9	2134.0	2036.8	1939.5	1856.2	1772.8	1727.2	1681.5	1648.5	1615.4
15°	2247.8	2096.3	1944.8	1841.6	1738.4	1660.4	1582.3	1536.7	1491.0	1458.0	1424.9
17.5°	2085.1	1932.3	1779.5	1674.9	1570.4	1499.6	1428.9	1384.5	1340.2	1319.7	1299.2
20°	1936.9	1782.8	1628.6	1530.1	1431.5	1362.0	1292.6	1268.8	1245.0	1225.8	1206.6
22.5°	1790.0	1641.9	1493.7	1399.1	1304.5	1254.2	1203.9	1184.8	1165.6	1151.0	1136.5
25°	1667.0	1519.5	1372.0	1289.3	1206.6	1167.6	1128.5	1116.0	1103.4	1088.8	1074.3
27.5°	1542.6	1402.4	1262.2	1196.0	1129.9	1098.1	1066.3	1050.5	1034.6	1022.7	1010.8
30°	1432.8	1303.2	1173.5	1118.6	1063.7	1035.9	1008.1	990.9	973.7	962.5	951.2
32.5°	1327.0	1211.9	1096.8	1049.8	1002.8	975.7	948.6	932.1	915.5	902.3	889.1
35°	1229.1	1129.2	1029.3	986.3	943.3	916.2	889.1	872.5	856.0	842.8	829.5
37.5°	1143.1	1052.5	961.8	921.5	881.1	857.3	833.5	816.3	799.1	785.2	771.3
40°	1062.4	982.3	902.3	863.3	824.2	798.4	772.6	757.4	742.2	729.6	717.1
42.5°	990.9	917.5	844.1	805.7	767.3	742.9	718.4	700.5	682.7	675.4	668.1
45°	915.5	850.7	785.9	748.8	711.8	686.0	660.2	645.0	629.8	623.1	616.5
47.5°	849.4	789.2	729.0	692.6	656.2	633.1	609.9	598.0	586.1	576.8	567.6
50°	784.5	726.3	668.1	633.1	598.0	578.2	558.3	543.8	529.2	522.6	516.0
52.5°	722.4	669.4	616.5	580.8	545.1	525.9	506.7	494.1	481.6	467.7	453.8
55°	652.2	605.9	559.6	527.9	496.1	476.3	456.4	441.9	427.3	412.8	398.2
57.5°	594.0	548.4	502.7	474.3	445.9	426.7	407.5	391.6	375.7	363.8	351.9
60°	530.5	490.8	451.1	423.4	395.6	377.1	358.5	343.3	328.1	322.2	316.2
62.5°	471.0	433.9	396.9	372.4	348.0	330.1	312.2	302.3	292.4	288.4	284.4
65°	410.1	378.4	346.6	324.1	301.6	286.4	271.2	266.6	262.0	258.6	255.3
67.5°	353.2	326.1	299.0	279.2	259.3	248.7	238.1	232.9	227.6	223.6	219.6
70°	301.6	277.8	254.0	236.8	219.6	209.7	199.8	195.1	190.5	183.2	176.0
72.5°	246.1	227.6	209.0	195.8	182.6	174.0	165.4	156.1	146.9	140.2	133.6
75°	203.7	185.2	166.7	154.1	141.6	131.6	121.7	118.4	115.1	113.1	111.1
77.5°	156.1	140.2	124.4	114.4	104.5	99.9	95.3	93.3	91.3	90.6	90.0
80°	112.5	99.2	86.0	80.7	75.4	74.1	72.8	71.4	70.1	69.5	68.8
82.5°	70.1	63.5	56.9	55.6	54.2	53.6	52.9	52.3	51.6	50.9	50.3
85°	41.0	38.4	35.7	35.1	34.4	33.7	33.1	33.1	33.1	33.1	33.1
87.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	16.5	15.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3226.8	3226.8	3226.8	3226.8
2.5°	2867.0	2860.4	2857.7	2855.1
5°	2457.5	2437.0	2432.4	2427.7
7.5°	2109.5	2100.9	2072.5	2044.1
10°	1827.1	1800.6	1788.7	1776.8
12.5°	1590.9	1566.4	1562.5	1558.5
15°	1407.7	1390.5	1384.5	1378.6
17.5°	1287.3	1275.4	1268.1	1260.8
20°	1198.0	1189.4	1184.1	1178.8
22.5°	1129.9	1123.2	1119.3	1115.3
25°	1064.4	1054.4	1051.1	1047.8
27.5°	1002.2	993.6	990.3	987.0
30°	944.0	936.7	932.1	927.4
32.5°	880.5	871.9	869.2	866.6
35°	824.2	818.9	816.3	813.7
37.5°	764.7	758.1	754.1	750.1
40°	713.8	710.5	708.5	706.5
42.5°	662.2	656.2	655.6	654.9
45°	610.6	604.6	603.3	602.0
47.5°	562.3	557.0	556.3	555.7
50°	508.7	501.4	496.1	490.8
52.5°	447.2	440.6	435.9	431.3
55°	391.0	383.7	379.7	375.7
57.5°	348.6	345.3	343.3	341.3
60°	314.2	312.2	310.9	309.6
62.5°	282.5	280.5	280.5	280.5
65°	253.4	251.4	249.4	247.4
67.5°	215.7	211.7	211.0	210.4
70°	170.0	164.1	163.4	162.7
72.5°	133.0	132.3	131.0	129.7
75°	109.8	108.5	108.5	108.5
77.5°	88.6	87.3	87.3	87.3
80°	68.1	67.5	68.1	68.8
82.5°	50.3	50.3	49.6	49.0
85°	32.4	31.8	31.8	31.8
87.5°	15.9	15.9	15.9	15.9
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832455

CATALOG NUMBER: S123RDP-S1165D935-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.03	18.49	17.40	18.80	19.11	21.70	23.15	22.06	23.46	23.78
	3H	18.29	19.60	18.67	19.93	20.29	23.24	24.54	23.62	24.87	25.23
	4H	18.70	19.92	19.10	20.27	20.65	23.75	24.97	24.15	25.32	25.70
	6H	19.01	20.14	19.43	20.51	20.90	24.09	25.22	24.51	25.59	25.98
	8H	19.12	20.19	19.54	20.58	20.98	24.19	25.26	24.62	25.65	26.05
	12H	19.19	20.21	19.62	20.59	21.02	24.24	25.26	24.67	25.65	26.07
4H	2H	17.82	19.04	18.22	19.39	19.77	21.76	22.98	22.16	23.33	23.71
	3H	19.24	20.25	19.65	20.65	21.06	23.47	24.48	23.88	24.88	25.28
	4H	19.72	20.63	20.15	21.04	21.48	24.10	25.00	24.53	25.42	25.86
	6H	20.12	20.91	20.58	21.35	21.81	24.56	25.35	25.02	25.80	26.26
	8H	20.25	20.99	20.72	21.43	21.90	24.71	25.44	25.17	25.89	26.35
	12H	20.36	21.01	20.84	21.49	21.96	24.79	25.45	25.28	25.93	26.40
8H	4H	20.07	20.81	20.54	21.25	21.72	24.10	24.84	24.57	25.28	25.75
	6H	20.56	21.16	21.06	21.66	22.13	24.62	25.23	25.12	25.72	26.20
	8H	20.75	21.29	21.27	21.81	22.30	24.81	25.35	25.32	25.86	26.35
	12H	20.92	21.40	21.43	21.89	22.46	24.95	25.43	25.46	25.92	26.49
12H	4H	20.11	20.77	20.60	21.25	21.72	24.08	24.74	24.56	25.22	25.69
	6H	20.62	21.16	21.13	21.67	22.16	24.59	25.14	25.11	25.65	26.14
	8H	20.86	21.34	21.37	21.83	22.40	24.82	25.29	25.33	25.79	26.35