

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332371-840

Luminaire Tested: **S123RDIP-S1165D585U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332371-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D585U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6564.6 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332371-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332371-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	69	63	80	72	65	60	64	59	55	58	54	50	51	48	45	42
4	78	68	60	54	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	55	46	41	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	28	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332371-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.8
10°-20°	511.4	7.8
20°-30°	736.4	11.2
30°-40°	829.4	12.6
40°-50°	793.5	12.1
50°-60°	649.8	9.9
60°-70°	438.4	6.7
70°-80°	220.6	3.4
80°-90°	60.6	0.9
90°-100°	158.3	2.4
100°-110°	448.4	6.8
110°-120°	441.1	6.7
120°-130°	351.8	5.4
130°-140°	277.4	4.2
140°-150°	207.0	3.2
150°-160°	144.3	2.2
160°-170°	84.8	1.3
170°-180°	27.6	0.4
0°-30°	1431.6	21.8
0°-40°	2261.0	34.4
0°-60°	3704.3	56.4
0°-90°	4423.9	67.4
90°-120°	1047.8	16.0
90°-150°	1884.1	28.7
90°-180°	2141.0	32.6
0°-180°	6564.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	1	7	14	16	17	5
95°	20	64	342	100	67	21
105°	67	99	463	810	733	71
115°	118	147	354	777	891	117
125°	164	194	331	599	703	146
135°	192	230	326	493	570	149
145°	219	251	322	405	445	138
155°	249	269	312	354	369	115
165°	272	280	298	316	322	77
175°	284	284	286	290	290	27
180°	285	285	285	285	285	



TEST NUMBER: P332371-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.7	27.9	24.9	22.2	19.3	18.0	18.4	18.7	19.1	19.4	19.0
90°	1.1	2.3	3.4	5.2	6.4	7.5	9.2	10.9	12.6	14.4	13.8
92.5°	7.2	10.6	15.5	19.9	24.7	33.3	48.4	73.1	97.5	88.6	66.9
95°	19.6	21.3	27.7	37.5	52.4	74.8	123.8	209.6	304.2	341.5	277.0
97.5°	33.4	34.0	39.0	47.5	62.2	86.5	133.3	230.0	387.5	529.4	566.3
100°	42.6	43.2	47.3	55.3	69.1	91.6	131.9	217.1	368.6	545.4	658.9
102.5°	52.3	53.3	57.0	64.5	77.0	97.6	133.7	206.1	341.0	515.5	663.6
105°	66.9	68.6	72.0	78.9	89.9	107.8	138.9	198.1	307.0	463.1	628.4
107.5°	82.2	84.0	87.4	94.1	104.4	121.0	148.2	197.5	285.4	416.8	566.9
110°	93.3	95.0	98.0	104.2	114.0	130.2	156.1	199.9	277.0	390.5	528.2



TEST NUMBER: P332371-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.4	105.2	108.1	114.4	124.2	139.9	163.9	204.5	272.5	373.0	494.5
115°	118.1	120.4	123.8	129.6	139.4	154.9	176.8	212.0	270.7	354.3	453.9
117.5°	132.7	135.3	138.3	143.5	154.5	168.8	190.6	221.9	271.8	343.2	429.4
120°	142.9	144.6	147.4	153.2	164.2	178.5	199.2	229.2	273.6	338.1	416.5
122.5°	151.6	153.3	156.2	162.4	172.9	188.2	208.5	236.2	276.8	334.9	405.9
125°	164.2	165.3	168.7	175.1	186.0	201.6	221.8	247.1	281.7	330.6	392.2
127.5°	173.7	175.4	179.8	186.1	198.2	213.8	233.3	256.1	287.2	328.5	380.3
130°	179.8	181.5	186.6	193.5	205.6	221.2	240.1	262.1	290.8	327.2	373.9
132.5°	184.3	186.5	192.2	200.5	212.6	227.6	246.2	267.6	293.7	326.7	367.8
135°	192.4	194.7	201.1	209.6	221.8	237.3	255.2	274.8	297.8	326.0	360.0
137.5°	200.0	202.4	208.6	217.8	229.8	244.2	261.4	280.0	300.5	324.8	353.3
140°	205.1	207.9	213.7	222.9	234.4	248.8	265.5	282.9	302.4	324.3	349.0
142.5°	210.6	213.0	219.2	227.5	239.0	252.6	268.7	285.6	303.8	323.4	345.4
145°	219.4	221.2	226.4	235.0	244.8	258.0	273.1	288.6	304.7	321.9	340.4
147.5°	228.4	229.4	234.6	242.1	251.5	262.8	276.5	290.4	304.7	319.8	335.6
150°	234.4	235.0	239.6	247.1	255.2	265.5	278.8	290.8	304.7	317.9	332.3
152.5°	240.4	240.5	245.2	251.8	258.8	268.7	280.1	291.9	303.4	315.7	328.7
155°	249.4	249.4	252.9	258.6	265.0	273.1	282.9	292.1	301.8	311.6	323.2
157.5°	256.5	257.0	259.7	264.9	270.2	276.5	284.3	292.7	299.8	308.0	316.9
160°	262.1	262.1	264.4	269.0	273.1	278.8	285.7	292.7	298.9	305.3	312.8
162.5°	266.2	266.2	268.1	271.8	275.3	280.1	286.2	292.2	297.1	302.6	308.6
165°	272.5	271.9	273.1	275.9	278.2	282.3	286.8	290.8	294.4	298.4	303.0
167.5°	277.2	276.5	277.0	279.2	280.8	283.4	286.7	289.9	291.5	294.2	297.6
170°	279.9	278.8	279.3	281.0	282.3	283.4	286.3	288.6	289.7	291.4	294.4
172.5°	281.8	281.0	281.2	282.5	283.2	283.9	286.3	288.1	288.3	289.1	291.1
175°	284.0	283.4	282.9	284.0	284.0	284.6	285.7	286.8	286.3	286.3	287.4
177.5°	285.0	284.6	284.1	284.6	284.6	284.6	285.0	285.9	285.0	284.6	285.0
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6



TEST NUMBER: P332371-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	18.8	18.7	18.5	18.5	18.1	17.9	17.7	17.3
90°	14.4	14.9	15.6	16.7	16.2	16.7	17.3	16.7
92.5°	48.5	38.5	34.0	31.0	30.0	28.2	28.8	27.8
95°	207.3	140.6	110.0	89.3	78.4	73.1	69.1	66.9
97.5°	516.9	414.0	339.7	270.8	228.3	202.4	186.8	181.9
100°	679.1	632.5	565.0	483.2	425.1	383.0	360.6	361.1
102.5°	733.1	731.5	692.3	640.4	595.1	561.8	543.0	529.8
105°	748.8	806.4	817.4	802.3	775.9	754.0	735.6	732.7
107.5°	703.4	797.0	847.4	867.9	868.4	861.0	854.7	849.5
110°	660.0	766.1	838.7	879.0	895.1	899.7	898.6	897.4



TEST NUMBER: P332371-840

CATALOG NUMBER: S123RDIP-S1165D585U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	617.2	725.5	806.9	858.7	888.2	902.5	906.9	907.1
115°	560.5	660.7	745.4	808.1	851.3	876.7	888.2	891.1
117.5°	519.3	605.8	681.9	745.6	790.6	819.6	836.3	840.1
120°	497.7	575.4	644.5	702.8	748.2	780.5	794.3	797.8
122.5°	480.6	551.0	615.0	669.0	709.5	738.5	753.8	758.1
125°	457.9	520.7	576.0	622.1	658.9	684.3	698.7	702.8
127.5°	438.1	494.1	544.0	585.9	618.7	640.4	653.4	657.1
130°	425.7	477.5	524.1	563.3	593.9	614.6	626.7	631.3
132.5°	414.1	461.8	505.2	542.6	571.3	592.0	602.7	605.9
135°	398.6	439.5	477.0	509.8	538.0	555.2	565.6	569.7
137.5°	384.5	418.0	450.2	478.7	502.4	519.9	528.7	531.3
140°	376.2	405.5	433.1	457.9	479.8	495.9	505.1	504.5
142.5°	368.3	393.5	417.5	439.0	457.7	472.0	480.3	479.7
145°	358.8	377.9	396.3	413.0	427.4	439.5	444.1	445.2
147.5°	351.1	366.2	381.1	392.9	403.8	412.0	416.5	416.9
150°	345.6	358.8	370.9	381.9	390.5	396.9	400.3	400.3
152.5°	340.5	351.9	362.6	371.7	378.5	384.5	386.5	386.5
155°	333.0	342.1	350.8	357.7	362.8	367.5	368.6	369.2
157.5°	324.9	332.5	339.3	344.7	349.2	352.6	353.6	353.5
160°	320.2	326.6	332.3	336.4	340.4	343.9	343.9	343.3
162.5°	314.8	320.1	325.5	329.0	331.6	334.7	334.7	334.1
165°	307.6	311.0	315.1	317.9	320.2	322.6	321.9	321.9
167.5°	301.3	304.0	306.3	308.4	309.4	311.0	310.4	310.4
170°	297.2	298.9	301.2	302.4	303.0	304.2	303.6	303.6
172.5°	293.6	294.8	296.6	297.3	297.4	298.6	297.6	297.1
175°	288.6	289.1	290.3	290.3	290.3	290.8	290.3	289.7
177.5°	285.5	285.9	286.4	286.4	285.9	286.4	285.5	285.5
180°	284.6	284.6	284.6	284.6	284.6	284.6	284.6	284.6

(END OF REPORT)