

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332372-840

Luminaire Tested: **S123RDIP-S1165D805U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332372-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7860.1 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	93	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	85	79	74	86	80	74	70	70	66	62	60	57	55	52	50	48	44
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	46	44	42	38
4	78	67	59	54	72	63	56	51	56	50	46	48	44	41	42	39	36	33
5	71	60	52	46	67	57	50	44	50	44	40	44	39	36	38	35	32	29
6	66	54	46	41	62	51	44	39	45	40	35	40	35	32	35	31	29	26
7	61	49	41	36	57	46	39	34	41	36	31	36	32	28	32	28	26	23
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	29	26	23	21
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19957	19957	19957	19957
5°	23791	20042	17650	20042
10°	29704	19928	15946	19928
15°	34867	19724	14540	19724
20°	38913	19420	13347	19420
25°	38292	19099	12613	19099
30°	27524	18804	11857	18804
35°	18378	18419	11369	18419
40°	13540	17956	10863	17956
45°	11357	17145	10368	17145
50°	10021	16083	9676	16083
55°	8788	14865	8728	14865
60°	7828	13702	7995	13702
65°	6872	12455	7440	12455
70°	5397	11339	6795	11339
75°	4754	9902	6209	9902
80°	4135	8412	6106	8412
85°	3335	6756	6472	6756



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.3	2.3
10°-20°	569.6	7.2
20°-30°	894.9	11.4
30°-40°	933.7	11.9
40°-50°	799.0	10.2
50°-60°	609.0	7.7
60°-70°	390.4	5.0
70°-80°	187.8	2.4
80°-90°	52.7	0.7
90°-100°	38.6	0.5
100°-110°	184.1	2.3
110°-120°	442.3	5.6
120°-130°	563.2	7.2
130°-140°	601.8	7.7
140°-150°	562.7	7.2
150°-160°	453.9	5.8
160°-170°	293.0	3.7
170°-180°	101.0	1.3
0°-30°	1646.9	21.0
0°-40°	2580.6	32.8
0°-60°	3988.6	50.7
0°-90°	4619.5	58.8
90°-120°	665.1	8.5
90°-150°	2392.8	30.4
90°-180°	3241.0	41.2
0°-180°	7860.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1854	1854	1854	1854	1854	
5°	2202	1855	1634	1855	2202	227
15°	3129	1770	1305	1770	3129	887
25°	3224	1608	1062	1608	3224	1386
35°	1399	1402	865	1402	1399	917
45°	746	1126	681	1126	746	587
55°	468	792	465	792	468	423
65°	270	489	292	489	270	265
75°	114	238	149	238	114	123
85°	27	55	52	55	27	32
90°	24	1	24	1	24	12
95°	30	48	30	48	30	25
105°	35	235	35	235	35	79
115°	464	441	464	441	464	429
125°	635	622	635	622	635	567
135°	782	774	782	774	782	603
145°	902	894	902	894	902	563
155°	983	984	983	984	983	453
165°	1036	1038	1036	1038	1036	292
175°	1059	1063	1059	1063	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1974.8	1977.3	1969.0	1967.8	1958.2	1955.7	1955.7	1942.4	1934.1	1923.4	1917.0
5°	2201.8	2214.5	2208.2	2193.8	2170.0	2164.4	2149.4	2125.6	2098.6	2065.3	2049.4
7.5°	2485.3	2502.6	2496.0	2473.9	2448.9	2428.8	2386.2	2346.7	2291.3	2242.7	2201.1
10°	2717.7	2699.5	2685.1	2663.7	2640.7	2603.4	2559.0	2497.8	2427.2	2371.7	2309.8
12.5°	2891.6	2888.7	2870.5	2848.5	2816.0	2780.6	2725.9	2651.5	2569.4	2489.1	2418.3
15°	3128.9	3133.6	3121.7	3098.7	3052.6	2989.9	2907.4	2876.5	2759.0	2671.7	2584.3
17.5°	3293.0	3292.1	3290.4	3258.5	3211.6	3166.9	3090.4	3009.0	2902.7	2779.7	2662.0
20°	3397.1	3389.2	3390.8	3355.1	3320.1	3268.5	3193.9	3075.6	2988.4	2846.3	2724.8
22.5°	3394.6	3393.0	3399.0	3386.8	3361.4	3321.8	3263.2	3163.3	3051.9	2908.5	2771.9
25°	3224.1	3217.7	3255.1	3265.4	3305.9	3313.0	3295.5	3240.8	3135.2	2987.6	2818.5
27.5°	2698.4	2694.8	2764.1	2850.7	2960.6	3046.0	3128.6	3168.4	3135.2	3029.5	2860.1
30°	2214.5	2289.1	2324.0	2449.4	2589.1	2755.8	2901.8	3040.7	3074.8	3028.9	2889.9
32.5°	1838.6	1903.7	1932.9	2040.5	2170.7	2365.9	2585.0	2781.7	2920.6	2955.8	2872.2
35°	1398.6	1399.4	1466.0	1513.6	1634.3	1835.1	2047.8	2311.3	2573.2	2771.7	2792.3
37.5°	1116.0	1119.9	1160.2	1207.7	1298.2	1404.4	1591.7	1810.8	2113.3	2418.0	2596.6
40°	963.6	970.7	1000.9	1047.7	1112.8	1193.0	1339.0	1545.4	1797.8	2136.7	2413.7
42.5°	865.8	877.4	892.9	929.0	969.3	1044.4	1162.5	1321.9	1551.5	1871.9	2191.5
45°	746.1	752.5	764.4	781.0	817.5	869.9	949.3	1056.4	1247.0	1504.9	1824.7
47.5°	658.1	654.8	667.3	680.9	705.2	740.8	794.1	881.5	1017.4	1224.4	1495.7
50°	598.4	597.6	606.4	616.7	639.7	665.9	709.6	775.5	883.4	1054.9	1303.3
52.5°	542.6	545.6	551.8	564.6	581.3	602.5	641.7	689.1	781.8	929.8	1136.9
55°	468.3	470.7	479.4	486.6	498.5	519.9	544.5	584.2	647.7	750.8	921.5
57.5°	405.5	404.3	412.7	414.4	428.0	445.5	464.4	495.2	541.3	618.0	733.0
60°	363.6	361.1	368.3	373.9	381.0	395.3	411.1	441.3	477.9	534.2	632.6
62.5°	325.4	324.3	329.5	335.1	341.0	354.0	367.3	390.5	419.4	466.9	544.9
65°	269.8	272.3	274.6	277.0	280.1	288.1	300.8	316.7	336.6	369.9	426.3
67.5°	212.1	214.5	215.3	220.2	227.0	232.0	239.7	253.9	267.6	295.8	327.8
70°	171.5	170.7	171.5	173.8	182.6	191.3	201.6	212.0	220.7	240.4	267.5
72.5°	147.3	145.9	147.9	148.5	152.7	155.1	161.6	171.3	182.6	196.0	215.4
75°	114.3	114.3	114.3	114.3	117.4	119.1	121.5	123.8	127.7	134.1	148.5
77.5°	84.4	84.6	85.7	86.5	87.2	88.1	89.6	91.9	93.3	96.6	102.9
80°	66.7	67.5	66.7	67.5	67.5	69.1	69.9	72.2	73.0	77.0	79.4
82.5°	50.2	49.7	50.2	51.0	51.0	52.5	52.7	54.4	54.6	56.7	59.1
85°	27.0	25.4	27.0	26.2	27.8	26.2	27.0	28.6	28.6	29.4	32.5
87.5°	11.1	12.3	10.9	11.5	11.4	12.0	11.8	11.7	12.8	12.0	12.2
90°	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4	19.7	19.0	16.7
92.5°	26.3	26.0	25.8	25.5	25.3	24.7	23.5	22.4	21.3	20.2	18.5
95°	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0	25.8	24.4	22.5
97.5°	32.5	32.3	32.2	32.0	31.8	31.0	29.6	28.3	26.9	25.4	38.1
100°	33.1	33.0	32.8	32.6	32.4	31.7	30.3	28.9	27.5	26.1	53.4
102.5°	33.8	33.4	33.1	32.8	32.5	34.5	38.9	43.2	47.6	51.9	81.8
105°	34.7	34.4	34.0	33.7	33.3	48.7	79.8	110.8	141.9	172.9	188.6
107.5°	109.1	132.5	155.9	179.4	202.7	225.8	248.6	271.4	294.2	316.9	314.4
110°	217.1	242.2	267.3	292.4	317.5	333.0	338.7	344.5	350.3	356.1	354.2



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.5	377.8	383.0	388.4	393.6	396.3	396.2	396.1	396.0	395.9	393.9
115°	464.2	463.5	462.8	462.1	461.4	460.2	458.5	456.7	454.9	453.2	451.6
117.5°	515.7	515.5	515.4	515.3	515.1	514.3	513.0	511.6	510.2	508.8	508.0
120°	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.5	546.1	544.7	544.2
122.5°	585.8	585.7	585.5	585.4	585.2	584.7	583.7	582.7	581.8	580.8	580.1
125°	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3	632.0	631.6	630.9
127.5°	681.9	682.2	682.6	682.9	683.2	683.1	682.6	682.0	681.5	680.9	680.0
130°	712.2	712.5	712.9	713.2	713.6	713.4	712.7	712.0	711.2	710.5	709.8
132.5°	739.9	740.4	740.9	741.4	741.8	741.7	741.0	740.3	739.7	739.0	738.4
135°	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4	781.7
137.5°	822.3	822.7	823.0	823.4	823.7	823.5	822.6	821.8	821.0	820.1	819.7
140°	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2	845.5	844.8	844.2
142.5°	868.5	869.0	869.4	869.9	870.4	870.4	869.8	869.3	868.7	868.2	867.6
145°	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5	901.2	900.8	900.5
147.5°	927.7	928.5	929.3	930.1	930.9	931.1	930.8	930.4	930.1	929.7	929.4
150°	946.6	947.2	947.7	948.2	948.8	948.8	948.5	948.1	947.8	947.5	947.1
152.5°	961.8	962.6	963.4	964.2	965.0	965.1	964.4	963.8	963.2	962.6	962.4
155°	982.9	984.0	985.0	986.1	987.1	987.2	986.3	985.5	984.6	983.7	983.5
157.5°	1000.8	1002.2	1003.5	1004.9	1006.2	1006.4	1005.3	1004.3	1003.3	1002.2	1002.4
160°	1012.2	1013.4	1014.6	1015.8	1017.0	1017.1	1016.1	1015.0	1014.0	1012.9	1013.1
162.5°	1022.9	1024.0	1025.0	1026.1	1027.2	1027.1	1026.0	1024.8	1023.6	1022.4	1022.6
165°	1035.8	1037.0	1038.2	1039.6	1040.8	1040.7	1039.3	1037.8	1036.4	1035.0	1035.2
167.5°	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1	1045.1
170°	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9	1050.9
172.5°	1054.0	1055.5	1057.1	1058.6	1060.2	1060.3	1058.8	1057.4	1056.0	1054.6	1054.5
175°	1058.7	1060.2	1061.6	1063.0	1064.3	1064.4	1063.2	1062.0	1060.8	1059.6	1059.3
177.5°	1060.2	1061.6	1063.0	1064.4	1065.8	1065.9	1064.8	1063.7	1062.6	1061.4	1061.3
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1914.5	1912.6	1903.7	1893.5	1880.2	1871.3	1864.3	1860.5	1849.1	1835.1	1825.5
5°	2032.8	2008.9	1983.5	1952.6	1924.0	1894.6	1876.3	1854.9	1828.8	1799.4	1778.8
7.5°	2159.4	2112.7	2062.4	2010.5	1959.2	1913.2	1872.6	1837.8	1796.0	1753.9	1724.4
10°	2256.5	2188.3	2117.7	2045.4	1979.5	1917.6	1870.0	1823.2	1773.2	1724.7	1688.3
12.5°	2344.8	2254.9	2173.5	2084.8	2000.5	1926.5	1857.9	1802.8	1742.7	1691.1	1649.5
15°	2456.6	2364.5	2266.0	2131.1	2019.2	1925.6	1842.2	1770.0	1697.0	1633.5	1593.0
17.5°	2561.0	2422.5	2290.2	2177.7	2032.3	1915.2	1813.5	1727.2	1647.0	1579.6	1529.8
20°	2604.2	2470.0	2326.4	2182.7	2039.8	1908.9	1790.6	1695.4	1612.0	1535.8	1489.9
22.5°	2630.2	2478.3	2327.0	2172.6	2020.8	1884.8	1767.8	1663.0	1572.7	1500.3	1443.5
25°	2660.6	2479.6	2312.9	2160.5	2005.7	1858.2	1719.2	1608.1	1510.5	1433.5	1373.1
27.5°	2680.6	2467.7	2270.7	2101.3	1944.3	1797.3	1670.0	1552.2	1453.2	1371.7	1307.0
30°	2684.3	2458.1	2238.3	2055.0	1895.4	1760.5	1625.6	1512.9	1408.1	1321.5	1261.2
32.5°	2689.5	2434.7	2194.4	1999.7	1836.3	1702.7	1580.4	1472.8	1365.5	1280.3	1218.7
35°	2668.5	2421.7	2128.0	1904.1	1740.6	1611.2	1501.0	1401.7	1296.2	1213.6	1150.9
37.5°	2578.3	2370.1	2059.1	1796.5	1625.6	1505.7	1415.8	1329.3	1232.5	1143.5	1084.4
40°	2487.5	2319.3	2005.7	1731.1	1552.6	1429.5	1348.6	1277.9	1184.3	1100.9	1037.4
42.5°	2352.3	2250.1	1954.9	1662.5	1470.0	1351.4	1283.1	1216.9	1134.7	1050.1	990.4
45°	2104.2	2117.7	1851.0	1553.3	1355.6	1236.6	1172.4	1126.3	1053.3	983.4	922.3
47.5°	1793.0	1919.2	1728.9	1436.9	1235.2	1123.5	1067.2	1027.0	977.9	909.3	853.5
50°	1589.8	1770.0	1631.1	1358.9	1159.6	1048.5	992.9	960.4	917.6	863.5	810.4
52.5°	1402.5	1596.0	1513.0	1271.8	1077.7	976.1	921.8	895.0	861.0	810.2	762.1
55°	1143.8	1339.8	1320.8	1140.5	954.8	863.5	822.3	792.1	769.1	731.0	693.0
57.5°	925.1	1111.1	1120.8	994.5	846.6	756.4	720.8	698.1	683.1	654.4	619.1
60°	787.4	958.1	991.4	896.2	769.1	689.7	654.8	636.5	624.7	601.7	574.6
62.5°	673.1	818.3	856.1	787.5	694.8	620.6	593.2	575.6	567.5	547.6	523.8
65°	515.1	635.8	672.3	634.2	585.7	526.2	504.0	489.0	481.8	470.7	453.2
67.5°	387.4	475.2	515.3	488.5	471.0	433.3	419.2	411.1	404.8	397.2	382.5
70°	311.1	376.2	417.5	410.3	396.1	376.2	365.9	360.3	354.0	347.7	335.0
72.5°	250.1	295.0	333.7	337.3	325.6	321.6	312.6	310.2	306.4	298.7	291.8
75°	165.9	196.8	223.8	234.2	238.9	242.9	238.9	238.1	237.3	231.0	227.0
77.5°	108.8	125.4	142.4	160.1	167.4	172.9	174.1	177.0	174.9	171.6	169.7
80°	83.3	87.4	99.2	114.3	126.2	131.0	134.1	135.7	134.9	134.1	131.0
82.5°	60.5	63.8	69.4	80.0	90.0	98.0	99.9	99.6	101.3	101.8	99.2
85°	32.5	33.3	34.9	36.6	42.1	50.8	53.2	54.7	56.4	56.4	51.6
87.5°	13.0	11.9	12.7	12.3	13.9	14.2	17.7	20.5	21.5	19.3	19.6
90°	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	16.8	15.0	13.3	12.7	13.2	13.7	14.2	14.6	14.2	13.7	13.2
95°	20.6	18.7	16.8	19.4	26.6	33.7	41.0	48.2	41.0	33.7	26.6
97.5°	50.7	63.3	75.9	83.9	87.2	90.4	93.6	96.7	93.6	90.4	87.2
100°	80.8	108.2	135.5	147.4	143.9	140.5	136.9	133.4	136.9	140.5	143.9
102.5°	111.7	141.7	171.6	185.2	182.7	180.2	177.6	175.1	177.6	180.2	182.7
105°	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3	237.2	239.1	241.1
107.5°	311.9	309.4	306.9	304.9	303.4	301.8	300.3	298.7	300.3	301.8	303.4
110°	352.2	350.3	348.3	346.7	345.3	343.9	342.4	341.0	342.4	343.9	345.3



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.0	390.1	388.1	386.6	385.3	384.1	382.7	381.5	382.7	384.1	385.3
115°	450.0	448.5	446.9	445.6	444.5	443.4	442.4	441.3	442.4	443.4	444.5
117.5°	507.2	506.3	505.5	504.4	503.2	501.9	500.6	499.3	500.6	501.9	503.2
120°	543.7	543.2	542.7	541.6	540.0	538.5	536.8	535.3	536.8	538.5	540.0
122.5°	579.5	578.8	578.0	577.1	575.8	574.5	573.2	571.9	573.2	574.5	575.8
125°	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.2	623.5	624.9	626.3
127.5°	679.2	678.3	677.5	676.4	675.0	673.6	672.2	670.8	672.2	673.6	675.0
130°	709.1	708.4	707.7	706.7	705.3	703.9	702.5	701.0	702.5	703.9	705.3
132.5°	737.8	737.3	736.7	735.8	734.4	733.0	731.5	730.1	731.5	733.0	734.4
135°	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5	775.6	776.6	777.7
137.5°	819.4	819.0	818.6	817.7	816.4	815.1	813.7	812.4	813.7	815.1	816.4
140°	843.7	843.2	842.6	841.9	840.8	839.8	838.7	837.7	838.7	839.8	840.8
142.5°	867.1	866.6	866.1	865.3	864.2	863.1	862.1	861.0	862.1	863.1	864.2
145°	900.1	899.8	899.4	898.7	897.4	896.2	894.9	893.7	894.9	896.2	897.4
147.5°	929.0	928.7	928.4	927.8	927.0	926.1	925.3	924.5	925.3	926.1	927.0
150°	946.7	946.3	946.0	945.5	945.0	944.5	944.0	943.4	944.0	944.5	945.0
152.5°	962.1	961.9	961.7	961.5	961.3	961.0	960.8	960.5	960.8	961.0	961.3
155°	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5	984.2	983.8	983.5
157.5°	1002.6	1002.7	1002.9	1003.0	1003.0	1003.1	1003.1	1003.1	1003.1	1003.1	1003.0
160°	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5	1014.3	1014.2	1014.0
162.5°	1022.8	1022.9	1023.1	1023.4	1023.9	1024.3	1024.8	1025.2	1024.8	1024.3	1023.9
165°	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.6	1038.2	1037.6	1037.1	1036.6
167.5°	1045.1	1045.1	1045.1	1045.5	1046.2	1046.9	1047.6	1048.3	1047.6	1046.9	1046.2
170°	1050.9	1050.9	1050.9	1051.2	1051.9	1052.6	1053.3	1054.0	1053.3	1052.6	1051.9
172.5°	1054.3	1054.2	1054.1	1054.4	1055.2	1056.1	1056.9	1057.7	1056.9	1056.1	1055.2
175°	1059.1	1058.9	1058.8	1059.1	1060.1	1061.0	1061.8	1062.7	1061.8	1061.0	1060.1
177.5°	1061.2	1061.0	1060.9	1061.2	1061.9	1062.6	1063.3	1063.9	1063.3	1062.6	1061.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1822.4	1814.1	1808.5	1795.7	1787.5	1778.6	1769.7	1775.4	1774.7	1774.1	1774.1
5°	1761.3	1743.0	1726.4	1705.0	1691.4	1674.8	1662.0	1660.4	1663.7	1652.5	1646.2
7.5°	1700.6	1675.7	1652.0	1628.4	1603.4	1583.4	1570.7	1564.9	1556.8	1549.9	1542.9
10°	1658.1	1628.7	1605.7	1576.3	1549.3	1525.5	1510.5	1500.2	1494.6	1489.0	1478.7
12.5°	1614.3	1585.6	1556.2	1523.0	1497.3	1469.7	1458.3	1446.8	1436.1	1430.0	1415.8
15°	1550.1	1512.9	1481.9	1446.9	1418.4	1391.4	1375.5	1352.5	1349.3	1341.4	1327.1
17.5°	1485.8	1445.3	1402.7	1376.7	1344.5	1316.5	1292.3	1284.5	1261.8	1253.2	1240.9
20°	1435.0	1397.8	1365.2	1331.1	1284.2	1258.1	1239.0	1228.7	1210.4	1199.3	1191.3
22.5°	1391.2	1353.3	1315.7	1275.9	1237.3	1207.9	1194.0	1177.9	1167.9	1152.4	1143.8
25°	1328.7	1287.4	1242.1	1199.3	1171.5	1149.3	1127.1	1112.8	1098.5	1091.4	1075.5
27.5°	1256.0	1212.8	1170.5	1138.0	1103.9	1082.0	1061.9	1049.1	1032.0	1020.0	1011.2
30°	1216.0	1165.2	1128.6	1099.3	1055.6	1035.0	1020.0	1004.1	991.4	978.7	970.0
32.5°	1169.6	1123.3	1088.6	1052.3	1018.9	996.2	976.7	962.8	952.0	939.9	931.2
35°	1096.9	1058.0	1022.3	985.8	961.2	938.2	915.1	903.2	892.9	881.8	873.9
37.5°	1031.2	994.8	960.9	926.2	895.8	877.1	858.5	849.4	835.5	828.0	819.9
40°	990.6	954.8	918.4	885.0	853.2	839.0	822.3	808.8	796.1	790.5	781.8
42.5°	946.1	910.4	879.6	843.7	817.7	798.3	782.9	768.2	758.6	750.5	745.6
45°	880.2	848.5	818.3	782.6	758.0	741.3	723.9	710.3	701.7	696.1	687.3
47.5°	816.3	784.6	753.9	722.8	698.9	679.9	662.5	653.1	641.5	634.7	628.7
50°	769.9	741.3	708.8	680.2	656.4	637.3	623.1	611.2	600.9	592.1	588.1
52.5°	727.4	696.9	668.8	642.1	617.0	595.4	582.4	569.9	562.1	552.1	547.5
55°	657.2	627.8	604.0	577.8	553.2	534.9	519.1	508.0	500.1	489.0	482.6
57.5°	591.3	565.0	536.5	513.8	488.5	473.0	459.9	444.8	435.2	426.4	420.2
60°	546.8	516.7	492.1	470.7	448.5	428.6	416.7	404.8	394.5	385.8	380.2
62.5°	500.5	474.1	450.8	427.5	407.2	389.9	376.1	366.1	357.0	351.4	345.9
65°	429.4	408.8	385.0	365.9	346.9	334.2	323.1	314.3	308.0	304.0	299.2
67.5°	364.0	344.0	323.2	304.5	291.8	282.1	274.8	267.3	264.2	259.0	255.9
70°	321.4	300.8	282.6	268.3	255.6	248.4	243.7	238.1	234.9	228.6	225.4
72.5°	275.1	260.1	247.0	235.3	225.1	218.6	212.6	205.7	200.7	193.7	190.5
75°	216.7	203.2	192.9	184.9	178.5	169.9	161.2	154.0	151.6	149.3	148.5
77.5°	160.5	151.9	144.4	137.7	129.9	123.5	121.6	120.0	119.6	118.3	118.3
80°	126.2	118.3	112.7	104.7	100.0	100.0	100.0	98.5	99.2	99.2	99.2
82.5°	93.8	86.5	83.5	80.7	79.7	80.3	80.3	80.7	80.2	81.4	80.8
85°	48.4	49.2	50.8	50.0	50.8	50.8	52.4	51.6	52.4	50.8	52.4
87.5°	19.4	21.6	22.7	23.8	24.9	24.7	25.5	25.7	26.5	26.6	26.7
90°	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4	21.0	21.7	22.3
92.5°	12.7	13.3	15.0	16.8	18.5	20.2	21.3	22.4	23.5	24.7	25.3
95°	19.4	16.8	18.7	20.6	22.5	24.4	25.8	27.0	28.2	29.4	30.0
97.5°	83.9	75.9	63.3	50.7	38.1	25.4	26.9	28.3	29.6	31.0	31.8
100°	147.4	135.5	108.2	80.8	53.4	26.1	27.5	28.9	30.3	31.7	32.4
102.5°	185.2	171.6	141.7	111.7	81.8	51.9	47.6	43.2	38.9	34.5	32.5
105°	243.0	236.1	220.3	204.5	188.6	172.9	141.9	110.8	79.8	48.7	33.3
107.5°	304.9	306.9	309.4	311.9	314.4	316.9	294.2	271.4	248.6	225.8	202.7
110°	346.7	348.3	350.3	352.2	354.2	356.1	350.3	344.5	338.7	333.0	317.5



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.6	388.1	390.1	392.0	393.9	395.9	396.0	396.1	396.2	396.3	393.6
115°	445.6	446.9	448.5	450.0	451.6	453.2	454.9	456.7	458.5	460.2	461.4
117.5°	504.4	505.5	506.3	507.2	508.0	508.8	510.2	511.6	513.0	514.3	515.1
120°	541.6	542.7	543.2	543.7	544.2	544.7	546.1	547.5	549.0	550.4	551.1
122.5°	577.1	578.0	578.8	579.5	580.1	580.8	581.8	582.7	583.7	584.7	585.2
125°	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3	632.7	633.0	633.4
127.5°	676.4	677.5	678.3	679.2	680.0	680.9	681.5	682.0	682.6	683.1	683.2
130°	706.7	707.7	708.4	709.1	709.8	710.5	711.2	712.0	712.7	713.4	713.6
132.5°	735.8	736.7	737.3	737.8	738.4	739.0	739.7	740.3	741.0	741.7	741.8
135°	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5	784.0	784.5	784.5
137.5°	817.7	818.6	819.0	819.4	819.7	820.1	821.0	821.8	822.6	823.5	823.7
140°	841.9	842.6	843.2	843.7	844.2	844.8	845.5	846.2	846.9	847.6	847.8
142.5°	865.3	866.1	866.6	867.1	867.6	868.2	868.7	869.3	869.8	870.4	870.4
145°	898.7	899.4	899.8	900.1	900.5	900.8	901.2	901.5	901.9	902.2	902.4
147.5°	927.8	928.4	928.7	929.0	929.4	929.7	930.1	930.4	930.8	931.1	930.9
150°	945.5	946.0	946.3	946.7	947.1	947.5	947.8	948.1	948.5	948.8	948.8
152.5°	961.5	961.7	961.9	962.1	962.4	962.6	963.2	963.8	964.4	965.1	965.0
155°	983.1	983.0	983.2	983.4	983.5	983.7	984.6	985.5	986.3	987.2	987.1
157.5°	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3	1004.3	1005.3	1006.4	1006.2
160°	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0	1016.1	1017.1	1017.0
162.5°	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6	1024.8	1026.0	1027.1	1027.2
165°	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.8	1039.3	1040.7	1040.8
167.5°	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8
170°	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4
172.5°	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0	1057.4	1058.8	1060.3	1060.2
175°	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8	1062.0	1063.2	1064.4	1064.3
177.5°	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6	1063.7	1064.8	1065.9	1065.8
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1766.6	1765.8	1766.6	1763.9	1766.6	1765.8	1766.6	1774.1	1774.1	1774.7	1775.4
5°	1643.8	1643.1	1640.6	1633.5	1640.6	1643.1	1643.8	1646.2	1652.5	1663.7	1660.4
7.5°	1536.6	1535.5	1528.5	1528.7	1528.5	1535.5	1536.6	1542.9	1549.9	1556.8	1564.9
10°	1473.2	1473.9	1464.4	1458.9	1464.4	1473.9	1473.2	1478.7	1489.0	1494.6	1500.2
12.5°	1411.6	1408.0	1400.3	1394.1	1400.3	1408.0	1411.6	1415.8	1430.0	1436.1	1446.8
15°	1330.3	1322.3	1303.3	1304.8	1303.3	1322.3	1330.3	1327.1	1341.4	1349.3	1352.5
17.5°	1234.6	1228.7	1228.4	1217.3	1228.4	1228.7	1234.6	1240.9	1253.2	1261.8	1284.5
20°	1178.7	1174.7	1176.3	1165.2	1176.3	1174.7	1178.7	1191.3	1199.3	1210.4	1228.7
22.5°	1134.9	1130.8	1124.2	1120.7	1124.2	1130.8	1134.9	1143.8	1152.4	1167.9	1177.9
25°	1070.8	1064.4	1058.0	1062.0	1058.0	1064.4	1070.8	1075.5	1091.4	1098.5	1112.8
27.5°	1006.6	1001.9	995.5	994.7	995.5	1001.9	1006.6	1011.2	1020.0	1032.0	1049.1
30°	965.9	961.2	958.1	954.0	958.1	961.2	965.9	970.0	978.7	991.4	1004.1
32.5°	924.7	923.7	918.1	917.3	918.1	923.7	924.7	931.2	939.9	952.0	962.8
35°	870.7	866.0	864.3	865.2	864.3	866.0	870.7	873.9	881.8	892.9	903.2
37.5°	819.4	813.0	810.2	807.4	810.2	813.0	819.4	819.9	828.0	835.5	849.4
40°	782.6	776.3	774.7	773.1	774.7	776.3	782.6	781.8	790.5	796.1	808.8
42.5°	741.3	738.8	737.8	735.0	737.8	738.8	741.3	745.6	750.5	758.6	768.2
45°	685.0	684.2	679.4	681.1	679.4	684.2	685.0	687.3	696.1	701.7	710.3
47.5°	625.6	622.1	618.7	621.0	618.7	622.1	625.6	628.7	634.7	641.5	653.1
50°	585.0	583.4	576.2	577.8	576.2	583.4	585.0	588.1	592.1	600.9	611.2
52.5°	544.3	538.3	535.6	534.6	535.6	538.3	544.3	547.5	552.1	562.1	569.9
55°	477.1	469.9	466.7	465.1	466.7	469.9	477.1	482.6	489.0	500.1	508.0
57.5°	411.0	409.1	406.6	408.3	406.6	409.1	411.0	420.2	426.4	435.2	444.8
60°	372.2	372.2	372.2	371.4	372.2	372.2	372.2	380.2	385.8	394.5	404.8
62.5°	342.4	340.5	339.9	341.0	339.9	340.5	342.4	345.9	351.4	357.0	366.1
65°	296.9	296.1	292.9	292.1	292.9	296.1	296.9	299.2	304.0	308.0	314.3
67.5°	253.9	251.0	250.0	248.9	250.0	251.0	253.9	255.9	259.0	264.2	267.3
70°	221.5	219.8	215.1	215.9	215.1	219.8	221.5	225.4	228.6	234.9	238.1
72.5°	186.5	184.9	184.0	182.9	184.0	184.9	186.5	190.5	193.7	200.7	205.7
75°	147.6	146.8	146.0	149.3	146.0	146.8	147.6	148.5	149.3	151.6	154.0
77.5°	118.3	118.3	118.8	117.4	118.8	118.3	118.3	118.3	118.3	119.6	120.0
80°	99.2	99.2	98.5	98.5	98.5	99.2	99.2	99.2	99.2	99.2	98.5
82.5°	79.6	80.2	80.7	79.4	80.7	80.2	79.6	80.8	81.4	80.2	80.7
85°	52.4	51.6	53.2	52.4	53.2	51.6	52.4	52.4	50.8	52.4	51.6
87.5°	28.0	26.9	26.9	27.6	26.9	26.9	28.0	26.7	26.6	26.5	25.7
90°	22.6	23.0	23.3	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4
92.5°	25.5	25.8	26.0	26.3	26.0	25.8	25.5	25.3	24.7	23.5	22.4
95°	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0
97.5°	32.0	32.2	32.3	32.5	32.3	32.2	32.0	31.8	31.0	29.6	28.3
100°	32.6	32.8	33.0	33.1	33.0	32.8	32.6	32.4	31.7	30.3	28.9
102.5°	32.8	33.1	33.4	33.8	33.4	33.1	32.8	32.5	34.5	38.9	43.2
105°	33.7	34.0	34.4	34.7	34.4	34.0	33.7	33.3	48.7	79.8	110.8
107.5°	179.4	155.9	132.5	109.1	132.5	155.9	179.4	202.7	225.8	248.6	271.4
110°	292.4	267.3	242.2	217.1	242.2	267.3	292.4	317.5	333.0	338.7	344.5



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	388.4	383.0	377.8	372.5	377.8	383.0	388.4	393.6	396.3	396.2	396.1
115°	462.1	462.8	463.5	464.2	463.5	462.8	462.1	461.4	460.2	458.5	456.7
117.5°	515.3	515.4	515.5	515.7	515.5	515.4	515.3	515.1	514.3	513.0	511.6
120°	551.1	551.1	551.1	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.5
122.5°	585.4	585.5	585.7	585.8	585.7	585.5	585.4	585.2	584.7	583.7	582.7
125°	633.7	634.1	634.4	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3
127.5°	682.9	682.6	682.2	681.9	682.2	682.6	682.9	683.2	683.1	682.6	682.0
130°	713.2	712.9	712.5	712.2	712.5	712.9	713.2	713.6	713.4	712.7	712.0
132.5°	741.4	740.9	740.4	739.9	740.4	740.9	741.4	741.8	741.7	741.0	740.3
135°	784.0	783.5	782.9	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5
137.5°	823.4	823.0	822.7	822.3	822.7	823.0	823.4	823.7	823.5	822.6	821.8
140°	847.4	847.1	846.7	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2
142.5°	869.9	869.4	869.0	868.5	869.0	869.4	869.9	870.4	870.4	869.8	869.3
145°	902.4	902.4	902.4	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5
147.5°	930.1	929.3	928.5	927.7	928.5	929.3	930.1	930.9	931.1	930.8	930.4
150°	948.2	947.7	947.2	946.6	947.2	947.7	948.2	948.8	948.8	948.5	948.1
152.5°	964.2	963.4	962.6	961.8	962.6	963.4	964.2	965.0	965.1	964.4	963.8
155°	986.1	985.0	984.0	982.9	984.0	985.0	986.1	987.1	987.2	986.3	985.5
157.5°	1004.9	1003.5	1002.2	1000.8	1002.2	1003.5	1004.9	1006.2	1006.4	1005.3	1004.3
160°	1015.8	1014.6	1013.4	1012.2	1013.4	1014.6	1015.8	1017.0	1017.1	1016.1	1015.0
162.5°	1026.1	1025.0	1024.0	1022.9	1024.0	1025.0	1026.1	1027.2	1027.1	1026.0	1024.8
165°	1039.6	1038.2	1037.0	1035.8	1037.0	1038.2	1039.6	1040.8	1040.7	1039.3	1037.8
167.5°	1049.4	1047.9	1046.5	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9
170°	1055.0	1053.6	1052.3	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6
172.5°	1058.6	1057.1	1055.5	1054.0	1055.5	1057.1	1058.6	1060.2	1060.3	1058.8	1057.4
175°	1063.0	1061.6	1060.2	1058.7	1060.2	1061.6	1063.0	1064.3	1064.4	1063.2	1062.0
177.5°	1064.4	1063.0	1061.6	1060.2	1061.6	1063.0	1064.4	1065.8	1065.9	1064.8	1063.7
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1769.7	1778.6	1787.5	1795.7	1808.5	1814.1	1822.4	1825.5	1835.1	1849.1	1860.5
5°	1662.0	1674.8	1691.4	1705.0	1726.4	1743.0	1761.3	1778.8	1799.4	1828.8	1854.9
7.5°	1570.7	1583.4	1603.4	1628.4	1652.0	1675.7	1700.6	1724.4	1753.9	1796.0	1837.8
10°	1510.5	1525.5	1549.3	1576.3	1605.7	1628.7	1658.1	1688.3	1724.7	1773.2	1823.2
12.5°	1458.3	1469.7	1497.3	1523.0	1556.2	1585.6	1614.3	1649.5	1691.1	1742.7	1802.8
15°	1375.5	1391.4	1418.4	1446.9	1481.9	1512.9	1550.1	1593.0	1633.5	1697.0	1770.0
17.5°	1292.3	1316.5	1344.5	1376.7	1402.7	1445.3	1485.8	1529.8	1579.6	1647.0	1727.2
20°	1239.0	1258.1	1284.2	1331.1	1365.2	1397.8	1435.0	1489.9	1535.8	1612.0	1695.4
22.5°	1194.0	1207.9	1237.3	1275.9	1315.7	1353.3	1391.2	1443.5	1500.3	1572.7	1663.0
25°	1127.1	1149.3	1171.5	1199.3	1242.1	1287.4	1328.7	1373.1	1433.5	1510.5	1608.1
27.5°	1061.9	1082.0	1103.9	1138.0	1170.5	1212.8	1256.0	1307.0	1371.7	1453.2	1552.2
30°	1020.0	1035.0	1055.6	1099.3	1128.6	1165.2	1216.0	1261.2	1321.5	1408.1	1512.9
32.5°	976.7	996.2	1018.9	1052.3	1088.6	1123.3	1169.6	1218.7	1280.3	1365.5	1472.8
35°	915.1	938.2	961.2	985.8	1022.3	1058.0	1096.9	1150.9	1213.6	1296.2	1401.7
37.5°	858.5	877.1	895.8	926.2	960.9	994.8	1031.2	1084.4	1143.5	1232.5	1329.3
40°	822.3	839.0	853.2	885.0	918.4	954.8	990.6	1037.4	1100.9	1184.3	1277.9
42.5°	782.9	798.3	817.7	843.7	879.6	910.4	946.1	990.4	1050.1	1134.7	1216.9
45°	723.9	741.3	758.0	782.6	818.3	848.5	880.2	922.3	983.4	1053.3	1126.3
47.5°	662.5	679.9	698.9	722.8	753.9	784.6	816.3	853.5	909.3	977.9	1027.0
50°	623.1	637.3	656.4	680.2	708.8	741.3	769.9	810.4	863.5	917.6	960.4
52.5°	582.4	595.4	617.0	642.1	668.8	696.9	727.4	762.1	810.2	861.0	895.0
55°	519.1	534.9	553.2	577.8	604.0	627.8	657.2	693.0	731.0	769.1	792.1
57.5°	459.9	473.0	488.5	513.8	536.5	565.0	591.3	619.1	654.4	683.1	698.1
60°	416.7	428.6	448.5	470.7	492.1	516.7	546.8	574.6	601.7	624.7	636.5
62.5°	376.1	389.9	407.2	427.5	450.8	474.1	500.5	523.8	547.6	567.5	575.6
65°	323.1	334.2	346.9	365.9	385.0	408.8	429.4	453.2	470.7	481.8	489.0
67.5°	274.8	282.1	291.8	304.5	323.2	344.0	364.0	382.5	397.2	404.8	411.1
70°	243.7	248.4	255.6	268.3	282.6	300.8	321.4	335.0	347.7	354.0	360.3
72.5°	212.6	218.6	225.1	235.3	247.0	260.1	275.1	291.8	298.7	306.4	310.2
75°	161.2	169.9	178.5	184.9	192.9	203.2	216.7	227.0	231.0	237.3	238.1
77.5°	121.6	123.5	129.9	137.7	144.4	151.9	160.5	169.7	171.6	174.9	177.0
80°	100.0	100.0	100.0	104.7	112.7	118.3	126.2	131.0	134.1	134.9	135.7
82.5°	80.3	80.3	79.7	80.7	83.5	86.5	93.8	99.2	101.8	101.3	99.6
85°	52.4	50.8	50.8	50.0	50.8	49.2	48.4	51.6	56.4	56.4	54.7
87.5°	25.5	24.7	24.9	23.8	22.7	21.6	19.4	19.6	19.3	21.5	20.5
90°	19.7	19.0	16.7	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	21.3	20.2	18.5	16.8	15.0	13.3	12.7	13.2	13.7	14.2	14.6
95°	25.8	24.4	22.5	20.6	18.7	16.8	19.4	26.6	33.7	41.0	48.2
97.5°	26.9	25.4	38.1	50.7	63.3	75.9	83.9	87.2	90.4	93.6	96.7
100°	27.5	26.1	53.4	80.8	108.2	135.5	147.4	143.9	140.5	136.9	133.4
102.5°	47.6	51.9	81.8	111.7	141.7	171.6	185.2	182.7	180.2	177.6	175.1
105°	141.9	172.9	188.6	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3
107.5°	294.2	316.9	314.4	311.9	309.4	306.9	304.9	303.4	301.8	300.3	298.7
110°	350.3	356.1	354.2	352.2	350.3	348.3	346.7	345.3	343.9	342.4	341.0



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	396.0	395.9	393.9	392.0	390.1	388.1	386.6	385.3	384.1	382.7	381.5
115°	454.9	453.2	451.6	450.0	448.5	446.9	445.6	444.5	443.4	442.4	441.3
117.5°	510.2	508.8	508.0	507.2	506.3	505.5	504.4	503.2	501.9	500.6	499.3
120°	546.1	544.7	544.2	543.7	543.2	542.7	541.6	540.0	538.5	536.8	535.3
122.5°	581.8	580.8	580.1	579.5	578.8	578.0	577.1	575.8	574.5	573.2	571.9
125°	632.0	631.6	630.9	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.2
127.5°	681.5	680.9	680.0	679.2	678.3	677.5	676.4	675.0	673.6	672.2	670.8
130°	711.2	710.5	709.8	709.1	708.4	707.7	706.7	705.3	703.9	702.5	701.0
132.5°	739.7	739.0	738.4	737.8	737.3	736.7	735.8	734.4	733.0	731.5	730.1
135°	782.9	782.4	781.7	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5
137.5°	821.0	820.1	819.7	819.4	819.0	818.6	817.7	816.4	815.1	813.7	812.4
140°	845.5	844.8	844.2	843.7	843.2	842.6	841.9	840.8	839.8	838.7	837.7
142.5°	868.7	868.2	867.6	867.1	866.6	866.1	865.3	864.2	863.1	862.1	861.0
145°	901.2	900.8	900.5	900.1	899.8	899.4	898.7	897.4	896.2	894.9	893.7
147.5°	930.1	929.7	929.4	929.0	928.7	928.4	927.8	927.0	926.1	925.3	924.5
150°	947.8	947.5	947.1	946.7	946.3	946.0	945.5	945.0	944.5	944.0	943.4
152.5°	963.2	962.6	962.4	962.1	961.9	961.7	961.5	961.3	961.0	960.8	960.5
155°	984.6	983.7	983.5	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5
157.5°	1003.3	1002.2	1002.4	1002.6	1002.7	1002.9	1003.0	1003.0	1003.1	1003.1	1003.1
160°	1014.0	1012.9	1013.1	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5
162.5°	1023.6	1022.4	1022.6	1022.8	1022.9	1023.1	1023.4	1023.9	1024.3	1024.8	1025.2
165°	1036.4	1035.0	1035.2	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.6	1038.2
167.5°	1046.5	1045.1	1045.1	1045.1	1045.1	1045.1	1045.5	1046.2	1046.9	1047.6	1048.3
170°	1052.3	1050.9	1050.9	1050.9	1050.9	1050.9	1051.2	1051.9	1052.6	1053.3	1054.0
172.5°	1056.0	1054.6	1054.5	1054.3	1054.2	1054.1	1054.4	1055.2	1056.1	1056.9	1057.7
175°	1060.8	1059.6	1059.3	1059.1	1058.9	1058.8	1059.1	1060.1	1061.0	1061.8	1062.7
177.5°	1062.6	1061.4	1061.3	1061.2	1061.0	1060.9	1061.2	1061.9	1062.6	1063.3	1063.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1864.3	1871.3	1880.2	1893.5	1903.7	1912.6	1914.5	1917.0	1923.4	1934.1	1942.4
5°	1876.3	1894.6	1924.0	1952.6	1983.5	2008.9	2032.8	2049.4	2065.3	2098.6	2125.6
7.5°	1872.6	1913.2	1959.2	2010.5	2062.4	2112.7	2159.4	2201.1	2242.7	2291.3	2346.7
10°	1870.0	1917.6	1979.5	2045.4	2117.7	2188.3	2256.5	2309.8	2371.7	2427.2	2497.8
12.5°	1857.9	1926.5	2000.5	2084.8	2173.5	2254.9	2344.8	2418.3	2489.1	2569.4	2651.5
15°	1842.2	1925.6	2019.2	2131.1	2266.0	2364.5	2456.6	2584.3	2671.7	2759.0	2876.5
17.5°	1813.5	1915.2	2032.3	2177.7	2290.2	2422.5	2561.0	2662.0	2779.7	2902.7	3009.0
20°	1790.6	1908.9	2039.8	2182.7	2326.4	2470.0	2604.2	2724.8	2846.3	2988.4	3075.6
22.5°	1767.8	1884.8	2020.8	2172.6	2327.0	2478.3	2630.2	2771.9	2908.5	3051.9	3163.3
25°	1719.2	1858.2	2005.7	2160.5	2312.9	2479.6	2660.6	2818.5	2987.6	3135.2	3240.8
27.5°	1670.0	1797.3	1944.3	2101.3	2270.7	2467.7	2680.6	2860.1	3029.5	3135.2	3168.4
30°	1625.6	1760.5	1895.4	2055.0	2238.3	2458.1	2684.3	2889.9	3028.9	3074.8	3040.7
32.5°	1580.4	1702.7	1836.3	1999.7	2194.4	2434.7	2689.5	2872.2	2955.8	2920.6	2781.7
35°	1501.0	1611.2	1740.6	1904.1	2128.0	2421.7	2668.5	2792.3	2771.7	2573.2	2311.3
37.5°	1415.8	1505.7	1625.6	1796.5	2059.1	2370.1	2578.3	2596.6	2418.0	2113.3	1810.8
40°	1348.6	1429.5	1552.6	1731.1	2005.7	2319.3	2487.5	2413.7	2136.7	1797.8	1545.4
42.5°	1283.1	1351.4	1470.0	1662.5	1954.9	2250.1	2352.3	2191.5	1871.9	1551.5	1321.9
45°	1172.4	1236.6	1355.6	1553.3	1851.0	2117.7	2104.2	1824.7	1504.9	1247.0	1056.4
47.5°	1067.2	1123.5	1235.2	1436.9	1728.9	1919.2	1793.0	1495.7	1224.4	1017.4	881.5
50°	992.9	1048.5	1159.6	1358.9	1631.1	1770.0	1589.8	1303.3	1054.9	883.4	775.5
52.5°	921.8	976.1	1077.7	1271.8	1513.0	1596.0	1402.5	1136.9	929.8	781.8	689.1
55°	822.3	863.5	954.8	1140.5	1320.8	1339.8	1143.8	921.5	750.8	647.7	584.2
57.5°	720.8	756.4	846.6	994.5	1120.8	1111.1	925.1	733.0	618.0	541.3	495.2
60°	654.8	689.7	769.1	896.2	991.4	958.1	787.4	632.6	534.2	477.9	441.3
62.5°	593.2	620.6	694.8	787.5	856.1	818.3	673.1	544.9	466.9	419.4	390.5
65°	504.0	526.2	585.7	634.2	672.3	635.8	515.1	426.3	369.9	336.6	316.7
67.5°	419.2	433.3	471.0	488.5	515.3	475.2	387.4	327.8	295.8	267.6	253.9
70°	365.9	376.2	396.1	410.3	417.5	376.2	311.1	267.5	240.4	220.7	212.0
72.5°	312.6	321.6	325.6	337.3	333.7	295.0	250.1	215.4	196.0	182.6	171.3
75°	238.9	242.9	238.9	234.2	223.8	196.8	165.9	148.5	134.1	127.7	123.8
77.5°	174.1	172.9	167.4	160.1	142.4	125.4	108.8	102.9	96.6	93.3	91.9
80°	134.1	131.0	126.2	114.3	99.2	87.4	83.3	79.4	77.0	73.0	72.2
82.5°	99.9	98.0	90.0	80.0	69.4	63.8	60.5	59.1	56.7	54.6	54.4
85°	53.2	50.8	42.1	36.6	34.9	33.3	32.5	32.5	29.4	28.6	28.6
87.5°	17.7	14.2	13.9	12.3	12.7	11.9	13.0	12.2	12.0	12.8	11.7
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4
92.5°	14.2	13.7	13.2	12.7	13.3	15.0	16.8	18.5	20.2	21.3	22.4
95°	41.0	33.7	26.6	19.4	16.8	18.7	20.6	22.5	24.4	25.8	27.0
97.5°	93.6	90.4	87.2	83.9	75.9	63.3	50.7	38.1	25.4	26.9	28.3
100°	136.9	140.5	143.9	147.4	135.5	108.2	80.8	53.4	26.1	27.5	28.9
102.5°	177.6	180.2	182.7	185.2	171.6	141.7	111.7	81.8	51.9	47.6	43.2
105°	237.2	239.1	241.1	243.0	236.1	220.3	204.5	188.6	172.9	141.9	110.8
107.5°	300.3	301.8	303.4	304.9	306.9	309.4	311.9	314.4	316.9	294.2	271.4
110°	342.4	343.9	345.3	346.7	348.3	350.3	352.2	354.2	356.1	350.3	344.5



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	382.7	384.1	385.3	386.6	388.1	390.1	392.0	393.9	395.9	396.0	396.1
115°	442.4	443.4	444.5	445.6	446.9	448.5	450.0	451.6	453.2	454.9	456.7
117.5°	500.6	501.9	503.2	504.4	505.5	506.3	507.2	508.0	508.8	510.2	511.6
120°	536.8	538.5	540.0	541.6	542.7	543.2	543.7	544.2	544.7	546.1	547.5
122.5°	573.2	574.5	575.8	577.1	578.0	578.8	579.5	580.1	580.8	581.8	582.7
125°	623.5	624.9	626.3	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3
127.5°	672.2	673.6	675.0	676.4	677.5	678.3	679.2	680.0	680.9	681.5	682.0
130°	702.5	703.9	705.3	706.7	707.7	708.4	709.1	709.8	710.5	711.2	712.0
132.5°	731.5	733.0	734.4	735.8	736.7	737.3	737.8	738.4	739.0	739.7	740.3
135°	775.6	776.6	777.7	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5
137.5°	813.7	815.1	816.4	817.7	818.6	819.0	819.4	819.7	820.1	821.0	821.8
140°	838.7	839.8	840.8	841.9	842.6	843.2	843.7	844.2	844.8	845.5	846.2
142.5°	862.1	863.1	864.2	865.3	866.1	866.6	867.1	867.6	868.2	868.7	869.3
145°	894.9	896.2	897.4	898.7	899.4	899.8	900.1	900.5	900.8	901.2	901.5
147.5°	925.3	926.1	927.0	927.8	928.4	928.7	929.0	929.4	929.7	930.1	930.4
150°	944.0	944.5	945.0	945.5	946.0	946.3	946.7	947.1	947.5	947.8	948.1
152.5°	960.8	961.0	961.3	961.5	961.7	961.9	962.1	962.4	962.6	963.2	963.8
155°	984.2	983.8	983.5	983.1	983.0	983.2	983.4	983.5	983.7	984.6	985.5
157.5°	1003.1	1003.1	1003.0	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3	1004.3
160°	1014.3	1014.2	1014.0	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0
162.5°	1024.8	1024.3	1023.9	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6	1024.8
165°	1037.6	1037.1	1036.6	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.8
167.5°	1047.6	1046.9	1046.2	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5	1047.9
170°	1053.3	1052.6	1051.9	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3	1053.6
172.5°	1056.9	1056.1	1055.2	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0	1057.4
175°	1061.8	1061.0	1060.1	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8	1062.0
177.5°	1063.3	1062.6	1061.9	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6	1063.7
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1	1854.1
2.5°	1955.7	1955.7	1958.2	1967.8	1969.0	1977.3	1974.8
5°	2149.4	2164.4	2170.0	2193.8	2208.2	2214.5	2201.8
7.5°	2386.2	2428.8	2448.9	2473.9	2496.0	2502.6	2485.3
10°	2559.0	2603.4	2640.7	2663.7	2685.1	2699.5	2717.7
12.5°	2725.9	2780.6	2816.0	2848.5	2870.5	2888.7	2891.6
15°	2907.4	2989.9	3052.6	3098.7	3121.7	3133.6	3128.9
17.5°	3090.4	3166.9	3211.6	3258.5	3290.4	3292.1	3293.0
20°	3193.9	3268.5	3320.1	3355.1	3390.8	3389.2	3397.1
22.5°	3263.2	3321.8	3361.4	3386.8	3399.0	3393.0	3394.6
25°	3295.5	3313.0	3305.9	3265.4	3255.1	3217.7	3224.1
27.5°	3128.6	3046.0	2960.6	2850.7	2764.1	2694.8	2698.4
30°	2901.8	2755.8	2589.1	2449.4	2324.0	2289.1	2214.5
32.5°	2585.0	2365.9	2170.7	2040.5	1932.9	1903.7	1838.6
35°	2047.8	1835.1	1634.3	1513.6	1466.0	1399.4	1398.6
37.5°	1591.7	1404.4	1298.2	1207.7	1160.2	1119.9	1116.0
40°	1339.0	1193.0	1112.8	1047.7	1000.9	970.7	963.6
42.5°	1162.5	1044.4	969.3	929.0	892.9	877.4	865.8
45°	949.3	869.9	817.5	781.0	764.4	752.5	746.1
47.5°	794.1	740.8	705.2	680.9	667.3	654.8	658.1
50°	709.6	665.9	639.7	616.7	606.4	597.6	598.4
52.5°	641.7	602.5	581.3	564.6	551.8	545.6	542.6
55°	544.5	519.9	498.5	486.6	479.4	470.7	468.3
57.5°	464.4	445.5	428.0	414.4	412.7	404.3	405.5
60°	411.1	395.3	381.0	373.9	368.3	361.1	363.6
62.5°	367.3	354.0	341.0	335.1	329.5	324.3	325.4
65°	300.8	288.1	280.1	277.0	274.6	272.3	269.8
67.5°	239.7	232.0	227.0	220.2	215.3	214.5	212.1
70°	201.6	191.3	182.6	173.8	171.5	170.7	171.5
72.5°	161.6	155.1	152.7	148.5	147.9	145.9	147.3
75°	121.5	119.1	117.4	114.3	114.3	114.3	114.3
77.5°	89.6	88.1	87.2	86.5	85.7	84.6	84.4
80°	69.9	69.1	67.5	67.5	66.7	67.5	66.7
82.5°	52.7	52.5	51.0	51.0	50.2	49.7	50.2
85°	27.0	26.2	27.8	26.2	27.0	25.4	27.0
87.5°	11.8	12.0	11.4	11.5	10.9	12.3	11.1
90°	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	23.5	24.7	25.3	25.5	25.8	26.0	26.3
95°	28.2	29.4	30.0	30.0	30.0	30.0	30.0
97.5°	29.6	31.0	31.8	32.0	32.2	32.3	32.5
100°	30.3	31.7	32.4	32.6	32.8	33.0	33.1
102.5°	38.9	34.5	32.5	32.8	33.1	33.4	33.8
105°	79.8	48.7	33.3	33.7	34.0	34.4	34.7
107.5°	248.6	225.8	202.7	179.4	155.9	132.5	109.1
110°	338.7	333.0	317.5	292.4	267.3	242.2	217.1



TEST NUMBER: P332372-840

CATALOG NUMBER: S123RDIP-S1165D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	396.2	396.3	393.6	388.4	383.0	377.8	372.5
115°	458.5	460.2	461.4	462.1	462.8	463.5	464.2
117.5°	513.0	514.3	515.1	515.3	515.4	515.5	515.7
120°	549.0	550.4	551.1	551.1	551.1	551.1	551.1
122.5°	583.7	584.7	585.2	585.4	585.5	585.7	585.8
125°	632.7	633.0	633.4	633.7	634.1	634.4	634.8
127.5°	682.6	683.1	683.2	682.9	682.6	682.2	681.9
130°	712.7	713.4	713.6	713.2	712.9	712.5	712.2
132.5°	741.0	741.7	741.8	741.4	740.9	740.4	739.9
135°	784.0	784.5	784.5	784.0	783.5	782.9	782.4
137.5°	822.6	823.5	823.7	823.4	823.0	822.7	822.3
140°	846.9	847.6	847.8	847.4	847.1	846.7	846.4
142.5°	869.8	870.4	870.4	869.9	869.4	869.0	868.5
145°	901.9	902.2	902.4	902.4	902.4	902.4	902.4
147.5°	930.8	931.1	930.9	930.1	929.3	928.5	927.7
150°	948.5	948.8	948.8	948.2	947.7	947.2	946.6
152.5°	964.4	965.1	965.0	964.2	963.4	962.6	961.8
155°	986.3	987.2	987.1	986.1	985.0	984.0	982.9
157.5°	1005.3	1006.4	1006.2	1004.9	1003.5	1002.2	1000.8
160°	1016.1	1017.1	1017.0	1015.8	1014.6	1013.4	1012.2
162.5°	1026.0	1027.1	1027.2	1026.1	1025.0	1024.0	1022.9
165°	1039.3	1040.7	1040.8	1039.6	1038.2	1037.0	1035.8
167.5°	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1
170°	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9
172.5°	1058.8	1060.3	1060.2	1058.6	1057.1	1055.5	1054.0
175°	1063.2	1064.4	1064.3	1063.0	1061.6	1060.2	1058.7
177.5°	1064.8	1065.9	1065.8	1064.4	1063.0	1061.6	1060.2
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7

(END OF REPORT)