

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832070

Luminaire Tested: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832070  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U840-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5850.6 lumens  
Efficiency: N/A  
Efficacy: 134.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 43.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25				
1	93	89	85	82	83	79	76	74	62	60	58	45	44	43	30	30	29	22				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25	19				
3	78	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	21	19	15				
5	65	55	47	41	58	49	43	38	39	34	31	29	26	24	20	18	17	13				
6	60	49	41	36	54	44	38	33	35	30	27	27	23	21	19	17	15	12				
7	56	44	37	32	50	40	34	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	26	29	25	21	22	19	17	16	14	13	10				
9	48	37	30	25	43	33	27	23	27	22	19	21	17	15	15	13	11	9				
10	45	34	27	22	40	31	25	21	25	20	17	19	16	14	14	12	11	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	12076	12076	12076	12076	12076
5°	14338	13881	12151	9823	9121
10°	12991	14100	12091	7871	6753
15°	8945	12090	11964	6433	5341
20°	6222	9308	11724	5424	4694
25°	4742	7094	11374	4821	4327
30°	4128	5671	10936	4477	4007
35°	3790	4784	10318	4185	3717
40°	3458	4272	9507	3901	3451
45°	3124	3908	8634	3631	3186
50°	2835	3605	7603	3366	2858
55°	2563	3310	6611	3108	2451
60°	2297	3010	5744	2822	2316
65°	2122	2672	4944	2537	2190
70°	1721	2310	4315	2294	1781
75°	1510	1838	3656	1905	1568
80°	1370	1556	2994	1599	1481
85°	1247	1359	2272	1445	1359

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 9109 cd/sqm



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.3	1.7
10°-20°	236.6	4.0
20°-30°	271.5	4.6
30°-40°	267.6	4.6
40°-50°	236.0	4.0
50°-60°	181.6	3.1
60°-70°	119.4	2.0
70°-80°	58.0	1.0
80°-90°	17.8	0.3
90°-100°	314.5	5.4
100°-110°	920.8	15.7
110°-120°	899.2	15.4
120°-130°	716.1	12.2
130°-140°	565.0	9.7
140°-150°	421.5	7.2
150°-160°	293.9	5.0
160°-170°	172.6	3.0
170°-180°	56.2	1.0
0°-30°	610.4	10.4
0°-40°	878.0	15.0
0°-60°	1295.5	22.1
0°-90°	1490.7	25.5
90°-120°	2134.6	36.5
90°-150°	3837.3	65.6
90°-180°	4360.0	74.5
0°-180°	5850.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1122	1122	1122	1122	1122	
5°	1327	1285	1125	909	844	121
15°	803	1085	1074	577	479	227
25°	399	597	958	406	364	189
35°	288	364	785	318	283	180
45°	205	257	567	238	209	159
55°	137	176	352	166	131	123
65°	83	105	194	100	86	82
75°	36	44	88	46	38	39
85°	10	11	18	12	11	11
90°	34	29	2	29	34	18
95°	136	696	40	696	136	221
105°	1492	943	136	943	1492	1489
115°	1815	722	240	722	1815	1770
125°	1431	674	334	674	1431	1295
135°	1160	664	392	664	1160	900
145°	907	656	447	656	907	576
155°	752	635	508	635	752	350
165°	656	608	555	608	656	187
175°	590	583	578	583	590	57
180°	580	580	580	580	580	



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1243.3	1239.4	1235.5	1234.4	1233.2	1229.5	1225.8	1217.6	1209.3	1200.8	1192.3
5°	1327.0	1327.5	1328.0	1326.8	1325.7	1320.8	1316.0	1305.9	1295.8	1284.7	1273.7
7.5°	1301.3	1308.6	1316.0	1317.4	1318.8	1322.4	1326.1	1323.8	1321.5	1317.4	1313.2
10°	1188.6	1188.1	1187.7	1195.9	1204.2	1228.8	1253.4	1266.1	1278.7	1290.0	1301.3
12.5°	1004.6	1005.3	1006.0	1033.1	1060.3	1083.5	1106.7	1138.9	1171.1	1205.8	1240.6
15°	802.7	813.9	825.2	849.4	873.5	908.5	943.4	986.7	1029.9	1084.9	1139.8
17.5°	659.1	664.0	668.8	692.0	715.3	748.4	781.5	830.5	879.5	950.3	1021.2
20°	543.2	547.6	552.0	568.8	585.6	617.3	649.0	695.7	742.4	812.6	882.7
22.5°	453.5	462.0	470.6	481.8	493.1	516.1	539.1	586.7	634.3	698.2	762.2
25°	399.3	403.2	407.1	416.7	426.4	448.5	470.6	502.1	533.6	597.3	661.0
27.5°	362.5	363.6	364.8	371.9	379.0	393.3	407.5	436.7	466.0	518.4	570.8
30°	332.1	334.2	336.2	341.8	347.3	357.6	368.0	388.7	409.4	456.3	503.2
32.5°	308.6	309.8	310.9	315.5	320.1	327.7	335.3	351.7	368.0	403.9	439.7
35°	288.4	288.6	288.9	292.3	295.8	303.1	310.5	324.1	337.6	364.1	390.5
37.5°	265.4	267.0	268.6	271.2	273.7	280.1	286.6	297.6	308.6	330.5	352.3
40°	246.1	247.5	248.8	251.8	254.8	259.9	264.9	275.1	285.2	304.0	322.9
42.5°	226.8	227.7	228.6	231.6	234.6	240.8	247.0	255.1	263.1	278.7	294.4
45°	205.2	207.5	209.8	213.0	216.2	221.5	226.8	235.0	243.3	256.7	270.0
47.5°	187.2	188.4	189.5	192.3	195.0	201.5	207.9	215.3	222.6	235.0	247.5
50°	169.3	169.7	170.2	172.7	175.3	181.0	186.8	195.3	203.8	215.3	226.8
52.5°	152.3	153.4	154.6	157.1	159.6	163.5	167.4	176.2	184.9	196.2	207.5
55°	136.6	137.3	138.0	139.8	141.7	146.3	150.9	158.5	166.1	176.4	186.8
57.5°	121.9	122.8	123.7	125.1	126.5	130.6	134.8	141.4	148.1	158.5	168.8
60°	106.7	107.9	109.0	110.6	112.2	115.5	118.7	124.7	130.6	139.8	149.0
62.5°	95.7	95.9	96.1	97.5	98.9	101.2	103.5	108.3	113.2	122.4	131.6
65°	83.3	83.9	84.6	85.3	86.0	87.9	89.7	93.8	98.0	104.9	111.8
67.5°	70.4	71.1	71.8	72.9	74.1	75.7	77.3	80.0	82.8	89.2	95.7
70°	54.7	54.7	54.7	56.6	58.4	61.2	63.9	66.0	68.1	73.4	78.7
72.5°	44.6	44.8	45.1	45.3	45.5	47.1	48.8	52.2	55.7	58.9	62.1
75°	36.3	36.6	36.8	37.0	37.3	37.7	38.2	39.3	40.5	44.2	47.8
77.5°	29.0	29.2	29.4	29.7	29.9	30.4	30.8	31.3	31.7	33.1	34.5
80°	22.1	22.3	22.5	22.8	23.0	23.2	23.5	23.9	24.4	25.1	25.8
82.5°	16.1	16.1	16.1	16.1	16.1	16.6	17.0	17.0	17.0	17.5	17.9
85°	10.1	10.1	10.1	10.3	10.6	10.6	10.6	10.8	11.0	11.0	11.0
87.5°	4.6	4.4	4.1	4.4	4.6	4.6	4.6	4.8	5.1	5.1	5.1
90°	34.0	35.2	34.0	32.9	34.0	31.7	30.5	29.3	28.2	29.3	25.8
92.5°	62.2	64.5	63.4	68.1	70.4	78.6	90.3	116.2	163.1	218.2	241.7
95°	136.1	140.8	149.0	159.6	181.9	224.1	286.3	422.4	564.4	695.8	619.5
97.5°	279.2	292.2	320.3	364.9	443.5	577.3	732.1	970.3	1106.4	1070.1	799.0
100°	735.7	734.5	780.3	865.9	984.4	1151.0	1288.3	1383.3	1342.3	1111.1	750.9
102.5°	1165.1	1199.1	1235.5	1298.9	1384.5	1474.9	1540.6	1520.6	1354.0	1034.9	680.5
105°	1492.5	1498.3	1535.9	1580.4	1634.4	1664.9	1642.6	1525.3	1280.1	943.3	625.4
107.5°	1706.0	1718.9	1734.2	1755.3	1762.3	1730.6	1639.1	1454.9	1174.5	862.4	585.5
110°	1828.0	1830.4	1832.7	1823.3	1790.5	1708.3	1560.5	1344.6	1075.9	795.5	564.4



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1852.7	1851.5	1839.7	1805.7	1738.8	1627.4	1457.3	1235.5	990.3	750.9	552.6
115°	1815.1	1809.2	1785.8	1734.2	1646.2	1518.3	1345.8	1141.6	924.6	721.6	551.5
117.5°	1733.0	1724.8	1689.6	1632.1	1540.6	1408.0	1249.6	1068.9	881.2	701.6	552.6
120°	1625.0	1618.0	1589.8	1524.1	1431.4	1312.9	1172.1	1013.7	848.3	688.7	557.3
122.5°	1524.1	1514.7	1483.1	1425.6	1345.8	1237.8	1110.0	970.3	821.3	680.5	565.5
125°	1431.4	1423.2	1393.9	1342.3	1267.2	1173.3	1060.7	932.8	799.0	673.5	573.7
127.5°	1351.7	1344.6	1317.6	1273.0	1205.0	1118.2	1014.9	898.8	777.9	670.0	583.1
130°	1285.9	1276.6	1251.9	1209.7	1147.5	1067.7	972.7	867.1	761.5	666.4	592.5
132.5°	1221.4	1215.5	1194.4	1152.2	1094.7	1019.6	932.8	837.7	746.2	665.3	599.6
135°	1160.4	1152.2	1131.1	1095.9	1038.4	971.5	895.2	811.9	733.3	664.1	606.6
137.5°	1095.9	1088.8	1071.2	1034.9	985.6	925.7	857.7	787.3	721.6	661.7	611.3
140°	1027.8	1029.0	1010.2	977.4	932.8	882.3	826.0	766.2	711.0	660.6	616.0
142.5°	964.5	965.6	949.2	921.0	884.7	842.4	795.5	746.2	701.6	658.2	619.5
145°	907.0	904.6	895.2	870.6	841.3	807.2	769.7	731.0	693.4	655.9	620.7
147.5°	857.7	856.5	847.1	829.5	806.1	781.4	749.7	718.1	685.2	652.4	620.7
150°	815.5	815.5	808.4	795.5	777.9	755.6	731.0	704.0	677.0	647.7	620.7
152.5°	780.3	780.3	776.7	765.0	752.1	734.5	713.4	691.1	667.6	641.8	617.2
155°	752.1	750.9	748.6	739.2	728.6	714.5	696.9	678.2	658.2	634.8	614.8
157.5°	725.1	725.1	722.8	715.7	706.3	694.6	680.5	664.1	647.7	628.9	611.3
160°	699.3	700.5	700.5	693.4	685.2	677.0	665.3	652.4	637.1	621.9	608.9
162.5°	675.8	677.0	677.0	671.1	666.4	659.4	648.8	638.3	626.5	614.8	604.3
165°	655.9	655.9	657.1	652.4	647.7	641.8	633.6	626.5	617.2	607.8	599.6
167.5°	635.9	635.9	637.1	633.6	631.2	626.5	621.9	616.0	607.8	600.7	594.9
170°	618.3	618.3	619.5	617.2	616.0	613.6	608.9	605.4	599.6	593.7	590.2
172.5°	601.9	603.1	605.4	603.1	603.1	601.9	598.4	596.0	591.3	587.8	586.7
175°	590.2	591.3	592.5	591.3	591.3	591.3	589.0	587.8	585.5	583.1	583.1
177.5°	582.0	582.0	584.3	583.1	584.3	584.3	583.1	582.0	580.8	579.6	580.8
180°	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1191.1	1190.0	1178.9	1167.9	1157.1	1146.3	1138.2	1130.2	1116.6	1103.0	1094.5
5°	1264.9	1256.2	1238.7	1221.2	1195.0	1168.8	1146.7	1124.6	1096.6	1068.5	1045.1
7.5°	1306.1	1299.0	1277.8	1256.7	1221.9	1187.2	1152.7	1118.2	1076.8	1035.4	1000.0
10°	1307.3	1313.2	1295.8	1278.3	1239.2	1200.1	1153.2	1106.2	1050.6	994.9	949.2
12.5°	1266.3	1292.1	1288.4	1284.7	1244.9	1205.1	1148.1	1091.1	1022.8	954.5	897.2
15°	1189.7	1239.6	1254.4	1269.1	1236.2	1203.3	1138.4	1073.6	993.3	913.1	847.3
17.5°	1091.1	1161.0	1199.9	1238.7	1214.8	1190.9	1119.8	1048.8	958.4	868.0	796.5
20°	974.2	1065.8	1126.7	1187.7	1178.9	1170.2	1096.8	1023.5	925.9	828.4	750.9
22.5°	858.8	955.4	1039.6	1123.7	1132.7	1141.7	1067.6	993.6	886.8	780.1	701.2
25°	759.2	857.4	957.7	1058.0	1078.2	1098.4	1028.1	957.7	847.1	736.4	658.0
27.5°	664.2	757.6	868.0	978.4	1015.2	1052.0	987.6	923.2	808.0	692.7	614.5
30°	586.7	670.2	782.9	895.6	946.9	998.2	939.0	879.9	765.6	651.3	574.7
32.5°	514.5	589.2	702.4	815.5	875.1	934.7	883.6	832.6	722.6	612.7	537.0
35°	457.4	524.4	629.9	735.5	802.2	868.9	827.0	785.2	677.8	570.4	498.8
37.5°	408.5	464.6	563.7	662.8	733.7	804.5	769.5	734.6	633.6	532.7	465.0
40°	368.0	413.1	505.3	597.5	667.0	736.4	706.5	676.6	586.2	495.9	432.6
42.5°	333.3	372.1	454.9	537.7	601.4	665.1	645.4	625.6	543.7	461.8	403.2
45°	302.7	335.3	408.2	481.1	539.8	598.4	582.8	567.2	496.5	425.9	372.1
47.5°	275.5	303.6	368.7	433.8	486.4	539.1	524.6	510.1	451.7	393.3	344.3
50°	250.7	274.6	328.9	383.2	430.5	477.9	466.0	454.0	405.7	357.4	315.1
52.5°	227.2	247.0	295.8	344.5	382.7	420.9	411.7	402.5	365.2	328.0	289.6
55°	204.9	223.1	264.3	305.4	338.1	370.7	361.5	352.3	323.4	294.4	260.6
57.5°	184.7	200.6	233.9	267.2	293.2	319.2	314.9	310.5	286.3	262.2	234.4
60°	163.3	177.6	206.3	235.0	256.0	276.9	271.8	266.8	249.5	232.3	208.4
62.5°	144.2	156.9	179.9	202.9	219.9	236.9	233.2	229.5	216.4	203.3	183.5
65°	124.2	136.6	155.2	173.9	187.2	200.6	197.3	194.1	184.2	174.3	158.5
67.5°	106.0	116.4	132.5	148.6	157.5	166.5	164.7	162.8	155.2	147.7	135.2
70°	87.6	96.6	109.9	123.3	129.5	135.7	136.4	137.1	130.2	123.3	114.1
72.5°	69.2	76.4	88.8	101.2	106.0	110.9	110.6	110.4	106.3	102.1	93.8
75°	53.1	58.4	68.1	77.7	81.9	86.0	86.9	87.9	83.9	80.0	75.4
77.5°	38.2	41.9	49.2	56.6	61.2	65.8	66.2	66.7	64.9	63.0	58.6
80°	26.9	28.1	32.7	37.3	42.1	46.9	47.6	48.3	46.5	44.6	41.9
82.5°	18.6	19.3	20.9	22.5	26.4	30.4	31.3	32.2	31.3	30.4	27.4
85°	11.3	11.5	12.2	12.9	14.7	16.6	17.5	18.4	17.9	17.5	15.9
87.5°	5.1	5.1	5.3	5.5	6.0	6.4	7.6	8.7	8.0	7.4	6.7
90°	22.3	18.8	15.3	12.9	10.6	7.0	4.7	2.3	4.7	7.0	10.6
92.5°	180.7	118.5	81.0	59.8	48.1	37.5	25.8	17.6	25.8	37.5	48.1
95°	427.1	252.3	152.5	106.8	76.3	56.3	43.4	39.9	43.4	56.3	76.3
97.5°	475.2	272.2	173.6	123.2	92.7	75.1	64.5	63.4	64.5	75.1	92.7
100°	442.3	268.7	186.6	140.8	112.6	96.2	88.0	86.8	88.0	96.2	112.6
102.5°	414.2	273.4	201.8	160.7	136.1	120.9	113.8	111.5	113.8	120.9	136.1
105°	403.6	282.8	219.4	183.0	160.7	146.7	139.6	136.1	139.6	146.7	160.7
107.5°	401.3	298.0	241.7	207.7	186.6	172.5	165.4	161.9	165.4	172.5	186.6
110°	407.1	318.0	265.2	232.3	212.4	199.5	193.6	190.1	193.6	199.5	212.4





TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	418.9	337.9	289.8	258.1	238.2	225.3	219.4	215.9	219.4	225.3	238.2
115°	431.8	360.2	315.6	283.9	264.0	252.3	245.2	240.5	245.2	252.3	264.0
117.5°	448.2	383.7	339.1	309.8	287.5	276.9	271.0	265.2	271.0	276.9	287.5
120°	467.0	406.0	363.7	334.4	312.1	300.4	294.5	291.0	294.5	300.4	312.1
122.5°	484.6	429.4	388.4	356.7	335.6	322.7	316.8	313.3	316.8	322.7	335.6
125°	503.3	451.7	410.7	379.0	356.7	343.8	336.7	334.4	336.7	343.8	356.7
127.5°	518.6	471.7	431.8	400.1	375.5	362.6	354.3	350.8	354.3	362.6	375.5
130°	533.9	489.3	450.6	418.9	394.2	380.2	369.6	366.1	369.6	380.2	394.2
132.5°	547.9	504.5	467.0	436.5	411.8	394.2	382.5	377.8	382.5	394.2	411.8
135°	559.7	519.8	483.4	451.7	427.1	409.5	396.6	391.9	396.6	409.5	427.1
137.5°	569.1	530.3	495.1	465.8	441.2	422.4	409.5	404.8	409.5	422.4	441.2
140°	576.1	540.9	506.9	477.5	454.1	435.3	423.6	417.7	423.6	435.3	454.1
142.5°	583.1	549.1	516.3	489.3	465.8	449.4	436.5	431.8	436.5	449.4	465.8
145°	587.8	556.1	525.6	498.7	478.7	461.1	450.6	447.0	450.6	461.1	478.7
147.5°	591.3	562.0	533.9	510.4	490.4	475.2	464.6	462.3	464.6	475.2	490.4
150°	592.5	567.9	540.9	519.8	503.3	488.1	478.7	477.5	478.7	488.1	503.3
152.5°	594.9	571.4	549.1	529.2	515.1	502.2	492.8	492.8	492.8	502.2	515.1
155°	594.9	576.1	556.1	539.7	526.8	515.1	508.0	508.0	508.0	515.1	526.8
157.5°	596.0	578.4	562.0	549.1	537.4	526.8	520.9	519.8	520.9	526.8	537.4
160°	596.0	582.0	567.9	556.1	547.9	538.5	533.9	533.9	533.9	538.5	547.9
162.5°	594.9	583.1	571.4	562.0	555.0	547.9	544.4	544.4	544.4	547.9	555.0
165°	592.5	584.3	574.9	566.7	562.0	556.1	553.8	555.0	553.8	556.1	562.0
167.5°	591.3	584.3	577.3	571.4	567.9	563.2	562.0	563.2	562.0	563.2	567.9
170°	587.8	583.1	577.3	574.9	572.6	569.1	567.9	570.2	567.9	569.1	572.6
172.5°	586.7	583.1	578.4	577.3	576.1	573.7	573.7	574.9	573.7	573.7	576.1
175°	584.3	582.0	579.6	578.4	578.4	576.1	577.3	578.4	577.3	576.1	578.4
177.5°	583.1	580.8	579.6	579.6	579.6	578.4	579.6	580.8	579.6	578.4	579.6
180°	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1086.0	1072.9	1059.8	1050.4	1040.9	1029.2	1017.5	1017.0	1016.6	1007.8	999.1
5°	1021.6	998.8	976.1	953.8	931.5	909.1	886.8	881.8	876.7	869.1	861.5
7.5°	964.6	928.2	891.9	863.4	834.9	812.6	790.2	775.1	759.9	748.2	736.4
10°	903.4	858.3	813.2	778.7	744.2	720.1	695.9	678.5	661.0	652.7	644.4
12.5°	839.9	790.9	741.9	708.1	674.3	645.4	616.4	600.5	584.6	573.1	561.6
15°	781.5	728.8	676.2	640.3	604.4	577.3	550.1	534.3	518.4	506.9	495.4
17.5°	724.9	671.8	618.7	582.3	546.0	521.4	496.8	481.4	466.0	458.8	451.7
20°	673.4	619.8	566.2	532.0	497.7	473.5	449.4	441.1	432.8	426.2	419.5
22.5°	622.4	570.8	519.3	486.4	453.5	436.1	418.6	411.9	405.2	400.2	395.1
25°	579.6	528.3	477.0	448.2	419.5	405.9	392.4	388.0	383.6	378.6	373.5
27.5°	536.3	487.6	438.8	415.8	392.8	381.8	370.7	365.2	359.7	355.6	351.4
30°	498.2	453.1	408.0	388.9	369.8	360.2	350.5	344.5	338.5	334.6	330.7
32.5°	461.4	421.3	381.3	365.0	348.7	339.2	329.8	324.1	318.3	313.7	309.1
35°	427.3	392.6	357.9	342.9	328.0	318.5	309.1	303.4	297.6	293.0	288.4
37.5°	397.4	365.9	334.4	320.4	306.3	298.1	289.8	283.8	277.8	273.0	268.2
40°	369.4	341.5	313.7	300.1	286.6	277.6	268.6	263.3	258.0	253.7	249.3
42.5°	344.5	319.0	293.5	280.1	266.8	258.3	249.8	243.6	237.3	234.8	232.3
45°	318.3	295.8	273.2	260.3	247.5	238.5	229.5	224.2	218.9	216.6	214.4
47.5°	295.3	274.4	253.4	240.8	228.1	220.1	212.1	207.9	203.8	200.6	197.3
50°	272.8	252.5	232.3	220.1	207.9	201.0	194.1	189.1	184.0	181.7	179.4
52.5°	251.1	232.7	214.4	201.9	189.5	182.8	176.2	171.8	167.4	162.6	157.8
55°	226.8	210.7	194.6	183.5	172.5	165.6	158.7	153.6	148.6	143.5	138.5
57.5°	206.5	190.7	174.8	164.9	155.0	148.3	141.7	136.2	130.6	126.5	122.4
60°	184.5	170.7	156.9	147.2	137.5	131.1	124.7	119.4	114.1	112.0	109.9
62.5°	163.8	150.9	138.0	129.5	121.0	114.8	108.6	105.1	101.7	100.3	98.9
65°	142.6	131.6	120.5	112.7	104.9	99.6	94.3	92.7	91.1	89.9	88.8
67.5°	122.8	113.4	104.0	97.1	90.2	86.5	82.8	81.0	79.1	77.7	76.4
70°	104.9	96.6	88.3	82.3	76.4	72.9	69.5	67.8	66.2	63.7	61.2
72.5°	85.6	79.1	72.7	68.1	63.5	60.5	57.5	54.3	51.1	48.8	46.5
75°	70.8	64.4	58.0	53.6	49.2	45.8	42.3	41.2	40.0	39.3	38.6
77.5°	54.3	48.8	43.2	39.8	36.3	34.7	33.1	32.4	31.7	31.5	31.3
80°	39.1	34.5	29.9	28.1	26.2	25.8	25.3	24.8	24.4	24.1	23.9
82.5°	24.4	22.1	19.8	19.3	18.9	18.6	18.4	18.2	17.9	17.7	17.5
85°	14.3	13.3	12.4	12.2	12.0	11.7	11.5	11.5	11.5	11.5	11.5
87.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.7	5.5
90°	12.9	15.3	18.8	22.3	25.8	29.3	28.2	29.3	30.5	31.7	34.0
92.5°	59.8	81.0	118.5	180.7	241.7	218.2	163.1	116.2	90.3	78.6	70.4
95°	106.8	152.5	252.3	427.1	619.5	695.8	564.4	422.4	286.3	224.1	181.9
97.5°	123.2	173.6	272.2	475.2	799.0	1070.1	1106.4	970.3	732.1	577.3	443.5
100°	140.8	186.6	268.7	442.3	750.9	1111.1	1342.3	1383.3	1288.3	1151.0	984.4
102.5°	160.7	201.8	273.4	414.2	680.5	1034.9	1354.0	1520.6	1540.6	1474.9	1384.5
105°	183.0	219.4	282.8	403.6	625.4	943.3	1280.1	1525.3	1642.6	1664.9	1634.4
107.5°	207.7	241.7	298.0	401.3	585.5	862.4	1174.5	1454.9	1639.1	1730.6	1762.3
110°	232.3	265.2	318.0	407.1	564.4	795.5	1075.9	1344.6	1560.5	1708.3	1790.5



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	258.1	289.8	337.9	418.9	552.6	750.9	990.3	1235.5	1457.3	1627.4	1738.8
115°	283.9	315.6	360.2	431.8	551.5	721.6	924.6	1141.6	1345.8	1518.3	1646.2
117.5°	309.8	339.1	383.7	448.2	552.6	701.6	881.2	1068.9	1249.6	1408.0	1540.6
120°	334.4	363.7	406.0	467.0	557.3	688.7	848.3	1013.7	1172.1	1312.9	1431.4
122.5°	356.7	388.4	429.4	484.6	565.5	680.5	821.3	970.3	1110.0	1237.8	1345.8
125°	379.0	410.7	451.7	503.3	573.7	673.5	799.0	932.8	1060.7	1173.3	1267.2
127.5°	400.1	431.8	471.7	518.6	583.1	670.0	777.9	898.8	1014.9	1118.2	1205.0
130°	418.9	450.6	489.3	533.9	592.5	666.4	761.5	867.1	972.7	1067.7	1147.5
132.5°	436.5	467.0	504.5	547.9	599.6	665.3	746.2	837.7	932.8	1019.6	1094.7
135°	451.7	483.4	519.8	559.7	606.6	664.1	733.3	811.9	895.2	971.5	1038.4
137.5°	465.8	495.1	530.3	569.1	611.3	661.7	721.6	787.3	857.7	925.7	985.6
140°	477.5	506.9	540.9	576.1	616.0	660.6	711.0	766.2	826.0	882.3	932.8
142.5°	489.3	516.3	549.1	583.1	619.5	658.2	701.6	746.2	795.5	842.4	884.7
145°	498.7	525.6	556.1	587.8	620.7	655.9	693.4	731.0	769.7	807.2	841.3
147.5°	510.4	533.9	562.0	591.3	620.7	652.4	685.2	718.1	749.7	781.4	806.1
150°	519.8	540.9	567.9	592.5	620.7	647.7	677.0	704.0	731.0	755.6	777.9
152.5°	529.2	549.1	571.4	594.9	617.2	641.8	667.6	691.1	713.4	734.5	752.1
155°	539.7	556.1	576.1	594.9	614.8	634.8	658.2	678.2	696.9	714.5	728.6
157.5°	549.1	562.0	578.4	596.0	611.3	628.9	647.7	664.1	680.5	694.6	706.3
160°	556.1	567.9	582.0	596.0	608.9	621.9	637.1	652.4	665.3	677.0	685.2
162.5°	562.0	571.4	583.1	594.9	604.3	614.8	626.5	638.3	648.8	659.4	666.4
165°	566.7	574.9	584.3	592.5	599.6	607.8	617.2	626.5	633.6	641.8	647.7
167.5°	571.4	577.3	584.3	591.3	594.9	600.7	607.8	616.0	621.9	626.5	631.2
170°	574.9	577.3	583.1	587.8	590.2	593.7	599.6	605.4	608.9	613.6	616.0
172.5°	577.3	578.4	583.1	586.7	586.7	587.8	591.3	596.0	598.4	601.9	603.1
175°	578.4	579.6	582.0	584.3	583.1	583.1	585.5	587.8	589.0	591.3	591.3
177.5°	579.6	579.6	580.8	583.1	580.8	579.6	580.8	582.0	583.1	584.3	584.3
180°	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1121.9	1121.9	1121.9	1121.9
2.5°	996.8	994.5	993.6	992.6
5°	854.4	847.3	845.7	844.1
7.5°	733.4	730.4	720.6	710.7
10°	635.2	626.0	621.9	617.8
12.5°	553.1	544.6	543.2	541.9
15°	489.4	483.4	481.4	479.3
17.5°	447.6	443.4	440.9	438.4
20°	416.5	413.5	411.7	409.8
22.5°	392.8	390.5	389.1	387.8
25°	370.1	366.6	365.5	364.3
27.5°	348.4	345.4	344.3	343.1
30°	328.2	325.7	324.1	322.4
32.5°	306.1	303.1	302.2	301.3
35°	286.6	284.7	283.8	282.9
37.5°	265.9	263.6	262.2	260.8
40°	248.2	247.0	246.3	245.6
42.5°	230.2	228.1	227.9	227.7
45°	212.3	210.2	209.8	209.3
47.5°	195.5	193.7	193.4	193.2
50°	176.9	174.3	172.5	170.7
52.5°	155.5	153.2	151.6	150.0
55°	135.9	133.4	132.0	130.6
57.5°	121.2	120.1	119.4	118.7
60°	109.2	108.6	108.1	107.6
62.5°	98.2	97.5	97.5	97.5
65°	88.1	87.4	86.7	86.0
67.5°	75.0	73.6	73.4	73.1
70°	59.1	57.0	56.8	56.6
72.5°	46.2	46.0	45.5	45.1
75°	38.2	37.7	37.7	37.7
77.5°	30.8	30.4	30.4	30.4
80°	23.7	23.5	23.7	23.9
82.5°	17.5	17.5	17.2	17.0
85°	11.3	11.0	11.0	11.0
87.5°	5.5	5.5	5.5	5.5
90°	32.9	34.0	35.2	34.0
92.5°	68.1	63.4	64.5	62.2
95°	159.6	149.0	140.8	136.1
97.5°	364.9	320.3	292.2	279.2
100°	865.9	780.3	734.5	735.7
102.5°	1298.9	1235.5	1199.1	1165.1
105°	1580.4	1535.9	1498.3	1492.5
107.5°	1755.3	1734.2	1718.9	1706.0
110°	1823.3	1832.7	1830.4	1828.0



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1805.7	1839.7	1851.5	1852.7
115°	1734.2	1785.8	1809.2	1815.1
117.5°	1632.1	1689.6	1724.8	1733.0
120°	1524.1	1589.8	1618.0	1625.0
122.5°	1425.6	1483.1	1514.7	1524.1
125°	1342.3	1393.9	1423.2	1431.4
127.5°	1273.0	1317.6	1344.6	1351.7
130°	1209.7	1251.9	1276.6	1285.9
132.5°	1152.2	1194.4	1215.5	1221.4
135°	1095.9	1131.1	1152.2	1160.4
137.5°	1034.9	1071.2	1088.8	1095.9
140°	977.4	1010.2	1029.0	1027.8
142.5°	921.0	949.2	965.6	964.5
145°	870.6	895.2	904.6	907.0
147.5°	829.5	847.1	856.5	857.7
150°	795.5	808.4	815.5	815.5
152.5°	765.0	776.7	780.3	780.3
155°	739.2	748.6	750.9	752.1
157.5°	715.7	722.8	725.1	725.1
160°	693.4	700.5	700.5	699.3
162.5°	671.1	677.0	677.0	675.8
165°	652.4	657.1	655.9	655.9
167.5°	633.6	637.1	635.9	635.9
170°	617.2	619.5	618.3	618.3
172.5°	603.1	605.4	603.1	601.9
175°	591.3	592.5	591.3	590.2
177.5°	583.1	584.3	582.0	582.0
180°	579.6	579.6	579.6	579.6



TEST NUMBER: P832070

CATALOG NUMBER: S123RDIP-S340D1195U840-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.49	7.14	7.64	8.27	9.86	11.15	11.81	12.30	12.94	14.53
	3H	7.70	8.28	8.85	9.42	11.02	12.64	13.22	13.80	14.37	15.97
	4H	8.07	8.62	9.24	9.77	11.37	13.12	13.68	14.29	14.82	16.42
	6H	8.34	8.85	9.52	10.00	11.61	13.42	13.93	14.60	15.08	16.70
	8H	8.42	8.91	9.60	10.07	11.68	13.50	13.98	14.67	15.14	16.75
	12H	8.47	8.93	9.65	10.08	11.71	13.52	13.98	14.70	15.14	16.77
4H	2H	7.19	7.74	8.36	8.89	10.49	11.13	11.68	12.30	12.82	14.43
	3H	8.54	9.01	9.72	10.17	11.79	12.77	13.23	13.95	14.40	16.02
	4H	8.99	9.42	10.17	10.57	12.21	13.37	13.80	14.55	14.95	16.59
	6H	9.35	9.71	10.54	10.89	12.52	13.80	14.16	14.98	15.34	16.97
	8H	9.47	9.81	10.66	10.98	12.62	13.93	14.27	15.11	15.44	17.08
	12H	9.54	9.85	10.74	11.03	12.68	13.98	14.29	15.18	15.47	17.12
8H	4H	9.30	9.63	10.48	10.80	12.45	13.33	13.66	14.51	14.83	16.48
	6H	9.75	10.03	10.96	11.24	12.88	13.82	14.09	15.02	15.31	16.95
	8H	9.95	10.19	11.15	11.38	13.04	14.00	14.24	15.21	15.43	17.09
	12H	10.08	10.29	11.29	11.48	13.17	14.11	14.32	15.32	15.51	17.20
12H	4H	9.30	9.61	10.50	10.79	12.43	13.27	13.57	14.47	14.75	16.40
	6H	9.81	10.05	11.02	11.24	12.90	13.79	14.03	15.00	15.22	16.88
	8H	10.02	10.24	11.23	11.42	13.11	13.98	14.19	15.19	15.38	17.07