

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831749

Luminaire Tested: S123DP-S560D840-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831749
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, -)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DP-S560D840-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2620.3 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831749
CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831749

CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86				86
2	101	94	88	82	99	92	86	81	88	84	80	85	81	78	82	79	76	74				74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64				64
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	54	78	67	59	54	65	58	53	63	57	52	61	56	52	50				50
6	74	62	54	48	73	61	53	48	60	53	47	58	52	47	56	51	47	45				45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40				40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34				34
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	17545	17545	17545	17545	17545
5°	22189	20943	17703	14266	13110
10°	22404	23083	17585	11372	9938
15°	16875	21431	17465	9630	8403
20°	11757	17341	17242	8422	7633
25°	8966	13336	16862	7748	7160
30°	7756	10596	16255	7272	6779
35°	7196	8946	15556	6928	6510
40°	6813	8025	14571	6600	6420
45°	6587	7427	13323	6345	6378
50°	6472	6954	11843	6112	6347
55°	6232	6608	10391	5891	6373
60°	6008	6237	8956	5683	6269
65°	5644	5886	7725	5461	6146
70°	5215	5438	6571	5095	5784
75°	4720	4874	5631	4733	5286
80°	3893	4265	4457	4128	4457
85°	3088	3458	3273	3507	3545

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 15210 cd/sqm



TEST NUMBER: P831749

CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.1	5.9
10°-20°	383.4	14.6
20°-30°	453.9	17.3
30°-40°	456.4	17.4
40°-50°	418.8	16.0
50°-60°	345.6	13.2
60°-70°	244.5	9.3
70°-80°	130.5	5.0
80°-90°	33.1	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	991.4	37.8
0°-40°	1447.8	55.3
0°-60°	2212.2	84.4
0°-90°	2620.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2620.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1630	1630	1630	1630	1630	
5°	2054	1938	1638	1320	1213	196
15°	1514	1923	1567	864	754	418
25°	755	1123	1420	652	603	356
35°	548	681	1184	527	495	344
45°	433	488	875	417	419	335
55°	332	352	554	314	340	297
65°	222	231	303	214	241	220
75°	114	117	135	114	127	119
85°	25	28	26	28	29	30
90°	0	0	0	0	0	



TEST NUMBER: P831749

CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0
2.5°	1837.3	1835.4	1833.5	1824.1	1814.6	1810.1	1805.5	1791.9	1778.3	1763.2	1748.0
5°	2053.6	2058.9	2064.2	2058.2	2052.1	2033.6	2015.1	1990.5	1965.9	1938.3	1910.7
7.5°	2153.5	2156.5	2159.5	2155.7	2152.0	2147.0	2142.1	2120.2	2098.3	2069.9	2041.5
10°	2049.8	2056.7	2063.5	2078.2	2093.0	2109.6	2126.2	2123.2	2120.2	2111.9	2103.6
12.5°	1822.2	1830.5	1838.8	1868.3	1897.8	1935.6	1973.5	2006.0	2038.5	2061.2	2083.9
15°	1514.3	1537.4	1560.5	1587.3	1614.2	1669.8	1725.4	1793.8	1862.3	1923.2	1984.0
17.5°	1247.3	1256.0	1264.7	1293.4	1322.2	1392.2	1462.1	1541.2	1620.2	1721.2	1822.2
20°	1026.4	1034.4	1042.3	1080.1	1118.0	1172.8	1227.6	1316.5	1405.4	1513.9	1622.5
22.5°	862.3	874.8	887.3	908.4	929.6	982.2	1034.8	1113.8	1192.8	1312.7	1432.6
25°	754.9	764.0	773.0	785.9	798.8	840.7	882.7	947.8	1012.8	1122.9	1232.9
27.5°	681.5	685.3	689.1	701.9	714.8	742.0	769.3	825.2	881.2	974.6	1068.0
30°	624.0	626.7	629.3	640.7	652.0	670.5	689.1	729.5	770.0	852.5	934.9
32.5°	583.9	585.8	587.7	596.4	605.1	618.4	631.6	661.1	690.6	758.7	826.7
35°	547.6	548.8	549.9	556.3	562.8	572.6	582.4	604.7	627.1	680.8	734.5
37.5°	515.9	517.4	518.9	522.7	526.5	535.2	543.9	561.6	579.4	620.6	661.9
40°	484.9	487.5	490.1	492.8	495.4	502.6	509.8	523.4	537.0	571.1	605.1
42.5°	458.4	461.0	463.7	464.8	465.9	470.1	474.3	486.7	499.2	524.6	549.9
45°	432.7	433.8	434.9	436.1	437.2	440.6	444.0	455.0	465.9	487.9	509.8
47.5°	409.2	409.2	409.2	410.0	410.7	413.8	416.8	424.7	432.7	449.7	466.7
50°	386.5	386.5	386.5	385.4	384.3	386.1	388.0	394.1	400.1	415.3	430.4
52.5°	359.3	359.3	359.3	359.7	360.0	360.0	360.0	365.3	370.6	384.3	397.9
55°	332.1	333.6	335.1	334.0	332.8	333.6	334.3	337.7	341.1	352.1	363.1
57.5°	304.8	305.6	306.3	306.0	305.6	306.0	306.3	309.4	312.4	320.7	329.0
60°	279.1	279.1	279.1	278.4	277.6	278.4	279.1	280.6	282.1	289.7	297.3
62.5°	250.4	250.7	251.1	251.5	251.9	251.1	250.4	252.3	254.2	259.8	265.5
65°	221.6	222.0	222.4	223.5	224.7	223.9	223.1	225.0	226.9	231.1	235.2
67.5°	195.9	195.2	194.4	194.8	195.2	196.3	197.4	197.8	198.2	202.7	207.3
70°	165.7	166.4	167.2	166.8	166.4	166.8	167.2	168.3	169.4	172.8	176.2
72.5°	138.4	138.8	139.2	139.2	139.2	139.9	140.7	141.8	143.0	144.9	146.7
75°	113.5	113.5	113.5	114.2	115.0	115.4	115.7	115.7	115.7	117.2	118.8
77.5°	86.2	88.1	90.0	89.6	89.3	90.0	90.8	91.9	93.0	93.8	94.6
80°	62.8	62.8	62.8	63.2	63.5	64.7	65.8	66.6	67.3	68.8	70.3
82.5°	40.1	40.5	40.8	42.0	43.1	43.9	44.6	45.8	46.9	46.9	46.9
85°	25.0	24.2	23.4	24.2	25.0	25.7	26.5	26.9	27.2	28.0	28.7
87.5°	12.1	12.1	12.1	12.1	12.1	12.5	12.9	12.9	12.9	12.9	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831749

CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0
2.5°	1743.5	1739.0	1722.3	1705.7	1686.8	1667.9	1653.9	1639.9	1619.1	1598.3	1581.3
5°	1889.5	1868.3	1833.1	1798.0	1750.3	1702.7	1670.5	1638.4	1595.3	1552.1	1517.7
7.5°	2005.2	1968.9	1919.7	1870.6	1808.2	1745.8	1686.8	1627.8	1562.0	1496.2	1442.5
10°	2079.0	2054.4	1997.7	1940.9	1857.3	1773.8	1691.3	1608.9	1524.1	1439.4	1368.3
12.5°	2086.2	2088.4	2036.2	1984.0	1889.5	1794.9	1694.7	1594.5	1487.8	1381.2	1298.4
15°	2023.0	2061.9	2033.2	2004.5	1909.2	1813.9	1690.6	1567.3	1444.3	1321.4	1225.7
17.5°	1905.8	1989.3	1993.5	1997.7	1902.3	1807.0	1670.5	1534.0	1394.8	1255.6	1155.0
20°	1745.8	1869.1	1911.4	1953.8	1876.3	1798.7	1652.0	1505.2	1349.4	1193.6	1088.1
22.5°	1582.4	1732.2	1809.7	1887.2	1829.7	1772.2	1616.1	1459.9	1295.3	1130.8	1023.8
25°	1396.3	1559.7	1678.8	1798.0	1762.8	1727.6	1573.7	1419.8	1244.7	1069.6	960.3
27.5°	1234.1	1400.1	1543.8	1687.5	1680.0	1672.4	1519.6	1366.8	1187.5	1008.3	902.8
30°	1089.6	1244.3	1405.0	1565.8	1584.3	1602.8	1455.3	1307.8	1128.2	948.5	846.8
32.5°	961.8	1096.8	1269.2	1441.7	1478.0	1514.3	1381.2	1248.1	1070.3	892.6	794.6
35°	857.0	979.5	1152.0	1324.5	1369.8	1415.2	1299.5	1183.8	1010.6	837.3	743.9
37.5°	764.3	866.8	1035.1	1203.4	1259.0	1314.6	1211.0	1107.4	945.1	782.9	697.0
40°	687.6	770.0	924.7	1079.4	1143.7	1208.0	1122.5	1037.0	883.1	729.2	650.1
42.5°	623.3	696.6	837.0	977.3	1038.9	1100.6	1028.3	956.1	819.2	682.3	610.0
45°	568.4	627.1	754.5	882.0	940.6	999.2	937.2	875.2	754.5	633.9	566.5
47.5°	517.0	567.3	676.2	785.1	837.3	889.5	841.1	792.7	690.6	588.5	527.6
50°	470.9	511.3	606.6	701.9	747.3	792.7	750.0	707.2	623.3	539.3	486.4
52.5°	430.8	463.7	543.5	623.3	662.2	701.2	664.5	627.8	561.2	494.7	448.5
55°	391.1	419.0	488.3	557.5	583.9	610.4	582.1	553.7	500.0	446.3	407.3
57.5°	354.0	379.0	435.7	492.4	512.8	533.3	507.5	481.8	441.4	400.9	368.4
60°	317.7	338.1	385.4	432.7	445.1	457.6	436.8	416.0	387.7	359.3	330.2
62.5°	284.0	302.6	337.7	372.9	381.2	389.5	373.7	357.8	336.2	314.7	292.0
65°	249.2	263.2	292.0	320.7	326.0	331.3	317.3	303.3	287.1	270.8	254.2
67.5°	217.1	226.9	250.4	273.8	274.2	274.6	263.2	251.9	242.8	233.7	220.5
70°	185.7	195.2	210.7	226.2	226.5	226.9	217.8	208.8	202.0	195.2	185.3
72.5°	153.5	160.4	172.1	183.8	183.0	182.3	176.6	170.9	165.7	160.4	153.2
75°	124.4	130.1	138.0	146.0	143.7	141.4	138.4	135.4	130.9	126.3	121.8
77.5°	98.0	101.4	105.9	110.4	108.9	107.4	104.8	102.1	98.7	95.3	93.4
80°	71.9	73.4	76.4	79.4	78.7	77.9	74.9	71.9	71.1	70.3	67.7
82.5°	48.8	50.7	51.4	52.2	51.8	51.4	49.2	46.9	46.1	45.4	45.0
85°	29.1	29.5	29.9	30.3	29.1	28.0	27.2	26.5	26.5	26.5	26.1
87.5°	13.2	13.6	13.6	13.6	13.2	12.9	12.1	11.3	11.7	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831749

CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0	1630.0
2.5°	1564.2	1549.5	1534.7	1523.4	1512.0	1492.8	1473.5	1468.9	1464.4	1458.0	1451.5
5°	1483.3	1447.0	1410.7	1378.2	1345.6	1320.3	1295.0	1278.3	1261.7	1249.6	1237.5
7.5°	1388.8	1334.3	1279.8	1241.3	1202.7	1166.0	1129.3	1117.6	1105.9	1090.0	1074.1
10°	1297.2	1237.1	1177.0	1126.7	1076.4	1040.4	1004.5	990.1	975.8	955.7	935.7
12.5°	1215.5	1149.7	1083.9	1033.2	982.6	947.8	913.0	892.2	871.4	860.0	848.7
15°	1130.1	1059.7	989.4	942.5	895.6	864.2	832.8	814.6	796.5	785.5	774.6
17.5°	1054.4	984.8	915.2	870.2	825.2	796.5	767.7	751.9	736.0	727.7	719.3
20°	982.6	914.5	846.4	802.5	758.7	735.2	711.8	701.6	691.4	684.5	677.7
22.5°	916.8	849.8	782.9	745.4	708.0	689.1	670.2	663.0	655.8	650.1	644.5
25°	851.0	791.2	731.4	699.7	667.9	652.4	636.9	629.7	622.5	616.8	611.2
27.5°	797.2	740.1	683.0	655.8	628.6	616.5	604.4	598.7	593.0	587.7	582.4
30°	745.1	694.0	642.9	619.5	596.0	585.1	574.1	568.4	562.8	557.8	552.9
32.5°	696.6	652.8	608.9	587.3	565.8	556.7	547.6	540.8	534.0	530.2	526.5
35°	650.5	611.2	571.8	554.1	536.3	527.2	518.1	512.5	506.8	503.8	500.7
37.5°	611.2	576.0	540.8	523.8	506.8	498.1	489.4	484.5	479.6	478.4	477.3
40°	571.1	540.8	510.6	493.9	477.3	469.7	462.2	459.1	456.1	455.4	454.6
42.5°	537.8	508.3	478.8	463.7	448.5	442.1	435.7	434.2	432.7	433.8	434.9
45°	499.2	474.6	450.1	436.1	422.1	416.8	411.5	410.3	409.2	411.5	413.8
47.5°	466.7	444.0	421.3	408.1	394.8	391.1	387.3	386.9	386.5	389.5	392.6
50°	433.4	411.5	389.5	379.0	368.4	365.0	361.6	362.7	363.8	368.7	373.7
52.5°	402.4	382.0	361.6	351.7	341.9	339.6	337.4	340.0	342.6	347.9	353.2
55°	368.4	349.8	331.3	323.7	316.2	313.9	311.6	316.9	322.2	327.1	332.1
57.5°	335.8	319.6	303.3	296.5	289.7	289.3	288.9	293.9	298.8	304.1	309.4
60°	301.0	287.4	273.8	268.5	263.2	264.0	264.7	270.4	276.1	280.2	284.4
62.5°	269.3	257.9	246.6	241.7	236.8	238.6	240.5	246.2	251.9	256.8	261.7
65°	237.5	228.1	218.6	215.2	211.8	214.4	217.1	222.0	226.9	230.3	233.7
67.5°	207.3	199.3	191.4	188.7	186.1	188.7	191.4	196.3	201.2	204.6	208.0
70°	175.5	169.1	162.6	160.7	158.8	161.9	164.9	169.1	173.2	176.6	180.0
72.5°	146.0	141.1	136.2	135.8	135.4	138.0	140.7	144.9	149.0	151.3	153.5
75°	117.2	114.6	111.9	111.6	111.2	113.8	116.5	118.8	121.0	122.9	124.8
77.5°	91.5	89.3	87.0	87.4	87.7	89.6	91.5	93.8	96.1	97.2	98.3
80°	65.1	64.3	63.5	64.3	65.1	66.6	68.1	69.6	71.1	71.9	72.6
82.5°	44.6	43.9	43.1	44.2	45.4	46.5	47.7	48.8	49.9	50.3	50.7
85°	25.7	26.9	28.0	28.0	28.0	28.4	28.7	29.1	29.5	29.1	28.7
87.5°	12.1	12.5	12.9	12.9	12.9	13.2	13.6	13.6	13.6	13.2	12.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831749

CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1630.0	1630.0	1630.0	1630.0
2.5°	1448.9	1446.2	1435.6	1425.1
5°	1228.4	1219.3	1216.3	1213.3
7.5°	1073.3	1072.6	1056.7	1040.8
10°	936.8	937.9	923.6	909.2
12.5°	839.2	829.8	828.6	827.5
15°	765.9	757.2	755.6	754.1
17.5°	714.0	708.7	707.2	705.7
20°	674.7	671.7	669.0	666.4
22.5°	640.7	636.9	634.6	632.4
25°	607.8	604.4	603.6	602.9
27.5°	578.3	574.1	574.1	574.1
30°	550.3	547.6	546.5	545.4
32.5°	524.2	521.9	521.9	521.9
35°	499.6	498.5	497.0	495.4
37.5°	477.3	477.3	476.5	475.8
40°	455.7	456.9	456.9	456.9
42.5°	436.1	437.2	437.2	437.2
45°	415.6	417.5	418.3	419.0
47.5°	395.6	398.6	399.4	400.1
50°	375.9	378.2	378.6	379.0
52.5°	355.9	358.5	360.4	362.3
55°	334.7	337.4	338.5	339.6
57.5°	312.0	314.7	315.0	315.4
60°	287.1	289.7	290.5	291.2
62.5°	263.2	264.7	265.5	266.3
65°	236.0	238.3	239.8	241.3
67.5°	209.9	211.8	211.8	211.8
70°	180.8	181.5	182.7	183.8
72.5°	153.9	154.3	154.3	154.3
75°	125.6	126.3	126.7	127.1
77.5°	98.7	99.1	99.1	99.1
80°	72.2	71.9	71.9	71.9
82.5°	49.5	48.4	48.4	48.4
85°	28.4	28.0	28.4	28.7
87.5°	12.9	12.9	12.9	12.9
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P831749

CATALOG NUMBER: S123DP-S560D840-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.44	18.94	17.80	19.26	19.57	19.67	21.18	20.04	21.49	21.81
	3H	19.13	20.48	19.50	20.81	21.17	21.14	22.49	21.52	22.82	23.18
	4H	19.73	21.00	20.13	21.35	21.73	21.62	22.89	22.02	23.24	23.62
	6H	20.13	21.31	20.54	21.67	22.06	21.92	23.10	22.33	23.46	23.86
	8H	20.24	21.36	20.67	21.75	22.15	22.00	23.12	22.43	23.51	23.91
	12H	20.31	21.38	20.74	21.76	22.19	22.04	23.11	22.47	23.49	23.92
4H	2H	18.08	19.35	18.48	19.70	20.08	19.91	21.18	20.30	21.53	21.90
	3H	19.96	21.02	20.37	21.42	21.82	21.58	22.63	21.99	23.03	23.44
	4H	20.68	21.64	21.12	22.05	22.49	22.18	23.14	22.62	23.55	23.99
	6H	21.19	22.02	21.65	22.46	22.92	22.62	23.45	23.08	23.89	24.35
	8H	21.34	22.12	21.80	22.56	23.03	22.75	23.52	23.21	23.96	24.43
	12H	21.44	22.13	21.92	22.61	23.08	22.82	23.51	23.30	23.99	24.46
8H	4H	20.99	21.77	21.46	22.21	22.68	22.33	23.11	22.80	23.55	24.02
	6H	21.61	22.25	22.10	22.74	23.22	22.86	23.50	23.36	23.99	24.47
	8H	21.82	22.39	22.33	22.90	23.39	23.04	23.62	23.56	24.13	24.61
	12H	21.97	22.47	22.48	22.97	23.53	23.17	23.68	23.68	24.17	24.74
12H	4H	21.02	21.72	21.51	22.20	22.67	22.34	23.03	22.82	23.51	23.98
	6H	21.66	22.23	22.17	22.74	23.23	22.88	23.45	23.39	23.96	24.45
	8H	21.92	22.43	22.43	22.92	23.49	23.11	23.61	23.62	24.10	24.67