

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332245-840

Luminaire Tested: **S123RDIP-S340D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332245-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2638.4 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332245-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332245-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27
5	69	58	50	44	63	54	46	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332245-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	2.1
10°-20°	151.6	5.7
20°-30°	218.3	8.3
30°-40°	245.9	9.3
40°-50°	235.2	8.9
50°-60°	192.6	7.3
60°-70°	130.0	4.9
70°-80°	65.4	2.5
80°-90°	18.7	0.7
90°-100°	98.1	3.7
100°-110°	277.8	10.5
110°-120°	273.3	10.4
120°-130°	218.0	8.3
130°-140°	171.9	6.5
140°-150°	128.3	4.9
150°-160°	89.4	3.4
160°-170°	52.5	2.0
170°-180°	17.1	0.6
0°-30°	424.3	16.1
0°-40°	670.2	25.4
0°-60°	1098.1	41.6
0°-90°	1312.0	49.7
90°-120°	649.2	24.6
90°-150°	1167.3	44.2
90°-180°	1326.0	50.3
0°-180°	2638.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	1	4	9	10	10	2
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	219	481	552	72
125°	102	120	205	371	435	90
135°	119	142	202	306	353	92
145°	136	156	199	251	276	85
155°	154	167	193	219	229	71
165°	169	174	185	196	199	48
175°	176	176	177	180	180	17
180°	176	176	176	176	176	



TEST NUMBER: P332245-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.2	8.4	7.6	6.9	6.2	5.9	6.1	6.3	6.5	6.7	6.6
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.8	6.8	7.9	8.9	8.6
92.5°	4.4	6.6	9.6	12.3	15.3	20.6	30.0	45.3	60.4	54.8	41.4
95°	12.1	13.2	17.2	23.2	32.5	46.4	76.7	129.9	188.4	211.7	171.7
97.5°	20.7	21.0	24.1	29.4	38.6	53.6	82.6	142.5	240.1	328.0	350.8
100°	26.5	26.8	29.3	34.2	42.8	56.8	81.7	134.5	228.4	338.0	408.3
102.5°	32.4	33.0	35.2	40.0	47.7	60.5	82.9	127.6	211.3	319.4	411.1
105°	41.4	42.5	44.6	48.9	55.6	66.8	86.0	122.8	190.3	286.9	389.3
107.5°	51.0	52.0	54.1	58.3	64.6	74.9	91.9	122.4	176.8	258.2	351.2
110°	57.8	58.9	60.7	64.6	70.7	80.7	96.7	123.8	171.7	242.0	327.3



TEST NUMBER: P332245-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.1	65.1	67.0	70.9	77.0	86.6	101.6	126.7	168.7	231.1	306.4
115°	73.1	74.6	76.7	80.3	86.3	96.0	109.6	131.3	167.7	219.4	281.2
117.5°	82.2	83.8	85.6	89.0	95.7	104.6	118.1	137.4	168.3	212.6	266.0
120°	88.5	89.6	91.4	94.9	101.7	110.6	123.5	142.0	169.6	209.4	258.0
122.5°	93.9	95.0	96.7	100.7	107.1	116.6	129.2	146.3	171.5	207.5	251.5
125°	101.7	102.4	104.5	108.5	115.2	124.9	137.4	153.1	174.5	204.8	243.1
127.5°	107.7	108.7	111.4	115.3	122.8	132.5	144.5	158.6	177.9	203.6	235.6
130°	111.4	112.4	115.6	119.9	127.4	137.0	148.9	162.4	180.3	202.7	231.6
132.5°	114.2	115.5	119.1	124.2	131.7	141.1	152.5	165.8	182.0	202.4	227.9
135°	119.2	120.6	124.5	129.9	137.4	147.0	158.0	170.3	184.5	202.0	223.1
137.5°	123.9	125.4	129.3	134.9	142.4	151.3	162.0	173.5	186.2	201.2	218.8
140°	127.0	128.9	132.4	138.1	145.2	154.2	164.5	175.2	187.3	201.0	216.2
142.5°	130.5	132.0	135.8	141.0	148.1	156.4	166.5	176.9	188.2	200.4	214.0
145°	135.9	137.0	140.3	145.6	151.7	159.9	169.2	178.7	188.7	199.4	210.9
147.5°	141.6	142.2	145.3	150.0	155.8	162.8	171.3	180.0	188.7	198.1	207.9
150°	145.2	145.6	148.5	153.1	158.0	164.5	172.7	180.3	188.7	197.0	205.9
152.5°	149.0	149.1	151.9	155.9	160.4	166.5	173.6	180.8	187.9	195.6	203.6
155°	154.5	154.5	156.6	160.3	164.2	169.2	175.2	181.0	187.0	193.1	200.2
157.5°	159.0	159.3	161.0	164.1	167.4	171.3	176.1	181.3	185.8	190.9	196.3
160°	162.4	162.4	163.8	166.6	169.2	172.7	177.0	181.3	185.2	189.1	193.8
162.5°	164.9	164.9	166.1	168.3	170.6	173.6	177.3	181.0	184.1	187.4	191.2
165°	168.7	168.4	169.2	171.0	172.4	174.9	177.7	180.3	182.4	184.9	187.7
167.5°	171.7	171.3	171.7	173.0	174.0	175.6	177.6	179.7	180.7	182.3	184.4
170°	173.4	172.7	173.1	174.1	174.9	175.6	177.3	178.7	179.6	180.6	182.4
172.5°	174.6	174.1	174.2	175.0	175.4	175.8	177.3	178.5	178.6	179.2	180.4
175°	175.9	175.6	175.2	175.9	175.9	176.3	177.0	177.7	177.3	177.3	178.0
177.5°	176.6	176.3	176.0	176.3	176.3	176.3	176.6	177.1	176.6	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P332245-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	6.5	6.5	6.5	6.6	6.4	6.4	6.4	6.2
90°	8.9	9.3	9.6	10.3	10.0	10.3	10.7	10.3
92.5°	30.1	23.8	21.0	19.2	18.6	17.5	17.9	17.2
95°	128.5	87.1	68.2	55.3	48.6	45.3	42.8	41.4
97.5°	320.2	256.5	210.5	167.8	141.5	125.4	115.7	112.7
100°	420.7	391.8	350.1	299.4	263.4	237.3	223.4	223.8
102.5°	454.1	453.2	428.9	396.8	368.7	348.1	336.5	328.2
105°	463.9	499.6	506.3	497.2	480.7	467.2	455.8	453.9
107.5°	435.8	493.7	525.0	537.8	538.1	533.4	529.6	526.3
110°	409.0	474.6	519.6	544.6	554.6	557.4	556.7	556.0



TEST NUMBER: P332245-840

CATALOG NUMBER: S123RDIP-S340D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.4	449.5	499.9	532.0	550.3	559.2	561.9	562.0
115°	347.2	409.3	461.8	500.7	527.5	543.1	550.3	552.1
117.5°	321.7	375.4	422.4	461.9	489.9	507.9	518.1	520.5
120°	308.3	356.5	399.3	435.4	463.5	483.5	492.1	494.2
122.5°	297.8	341.3	381.0	414.5	439.6	457.6	467.0	469.7
125°	283.7	322.7	356.9	385.5	408.3	423.9	432.9	435.4
127.5°	271.5	306.1	337.0	363.0	383.3	396.8	404.9	407.1
130°	263.7	295.9	324.8	349.0	367.9	380.8	388.3	391.1
132.5°	256.6	286.1	313.1	336.2	354.0	366.8	373.4	375.5
135°	246.9	272.3	295.5	315.8	333.4	344.1	350.4	352.9
137.5°	238.1	258.9	278.9	296.6	311.2	322.1	327.5	329.2
140°	233.1	251.3	268.3	283.7	297.3	307.3	313.0	312.7
142.5°	228.2	243.8	258.6	272.0	283.6	292.5	297.5	297.2
145°	222.4	234.1	245.5	255.9	264.8	272.3	275.2	275.9
147.5°	217.5	226.9	236.1	243.5	250.2	255.3	258.0	258.3
150°	214.1	222.4	229.8	236.6	242.0	245.9	248.0	248.0
152.5°	211.0	218.0	224.7	230.4	234.5	238.1	239.4	239.4
155°	206.3	212.0	217.3	221.6	224.8	227.7	228.4	228.7
157.5°	201.3	206.0	210.2	213.6	216.3	218.4	219.0	218.9
160°	198.4	202.4	205.9	208.4	210.9	213.1	213.1	212.7
162.5°	195.0	198.3	201.7	203.9	205.5	207.3	207.3	207.0
165°	190.6	192.7	195.2	197.0	198.4	199.9	199.4	199.4
167.5°	186.7	188.3	189.8	191.1	191.7	192.7	192.4	192.4
170°	184.1	185.2	186.6	187.3	187.7	188.4	188.0	188.0
172.5°	181.9	182.7	183.8	184.2	184.3	185.0	184.4	184.1
175°	178.7	179.2	179.9	179.9	179.9	180.3	179.9	179.6
177.5°	176.8	177.1	177.4	177.4	177.1	177.4	176.8	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)