

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332250-840

Luminaire Tested: **S123RDIP-S340D585U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332250-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3344.5 lumens  
Efficiency: N/A  
Efficacy: 130.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332250-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332250-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29
3	80	71	64	58	72	65	58	54	53	49	45	42	39	37	33	31	29	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	42	35	30	35	29	26	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332250-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	1.6
10°-20°	151.6	4.5
20°-30°	218.3	6.5
30°-40°	245.9	7.4
40°-50°	235.2	7.0
50°-60°	192.6	5.8
60°-70°	130.0	3.9
70°-80°	65.4	2.0
80°-90°	19.5	0.6
90°-100°	47.8	1.4
100°-110°	143.0	4.3
110°-120°	243.2	7.3
120°-130°	319.9	9.6
130°-140°	359.5	10.7
140°-150°	353.4	10.6
150°-160°	297.5	8.9
160°-170°	198.0	5.9
170°-180°	69.3	2.1
0°-30°	424.3	12.7
0°-40°	670.2	20.0
0°-60°	1098.1	32.8
0°-90°	1312.8	39.3
90°-120°	433.9	13.0
90°-150°	1466.7	43.9
90°-180°	2032.0	60.8
0°-180°	3344.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	1	6	14	16	17	3
95°	34	38	43	45	45	38
105°	130	131	136	136	137	139
115°	245	246	245	246	245	242
125°	358	360	359	357	354	319
135°	465	468	468	465	464	358
145°	564	565	567	566	564	352
155°	646	646	646	648	645	297
165°	703	702	702	705	701	198
175°	732	729	729	732	729	69
180°	733	733	733	733	733	



TEST NUMBER: P332250-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.2	8.5	7.8	7.2	6.5	6.4	6.7	7.0	7.4	7.7	7.7
90°	0.6	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3
92.5°	13.9	14.8	15.7	16.6	17.5	18.4	19.3	20.2	21.2	22.1	22.5
95°	34.0	34.8	35.7	36.7	37.6	38.6	39.6	40.6	41.6	42.6	43.1
97.5°	60.4	61.0	61.7	62.4	63.0	63.7	64.4	65.2	65.9	66.8	67.3
100°	78.4	79.1	79.9	80.7	81.4	82.1	82.7	83.4	84.0	84.6	85.0
102.5°	99.1	99.6	100.0	100.5	100.9	101.6	102.4	103.3	104.1	104.9	105.3
105°	129.6	129.9	130.1	130.4	130.7	131.3	132.5	133.6	134.8	135.9	135.9
107.5°	165.1	165.2	165.4	165.5	165.7	166.0	166.4	166.9	167.4	167.8	168.2
110°	187.2	187.4	187.7	187.9	188.2	188.4	188.7	189.0	189.2	189.6	190.1



TEST NUMBER: P332250-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	210.4	210.6	210.7	210.9	211.0	211.1	211.1	211.2	211.2	211.8
115°	244.8	245.2	245.6	246.0	246.3	246.4	246.1	245.9	245.6	245.4	245.5
117.5°	279.6	279.8	280.1	280.3	280.6	280.5	280.2	279.9	279.6	279.2	279.2
120°	301.2	302.1	302.8	303.6	304.4	304.4	303.8	303.2	302.5	301.8	301.7
122.5°	323.9	324.4	325.0	325.5	326.1	326.2	325.9	325.6	325.2	324.9	324.6
125°	358.3	358.7	359.0	359.4	359.8	359.9	359.6	359.4	359.1	358.9	358.3
127.5°	390.1	390.9	391.7	392.5	393.3	393.6	393.3	393.0	392.7	392.5	391.8
130°	411.3	412.3	413.3	414.3	415.4	415.7	415.4	415.0	414.5	414.1	413.6
132.5°	432.4	433.5	434.5	435.6	436.6	437.0	436.7	436.4	436.1	435.9	435.2
135°	464.8	465.6	466.4	467.2	467.9	468.3	468.1	468.0	467.9	467.8	467.3
137.5°	494.8	495.4	496.0	496.8	497.4	497.9	498.2	498.5	498.9	499.2	498.7
140°	515.5	516.1	516.8	517.5	518.1	518.5	518.6	518.8	518.9	519.0	518.9
142.5°	534.4	535.0	535.7	536.3	536.9	537.5	537.7	537.9	538.2	538.4	538.3
145°	563.9	564.2	564.4	564.7	564.9	565.2	565.6	566.0	566.4	566.8	566.6
147.5°	589.8	590.2	590.7	591.1	591.6	592.0	592.4	592.7	593.1	593.4	593.4
150°	607.7	607.9	608.2	608.4	608.7	608.9	609.3	609.5	609.8	610.0	610.0
152.5°	622.5	622.8	623.2	623.5	623.9	624.1	624.3	624.4	624.6	624.7	624.9
155°	645.7	645.7	645.7	645.7	645.7	645.8	645.9	646.0	646.2	646.3	646.8
157.5°	665.5	665.4	665.2	665.1	664.9	664.9	665.0	665.1	665.2	665.3	665.8
160°	677.9	677.7	677.4	677.2	676.9	676.8	676.8	676.8	676.8	676.8	677.4
162.5°	689.0	688.6	688.3	687.9	687.6	687.5	687.6	687.7	687.8	687.9	688.5
165°	703.3	703.0	702.6	702.2	701.8	701.6	701.6	701.6	701.6	701.6	702.4
167.5°	714.7	714.2	713.7	713.2	712.7	712.5	712.6	712.7	712.8	712.9	713.7
170°	721.1	720.6	720.1	719.6	719.1	718.8	718.8	718.8	718.8	718.8	719.7
172.5°	726.2	725.7	725.2	724.7	724.2	724.0	724.0	724.0	724.0	724.0	724.8
175°	731.5	731.0	730.5	730.0	729.5	729.2	729.2	729.2	729.2	729.2	730.0
177.5°	733.8	733.4	733.0	732.5	732.1	731.8	731.8	731.8	731.8	731.8	732.5
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P332250-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	7.7	7.7	7.8	7.8	7.7	7.7	7.7	7.6
90°	14.8	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	22.9	23.3	23.7	23.9	23.7	23.5	23.4	23.2
95°	43.6	44.1	44.6	44.9	44.9	44.9	44.9	44.9
97.5°	67.9	68.5	69.1	69.3	69.3	69.2	69.2	69.1
100°	85.4	85.8	86.2	86.5	86.7	87.1	87.3	87.6
102.5°	105.7	106.1	106.4	106.6	106.6	106.5	106.5	106.4
105°	135.9	135.9	135.9	136.0	136.3	136.5	136.8	137.1
107.5°	168.6	169.1	169.5	169.7	169.5	169.4	169.2	169.1
110°	190.6	191.1	191.6	191.7	191.5	191.2	191.0	190.7





TEST NUMBER: P332250-840

CATALOG NUMBER: S123RDIP-S340D585U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.4	213.0	213.6	213.9	213.9	213.8	213.8	213.7
115°	245.6	245.8	245.9	245.9	245.8	245.6	245.5	245.4
117.5°	279.2	279.1	279.1	278.9	278.6	278.2	277.9	277.5
120°	301.5	301.4	301.3	301.1	300.8	300.6	300.3	300.1
122.5°	324.2	323.9	323.6	323.2	322.9	322.4	322.1	321.7
125°	357.8	357.3	356.8	356.3	355.8	355.3	354.8	354.3
127.5°	391.0	390.3	389.6	389.0	388.4	387.8	387.2	386.6
130°	413.1	412.6	412.1	411.4	410.5	409.6	408.7	407.8
132.5°	434.5	433.9	433.3	432.7	432.0	431.3	430.6	429.9
135°	466.7	466.2	465.6	465.2	465.0	464.7	464.5	464.2
137.5°	498.1	497.6	497.1	496.6	496.0	495.5	495.0	494.5
140°	518.8	518.6	518.5	518.0	517.1	516.1	515.2	514.4
142.5°	538.1	538.0	537.9	537.5	536.7	536.0	535.3	534.6
145°	566.5	566.4	566.3	565.9	565.4	564.9	564.4	563.9
147.5°	593.4	593.4	593.4	593.0	592.3	591.5	590.8	590.0
150°	610.0	610.0	610.0	609.7	608.8	608.0	607.3	606.5
152.5°	625.2	625.4	625.6	625.3	624.7	624.0	623.4	622.7
155°	647.3	647.8	648.3	648.1	647.2	646.3	645.5	644.6
157.5°	666.4	666.9	667.4	667.3	666.6	665.9	665.2	664.5
160°	678.1	678.7	679.3	679.4	678.9	678.4	677.9	677.4
162.5°	689.1	689.8	690.4	690.3	689.5	688.7	687.9	687.1
165°	703.2	703.9	704.7	704.6	703.7	702.8	702.0	701.0
167.5°	714.5	715.3	716.1	716.1	715.3	714.5	713.7	712.9
170°	720.6	721.5	722.5	722.5	721.5	720.6	719.7	718.8
172.5°	725.5	726.3	727.1	727.1	726.2	725.3	724.4	723.5
175°	730.7	731.5	732.4	732.3	731.3	730.4	729.5	728.6
177.5°	733.2	733.8	734.4	734.3	733.6	732.9	732.2	731.4
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3

(END OF REPORT)