

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332256-840

Luminaire Tested: **S123RDIP-S340D805U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332256-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D805U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4098.4 lumens  
Efficiency: N/A  
Efficacy: 131.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332256-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332256-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	42	39	36	33	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	15
6	60	49	41	36	54	44	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	29	33	28	24	25	22	19	19	16	15	12
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332256-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	1.3
10°-20°	151.6	3.7
20°-30°	218.3	5.3
30°-40°	245.9	6.0
40°-50°	235.2	5.7
50°-60°	192.6	4.7
60°-70°	130.0	3.2
70°-80°	65.4	1.6
80°-90°	20.3	0.5
90°-100°	65.5	1.6
100°-110°	196.0	4.8
110°-120°	333.3	8.1
120°-130°	438.5	10.7
130°-140°	492.8	12.0
140°-150°	484.4	11.8
150°-160°	407.8	10.0
160°-170°	271.5	6.6
170°-180°	95.1	2.3
0°-30°	424.3	10.4
0°-40°	670.2	16.4
0°-60°	1098.1	26.8
0°-90°	1313.6	32.1
90°-120°	594.8	14.5
90°-150°	2010.5	49.1
90°-180°	2785.0	68.0
0°-180°	4098.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	1	9	19	22	24	4
95°	47	52	58	61	62	52
105°	178	180	186	186	188	190
115°	336	338	336	337	336	332
125°	491	493	492	489	486	438
135°	637	642	641	638	636	491
145°	773	775	777	776	773	483
155°	885	885	886	889	884	407
165°	964	962	962	966	961	272
175°	1003	1000	1000	1004	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P332256-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.2	8.6	8.1	7.5	6.9	6.9	7.3	7.8	8.2	8.7	8.8
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7
92.5°	19.1	20.3	21.5	22.7	23.8	25.1	26.5	27.8	29.0	30.3	30.9
95°	46.6	47.8	49.1	50.3	51.5	52.8	54.2	55.6	57.1	58.5	59.2
97.5°	82.7	83.6	84.5	85.4	86.4	87.4	88.4	89.4	90.4	91.4	92.2
100°	107.3	108.5	109.5	110.6	111.6	112.6	113.4	114.3	115.2	116.0	116.6
102.5°	135.8	136.4	137.0	137.7	138.4	139.3	140.4	141.6	142.7	143.9	144.4
105°	177.6	178.0	178.3	178.7	179.0	180.1	181.6	183.2	184.8	186.3	186.3
107.5°	226.3	226.5	226.7	226.9	227.1	227.5	228.2	228.8	229.4	230.0	230.7
110°	256.6	256.9	257.3	257.6	258.0	258.3	258.7	259.0	259.4	259.7	260.4



TEST NUMBER: P332256-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	288.4	288.6	288.8	289.0	289.1	289.2	289.3	289.4	289.4	290.3
115°	335.6	336.1	336.6	337.1	337.7	337.8	337.4	337.1	336.7	336.4	336.5
117.5°	383.2	383.6	384.0	384.3	384.7	384.6	384.2	383.6	383.2	382.7	382.7
120°	412.9	413.9	415.1	416.1	417.2	417.3	416.4	415.5	414.7	413.7	413.5
122.5°	443.9	444.6	445.5	446.2	447.0	447.2	446.7	446.3	445.8	445.4	444.8
125°	491.1	491.6	492.1	492.7	493.2	493.3	492.9	492.6	492.2	491.9	491.2
127.5°	534.7	535.8	536.9	538.1	539.2	539.6	539.2	538.8	538.4	538.0	537.0
130°	563.7	565.1	566.5	567.9	569.4	569.8	569.3	568.8	568.3	567.6	566.9
132.5°	592.8	594.2	595.6	597.0	598.4	599.0	598.5	598.1	597.7	597.3	596.5
135°	637.1	638.2	639.2	640.4	641.4	641.9	641.7	641.5	641.3	641.2	640.5
137.5°	678.2	679.1	679.9	680.9	681.8	682.4	682.9	683.3	683.8	684.2	683.5
140°	706.6	707.5	708.4	709.3	710.1	710.6	710.8	711.0	711.2	711.3	711.2
142.5°	732.6	733.5	734.3	735.2	736.1	736.7	737.0	737.3	737.6	737.9	737.7
145°	773.0	773.4	773.7	774.1	774.4	774.8	775.4	775.9	776.4	776.9	776.8
147.5°	808.4	809.0	809.6	810.2	810.9	811.4	811.9	812.4	812.9	813.4	813.4
150°	832.9	833.3	833.6	834.0	834.4	834.8	835.1	835.5	835.8	836.2	836.2
152.5°	853.2	853.6	854.1	854.6	855.2	855.6	855.8	856.0	856.2	856.4	856.7
155°	885.0	885.0	885.0	885.0	885.0	885.1	885.3	885.6	885.8	885.9	886.6
157.5°	912.2	912.0	911.8	911.6	911.4	911.4	911.5	911.7	911.8	911.9	912.7
160°	929.3	929.0	928.6	928.3	927.9	927.8	927.8	927.8	927.8	927.8	928.6
162.5°	944.4	944.0	943.5	943.0	942.5	942.3	942.5	942.6	942.7	942.9	943.7
165°	964.0	963.5	963.0	962.5	961.9	961.7	961.7	961.7	961.7	961.7	962.7
167.5°	979.7	979.0	978.3	977.5	976.8	976.6	976.7	976.8	977.0	977.1	978.3
170°	988.6	987.8	987.1	986.4	985.7	985.3	985.3	985.3	985.3	985.3	986.6
172.5°	995.4	994.8	994.1	993.4	992.7	992.3	992.3	992.3	992.3	992.3	993.4
175°	1002.7	1002.0	1001.4	1000.7	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7
177.5°	1005.7	1005.2	1004.6	1004.0	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332256-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	8.8	8.9	8.9	8.9	8.9	8.9	8.9	8.9
90°	20.4	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	31.4	32.0	32.5	32.7	32.5	32.3	32.1	31.9
95°	59.8	60.5	61.2	61.6	61.6	61.6	61.6	61.6
97.5°	93.0	93.8	94.6	95.0	94.9	94.9	94.8	94.7
100°	117.1	117.6	118.2	118.7	119.0	119.3	119.7	120.0
102.5°	144.9	145.4	145.9	146.2	146.1	146.0	146.0	145.9
105°	186.3	186.3	186.3	186.5	186.8	187.2	187.5	187.9
107.5°	231.2	231.8	232.4	232.5	232.3	232.1	231.9	231.7
110°	261.2	261.9	262.6	262.8	262.4	262.1	261.7	261.4





TEST NUMBER: P332256-840

CATALOG NUMBER: S123RDIP-S340D805U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.1	292.0	292.9	293.2	293.2	293.1	293.0	293.0
115°	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4
117.5°	382.7	382.6	382.6	382.3	381.9	381.4	380.9	380.4
120°	413.3	413.2	413.0	412.7	412.4	412.0	411.7	411.3
122.5°	444.4	443.9	443.5	443.0	442.5	442.0	441.5	441.0
125°	490.5	489.8	489.1	488.4	487.7	487.0	486.3	485.5
127.5°	536.0	535.0	534.1	533.2	532.4	531.6	530.8	530.0
130°	566.3	565.6	564.9	563.9	562.7	561.5	560.3	559.0
132.5°	595.7	594.8	594.0	593.1	592.2	591.2	590.3	589.4
135°	639.7	639.0	638.3	637.8	637.4	637.1	636.7	636.4
137.5°	682.8	682.1	681.3	680.5	679.9	679.2	678.6	677.9
140°	711.0	710.8	710.6	710.0	708.7	707.5	706.3	705.1
142.5°	737.6	737.4	737.2	736.7	735.7	734.8	733.8	732.9
145°	776.6	776.4	776.2	775.8	775.1	774.4	773.7	773.0
147.5°	813.4	813.4	813.4	812.8	811.8	810.7	809.7	808.7
150°	836.2	836.2	836.2	835.7	834.6	833.5	832.4	831.4
152.5°	856.9	857.2	857.5	857.2	856.3	855.4	854.4	853.5
155°	887.3	888.0	888.7	888.4	887.2	886.0	884.7	883.5
157.5°	913.4	914.1	914.8	914.7	913.8	912.8	911.8	910.8
160°	929.5	930.4	931.2	931.3	930.6	929.9	929.2	928.5
162.5°	944.6	945.5	946.4	946.2	945.1	944.0	942.9	941.8
165°	963.8	964.8	965.9	965.8	964.6	963.3	962.1	960.9
167.5°	979.4	980.4	981.5	981.5	980.4	979.4	978.3	977.1
170°	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.3
172.5°	994.5	995.6	996.6	996.6	995.3	994.1	992.9	991.7
175°	1001.7	1002.7	1003.8	1003.7	1002.5	1001.3	1000.0	998.8
177.5°	1004.9	1005.7	1006.5	1006.5	1005.5	1004.5	1003.6	1002.6
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1

(END OF REPORT)