

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332293-840

Luminaire Tested: **S123RDIP-S560D1025U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332293-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5905.1 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332293-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332293-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		44	44	44	37
1	95	91	87	84	86	82	79	76	67	65	63		52	51	50		39	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52		46	44	42		35	33	32	27
3	79	70	63	57	71	64	58	53	52	48	44		41	38	36		31	29	27	23
4	72	62	55	49	65	57	50	45	46	41	38		37	33	31		28	26	24	20
5	67	55	48	42	60	51	44	39	41	36	33		33	29	27		25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	28		30	26	23		23	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25		27	23	21		21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22		25	21	18		19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20		23	19	17		18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18		21	17	15		16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332293-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.5
10°-20°	249.2	4.2
20°-30°	358.8	6.1
30°-40°	404.2	6.8
40°-50°	386.7	6.5
50°-60°	316.7	5.4
60°-70°	213.7	3.6
70°-80°	107.5	1.8
80°-90°	32.3	0.5
90°-100°	277.1	4.7
100°-110°	784.7	13.3
110°-120°	771.9	13.1
120°-130°	615.7	10.4
130°-140°	485.5	8.2
140°-150°	362.3	6.1
150°-160°	252.5	4.3
160°-170°	148.4	2.5
170°-180°	48.3	0.8
0°-30°	697.6	11.8
0°-40°	1101.8	18.7
0°-60°	1805.2	30.6
0°-90°	2158.6	36.6
90°-120°	1833.8	31.1
90°-150°	3297.3	55.8
90°-180°	3746.0	63.4
0°-180°	5905.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	2	12	25	28	29	4
95°	34	111	598	174	117	37
105°	117	173	810	1417	1282	124
115°	207	258	620	1359	1559	205
125°	287	339	579	1048	1230	255
135°	337	402	571	863	997	260
145°	384	440	564	708	779	241
155°	436	471	545	620	646	201
165°	477	490	522	554	564	134
175°	497	498	501	508	507	47
180°	498	498	498	498	498	



TEST NUMBER: P332293-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.2	14.1	13.0	12.1	11.0	10.7	11.3	11.9	12.5	13.1	12.7
90°	2.0	4.0	6.1	9.1	11.1	13.1	16.2	19.2	22.2	25.2	24.2
92.5°	12.5	18.6	27.1	34.8	43.3	58.3	84.6	128.1	170.6	155.0	116.9
95°	34.2	37.3	48.4	65.5	91.7	131.1	216.7	366.9	532.2	597.7	484.8
97.5°	58.5	59.5	68.2	83.0	108.9	151.4	233.3	402.6	678.2	926.3	991.1
100°	74.6	75.6	82.7	96.7	121.0	160.3	230.9	380.0	645.1	954.6	1153.2
102.5°	91.5	93.3	99.6	112.9	134.7	170.8	234.1	360.6	596.7	902.2	1161.2
105°	116.9	120.0	126.0	138.1	157.2	188.5	243.0	346.8	537.2	810.4	1099.7
107.5°	143.9	146.9	152.8	164.7	182.7	211.7	259.4	345.8	499.4	729.4	992.1
110°	163.3	166.3	171.4	182.5	199.5	227.8	273.2	349.8	484.8	683.5	924.3



TEST NUMBER: P332293-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.1	184.1	189.1	200.2	217.3	244.8	286.9	357.9	476.8	652.8	865.5
115°	206.6	210.7	216.7	226.8	244.0	271.1	309.4	370.9	473.7	620.0	794.4
117.5°	232.3	236.9	242.0	251.2	270.3	295.6	333.5	388.3	475.5	600.6	751.3
120°	249.9	253.0	258.0	268.1	287.3	312.5	348.8	401.2	478.8	591.7	728.8
122.5°	265.3	268.3	273.4	284.3	302.7	329.4	364.9	413.3	484.4	586.0	710.2
125°	287.3	289.3	295.4	306.4	325.6	352.8	388.1	432.4	492.9	578.7	686.5
127.5°	304.1	307.0	314.5	325.8	347.0	374.2	408.3	448.2	502.6	575.0	665.5
130°	314.5	317.5	326.6	338.7	359.8	387.1	420.3	458.7	509.1	572.6	654.2
132.5°	322.6	326.4	336.3	350.8	371.9	398.4	430.8	468.4	513.9	571.8	643.7
135°	336.7	340.7	351.8	366.9	388.1	415.3	446.6	480.8	521.2	570.6	630.1
137.5°	350.0	354.3	365.1	381.2	402.2	427.4	457.5	490.1	525.9	568.4	618.1
140°	358.9	363.9	374.0	390.1	410.3	435.5	464.7	494.9	529.2	567.5	610.9
142.5°	368.5	372.7	383.6	398.2	418.3	441.9	470.4	499.8	531.6	565.9	604.4
145°	384.1	387.1	396.2	411.3	428.4	451.6	477.8	505.0	533.2	563.5	595.7
147.5°	399.8	401.6	410.5	423.5	440.1	459.9	483.8	508.3	533.2	559.7	587.2
150°	410.3	411.3	419.3	432.4	446.6	464.7	487.9	509.1	533.2	556.4	581.6
152.5°	420.7	420.9	429.0	440.5	453.0	470.4	490.3	510.7	530.8	552.4	575.2
155°	436.5	436.5	442.5	452.6	463.7	477.8	494.9	511.1	528.2	545.3	565.5
157.5°	449.0	449.8	454.6	463.5	472.9	483.8	497.6	512.1	524.8	539.1	554.6
160°	458.7	458.7	462.7	470.7	477.8	487.9	500.0	512.1	523.2	534.2	547.3
162.5°	466.0	466.0	469.2	475.5	481.8	490.3	500.8	511.3	520.0	529.4	540.1
165°	476.8	475.7	477.8	482.8	486.9	493.9	502.0	509.1	515.1	522.2	530.2
167.5°	485.0	483.8	484.8	488.7	491.5	495.9	501.8	507.5	510.3	514.9	520.8
170°	489.9	487.9	488.9	491.9	493.9	495.9	501.0	505.0	507.1	510.1	515.1
172.5°	493.1	491.9	492.1	494.3	495.5	496.8	501.0	504.2	504.6	506.0	509.5
175°	497.0	495.9	494.9	497.0	497.0	498.0	500.0	502.0	501.0	501.0	503.0
177.5°	498.8	498.0	497.2	498.0	498.0	498.0	498.8	500.4	498.8	498.0	498.8
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P332293-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	12.8	12.8	12.9	13.2	12.8	12.9	13.0	12.6
90°	25.2	26.3	27.3	29.2	28.2	29.2	30.2	29.2
92.5°	84.8	67.4	59.5	54.2	52.4	49.4	50.4	48.6
95°	362.8	246.0	192.6	156.2	137.1	128.1	121.0	116.9
97.5°	904.6	724.6	594.5	473.9	399.6	354.3	327.0	318.3
100°	1188.5	1106.8	988.9	845.8	744.0	670.3	631.1	632.1
102.5°	1282.8	1280.2	1211.4	1120.7	1041.5	983.2	950.4	927.2
105°	1310.4	1411.3	1430.4	1404.2	1357.8	1319.5	1287.3	1282.2
107.5°	1231.0	1394.7	1483.0	1518.9	1519.7	1506.8	1495.9	1486.6
110°	1155.2	1340.7	1467.6	1538.2	1566.5	1574.6	1572.6	1570.5



TEST NUMBER: P332293-840

CATALOG NUMBER: S123RDIP-S560D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1080.2	1269.7	1412.0	1502.8	1554.4	1579.3	1587.0	1587.4
115°	980.8	1156.2	1304.3	1414.2	1489.9	1534.2	1554.4	1559.4
117.5°	908.9	1060.3	1193.3	1304.7	1383.6	1434.4	1463.5	1470.3
120°	870.9	1007.0	1128.0	1229.8	1309.4	1365.8	1390.1	1396.1
122.5°	841.1	964.3	1076.4	1170.9	1241.7	1292.5	1319.1	1326.8
125°	801.4	911.3	1008.0	1088.6	1153.2	1197.5	1222.7	1229.8
127.5°	766.7	864.6	952.0	1025.3	1082.8	1120.7	1143.5	1149.9
130°	745.0	835.7	917.3	985.8	1039.3	1075.6	1096.7	1104.8
132.5°	724.8	808.2	884.2	949.6	999.8	1036.0	1054.8	1060.5
135°	697.5	769.1	834.7	892.1	941.5	971.7	989.9	996.9
137.5°	672.8	731.4	787.9	837.7	879.2	909.9	925.1	929.8
140°	658.2	709.6	758.0	801.4	839.7	867.9	884.0	883.0
142.5°	644.5	688.7	730.6	768.3	801.0	826.0	840.5	839.5
145°	628.0	661.3	693.5	722.8	747.9	769.1	777.2	779.2
147.5°	614.5	640.9	666.9	687.7	706.8	721.1	728.8	729.6
150°	604.8	628.0	649.1	668.3	683.5	694.5	700.5	700.5
152.5°	595.9	615.9	634.7	650.6	662.5	672.8	676.4	676.4
155°	582.6	598.7	613.9	626.0	635.1	643.1	645.1	646.1
157.5°	568.6	582.0	593.7	603.2	611.1	617.1	618.7	618.5
160°	560.5	571.6	581.6	588.7	595.7	601.8	601.8	600.8
162.5°	550.8	560.3	569.6	575.8	580.5	585.6	585.6	584.6
165°	538.3	544.3	551.4	556.4	560.5	564.5	563.5	563.5
167.5°	527.4	532.0	536.0	539.7	541.5	544.3	543.3	543.3
170°	520.2	523.2	527.1	529.2	530.2	532.2	531.2	531.2
172.5°	513.7	515.9	519.2	520.4	520.6	522.6	520.8	520.0
175°	505.0	506.0	508.1	508.1	508.1	509.1	508.1	507.1
177.5°	499.6	500.4	501.2	501.2	500.4	501.2	499.6	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0

(END OF REPORT)