

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832465

Luminaire Tested: S123RDP-S340D940-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832465
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S340D940-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1313.4 lumens
 Efficiency: N/A
 Efficacy: 105.9 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 12.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832465
CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832465

CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	10663	10663	10663	10663	10663
5°	12661	12257	10730	8674	8053
10°	11471	12450	10676	6949	5962
15°	7899	10674	10564	5680	4716
20°	5495	8219	10352	4789	4145
25°	4187	6264	10043	4257	3821
30°	3644	5008	9657	3952	3539
35°	3347	4225	9110	3696	3282
40°	3053	3773	8396	3444	3048
45°	2757	3449	7623	3206	2813
50°	2503	3183	6713	2972	2524
55°	2263	2924	5838	2744	2164
60°	2028	2659	5072	2493	2045
65°	1872	2358	4365	2239	1936
70°	1520	2039	3808	2027	1574
75°	1335	1622	3227	1680	1385
80°	1209	1370	2641	1407	1308
85°	1099	1198	2001	1284	1198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8044 cd/sqm

TEST NUMBER: P832465
 CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.3	6.9
10°-20°	208.9	15.9
20°-30°	239.7	18.3
30°-40°	236.3	18.0
40°-50°	208.4	15.9
50°-60°	160.3	12.2
60°-70°	105.4	8.0
70°-80°	51.2	3.9
80°-90°	12.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.0	41.0
0°-40°	775.3	59.0
0°-60°	1143.9	87.1
0°-90°	1313.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1313.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	991	991	991	991	991	
5°	1172	1134	993	803	745	107
15°	709	958	948	510	423	200
25°	352	527	846	358	322	167
35°	255	322	693	281	250	159
45°	181	227	501	211	185	141
55°	121	156	311	146	115	108
65°	74	93	171	88	76	72
75°	32	39	78	40	33	35
85°	9	10	16	10	10	10
90°	0	0	0	0	0	

TEST NUMBER: P832465

CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1097.9	1094.4	1090.9	1089.9	1088.9	1085.7	1082.4	1075.1	1067.8	1060.3	1052.8
5°	1171.8	1172.2	1172.6	1171.6	1170.6	1166.3	1162.0	1153.1	1144.2	1134.4	1124.7
7.5°	1149.0	1155.5	1162.0	1163.2	1164.5	1167.7	1171.0	1168.9	1166.9	1163.2	1159.6
10°	1049.5	1049.1	1048.7	1056.0	1063.3	1085.1	1106.8	1118.0	1129.1	1139.1	1149.0
12.5°	887.1	887.7	888.3	912.2	936.2	956.7	977.2	1005.7	1034.1	1064.8	1095.4
15°	708.8	718.7	728.7	750.0	771.3	802.2	833.0	871.2	909.4	957.9	1006.5
17.5°	582.0	586.3	590.6	611.1	631.6	660.8	690.1	733.3	776.6	839.1	901.7
20°	479.7	483.5	487.4	502.2	517.0	545.1	573.1	614.3	655.5	717.5	779.4
22.5°	400.5	408.0	415.5	425.5	435.4	455.7	476.0	518.1	560.1	616.6	673.0
25°	352.5	356.0	359.5	368.0	376.5	396.0	415.5	443.3	471.1	527.4	583.7
27.5°	320.1	321.1	322.1	328.4	334.7	347.3	359.9	385.6	411.4	457.7	504.0
30°	293.2	295.1	296.9	301.8	306.7	315.8	324.9	343.2	361.5	402.9	444.3
32.5°	272.5	273.5	274.6	278.6	282.7	289.4	296.1	310.5	324.9	356.6	388.3
35°	254.7	254.9	255.1	258.1	261.2	267.7	274.2	286.1	298.1	321.5	344.8
37.5°	234.4	235.8	237.2	239.4	241.7	247.4	253.0	262.8	272.5	291.8	311.1
40°	217.3	218.5	219.7	222.4	225.0	229.5	233.9	242.9	251.8	268.5	285.1
42.5°	200.2	201.0	201.9	204.5	207.1	212.6	218.1	225.2	232.3	246.1	259.9
45°	181.1	183.2	185.2	188.1	190.9	195.6	200.2	207.5	214.9	226.6	238.4
47.5°	165.3	166.3	167.3	169.8	172.2	177.9	183.6	190.1	196.6	207.5	218.5
50°	149.5	149.9	150.3	152.5	154.7	159.8	164.9	172.4	179.9	190.1	200.2
52.5°	134.4	135.5	136.5	138.7	140.9	144.4	147.8	155.6	163.3	173.2	183.2
55°	120.6	121.2	121.8	123.5	125.1	129.2	133.2	139.9	146.6	155.8	164.9
57.5°	107.6	108.4	109.3	110.5	111.7	115.3	119.0	124.9	130.8	139.9	149.1
60°	94.2	95.2	96.3	97.7	99.1	101.9	104.8	110.1	115.3	123.5	131.6
62.5°	84.5	84.7	84.9	86.1	87.3	89.4	91.4	95.7	99.9	108.0	116.2
65°	73.5	74.1	74.7	75.3	76.0	77.6	79.2	82.9	86.5	92.6	98.7
67.5°	62.1	62.8	63.4	64.4	65.4	66.8	68.2	70.7	73.1	78.8	84.5
70°	48.3	48.3	48.3	50.0	51.6	54.0	56.5	58.3	60.1	64.8	69.5
72.5°	39.4	39.6	39.8	40.0	40.2	41.6	43.1	46.1	49.1	52.0	54.8
75°	32.1	32.3	32.5	32.7	32.9	33.3	33.7	34.7	35.7	39.0	42.2
77.5°	25.6	25.8	26.0	26.2	26.4	26.8	27.2	27.6	28.0	29.2	30.5
80°	19.5	19.7	19.9	20.1	20.3	20.5	20.7	21.1	21.5	22.1	22.7
82.5°	14.2	14.2	14.2	14.2	14.2	14.6	15.0	15.0	15.0	15.4	15.8
85°	8.9	8.9	8.9	9.1	9.3	9.3	9.3	9.5	9.7	9.7	9.7
87.5°	4.1	3.9	3.7	3.9	4.1	4.1	4.1	4.3	4.5	4.5	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832465

CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1051.8	1050.7	1041.0	1031.2	1021.7	1012.2	1005.0	997.9	986.0	974.0	966.5
5°	1116.9	1109.2	1093.8	1078.4	1055.2	1032.1	1012.6	993.1	968.3	943.5	922.8
7.5°	1153.3	1147.0	1128.3	1109.6	1079.0	1048.3	1017.8	987.4	950.8	914.3	883.0
10°	1154.3	1159.6	1144.2	1128.7	1094.2	1059.7	1018.2	976.8	927.7	878.5	838.1
12.5°	1118.2	1140.9	1137.7	1134.4	1099.3	1064.1	1013.8	963.4	903.1	842.8	792.2
15°	1050.5	1094.6	1107.6	1120.6	1091.6	1062.5	1005.2	948.0	877.1	806.2	748.1
17.5°	963.4	1025.1	1059.5	1093.8	1072.7	1051.6	988.8	926.0	846.2	766.4	703.3
20°	860.2	941.1	994.9	1048.7	1041.0	1033.3	968.5	903.7	817.6	731.5	663.1
22.5°	758.3	843.6	917.9	992.3	1000.2	1008.1	942.7	877.3	783.1	688.8	619.2
25°	670.4	757.1	845.6	934.2	952.0	969.9	907.8	845.6	747.9	650.3	581.0
27.5°	586.5	668.9	766.4	863.9	896.4	928.9	872.0	815.2	713.4	611.7	542.6
30°	518.1	591.8	691.3	790.8	836.1	881.4	829.2	777.0	676.1	575.1	507.5
32.5°	454.3	520.3	620.2	720.1	772.7	825.3	780.2	735.2	638.1	541.0	474.2
35°	403.9	463.0	556.2	649.5	708.3	767.2	730.3	693.3	598.5	503.6	440.5
37.5°	360.7	410.2	497.7	585.3	647.8	710.4	679.5	648.6	559.5	470.3	410.6
40°	324.9	364.7	446.2	527.6	588.9	650.3	623.9	597.5	517.7	437.8	382.0
42.5°	294.3	328.6	401.7	474.8	531.1	587.3	569.8	552.4	480.1	407.8	356.0
45°	267.3	296.1	360.5	424.8	476.6	528.4	514.6	500.8	438.5	376.1	328.6
47.5°	243.3	268.1	325.5	383.0	429.5	476.0	463.2	450.4	398.8	347.3	304.0
50°	221.4	242.5	290.4	338.3	380.2	422.0	411.4	400.9	358.2	315.6	278.2
52.5°	200.6	218.1	261.2	304.2	337.9	371.6	363.5	355.4	322.5	289.6	255.7
55°	180.9	197.0	233.3	269.7	298.5	327.4	319.2	311.1	285.5	259.9	230.1
57.5°	163.1	177.1	206.5	236.0	258.9	281.9	278.0	274.2	252.8	231.5	206.9
60°	144.2	156.8	182.2	207.5	226.0	244.5	240.0	235.6	220.3	205.1	184.0
62.5°	127.3	138.5	158.8	179.1	194.1	209.2	205.9	202.7	191.1	179.5	162.1
65°	109.7	120.6	137.1	153.5	165.3	177.1	174.2	171.4	162.7	153.9	139.9
67.5°	93.6	102.8	117.0	131.2	139.1	147.0	145.4	143.8	137.1	130.4	119.4
70°	77.4	85.3	97.1	108.9	114.3	119.8	120.4	121.0	114.9	108.9	100.7
72.5°	61.1	67.4	78.4	89.4	93.6	97.9	97.7	97.5	93.8	90.2	82.9
75°	46.9	51.6	60.1	68.6	72.3	76.0	76.8	77.6	74.1	70.7	66.6
77.5°	33.7	37.0	43.5	50.0	54.0	58.1	58.5	58.9	57.3	55.6	51.8
80°	23.8	24.8	28.8	32.9	37.2	41.4	42.0	42.6	41.0	39.4	37.0
82.5°	16.4	17.1	18.5	19.9	23.4	26.8	27.6	28.4	27.6	26.8	24.2
85°	10.0	10.2	10.8	11.4	13.0	14.6	15.4	16.2	15.8	15.4	14.0
87.5°	4.5	4.5	4.7	4.9	5.3	5.7	6.7	7.7	7.1	6.5	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832465

CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	958.9	947.4	935.8	927.5	919.1	908.8	898.4	898.0	897.6	889.9	882.2
5°	902.1	882.0	861.9	842.2	822.5	802.8	783.1	778.6	774.1	767.4	760.7
7.5°	851.7	819.6	787.5	762.4	737.2	717.5	697.8	684.4	671.0	660.6	650.3
10°	797.7	757.9	718.1	687.6	657.2	635.8	614.5	599.1	583.7	576.3	569.0
12.5°	741.6	698.4	655.1	625.3	595.4	569.8	544.3	530.2	516.2	506.1	495.9
15°	690.1	643.6	597.1	565.4	533.7	509.7	485.8	471.8	457.7	447.6	437.4
17.5°	640.1	593.2	546.3	514.2	482.1	460.4	438.7	425.0	411.4	405.1	398.8
20°	594.6	547.3	500.0	469.7	439.5	418.1	396.8	389.5	382.2	376.3	370.4
22.5°	549.5	504.0	458.6	429.5	400.5	385.0	369.6	363.7	357.8	353.4	348.9
25°	511.8	466.5	421.2	395.8	370.4	358.4	346.5	342.6	338.7	334.3	329.8
27.5°	473.6	430.5	387.5	367.2	346.9	337.1	327.4	322.5	317.6	314.0	310.3
30°	439.9	400.1	360.3	343.4	326.6	318.0	309.5	304.2	298.9	295.5	292.0
32.5°	407.4	372.0	336.7	322.3	307.9	299.5	291.2	286.1	281.1	277.0	272.9
35°	377.3	346.7	316.0	302.8	289.6	281.3	272.9	267.9	262.8	258.7	254.7
37.5°	350.9	323.1	295.3	282.9	270.5	263.2	255.9	250.6	245.3	241.1	236.8
40°	326.1	301.6	277.0	265.0	253.0	245.1	237.2	232.5	227.9	224.0	220.1
42.5°	304.2	281.7	259.1	247.4	235.6	228.1	220.5	215.1	209.6	207.3	205.1
45°	281.1	261.2	241.3	229.9	218.5	210.6	202.7	198.0	193.3	191.3	189.3
47.5°	260.8	242.3	223.8	212.6	201.5	194.3	187.2	183.6	179.9	177.1	174.2
50°	240.9	223.0	205.1	194.3	183.6	177.5	171.4	166.9	162.5	160.4	158.4
52.5°	221.8	205.5	189.3	178.3	167.3	161.4	155.6	151.7	147.8	143.6	139.3
55°	200.2	186.0	171.8	162.1	152.3	146.2	140.1	135.7	131.2	126.7	122.3
57.5°	182.4	168.4	154.3	145.6	136.9	131.0	125.1	120.2	115.3	111.7	108.0
60°	162.9	150.7	138.5	130.0	121.4	115.8	110.1	105.4	100.7	98.9	97.1
62.5°	144.6	133.2	121.8	114.3	106.8	101.3	95.9	92.8	89.8	88.5	87.3
65°	125.9	116.2	106.4	99.5	92.6	87.9	83.3	81.8	80.4	79.4	78.4
67.5°	108.4	100.1	91.8	85.7	79.6	76.4	73.1	71.5	69.9	68.6	67.4
70°	92.6	85.3	78.0	72.7	67.4	64.4	61.3	59.9	58.5	56.3	54.0
72.5°	75.5	69.9	64.2	60.1	56.1	53.4	50.8	47.9	45.1	43.1	41.0
75°	62.5	56.9	51.2	47.3	43.5	40.4	37.4	36.4	35.3	34.7	34.1
77.5°	47.9	43.1	38.2	35.1	32.1	30.7	29.2	28.6	28.0	27.8	27.6
80°	34.5	30.5	26.4	24.8	23.2	22.7	22.3	21.9	21.5	21.3	21.1
82.5°	21.5	19.5	17.5	17.1	16.7	16.4	16.2	16.0	15.8	15.6	15.4
85°	12.6	11.8	11.0	10.8	10.6	10.4	10.2	10.2	10.2	10.2	10.2
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.1	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832465

CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	990.6	990.6	990.6	990.6
2.5°	880.2	878.1	877.3	876.5
5°	754.4	748.1	746.7	745.3
7.5°	647.6	645.0	636.3	627.5
10°	560.9	552.8	549.1	545.5
12.5°	488.4	480.9	479.7	478.5
15°	432.2	426.9	425.0	423.2
17.5°	395.2	391.5	389.3	387.1
20°	367.8	365.1	363.5	361.9
22.5°	346.9	344.8	343.6	342.4
25°	326.8	323.7	322.7	321.7
27.5°	307.7	305.0	304.0	303.0
30°	289.8	287.6	286.1	284.7
32.5°	270.3	267.7	266.8	266.0
35°	253.0	251.4	250.6	249.8
37.5°	234.8	232.7	231.5	230.3
40°	219.1	218.1	217.5	216.9
42.5°	203.3	201.5	201.3	201.0
45°	187.4	185.6	185.2	184.8
47.5°	172.6	171.0	170.8	170.6
50°	156.2	153.9	152.3	150.7
52.5°	137.3	135.3	133.8	132.4
55°	120.0	117.8	116.6	115.3
57.5°	107.0	106.0	105.4	104.8
60°	96.5	95.9	95.4	95.0
62.5°	86.7	86.1	86.1	86.1
65°	77.8	77.2	76.6	76.0
67.5°	66.2	65.0	64.8	64.6
70°	52.2	50.4	50.2	50.0
72.5°	40.8	40.6	40.2	39.8
75°	33.7	33.3	33.3	33.3
77.5°	27.2	26.8	26.8	26.8
80°	20.9	20.7	20.9	21.1
82.5°	15.4	15.4	15.2	15.0
85°	10.0	9.7	9.7	9.7
87.5°	4.9	4.9	4.9	4.9
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832465

CATALOG NUMBER: S123RDP-S340D940-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.93	14.38	13.29	14.70	15.01	17.59	19.05	17.96	19.36	19.68
	3H	14.19	15.50	14.57	15.82	16.19	19.13	20.44	19.51	20.76	21.13
	4H	14.60	15.82	15.00	16.17	16.55	19.65	20.87	20.05	21.22	21.60
	6H	14.91	16.04	15.32	16.40	16.80	19.99	21.12	20.40	21.48	21.88
	8H	15.01	16.08	15.44	16.47	16.88	20.09	21.16	20.51	21.55	21.95
	12H	15.08	16.11	15.51	16.49	16.92	20.14	21.16	20.57	21.54	21.97
4H	2H	13.72	14.94	14.12	15.29	15.67	17.66	18.88	18.06	19.23	19.61
	3H	15.14	16.15	15.55	16.55	16.95	19.36	20.37	19.78	20.78	21.18
	4H	15.62	16.53	16.05	16.94	17.38	19.99	20.90	20.43	21.32	21.76
	6H	16.02	16.80	16.48	17.25	17.71	20.46	21.25	20.92	21.69	22.15
	8H	16.15	16.89	16.62	17.33	17.80	20.60	21.34	21.07	21.78	22.25
	12H	16.25	16.91	16.74	17.39	17.86	20.69	21.35	21.17	21.83	22.30
8H	4H	15.97	16.71	16.44	17.15	17.62	20.00	20.74	20.47	21.18	21.65
	6H	16.46	17.06	16.96	17.55	18.03	20.52	21.12	21.02	21.62	22.09
	8H	16.65	17.19	17.17	17.70	18.19	20.70	21.25	21.22	21.76	22.25
	12H	16.81	17.29	17.33	17.78	18.35	20.85	21.32	21.36	21.82	22.38
12H	4H	16.01	16.67	16.49	17.15	17.62	19.98	20.63	20.46	21.11	21.58
	6H	16.51	17.06	17.03	17.57	18.06	20.49	21.03	21.01	21.55	22.04
	8H	16.76	17.24	17.27	17.73	18.30	20.71	21.19	21.22	21.68	22.25