

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332273-840

Luminaire Tested: **S123RDIP-S560D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332273-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3620.9 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332273-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332273-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	51	49	47	43
3	84	74	67	61	78	70	64	58	61	56	52	53	50	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28	25
7	61	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332273-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	2.5
10°-20°	249.2	6.9
20°-30°	358.8	9.9
30°-40°	404.2	11.2
40°-50°	386.7	10.7
50°-60°	316.7	8.7
60°-70°	213.7	5.9
70°-80°	107.5	3.0
80°-90°	29.8	0.8
90°-100°	17.5	0.5
100°-110°	83.2	2.3
110°-120°	199.9	5.5
120°-130°	254.6	7.0
130°-140°	272.0	7.5
140°-150°	254.4	7.0
150°-160°	205.2	5.7
160°-170°	132.4	3.7
170°-180°	45.6	1.3
0°-30°	697.6	19.3
0°-40°	1101.8	30.4
0°-60°	1805.2	49.9
0°-90°	2156.1	59.5
90°-120°	300.6	8.3
90°-150°	1081.5	29.9
90°-180°	1465.0	40.5
0°-180°	3620.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	0	4	9	10	11	3
95°	22	8	11	13	14	27
105°	106	108	78	18	16	113
115°	199	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	269
145°	404	406	407	408	408	253
155°	445	444	445	446	444	205
165°	469	468	468	470	468	133
175°	480	479	479	481	479	46
180°	480	480	480	480	480	



TEST NUMBER: P332273-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	14.9	13.5	12.2	10.9	9.5	8.9	9.2	9.4	9.6	9.8	9.7
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	6.7	6.5	6.2	6.0	5.8	6.1	6.8	7.6	8.4	9.1	9.6
95°	21.8	18.5	15.2	12.0	8.8	7.6	8.5	9.3	10.2	11.1	11.6
97.5°	43.7	42.3	40.8	39.4	37.9	34.3	28.6	22.9	17.2	11.5	12.1
100°	60.3	61.9	63.5	65.0	66.7	61.3	48.9	36.6	24.1	11.8	12.4
102.5°	79.2	80.3	81.4	82.6	83.7	77.6	64.0	50.5	37.0	23.5	21.5
105°	106.3	107.2	108.1	109.0	109.9	106.7	99.6	92.4	85.3	78.2	64.1
107.5°	135.0	135.7	136.4	137.1	137.8	138.8	139.9	141.0	142.1	143.2	132.9
110°	154.2	154.8	155.4	156.0	156.7	157.4	158.3	159.2	160.1	161.0	158.3



TEST NUMBER: P332273-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.4	173.0	173.6	174.1	174.7	175.4	176.3	177.2	178.0	178.9	178.9
115°	199.4	200.0	200.5	200.9	201.4	202.0	202.7	203.4	204.1	204.8	205.6
117.5°	225.7	226.3	226.8	227.4	228.0	228.5	228.8	229.2	229.6	229.9	230.6
120°	242.0	242.7	243.4	244.1	244.8	245.3	245.5	245.8	246.0	246.2	246.9
122.5°	258.5	259.1	259.6	260.2	260.8	261.3	261.6	261.9	262.2	262.5	263.0
125°	281.2	281.9	282.5	283.1	283.8	284.2	284.6	284.9	285.2	285.5	285.7
127.5°	303.2	303.9	304.5	305.1	305.7	306.2	306.6	307.0	307.4	307.7	308.0
130°	316.9	317.5	318.1	318.8	319.4	319.9	320.2	320.5	320.8	321.1	321.4
132.5°	330.0	330.6	331.3	331.9	332.5	333.0	333.3	333.6	333.8	334.1	334.4
135°	350.1	350.5	351.0	351.5	351.9	352.3	352.6	353.0	353.4	353.7	353.9
137.5°	367.2	367.8	368.4	369.0	369.6	370.0	370.2	370.3	370.5	370.7	371.1
140°	378.6	379.1	379.6	380.0	380.5	380.9	381.1	381.3	381.6	381.8	382.1
142.5°	389.2	389.7	390.1	390.6	391.1	391.4	391.7	391.9	392.1	392.4	392.6
145°	403.9	404.6	405.1	405.7	406.2	406.6	406.7	406.9	407.0	407.2	407.4
147.5°	417.9	418.3	418.6	419.0	419.3	419.6	419.8	419.9	420.1	420.2	420.4
150°	426.5	426.7	426.9	427.2	427.4	427.6	427.8	427.9	428.1	428.2	428.4
152.5°	434.1	434.2	434.3	434.4	434.5	434.7	434.7	434.8	434.9	435.0	435.4
155°	445.0	444.8	444.6	444.5	444.3	444.3	444.4	444.4	444.5	444.6	445.0
157.5°	453.4	453.4	453.4	453.3	453.3	453.3	453.2	453.1	453.0	453.0	453.4
160°	458.6	458.5	458.4	458.3	458.3	458.2	458.1	458.0	458.0	457.9	458.3
162.5°	463.4	463.2	463.0	462.8	462.6	462.4	462.3	462.3	462.2	462.1	462.6
165°	469.3	469.0	468.8	468.6	468.3	468.2	468.1	468.0	467.9	467.9	468.5
167.5°	473.8	473.5	473.2	472.9	472.5	472.4	472.4	472.4	472.4	472.4	473.0
170°	476.4	476.1	475.7	475.4	475.1	474.9	474.9	474.9	474.9	474.9	475.6
172.5°	478.1	477.8	477.4	477.0	476.6	476.5	476.5	476.6	476.7	476.7	477.4
175°	480.3	479.9	479.5	479.2	478.8	478.6	478.7	478.8	478.8	478.9	479.5
177.5°	480.9	480.6	480.3	480.0	479.6	479.5	479.6	479.6	479.7	479.8	480.3
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332273-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	9.6	9.5	9.5	9.4	9.3	9.2	9.1	9.0
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.2	10.7	11.2	11.5	11.5	11.6	11.7	11.8
95°	12.2	12.7	13.3	13.5	13.5	13.5	13.5	13.5
97.5°	12.7	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.6	14.7	14.8	14.9	14.9
102.5°	19.6	17.6	15.7	14.7	14.8	14.9	15.1	15.2
105°	50.1	36.1	22.0	15.0	15.2	15.3	15.6	15.7
107.5°	122.7	112.4	102.1	91.6	81.1	70.5	59.9	49.3
110°	155.7	153.1	150.5	143.5	132.2	120.8	109.5	98.2



TEST NUMBER: P332273-840

CATALOG NUMBER: S123RDIP-S560D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	179.0	179.0	179.2	177.9	175.5	173.2	170.8	168.3
115°	206.4	207.2	208.0	208.5	208.8	209.2	209.5	209.8
117.5°	231.3	231.9	232.5	232.9	232.9	233.0	233.1	233.1
120°	247.5	248.1	248.7	249.1	249.1	249.1	249.1	249.1
122.5°	263.4	263.9	264.3	264.5	264.6	264.7	264.7	264.8
125°	285.8	286.0	286.1	286.3	286.4	286.6	286.8	286.9
127.5°	308.2	308.5	308.8	308.8	308.6	308.5	308.3	308.2
130°	321.8	322.1	322.4	322.6	322.3	322.2	322.0	321.8
132.5°	334.7	335.0	335.3	335.4	335.1	334.9	334.7	334.5
135°	354.2	354.4	354.6	354.6	354.4	354.2	353.9	353.7
137.5°	371.4	371.8	372.2	372.3	372.1	372.0	371.8	371.7
140°	382.4	382.7	383.1	383.1	383.0	382.8	382.7	382.5
142.5°	392.9	393.1	393.4	393.4	393.2	392.9	392.7	392.5
145°	407.5	407.7	407.8	407.9	407.9	407.9	407.9	407.9
147.5°	420.5	420.7	420.9	420.8	420.4	420.0	419.7	419.3
150°	428.6	428.7	428.9	428.8	428.6	428.4	428.1	427.9
152.5°	435.7	436.0	436.3	436.2	435.9	435.5	435.0	434.7
155°	445.5	445.9	446.3	446.2	445.8	445.2	444.7	444.2
157.5°	453.9	454.4	454.9	454.8	454.2	453.6	452.9	452.3
160°	458.8	459.3	459.8	459.7	459.2	458.6	458.1	457.5
162.5°	463.2	463.7	464.2	464.3	463.8	463.3	462.8	462.3
165°	469.1	469.8	470.4	470.4	469.9	469.3	468.8	468.2
167.5°	473.6	474.3	474.9	474.9	474.3	473.6	473.0	472.4
170°	476.3	476.9	477.5	477.5	476.9	476.3	475.6	474.9
172.5°	478.0	478.6	479.2	479.2	478.5	477.8	477.1	476.4
175°	480.0	480.6	481.1	481.1	480.5	479.8	479.2	478.6
177.5°	480.8	481.3	481.8	481.7	481.1	480.5	479.8	479.2
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

(END OF REPORT)