

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332309-840

Luminaire Tested: **S123RDIP-S775D585U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332309-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5311.7 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332309-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332309-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	53	52	47
2	91	84	77	72	84	78	73	68	67	63	60	58	55	52	49	46	45	40
3	83	74	67	61	77	69	62	57	60	55	51	51	48	44	43	41	38	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	59	50	45	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	49	36	29	25	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14034	14034	14034
5°	14088	13894	13973
10°	14008	13719	13672
15°	13857	13397	13256
20°	13651	12997	12693
25°	13438	12545	12144
30°	13155	12026	11368
35°	12867	11506	10657
40°	12600	10891	9777
45°	12250	10286	8983
50°	11863	9597	8092
55°	11470	8811	7263
60°	11108	7967	6351
65°	10639	7055	5440
70°	10049	5923	4393
75°	9191	4662	4134
80°	8195	4135	3800
85°	6916	3656	3396



TEST NUMBER: P332309-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.3
10°-20°	340.6	6.4
20°-30°	490.5	9.2
30°-40°	552.5	10.4
40°-50°	528.6	10.0
50°-60°	432.9	8.1
60°-70°	292.0	5.5
70°-80°	146.9	2.8
80°-90°	41.0	0.8
90°-100°	28.2	0.5
100°-110°	134.3	2.5
110°-120°	322.7	6.1
120°-130°	410.9	7.7
130°-140°	439.0	8.3
140°-150°	410.5	7.7
150°-160°	331.2	6.2
160°-170°	213.7	4.0
170°-180°	73.7	1.4
0°-30°	953.6	18.0
0°-40°	1506.1	28.4
0°-60°	2467.5	46.5
0°-90°	2947.5	55.5
90°-120°	485.2	9.1
90°-150°	1745.7	32.9
90°-180°	2364.0	44.5
0°-180°	5311.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1244	1231	1202	1197	1190	350
25°	1132	1104	1056	1035	1022	520
35°	979	940	876	832	811	613
45°	805	755	676	617	590	621
55°	611	557	470	410	387	548
65°	418	358	277	227	214	413
75°	221	170	112	102	99	236
85°	56	34	30	28	28	63
90°	1	6	14	16	17	4
95°	35	13	18	22	22	43
105°	172	175	126	30	25	182
115°	322	326	331	336	339	318
125°	454	458	461	462	463	405
135°	565	568	571	572	571	435
145°	652	656	657	658	658	408
155°	718	717	718	720	717	331
165°	757	756	755	759	756	214
175°	775	773	773	777	772	74
180°	775	775	775	775	775	



TEST NUMBER: P332309-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1308.0	1307.3	1306.5	1305.8	1305.0	1303.5	1301.2	1299.0	1296.8	1294.4	1296.6
5°	1303.8	1302.6	1301.4	1300.3	1299.1	1297.1	1294.2	1291.4	1288.6	1285.9	1287.9
7.5°	1291.7	1290.5	1289.2	1287.9	1286.7	1284.1	1280.5	1276.9	1273.2	1269.5	1270.7
10°	1281.6	1279.9	1278.3	1276.7	1275.0	1272.0	1267.8	1263.6	1259.4	1255.2	1255.4
12.5°	1267.2	1265.4	1263.5	1261.7	1259.9	1256.4	1251.2	1246.1	1240.8	1235.7	1235.6
15°	1243.5	1240.9	1238.3	1235.8	1233.1	1228.6	1222.0	1215.5	1208.8	1202.2	1201.1
17.5°	1213.7	1210.7	1207.7	1204.7	1201.6	1196.0	1187.6	1179.2	1170.8	1162.6	1160.0
20°	1191.7	1187.9	1184.2	1180.4	1176.7	1170.3	1161.3	1152.5	1143.6	1134.6	1131.6
22.5°	1167.2	1162.9	1158.5	1154.2	1149.8	1143.0	1133.5	1124.0	1114.5	1105.0	1101.2
25°	1131.5	1125.6	1119.6	1113.8	1107.9	1099.5	1088.7	1077.9	1067.1	1056.3	1051.4
27.5°	1088.0	1081.6	1075.1	1068.6	1062.2	1052.9	1040.9	1028.9	1016.7	1004.7	997.8
30°	1058.4	1051.4	1044.4	1037.3	1030.3	1020.2	1007.0	993.8	980.7	967.6	959.6
32.5°	1028.9	1020.9	1012.9	1004.9	996.9	985.9	972.0	958.2	944.2	930.3	921.6
35°	979.2	970.7	962.2	953.8	945.3	933.8	919.3	904.6	890.1	875.6	865.5
37.5°	928.9	919.4	910.0	900.6	891.2	878.8	863.2	847.7	832.1	816.6	805.1
40°	896.7	886.4	876.0	865.7	855.4	841.8	825.2	808.5	791.7	775.1	762.9
42.5°	860.3	850.0	839.6	829.3	819.0	805.2	787.9	770.6	753.5	736.2	722.9
45°	804.7	794.2	783.6	773.0	762.3	748.1	729.9	711.9	693.8	675.7	662.3
47.5°	749.1	737.5	725.9	714.3	702.7	687.8	669.7	651.6	633.5	615.4	600.9
50°	708.4	697.4	686.4	675.3	664.3	649.2	630.3	611.2	592.2	573.1	558.6
52.5°	672.1	660.1	648.1	636.1	624.2	608.7	589.9	571.1	552.2	533.3	518.3
55°	611.2	599.7	588.1	576.6	565.1	549.4	529.4	509.5	489.5	469.5	455.9
57.5°	554.9	542.4	529.9	517.3	504.7	488.5	468.4	448.3	428.2	408.2	395.3
60°	516.0	503.1	490.2	477.3	464.3	448.1	428.6	409.1	389.6	370.1	357.4
62.5°	477.1	464.1	451.2	438.3	425.5	409.2	389.7	370.2	350.7	331.1	319.2
65°	417.7	404.8	391.8	378.9	366.0	350.3	332.0	313.7	295.4	277.0	265.5
67.5°	358.3	345.2	332.1	319.0	306.0	290.6	273.1	255.5	237.9	220.4	211.8
70°	319.3	306.7	294.0	281.2	268.6	254.0	237.5	221.2	204.7	188.2	180.0
72.5°	280.4	267.9	255.4	242.9	230.5	216.7	201.8	186.8	171.9	156.9	150.2
75°	221.0	209.7	198.4	187.1	175.9	163.8	150.9	137.9	125.0	112.1	109.8
77.5°	166.8	156.6	146.4	136.2	126.0	116.8	108.5	100.2	91.9	83.5	82.3
80°	132.2	122.5	112.9	103.3	93.6	86.3	81.4	76.4	71.6	66.7	65.9
82.5°	99.2	90.9	82.5	74.2	65.9	60.6	58.3	55.9	53.7	51.4	50.7
85°	56.0	50.9	45.7	40.5	35.3	32.4	31.7	31.0	30.3	29.6	29.2
87.5°	20.4	18.6	16.8	14.9	13.1	12.4	12.7	13.1	13.4	13.7	13.6
90°	0.6	1.8	3.1	4.4	5.7	7.2	8.8	10.5	12.1	13.8	14.3
92.5°	10.7	10.4	10.0	9.6	9.3	9.7	11.0	12.2	13.5	14.7	15.6
95°	35.1	29.9	24.6	19.4	14.1	12.2	13.6	15.0	16.5	17.9	18.8
97.5°	70.6	68.3	65.9	63.5	61.2	55.4	46.2	37.0	27.8	18.6	19.6
100°	97.4	99.9	102.5	105.0	107.6	98.9	78.9	59.0	39.0	19.0	20.0
102.5°	127.7	129.6	131.5	133.3	135.1	125.1	103.3	81.5	59.7	37.9	34.7
105°	171.7	173.1	174.5	175.8	177.2	172.2	160.7	149.2	137.6	126.1	103.5
107.5°	217.9	219.0	220.3	221.4	222.5	223.9	225.7	227.5	229.3	231.2	214.6
110°	248.8	249.8	250.9	251.9	252.9	254.2	255.5	256.9	258.3	259.7	255.5



TEST NUMBER: P332309-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.3	279.2	280.1	281.0	282.0	283.2	284.6	286.0	287.4	288.8	288.9
115°	321.9	322.8	323.5	324.3	325.1	326.0	327.2	328.3	329.4	330.6	331.9
117.5°	364.3	365.2	366.2	367.1	368.0	368.8	369.4	370.0	370.6	371.1	372.2
120°	390.5	391.6	392.8	393.9	395.2	395.9	396.3	396.7	397.1	397.4	398.5
122.5°	417.3	418.2	419.1	420.1	421.0	421.7	422.2	422.7	423.2	423.7	424.4
125°	453.8	454.9	456.0	457.0	458.0	458.8	459.3	459.8	460.3	460.8	461.0
127.5°	489.4	490.4	491.4	492.4	493.4	494.2	494.8	495.5	496.1	496.8	497.2
130°	511.5	512.5	513.5	514.5	515.5	516.3	516.8	517.4	517.9	518.4	518.9
132.5°	532.7	533.7	534.7	535.7	536.7	537.5	537.9	538.3	538.7	539.2	539.7
135°	565.0	565.8	566.5	567.3	568.2	568.8	569.3	569.8	570.3	570.8	571.2
137.5°	592.7	593.7	594.6	595.6	596.5	597.2	597.4	597.7	598.0	598.3	599.0
140°	611.1	611.9	612.7	613.4	614.2	614.8	615.1	615.5	615.9	616.3	616.8
142.5°	628.1	628.9	629.8	630.5	631.3	631.8	632.2	632.6	633.0	633.4	633.8
145°	652.0	652.9	653.8	654.7	655.6	656.2	656.4	656.7	656.9	657.2	657.4
147.5°	674.5	675.1	675.7	676.2	676.8	677.2	677.5	677.7	678.0	678.3	678.5
150°	688.3	688.7	689.0	689.4	689.8	690.1	690.4	690.6	690.9	691.2	691.5
152.5°	700.7	700.9	701.0	701.3	701.5	701.7	701.8	702.0	702.1	702.3	702.7
155°	718.2	718.0	717.7	717.5	717.2	717.2	717.3	717.4	717.5	717.7	718.3
157.5°	731.8	731.8	731.7	731.7	731.7	731.6	731.5	731.4	731.2	731.1	732.0
160°	740.1	740.0	739.9	739.7	739.6	739.5	739.3	739.2	739.1	739.0	739.7
162.5°	748.0	747.6	747.3	747.0	746.6	746.4	746.3	746.2	746.0	745.9	746.8
165°	757.4	757.0	756.7	756.3	755.9	755.6	755.5	755.4	755.3	755.1	756.2
167.5°	764.8	764.3	763.8	763.3	762.8	762.4	762.4	762.4	762.4	762.4	763.6
170°	768.9	768.4	767.9	767.4	766.9	766.6	766.6	766.6	766.6	766.6	767.7
172.5°	771.7	771.1	770.4	769.8	769.2	769.0	769.1	769.2	769.3	769.4	770.4
175°	775.3	774.7	774.0	773.4	772.7	772.4	772.5	772.7	772.8	773.0	773.9
177.5°	776.2	775.7	775.2	774.7	774.2	774.0	774.1	774.2	774.3	774.4	775.2
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3



TEST NUMBER: P332309-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1298.6	1300.7	1302.7	1303.6	1303.2	1302.8	1302.4	1302.1
5°	1290.0	1292.1	1294.2	1295.1	1294.6	1294.1	1293.6	1293.2
7.5°	1271.9	1273.0	1274.2	1274.4	1273.6	1272.8	1272.0	1271.2
10°	1255.7	1255.9	1256.1	1255.7	1254.5	1253.2	1252.1	1250.9
12.5°	1235.4	1235.3	1235.2	1234.4	1233.0	1231.6	1230.3	1228.9
15°	1199.9	1198.7	1197.6	1196.2	1194.6	1192.9	1191.2	1189.6
17.5°	1157.5	1155.1	1152.6	1150.1	1147.6	1145.2	1142.8	1140.3
20°	1128.5	1125.4	1122.4	1119.4	1116.6	1113.8	1111.0	1108.1
22.5°	1097.4	1093.6	1089.7	1086.5	1083.9	1081.3	1078.6	1076.0
25°	1046.5	1041.6	1036.6	1032.9	1030.3	1027.6	1025.1	1022.5
27.5°	991.0	984.2	977.3	971.9	968.0	964.0	960.1	956.1
30°	951.6	943.5	935.5	929.7	925.9	922.2	918.4	914.6
32.5°	912.8	904.1	895.3	889.0	885.0	881.1	877.2	873.2
35°	855.4	845.3	835.2	828.0	823.7	819.5	815.3	811.0
37.5°	793.6	782.1	770.6	762.3	757.1	751.8	746.7	741.4
40°	750.6	738.4	726.2	717.4	712.0	706.6	701.1	695.8
42.5°	709.4	696.1	682.8	673.7	668.8	664.0	659.1	654.3
45°	648.9	635.5	622.1	612.6	606.9	601.3	595.7	590.1
47.5°	586.2	571.7	557.1	547.3	542.3	537.2	532.3	527.3
50°	544.0	529.4	514.8	504.8	499.5	494.0	488.7	483.2
52.5°	503.1	488.0	472.8	462.8	458.0	453.1	448.3	443.4
55°	442.2	428.6	415.0	405.8	401.1	396.4	391.7	387.0
57.5°	382.4	369.5	356.7	348.2	344.3	340.2	336.2	332.2
60°	344.7	332.0	319.3	311.0	307.0	303.0	299.0	295.0
62.5°	307.3	295.4	283.5	275.4	271.1	267.0	262.9	258.6
65°	254.0	242.5	231.0	223.9	221.4	218.7	216.2	213.6
67.5°	203.2	194.6	185.9	180.3	177.5	174.7	172.0	169.2
70°	171.8	163.5	155.3	150.0	147.3	144.7	142.2	139.6
72.5°	143.5	136.7	130.1	126.1	125.0	124.0	122.9	121.8
75°	107.3	105.0	102.7	101.3	100.8	100.4	99.9	99.4
77.5°	81.0	79.7	78.5	77.6	77.2	76.6	76.1	75.7
80°	65.2	64.5	63.8	63.2	62.7	62.3	61.8	61.3
82.5°	50.0	49.3	48.6	48.2	48.1	48.0	47.9	47.8
85°	28.7	28.2	27.8	27.5	27.5	27.5	27.5	27.5
87.5°	13.6	13.5	13.4	13.3	13.1	13.0	12.9	12.7
90°	14.8	15.3	15.9	16.3	16.6	16.8	17.1	17.3
92.5°	16.4	17.2	18.0	18.5	18.7	18.8	19.0	19.1
95°	19.7	20.5	21.4	21.9	21.9	21.9	21.9	21.9
97.5°	20.6	21.6	22.6	23.2	23.3	23.4	23.6	23.7
100°	21.0	22.1	23.1	23.6	23.8	23.9	24.0	24.2
102.5°	31.5	28.4	25.2	23.7	23.9	24.2	24.4	24.6
105°	80.8	58.2	35.5	24.3	24.5	24.8	25.0	25.3
107.5°	197.9	181.4	164.7	147.9	130.8	113.7	96.6	79.6
110°	251.4	247.1	242.9	231.6	213.3	195.0	176.7	158.3



TEST NUMBER: P332309-840

CATALOG NUMBER: S123RDIP-S775D585U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.9	289.0	289.1	287.2	283.4	279.4	275.6	271.8
115°	333.2	334.5	335.8	336.6	337.1	337.7	338.2	338.7
117.5°	373.2	374.3	375.3	375.9	376.0	376.1	376.2	376.3
120°	399.5	400.5	401.5	402.0	402.0	402.0	402.0	402.0
122.5°	425.2	425.9	426.6	427.0	427.1	427.2	427.3	427.4
125°	461.3	461.5	461.8	462.1	462.3	462.6	462.8	463.1
127.5°	497.6	498.0	498.4	498.5	498.2	498.0	497.7	497.5
130°	519.4	519.9	520.4	520.6	520.3	520.1	519.8	519.6
132.5°	540.2	540.7	541.2	541.3	540.9	540.5	540.2	539.8
135°	571.6	572.0	572.3	572.3	572.0	571.6	571.2	570.8
137.5°	599.6	600.2	600.8	601.0	600.7	600.5	600.2	600.0
140°	617.3	617.8	618.3	618.4	618.2	617.9	617.7	617.4
142.5°	634.2	634.6	635.0	635.0	634.7	634.3	633.9	633.6
145°	657.7	657.9	658.2	658.3	658.3	658.3	658.3	658.3
147.5°	678.8	679.0	679.3	679.1	678.5	677.9	677.4	676.8
150°	691.7	692.0	692.2	692.2	691.8	691.4	690.9	690.6
152.5°	703.2	703.6	704.1	704.0	703.5	702.9	702.3	701.7
155°	718.9	719.6	720.2	720.1	719.4	718.6	717.9	717.1
157.5°	732.7	733.5	734.3	734.1	733.1	732.2	731.1	730.1
160°	740.5	741.2	742.0	741.9	741.1	740.2	739.3	738.4
162.5°	747.6	748.5	749.4	749.4	748.6	747.8	747.0	746.3
165°	757.2	758.2	759.2	759.3	758.4	757.5	756.6	755.7
167.5°	764.6	765.6	766.6	766.6	765.6	764.6	763.6	762.4
170°	768.7	769.7	770.7	770.7	769.7	768.7	767.7	766.6
172.5°	771.4	772.4	773.5	773.5	772.3	771.2	770.0	768.9
175°	774.8	775.7	776.6	776.5	775.5	774.5	773.5	772.3
177.5°	776.0	776.8	777.6	777.5	776.5	775.5	774.5	773.5
180°	775.3	775.3	775.3	775.3	775.3	775.3	775.3	775.3

(END OF REPORT)