

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332314-840

Luminaire Tested: **S123RDIP-S775D805U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332314-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U840-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6012.5 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13295	13295	13295	13295
5°	15847	13351	11757	13351
10°	19787	13274	10622	13274
15°	23226	13138	9686	13138
20°	25921	12936	8891	12936
25°	25508	12722	8402	12722
30°	18334	12525	7899	12525
35°	12242	12269	7573	12269
40°	9020	11960	7235	11960
45°	7566	11420	6905	11420
50°	6677	10712	6445	10712
55°	5853	9903	5814	9903
60°	5214	9128	5326	9128
65°	4579	8295	4956	8295
70°	3594	7553	4526	7553
75°	3165	6596	4134	6596
80°	2752	5604	4060	5604
85°	2223	4508	4310	4508



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	2.0
10°-20°	379.5	6.3
20°-30°	596.1	9.9
30°-40°	621.9	10.3
40°-50°	532.3	8.9
50°-60°	405.7	6.7
60°-70°	260.0	4.3
70°-80°	125.1	2.1
80°-90°	36.1	0.6
90°-100°	217.1	3.6
100°-110°	614.6	10.2
110°-120°	604.6	10.1
120°-130°	482.3	8.0
130°-140°	380.2	6.3
140°-150°	283.8	4.7
150°-160°	197.8	3.3
160°-170°	116.2	1.9
170°-180°	37.8	0.6
0°-30°	1097.0	18.2
0°-40°	1719.0	28.6
0°-60°	2656.9	44.2
0°-90°	3078.2	51.2
90°-120°	1436.3	23.9
90°-150°	2582.6	43.0
90°-180°	2934.0	48.8
0°-180°	6012.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1235	1235	1235	1235	1235	
5°	1467	1236	1088	1236	1467	151
15°	2084	1179	869	1179	2084	591
25°	2148	1071	707	1071	2148	923
35°	932	934	576	934	932	611
45°	497	750	454	750	497	391
55°	312	528	310	528	312	282
65°	180	326	195	326	180	177
75°	76	159	99	159	76	82
85°	18	36	35	36	18	21
90°	23	2	23	2	23	13
95°	92	27	92	27	92	165
105°	1004	92	1004	92	1004	991
115°	1221	162	1221	162	1221	1187
125°	963	225	963	225	963	873
135°	781	264	781	264	781	606
145°	610	301	610	301	610	388
155°	506	342	506	342	506	236
165°	441	373	441	373	441	126
175°	397	389	397	389	397	39
180°	390	390	390	390	390	



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1315.5	1317.2	1311.6	1310.8	1304.4	1302.7	1302.7	1293.8	1288.4	1281.2	1277.0
5°	1466.6	1475.1	1470.9	1461.4	1445.5	1441.8	1431.8	1415.9	1398.0	1375.7	1365.1
7.5°	1655.5	1667.1	1662.6	1647.9	1631.3	1617.9	1589.5	1563.2	1526.3	1493.9	1466.2
10°	1810.3	1798.2	1788.7	1774.3	1759.1	1734.1	1704.6	1663.9	1616.8	1579.8	1538.5
12.5°	1926.2	1924.2	1912.2	1897.4	1875.8	1852.2	1815.8	1766.3	1711.5	1658.1	1610.9
15°	2084.2	2087.4	2079.4	2064.1	2033.5	1991.7	1936.7	1916.0	1837.9	1779.7	1721.5
17.5°	2193.5	2192.9	2191.8	2170.6	2139.3	2109.6	2058.6	2004.4	1933.5	1851.6	1773.2
20°	2262.9	2257.7	2258.7	2234.8	2211.6	2177.3	2127.6	2048.8	1990.6	1896.0	1815.0
22.5°	2261.2	2260.2	2264.2	2256.0	2239.1	2212.8	2173.6	2107.2	2033.0	1937.4	1846.3
25°	2147.7	2143.4	2168.3	2175.1	2202.1	2206.9	2195.2	2158.8	2088.4	1990.0	1877.4
27.5°	1797.5	1795.1	1841.2	1899.0	1972.1	2029.0	2084.0	2110.5	2088.4	2018.0	1905.2
30°	1475.1	1524.8	1548.1	1631.6	1724.6	1835.7	1933.0	2025.5	2048.2	2017.6	1925.0
32.5°	1224.8	1268.1	1287.5	1359.2	1445.9	1576.0	1721.9	1852.9	1945.5	1968.9	1913.2
35°	931.6	932.1	976.5	1008.2	1088.6	1222.3	1364.1	1539.6	1714.0	1846.2	1860.0
37.5°	743.4	746.0	772.8	804.5	864.7	935.5	1060.3	1206.2	1407.8	1610.6	1729.6
40°	641.9	646.6	666.7	697.9	741.2	794.7	891.9	1029.5	1197.5	1423.3	1607.8
42.5°	576.7	584.4	594.8	618.8	645.7	695.7	774.4	880.5	1033.4	1246.9	1459.8
45°	497.0	501.2	509.2	520.3	544.6	579.5	632.4	703.7	830.6	1002.5	1215.5
47.5°	438.4	436.2	444.5	453.5	469.7	493.5	529.0	587.2	677.7	815.6	996.3
50°	398.7	398.1	403.9	410.8	426.2	443.6	472.7	516.5	588.4	702.7	868.2
52.5°	361.4	363.5	367.6	376.2	387.2	401.3	427.4	459.0	520.8	619.4	757.3
55°	311.9	313.6	319.3	324.1	332.0	346.3	362.7	389.1	431.4	500.2	613.8
57.5°	270.0	269.3	274.9	276.1	285.1	296.7	309.4	329.9	360.6	411.6	488.2
60°	242.2	240.5	245.3	249.0	253.8	263.3	273.9	294.0	318.3	355.8	421.4
62.5°	216.8	216.0	219.5	223.2	227.1	235.8	244.7	260.1	279.3	311.0	363.0
65°	179.8	181.4	182.9	184.5	186.6	191.9	200.4	211.0	224.2	246.4	283.9
67.5°	141.3	142.9	143.4	146.6	151.2	154.5	159.7	169.1	178.2	197.0	218.3
70°	114.2	113.7	114.2	115.8	121.6	127.4	134.3	141.2	146.9	160.2	178.1
72.5°	98.2	97.1	98.6	98.9	101.7	103.3	107.7	114.1	121.6	130.6	143.5
75°	76.1	76.1	76.1	76.1	78.3	79.3	80.9	82.5	85.1	89.4	98.9
77.5°	56.2	56.4	57.1	57.7	58.1	58.7	59.7	61.2	62.2	64.4	68.6
80°	44.4	44.9	44.4	44.9	44.9	45.9	46.6	48.1	48.7	51.3	52.9
82.5°	33.4	33.1	33.4	33.9	33.9	35.0	35.1	36.3	36.4	37.8	39.4
85°	18.0	17.0	18.0	17.5	18.5	17.5	18.0	19.0	19.0	19.6	21.7
87.5°	8.8	9.8	8.8	9.1	9.2	9.3	9.2	9.0	9.7	9.5	9.4
90°	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7	19.0	19.7	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4	91.6	121.4	133.6
95°	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3	379.8	468.2	416.9
97.5°	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5	776.3	725.6	531.2
100°	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9	903.2	747.7	505.3
102.5°	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7	909.6	706.6	467.4
105°	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4	861.4	634.8	420.8
107.5°	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2	777.1	571.3	391.1
110°	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8	724.0	535.3	379.8



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1	677.9	511.3	373.4
115°	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2	622.2	485.5	371.1
117.5°	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9	588.5	470.4	372.5
120°	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2	570.9	463.4	375.1
122.5°	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8	556.3	459.1	379.4
125°	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6	537.7	453.2	386.1
127.5°	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6	521.3	450.4	393.6
130°	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5	512.4	448.5	398.7
132.5°	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6	504.2	447.8	402.5
135°	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3	493.4	446.9	408.2
137.5°	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9	484.1	445.1	412.0
140°	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5	478.5	444.5	414.5
142.5°	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8	473.4	443.2	416.4
145°	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9	466.7	441.3	417.7
147.5°	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3	460.0	438.4	417.7
150°	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7	455.6	435.9	417.7
152.5°	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8	450.5	432.6	415.8
155°	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4	442.9	427.2	413.7
157.5°	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2	434.4	422.2	411.0
160°	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0	428.7	418.5	409.8
162.5°	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4	423.0	414.7	407.3
165°	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6	415.3	409.0	403.4
167.5°	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0	407.9	403.3	399.7
170°	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4	403.4	399.5	397.2
172.5°	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3	399.0	396.4	395.3
175°	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6	393.9	392.4	392.4
177.5°	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3	390.6	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1275.3	1273.9	1268.1	1261.3	1252.4	1246.5	1241.8	1239.3	1231.7	1222.3	1216.1
5°	1354.0	1338.2	1321.3	1300.6	1281.6	1262.0	1249.9	1235.6	1218.2	1198.6	1184.9
7.5°	1438.5	1407.3	1373.8	1339.3	1305.0	1274.4	1247.4	1224.2	1196.4	1168.3	1148.7
10°	1503.2	1457.6	1410.6	1362.5	1318.6	1277.4	1245.7	1214.5	1181.1	1148.9	1124.6
12.5°	1562.0	1502.1	1447.8	1388.8	1332.6	1283.3	1237.6	1200.9	1160.8	1126.5	1098.7
15°	1636.4	1575.1	1509.4	1419.6	1345.0	1282.6	1227.2	1179.0	1130.4	1088.1	1061.2
17.5°	1706.0	1613.7	1525.6	1450.6	1353.7	1275.8	1208.0	1150.4	1097.1	1052.3	1019.1
20°	1734.7	1645.4	1549.6	1454.0	1358.8	1271.5	1192.8	1129.3	1073.8	1023.1	992.4
22.5°	1752.0	1650.8	1550.0	1447.2	1346.2	1255.5	1177.6	1107.7	1047.6	999.4	961.5
25°	1772.2	1651.7	1540.7	1439.2	1336.1	1237.7	1145.2	1071.2	1006.1	954.8	914.6
27.5°	1785.5	1643.8	1512.6	1399.7	1295.2	1197.2	1112.4	1034.0	968.0	913.7	870.6
30°	1788.1	1637.4	1491.0	1368.9	1262.5	1172.7	1082.8	1007.7	938.0	880.3	840.1
32.5°	1791.5	1621.7	1461.8	1332.0	1223.2	1134.2	1052.8	981.1	909.6	852.8	811.8
35°	1777.6	1613.2	1417.4	1268.4	1159.4	1073.3	999.8	933.7	863.4	808.4	766.6
37.5°	1717.5	1578.7	1371.6	1196.7	1082.8	1003.0	943.1	885.4	821.0	761.6	722.4
40°	1657.0	1544.9	1336.1	1153.2	1034.2	952.2	898.3	851.2	788.8	733.4	691.1
42.5°	1566.9	1498.8	1302.2	1107.4	979.2	900.2	854.7	810.6	755.9	699.5	659.7
45°	1401.6	1410.6	1232.9	1034.7	903.0	823.7	780.9	750.2	701.7	655.1	614.4
47.5°	1194.4	1278.4	1151.7	957.2	822.7	748.3	710.9	684.2	651.4	605.7	568.6
50°	1059.0	1179.0	1086.5	905.1	772.4	698.4	661.5	639.7	611.2	575.2	539.8
52.5°	934.2	1063.2	1007.8	847.2	717.9	650.3	614.1	596.2	573.5	539.7	507.7
55°	761.8	892.5	879.8	759.7	636.0	575.2	547.8	527.7	512.3	487.0	461.6
57.5°	616.3	740.1	746.7	662.5	563.9	503.8	480.2	465.0	455.0	435.9	412.4
60°	524.5	638.1	660.4	596.9	512.3	459.5	436.2	424.0	416.1	400.8	382.8
62.5°	448.4	545.1	570.3	524.6	462.8	413.3	395.2	383.4	378.0	364.8	348.9
65°	343.2	423.5	447.8	422.4	390.2	350.5	335.8	325.7	320.9	313.6	301.8
67.5°	258.0	316.6	343.3	325.4	313.8	288.7	279.2	273.9	269.6	264.6	254.9
70°	207.2	250.6	278.1	273.4	263.9	250.6	243.8	240.0	235.8	231.6	223.1
72.5°	166.6	196.5	222.3	224.7	216.9	214.2	208.2	206.6	204.1	199.0	194.4
75°	110.5	131.1	149.1	155.9	159.2	161.8	159.2	158.6	158.0	153.9	151.2
77.5°	72.4	83.5	94.8	106.5	111.6	115.1	116.0	118.0	116.5	114.3	113.0
80°	55.5	58.2	66.0	76.1	84.0	87.3	89.4	90.4	89.9	89.4	87.3
82.5°	40.3	42.5	46.3	53.3	60.0	65.2	66.6	66.3	67.5	67.8	66.0
85°	21.7	22.2	23.2	24.3	28.0	33.8	35.4	36.5	37.6	37.6	34.3
87.5°	9.8	8.9	9.3	8.9	9.9	9.8	12.0	13.8	14.5	13.2	13.7
90°	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6	3.1	4.7	7.1
92.5°	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8	14.5	21.2	27.4
95°	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9	29.2	37.9	51.3
97.5°	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7	46.6	53.4	65.0
100°	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5	59.2	64.7	75.8
102.5°	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7	73.1	78.0	88.5
105°	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6	93.9	98.7	108.2
107.5°	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7	115.1	119.7	129.0
110°	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9	130.3	134.2	142.9



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8	144.2	148.1	156.8
115°	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9	165.0	169.8	177.6
117.5°	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9	185.5	189.5	196.7
120°	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8	198.1	202.1	210.1
122.5°	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8	210.2	214.1	222.7
125°	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0	226.6	231.4	240.0
127.5°	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1	240.4	246.3	255.2
130°	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3	248.7	255.8	265.3
132.5°	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7	255.7	263.4	274.8
135°	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7	266.9	275.6	287.4
137.5°	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1	277.4	286.0	298.6
140°	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0	285.0	293.0	305.6
142.5°	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6	292.0	300.5	311.8
145°	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8	303.2	310.3	322.1
147.5°	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2	314.6	321.5	331.7
150°	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3	322.1	328.4	338.7
152.5°	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5	329.7	336.0	345.1
155°	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8	341.8	346.6	354.5
157.5°	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6	352.2	356.1	363.0
160°	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2	359.2	362.4	368.7
162.5°	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0	365.0	367.5	372.5
165°	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4	372.6	374.3	378.2
167.5°	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9	379.0	379.8	382.7
170°	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7	382.1	382.9	385.3
172.5°	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3	385.3	385.5	387.2
175°	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2	388.5	387.7	389.2
177.5°	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6	390.0	389.4	390.0
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1214.0	1208.4	1204.7	1196.2	1190.6	1184.8	1178.8	1182.7	1182.2	1181.7	1181.7
5°	1173.3	1161.0	1149.9	1135.7	1126.7	1115.6	1107.1	1106.1	1108.2	1100.8	1096.5
7.5°	1132.9	1116.2	1100.4	1084.7	1068.0	1054.7	1046.3	1042.4	1037.0	1032.5	1027.7
10°	1104.5	1084.9	1069.5	1050.1	1032.1	1016.2	1006.1	999.3	995.5	991.9	985.0
12.5°	1075.3	1056.1	1036.6	1014.5	997.3	979.0	971.5	963.7	956.6	952.5	943.1
15°	1032.6	1007.7	987.1	963.8	944.8	926.9	916.3	900.9	898.8	893.5	884.0
17.5°	989.8	962.8	934.3	917.2	895.6	877.0	860.8	855.7	840.5	834.9	826.6
20°	955.9	931.1	909.4	886.7	855.5	838.0	825.4	818.5	806.3	798.9	793.6
22.5°	926.8	901.5	876.4	849.9	824.2	804.6	795.3	784.6	778.0	767.6	761.8
25°	885.0	857.6	827.5	798.9	780.4	765.6	750.7	741.2	731.7	727.0	716.4
27.5°	836.7	807.9	779.7	758.1	735.4	720.7	707.3	698.8	687.4	679.4	673.6
30°	810.0	776.2	751.8	732.3	703.2	689.4	679.4	668.8	660.4	651.9	646.1
32.5°	779.1	748.2	725.2	700.9	678.6	663.7	650.7	641.4	634.1	626.1	620.3
35°	730.6	704.8	681.0	656.6	640.3	624.9	609.7	601.7	594.8	587.4	582.1
37.5°	686.9	662.7	640.1	617.0	596.7	584.2	571.9	565.8	556.5	551.6	546.1
40°	659.8	636.0	611.7	589.6	568.4	558.9	547.8	538.8	530.3	526.6	520.8
42.5°	630.3	606.4	585.9	562.0	544.7	531.8	521.5	511.7	505.3	500.0	496.7
45°	586.3	565.2	545.1	521.3	504.9	493.8	482.2	473.2	467.4	463.7	457.9
47.5°	543.7	522.6	502.2	481.4	465.5	452.9	441.3	435.0	427.3	422.7	418.9
50°	512.8	493.8	472.1	453.1	437.3	424.5	415.1	407.1	400.2	394.5	391.8
52.5°	484.5	464.2	445.5	427.8	411.0	396.7	388.0	379.6	374.5	367.8	364.7
55°	437.8	418.2	402.3	384.9	368.5	356.4	345.8	338.4	333.1	325.7	321.4
57.5°	393.8	376.4	357.4	342.2	325.4	315.1	306.3	296.3	289.8	284.1	279.9
60°	364.3	344.2	327.8	313.6	298.7	285.5	277.6	269.6	262.8	256.9	253.3
62.5°	333.5	315.9	300.3	284.8	271.2	259.7	250.5	243.9	237.8	234.1	230.5
65°	286.0	272.3	256.4	243.8	231.1	222.6	215.2	209.3	205.1	202.5	199.3
67.5°	242.5	229.1	215.3	202.8	194.4	187.9	183.1	178.0	175.9	172.6	170.5
70°	214.1	200.4	188.2	178.7	170.3	165.5	162.3	158.6	156.5	152.3	150.2
72.5°	183.3	173.3	164.5	156.7	150.0	145.6	141.6	137.0	133.7	129.0	126.9
75°	144.3	135.3	128.5	123.2	119.0	113.1	107.3	102.6	101.0	99.4	98.9
77.5°	106.9	101.2	96.2	91.8	86.5	82.3	81.0	80.0	79.6	78.8	78.8
80°	84.0	78.8	75.0	69.8	66.7	66.7	66.7	65.5	66.0	66.0	66.0
82.5°	62.5	57.7	55.6	53.7	53.1	53.5	53.5	53.7	53.4	54.2	53.8
85°	32.2	32.8	33.8	33.3	33.8	33.8	34.9	34.3	34.9	33.8	34.9
87.5°	13.5	15.1	16.1	17.0	17.9	17.9	18.2	18.3	18.9	19.1	19.4
90°	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7	20.5	21.3	22.9
92.5°	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4	52.7	46.6	42.5
95°	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3	192.7	150.8	122.4
97.5°	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5	567.5	465.6	371.2
100°	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9	866.9	774.6	662.4
102.5°	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7	1002.7	948.9	877.8
105°	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4	1105.3	1120.3	1099.8
107.5°	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2	1092.4	1161.5	1189.6
110°	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8	1050.1	1149.5	1204.9



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1	994.5	1106.0	1177.0
115°	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2	905.5	1021.7	1107.7
117.5°	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9	830.4	934.6	1022.0
120°	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2	788.7	883.5	963.2
122.5°	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8	755.3	843.0	917.2
125°	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6	713.8	789.5	852.7
127.5°	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6	677.2	745.7	803.1
130°	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5	654.5	718.5	772.1
132.5°	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6	633.1	692.6	743.8
135°	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3	602.4	653.7	698.7
137.5°	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9	572.9	617.1	656.1
140°	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5	555.8	593.7	627.6
142.5°	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8	539.4	572.3	601.8
145°	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9	518.0	543.2	566.1
147.5°	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3	502.0	522.4	538.7
150°	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7	491.9	508.5	523.4
152.5°	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8	482.4	497.1	509.6
155°	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4	469.0	480.8	490.3
157.5°	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2	455.9	465.0	472.4
160°	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0	447.7	455.6	461.1
162.5°	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4	438.8	446.1	451.0
165°	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6	426.4	431.9	435.9
167.5°	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0	416.7	419.9	422.7
170°	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4	409.8	412.9	414.5
172.5°	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3	404.0	406.6	407.6
175°	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6	396.4	397.9	397.9
177.5°	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3	391.9	392.5	392.5
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1176.7	1176.3	1176.7	1175.0	1176.7	1176.3	1176.7	1181.7	1181.7	1182.2	1182.7
5°	1095.0	1094.4	1092.9	1088.1	1092.9	1094.4	1095.0	1096.5	1100.8	1108.2	1106.1
7.5°	1023.6	1022.9	1018.2	1018.3	1018.2	1022.9	1023.6	1027.7	1032.5	1037.0	1042.4
10°	981.3	981.8	975.5	971.8	975.5	981.8	981.3	985.0	991.9	995.5	999.3
12.5°	940.3	937.9	932.7	928.7	932.7	937.9	940.3	943.1	952.5	956.6	963.7
15°	886.2	880.8	868.2	869.2	868.2	880.8	886.2	884.0	893.5	898.8	900.9
17.5°	822.3	818.5	818.2	810.8	818.2	818.5	822.3	826.6	834.9	840.5	855.7
20°	785.2	782.5	783.6	776.2	783.6	782.5	785.2	793.6	798.9	806.3	818.5
22.5°	756.0	753.4	748.9	746.6	748.9	753.4	756.0	761.8	767.6	778.0	784.6
25°	713.3	709.0	704.8	707.4	704.8	709.0	713.3	716.4	727.0	731.7	741.2
27.5°	670.6	667.3	663.1	662.6	663.1	667.3	670.6	673.6	679.4	687.4	698.8
30°	643.5	640.3	638.1	635.5	638.1	640.3	643.5	646.1	651.9	660.4	668.8
32.5°	615.9	615.3	611.5	611.0	611.5	615.3	615.9	620.3	626.1	634.1	641.4
35°	580.0	576.8	575.7	576.3	575.7	576.8	580.0	582.1	587.4	594.8	601.7
37.5°	545.8	541.6	539.7	537.9	539.7	541.6	545.8	546.1	551.6	556.5	565.8
40°	521.3	517.1	516.0	514.9	516.0	517.1	521.3	520.8	526.6	530.3	538.8
42.5°	493.8	492.1	491.5	489.6	491.5	492.1	493.8	496.7	500.0	505.3	511.7
45°	456.3	455.8	452.6	453.6	452.6	455.8	456.3	457.9	463.7	467.4	473.2
47.5°	416.8	414.4	412.2	413.6	412.2	414.4	416.8	418.9	422.7	427.3	435.0
50°	389.7	388.6	383.8	384.9	383.8	388.6	389.7	391.8	394.5	400.2	407.1
52.5°	362.6	358.6	356.8	356.2	356.8	358.6	362.6	364.7	367.8	374.5	379.6
55°	317.8	313.0	310.8	309.8	310.8	313.0	317.8	321.4	325.7	333.1	338.4
57.5°	273.8	272.5	270.8	272.0	270.8	272.5	273.8	279.9	284.1	289.8	296.3
60°	247.9	247.9	247.9	247.4	247.9	247.9	247.9	253.3	256.9	262.8	269.6
62.5°	228.1	226.8	226.4	227.1	226.4	226.8	228.1	230.5	234.1	237.8	243.9
65°	197.7	197.2	195.1	194.6	195.1	197.2	197.7	199.3	202.5	205.1	209.3
67.5°	169.1	167.1	166.5	165.8	166.5	167.1	169.1	170.5	172.6	175.9	178.0
70°	147.5	146.4	143.3	143.8	143.3	146.4	147.5	150.2	152.3	156.5	158.6
72.5°	124.2	123.2	122.6	121.8	122.6	123.2	124.2	126.9	129.0	133.7	137.0
75°	98.4	97.9	97.3	99.4	97.3	97.9	98.4	98.9	99.4	101.0	102.6
77.5°	78.8	78.8	79.1	78.3	79.1	78.8	78.8	78.8	78.8	79.6	80.0
80°	66.0	66.0	65.5	65.5	65.5	66.0	66.0	66.0	66.0	66.0	65.5
82.5°	53.0	53.4	53.7	52.9	53.7	53.4	53.0	53.8	54.2	53.4	53.7
85°	34.9	34.3	35.4	34.9	35.4	34.3	34.9	34.9	33.8	34.9	34.3
87.5°	20.1	19.4	19.6	19.8	19.6	19.4	20.1	19.4	19.1	18.9	18.3
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.3	20.5	19.7
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.6	52.7	66.4
95°	107.3	100.3	94.7	91.6	94.7	100.3	107.3	122.4	150.8	192.7	284.3
97.5°	313.0	277.4	256.1	249.3	256.1	277.4	313.0	371.2	465.6	567.5	708.5
100°	582.7	525.0	494.2	495.0	494.2	525.0	582.7	662.4	774.6	866.9	930.9
102.5°	815.8	770.1	744.4	726.2	744.4	770.1	815.8	877.8	948.9	1002.7	1004.7
105°	1063.5	1033.5	1008.2	1004.3	1008.2	1033.5	1063.5	1099.8	1120.3	1105.3	1026.4
107.5°	1190.3	1180.2	1171.6	1164.4	1171.6	1180.2	1190.3	1189.6	1161.5	1092.4	964.2
110°	1226.9	1233.2	1231.6	1230.1	1231.6	1233.2	1226.9	1204.9	1149.5	1050.1	904.8



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.5	1237.1	1243.0	1243.3	1243.0	1237.1	1217.5	1177.0	1106.0	994.5	846.1
115°	1166.9	1201.6	1217.5	1221.4	1217.5	1201.6	1166.9	1107.7	1021.7	905.5	768.2
117.5°	1083.7	1123.5	1146.2	1151.7	1146.2	1123.5	1083.7	1022.0	934.6	830.4	711.9
120°	1025.6	1069.9	1088.7	1093.5	1088.7	1069.9	1025.6	963.2	883.5	788.7	682.2
122.5°	972.5	1012.3	1033.2	1039.2	1033.2	1012.3	972.5	917.2	843.0	755.3	658.8
125°	903.2	938.0	957.7	963.2	957.7	938.0	903.2	852.7	789.5	713.8	627.6
127.5°	848.1	877.8	895.6	900.7	895.6	877.8	848.1	803.1	745.7	677.2	600.6
130°	814.1	842.4	859.0	865.4	859.0	842.4	814.1	772.1	718.5	654.5	583.5
132.5°	783.0	811.5	826.2	830.6	826.2	811.5	783.0	743.8	692.6	633.1	567.6
135°	737.4	761.1	775.3	780.8	775.3	761.1	737.4	698.7	653.7	602.4	546.3
137.5°	688.6	712.7	724.7	728.3	724.7	712.7	688.6	656.1	617.1	572.9	526.9
140°	657.7	679.7	692.5	691.7	692.5	679.7	657.7	627.6	593.7	555.8	515.5
142.5°	627.3	646.9	658.3	657.5	658.3	646.9	627.3	601.8	572.3	539.4	504.8
145°	585.8	602.4	608.7	610.3	608.7	602.4	585.8	566.1	543.2	518.0	491.9
147.5°	553.6	564.8	570.9	571.5	570.9	564.8	553.6	538.7	522.4	502.0	481.3
150°	535.3	544.0	548.8	548.8	548.8	544.0	535.3	523.4	508.5	491.9	473.7
152.5°	518.9	526.9	529.8	529.8	529.8	526.9	518.9	509.6	497.1	482.4	466.8
155°	497.4	503.7	505.3	506.0	505.3	503.7	497.4	490.3	480.8	469.0	456.4
157.5°	478.6	483.3	484.6	484.4	484.6	483.3	478.6	472.4	465.0	455.9	445.2
160°	466.7	471.3	471.3	470.6	471.3	471.3	466.7	461.1	455.6	447.7	439.0
162.5°	454.6	458.7	458.7	458.0	458.7	458.7	454.6	451.0	446.1	438.8	431.4
165°	439.0	442.1	441.3	441.3	441.3	442.1	439.0	435.9	431.9	426.4	421.6
167.5°	424.1	426.4	425.6	425.6	425.6	426.4	424.1	422.7	419.9	416.7	413.0
170°	415.3	416.9	416.1	416.1	416.1	416.9	415.3	414.5	412.9	409.8	407.4
172.5°	407.7	409.3	407.9	407.3	407.9	409.3	407.7	407.6	406.6	404.0	402.3
175°	397.9	398.7	397.9	397.2	397.9	398.7	397.9	397.9	397.9	396.4	395.6
177.5°	391.9	392.5	391.3	391.3	391.3	392.5	391.9	392.5	392.5	391.9	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1178.8	1184.8	1190.6	1196.2	1204.7	1208.4	1214.0	1216.1	1222.3	1231.7	1239.3
5°	1107.1	1115.6	1126.7	1135.7	1149.9	1161.0	1173.3	1184.9	1198.6	1218.2	1235.6
7.5°	1046.3	1054.7	1068.0	1084.7	1100.4	1116.2	1132.9	1148.7	1168.3	1196.4	1224.2
10°	1006.1	1016.2	1032.1	1050.1	1069.5	1084.9	1104.5	1124.6	1148.9	1181.1	1214.5
12.5°	971.5	979.0	997.3	1014.5	1036.6	1056.1	1075.3	1098.7	1126.5	1160.8	1200.9
15°	916.3	926.9	944.8	963.8	987.1	1007.7	1032.6	1061.2	1088.1	1130.4	1179.0
17.5°	860.8	877.0	895.6	917.2	934.3	962.8	989.8	1019.1	1052.3	1097.1	1150.4
20°	825.4	838.0	855.5	886.7	909.4	931.1	955.9	992.4	1023.1	1073.8	1129.3
22.5°	795.3	804.6	824.2	849.9	876.4	901.5	926.8	961.5	999.4	1047.6	1107.7
25°	750.7	765.6	780.4	798.9	827.5	857.6	885.0	914.6	954.8	1006.1	1071.2
27.5°	707.3	720.7	735.4	758.1	779.7	807.9	836.7	870.6	913.7	968.0	1034.0
30°	679.4	689.4	703.2	732.3	751.8	776.2	810.0	840.1	880.3	938.0	1007.7
32.5°	650.7	663.7	678.6	700.9	725.2	748.2	779.1	811.8	852.8	909.6	981.1
35°	609.7	624.9	640.3	656.6	681.0	704.8	730.6	766.6	808.4	863.4	933.7
37.5°	571.9	584.2	596.7	617.0	640.1	662.7	686.9	722.4	761.6	821.0	885.4
40°	547.8	558.9	568.4	589.6	611.7	636.0	659.8	691.1	733.4	788.8	851.2
42.5°	521.5	531.8	544.7	562.0	585.9	606.4	630.3	659.7	699.5	755.9	810.6
45°	482.2	493.8	504.9	521.3	545.1	565.2	586.3	614.4	655.1	701.7	750.2
47.5°	441.3	452.9	465.5	481.4	502.2	522.6	543.7	568.6	605.7	651.4	684.2
50°	415.1	424.5	437.3	453.1	472.1	493.8	512.8	539.8	575.2	611.2	639.7
52.5°	388.0	396.7	411.0	427.8	445.5	464.2	484.5	507.7	539.7	573.5	596.2
55°	345.8	356.4	368.5	384.9	402.3	418.2	437.8	461.6	487.0	512.3	527.7
57.5°	306.3	315.1	325.4	342.2	357.4	376.4	393.8	412.4	435.9	455.0	465.0
60°	277.6	285.5	298.7	313.6	327.8	344.2	364.3	382.8	400.8	416.1	424.0
62.5°	250.5	259.7	271.2	284.8	300.3	315.9	333.5	348.9	364.8	378.0	383.4
65°	215.2	222.6	231.1	243.8	256.4	272.3	286.0	301.8	313.6	320.9	325.7
67.5°	183.1	187.9	194.4	202.8	215.3	229.1	242.5	254.9	264.6	269.6	273.9
70°	162.3	165.5	170.3	178.7	188.2	200.4	214.1	223.1	231.6	235.8	240.0
72.5°	141.6	145.6	150.0	156.7	164.5	173.3	183.3	194.4	199.0	204.1	206.6
75°	107.3	113.1	119.0	123.2	128.5	135.3	144.3	151.2	153.9	158.0	158.6
77.5°	81.0	82.3	86.5	91.8	96.2	101.2	106.9	113.0	114.3	116.5	118.0
80°	66.7	66.7	66.7	69.8	75.0	78.8	84.0	87.3	89.4	89.9	90.4
82.5°	53.5	53.5	53.1	53.7	55.6	57.7	62.5	66.0	67.8	67.5	66.3
85°	34.9	33.8	33.8	33.3	33.8	32.8	32.2	34.3	37.6	37.6	36.5
87.5°	18.2	17.9	17.9	17.0	16.1	15.1	13.5	13.7	13.2	14.5	13.8
90°	19.0	19.7	17.4	15.0	12.6	10.3	8.7	7.1	4.7	3.1	1.6
92.5°	91.6	121.4	133.6	100.3	66.3	45.6	33.9	27.4	21.2	14.5	9.8
95°	379.8	468.2	416.9	287.4	169.8	102.6	71.8	51.3	37.9	29.2	26.9
97.5°	776.3	725.6	531.2	315.4	182.7	118.6	85.2	65.0	53.4	46.6	45.7
100°	903.2	747.7	505.3	297.6	180.8	125.5	94.7	75.8	64.7	59.2	58.5
102.5°	909.6	706.6	467.4	282.5	183.3	133.7	105.5	88.5	78.0	73.1	71.7
105°	861.4	634.8	420.8	271.6	190.3	147.6	123.2	108.2	98.7	93.9	91.6
107.5°	777.1	571.3	391.1	270.8	203.2	165.8	143.1	129.0	119.7	115.1	112.7
110°	724.0	535.3	379.8	274.0	214.0	178.4	156.3	142.9	134.2	130.3	127.9



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	677.9	511.3	373.4	280.2	224.7	191.7	170.3	156.8	148.1	144.2	141.8
115°	622.2	485.5	371.1	290.5	242.4	212.4	191.1	177.6	169.8	165.0	161.9
117.5°	588.5	470.4	372.5	304.2	261.2	231.5	211.8	196.7	189.5	185.5	181.9
120°	570.9	463.4	375.1	314.3	273.2	244.8	225.0	210.1	202.1	198.1	195.8
122.5°	556.3	459.1	379.4	323.7	285.8	258.0	237.0	222.7	214.1	210.2	207.8
125°	537.7	453.2	386.1	338.7	304.0	276.3	255.0	240.0	231.4	226.6	225.0
127.5°	521.3	450.4	393.6	351.0	319.7	293.1	271.8	255.2	246.3	240.4	238.1
130°	512.4	448.5	398.7	359.2	329.2	303.2	281.9	265.3	255.8	248.7	246.3
132.5°	504.2	447.8	402.5	366.8	337.4	312.0	291.3	274.8	263.4	255.7	252.7
135°	493.4	446.9	408.2	376.6	349.7	325.3	304.0	287.4	275.6	266.9	263.7
137.5°	484.1	445.1	412.0	383.8	358.3	334.8	315.0	298.6	286.0	277.4	274.1
140°	478.5	444.5	414.5	387.7	364.0	341.0	321.3	305.6	293.0	285.0	281.0
142.5°	473.4	443.2	416.4	391.4	368.4	346.1	327.7	311.8	300.5	292.0	288.6
145°	466.7	441.3	417.7	395.6	374.3	353.8	335.6	322.1	310.3	303.2	300.8
147.5°	460.0	438.4	417.7	398.1	379.0	360.2	344.7	331.7	321.5	314.6	313.2
150°	455.6	435.9	417.7	398.7	382.1	364.0	349.7	338.7	328.4	322.1	321.3
152.5°	450.5	432.6	415.8	400.0	384.1	368.4	354.8	345.1	336.0	329.7	329.5
155°	442.9	427.2	413.7	400.3	387.7	374.3	363.1	354.5	346.6	341.8	341.8
157.5°	434.4	422.2	411.0	401.1	389.7	379.0	370.4	363.0	356.1	352.2	351.6
160°	428.7	418.5	409.8	401.1	391.6	382.1	374.3	368.7	362.4	359.2	359.2
162.5°	423.0	414.7	407.3	400.4	392.2	384.1	377.4	372.5	367.5	365.0	365.0
165°	415.3	409.0	403.4	398.7	393.1	386.9	381.3	378.2	374.3	372.6	373.4
167.5°	407.9	403.3	399.7	397.5	393.0	388.5	385.0	382.7	379.8	379.0	379.9
170°	403.4	399.5	397.2	395.6	392.4	388.5	386.9	385.3	382.9	382.1	383.7
172.5°	399.0	396.4	395.3	395.0	392.4	389.1	388.1	387.2	385.5	385.3	386.3
175°	393.9	392.4	392.4	393.1	391.6	390.0	389.2	389.2	387.7	388.5	389.2
177.5°	390.6	390.0	390.6	391.9	390.6	390.0	390.0	390.0	389.4	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1241.8	1246.5	1252.4	1261.3	1268.1	1273.9	1275.3	1277.0	1281.2	1288.4	1293.8
5°	1249.9	1262.0	1281.6	1300.6	1321.3	1338.2	1354.0	1365.1	1375.7	1398.0	1415.9
7.5°	1247.4	1274.4	1305.0	1339.3	1373.8	1407.3	1438.5	1466.2	1493.9	1526.3	1563.2
10°	1245.7	1277.4	1318.6	1362.5	1410.6	1457.6	1503.2	1538.5	1579.8	1616.8	1663.9
12.5°	1237.6	1283.3	1332.6	1388.8	1447.8	1502.1	1562.0	1610.9	1658.1	1711.5	1766.3
15°	1227.2	1282.6	1345.0	1419.6	1509.4	1575.1	1636.4	1721.5	1779.7	1837.9	1916.0
17.5°	1208.0	1275.8	1353.7	1450.6	1525.6	1613.7	1706.0	1773.2	1851.6	1933.5	2004.4
20°	1192.8	1271.5	1358.8	1454.0	1549.6	1645.4	1734.7	1815.0	1896.0	1990.6	2048.8
22.5°	1177.6	1255.5	1346.2	1447.2	1550.0	1650.8	1752.0	1846.3	1937.4	2033.0	2107.2
25°	1145.2	1237.7	1336.1	1439.2	1540.7	1651.7	1772.2	1877.4	1990.0	2088.4	2158.8
27.5°	1112.4	1197.2	1295.2	1399.7	1512.6	1643.8	1785.5	1905.2	2018.0	2088.4	2110.5
30°	1082.8	1172.7	1262.5	1368.9	1491.0	1637.4	1788.1	1925.0	2017.6	2048.2	2025.5
32.5°	1052.8	1134.2	1223.2	1332.0	1461.8	1621.7	1791.5	1913.2	1968.9	1945.5	1852.9
35°	999.8	1073.3	1159.4	1268.4	1417.4	1613.2	1777.6	1860.0	1846.2	1714.0	1539.6
37.5°	943.1	1003.0	1082.8	1196.7	1371.6	1578.7	1717.5	1729.6	1610.6	1407.8	1206.2
40°	898.3	952.2	1034.2	1153.2	1336.1	1544.9	1657.0	1607.8	1423.3	1197.5	1029.5
42.5°	854.7	900.2	979.2	1107.4	1302.2	1498.8	1566.9	1459.8	1246.9	1033.4	880.5
45°	780.9	823.7	903.0	1034.7	1232.9	1410.6	1401.6	1215.5	1002.5	830.6	703.7
47.5°	710.9	748.3	822.7	957.2	1151.7	1278.4	1194.4	996.3	815.6	677.7	587.2
50°	661.5	698.4	772.4	905.1	1086.5	1179.0	1059.0	868.2	702.7	588.4	516.5
52.5°	614.1	650.3	717.9	847.2	1007.8	1063.2	934.2	757.3	619.4	520.8	459.0
55°	547.8	575.2	636.0	759.7	879.8	892.5	761.8	613.8	500.2	431.4	389.1
57.5°	480.2	503.8	563.9	662.5	746.7	740.1	616.3	488.2	411.6	360.6	329.9
60°	436.2	459.5	512.3	596.9	660.4	638.1	524.5	421.4	355.8	318.3	294.0
62.5°	395.2	413.3	462.8	524.6	570.3	545.1	448.4	363.0	311.0	279.3	260.1
65°	335.8	350.5	390.2	422.4	447.8	423.5	343.2	283.9	246.4	224.2	211.0
67.5°	279.2	288.7	313.8	325.4	343.3	316.6	258.0	218.3	197.0	178.2	169.1
70°	243.8	250.6	263.9	273.4	278.1	250.6	207.2	178.1	160.2	146.9	141.2
72.5°	208.2	214.2	216.9	224.7	222.3	196.5	166.6	143.5	130.6	121.6	114.1
75°	159.2	161.8	159.2	155.9	149.1	131.1	110.5	98.9	89.4	85.1	82.5
77.5°	116.0	115.1	111.6	106.5	94.8	83.5	72.4	68.6	64.4	62.2	61.2
80°	89.4	87.3	84.0	76.1	66.0	58.2	55.5	52.9	51.3	48.7	48.1
82.5°	66.6	65.2	60.0	53.3	46.3	42.5	40.3	39.4	37.8	36.4	36.3
85°	35.4	33.8	28.0	24.3	23.2	22.2	21.7	21.7	19.6	19.0	19.0
87.5°	12.0	9.8	9.9	8.9	9.3	8.9	9.8	9.4	9.5	9.7	9.0
90°	3.1	4.7	7.1	8.7	10.3	12.6	15.0	17.4	19.7	19.0	19.7
92.5°	14.5	21.2	27.4	33.9	45.6	66.3	100.3	133.6	121.4	91.6	66.4
95°	29.2	37.9	51.3	71.8	102.6	169.8	287.4	416.9	468.2	379.8	284.3
97.5°	46.6	53.4	65.0	85.2	118.6	182.7	315.4	531.2	725.6	776.3	708.5
100°	59.2	64.7	75.8	94.7	125.5	180.8	297.6	505.3	747.7	903.2	930.9
102.5°	73.1	78.0	88.5	105.5	133.7	183.3	282.5	467.4	706.6	909.6	1004.7
105°	93.9	98.7	108.2	123.2	147.6	190.3	271.6	420.8	634.8	861.4	1026.4
107.5°	115.1	119.7	129.0	143.1	165.8	203.2	270.8	391.1	571.3	777.1	964.2
110°	130.3	134.2	142.9	156.3	178.4	214.0	274.0	379.8	535.3	724.0	904.8



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.2	148.1	156.8	170.3	191.7	224.7	280.2	373.4	511.3	677.9	846.1
115°	165.0	169.8	177.6	191.1	212.4	242.4	290.5	371.1	485.5	622.2	768.2
117.5°	185.5	189.5	196.7	211.8	231.5	261.2	304.2	372.5	470.4	588.5	711.9
120°	198.1	202.1	210.1	225.0	244.8	273.2	314.3	375.1	463.4	570.9	682.2
122.5°	210.2	214.1	222.7	237.0	258.0	285.8	323.7	379.4	459.1	556.3	658.8
125°	226.6	231.4	240.0	255.0	276.3	304.0	338.7	386.1	453.2	537.7	627.6
127.5°	240.4	246.3	255.2	271.8	293.1	319.7	351.0	393.6	450.4	521.3	600.6
130°	248.7	255.8	265.3	281.9	303.2	329.2	359.2	398.7	448.5	512.4	583.5
132.5°	255.7	263.4	274.8	291.3	312.0	337.4	366.8	402.5	447.8	504.2	567.6
135°	266.9	275.6	287.4	304.0	325.3	349.7	376.6	408.2	446.9	493.4	546.3
137.5°	277.4	286.0	298.6	315.0	334.8	358.3	383.8	412.0	445.1	484.1	526.9
140°	285.0	293.0	305.6	321.3	341.0	364.0	387.7	414.5	444.5	478.5	515.5
142.5°	292.0	300.5	311.8	327.7	346.1	368.4	391.4	416.4	443.2	473.4	504.8
145°	303.2	310.3	322.1	335.6	353.8	374.3	395.6	417.7	441.3	466.7	491.9
147.5°	314.6	321.5	331.7	344.7	360.2	379.0	398.1	417.7	438.4	460.0	481.3
150°	322.1	328.4	338.7	349.7	364.0	382.1	398.7	417.7	435.9	455.6	473.7
152.5°	329.7	336.0	345.1	354.8	368.4	384.1	400.0	415.8	432.6	450.5	466.8
155°	341.8	346.6	354.5	363.1	374.3	387.7	400.3	413.7	427.2	442.9	456.4
157.5°	352.2	356.1	363.0	370.4	379.0	389.7	401.1	411.0	422.2	434.4	445.2
160°	359.2	362.4	368.7	374.3	382.1	391.6	401.1	409.8	418.5	428.7	439.0
162.5°	365.0	367.5	372.5	377.4	384.1	392.2	400.4	407.3	414.7	423.0	431.4
165°	372.6	374.3	378.2	381.3	386.9	393.1	398.7	403.4	409.0	415.3	421.6
167.5°	379.0	379.8	382.7	385.0	388.5	393.0	397.5	399.7	403.3	407.9	413.0
170°	382.1	382.9	385.3	386.9	388.5	392.4	395.6	397.2	399.5	403.4	407.4
172.5°	385.3	385.5	387.2	388.1	389.1	392.4	395.0	395.3	396.4	399.0	402.3
175°	388.5	387.7	389.2	389.2	390.0	391.6	393.1	392.4	392.4	393.9	395.6
177.5°	390.0	389.4	390.0	390.0	390.0	390.6	391.9	390.6	390.0	390.6	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1302.7	1302.7	1304.4	1310.8	1311.6	1317.2	1315.5
5°	1431.8	1441.8	1445.5	1461.4	1470.9	1475.1	1466.6
7.5°	1589.5	1617.9	1631.3	1647.9	1662.6	1667.1	1655.5
10°	1704.6	1734.1	1759.1	1774.3	1788.7	1798.2	1810.3
12.5°	1815.8	1852.2	1875.8	1897.4	1912.2	1924.2	1926.2
15°	1936.7	1991.7	2033.5	2064.1	2079.4	2087.4	2084.2
17.5°	2058.6	2109.6	2139.3	2170.6	2191.8	2192.9	2193.5
20°	2127.6	2177.3	2211.6	2234.8	2258.7	2257.7	2262.9
22.5°	2173.6	2212.8	2239.1	2256.0	2264.2	2260.2	2261.2
25°	2195.2	2206.9	2202.1	2175.1	2168.3	2143.4	2147.7
27.5°	2084.0	2029.0	1972.1	1899.0	1841.2	1795.1	1797.5
30°	1933.0	1835.7	1724.6	1631.6	1548.1	1524.8	1475.1
32.5°	1721.9	1576.0	1445.9	1359.2	1287.5	1268.1	1224.8
35°	1364.1	1222.3	1088.6	1008.2	976.5	932.1	931.6
37.5°	1060.3	935.5	864.7	804.5	772.8	746.0	743.4
40°	891.9	794.7	741.2	697.9	666.7	646.6	641.9
42.5°	774.4	695.7	645.7	618.8	594.8	584.4	576.7
45°	632.4	579.5	544.6	520.3	509.2	501.2	497.0
47.5°	529.0	493.5	469.7	453.5	444.5	436.2	438.4
50°	472.7	443.6	426.2	410.8	403.9	398.1	398.7
52.5°	427.4	401.3	387.2	376.2	367.6	363.5	361.4
55°	362.7	346.3	332.0	324.1	319.3	313.6	311.9
57.5°	309.4	296.7	285.1	276.1	274.9	269.3	270.0
60°	273.9	263.3	253.8	249.0	245.3	240.5	242.2
62.5°	244.7	235.8	227.1	223.2	219.5	216.0	216.8
65°	200.4	191.9	186.6	184.5	182.9	181.4	179.8
67.5°	159.7	154.5	151.2	146.6	143.4	142.9	141.3
70°	134.3	127.4	121.6	115.8	114.2	113.7	114.2
72.5°	107.7	103.3	101.7	98.9	98.6	97.1	98.2
75°	80.9	79.3	78.3	76.1	76.1	76.1	76.1
77.5°	59.7	58.7	58.1	57.7	57.1	56.4	56.2
80°	46.6	45.9	44.9	44.9	44.4	44.9	44.4
82.5°	35.1	35.0	33.9	33.9	33.4	33.1	33.4
85°	18.0	17.5	18.5	17.5	18.0	17.0	18.0
87.5°	9.2	9.3	9.2	9.1	8.8	9.8	8.8
90°	20.5	21.3	22.9	22.1	22.9	23.7	22.9
92.5°	52.7	46.6	42.5	41.1	38.7	39.5	38.1
95°	192.7	150.8	122.4	107.3	100.3	94.7	91.6
97.5°	567.5	465.6	371.2	313.0	277.4	256.1	249.3
100°	866.9	774.6	662.4	582.7	525.0	494.2	495.0
102.5°	1002.7	948.9	877.8	815.8	770.1	744.4	726.2
105°	1105.3	1120.3	1099.8	1063.5	1033.5	1008.2	1004.3
107.5°	1092.4	1161.5	1189.6	1190.3	1180.2	1171.6	1164.4
110°	1050.1	1149.5	1204.9	1226.9	1233.2	1231.6	1230.1



TEST NUMBER: P332314-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	994.5	1106.0	1177.0	1217.5	1237.1	1243.0	1243.3
115°	905.5	1021.7	1107.7	1166.9	1201.6	1217.5	1221.4
117.5°	830.4	934.6	1022.0	1083.7	1123.5	1146.2	1151.7
120°	788.7	883.5	963.2	1025.6	1069.9	1088.7	1093.5
122.5°	755.3	843.0	917.2	972.5	1012.3	1033.2	1039.2
125°	713.8	789.5	852.7	903.2	938.0	957.7	963.2
127.5°	677.2	745.7	803.1	848.1	877.8	895.6	900.7
130°	654.5	718.5	772.1	814.1	842.4	859.0	865.4
132.5°	633.1	692.6	743.8	783.0	811.5	826.2	830.6
135°	602.4	653.7	698.7	737.4	761.1	775.3	780.8
137.5°	572.9	617.1	656.1	688.6	712.7	724.7	728.3
140°	555.8	593.7	627.6	657.7	679.7	692.5	691.7
142.5°	539.4	572.3	601.8	627.3	646.9	658.3	657.5
145°	518.0	543.2	566.1	585.8	602.4	608.7	610.3
147.5°	502.0	522.4	538.7	553.6	564.8	570.9	571.5
150°	491.9	508.5	523.4	535.3	544.0	548.8	548.8
152.5°	482.4	497.1	509.6	518.9	526.9	529.8	529.8
155°	469.0	480.8	490.3	497.4	503.7	505.3	506.0
157.5°	455.9	465.0	472.4	478.6	483.3	484.6	484.4
160°	447.7	455.6	461.1	466.7	471.3	471.3	470.6
162.5°	438.8	446.1	451.0	454.6	458.7	458.7	458.0
165°	426.4	431.9	435.9	439.0	442.1	441.3	441.3
167.5°	416.7	419.9	422.7	424.1	426.4	425.6	425.6
170°	409.8	412.9	414.5	415.3	416.9	416.1	416.1
172.5°	404.0	406.6	407.6	407.7	409.3	407.9	407.3
175°	396.4	397.9	397.9	397.9	398.7	397.9	397.2
177.5°	391.9	392.5	392.5	391.9	392.5	391.3	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0

(END OF REPORT)