

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332641-927

Luminaire Tested: **S124DIP-S1020D590U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332641-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D590U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5130.3 lumens  
Efficiency: N/A  
Efficacy: 105.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332641-927

CATALOG NUMBER: S124DIP-S1020D590U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332641-927

CATALOG NUMBER: S124DIP-S1020D590U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44	41
4	78	66	58	52	73	63	56	50	56	50	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11035	11035	11035
5°	11068	10935	11015
10°	10999	10846	10900
15°	10866	10692	10719
20°	10689	10501	10510
25°	10488	10283	10253
30°	10241	10026	9934
35°	9984	9758	9629
40°	9720	9454	9280
45°	9442	9154	8978
50°	9134	8887	8611
55°	8802	8541	8263
60°	8472	8152	7905
65°	8097	7782	7469
70°	7678	7291	7006
75°	7037	6697	6525
80°	6267	6007	5858
85°	5483	5280	5169



TEST NUMBER: P332641-927

CATALOG NUMBER: S124DIP-S1020D590U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.7	2.5
10°-20°	362.7	7.1
20°-30°	533.8	10.4
30°-40°	620.6	12.1
40°-50°	620.6	12.1
50°-60°	542.9	10.6
60°-70°	403.2	7.9
70°-80°	229.1	4.5
80°-90°	67.9	1.3
90°-100°	38.5	0.8
100°-110°	114.1	2.2
110°-120°	193.7	3.8
120°-130°	255.5	5.0
130°-140°	286.9	5.6
140°-150°	281.9	5.5
150°-160°	237.1	4.6
160°-170°	157.8	3.1
170°-180°	55.2	1.1
0°-30°	1025.2	20.0
0°-40°	1645.9	32.1
0°-60°	2809.4	54.8
0°-90°	3509.5	68.4
90°-120°	346.4	6.8
90°-150°	1170.7	22.8
90°-180°	1621.0	31.6
0°-180°	5130.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1367	1367	1367	1367	1367	
5°	1366	1361	1349	1361	1359	129
15°	1300	1295	1279	1285	1282	366
25°	1177	1169	1154	1155	1151	541
35°	1013	1005	990	983	977	633
45°	827	819	802	790	786	637
55°	625	621	607	594	587	560
65°	424	418	407	397	391	420
75°	226	220	215	210	209	240
85°	59	59	57	57	56	65
90°	1	6	10	13	14	5
95°	27	31	34	36	36	30
105°	105	106	108	109	110	112
115°	197	197	196	196	195	194
125°	287	287	286	286	285	256
135°	370	373	373	372	370	286
145°	450	451	452	451	450	281
155°	515	515	515	516	515	237
165°	561	559	558	561	559	158
175°	583	581	581	583	581	55
180°	584	584	584	584	584	



TEST NUMBER: P332641-927

CATALOG NUMBER: S124DIP-S1020D590U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1370.4	1369.8	1369.2	1368.7	1368.1	1366.7	1364.5	1362.4	1360.3	1358.1	1360.1
5°	1365.8	1364.9	1363.9	1362.9	1361.9	1360.1	1357.4	1354.7	1352.1	1349.4	1352.1
7.5°	1353.1	1352.1	1351.1	1350.2	1349.2	1347.3	1344.3	1341.3	1338.3	1335.4	1337.5
10°	1341.7	1340.8	1339.7	1338.8	1337.8	1335.8	1332.6	1329.4	1326.3	1323.1	1325.0
12.5°	1326.8	1325.9	1324.8	1323.9	1322.9	1320.7	1317.4	1314.1	1310.7	1307.3	1309.5
15°	1300.1	1299.1	1298.1	1297.2	1296.2	1293.9	1290.2	1286.6	1282.9	1279.3	1280.7
17.5°	1267.9	1266.7	1265.4	1264.2	1263.1	1260.7	1257.2	1253.8	1250.3	1246.9	1247.8
20°	1244.2	1243.0	1241.8	1240.6	1239.4	1236.9	1233.3	1229.6	1226.0	1222.3	1223.1
22.5°	1218.9	1217.2	1215.6	1214.0	1212.4	1209.7	1206.1	1202.5	1198.8	1195.2	1196.5
25°	1177.4	1175.8	1174.0	1172.3	1170.6	1168.1	1164.7	1161.3	1157.9	1154.4	1154.7
27.5°	1130.1	1128.4	1126.6	1124.8	1123.1	1120.6	1117.5	1114.3	1111.1	1107.9	1107.4
30°	1098.6	1096.6	1094.6	1092.7	1090.8	1088.2	1085.1	1081.9	1078.7	1075.5	1074.6
32.5°	1065.2	1063.5	1061.8	1060.0	1058.3	1055.7	1052.3	1049.0	1045.6	1042.3	1041.1
35°	1013.1	1011.5	1009.7	1008.1	1006.3	1003.8	1000.4	997.0	993.6	990.1	988.4
37.5°	958.1	956.6	955.1	953.5	951.9	949.4	945.6	942.0	938.3	934.7	932.9
40°	922.3	920.3	918.3	916.4	914.4	911.6	908.0	904.4	900.7	897.1	894.6
42.5°	883.7	882.5	881.3	880.2	879.0	876.4	872.4	868.3	864.3	860.2	857.4
45°	827.0	825.2	823.6	821.8	820.1	817.3	813.4	809.5	805.6	801.8	799.1
47.5°	767.5	766.4	765.2	764.1	762.9	760.5	756.9	753.3	749.7	746.1	743.1
50°	727.3	726.3	725.3	724.4	723.3	721.2	717.8	714.4	711.0	707.6	704.2
52.5°	687.9	686.7	685.5	684.4	683.2	680.8	677.2	673.6	669.9	666.4	663.4
55°	625.4	624.6	623.9	623.2	622.5	620.4	617.0	613.6	610.2	606.8	603.9
57.5°	565.9	565.0	564.2	563.3	562.5	560.4	557.1	553.7	550.3	547.0	544.2
60°	524.7	523.4	522.2	521.0	519.8	517.6	514.4	511.3	508.1	504.9	502.7
62.5°	484.3	483.3	482.3	481.3	480.2	478.1	474.7	471.3	467.9	464.6	462.6
65°	423.9	422.6	421.4	420.3	419.0	417.2	414.7	412.3	409.9	407.4	405.0
67.5°	363.0	361.9	360.8	359.7	358.5	356.8	354.4	352.1	349.7	347.5	345.1
70°	325.3	323.6	321.9	320.2	318.5	316.6	314.7	312.8	310.9	308.9	306.9
72.5°	285.0	283.3	281.6	279.9	278.2	276.6	275.0	273.5	271.9	270.3	268.8
75°	225.6	224.4	223.2	222.0	220.8	219.5	218.3	217.1	215.9	214.7	213.7
77.5°	168.9	168.3	167.8	167.3	166.8	166.0	164.9	163.8	162.7	161.7	161.4
80°	134.8	134.0	133.2	132.5	131.8	131.2	130.7	130.2	129.8	129.2	128.7
82.5°	101.4	101.1	100.8	100.4	100.1	99.8	99.7	99.7	99.6	99.4	99.2
85°	59.2	59.2	59.2	59.2	59.2	58.9	58.4	57.9	57.4	57.0	57.0
87.5°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
90°	1.3	2.5	3.6	4.7	5.8	6.7	7.5	8.3	9.1	9.9	10.5
92.5°	9.7	10.9	12.2	13.5	14.7	15.6	16.2	16.8	17.3	17.9	18.2
95°	27.1	28.0	28.9	29.8	30.7	31.5	32.2	33.0	33.7	34.3	34.6
97.5°	47.4	48.1	48.8	49.5	50.2	51.0	51.8	52.7	53.5	54.3	54.7
100°	63.2	63.7	64.1	64.5	64.9	65.5	66.4	67.3	68.2	69.2	69.3
102.5°	79.9	80.0	80.2	80.3	80.5	81.0	81.8	82.6	83.5	84.3	84.6
105°	105.3	105.4	105.4	105.6	105.7	105.9	106.3	106.7	107.1	107.5	107.8
107.5°	131.9	132.1	132.1	132.3	132.5	132.5	132.5	132.6	132.7	132.8	133.0
110°	150.0	150.2	150.4	150.6	150.8	150.8	150.8	150.7	150.6	150.4	150.3



TEST NUMBER: P332641-927

CATALOG NUMBER: S124DIP-S1020D590U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.8	168.8	168.9	168.9	169.0	168.9	168.7	168.5	168.3	168.2	168.1
115°	197.0	197.0	197.0	197.0	197.0	196.9	196.7	196.5	196.3	196.1	196.0
117.5°	223.6	223.6	223.7	223.8	223.9	223.9	223.7	223.6	223.4	223.3	222.9
120°	241.3	241.7	242.1	242.5	242.9	243.0	242.6	242.3	242.0	241.7	241.2
122.5°	259.7	259.8	260.0	260.2	260.3	260.4	260.2	260.1	259.9	259.8	259.4
125°	286.9	286.9	286.9	286.9	286.9	286.8	286.8	286.7	286.5	286.5	286.2
127.5°	311.6	311.9	312.2	312.5	312.8	312.8	312.7	312.5	312.4	312.2	312.0
130°	328.9	329.2	329.5	329.9	330.1	330.3	330.3	330.3	330.3	330.3	330.1
132.5°	346.7	346.9	347.1	347.3	347.5	347.6	347.5	347.5	347.4	347.3	347.1
135°	370.0	370.7	371.2	371.9	372.5	372.7	372.7	372.7	372.7	372.7	372.6
137.5°	395.5	395.8	396.1	396.3	396.6	396.9	397.0	397.2	397.4	397.5	397.3
140°	412.5	412.7	412.9	413.1	413.3	413.4	413.4	413.4	413.4	413.4	413.3
142.5°	428.0	428.3	428.5	428.6	428.9	428.9	428.8	428.7	428.6	428.6	428.6
145°	449.6	450.0	450.4	450.8	451.1	451.4	451.5	451.6	451.7	451.8	451.7
147.5°	470.9	471.3	471.8	472.3	472.9	473.0	472.9	472.9	472.8	472.7	472.6
150°	483.9	484.3	484.7	485.1	485.5	485.7	485.7	485.7	485.7	485.7	485.7
152.5°	496.2	496.5	496.7	496.9	497.2	497.3	497.4	497.5	497.6	497.6	497.9
155°	515.1	515.1	515.1	515.1	515.1	515.0	514.9	514.8	514.8	514.6	515.0
157.5°	531.0	530.8	530.6	530.4	530.3	530.1	530.1	530.1	530.1	530.0	530.4
160°	540.3	540.3	540.2	540.1	540.0	539.9	539.8	539.7	539.6	539.5	539.8
162.5°	549.1	548.8	548.5	548.3	548.0	547.8	547.7	547.6	547.6	547.4	548.0
165°	560.7	560.4	560.1	559.8	559.5	559.3	559.0	558.9	558.6	558.5	559.0
167.5°	569.7	569.3	568.8	568.4	568.0	567.8	567.8	567.8	567.8	567.8	568.5
170°	574.7	574.3	573.7	573.2	572.7	572.5	572.6	572.7	572.8	572.9	573.5
172.5°	578.3	577.9	577.5	577.1	576.6	576.5	576.5	576.5	576.5	576.6	577.2
175°	583.3	582.8	582.3	581.8	581.3	581.0	580.9	580.8	580.7	580.6	581.3
177.5°	584.9	584.6	584.2	583.8	583.3	583.1	583.1	583.1	583.1	583.1	583.7
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2



TEST NUMBER: P332641-927

CATALOG NUMBER: S124DIP-S1020D590U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1362.0	1364.0	1366.0	1366.8	1366.6	1366.4	1366.2	1366.0
5°	1354.7	1357.4	1360.1	1361.2	1360.7	1360.2	1359.7	1359.2
7.5°	1339.7	1341.8	1343.9	1344.9	1344.6	1344.3	1343.9	1343.7
10°	1327.0	1329.0	1330.9	1331.6	1331.1	1330.6	1330.2	1329.7
12.5°	1311.6	1313.8	1315.9	1316.6	1316.0	1315.3	1314.5	1313.9
15°	1282.2	1283.7	1285.2	1285.5	1284.8	1284.0	1283.3	1282.5
17.5°	1248.7	1249.7	1250.5	1250.8	1250.3	1249.8	1249.4	1248.8
20°	1223.8	1224.6	1225.3	1225.3	1224.9	1224.4	1223.9	1223.4
22.5°	1197.8	1199.1	1200.4	1200.6	1199.8	1198.9	1198.0	1197.1
25°	1154.9	1155.2	1155.4	1155.0	1154.1	1153.1	1152.1	1151.1
27.5°	1106.8	1106.2	1105.6	1104.8	1103.5	1102.3	1101.1	1099.9
30°	1073.6	1072.6	1071.7	1070.6	1069.4	1068.1	1066.9	1065.7
32.5°	1039.9	1038.8	1037.6	1036.4	1035.1	1034.0	1032.8	1031.5
35°	986.7	985.0	983.3	981.8	980.6	979.5	978.2	977.0
37.5°	931.0	929.2	927.3	925.6	924.0	922.3	920.8	919.2
40°	892.2	889.7	887.3	885.5	884.2	883.0	881.9	880.6
42.5°	854.6	851.8	848.9	847.1	846.3	845.4	844.6	843.8
45°	796.4	793.7	791.0	789.3	788.6	787.9	787.1	786.4
47.5°	740.1	737.0	734.0	731.6	729.8	727.9	726.0	724.2
50°	700.8	697.4	694.0	691.5	690.0	688.6	687.1	685.6
52.5°	660.4	657.3	654.3	651.9	650.0	648.2	646.3	644.4
55°	600.9	598.0	595.1	592.9	591.4	590.0	588.5	587.1
57.5°	541.5	538.7	535.9	533.8	532.3	531.0	529.6	528.1
60°	500.6	498.4	496.1	494.5	493.2	492.0	490.8	489.6
62.5°	460.7	458.6	456.6	455.0	453.8	452.6	451.4	450.2
65°	402.6	400.1	397.7	395.9	394.7	393.5	392.2	391.0
67.5°	342.8	340.4	338.1	336.8	336.4	336.0	335.7	335.4
70°	305.0	303.0	301.1	299.8	299.0	298.3	297.5	296.8
72.5°	267.2	265.6	264.1	262.9	262.2	261.5	260.8	260.0
75°	212.7	211.8	210.8	210.2	209.9	209.7	209.5	209.2
77.5°	161.1	160.8	160.5	160.0	159.4	158.8	158.1	157.5
80°	128.3	127.8	127.3	126.9	126.7	126.4	126.2	126.0
82.5°	98.9	98.5	98.3	98.0	97.8	97.5	97.3	97.0
85°	57.0	57.0	57.0	56.8	56.6	56.3	56.1	55.8
87.5°	23.3	23.4	23.5	23.6	23.6	23.7	23.7	23.8
90°	11.2	11.7	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	18.6	19.0	19.3	19.6	19.7	19.8	20.0	20.0
95°	34.9	35.3	35.6	35.7	35.7	35.7	35.7	35.7
97.5°	55.1	55.4	55.8	55.9	55.9	55.9	55.9	55.9
100°	69.6	69.7	69.9	70.0	70.0	70.0	70.0	70.0
102.5°	84.8	85.2	85.4	85.6	85.7	85.8	85.9	86.0
105°	108.1	108.4	108.8	109.0	109.3	109.6	110.0	110.3
107.5°	133.3	133.6	133.9	134.0	134.0	134.0	134.0	134.0
110°	150.0	149.9	149.6	149.7	150.0	150.3	150.6	150.9





TEST NUMBER: P332641-927

CATALOG NUMBER: S124DIP-S1020D590U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.1	168.0	168.0	168.0	168.1	168.1	168.2	168.3
115°	195.9	195.8	195.7	195.6	195.5	195.4	195.3	195.2
117.5°	222.6	222.3	221.9	221.7	221.4	221.3	221.0	220.9
120°	240.7	240.2	239.7	239.6	239.8	240.0	240.2	240.3
122.5°	259.1	258.8	258.4	258.1	257.7	257.4	257.0	256.7
125°	286.1	285.8	285.7	285.4	285.3	285.0	284.9	284.6
127.5°	311.8	311.6	311.4	311.2	311.1	310.9	310.8	310.6
130°	329.9	329.7	329.5	329.2	328.8	328.4	328.0	327.6
132.5°	346.9	346.7	346.5	346.3	346.1	345.9	345.8	345.6
135°	372.3	372.2	371.9	371.7	371.4	371.1	370.8	370.5
137.5°	397.0	396.7	396.5	396.3	396.4	396.5	396.6	396.6
140°	413.2	413.1	413.0	412.9	412.8	412.7	412.6	412.5
142.5°	428.6	428.6	428.5	428.5	428.5	428.5	428.4	428.4
145°	451.6	451.5	451.4	451.2	450.9	450.6	450.3	450.0
147.5°	472.5	472.5	472.4	472.3	472.2	472.1	472.0	471.9
150°	485.7	485.7	485.7	485.7	485.5	485.4	485.4	485.3
152.5°	498.1	498.4	498.6	498.6	498.4	498.0	497.8	497.6
155°	515.4	515.8	516.3	516.3	515.8	515.4	515.0	514.6
157.5°	530.7	531.0	531.3	531.2	530.9	530.6	530.2	529.9
160°	540.1	540.3	540.7	540.6	540.1	539.6	539.1	538.6
162.5°	548.5	549.1	549.6	549.6	549.1	548.6	548.1	547.6
165°	559.7	560.2	560.9	560.9	560.5	560.2	559.8	559.4
167.5°	569.0	569.7	570.3	570.2	569.7	569.0	568.4	567.8
170°	574.1	574.7	575.3	575.3	574.6	573.9	573.1	572.4
172.5°	577.9	578.6	579.2	579.2	578.5	577.8	577.1	576.5
175°	582.0	582.7	583.4	583.4	582.7	582.0	581.3	580.6
177.5°	584.2	584.8	585.3	585.3	584.7	584.1	583.4	582.7
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2

(END OF REPORT)