

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332316-840

Luminaire Tested: **S123RDIP-S775D805U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332316-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5733.1 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332316-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332316-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	46	44	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14034	14034	14034
5°	14088	13894	13973
10°	14008	13719	13672
15°	13857	13397	13256
20°	13651	12997	12693
25°	13438	12545	12144
30°	13155	12026	11368
35°	12867	11506	10657
40°	12600	10891	9777
45°	12250	10286	8983
50°	11863	9597	8092
55°	11470	8811	7263
60°	11108	7967	6351
65°	10639	7055	5440
70°	10049	5923	4393
75°	9191	4662	4134
80°	8195	4135	3800
85°	6916	3656	3396



TEST NUMBER: P332316-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.1
10°-20°	340.6	5.9
20°-30°	490.5	8.6
30°-40°	552.5	9.6
40°-50°	528.6	9.2
50°-60°	432.9	7.6
60°-70°	292.0	5.1
70°-80°	146.9	2.6
80°-90°	41.8	0.7
90°-100°	65.5	1.1
100°-110°	196.0	3.4
110°-120°	333.3	5.8
120°-130°	438.5	7.6
130°-140°	492.8	8.6
140°-150°	484.4	8.4
150°-160°	407.8	7.1
160°-170°	271.5	4.7
170°-180°	95.1	1.7
0°-30°	953.6	16.6
0°-40°	1506.1	26.3
0°-60°	2467.5	43.0
0°-90°	2948.3	51.4
90°-120°	594.8	10.4
90°-150°	2010.5	35.1
90°-180°	2785.0	48.6
0°-180°	5733.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1244	1231	1202	1197	1190	350
25°	1132	1104	1056	1035	1022	520
35°	979	940	876	832	811	613
45°	805	755	676	617	590	621
55°	611	557	470	410	387	548
65°	418	358	277	227	214	413
75°	221	170	112	102	99	236
85°	56	34	30	28	28	63
90°	1	9	19	22	24	6
95°	47	52	58	61	62	52
105°	178	180	186	186	188	190
115°	336	338	336	337	336	332
125°	491	493	492	489	486	438
135°	637	642	641	638	636	491
145°	773	775	777	776	773	483
155°	885	885	886	889	884	407
165°	964	962	962	966	961	272
175°	1003	1000	1000	1004	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P332316-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1308.0	1307.3	1306.5	1305.8	1305.0	1303.5	1301.2	1299.0	1296.8	1294.4	1296.6
5°	1303.8	1302.6	1301.4	1300.3	1299.1	1297.1	1294.2	1291.4	1288.6	1285.9	1287.9
7.5°	1291.7	1290.5	1289.2	1287.9	1286.7	1284.1	1280.5	1276.9	1273.2	1269.5	1270.7
10°	1281.6	1279.9	1278.3	1276.7	1275.0	1272.0	1267.8	1263.6	1259.4	1255.2	1255.4
12.5°	1267.2	1265.4	1263.5	1261.7	1259.9	1256.4	1251.2	1246.1	1240.8	1235.7	1235.6
15°	1243.5	1240.9	1238.3	1235.8	1233.1	1228.6	1222.0	1215.5	1208.8	1202.2	1201.1
17.5°	1213.7	1210.7	1207.7	1204.7	1201.6	1196.0	1187.6	1179.2	1170.8	1162.6	1160.0
20°	1191.7	1187.9	1184.2	1180.4	1176.7	1170.3	1161.3	1152.5	1143.6	1134.6	1131.6
22.5°	1167.2	1162.9	1158.5	1154.2	1149.8	1143.0	1133.5	1124.0	1114.5	1105.0	1101.2
25°	1131.5	1125.6	1119.6	1113.8	1107.9	1099.5	1088.7	1077.9	1067.1	1056.3	1051.4
27.5°	1088.0	1081.6	1075.1	1068.6	1062.2	1052.9	1040.9	1028.9	1016.7	1004.7	997.8
30°	1058.4	1051.4	1044.4	1037.3	1030.3	1020.2	1007.0	993.8	980.7	967.6	959.6
32.5°	1028.9	1020.9	1012.9	1004.9	996.9	985.9	972.0	958.2	944.2	930.3	921.6
35°	979.2	970.7	962.2	953.8	945.3	933.8	919.3	904.6	890.1	875.6	865.5
37.5°	928.9	919.4	910.0	900.6	891.2	878.8	863.2	847.7	832.1	816.6	805.1
40°	896.7	886.4	876.0	865.7	855.4	841.8	825.2	808.5	791.7	775.1	762.9
42.5°	860.3	850.0	839.6	829.3	819.0	805.2	787.9	770.6	753.5	736.2	722.9
45°	804.7	794.2	783.6	773.0	762.3	748.1	729.9	711.9	693.8	675.7	662.3
47.5°	749.1	737.5	725.9	714.3	702.7	687.8	669.7	651.6	633.5	615.4	600.9
50°	708.4	697.4	686.4	675.3	664.3	649.2	630.3	611.2	592.2	573.1	558.6
52.5°	672.1	660.1	648.1	636.1	624.2	608.7	589.9	571.1	552.2	533.3	518.3
55°	611.2	599.7	588.1	576.6	565.1	549.4	529.4	509.5	489.5	469.5	455.9
57.5°	554.9	542.4	529.9	517.3	504.7	488.5	468.4	448.3	428.2	408.2	395.3
60°	516.0	503.1	490.2	477.3	464.3	448.1	428.6	409.1	389.6	370.1	357.4
62.5°	477.1	464.1	451.2	438.3	425.5	409.2	389.7	370.2	350.7	331.1	319.2
65°	417.7	404.8	391.8	378.9	366.0	350.3	332.0	313.7	295.4	277.0	265.5
67.5°	358.3	345.2	332.1	319.0	306.0	290.6	273.1	255.5	237.9	220.4	211.8
70°	319.3	306.7	294.0	281.2	268.6	254.0	237.5	221.2	204.7	188.2	180.0
72.5°	280.4	267.9	255.4	242.9	230.5	216.7	201.8	186.8	171.9	156.9	150.2
75°	221.0	209.7	198.4	187.1	175.9	163.8	150.9	137.9	125.0	112.1	109.8
77.5°	166.8	156.6	146.4	136.2	126.0	116.8	108.5	100.2	91.9	83.5	82.3
80°	132.2	122.5	112.9	103.3	93.6	86.3	81.4	76.4	71.6	66.7	65.9
82.5°	99.2	90.9	82.5	74.2	65.9	60.6	58.3	55.9	53.7	51.4	50.7
85°	56.0	50.9	45.7	40.5	35.3	32.4	31.7	31.0	30.3	29.6	29.2
87.5°	20.5	18.8	17.1	15.3	13.6	12.9	13.4	13.8	14.3	14.7	14.7
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7
92.5°	19.1	20.3	21.5	22.7	23.8	25.1	26.5	27.8	29.0	30.3	30.9
95°	46.6	47.8	49.1	50.3	51.5	52.8	54.2	55.6	57.1	58.5	59.2
97.5°	82.7	83.6	84.5	85.4	86.4	87.4	88.4	89.4	90.4	91.4	92.2
100°	107.3	108.5	109.5	110.6	111.6	112.6	113.4	114.3	115.2	116.0	116.6
102.5°	135.8	136.4	137.0	137.7	138.4	139.3	140.4	141.6	142.7	143.9	144.4
105°	177.6	178.0	178.3	178.7	179.0	180.1	181.6	183.2	184.8	186.3	186.3
107.5°	226.3	226.5	226.7	226.9	227.1	227.5	228.2	228.8	229.4	230.0	230.7
110°	256.6	256.9	257.3	257.6	258.0	258.3	258.7	259.0	259.4	259.7	260.4



TEST NUMBER: P332316-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	288.4	288.6	288.8	289.0	289.1	289.2	289.3	289.4	289.4	290.3
115°	335.6	336.1	336.6	337.1	337.7	337.8	337.4	337.1	336.7	336.4	336.5
117.5°	383.2	383.6	384.0	384.3	384.7	384.6	384.2	383.6	383.2	382.7	382.7
120°	412.9	413.9	415.1	416.1	417.2	417.3	416.4	415.5	414.7	413.7	413.5
122.5°	443.9	444.6	445.5	446.2	447.0	447.2	446.7	446.3	445.8	445.4	444.8
125°	491.1	491.6	492.1	492.7	493.2	493.3	492.9	492.6	492.2	491.9	491.2
127.5°	534.7	535.8	536.9	538.1	539.2	539.6	539.2	538.8	538.4	538.0	537.0
130°	563.7	565.1	566.5	567.9	569.4	569.8	569.3	568.8	568.3	567.6	566.9
132.5°	592.8	594.2	595.6	597.0	598.4	599.0	598.5	598.1	597.7	597.3	596.5
135°	637.1	638.2	639.2	640.4	641.4	641.9	641.7	641.5	641.3	641.2	640.5
137.5°	678.2	679.1	679.9	680.9	681.8	682.4	682.9	683.3	683.8	684.2	683.5
140°	706.6	707.5	708.4	709.3	710.1	710.6	710.8	711.0	711.2	711.3	711.2
142.5°	732.6	733.5	734.3	735.2	736.1	736.7	737.0	737.3	737.6	737.9	737.7
145°	773.0	773.4	773.7	774.1	774.4	774.8	775.4	775.9	776.4	776.9	776.8
147.5°	808.4	809.0	809.6	810.2	810.9	811.4	811.9	812.4	812.9	813.4	813.4
150°	832.9	833.3	833.6	834.0	834.4	834.8	835.1	835.5	835.8	836.2	836.2
152.5°	853.2	853.6	854.1	854.6	855.2	855.6	855.8	856.0	856.2	856.4	856.7
155°	885.0	885.0	885.0	885.0	885.0	885.1	885.3	885.6	885.8	885.9	886.6
157.5°	912.2	912.0	911.8	911.6	911.4	911.4	911.5	911.7	911.8	911.9	912.7
160°	929.3	929.0	928.6	928.3	927.9	927.8	927.8	927.8	927.8	927.8	928.6
162.5°	944.4	944.0	943.5	943.0	942.5	942.3	942.5	942.6	942.7	942.9	943.7
165°	964.0	963.5	963.0	962.5	961.9	961.7	961.7	961.7	961.7	961.7	962.7
167.5°	979.7	979.0	978.3	977.5	976.8	976.6	976.7	976.8	977.0	977.1	978.3
170°	988.6	987.8	987.1	986.4	985.7	985.3	985.3	985.3	985.3	985.3	986.6
172.5°	995.4	994.8	994.1	993.4	992.7	992.3	992.3	992.3	992.3	992.3	993.4
175°	1002.7	1002.0	1001.4	1000.7	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7
177.5°	1005.7	1005.2	1004.6	1004.0	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332316-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1298.6	1300.7	1302.7	1303.6	1303.2	1302.8	1302.4	1302.1
5°	1290.0	1292.1	1294.2	1295.1	1294.6	1294.1	1293.6	1293.2
7.5°	1271.9	1273.0	1274.2	1274.4	1273.6	1272.8	1272.0	1271.2
10°	1255.7	1255.9	1256.1	1255.7	1254.5	1253.2	1252.1	1250.9
12.5°	1235.4	1235.3	1235.2	1234.4	1233.0	1231.6	1230.3	1228.9
15°	1199.9	1198.7	1197.6	1196.2	1194.6	1192.9	1191.2	1189.6
17.5°	1157.5	1155.1	1152.6	1150.1	1147.6	1145.2	1142.8	1140.3
20°	1128.5	1125.4	1122.4	1119.4	1116.6	1113.8	1111.0	1108.1
22.5°	1097.4	1093.6	1089.7	1086.5	1083.9	1081.3	1078.6	1076.0
25°	1046.5	1041.6	1036.6	1032.9	1030.3	1027.6	1025.1	1022.5
27.5°	991.0	984.2	977.3	971.9	968.0	964.0	960.1	956.1
30°	951.6	943.5	935.5	929.7	925.9	922.2	918.4	914.6
32.5°	912.8	904.1	895.3	889.0	885.0	881.1	877.2	873.2
35°	855.4	845.3	835.2	828.0	823.7	819.5	815.3	811.0
37.5°	793.6	782.1	770.6	762.3	757.1	751.8	746.7	741.4
40°	750.6	738.4	726.2	717.4	712.0	706.6	701.1	695.8
42.5°	709.4	696.1	682.8	673.7	668.8	664.0	659.1	654.3
45°	648.9	635.5	622.1	612.6	606.9	601.3	595.7	590.1
47.5°	586.2	571.7	557.1	547.3	542.3	537.2	532.3	527.3
50°	544.0	529.4	514.8	504.8	499.5	494.0	488.7	483.2
52.5°	503.1	488.0	472.8	462.8	458.0	453.1	448.3	443.4
55°	442.2	428.6	415.0	405.8	401.1	396.4	391.7	387.0
57.5°	382.4	369.5	356.7	348.2	344.3	340.2	336.2	332.2
60°	344.7	332.0	319.3	311.0	307.0	303.0	299.0	295.0
62.5°	307.3	295.4	283.5	275.4	271.1	267.0	262.9	258.6
65°	254.0	242.5	231.0	223.9	221.4	218.7	216.2	213.6
67.5°	203.2	194.6	185.9	180.3	177.5	174.7	172.0	169.2
70°	171.8	163.5	155.3	150.0	147.3	144.7	142.2	139.6
72.5°	143.5	136.7	130.1	126.1	125.0	124.0	122.9	121.8
75°	107.3	105.0	102.7	101.3	100.8	100.4	99.9	99.4
77.5°	81.0	79.7	78.5	77.6	77.2	76.6	76.1	75.7
80°	65.2	64.5	63.8	63.2	62.7	62.3	61.8	61.3
82.5°	50.0	49.3	48.6	48.2	48.1	48.0	47.9	47.8
85°	28.7	28.2	27.8	27.5	27.5	27.5	27.5	27.5
87.5°	14.6	14.6	14.6	14.5	14.4	14.2	14.1	14.0
90°	20.4	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	31.4	32.0	32.5	32.7	32.5	32.3	32.1	31.9
95°	59.8	60.5	61.2	61.6	61.6	61.6	61.6	61.6
97.5°	93.0	93.8	94.6	95.0	94.9	94.9	94.8	94.7
100°	117.1	117.6	118.2	118.7	119.0	119.3	119.7	120.0
102.5°	144.9	145.4	145.9	146.2	146.1	146.0	146.0	145.9
105°	186.3	186.3	186.3	186.5	186.8	187.2	187.5	187.9
107.5°	231.2	231.8	232.4	232.5	232.3	232.1	231.9	231.7
110°	261.2	261.9	262.6	262.8	262.4	262.1	261.7	261.4



TEST NUMBER: P332316-840

CATALOG NUMBER: S123RDIP-S775D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.1	292.0	292.9	293.2	293.2	293.1	293.0	293.0
115°	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4
117.5°	382.7	382.6	382.6	382.3	381.9	381.4	380.9	380.4
120°	413.3	413.2	413.0	412.7	412.4	412.0	411.7	411.3
122.5°	444.4	443.9	443.5	443.0	442.5	442.0	441.5	441.0
125°	490.5	489.8	489.1	488.4	487.7	487.0	486.3	485.5
127.5°	536.0	535.0	534.1	533.2	532.4	531.6	530.8	530.0
130°	566.3	565.6	564.9	563.9	562.7	561.5	560.3	559.0
132.5°	595.7	594.8	594.0	593.1	592.2	591.2	590.3	589.4
135°	639.7	639.0	638.3	637.8	637.4	637.1	636.7	636.4
137.5°	682.8	682.1	681.3	680.5	679.9	679.2	678.6	677.9
140°	711.0	710.8	710.6	710.0	708.7	707.5	706.3	705.1
142.5°	737.6	737.4	737.2	736.7	735.7	734.8	733.8	732.9
145°	776.6	776.4	776.2	775.8	775.1	774.4	773.7	773.0
147.5°	813.4	813.4	813.4	812.8	811.8	810.7	809.7	808.7
150°	836.2	836.2	836.2	835.7	834.6	833.5	832.4	831.4
152.5°	856.9	857.2	857.5	857.2	856.3	855.4	854.4	853.5
155°	887.3	888.0	888.7	888.4	887.2	886.0	884.7	883.5
157.5°	913.4	914.1	914.8	914.7	913.8	912.8	911.8	910.8
160°	929.5	930.4	931.2	931.3	930.6	929.9	929.2	928.5
162.5°	944.6	945.5	946.4	946.2	945.1	944.0	942.9	941.8
165°	963.8	964.8	965.9	965.8	964.6	963.3	962.1	960.9
167.5°	979.4	980.4	981.5	981.5	980.4	979.4	978.3	977.1
170°	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.3
172.5°	994.5	995.6	996.6	996.6	995.3	994.1	992.9	991.7
175°	1001.7	1002.7	1003.8	1003.7	1002.5	1001.3	1000.0	998.8
177.5°	1004.9	1005.7	1006.5	1006.5	1005.5	1004.5	1003.6	1002.6
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1

(END OF REPORT)