

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332033-940

Luminaire Tested: **S123DIP-S1000D1025U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332033-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7329.5 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332033-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332033-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29	26
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332033-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	1.8
10°-20°	375.4	5.1
20°-30°	554.6	7.6
30°-40°	647.8	8.8
40°-50°	651.3	8.9
50°-60°	572.1	7.8
60°-70°	426.2	5.8
70°-80°	242.8	3.3
80°-90°	73.0	1.0
90°-100°	43.6	0.6
100°-110°	207.6	2.8
110°-120°	498.6	6.8
120°-130°	634.9	8.7
130°-140°	678.4	9.3
140°-150°	634.4	8.7
150°-160°	511.7	7.0
160°-170°	330.3	4.5
170°-180°	113.8	1.6
0°-30°	1062.9	14.5
0°-40°	1710.7	23.3
0°-60°	2934.1	40.0
0°-90°	3676.1	50.2
90°-120°	749.8	10.2
90°-150°	2697.6	36.8
90°-180°	3653.0	49.8
0°-180°	7329.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	10	21	25	27	6
95°	54	20	28	34	34	67
105°	265	270	195	46	39	281
115°	498	503	511	520	523	491
125°	701	708	712	714	716	626
135°	873	878	882	884	882	672
145°	1008	1014	1016	1017	1017	630
155°	1110	1108	1109	1113	1108	511
165°	1170	1168	1167	1173	1168	331
175°	1198	1194	1194	1200	1194	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P332033-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.4	25.1	24.9	24.7	24.4	24.4	24.7	25.1	25.3	25.6	25.6
90°	0.9	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1
92.5°	16.6	16.0	15.4	14.9	14.4	15.1	16.9	18.9	20.9	22.8	24.1
95°	54.3	46.2	38.1	30.0	21.8	18.9	21.0	23.3	25.4	27.6	29.0
97.5°	109.1	105.5	101.8	98.2	94.5	85.6	71.4	57.2	42.9	28.6	30.2
100°	150.4	154.4	158.4	162.3	166.2	152.8	121.9	91.0	60.2	29.3	30.9
102.5°	197.4	200.3	203.1	206.0	208.8	193.4	159.7	126.0	92.3	58.6	53.7
105°	265.2	267.4	269.6	271.8	273.9	266.1	248.3	230.5	212.8	194.9	159.9
107.5°	336.8	338.6	340.3	342.1	343.8	346.1	348.8	351.7	354.5	357.3	331.6
110°	384.5	386.1	387.6	389.2	390.8	392.7	394.8	397.1	399.2	401.4	394.8



TEST NUMBER: P332033-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.1	431.5	432.9	434.4	435.8	437.6	439.8	441.9	444.1	446.3	446.4
115°	497.6	498.7	499.9	501.1	502.3	503.8	505.5	507.3	509.1	510.9	512.9
117.5°	562.8	564.4	565.8	567.3	568.7	569.9	570.8	571.8	572.7	573.5	575.2
120°	603.4	605.2	607.0	608.8	610.6	611.8	612.3	613.0	613.6	614.1	615.7
122.5°	644.8	646.2	647.6	649.2	650.6	651.8	652.5	653.3	654.0	654.7	655.9
125°	701.3	702.9	704.5	706.1	707.7	708.9	709.7	710.4	711.2	712.0	712.5
127.5°	756.2	757.8	759.4	760.9	762.5	763.8	764.7	765.7	766.6	767.6	768.2
130°	790.4	791.9	793.5	795.1	796.7	797.9	798.7	799.5	800.2	801.0	801.8
132.5°	823.1	824.7	826.3	827.9	829.5	830.5	831.2	831.8	832.5	833.1	833.9
135°	873.2	874.3	875.5	876.7	877.9	878.9	879.7	880.5	881.3	882.1	882.6
137.5°	915.9	917.4	918.9	920.4	921.9	922.8	923.3	923.7	924.2	924.6	925.5
140°	944.3	945.6	946.7	947.9	949.1	950.0	950.6	951.2	951.8	952.3	953.1
142.5°	970.7	971.9	973.0	974.3	975.4	976.3	977.0	977.5	978.1	978.7	979.4
145°	1007.5	1009.0	1010.3	1011.7	1013.1	1014.0	1014.4	1014.8	1015.1	1015.6	1015.9
147.5°	1042.2	1043.2	1044.1	1045.0	1045.9	1046.5	1047.0	1047.3	1047.8	1048.1	1048.6
150°	1063.6	1064.3	1064.8	1065.4	1066.0	1066.5	1066.8	1067.3	1067.6	1068.1	1068.4
152.5°	1082.8	1083.2	1083.4	1083.7	1084.0	1084.2	1084.4	1084.7	1084.9	1085.1	1085.8
155°	1109.9	1109.5	1109.1	1108.8	1108.3	1108.2	1108.4	1108.6	1108.8	1109.0	1110.0
157.5°	1130.9	1130.9	1130.9	1130.8	1130.8	1130.6	1130.4	1130.2	1130.1	1129.8	1131.0
160°	1143.7	1143.5	1143.4	1143.2	1142.9	1142.7	1142.5	1142.4	1142.1	1141.9	1143.2
162.5°	1155.8	1155.3	1154.8	1154.3	1153.8	1153.4	1153.2	1153.0	1152.8	1152.6	1154.0
165°	1170.5	1169.8	1169.2	1168.7	1168.1	1167.7	1167.4	1167.2	1167.1	1166.9	1168.4
167.5°	1181.8	1181.1	1180.3	1179.5	1178.7	1178.2	1178.2	1178.2	1178.2	1178.2	1179.8
170°	1188.2	1187.4	1186.7	1185.9	1185.1	1184.6	1184.6	1184.6	1184.6	1184.6	1186.2
172.5°	1192.5	1191.6	1190.6	1189.6	1188.7	1188.3	1188.5	1188.7	1188.7	1188.9	1190.5
175°	1198.0	1197.0	1196.1	1195.1	1194.1	1193.6	1193.8	1194.1	1194.3	1194.4	1195.9
177.5°	1199.4	1198.6	1197.8	1197.0	1196.3	1196.0	1196.1	1196.3	1196.4	1196.6	1197.8
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332033-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	25.5	25.5	25.4	25.4	25.5	25.6	25.7	25.8
90°	22.9	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	25.3	26.6	27.8	28.6	28.8	29.1	29.3	29.5
95°	30.3	31.7	33.2	33.8	33.8	33.8	33.8	33.8
97.5°	31.8	33.4	35.0	35.8	36.1	36.3	36.5	36.6
100°	32.5	34.2	35.7	36.6	36.8	37.0	37.2	37.4
102.5°	48.8	43.9	39.0	36.6	37.0	37.4	37.7	38.1
105°	124.9	89.9	54.9	37.5	38.0	38.3	38.8	39.1
107.5°	305.9	280.3	254.6	228.5	202.2	175.8	149.4	123.0
110°	388.3	381.8	375.3	357.9	329.6	301.3	273.0	244.8



TEST NUMBER: P332033-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	446.5	446.7	446.7	443.8	437.8	431.9	425.9	419.9
115°	514.9	516.8	518.8	520.2	520.9	521.7	522.5	523.3
117.5°	576.8	578.3	579.9	580.8	580.9	581.0	581.2	581.4
120°	617.3	618.8	620.5	621.3	621.3	621.3	621.3	621.3
122.5°	656.9	658.1	659.2	659.8	660.0	660.1	660.2	660.4
125°	712.8	713.2	713.6	714.0	714.4	714.8	715.2	715.6
127.5°	768.8	769.5	770.1	770.3	769.8	769.5	769.0	768.7
130°	802.6	803.4	804.2	804.4	804.1	803.6	803.3	802.8
132.5°	834.6	835.4	836.2	836.3	835.8	835.3	834.7	834.2
135°	883.2	883.9	884.4	884.4	883.9	883.2	882.6	882.1
137.5°	926.5	927.5	928.4	928.6	928.3	927.9	927.5	927.1
140°	954.0	954.8	955.6	955.7	955.3	954.9	954.6	954.1
142.5°	980.0	980.6	981.2	981.2	980.7	980.2	979.6	979.1
145°	1016.4	1016.7	1017.2	1017.4	1017.4	1017.4	1017.4	1017.4
147.5°	1048.9	1049.3	1049.7	1049.5	1048.6	1047.7	1046.7	1045.8
150°	1068.9	1069.3	1069.7	1069.5	1069.0	1068.4	1067.7	1067.2
152.5°	1086.5	1087.3	1088.0	1087.9	1087.0	1086.1	1085.2	1084.2
155°	1111.0	1112.0	1112.9	1112.9	1111.7	1110.5	1109.3	1108.1
157.5°	1132.2	1133.4	1134.6	1134.4	1132.8	1131.3	1129.8	1128.3
160°	1144.3	1145.5	1146.7	1146.6	1145.2	1143.8	1142.5	1141.0
162.5°	1155.3	1156.6	1158.0	1158.1	1156.8	1155.6	1154.4	1153.2
165°	1170.0	1171.6	1173.2	1173.3	1171.9	1170.5	1169.1	1167.8
167.5°	1181.4	1183.0	1184.5	1184.5	1183.0	1181.4	1179.8	1178.2
170°	1187.8	1189.5	1191.0	1191.0	1189.5	1187.8	1186.2	1184.6
172.5°	1192.1	1193.6	1195.2	1195.2	1193.5	1191.7	1190.0	1188.2
175°	1197.2	1198.6	1200.0	1199.9	1198.3	1196.8	1195.2	1193.6
177.5°	1199.1	1200.4	1201.7	1201.5	1199.9	1198.4	1196.8	1195.2
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0

(END OF REPORT)