

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332034-940

Luminaire Tested: **S123DIP-S1000D1025U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332034-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6815.6 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332034-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332034-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	87	84	81	75	72	70	63	62	60	53	51	50	45
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	40	35	41	36	31	36	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	24	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332034-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	2.0
10°-20°	375.4	5.5
20°-30°	554.6	8.1
30°-40°	647.8	9.5
40°-50°	651.3	9.6
50°-60°	572.1	8.4
60°-70°	426.2	6.3
70°-80°	242.8	3.6
80°-90°	73.0	1.1
90°-100°	73.8	1.1
100°-110°	220.9	3.2
110°-120°	375.8	5.5
120°-130°	494.3	7.3
130°-140°	555.6	8.2
140°-150°	546.1	8.0
150°-160°	459.7	6.7
160°-170°	306.0	4.5
170°-180°	107.2	1.6
0°-30°	1062.9	15.6
0°-40°	1710.7	25.1
0°-60°	2934.1	43.0
0°-90°	3676.1	53.9
90°-120°	670.6	9.8
90°-150°	2266.5	33.3
90°-180°	3139.0	46.1
0°-180°	6815.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	10	21	25	27	7
95°	52	59	66	69	70	59
105°	200	202	210	210	212	214
115°	378	381	379	380	379	374
125°	554	556	555	551	547	494
135°	718	723	723	719	718	553
145°	871	873	876	875	871	544
155°	998	998	999	1002	996	459
165°	1087	1084	1084	1089	1083	306
175°	1130	1127	1127	1132	1126	107
180°	1133	1133	1133	1133	1133	



TEST NUMBER: P332034-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.4	25.1	24.9	24.7	24.4	24.4	24.7	25.1	25.3	25.6	25.6
90°	0.9	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1
92.5°	21.6	22.9	24.3	25.6	26.9	28.4	29.8	31.2	32.7	34.2	34.8
95°	52.5	53.9	55.3	56.7	58.1	59.6	61.1	62.7	64.3	65.9	66.7
97.5°	93.3	94.3	95.3	96.4	97.4	98.4	99.6	100.8	101.9	103.1	104.0
100°	121.1	122.3	123.4	124.6	125.8	126.9	127.9	128.9	129.8	130.8	131.4
102.5°	153.1	153.8	154.5	155.2	156.0	156.9	158.3	159.5	160.9	162.2	162.7
105°	200.3	200.6	201.1	201.4	201.9	203.0	204.7	206.5	208.3	210.1	210.1
107.5°	255.1	255.4	255.6	255.8	256.1	256.5	257.3	258.0	258.7	259.4	260.0
110°	289.3	289.7	290.1	290.4	290.9	291.2	291.7	292.0	292.5	292.8	293.6



TEST NUMBER: P332034-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	324.9	325.1	325.4	325.6	325.8	326.0	326.1	326.2	326.3	326.3	327.3
115°	378.3	378.9	379.5	380.0	380.7	380.8	380.4	380.0	379.6	379.2	379.4
117.5°	432.0	432.5	432.8	433.3	433.6	433.5	433.1	432.6	432.0	431.5	431.5
120°	465.6	466.7	467.9	469.1	470.3	470.4	469.4	468.4	467.4	466.5	466.2
122.5°	500.4	501.3	502.1	503.0	503.9	504.1	503.5	503.0	502.6	502.0	501.5
125°	553.7	554.3	554.8	555.4	556.0	556.2	555.7	555.4	554.9	554.6	553.8
127.5°	602.8	604.0	605.3	606.5	607.9	608.2	607.8	607.4	607.0	606.5	605.4
130°	635.5	637.1	638.7	640.2	641.9	642.4	641.8	641.1	640.6	640.0	639.2
132.5°	668.3	669.9	671.5	673.1	674.7	675.2	674.8	674.3	673.9	673.4	672.5
135°	718.4	719.5	720.7	721.8	723.1	723.5	723.4	723.2	723.0	722.7	722.0
137.5°	764.6	765.6	766.6	767.6	768.6	769.3	769.8	770.3	770.9	771.3	770.5
140°	796.7	797.6	798.6	799.6	800.6	801.2	801.4	801.6	801.8	802.0	801.8
142.5°	825.8	826.8	827.9	828.8	829.8	830.5	830.8	831.2	831.5	831.9	831.7
145°	871.4	871.8	872.2	872.6	873.0	873.5	874.1	874.7	875.3	875.8	875.7
147.5°	911.3	912.0	912.8	913.5	914.2	914.8	915.3	915.9	916.4	917.0	917.0
150°	939.1	939.5	939.9	940.2	940.7	941.0	941.5	941.8	942.3	942.6	942.6
152.5°	961.9	962.4	963.0	963.5	964.0	964.5	964.7	964.9	965.2	965.5	965.7
155°	997.8	997.8	997.8	997.8	997.8	997.9	998.1	998.3	998.5	998.7	999.5
157.5°	1028.4	1028.2	1028.0	1027.7	1027.5	1027.4	1027.6	1027.8	1028.0	1028.1	1028.9
160°	1047.7	1047.2	1046.9	1046.5	1046.1	1045.9	1045.9	1045.9	1045.9	1045.9	1046.9
162.5°	1064.8	1064.2	1063.6	1063.1	1062.6	1062.4	1062.5	1062.7	1062.8	1063.0	1064.0
165°	1086.8	1086.2	1085.7	1085.0	1084.5	1084.1	1084.1	1084.1	1084.1	1084.1	1085.3
167.5°	1104.5	1103.7	1102.9	1102.1	1101.3	1101.0	1101.2	1101.3	1101.4	1101.6	1102.9
170°	1114.5	1113.7	1112.9	1112.1	1111.3	1110.9	1110.9	1110.9	1110.9	1110.9	1112.2
172.5°	1122.2	1121.5	1120.7	1119.9	1119.1	1118.7	1118.7	1118.7	1118.7	1118.7	1119.9
175°	1130.4	1129.6	1128.8	1128.1	1127.3	1126.9	1126.9	1126.9	1126.9	1126.9	1128.1
177.5°	1133.8	1133.2	1132.6	1131.9	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1131.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332034-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	25.5	25.5	25.4	25.4	25.5	25.6	25.7	25.8
90°	22.9	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	35.5	36.1	36.7	36.9	36.6	36.5	36.2	35.9
95°	67.4	68.2	69.0	69.5	69.5	69.5	69.5	69.5
97.5°	104.9	105.8	106.7	107.1	107.1	107.0	106.9	106.8
100°	132.1	132.6	133.2	133.8	134.1	134.5	134.9	135.3
102.5°	163.4	164.0	164.5	164.8	164.7	164.6	164.6	164.5
105°	210.1	210.1	210.1	210.3	210.6	211.1	211.4	211.9
107.5°	260.6	261.3	261.9	262.1	261.9	261.6	261.4	261.2
110°	294.4	295.2	296.0	296.2	295.8	295.4	295.1	294.6



TEST NUMBER: P332034-940

CATALOG NUMBER: S123DIP-S1000D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	328.2	329.1	330.1	330.6	330.5	330.4	330.3	330.2
115°	379.6	379.8	380.0	380.0	379.8	379.6	379.4	379.2
117.5°	431.4	431.4	431.4	431.1	430.5	430.0	429.4	428.8
120°	466.0	465.8	465.7	465.3	464.9	464.6	464.1	463.8
122.5°	501.0	500.5	500.0	499.4	498.9	498.3	497.8	497.2
125°	552.9	552.1	551.3	550.5	549.8	549.0	548.2	547.4
127.5°	604.3	603.2	602.1	601.1	600.2	599.2	598.3	597.4
130°	638.4	637.6	636.9	635.7	634.4	632.9	631.6	630.2
132.5°	671.5	670.7	669.7	668.7	667.6	666.6	665.5	664.4
135°	721.2	720.4	719.6	719.0	718.6	718.2	717.8	717.5
137.5°	769.7	768.9	768.0	767.2	766.5	765.7	765.0	764.3
140°	801.6	801.4	801.2	800.4	799.1	797.6	796.3	794.9
142.5°	831.5	831.3	831.1	830.5	829.4	828.3	827.2	826.2
145°	875.5	875.3	875.0	874.6	873.8	873.0	872.2	871.4
147.5°	917.0	917.0	917.0	916.4	915.3	914.0	912.8	911.7
150°	942.6	942.6	942.6	942.0	940.8	939.7	938.4	937.3
152.5°	966.1	966.3	966.7	966.3	965.3	964.3	963.2	962.2
155°	1000.3	1001.1	1001.8	1001.6	1000.2	998.8	997.4	996.0
157.5°	1029.7	1030.6	1031.4	1031.3	1030.2	1029.0	1028.0	1026.8
160°	1047.8	1048.8	1049.8	1049.9	1049.2	1048.4	1047.6	1046.8
162.5°	1065.0	1066.0	1066.9	1066.8	1065.5	1064.3	1063.0	1061.8
165°	1086.5	1087.7	1088.9	1088.8	1087.4	1086.0	1084.7	1083.3
167.5°	1104.0	1105.3	1106.5	1106.5	1105.3	1104.0	1102.9	1101.6
170°	1113.7	1115.0	1116.4	1116.4	1115.0	1113.7	1112.2	1110.9
172.5°	1121.1	1122.4	1123.6	1123.6	1122.1	1120.8	1119.4	1117.9
175°	1129.3	1130.4	1131.7	1131.5	1130.2	1128.7	1127.4	1126.0
177.5°	1132.9	1133.8	1134.8	1134.7	1133.6	1132.5	1131.4	1130.2
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1

(END OF REPORT)