

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332015-940

Luminaire Tested: **S123DIP-S1000D585U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332015-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5762.3 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332015-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332015-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	32	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332015-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	2.3
10°-20°	375.4	6.5
20°-30°	554.6	9.6
30°-40°	647.8	11.2
40°-50°	651.3	11.3
50°-60°	572.1	9.9
60°-70°	426.2	7.4
70°-80°	242.8	4.2
80°-90°	71.6	1.2
90°-100°	24.9	0.4
100°-110°	118.6	2.1
110°-120°	284.9	4.9
120°-130°	362.8	6.3
130°-140°	387.7	6.7
140°-150°	362.5	6.3
150°-160°	292.4	5.1
160°-170°	188.7	3.3
170°-180°	65.0	1.1
0°-30°	1062.9	18.4
0°-40°	1710.7	29.7
0°-60°	2934.1	50.9
0°-90°	3674.7	63.8
90°-120°	428.4	7.4
90°-150°	1541.4	26.8
90°-180°	2088.0	36.2
0°-180°	5762.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	0	6	12	14	15	5
95°	31	12	16	19	19	38
105°	152	154	111	26	22	161
115°	284	287	292	297	299	281
125°	401	405	407	408	409	358
135°	499	502	504	505	504	384
145°	576	579	580	581	581	360
155°	634	633	634	636	633	292
165°	669	667	667	670	667	189
175°	685	682	682	686	682	65
180°	685	685	685	685	685	



TEST NUMBER: P332015-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.3	25.0	24.5	24.1	23.6	23.5	23.5	23.6	23.7	23.8	23.7
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	9.5	9.2	8.8	8.5	8.2	8.6	9.7	10.8	11.9	13.0	13.7
95°	31.0	26.4	21.8	17.1	12.5	10.8	12.0	13.3	14.5	15.8	16.6
97.5°	62.3	60.3	58.2	56.1	54.0	49.0	40.8	32.6	24.5	16.4	17.3
100°	86.0	88.2	90.5	92.7	95.0	87.3	69.6	52.1	34.4	16.8	17.7
102.5°	112.8	114.4	116.1	117.7	119.3	110.5	91.2	72.0	52.7	33.4	30.7
105°	151.6	152.8	154.1	155.2	156.5	152.0	141.9	131.7	121.5	111.4	91.4
107.5°	192.4	193.4	194.5	195.5	196.4	197.7	199.3	200.9	202.5	204.1	189.5
110°	219.7	220.6	221.5	222.4	223.3	224.4	225.6	226.9	228.1	229.3	225.6



TEST NUMBER: P332015-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.6	247.4	248.2	249.0	250.0	251.3	252.5	253.8	255.0	255.1
115°	284.3	285.0	285.6	286.3	287.0	287.8	288.9	289.9	290.9	291.9	293.1
117.5°	321.6	322.4	323.3	324.1	324.9	325.7	326.2	326.7	327.3	327.7	328.7
120°	344.8	345.8	346.9	347.9	348.9	349.6	349.9	350.3	350.6	350.9	351.9
122.5°	368.5	369.3	370.1	371.0	371.8	372.4	372.8	373.3	373.7	374.2	374.8
125°	400.7	401.7	402.6	403.5	404.4	405.1	405.6	406.0	406.4	406.9	407.1
127.5°	432.1	433.0	433.9	434.8	435.7	436.4	436.9	437.6	438.1	438.6	439.0
130°	451.7	452.5	453.4	454.3	455.2	455.9	456.4	456.8	457.3	457.7	458.2
132.5°	470.4	471.3	472.2	473.1	473.9	474.6	474.9	475.3	475.6	476.1	476.5
135°	498.9	499.6	500.2	501.0	501.7	502.2	502.7	503.1	503.5	504.0	504.4
137.5°	523.3	524.2	525.0	525.9	526.7	527.4	527.5	527.8	528.1	528.3	528.9
140°	539.6	540.3	541.0	541.6	542.3	542.9	543.1	543.5	543.9	544.2	544.7
142.5°	554.6	555.4	556.1	556.7	557.4	557.9	558.2	558.6	558.9	559.3	559.6
145°	575.7	576.5	577.3	578.1	578.9	579.4	579.6	579.9	580.1	580.3	580.5
147.5°	595.6	596.1	596.6	597.1	597.6	598.0	598.2	598.4	598.7	599.0	599.1
150°	607.8	608.1	608.4	608.8	609.1	609.4	609.7	609.8	610.1	610.3	610.6
152.5°	618.8	618.9	619.0	619.2	619.4	619.6	619.6	619.8	619.9	620.1	620.5
155°	634.2	634.0	633.7	633.6	633.3	633.3	633.4	633.5	633.6	633.7	634.3
157.5°	646.2	646.2	646.1	646.1	646.1	646.0	646.0	645.9	645.7	645.6	646.3
160°	653.5	653.4	653.4	653.2	653.1	653.0	652.8	652.7	652.6	652.6	653.2
162.5°	660.5	660.1	659.9	659.6	659.2	659.1	659.0	658.9	658.7	658.6	659.4
165°	668.8	668.4	668.2	667.8	667.4	667.2	667.1	667.0	666.9	666.7	667.7
167.5°	675.3	674.8	674.4	674.0	673.5	673.2	673.2	673.2	673.2	673.2	674.2
170°	678.9	678.5	678.1	677.6	677.2	676.9	676.9	676.9	676.9	676.9	677.9
172.5°	681.4	680.9	680.3	679.8	679.2	679.0	679.1	679.2	679.3	679.4	680.3
175°	684.6	684.0	683.4	682.9	682.3	682.1	682.2	682.3	682.4	682.5	683.3
177.5°	685.4	684.9	684.5	684.0	683.6	683.4	683.5	683.6	683.7	683.8	684.5
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332015-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	23.5	23.5	23.3	23.3	23.3	23.4	23.4	23.5
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	14.4	15.2	15.9	16.3	16.5	16.6	16.8	16.9
95°	17.4	18.1	18.9	19.4	19.4	19.4	19.4	19.4
97.5°	18.2	19.1	20.0	20.5	20.6	20.7	20.9	21.0
100°	18.5	19.5	20.4	20.9	21.0	21.1	21.2	21.4
102.5°	27.8	25.1	22.3	21.0	21.1	21.4	21.6	21.8
105°	71.3	51.4	31.4	21.5	21.7	21.9	22.1	22.4
107.5°	174.8	160.2	145.4	130.6	115.5	100.4	85.3	70.3
110°	221.9	218.2	214.5	204.5	188.3	172.2	156.0	139.8



TEST NUMBER: P332015-940

CATALOG NUMBER: S123DIP-S1000D585U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.1	255.2	255.3	253.6	250.2	246.7	243.3	240.0
115°	294.2	295.3	296.5	297.2	297.7	298.2	298.6	299.1
117.5°	329.6	330.5	331.4	331.9	332.0	332.1	332.2	332.3
120°	352.8	353.7	354.5	355.0	355.0	355.0	355.0	355.0
122.5°	375.4	376.0	376.7	377.0	377.1	377.2	377.3	377.4
125°	407.3	407.5	407.8	408.0	408.2	408.5	408.7	408.9
127.5°	439.3	439.7	440.1	440.1	439.9	439.7	439.4	439.3
130°	458.6	459.1	459.5	459.7	459.4	459.2	459.0	458.8
132.5°	477.0	477.4	477.9	478.0	477.6	477.2	477.0	476.6
135°	504.7	505.1	505.3	505.3	505.1	504.7	504.4	504.0
137.5°	529.4	529.9	530.5	530.7	530.4	530.2	529.9	529.8
140°	545.1	545.5	546.0	546.1	545.9	545.6	545.5	545.2
142.5°	560.0	560.4	560.7	560.7	560.4	560.1	559.7	559.5
145°	580.8	580.9	581.2	581.3	581.3	581.3	581.3	581.3
147.5°	599.4	599.6	599.9	599.7	599.1	598.6	598.2	597.6
150°	610.7	611.0	611.2	611.2	610.8	610.5	610.1	609.8
152.5°	620.9	621.3	621.7	621.6	621.2	620.6	620.1	619.6
155°	634.8	635.4	636.0	635.9	635.3	634.5	633.9	633.2
157.5°	646.9	647.6	648.4	648.2	647.3	646.5	645.6	644.7
160°	653.9	654.5	655.2	655.1	654.4	653.6	652.8	652.0
162.5°	660.1	660.9	661.7	661.7	661.0	660.3	659.6	659.0
165°	668.6	669.5	670.4	670.5	669.7	668.9	668.1	667.3
167.5°	675.1	676.0	676.9	676.9	676.0	675.1	674.2	673.2
170°	678.8	679.7	680.6	680.6	679.7	678.8	677.9	676.9
172.5°	681.2	682.1	683.0	683.0	682.0	681.0	679.9	678.9
175°	684.1	684.9	685.7	685.6	684.7	683.9	683.0	682.0
177.5°	685.2	685.9	686.6	686.5	685.6	684.7	683.9	683.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6

(END OF REPORT)