

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332020-940

Luminaire Tested: **S123DIP-S1000D805U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332020-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6373.9 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	68	66	64	58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	24	46	35	28	23	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13481	13481	13481	13481
5°	16077	13539	11998	13539
10°	20122	13470	10837	13470
15°	24681	13362	10089	13362
20°	29402	13192	9606	13192
25°	31220	12986	9499	12986
30°	26759	12837	9548	12837
35°	18611	12623	9648	12623
40°	14018	12372	9618	12372
45°	11639	12000	9496	12000
50°	10426	11238	9409	11238
55°	9747	10419	9293	10419
60°	9143	9563	9197	9563
65°	8593	8716	8904	8716
70°	8060	7755	8478	7755
75°	7216	6791	7773	6791
80°	6316	5566	6695	5566
85°	4940	4039	4495	4039



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	1.9
10°-20°	395.6	6.2
20°-30°	664.0	10.4
30°-40°	751.8	11.8
40°-50°	674.2	10.6
50°-60°	544.1	8.5
60°-70°	379.1	5.9
70°-80°	199.3	3.1
80°-90°	51.4	0.8
90°-100°	191.7	3.0
100°-110°	542.7	8.5
110°-120°	533.9	8.4
120°-130°	425.8	6.7
130°-140°	335.7	5.3
140°-150°	250.6	3.9
150°-160°	174.7	2.7
160°-170°	102.6	1.6
170°-180°	33.4	0.5
0°-30°	1182.9	18.6
0°-40°	1934.7	30.4
0°-60°	3153.0	49.5
0°-90°	3782.8	59.3
90°-120°	1268.2	19.9
90°-150°	2280.4	35.8
90°-180°	2591.0	40.7
0°-180°	6373.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1488	1253	1110	1253	1488	154
15°	2215	1199	905	1199	2215	639
25°	2629	1093	800	1093	2629	1153
35°	1416	961	734	961	1416	920
45°	765	788	624	788	765	605
55°	519	555	495	555	519	466
65°	337	342	350	342	337	336
75°	174	163	187	163	174	186
85°	40	33	36	33	40	48
90°	20	1	20	1	20	13
95°	81	24	81	24	81	146
105°	887	81	887	81	887	875
115°	1078	143	1078	143	1078	1048
125°	850	199	850	199	850	771
135°	690	233	690	233	690	535
145°	539	266	539	266	539	343
155°	447	302	447	302	447	208
165°	390	330	390	330	390	111
175°	351	344	351	344	351	34
180°	344	344	344	344	344	



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1329.1	1328.2	1325.7	1327.7	1323.8	1318.5	1317.9	1313.1	1299.0	1298.1	1294.2
5°	1487.9	1483.0	1482.4	1481.8	1473.3	1461.8	1439.9	1438.2	1409.0	1394.5	1376.8
7.5°	1693.4	1696.0	1687.1	1679.4	1653.4	1636.3	1612.8	1582.9	1547.1	1510.8	1486.7
10°	1841.0	1861.1	1836.2	1819.2	1803.4	1773.7	1739.1	1696.0	1653.0	1602.6	1564.3
12.5°	1999.3	2009.1	2004.1	1988.2	1963.6	1918.3	1857.1	1809.6	1770.0	1686.0	1652.2
15°	2214.8	2251.8	2228.2	2173.5	2174.8	2131.7	2051.6	1963.6	1916.9	1843.4	1743.4
17.5°	2444.4	2449.1	2439.0	2393.4	2363.1	2303.9	2230.0	2145.6	2051.0	1962.1	1856.0
20°	2566.8	2563.1	2541.9	2518.2	2466.0	2419.9	2339.2	2245.1	2123.8	2036.4	1920.6
22.5°	2634.7	2628.7	2618.6	2598.8	2555.4	2505.9	2433.4	2330.6	2215.1	2094.7	1960.8
25°	2628.7	2636.5	2637.8	2632.3	2617.2	2587.4	2530.3	2448.5	2333.2	2178.4	2038.9
27.5°	2390.8	2402.0	2434.4	2463.2	2495.3	2528.1	2523.7	2483.1	2397.7	2264.1	2093.5
30°	2152.9	2128.7	2188.7	2264.6	2316.1	2407.2	2458.2	2461.2	2413.2	2298.6	2132.3
32.5°	1822.8	1849.5	1876.1	1969.4	2082.1	2184.3	2285.8	2367.5	2376.9	2300.5	2155.1
35°	1416.3	1449.7	1498.2	1546.8	1668.1	1772.5	1950.9	2106.2	2230.0	2246.4	2157.1
37.5°	1141.3	1157.8	1188.5	1237.2	1316.5	1440.3	1578.3	1774.7	1954.0	2087.4	2093.2
40°	997.6	1002.5	1037.1	1074.1	1138.4	1240.3	1364.7	1538.2	1753.0	1939.4	2017.0
42.5°	889.8	900.4	915.2	950.7	1001.9	1078.6	1194.3	1337.7	1534.6	1749.0	1900.9
45°	764.6	776.7	785.8	809.5	845.9	897.4	978.2	1109.2	1259.1	1480.6	1685.1
47.5°	681.8	682.8	689.6	707.4	732.2	770.9	828.0	912.1	1049.7	1229.4	1439.3
50°	622.6	632.3	634.7	648.6	668.1	696.6	744.0	815.6	928.4	1086.2	1279.2
52.5°	580.9	583.7	590.6	600.7	617.6	639.8	680.8	736.9	825.5	959.9	1137.4
55°	519.4	519.4	526.1	534.0	543.7	563.7	591.0	632.3	699.6	804.1	950.8
57.5°	462.6	465.7	470.4	472.8	481.1	494.3	517.1	548.4	598.7	679.0	795.8
60°	424.7	430.3	429.6	434.4	441.8	452.1	471.4	497.0	541.9	606.2	704.5
62.5°	391.7	391.4	391.3	397.1	404.4	414.2	426.9	448.9	487.1	544.0	627.8
65°	337.4	336.2	340.5	344.0	346.5	353.7	363.5	382.9	408.4	450.8	515.8
67.5°	289.1	285.5	287.8	289.1	293.2	298.9	308.0	320.0	340.3	374.4	423.3
70°	256.1	253.1	252.4	253.6	257.3	261.5	268.2	279.7	298.5	325.8	361.7
72.5°	222.1	220.0	219.9	222.6	224.3	227.0	231.8	242.4	257.3	277.8	311.2
75°	173.5	173.5	173.5	174.2	175.9	178.4	182.0	187.5	199.0	213.6	236.0
77.5°	130.1	130.0	129.2	129.1	131.8	132.9	133.8	138.8	145.3	155.1	171.5
80°	101.9	98.9	100.1	101.9	103.2	103.8	105.6	106.8	112.3	117.7	129.2
82.5°	75.7	73.2	73.4	76.2	76.4	77.0	78.9	80.6	82.7	87.7	93.8
85°	40.0	40.0	40.7	40.7	41.3	40.7	42.4	43.1	43.1	46.1	49.8
87.5°	18.6	17.7	18.1	18.5	18.1	18.4	18.6	19.0	19.4	20.0	20.1
90°	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4	16.8	17.4	15.3
92.5°	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7	80.9	107.2	118.0
95°	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0	335.4	413.4	368.1
97.5°	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6	685.5	640.7	469.0
100°	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0	797.5	660.2	446.2
102.5°	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2	803.2	623.9	412.7
105°	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3	760.6	560.5	371.6
107.5°	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4	686.2	504.4	345.4
110°	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0	639.3	472.7	335.4



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1	598.6	451.5	329.8
115°	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3	549.4	428.7	327.7
117.5°	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6	519.7	415.4	329.0
120°	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4	504.1	409.2	331.2
122.5°	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8	491.2	405.4	335.0
125°	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2	474.7	400.2	340.9
127.5°	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3	460.3	397.7	347.6
130°	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2	452.5	396.0	352.0
132.5°	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2	445.2	395.4	355.4
135°	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4	435.7	394.6	360.4
137.5°	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3	427.5	393.1	363.8
140°	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2	422.5	392.5	366.0
142.5°	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8	418.0	391.4	367.7
145°	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4	412.1	389.7	368.8
147.5°	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0	406.2	387.1	368.8
150°	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3	402.3	384.9	368.8
152.5°	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1	397.8	382.0	367.1
155°	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0	391.1	377.2	365.3
157.5°	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2	383.6	372.8	362.9
160°	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6	378.5	369.5	361.9
162.5°	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9	373.5	366.1	359.6
165°	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3	366.7	361.1	356.2
167.5°	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7	360.2	356.1	352.9
170°	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7	356.2	352.8	350.7
172.5°	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3	352.3	350.0	349.0
175°	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3	347.9	346.5	346.5
177.5°	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1291.3	1287.4	1283.5	1276.8	1270.9	1262.7	1260.2	1257.3	1248.6	1240.8	1234.9
5°	1370.1	1355.6	1334.4	1314.9	1299.1	1277.9	1265.8	1253.0	1234.8	1218.4	1205.1
7.5°	1452.7	1424.1	1391.1	1355.3	1322.1	1290.0	1264.2	1241.2	1215.7	1191.5	1172.7
10°	1518.2	1476.9	1430.8	1381.1	1338.6	1297.4	1262.8	1232.4	1199.6	1171.1	1147.5
12.5°	1593.0	1531.8	1468.2	1407.7	1357.5	1300.3	1258.4	1219.8	1182.7	1148.3	1121.8
15°	1681.4	1603.7	1528.6	1445.4	1369.0	1297.4	1247.6	1199.1	1155.9	1120.8	1086.8
17.5°	1762.0	1674.0	1574.9	1473.8	1381.5	1296.6	1227.0	1172.1	1118.2	1075.1	1041.3
20°	1807.7	1707.5	1595.3	1490.3	1388.4	1293.7	1217.3	1151.7	1093.4	1047.9	1009.7
22.5°	1847.0	1729.8	1613.7	1501.5	1387.9	1285.9	1199.3	1131.8	1068.7	1024.1	983.5
25°	1887.8	1747.6	1631.1	1499.4	1372.6	1267.0	1169.9	1093.4	1030.4	978.2	936.3
27.5°	1922.7	1746.4	1608.1	1466.5	1348.5	1242.7	1139.1	1057.0	990.1	933.4	890.9
30°	1946.0	1748.8	1584.4	1444.2	1325.3	1216.0	1115.3	1032.8	962.4	904.7	864.7
32.5°	1960.6	1747.3	1562.5	1413.1	1288.3	1191.8	1089.6	1004.2	931.8	875.1	836.5
35°	1969.1	1736.7	1524.9	1348.9	1228.8	1134.7	1049.2	960.6	884.8	832.0	788.3
37.5°	1952.0	1714.2	1481.2	1287.0	1155.5	1062.8	990.9	915.4	842.8	784.7	747.1
40°	1925.4	1699.7	1447.2	1243.3	1105.0	1015.7	954.5	880.5	808.9	753.7	718.5
42.5°	1874.4	1670.0	1409.9	1194.8	1052.6	963.3	907.0	845.1	777.3	725.5	690.3
45°	1750.0	1605.6	1353.8	1122.0	975.1	882.9	833.1	788.3	726.9	676.5	646.2
47.5°	1577.4	1508.6	1272.7	1045.2	894.3	805.6	753.9	717.7	673.0	632.3	603.2
50°	1457.5	1429.1	1217.8	992.7	840.4	753.7	703.9	671.1	639.0	598.3	571.6
52.5°	1319.2	1336.8	1153.8	938.3	785.6	700.3	653.4	627.4	598.2	564.8	541.5
55°	1124.4	1188.1	1043.1	847.1	703.9	622.6	578.3	555.2	538.2	513.4	493.3
57.5°	942.0	1023.1	923.5	753.0	623.7	553.5	511.0	485.9	475.0	462.0	446.2
60°	833.7	913.8	838.0	689.9	569.8	503.0	465.4	444.2	433.3	424.2	410.8
62.5°	737.2	818.2	754.5	625.9	516.8	455.0	422.2	401.4	393.0	388.3	376.8
65°	604.4	674.1	631.7	526.1	441.1	386.6	356.8	342.2	334.4	332.5	325.2
67.5°	491.9	545.0	514.1	436.4	369.5	322.4	297.1	284.7	278.7	278.0	272.6
70°	418.1	467.9	444.2	373.8	316.1	279.1	257.3	246.4	242.7	242.1	239.1
72.5°	360.8	395.5	376.7	318.0	273.4	239.8	223.8	212.4	208.2	209.1	207.1
75°	267.0	293.1	282.1	241.5	205.7	183.9	170.5	163.3	159.6	161.4	159.0
77.5°	192.1	208.7	198.8	170.7	148.6	132.8	123.0	118.4	115.2	115.0	114.0
80°	145.0	154.7	149.3	132.2	114.0	100.8	92.8	89.8	88.0	87.4	86.8
82.5°	103.3	111.6	105.1	93.5	81.1	73.0	68.6	64.6	63.2	63.6	63.0
85°	52.2	55.2	52.8	45.5	40.7	37.0	34.6	32.7	31.6	32.2	30.9
87.5°	20.6	20.7	18.8	16.6	15.3	13.5	13.2	11.9	11.2	11.5	11.4
90°	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4	2.8	4.2	6.2
92.5°	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6	12.8	18.7	24.2
95°	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7	25.8	33.4	45.3
97.5°	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4	41.1	47.2	57.4
100°	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6	52.3	57.2	67.0
102.5°	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3	64.6	68.8	78.1
105°	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9	82.9	87.1	95.5
107.5°	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5	101.7	105.7	113.9
110°	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0	115.0	118.5	126.2



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2	127.3	130.8	138.5
115°	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9	145.7	149.9	156.9
117.5°	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6	163.8	167.3	173.7
120°	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9	175.0	178.4	185.5
122.5°	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5	185.6	189.0	196.6
125°	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7	200.1	204.3	212.0
127.5°	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3	212.3	217.5	225.3
130°	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5	219.6	225.9	234.3
132.5°	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1	225.8	232.6	242.6
135°	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8	235.7	243.3	253.8
137.5°	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0	245.0	252.5	263.7
140°	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2	251.6	258.7	269.8
142.5°	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9	257.8	265.4	275.4
145°	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6	267.7	274.0	284.5
147.5°	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5	277.8	283.9	292.9
150°	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7	284.5	290.0	299.1
152.5°	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0	291.1	296.7	304.7
155°	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8	301.8	306.0	313.0
157.5°	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5	311.0	314.4	320.6
160°	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2	317.2	320.0	325.6
162.5°	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3	322.3	324.5	329.0
165°	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8	329.0	330.5	333.9
167.5°	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5	334.7	335.4	338.0
170°	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9	337.4	338.1	340.2
172.5°	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1	340.2	340.4	341.9
175°	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7	343.0	342.3	343.7
177.5°	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9	344.4	343.8	344.4
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1231.5	1228.2	1223.3	1216.0	1210.2	1201.0	1201.0	1202.5	1202.5	1201.9	1201.0
5°	1194.2	1185.1	1174.2	1161.5	1148.1	1134.7	1132.3	1127.5	1123.8	1121.3	1118.3
7.5°	1154.8	1138.6	1122.7	1104.8	1088.6	1075.1	1065.8	1058.0	1053.0	1047.7	1043.8
10°	1128.0	1108.0	1089.2	1070.4	1049.7	1033.4	1023.1	1015.7	1010.3	1005.5	1003.1
12.5°	1096.4	1073.5	1052.8	1034.9	1012.4	995.5	985.7	982.3	975.9	965.6	960.3
15°	1050.3	1029.1	1004.2	977.0	966.0	945.4	933.9	928.4	924.8	916.9	914.4
17.5°	1010.9	983.1	955.2	934.9	914.5	897.9	891.4	884.6	879.8	873.3	871.4
20°	979.4	954.5	929.0	907.1	885.9	867.7	862.3	857.4	852.6	849.5	847.1
22.5°	947.4	922.5	901.3	880.9	858.3	846.3	840.4	835.1	831.7	829.6	827.2
25°	902.3	880.5	856.8	838.6	820.4	812.5	808.9	805.8	803.4	800.4	799.8
27.5°	862.0	838.2	819.0	802.1	789.0	782.4	778.9	777.4	777.9	779.0	779.7
30°	832.0	810.1	794.3	779.7	767.6	761.5	760.9	760.9	763.4	763.9	765.2
32.5°	804.2	786.3	770.5	756.4	747.3	743.1	745.4	745.4	747.3	748.9	751.1
35°	763.9	748.1	736.0	723.9	716.0	717.8	719.1	720.2	723.3	726.9	729.4
37.5°	725.5	711.8	699.2	689.6	686.1	689.3	692.2	694.8	698.3	701.1	703.6
40°	697.9	687.5	675.4	666.9	668.1	669.9	672.3	675.4	678.4	680.2	682.7
42.5°	672.1	661.3	652.1	645.1	646.8	649.1	650.5	652.1	655.6	658.9	660.3
45°	632.9	624.4	615.9	611.6	612.9	614.1	615.3	617.2	620.2	622.6	623.2
47.5°	588.8	582.9	577.2	573.1	575.0	574.5	576.1	580.0	580.9	582.4	585.8
50°	560.7	555.2	548.6	547.3	547.3	547.3	548.0	552.8	552.8	555.2	557.7
52.5°	529.6	526.1	521.8	519.7	518.7	518.7	521.2	523.7	524.7	528.1	530.5
55°	483.7	480.0	476.4	474.5	473.3	474.5	479.4	480.5	483.7	485.4	487.2
57.5°	435.7	432.9	430.0	429.0	428.7	430.3	433.0	436.7	437.4	443.0	445.8
60°	404.1	399.8	397.4	397.4	396.3	401.7	400.5	406.5	407.8	411.4	415.6
62.5°	371.6	365.9	364.9	364.9	366.7	368.2	369.9	372.6	375.8	380.3	383.6
65°	319.1	316.1	320.4	319.8	318.6	322.2	322.2	325.2	328.9	333.1	339.8
67.5°	269.6	268.0	268.3	268.3	270.2	272.2	273.9	276.6	281.0	285.4	289.8
70°	236.0	237.9	234.9	237.3	239.1	239.7	240.9	244.5	249.4	252.4	257.3
72.5°	203.5	203.4	203.8	204.7	206.5	207.7	208.8	213.0	218.3	220.9	224.8
75°	156.6	156.0	157.7	157.7	160.8	162.0	163.3	165.1	169.9	173.5	176.6
77.5°	114.3	115.0	114.7	116.7	115.9	116.1	119.9	121.7	122.3	129.4	131.0
80°	86.1	87.4	88.0	88.6	89.2	88.0	92.2	94.1	94.1	98.3	101.3
82.5°	61.9	62.6	64.2	64.8	64.9	66.2	66.5	67.9	69.3	71.2	75.1
85°	30.9	32.7	33.3	32.7	33.3	32.2	34.0	34.6	35.2	35.2	35.2
87.5°	11.2	12.0	11.9	12.8	12.8	13.6	13.6	12.8	12.8	14.4	12.8
90°	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4	18.1	18.8	20.2
92.5°	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7	46.5	41.1	37.5
95°	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0	170.1	133.1	108.1
97.5°	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6	501.1	411.2	327.8
100°	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0	765.4	683.9	584.9
102.5°	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2	885.4	837.9	775.1
105°	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3	976.0	989.3	971.2
107.5°	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4	964.6	1025.6	1050.4
110°	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0	927.2	1015.0	1063.9



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1	878.2	976.6	1039.3
115°	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3	799.6	902.1	978.1
117.5°	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6	733.3	825.3	902.4
120°	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4	696.4	780.2	850.5
122.5°	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8	666.9	744.4	809.9
125°	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2	630.3	697.1	753.0
127.5°	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3	598.0	658.4	709.2
130°	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2	577.9	634.5	681.8
132.5°	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2	559.0	611.5	656.7
135°	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4	531.9	577.2	617.0
137.5°	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3	505.9	544.9	579.3
140°	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2	490.8	524.2	554.2
142.5°	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8	476.3	505.3	531.4
145°	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4	457.4	479.7	499.9
147.5°	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0	443.3	461.3	475.6
150°	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3	434.4	449.0	462.2
152.5°	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1	426.0	438.9	450.0
155°	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0	414.1	424.5	432.9
157.5°	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2	402.5	410.6	417.1
160°	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6	395.3	402.3	407.2
162.5°	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9	387.4	393.9	398.2
165°	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3	376.5	381.4	384.9
167.5°	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7	367.9	370.8	373.3
170°	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7	361.9	364.6	366.0
172.5°	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3	356.8	359.0	359.9
175°	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3	350.0	351.3	351.3
177.5°	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5	346.1	346.6	346.6
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1197.6	1197.1	1200.5	1198.1	1200.5	1197.1	1197.6	1201.0	1201.9	1202.5	1202.5
5°	1114.7	1116.5	1110.4	1110.4	1110.4	1116.5	1114.7	1118.3	1121.3	1123.8	1127.5
7.5°	1040.9	1038.2	1038.5	1035.2	1038.5	1038.2	1040.9	1043.8	1047.7	1053.0	1058.0
10°	995.8	992.1	990.9	991.5	990.9	992.1	995.8	1003.1	1005.5	1010.3	1015.7
12.5°	958.4	957.7	949.7	949.8	949.7	957.7	958.4	960.3	965.6	975.9	982.3
15°	914.4	902.9	901.7	905.4	901.7	902.9	914.4	914.4	916.9	924.8	928.4
17.5°	870.4	864.3	864.7	862.9	864.7	864.3	870.4	871.4	873.3	879.8	884.6
20°	847.1	843.5	842.8	838.6	842.8	843.5	847.1	847.1	849.5	852.6	857.4
22.5°	825.7	824.6	824.9	820.2	824.9	824.6	825.7	827.2	829.6	831.7	835.1
25°	799.2	802.2	799.8	799.8	799.8	802.2	799.2	799.8	800.4	803.4	805.8
27.5°	781.2	781.0	779.9	779.9	779.9	781.0	781.2	779.7	779.0	777.9	777.4
30°	767.6	767.0	768.2	768.2	768.2	767.0	767.6	765.2	763.9	763.4	760.9
32.5°	754.0	754.8	755.1	755.5	755.1	754.8	754.0	751.1	748.9	747.3	745.4
35°	733.0	733.6	735.5	734.2	735.5	733.6	733.0	729.4	726.9	723.3	720.2
37.5°	704.6	707.4	706.8	707.8	706.8	707.4	704.6	703.6	701.1	698.3	694.8
40°	683.2	685.1	684.5	684.5	684.5	685.1	683.2	682.7	680.2	678.4	675.4
42.5°	661.4	662.7	661.2	660.2	661.2	662.7	661.4	660.3	658.9	655.6	652.1
45°	625.6	624.4	626.2	623.8	626.2	624.4	625.6	623.2	622.6	620.2	617.2
47.5°	585.6	586.7	587.3	589.1	587.3	586.7	585.6	585.8	582.4	580.9	580.0
50°	558.8	562.5	562.5	561.9	562.5	562.5	558.8	557.7	555.2	552.8	552.8
52.5°	532.6	534.3	536.8	536.6	536.8	534.3	532.6	530.5	528.1	524.7	523.7
55°	492.1	493.3	494.5	495.2	494.5	493.3	492.1	487.2	485.4	483.7	480.5
57.5°	450.1	449.6	452.5	453.4	452.5	449.6	450.1	445.8	443.0	437.4	436.7
60°	420.5	420.5	425.3	427.2	425.3	420.5	420.5	415.6	411.4	407.8	406.5
62.5°	389.0	390.9	395.7	393.2	395.7	390.9	389.0	383.6	380.3	375.8	372.6
65°	342.9	347.7	347.1	349.6	347.1	347.7	342.9	339.8	333.1	328.9	325.2
67.5°	294.6	297.7	302.0	302.5	302.0	297.7	294.6	289.8	285.4	281.0	276.6
70°	262.2	265.2	267.6	269.4	267.6	265.2	262.2	257.3	252.4	249.4	244.5
72.5°	230.6	232.2	238.0	235.4	238.0	232.2	230.6	224.8	220.9	218.3	213.0
75°	180.8	185.0	188.7	186.9	188.7	185.0	180.8	176.6	173.5	169.9	165.1
77.5°	133.8	137.9	139.6	138.1	139.6	137.9	133.8	131.0	129.4	122.3	121.7
80°	105.6	105.0	108.6	108.0	108.6	105.0	105.6	101.3	98.3	94.1	94.1
82.5°	77.4	76.9	78.6	78.9	78.6	76.9	77.4	75.1	71.2	69.3	67.9
85°	37.6	39.4	37.0	36.4	37.0	39.4	37.6	35.2	35.2	35.2	34.6
87.5°	12.7	12.8	12.4	11.8	12.4	12.8	12.7	12.8	14.4	12.8	12.8
90°	19.5	20.2	21.0	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4
92.5°	36.3	34.2	34.9	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7
95°	94.8	88.5	83.6	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0
97.5°	276.3	245.0	226.1	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6
100°	514.5	463.6	436.4	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0
102.5°	720.3	680.0	657.3	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2
105°	939.1	912.6	890.3	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3
107.5°	1051.1	1042.1	1034.6	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4
110°	1083.3	1089.0	1087.5	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1075.0	1092.3	1097.6	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1
115°	1030.4	1061.0	1075.0	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3
117.5°	956.9	992.0	1012.1	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6
120°	905.6	944.7	961.4	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4
122.5°	858.7	893.9	912.3	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8
125°	797.5	828.2	845.6	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2
127.5°	748.9	775.1	790.9	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3
130°	718.8	743.9	758.5	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2
132.5°	691.4	716.6	729.5	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2
135°	651.1	672.1	684.6	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4
137.5°	608.1	629.3	639.9	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3
140°	580.8	600.2	611.4	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2
142.5°	553.9	571.2	581.3	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8
145°	517.3	531.9	537.5	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4
147.5°	488.8	498.7	504.1	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0
150°	472.7	480.4	484.6	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3
152.5°	458.2	465.3	467.8	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1
155°	439.2	444.8	446.2	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0
157.5°	422.6	426.8	427.9	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2
160°	412.1	416.2	416.2	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6
162.5°	401.4	405.0	405.0	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9
165°	387.6	390.4	389.7	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3
167.5°	374.5	376.5	375.8	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7
170°	366.7	368.1	367.4	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7
172.5°	360.0	361.4	360.2	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3
175°	351.3	352.0	351.3	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3
177.5°	346.1	346.6	345.5	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1201.0	1201.0	1210.2	1216.0	1223.3	1228.2	1231.5	1234.9	1240.8	1248.6	1257.3
5°	1132.3	1134.7	1148.1	1161.5	1174.2	1185.1	1194.2	1205.1	1218.4	1234.8	1253.0
7.5°	1065.8	1075.1	1088.6	1104.8	1122.7	1138.6	1154.8	1172.7	1191.5	1215.7	1241.2
10°	1023.1	1033.4	1049.7	1070.4	1089.2	1108.0	1128.0	1147.5	1171.1	1199.6	1232.4
12.5°	985.7	995.5	1012.4	1034.9	1052.8	1073.5	1096.4	1121.8	1148.3	1182.7	1219.8
15°	933.9	945.4	966.0	977.0	1004.2	1029.1	1050.3	1086.8	1120.8	1155.9	1199.1
17.5°	891.4	897.9	914.5	934.9	955.2	983.1	1010.9	1041.3	1075.1	1118.2	1172.1
20°	862.3	867.7	885.9	907.1	929.0	954.5	979.4	1009.7	1047.9	1093.4	1151.7
22.5°	840.4	846.3	858.3	880.9	901.3	922.5	947.4	983.5	1024.1	1068.7	1131.8
25°	808.9	812.5	820.4	838.6	856.8	880.5	902.3	936.3	978.2	1030.4	1093.4
27.5°	778.9	782.4	789.0	802.1	819.0	838.2	862.0	890.9	933.4	990.1	1057.0
30°	760.9	761.5	767.6	779.7	794.3	810.1	832.0	864.7	904.7	962.4	1032.8
32.5°	745.4	743.1	747.3	756.4	770.5	786.3	804.2	836.5	875.1	931.8	1004.2
35°	719.1	717.8	716.0	723.9	736.0	748.1	763.9	788.3	832.0	884.8	960.6
37.5°	692.2	689.3	686.1	689.6	699.2	711.8	725.5	747.1	784.7	842.8	915.4
40°	672.3	669.9	668.1	666.9	675.4	687.5	697.9	718.5	753.7	808.9	880.5
42.5°	650.5	649.1	646.8	645.1	652.1	661.3	672.1	690.3	725.5	777.3	845.1
45°	615.3	614.1	612.9	611.6	615.9	624.4	632.9	646.2	676.5	726.9	788.3
47.5°	576.1	574.5	575.0	573.1	577.2	582.9	588.8	603.2	632.3	673.0	717.7
50°	548.0	547.3	547.3	547.3	548.6	555.2	560.7	571.6	598.3	639.0	671.1
52.5°	521.2	518.7	518.7	519.7	521.8	526.1	529.6	541.5	564.8	598.2	627.4
55°	479.4	474.5	473.3	474.5	476.4	480.0	483.7	493.3	513.4	538.2	555.2
57.5°	433.0	430.3	428.7	429.0	430.0	432.9	435.7	446.2	462.0	475.0	485.9
60°	400.5	401.7	396.3	397.4	397.4	399.8	404.1	410.8	424.2	433.3	444.2
62.5°	369.9	368.2	366.7	364.9	364.9	365.9	371.6	376.8	388.3	393.0	401.4
65°	322.2	322.2	318.6	319.8	320.4	316.1	319.1	325.2	332.5	334.4	342.2
67.5°	273.9	272.2	270.2	268.3	268.3	268.0	269.6	272.6	278.0	278.7	284.7
70°	240.9	239.7	239.1	237.3	234.9	237.9	236.0	239.1	242.1	242.7	246.4
72.5°	208.8	207.7	206.5	204.7	203.8	203.4	203.5	207.1	209.1	208.2	212.4
75°	163.3	162.0	160.8	157.7	157.7	156.0	156.6	159.0	161.4	159.6	163.3
77.5°	119.9	116.1	115.9	116.7	114.7	115.0	114.3	114.0	115.0	115.2	118.4
80°	92.2	88.0	89.2	88.6	88.0	87.4	86.1	86.8	87.4	88.0	89.8
82.5°	66.5	66.2	64.9	64.8	64.2	62.6	61.9	63.0	63.6	63.2	64.6
85°	34.0	32.2	33.3	32.7	33.3	32.7	30.9	30.9	32.2	31.6	32.7
87.5°	13.6	13.6	12.8	12.8	11.9	12.0	11.2	11.4	11.5	11.2	11.9
90°	16.8	17.4	15.3	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4
92.5°	80.9	107.2	118.0	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6
95°	335.4	413.4	368.1	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7
97.5°	685.5	640.7	469.0	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4
100°	797.5	660.2	446.2	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6
102.5°	803.2	623.9	412.7	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3
105°	760.6	560.5	371.6	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9
107.5°	686.2	504.4	345.4	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5
110°	639.3	472.7	335.4	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	598.6	451.5	329.8	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2
115°	549.4	428.7	327.7	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9
117.5°	519.7	415.4	329.0	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6
120°	504.1	409.2	331.2	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9
122.5°	491.2	405.4	335.0	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5
125°	474.7	400.2	340.9	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7
127.5°	460.3	397.7	347.6	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3
130°	452.5	396.0	352.0	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5
132.5°	445.2	395.4	355.4	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1
135°	435.7	394.6	360.4	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8
137.5°	427.5	393.1	363.8	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0
140°	422.5	392.5	366.0	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2
142.5°	418.0	391.4	367.7	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9
145°	412.1	389.7	368.8	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6
147.5°	406.2	387.1	368.8	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5
150°	402.3	384.9	368.8	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7
152.5°	397.8	382.0	367.1	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0
155°	391.1	377.2	365.3	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8
157.5°	383.6	372.8	362.9	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5
160°	378.5	369.5	361.9	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2
162.5°	373.5	366.1	359.6	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3
165°	366.7	361.1	356.2	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8
167.5°	360.2	356.1	352.9	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5
170°	356.2	352.8	350.7	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9
172.5°	352.3	350.0	349.0	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1
175°	347.9	346.5	346.5	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7
177.5°	344.9	344.4	344.9	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1260.2	1262.7	1270.9	1276.8	1283.5	1287.4	1291.3	1294.2	1298.1	1299.0	1313.1
5°	1265.8	1277.9	1299.1	1314.9	1334.4	1355.6	1370.1	1376.8	1394.5	1409.0	1438.2
7.5°	1264.2	1290.0	1322.1	1355.3	1391.1	1424.1	1452.7	1486.7	1510.8	1547.1	1582.9
10°	1262.8	1297.4	1338.6	1381.1	1430.8	1476.9	1518.2	1564.3	1602.6	1653.0	1696.0
12.5°	1258.4	1300.3	1357.5	1407.7	1468.2	1531.8	1593.0	1652.2	1686.0	1770.0	1809.6
15°	1247.6	1297.4	1369.0	1445.4	1528.6	1603.7	1681.4	1743.4	1843.4	1916.9	1963.6
17.5°	1227.0	1296.6	1381.5	1473.8	1574.9	1674.0	1762.0	1856.0	1962.1	2051.0	2145.6
20°	1217.3	1293.7	1388.4	1490.3	1595.3	1707.5	1807.7	1920.6	2036.4	2123.8	2245.1
22.5°	1199.3	1285.9	1387.9	1501.5	1613.7	1729.8	1847.0	1960.8	2094.7	2215.1	2330.6
25°	1169.9	1267.0	1372.6	1499.4	1631.1	1747.6	1887.8	2038.9	2178.4	2333.2	2448.5
27.5°	1139.1	1242.7	1348.5	1466.5	1608.1	1746.4	1922.7	2093.5	2264.1	2397.7	2483.1
30°	1115.3	1216.0	1325.3	1444.2	1584.4	1748.8	1946.0	2132.3	2298.6	2413.2	2461.2
32.5°	1089.6	1191.8	1288.3	1413.1	1562.5	1747.3	1960.6	2155.1	2300.5	2376.9	2367.5
35°	1049.2	1134.7	1228.8	1348.9	1524.9	1736.7	1969.1	2157.1	2246.4	2230.0	2106.2
37.5°	990.9	1062.8	1155.5	1287.0	1481.2	1714.2	1952.0	2093.2	2087.4	1954.0	1774.7
40°	954.5	1015.7	1105.0	1243.3	1447.2	1699.7	1925.4	2017.0	1939.4	1753.0	1538.2
42.5°	907.0	963.3	1052.6	1194.8	1409.9	1670.0	1874.4	1900.9	1749.0	1534.6	1337.7
45°	833.1	882.9	975.1	1122.0	1353.8	1605.6	1750.0	1685.1	1480.6	1259.1	1109.2
47.5°	753.9	805.6	894.3	1045.2	1272.7	1508.6	1577.4	1439.3	1229.4	1049.7	912.1
50°	703.9	753.7	840.4	992.7	1217.8	1429.1	1457.5	1279.2	1086.2	928.4	815.6
52.5°	653.4	700.3	785.6	938.3	1153.8	1336.8	1319.2	1137.4	959.9	825.5	736.9
55°	578.3	622.6	703.9	847.1	1043.1	1188.1	1124.4	950.8	804.1	699.6	632.3
57.5°	511.0	553.5	623.7	753.0	923.5	1023.1	942.0	795.8	679.0	598.7	548.4
60°	465.4	503.0	569.8	689.9	838.0	913.8	833.7	704.5	606.2	541.9	497.0
62.5°	422.2	455.0	516.8	625.9	754.5	818.2	737.2	627.8	544.0	487.1	448.9
65°	356.8	386.6	441.1	526.1	631.7	674.1	604.4	515.8	450.8	408.4	382.9
67.5°	297.1	322.4	369.5	436.4	514.1	545.0	491.9	423.3	374.4	340.3	320.0
70°	257.3	279.1	316.1	373.8	444.2	467.9	418.1	361.7	325.8	298.5	279.7
72.5°	223.8	239.8	273.4	318.0	376.7	395.5	360.8	311.2	277.8	257.3	242.4
75°	170.5	183.9	205.7	241.5	282.1	293.1	267.0	236.0	213.6	199.0	187.5
77.5°	123.0	132.8	148.6	170.7	198.8	208.7	192.1	171.5	155.1	145.3	138.8
80°	92.8	100.8	114.0	132.2	149.3	154.7	145.0	129.2	117.7	112.3	106.8
82.5°	68.6	73.0	81.1	93.5	105.1	111.6	103.3	93.8	87.7	82.7	80.6
85°	34.6	37.0	40.7	45.5	52.8	55.2	52.2	49.8	46.1	43.1	43.1
87.5°	13.2	13.5	15.3	16.6	18.8	20.7	20.6	20.1	20.0	19.4	19.0
90°	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4
92.5°	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7
95°	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0
97.5°	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6
100°	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0
102.5°	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2
105°	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3
107.5°	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4
110°	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1
115°	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3
117.5°	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6
120°	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4
122.5°	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8
125°	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2
127.5°	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3
130°	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2
132.5°	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2
135°	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4
137.5°	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3
140°	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2
142.5°	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8
145°	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4
147.5°	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0
150°	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3
152.5°	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1
155°	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0
157.5°	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2
160°	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6
162.5°	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9
165°	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3
167.5°	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7
170°	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7
172.5°	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3
175°	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3
177.5°	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1317.9	1318.5	1323.8	1327.7	1325.7	1328.2	1329.1
5°	1439.9	1461.8	1473.3	1481.8	1482.4	1483.0	1487.9
7.5°	1612.8	1636.3	1653.4	1679.4	1687.1	1696.0	1693.4
10°	1739.1	1773.7	1803.4	1819.2	1836.2	1861.1	1841.0
12.5°	1857.1	1918.3	1963.6	1988.2	2004.1	2009.1	1999.3
15°	2051.6	2131.7	2174.8	2173.5	2228.2	2251.8	2214.8
17.5°	2230.0	2303.9	2363.1	2393.4	2439.0	2449.1	2444.4
20°	2339.2	2419.9	2466.0	2518.2	2541.9	2563.1	2566.8
22.5°	2433.4	2505.9	2555.4	2598.8	2618.6	2628.7	2634.7
25°	2530.3	2587.4	2617.2	2632.3	2637.8	2636.5	2628.7
27.5°	2523.7	2528.1	2495.3	2463.2	2434.4	2402.0	2390.8
30°	2458.2	2407.2	2316.1	2264.6	2188.7	2128.7	2152.9
32.5°	2285.8	2184.3	2082.1	1969.4	1876.1	1849.5	1822.8
35°	1950.9	1772.5	1668.1	1546.8	1498.2	1449.7	1416.3
37.5°	1578.3	1440.3	1316.5	1237.2	1188.5	1157.8	1141.3
40°	1364.7	1240.3	1138.4	1074.1	1037.1	1002.5	997.6
42.5°	1194.3	1078.6	1001.9	950.7	915.2	900.4	889.8
45°	978.2	897.4	845.9	809.5	785.8	776.7	764.6
47.5°	828.0	770.9	732.2	707.4	689.6	682.8	681.8
50°	744.0	696.6	668.1	648.6	634.7	632.3	622.6
52.5°	680.8	639.8	617.6	600.7	590.6	583.7	580.9
55°	591.0	563.7	543.7	534.0	526.1	519.4	519.4
57.5°	517.1	494.3	481.1	472.8	470.4	465.7	462.6
60°	471.4	452.1	441.8	434.4	429.6	430.3	424.7
62.5°	426.9	414.2	404.4	397.1	391.3	391.4	391.7
65°	363.5	353.7	346.5	344.0	340.5	336.2	337.4
67.5°	308.0	298.9	293.2	289.1	287.8	285.5	289.1
70°	268.2	261.5	257.3	253.6	252.4	253.1	256.1
72.5°	231.8	227.0	224.3	222.6	219.9	220.0	222.1
75°	182.0	178.4	175.9	174.2	173.5	173.5	173.5
77.5°	133.8	132.9	131.8	129.1	129.2	130.0	130.1
80°	105.6	103.8	103.2	101.9	100.1	98.9	101.9
82.5°	78.9	77.0	76.4	76.2	73.4	73.2	75.7
85°	42.4	40.7	41.3	40.7	40.7	40.0	40.0
87.5°	18.6	18.4	18.1	18.5	18.1	17.7	18.6
90°	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P332020-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)