

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332025-940

Luminaire Tested: **S123DIP-S1000D805U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332025-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6134.4 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332025-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332025-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	95	92	88	93	89	86	83	78	75	73	67	65	64	58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	47	42	38	40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332025-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	2.2
10°-20°	375.4	6.1
20°-30°	554.6	9.0
30°-40°	647.8	10.6
40°-50°	651.3	10.6
50°-60°	572.1	9.3
60°-70°	426.2	6.9
70°-80°	242.8	4.0
80°-90°	72.3	1.2
90°-100°	57.8	0.9
100°-110°	173.1	2.8
110°-120°	294.3	4.8
120°-130°	387.1	6.3
130°-140°	435.1	7.1
140°-150°	427.7	7.0
150°-160°	360.1	5.9
160°-170°	239.7	3.9
170°-180°	83.9	1.4
0°-30°	1062.9	17.3
0°-40°	1710.7	27.9
0°-60°	2934.1	47.8
0°-90°	3675.4	59.9
90°-120°	525.2	8.6
90°-150°	1775.2	28.9
90°-180°	2459.0	40.1
0°-180°	6134.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	8	17	19	21	6
95°	41	46	52	54	54	46
105°	157	159	164	165	166	168
115°	296	298	297	298	297	293
125°	434	436	434	432	429	387
135°	563	567	566	563	562	433
145°	682	684	686	685	682	426
155°	782	782	782	785	780	360
165°	851	849	849	853	848	240
175°	885	883	883	886	882	84
180°	888	888	888	888	888	



TEST NUMBER: P332025-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.4	25.1	24.7	24.3	24.1	24.0	24.2	24.3	24.5	24.7	24.6
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	16.9	17.9	19.0	20.1	21.0	22.2	23.4	24.5	25.6	26.8	27.3
95°	41.1	42.2	43.3	44.4	45.5	46.6	47.9	49.1	50.4	51.6	52.3
97.5°	73.0	73.8	74.6	75.4	76.3	77.1	78.0	78.9	79.8	80.7	81.4
100°	94.8	95.8	96.7	97.6	98.5	99.4	100.1	100.9	101.7	102.5	103.0
102.5°	119.9	120.5	121.0	121.6	122.2	123.0	123.9	125.0	126.0	127.1	127.5
105°	156.9	157.2	157.5	157.8	158.1	159.0	160.3	161.8	163.2	164.5	164.5
107.5°	199.8	200.0	200.2	200.4	200.5	200.9	201.5	202.1	202.6	203.1	203.7
110°	226.6	226.9	227.2	227.5	227.8	228.1	228.5	228.7	229.1	229.3	230.0



TEST NUMBER: P332025-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.5	254.7	254.9	255.0	255.2	255.3	255.4	255.5	255.6	255.6	256.4
115°	296.3	296.8	297.2	297.7	298.2	298.3	297.9	297.7	297.3	297.0	297.1
117.5°	338.4	338.8	339.0	339.3	339.7	339.6	339.2	338.8	338.4	338.0	338.0
120°	364.6	365.5	366.5	367.4	368.4	368.5	367.7	366.8	366.1	365.3	365.2
122.5°	392.0	392.6	393.3	394.0	394.7	394.8	394.4	394.0	393.6	393.2	392.8
125°	433.6	434.1	434.5	435.1	435.5	435.6	435.2	435.0	434.6	434.4	433.7
127.5°	472.2	473.1	474.1	475.1	476.1	476.4	476.1	475.7	475.4	475.0	474.2
130°	497.8	499.0	500.2	501.5	502.7	503.1	502.7	502.2	501.8	501.2	500.6
132.5°	523.4	524.7	525.9	527.2	528.4	528.9	528.5	528.2	527.8	527.4	526.7
135°	562.6	563.6	564.5	565.4	566.3	566.8	566.6	566.4	566.2	566.1	565.5
137.5°	598.9	599.7	600.4	601.2	602.0	602.5	603.0	603.3	603.8	604.1	603.5
140°	623.9	624.7	625.5	626.3	627.1	627.5	627.7	627.9	628.0	628.1	628.0
142.5°	646.8	647.6	648.4	649.2	650.0	650.5	650.8	651.0	651.3	651.6	651.4
145°	682.5	682.9	683.1	683.5	683.8	684.1	684.7	685.1	685.5	686.0	685.9
147.5°	713.8	714.3	714.9	715.4	716.0	716.5	716.9	717.4	717.8	718.3	718.3
150°	735.5	735.8	736.1	736.5	736.7	737.1	737.4	737.7	738.0	738.3	738.3
152.5°	753.4	753.8	754.2	754.7	755.1	755.5	755.6	755.8	756.0	756.2	756.4
155°	781.5	781.5	781.5	781.5	781.5	781.6	781.8	781.9	782.1	782.2	782.8
157.5°	805.5	805.3	805.1	804.9	804.8	804.8	804.9	805.0	805.1	805.2	805.9
160°	820.6	820.3	819.9	819.7	819.3	819.2	819.2	819.2	819.2	819.2	819.9
162.5°	833.9	833.6	833.1	832.7	832.2	832.1	832.2	832.3	832.4	832.6	833.3
165°	851.2	850.8	850.3	849.9	849.4	849.2	849.2	849.2	849.2	849.2	850.1
167.5°	865.0	864.4	863.8	863.2	862.6	862.4	862.5	862.6	862.7	862.8	863.8
170°	872.9	872.3	871.6	871.0	870.4	870.0	870.0	870.0	870.0	870.0	871.2
172.5°	879.0	878.4	877.8	877.2	876.6	876.2	876.2	876.2	876.2	876.2	877.2
175°	885.4	884.8	884.2	883.6	883.0	882.6	882.6	882.6	882.6	882.6	883.6
177.5°	888.1	887.6	887.1	886.5	886.1	885.8	885.8	885.8	885.8	885.8	886.5
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332025-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	24.5	24.4	24.3	24.3	24.3	24.4	24.5	24.6
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	27.7	28.3	28.7	28.9	28.7	28.5	28.4	28.2
95°	52.8	53.4	54.0	54.4	54.4	54.4	54.4	54.4
97.5°	82.1	82.8	83.6	83.9	83.8	83.8	83.7	83.6
100°	103.4	103.9	104.3	104.8	105.0	105.3	105.7	105.9
102.5°	128.0	128.4	128.9	129.1	129.0	128.9	128.9	128.9
105°	164.5	164.5	164.5	164.7	165.0	165.3	165.6	165.9
107.5°	204.1	204.6	205.2	205.3	205.1	204.9	204.7	204.6
110°	230.6	231.2	231.8	232.0	231.7	231.4	231.0	230.8



TEST NUMBER: P332025-940

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.1	257.8	258.6	258.9	258.9	258.8	258.7	258.7
115°	297.3	297.5	297.7	297.7	297.5	297.3	297.1	297.0
117.5°	338.0	337.9	337.9	337.6	337.2	336.8	336.4	335.9
120°	365.0	364.9	364.7	364.4	364.2	363.8	363.6	363.2
122.5°	392.4	392.0	391.6	391.2	390.7	390.3	389.9	389.4
125°	433.1	432.5	431.9	431.2	430.6	430.0	429.4	428.7
127.5°	473.3	472.4	471.6	470.8	470.1	469.4	468.7	468.0
130°	500.1	499.4	498.8	497.9	496.9	495.8	494.7	493.6
132.5°	526.0	525.2	524.5	523.7	522.9	522.0	521.2	520.4
135°	564.9	564.3	563.7	563.2	562.8	562.6	562.2	562.0
137.5°	602.9	602.3	601.5	600.9	600.4	599.8	599.2	598.6
140°	627.9	627.7	627.5	627.0	625.8	624.7	623.7	622.6
142.5°	651.3	651.1	650.9	650.5	649.6	648.8	647.9	647.1
145°	685.7	685.5	685.4	685.0	684.4	683.8	683.1	682.5
147.5°	718.3	718.3	718.3	717.7	716.8	715.9	715.0	714.1
150°	738.3	738.3	738.3	737.9	736.9	736.0	735.0	734.1
152.5°	756.6	756.9	757.2	756.9	756.1	755.3	754.5	753.7
155°	783.5	784.1	784.7	784.4	783.4	782.3	781.2	780.2
157.5°	806.6	807.2	807.8	807.7	806.9	806.0	805.1	804.2
160°	820.7	821.5	822.2	822.3	821.7	821.1	820.5	819.8
162.5°	834.1	834.9	835.7	835.5	834.6	833.6	832.6	831.6
165°	851.0	851.9	852.9	852.8	851.8	850.6	849.5	848.5
167.5°	864.8	865.7	866.7	866.7	865.7	864.8	863.8	862.8
170°	872.3	873.3	874.4	874.4	873.3	872.3	871.2	870.0
172.5°	878.2	879.1	880.0	880.0	878.9	877.8	876.7	875.7
175°	884.5	885.4	886.4	886.3	885.2	884.1	883.0	881.9
177.5°	887.3	888.1	888.8	888.8	887.9	887.0	886.2	885.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5

(END OF REPORT)