

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831176

Luminaire Tested: S123DIP-S1000D805U940-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831176
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U940-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6703.5 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61		
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53		
2	92	85	79	74	86	80	75	71	71	67	63	62	59	56	53	51	49	45		
3	85	76	69	63	79	71	65	60	63	58	54	55	52	48	48	45	43	39		
4	78	68	60	54	73	64	57	52	57	51	47	50	46	42	44	40	38	35		
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	34	31		
6	67	55	47	41	63	52	45	40	47	41	36	41	37	33	36	33	30	27		
7	62	50	42	37	58	48	40	35	43	37	33	38	33	30	34	30	27	25		
8	58	46	38	33	54	44	37	32	39	34	29	35	30	27	31	28	25	23		
9	54	42	35	30	51	40	33	29	36	31	27	33	28	25	29	25	23	21		
10	51	39	32	27	48	37	31	26	34	28	25	30	26	23	27	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	27527	27527	27527	27527	27527
5°	34813	32857	27773	22382	20567
10°	35151	36214	27588	17841	15591
15°	26475	33623	27400	15109	13184
20°	18447	27207	27050	13213	11976
25°	14066	20923	26454	12156	11233
30°	12168	16623	25502	11409	10634
35°	11290	14034	24404	10868	10214
40°	10689	12590	22861	10354	10072
45°	10333	11651	20900	9954	10007
50°	10155	10910	18581	9589	9955
55°	9777	10367	16302	9242	9999
60°	9427	9784	14051	8917	9836
65°	8856	9233	12121	8568	9643
70°	8179	8535	10307	7994	9076
75°	7403	7648	8833	7428	8293
80°	6106	6695	6986	6471	6986
85°	4841	5422	5125	5496	5570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 23863 cd/sqm



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.8	3.6
10°-20°	601.5	9.0
20°-30°	712.2	10.6
30°-40°	716.1	10.7
40°-50°	657.0	9.8
50°-60°	542.2	8.1
60°-70°	383.6	5.7
70°-80°	204.8	3.1
80°-90°	53.9	0.8
90°-100°	186.9	2.8
100°-110°	547.1	8.2
110°-120°	534.3	8.0
120°-130°	425.5	6.3
130°-140°	335.7	5.0
140°-150°	250.4	3.7
150°-160°	174.6	2.6
160°-170°	102.6	1.5
170°-180°	33.4	0.5
0°-30°	1555.4	23.2
0°-40°	2271.5	33.9
0°-60°	3470.7	51.8
0°-90°	4112.9	61.4
90°-120°	1268.3	18.9
90°-150°	2280.0	34.0
90°-180°	2591.0	38.7
0°-180°	6703.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2557	2557	2557	2557	2557	
5°	3222	3041	2570	2071	1904	307
15°	2376	3017	2459	1356	1183	656
25°	1184	1762	2227	1024	946	559
35°	859	1068	1857	827	777	540
45°	679	765	1373	654	657	526
55°	521	552	869	492	533	466
65°	348	362	476	336	379	346
75°	178	184	212	179	199	187
85°	39	44	42	44	45	44
90°	20	17	1	17	20	13
95°	81	413	24	413	81	131
105°	887	560	81	560	887	885
115°	1078	429	143	429	1078	1052
125°	850	400	199	400	850	770
135°	690	395	233	395	690	535
145°	539	390	266	390	539	342
155°	447	377	302	377	447	208
165°	390	361	330	361	390	111
175°	351	346	344	346	351	34
180°	344	344	344	344	344	



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3
2.5°	2882.5	2879.5	2876.6	2861.7	2846.9	2839.8	2832.7	2811.3	2789.9	2766.2	2742.5
5°	3221.9	3230.2	3238.5	3229.0	3219.5	3190.5	3161.4	3122.8	3084.2	3040.9	2997.6
7.5°	3378.5	3383.3	3388.0	3382.1	3376.2	3368.5	3360.7	3326.3	3291.9	3247.4	3202.9
10°	3216.0	3226.6	3237.3	3260.5	3283.6	3309.7	3335.8	3331.1	3326.3	3313.3	3300.2
12.5°	2858.8	2871.8	2884.9	2931.2	2977.4	3036.8	3096.1	3147.1	3198.2	3233.8	3269.4
15°	2375.8	2412.0	2448.2	2490.3	2532.4	2619.6	2706.9	2814.3	2921.7	3017.2	3112.7
17.5°	1956.9	1970.5	1984.2	2029.3	2074.4	2184.1	2293.9	2417.9	2541.9	2700.3	2858.8
20°	1610.4	1622.8	1635.3	1694.6	1753.9	1840.0	1926.0	2065.5	2204.9	2375.2	2545.5
22.5°	1352.8	1372.4	1392.0	1425.2	1458.5	1540.9	1623.4	1747.4	1871.4	2059.5	2247.6
25°	1184.3	1198.6	1212.8	1233.0	1253.2	1319.0	1384.9	1486.9	1589.0	1761.7	1934.3
27.5°	1069.2	1075.2	1081.1	1101.3	1121.4	1164.2	1206.9	1294.7	1382.5	1529.1	1675.6
30°	979.0	983.2	987.3	1005.1	1022.9	1052.0	1081.1	1144.6	1208.1	1337.4	1466.8
32.5°	916.1	919.1	922.1	935.7	949.4	970.1	990.9	1037.2	1083.5	1190.3	1297.1
35°	859.2	861.0	862.7	872.8	882.9	898.3	913.8	948.8	983.8	1068.0	1152.3
37.5°	809.3	811.7	814.1	820.0	825.9	839.6	853.2	881.1	909.0	973.7	1038.4
40°	760.7	764.8	769.0	773.1	777.3	788.6	799.8	821.2	842.6	896.0	949.4
42.5°	719.1	723.3	727.4	729.2	731.0	737.5	744.1	763.6	783.2	823.0	862.7
45°	678.8	680.6	682.4	684.1	685.9	691.3	696.6	713.8	731.0	765.4	799.8
47.5°	642.0	642.0	642.0	643.2	644.4	649.1	653.9	666.3	678.8	705.5	732.2
50°	606.4	606.4	606.4	604.6	602.8	605.8	608.8	618.3	627.8	651.5	675.2
52.5°	563.7	563.7	563.7	564.3	564.9	564.9	564.9	573.2	581.5	602.8	624.2
55°	521.0	523.3	525.7	523.9	522.1	523.3	524.5	529.9	535.2	552.4	569.6
57.5°	478.2	479.4	480.6	480.0	479.4	480.0	480.6	485.4	490.1	503.2	516.2
60°	437.9	437.9	437.9	436.7	435.5	436.7	437.9	440.3	442.6	454.5	466.4
62.5°	392.8	393.4	394.0	394.6	395.2	394.0	392.8	395.8	398.7	407.6	416.5
65°	347.7	348.3	348.9	350.7	352.5	351.3	350.1	353.0	356.0	362.5	369.1
67.5°	307.4	306.2	305.0	305.6	306.2	307.9	309.7	310.3	310.9	318.0	325.2
70°	259.9	261.1	262.3	261.7	261.1	261.7	262.3	264.0	265.8	271.2	276.5
72.5°	217.2	217.8	218.4	218.4	218.4	219.5	220.7	222.5	224.3	227.3	230.2
75°	178.0	178.0	178.0	179.2	180.4	181.0	181.6	181.6	181.6	183.9	186.3
77.5°	135.3	138.3	141.2	140.6	140.0	141.2	142.4	144.2	146.0	147.2	148.3
80°	98.5	98.5	98.5	99.1	99.7	101.5	103.2	104.4	105.6	108.0	110.4
82.5°	62.9	63.5	64.1	65.9	67.6	68.8	70.0	71.8	73.6	73.6	73.6
85°	39.2	38.0	36.8	38.0	39.2	40.3	41.5	42.1	42.7	43.9	45.1
87.5°	19.0	19.0	19.0	19.0	19.0	19.6	20.2	20.2	20.2	20.2	20.2
90°	20.2	20.9	20.2	19.5	20.2	18.8	18.1	17.4	16.7	17.4	15.3
92.5°	36.9	38.3	37.6	40.4	41.8	46.7	53.7	69.0	96.9	129.7	143.6
95°	80.9	83.7	88.5	94.8	108.1	133.2	170.1	251.0	335.3	413.4	368.1
97.5°	165.9	173.6	190.3	216.8	263.5	343.0	435.0	576.5	657.4	635.8	474.8
100°	437.1	436.4	463.6	514.5	584.9	683.9	765.5	821.9	797.5	660.2	446.2
102.5°	692.3	712.5	734.1	771.8	822.6	876.3	915.4	903.5	804.5	614.9	404.4
105°	886.8	890.3	912.6	939.1	971.1	989.3	976.0	906.3	760.6	560.5	371.6
107.5°	1013.7	1021.3	1030.4	1042.9	1047.1	1028.3	973.9	864.5	697.9	512.4	347.9
110°	1086.2	1087.6	1089.0	1083.4	1063.9	1015.1	927.2	798.9	639.3	472.7	335.3



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1100.8	1100.1	1093.1	1072.9	1033.2	967.0	865.9	734.1	588.4	446.2	328.4
115°	1078.5	1075.0	1061.1	1030.4	978.1	902.1	799.6	678.3	549.4	428.8	327.7
117.5°	1029.7	1024.8	1003.9	969.7	915.4	836.6	742.5	635.1	523.6	416.9	328.4
120°	965.6	961.4	944.6	905.6	850.5	780.1	696.5	602.3	504.0	409.2	331.1
122.5°	905.6	900.0	881.2	847.0	799.6	735.5	659.5	576.5	488.0	404.4	336.0
125°	850.5	845.7	828.2	797.5	752.9	697.2	630.2	554.2	474.8	400.2	340.9
127.5°	803.1	798.9	782.9	756.4	716.0	664.4	603.0	534.0	462.2	398.1	346.5
130°	764.1	758.5	743.9	718.8	681.8	634.4	577.9	515.2	452.5	396.0	352.1
132.5°	725.7	722.3	709.7	684.6	650.4	605.8	554.2	497.8	443.4	395.3	356.2
135°	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4	435.7	394.6	360.4
137.5°	651.1	647.0	636.5	614.9	585.6	550.1	509.6	467.8	428.8	393.2	363.2
140°	610.7	611.4	600.3	580.7	554.2	524.3	490.8	455.2	422.5	392.5	366.0
142.5°	573.1	573.8	564.0	547.3	525.7	500.6	472.7	443.4	416.9	391.1	368.1
145°	538.9	537.5	531.9	517.3	499.9	479.6	457.3	434.3	412.0	389.7	368.8
147.5°	509.6	508.9	503.3	492.9	478.9	464.3	445.5	426.7	407.1	387.6	368.8
150°	484.5	484.5	480.3	472.7	462.2	449.0	434.3	418.3	402.3	384.8	368.8
152.5°	463.6	463.6	461.5	454.5	446.9	436.4	423.9	410.6	396.7	381.3	366.7
155°	446.9	446.2	444.8	439.2	432.9	424.6	414.1	403.0	391.1	377.2	365.3
157.5°	430.8	430.8	429.4	425.3	419.7	412.7	404.4	394.6	384.8	373.7	363.2
160°	415.5	416.2	416.2	412.0	407.1	402.3	395.3	387.6	378.6	369.5	361.8
162.5°	401.6	402.3	402.3	398.8	396.0	391.8	385.5	379.3	372.3	365.3	359.0
165°	389.7	389.7	390.4	387.6	384.8	381.3	376.5	372.3	366.7	361.1	356.2
167.5°	377.9	377.9	378.6	376.5	375.1	372.3	369.5	366.0	361.1	356.9	353.5
170°	367.4	367.4	368.1	366.7	366.0	364.6	361.8	359.7	356.2	352.8	350.7
172.5°	357.6	358.3	359.7	358.3	358.3	357.6	355.6	354.2	351.4	349.3	348.6
175°	350.7	351.4	352.1	351.4	351.4	351.4	350.0	349.3	347.9	346.5	346.5
177.5°	345.8	345.8	347.2	346.5	347.2	347.2	346.5	345.8	345.1	344.4	345.1
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3
2.5°	2735.4	2728.2	2702.1	2676.0	2646.3	2616.7	2594.7	2572.8	2540.1	2507.5	2480.8
5°	2964.4	2931.2	2876.0	2820.8	2746.0	2671.3	2620.8	2570.4	2502.8	2435.1	2381.1
7.5°	3146.0	3089.0	3011.9	2934.7	2836.8	2738.9	2646.3	2553.8	2450.5	2347.3	2263.0
10°	3261.7	3223.1	3134.1	3045.1	2914.0	2782.8	2653.5	2524.1	2391.2	2258.3	2146.7
12.5°	3272.9	3276.5	3194.6	3112.7	2964.4	2816.0	2658.8	2501.6	2334.2	2166.9	2037.0
15°	3173.8	3235.0	3189.9	3144.8	2995.2	2845.7	2652.3	2458.8	2266.0	2073.2	1923.1
17.5°	2989.9	3121.0	3127.6	3134.1	2984.6	2835.0	2620.8	2406.6	2188.3	1969.9	1812.1
20°	2738.9	2932.3	2998.8	3065.3	2943.6	2822.0	2591.8	2361.5	2117.1	1872.6	1707.1
22.5°	2482.6	2717.6	2839.2	2960.8	2870.6	2780.4	2535.4	2290.3	2032.2	1774.1	1606.2
25°	2190.7	2447.0	2633.9	2820.8	2765.6	2710.4	2468.9	2227.4	1952.7	1678.0	1506.5
27.5°	1936.1	2196.6	2422.1	2647.5	2635.7	2623.8	2384.1	2144.4	1863.1	1581.9	1416.3
30°	1709.4	1952.1	2204.3	2456.5	2485.6	2514.6	2283.2	2051.8	1770.0	1488.1	1328.5
32.5°	1508.9	1720.7	1991.3	2261.9	2318.8	2375.8	2166.9	1958.1	1679.2	1400.3	1246.6
35°	1344.5	1536.8	1807.3	2077.9	2149.1	2220.3	2038.8	1857.2	1585.4	1313.7	1167.1
37.5°	1199.2	1360.0	1624.0	1888.0	1975.3	2062.5	1899.9	1737.3	1482.8	1228.2	1093.5
40°	1078.7	1208.1	1450.7	1693.4	1794.3	1895.2	1761.1	1627.0	1385.5	1144.0	1020.0
42.5°	977.8	1093.0	1313.1	1533.2	1629.9	1726.7	1613.3	1500.0	1285.2	1070.4	957.1
45°	891.8	983.8	1183.7	1383.7	1475.7	1567.6	1470.3	1373.0	1183.7	994.5	888.8
47.5°	811.1	890.0	1060.9	1231.8	1313.7	1395.6	1319.6	1243.7	1083.5	923.3	827.7
50°	738.7	802.2	951.7	1101.3	1172.5	1243.7	1176.6	1109.6	977.8	846.1	763.1
52.5°	675.8	727.4	852.6	977.8	1039.0	1100.1	1042.5	985.0	880.5	776.1	703.7
55°	613.5	657.4	766.0	874.6	916.1	957.7	913.2	868.7	784.4	700.2	639.0
57.5°	555.4	594.5	683.5	772.5	804.6	836.6	796.3	755.9	692.4	629.0	577.9
60°	498.4	530.5	604.6	678.8	698.4	718.0	685.3	652.7	608.2	563.7	518.0
62.5°	445.6	474.7	529.9	585.0	598.1	611.2	586.2	561.3	527.5	493.7	458.1
65°	391.0	413.0	458.1	503.2	511.5	519.8	497.8	475.9	450.4	424.8	398.7
67.5°	340.6	356.0	392.8	429.6	430.2	430.8	413.0	395.2	380.9	366.7	345.9
70°	291.3	306.2	330.5	354.8	355.4	356.0	341.8	327.5	316.8	306.2	290.7
72.5°	240.9	251.6	270.0	288.4	287.2	286.0	277.1	268.2	259.9	251.6	240.3
75°	195.2	204.1	216.6	229.0	225.5	221.9	217.2	212.4	205.3	198.2	191.1
77.5°	153.7	159.0	166.1	173.3	170.9	168.5	164.4	160.2	154.9	149.5	146.6
80°	112.7	115.1	119.9	124.6	123.4	122.2	117.5	112.7	111.6	110.4	106.2
82.5°	76.5	79.5	80.7	81.9	81.3	80.7	77.1	73.6	72.4	71.2	70.6
85°	45.7	46.3	46.9	47.5	45.7	43.9	42.7	41.5	41.5	41.5	40.9
87.5°	20.8	21.4	21.4	21.4	20.8	20.2	19.0	17.8	18.4	19.0	19.0
90°	13.2	11.2	9.1	7.7	6.3	4.2	2.8	1.4	2.8	4.2	6.3
92.5°	107.4	70.4	48.1	35.6	28.6	22.3	15.3	10.5	15.3	22.3	28.6
95°	253.8	149.9	90.6	63.4	45.3	33.5	25.8	23.7	25.8	33.5	45.3
97.5°	282.3	161.7	103.2	73.2	55.1	44.6	38.3	37.6	38.3	44.6	55.1
100°	262.8	159.6	110.8	83.7	66.9	57.2	52.3	51.6	52.3	57.2	66.9
102.5°	246.1	162.4	119.9	95.5	80.9	71.8	67.6	66.2	67.6	71.8	80.9
105°	239.8	168.0	130.4	108.8	95.5	87.1	83.0	80.9	83.0	87.1	95.5
107.5°	238.4	177.1	143.6	123.4	110.8	102.5	98.3	96.2	98.3	102.5	110.8
110°	241.9	188.9	157.6	138.0	126.2	118.5	115.0	112.9	115.0	118.5	126.2



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	248.9	200.8	172.2	153.4	141.5	133.9	130.4	128.3	130.4	133.9	141.5
115°	256.6	214.0	187.5	168.7	156.9	149.9	145.7	142.9	145.7	149.9	156.9
117.5°	266.3	228.0	201.5	184.0	170.8	164.5	161.0	157.6	161.0	164.5	170.8
120°	277.5	241.2	216.1	198.7	185.4	178.5	175.0	172.9	175.0	178.5	185.4
122.5°	287.9	255.2	230.8	211.9	199.4	191.7	188.2	186.1	188.2	191.7	199.4
125°	299.1	268.4	244.0	225.2	211.9	204.3	200.1	198.7	200.1	204.3	211.9
127.5°	308.1	280.3	256.6	237.7	223.1	215.4	210.5	208.4	210.5	215.4	223.1
130°	317.2	290.7	267.7	248.9	234.2	225.9	219.6	217.5	219.6	225.9	234.2
132.5°	325.6	299.8	277.5	259.3	244.7	234.2	227.3	224.5	227.3	234.2	244.7
135°	332.5	308.8	287.2	268.4	253.8	243.3	235.6	232.9	235.6	243.3	253.8
137.5°	338.1	315.1	294.2	276.8	262.1	251.0	243.3	240.5	243.3	251.0	262.1
140°	342.3	321.4	301.2	283.7	269.8	258.6	251.7	248.2	251.7	258.6	269.8
142.5°	346.5	326.3	306.7	290.7	276.8	267.0	259.3	256.6	259.3	267.0	276.8
145°	349.3	330.5	312.3	296.3	284.4	274.0	267.7	265.6	267.7	274.0	284.4
147.5°	351.4	333.9	317.2	303.3	291.4	282.3	276.1	274.7	276.1	282.3	291.4
150°	352.1	337.4	321.4	308.8	299.1	290.0	284.4	283.7	284.4	290.0	299.1
152.5°	353.5	339.5	326.3	314.4	306.1	298.4	292.8	292.8	292.8	298.4	306.1
155°	353.5	342.3	330.5	320.7	313.0	306.1	301.9	301.9	301.9	306.1	313.0
157.5°	354.2	343.7	333.9	326.3	319.3	313.0	309.5	308.8	309.5	313.0	319.3
160°	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2	317.2	320.0	325.6
162.5°	353.5	346.5	339.5	333.9	329.8	325.6	323.5	323.5	323.5	325.6	329.8
165°	352.1	347.2	341.6	336.7	333.9	330.5	329.1	329.8	329.1	330.5	333.9
167.5°	351.4	347.2	343.0	339.5	337.4	334.6	333.9	334.6	333.9	334.6	337.4
170°	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.8	337.4	338.1	340.2
172.5°	348.6	346.5	343.7	343.0	342.3	340.9	340.9	341.6	340.9	340.9	342.3
175°	347.2	345.8	344.4	343.7	343.7	342.3	343.0	343.7	343.0	342.3	343.7
177.5°	346.5	345.1	344.4	344.4	344.4	343.7	344.4	345.1	344.4	343.7	344.4
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3	2557.3
2.5°	2454.1	2431.0	2407.8	2390.0	2372.2	2342.0	2311.7	2304.6	2297.5	2287.4	2277.3
5°	2327.1	2270.2	2213.2	2162.2	2111.1	2071.4	2031.6	2005.5	1979.4	1960.4	1941.4
7.5°	2178.8	2093.3	2007.9	1947.4	1886.9	1829.3	1771.7	1753.4	1735.0	1710.0	1685.1
10°	2035.2	1940.9	1846.5	1767.6	1688.7	1632.3	1575.9	1553.4	1530.8	1499.4	1468.0
12.5°	1907.0	1803.8	1700.5	1621.0	1541.5	1486.9	1432.4	1399.7	1367.1	1349.3	1331.5
15°	1772.9	1662.6	1552.2	1478.6	1405.1	1355.8	1306.6	1278.1	1249.6	1232.4	1215.2
17.5°	1654.3	1545.1	1435.9	1365.3	1294.7	1249.6	1204.5	1179.6	1154.7	1141.6	1128.6
20°	1541.5	1434.7	1327.9	1259.1	1190.3	1153.5	1116.7	1100.7	1084.6	1074.0	1063.3
22.5°	1438.3	1333.3	1228.2	1169.5	1110.8	1081.1	1051.4	1040.1	1028.9	1020.0	1011.1
25°	1335.0	1241.3	1147.5	1097.7	1047.9	1023.5	999.2	987.9	976.7	967.8	958.9
27.5°	1250.8	1161.2	1071.6	1028.9	986.2	967.2	948.2	939.3	930.4	922.1	913.8
30°	1168.9	1088.8	1008.7	971.9	935.1	917.9	900.7	891.8	882.9	875.2	867.5
32.5°	1093.0	1024.1	955.3	921.5	887.7	873.4	859.2	848.5	837.8	831.9	825.9
35°	1020.6	958.9	897.1	869.3	841.4	827.1	812.9	804.0	795.1	790.3	785.6
37.5°	958.9	903.7	848.5	821.8	795.1	781.4	767.8	760.1	752.4	750.6	748.8
40°	896.0	848.5	801.0	774.9	748.8	736.9	725.1	720.3	715.6	714.4	713.2
42.5°	843.7	797.5	751.2	727.4	703.7	693.6	683.5	681.2	678.8	680.6	682.4
45°	783.2	744.7	706.1	684.1	662.2	653.9	645.6	643.8	642.0	645.6	649.1
47.5°	732.2	696.6	661.0	640.2	619.5	613.5	607.6	607.0	606.4	611.2	615.9
50°	680.0	645.6	611.2	594.5	577.9	572.6	567.2	569.0	570.8	578.5	586.2
52.5°	631.3	599.3	567.2	551.8	536.4	532.8	529.3	533.4	537.6	545.9	554.2
55°	577.9	548.9	519.8	507.9	496.0	492.5	488.9	497.2	505.5	513.2	521.0
57.5°	526.9	501.4	475.9	465.2	454.5	453.9	453.3	461.0	468.7	477.1	485.4
60°	472.3	450.9	429.6	421.3	413.0	414.2	415.3	424.2	433.1	439.7	446.2
62.5°	422.5	404.7	386.9	379.2	371.4	374.4	377.4	386.3	395.2	402.9	410.6
65°	372.6	357.8	343.0	337.6	332.3	336.4	340.6	348.3	356.0	361.4	366.7
67.5°	325.2	312.7	300.2	296.1	291.9	296.1	300.2	307.9	315.7	321.0	326.3
70°	275.3	265.2	255.1	252.2	249.2	254.0	258.7	265.2	271.8	277.1	282.4
72.5°	229.0	221.3	213.6	213.0	212.4	216.6	220.7	227.3	233.8	237.3	240.9
75°	183.9	179.8	175.6	175.0	174.4	178.6	182.8	186.3	189.9	192.8	195.8
77.5°	143.6	140.0	136.5	137.1	137.7	140.6	143.6	147.2	150.7	152.5	154.3
80°	102.1	100.9	99.7	100.9	102.1	104.4	106.8	109.2	111.6	112.7	113.9
82.5°	70.0	68.8	67.6	69.4	71.2	73.0	74.8	76.5	78.3	78.9	79.5
85°	40.3	42.1	43.9	43.9	43.9	44.5	45.1	45.7	46.3	45.7	45.1
87.5°	19.0	19.6	20.2	20.2	20.2	20.8	21.4	21.4	21.4	20.8	20.2
90°	7.7	9.1	11.2	13.2	15.3	17.4	16.7	17.4	18.1	18.8	20.2
92.5°	35.6	48.1	70.4	107.4	143.6	129.7	96.9	69.0	53.7	46.7	41.8
95°	63.4	90.6	149.9	253.8	368.1	413.4	335.3	251.0	170.1	133.2	108.1
97.5°	73.2	103.2	161.7	282.3	474.8	635.8	657.4	576.5	435.0	343.0	263.5
100°	83.7	110.8	159.6	262.8	446.2	660.2	797.5	821.9	765.5	683.9	584.9
102.5°	95.5	119.9	162.4	246.1	404.4	614.9	804.5	903.5	915.4	876.3	822.6
105°	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3	976.0	989.3	971.1
107.5°	123.4	143.6	177.1	238.4	347.9	512.4	697.9	864.5	973.9	1028.3	1047.1
110°	138.0	157.6	188.9	241.9	335.3	472.7	639.3	798.9	927.2	1015.1	1063.9



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	153.4	172.2	200.8	248.9	328.4	446.2	588.4	734.1	865.9	967.0	1033.2
115°	168.7	187.5	214.0	256.6	327.7	428.8	549.4	678.3	799.6	902.1	978.1
117.5°	184.0	201.5	228.0	266.3	328.4	416.9	523.6	635.1	742.5	836.6	915.4
120°	198.7	216.1	241.2	277.5	331.1	409.2	504.0	602.3	696.5	780.1	850.5
122.5°	211.9	230.8	255.2	287.9	336.0	404.4	488.0	576.5	659.5	735.5	799.6
125°	225.2	244.0	268.4	299.1	340.9	400.2	474.8	554.2	630.2	697.2	752.9
127.5°	237.7	256.6	280.3	308.1	346.5	398.1	462.2	534.0	603.0	664.4	716.0
130°	248.9	267.7	290.7	317.2	352.1	396.0	452.5	515.2	577.9	634.4	681.8
132.5°	259.3	277.5	299.8	325.6	356.2	395.3	443.4	497.8	554.2	605.8	650.4
135°	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4	531.9	577.2	617.0
137.5°	276.8	294.2	315.1	338.1	363.2	393.2	428.8	467.8	509.6	550.1	585.6
140°	283.7	301.2	321.4	342.3	366.0	392.5	422.5	455.2	490.8	524.3	554.2
142.5°	290.7	306.7	326.3	346.5	368.1	391.1	416.9	443.4	472.7	500.6	525.7
145°	296.3	312.3	330.5	349.3	368.8	389.7	412.0	434.3	457.3	479.6	499.9
147.5°	303.3	317.2	333.9	351.4	368.8	387.6	407.1	426.7	445.5	464.3	478.9
150°	308.8	321.4	337.4	352.1	368.8	384.8	402.3	418.3	434.3	449.0	462.2
152.5°	314.4	326.3	339.5	353.5	366.7	381.3	396.7	410.6	423.9	436.4	446.9
155°	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0	414.1	424.6	432.9
157.5°	326.3	333.9	343.7	354.2	363.2	373.7	384.8	394.6	404.4	412.7	419.7
160°	330.5	337.4	345.8	354.2	361.8	369.5	378.6	387.6	395.3	402.3	407.1
162.5°	333.9	339.5	346.5	353.5	359.0	365.3	372.3	379.3	385.5	391.8	396.0
165°	336.7	341.6	347.2	352.1	356.2	361.1	366.7	372.3	376.5	381.3	384.8
167.5°	339.5	343.0	347.2	351.4	353.5	356.9	361.1	366.0	369.5	372.3	375.1
170°	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7	361.8	364.6	366.0
172.5°	343.0	343.7	346.5	348.6	348.6	349.3	351.4	354.2	355.6	357.6	358.3
175°	343.7	344.4	345.8	347.2	346.5	346.5	347.9	349.3	350.0	351.4	351.4
177.5°	344.4	344.4	345.1	346.5	345.1	344.4	345.1	345.8	346.5	347.2	347.2
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2557.3	2557.3	2557.3	2557.3
2.5°	2273.1	2269.0	2252.4	2235.7
5°	1927.2	1913.0	1908.2	1903.5
7.5°	1683.9	1682.7	1657.8	1632.9
10°	1469.7	1471.5	1449.0	1426.4
12.5°	1316.6	1301.8	1300.0	1298.3
15°	1201.5	1187.9	1185.5	1183.1
17.5°	1120.2	1111.9	1109.6	1107.2
20°	1058.5	1053.8	1049.6	1045.5
22.5°	1005.1	999.2	995.6	992.1
25°	953.5	948.2	947.0	945.8
27.5°	907.2	900.7	900.7	900.7
30°	863.3	859.2	857.4	855.6
32.5°	822.4	818.8	818.8	818.8
35°	783.8	782.0	779.7	777.3
37.5°	748.8	748.8	747.6	746.4
40°	715.0	716.8	716.8	716.8
42.5°	684.1	685.9	685.9	685.9
45°	652.1	655.1	656.2	657.4
47.5°	620.6	625.4	626.6	627.8
50°	589.8	593.4	593.9	594.5
52.5°	558.3	562.5	565.5	568.4
55°	525.1	529.3	531.0	532.8
57.5°	489.5	493.7	494.3	494.9
60°	450.4	454.5	455.7	456.9
62.5°	413.0	415.3	416.5	417.7
65°	370.3	373.8	376.2	378.6
67.5°	329.3	332.3	332.3	332.3
70°	283.6	284.8	286.6	288.4
72.5°	241.5	242.1	242.1	242.1
75°	197.0	198.2	198.8	199.4
77.5°	154.9	155.5	155.5	155.5
80°	113.3	112.7	112.7	112.7
82.5°	77.7	75.9	75.9	75.9
85°	44.5	43.9	44.5	45.1
87.5°	20.2	20.2	20.2	20.2
90°	19.5	20.2	20.9	20.2
92.5°	40.4	37.6	38.3	36.9
95°	94.8	88.5	83.7	80.9
97.5°	216.8	190.3	173.6	165.9
100°	514.5	463.6	436.4	437.1
102.5°	771.8	734.1	712.5	692.3
105°	939.1	912.6	890.3	886.8
107.5°	1042.9	1030.4	1021.3	1013.7
110°	1083.4	1089.0	1087.6	1086.2



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1072.9	1093.1	1100.1	1100.8
115°	1030.4	1061.1	1075.0	1078.5
117.5°	969.7	1003.9	1024.8	1029.7
120°	905.6	944.6	961.4	965.6
122.5°	847.0	881.2	900.0	905.6
125°	797.5	828.2	845.7	850.5
127.5°	756.4	782.9	798.9	803.1
130°	718.8	743.9	758.5	764.1
132.5°	684.6	709.7	722.3	725.7
135°	651.1	672.1	684.6	689.5
137.5°	614.9	636.5	647.0	651.1
140°	580.7	600.3	611.4	610.7
142.5°	547.3	564.0	573.8	573.1
145°	517.3	531.9	537.5	538.9
147.5°	492.9	503.3	508.9	509.6
150°	472.7	480.3	484.5	484.5
152.5°	454.5	461.5	463.6	463.6
155°	439.2	444.8	446.2	446.9
157.5°	425.3	429.4	430.8	430.8
160°	412.0	416.2	416.2	415.5
162.5°	398.8	402.3	402.3	401.6
165°	387.6	390.4	389.7	389.7
167.5°	376.5	378.6	377.9	377.9
170°	366.7	368.1	367.4	367.4
172.5°	358.3	359.7	358.3	357.6
175°	351.4	352.1	351.4	350.7
177.5°	346.5	347.2	345.8	345.8
180°	344.4	344.4	344.4	344.4



TEST NUMBER: P831176

CATALOG NUMBER: S123DIP-S1000D805U940-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.09	17.01	16.95	17.89	18.99	18.32	19.25	19.18	20.13	21.23
	3H	17.74	18.57	18.61	19.45	20.58	19.75	20.58	20.63	21.47	22.60
	4H	18.32	19.10	19.21	19.99	21.13	20.21	20.99	21.10	21.88	23.02
	6H	18.69	19.41	19.59	20.31	21.47	20.48	21.21	21.39	22.10	23.26
	8H	18.79	19.48	19.70	20.39	21.54	20.55	21.23	21.46	22.15	23.30
	12H	18.84	19.49	19.75	20.40	21.58	20.57	21.22	21.48	22.13	23.31
4H	2H	16.67	17.45	17.56	18.34	19.48	18.49	19.28	19.39	20.17	21.31
	3H	18.50	19.16	19.41	20.08	21.23	20.12	20.77	21.02	21.69	22.85
	4H	19.20	19.80	20.12	20.72	21.90	20.70	21.30	21.62	22.22	23.40
	6H	19.68	20.19	20.61	21.14	22.32	21.11	21.62	22.04	22.57	23.75
	8H	19.82	20.30	20.75	21.24	22.43	21.23	21.70	22.16	22.64	23.84
	12H	19.89	20.32	20.84	21.28	22.48	21.27	21.70	22.22	22.66	23.86
8H	4H	19.47	19.95	20.41	20.89	22.08	20.82	21.29	21.75	22.23	23.42
	6H	20.07	20.46	21.02	21.44	22.63	21.32	21.71	22.28	22.69	23.89
	8H	20.27	20.62	21.24	21.59	22.80	21.50	21.85	22.47	22.82	24.03
	12H	20.40	20.71	21.37	21.67	22.93	21.60	21.91	22.57	22.87	24.13
12H	4H	19.48	19.91	20.43	20.86	22.06	20.79	21.22	21.74	22.18	23.38
	6H	20.12	20.47	21.08	21.44	22.65	21.33	21.68	22.30	22.65	23.86
	8H	20.35	20.66	21.32	21.62	22.88	21.54	21.84	22.51	22.81	24.07