

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332523-927

Luminaire Tested: **S124DIP-S350D1035U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332523-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D1035U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4474.5 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332523-927

CATALOG NUMBER: S124DIP-S350D1035U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332523-927

CATALOG NUMBER: S124DIP-S350D1035U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	59	58	46	44	43	31	30	29	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332523-927

CATALOG NUMBER: S124DIP-S350D1035U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	1.0
10°-20°	124.2	2.8
20°-30°	182.8	4.1
30°-40°	212.5	4.7
40°-50°	212.5	4.7
50°-60°	185.9	4.2
60°-70°	138.0	3.1
70°-80°	78.4	1.8
80°-90°	25.7	0.6
90°-100°	36.2	0.8
100°-110°	230.6	5.2
110°-120°	441.1	9.9
120°-130°	559.9	12.5
130°-140°	599.1	13.4
140°-150°	560.2	12.5
150°-160°	451.8	10.1
160°-170°	291.4	6.5
170°-180°	100.4	2.2
0°-30°	351.0	7.8
0°-40°	563.5	12.6
0°-60°	961.8	21.5
0°-90°	1203.9	26.9
90°-120°	707.8	15.8
90°-150°	2427.0	54.2
90°-180°	3271.0	73.1
0°-180°	4474.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	2	11	17	22	24	3
95°	44	18	17	22	23	56
105°	238	243	247	252	225	249
115°	444	447	446	448	448	437
125°	625	628	626	629	630	558
135°	775	774	777	779	780	597
145°	894	896	896	897	898	558
155°	980	980	978	981	979	452
165°	1034	1030	1030	1035	1029	292
175°	1057	1053	1053	1060	1051	101
180°	1057	1057	1057	1057	1057	



TEST NUMBER: P332523-927

CATALOG NUMBER: S124DIP-S350D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.2	8.6	9.0	9.3	9.6	9.8	10.1	10.2	10.5	10.7	10.9
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	10.0	10.1	10.1	10.3	10.4	11.2	12.5	13.9	15.4	16.8	17.8
95°	43.5	37.5	31.5	25.6	19.6	16.7	16.9	17.0	17.2	17.4	18.5
97.5°	92.4	96.1	99.8	103.5	107.3	99.3	79.7	60.1	40.5	20.9	21.0
100°	129.7	132.8	136.0	139.2	142.4	131.8	107.6	83.3	59.0	34.8	31.8
102.5°	171.4	173.8	176.1	178.4	180.7	180.3	177.1	174.0	170.8	167.6	135.4
105°	238.1	239.1	240.1	241.2	242.2	243.2	244.1	244.9	245.9	246.8	248.3
107.5°	299.8	300.4	301.0	301.4	302.0	302.9	304.0	305.2	306.4	307.6	308.4
110°	341.7	342.1	342.7	343.2	343.7	344.5	345.5	346.7	347.7	348.7	349.1



TEST NUMBER: P332523-927

CATALOG NUMBER: S124DIP-S350D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.1	383.1	384.0	385.0	386.0	386.7	387.1	387.6	388.1	388.6	388.6
115°	444.4	445.0	445.5	446.0	446.6	446.7	446.6	446.4	446.2	446.0	446.4
117.5°	500.6	501.3	502.0	502.7	503.4	503.9	504.3	504.7	505.1	505.5	505.4
120°	538.5	539.2	540.0	540.7	541.4	541.6	541.5	541.3	541.1	540.9	541.3
122.5°	573.9	574.4	574.8	575.2	575.7	576.0	576.2	576.5	576.7	576.9	577.2
125°	624.7	625.4	626.1	626.9	627.6	627.7	627.4	627.0	626.7	626.3	626.9
127.5°	672.8	673.0	673.2	673.4	673.5	674.0	674.9	675.7	676.4	677.2	677.2
130°	703.9	704.0	704.2	704.3	704.5	704.9	705.4	705.9	706.5	707.0	707.2
132.5°	732.3	732.6	732.9	733.2	733.6	734.0	734.7	735.4	736.0	736.7	736.9
135°	775.0	774.8	774.7	774.4	774.3	774.5	775.2	775.9	776.7	777.4	777.7
137.5°	812.8	812.9	812.9	813.0	813.1	813.5	814.3	815.1	815.8	816.6	817.0
140°	837.5	837.8	838.2	838.5	838.8	839.2	839.6	840.0	840.3	840.7	841.1
142.5°	859.6	860.2	860.9	861.5	862.1	862.5	862.8	863.0	863.2	863.4	863.8
145°	893.6	894.1	894.7	895.2	895.7	896.0	896.0	896.0	896.0	896.0	896.2
147.5°	920.7	921.6	922.7	923.6	924.6	925.0	924.8	924.6	924.5	924.3	924.5
150°	940.2	941.0	941.7	942.4	943.1	943.3	943.2	943.0	942.9	942.6	942.6
152.5°	956.7	957.3	957.8	958.4	958.9	959.1	958.8	958.5	958.1	957.8	958.1
155°	979.9	980.0	980.2	980.3	980.5	980.3	979.9	979.3	978.7	978.3	978.9
157.5°	999.3	999.2	999.0	998.9	998.9	998.5	997.9	997.3	996.7	996.1	997.0
160°	1010.7	1010.1	1009.6	1009.1	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5
162.5°	1020.8	1020.1	1019.5	1018.7	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0
165°	1033.6	1032.7	1031.8	1030.9	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0
167.5°	1043.7	1042.8	1041.9	1041.0	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7
170°	1049.4	1048.4	1047.3	1046.2	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9
172.5°	1053.2	1052.2	1051.1	1050.0	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7
175°	1057.3	1056.3	1055.2	1054.2	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9
177.5°	1059.2	1058.2	1057.2	1056.3	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332523-927

CATALOG NUMBER: S124DIP-S350D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	11.1	11.3	11.5	11.6	11.7	11.8	11.9	12.0
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	18.9	20.0	21.0	21.5	21.6	21.7	21.8	21.9
95°	19.5	20.6	21.6	22.3	22.4	22.6	22.7	22.9
97.5°	21.1	21.2	21.3	21.5	21.6	21.8	21.9	22.2
100°	28.8	25.8	22.8	21.5	21.6	21.8	21.9	22.2
102.5°	103.2	71.0	38.7	22.7	22.7	22.7	22.7	22.8
105°	249.9	251.4	253.0	250.7	244.4	238.1	231.7	225.4
107.5°	309.2	310.0	310.7	311.4	312.1	312.8	313.5	314.1
110°	349.4	349.8	350.1	350.6	351.1	351.6	352.2	352.7



TEST NUMBER: P332523-927

CATALOG NUMBER: S124DIP-S350D1035U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	388.5	388.4	388.3	388.6	389.3	390.0	390.6	391.3
115°	446.7	447.1	447.4	447.6	447.6	447.6	447.6	447.6
117.5°	505.3	505.3	505.2	505.2	505.1	505.0	504.9	504.9
120°	541.6	541.9	542.3	542.3	541.9	541.6	541.3	540.9
122.5°	577.4	577.6	577.8	577.7	577.4	577.0	576.7	576.3
125°	627.4	627.9	628.4	628.8	629.0	629.2	629.3	629.5
127.5°	677.1	676.9	676.8	676.7	676.6	676.4	676.3	676.1
130°	707.3	707.5	707.7	707.8	707.8	707.8	707.8	707.8
132.5°	737.0	737.3	737.4	737.4	737.3	737.1	737.0	736.9
135°	778.1	778.4	778.8	779.1	779.5	779.8	780.1	780.5
137.5°	817.4	817.8	818.2	818.2	818.2	818.1	817.9	817.8
140°	841.7	842.2	842.7	843.1	843.3	843.4	843.6	843.8
142.5°	864.2	864.6	865.0	865.1	865.2	865.2	865.3	865.3
145°	896.4	896.5	896.7	897.0	897.3	897.6	898.0	898.3
147.5°	924.6	924.7	924.9	925.0	925.2	925.3	925.6	925.7
150°	942.6	942.6	942.6	942.7	942.9	943.1	943.3	943.4
152.5°	958.4	958.7	958.9	959.0	958.9	958.9	958.7	958.6
155°	979.6	980.3	981.0	981.1	980.6	980.1	979.5	979.1
157.5°	997.9	998.9	999.7	999.7	998.9	997.9	997.0	996.1
160°	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5
162.5°	1019.1	1020.2	1021.2	1021.1	1019.9	1018.7	1017.6	1016.4
165°	1032.5	1033.9	1035.2	1035.1	1033.6	1032.0	1030.4	1028.8
167.5°	1042.2	1043.8	1045.3	1045.2	1043.5	1041.7	1039.9	1038.2
170°	1048.3	1049.6	1051.1	1050.9	1049.2	1047.4	1045.6	1043.9
172.5°	1052.1	1053.4	1054.9	1054.6	1052.7	1050.8	1048.9	1047.0
175°	1056.5	1058.1	1059.7	1059.4	1057.3	1055.2	1053.1	1051.0
177.5°	1058.3	1059.4	1060.6	1060.3	1058.6	1056.9	1055.2	1053.5
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3

(END OF REPORT)