

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831256

Luminaire Tested: S123DIP-S1165D365U940-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831256
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U940-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5860.3 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	110	110	110	110	101	101	101	92	92	92	85	85	85	81				
1	106	101	98	94	101	97	94	91	90	87	85	83	81	79	76	75	73	70				
2	97	90	84	79	93	86	81	76	80	75	72	74	70	67	68	65	63	60				
3	89	80	73	67	85	77	70	65	71	66	61	66	62	58	61	58	55	52				
4	82	72	64	58	79	69	62	56	64	58	54	60	55	51	56	52	48	46				
5	76	65	56	51	73	62	55	49	58	52	47	54	49	45	51	46	43	40				
6	71	59	51	45	68	57	49	44	53	47	42	50	44	40	47	42	39	36				
7	66	54	46	40	63	52	45	39	49	42	38	46	40	36	43	38	35	33				
8	62	49	42	36	59	48	41	36	45	39	34	42	37	33	40	35	32	30				
9	58	46	38	33	56	44	37	32	42	36	31	39	34	30	37	33	29	27				
10	54	42	35	30	52	41	34	30	39	33	29	37	32	28	35	30	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	31792	31792	31792	31792	31792
5°	40207	37948	32076	25849	23754
10°	40596	41825	31863	20605	18006
15°	30577	38832	31646	17450	15228
20°	21305	31423	31242	15260	13832
25°	16245	24164	30553	14039	12973
30°	14054	19198	29453	13176	12282
35°	13039	16209	28185	12553	11796
40°	12344	14540	26402	11959	11632
45°	11934	13457	24138	11496	11558
50°	11729	12599	21460	11074	11499
55°	11292	11973	18828	10674	11549
60°	10887	11300	16228	10297	11360
65°	10229	10664	13998	9897	11135
70°	9448	9857	11906	9231	10480
75°	8551	8833	10202	8580	9578
80°	7054	7730	8071	7476	8071
85°	5582	6262	5928	6348	6434

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 27560 cd/sqm



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.2	4.8
10°-20°	694.7	11.9
20°-30°	822.5	14.0
30°-40°	827.0	14.1
40°-50°	758.8	12.9
50°-60°	626.3	10.7
60°-70°	443.0	7.6
70°-80°	236.5	4.0
80°-90°	60.9	1.0
90°-100°	25.8	0.4
100°-110°	78.2	1.3
110°-120°	133.1	2.3
120°-130°	175.0	3.0
130°-140°	196.8	3.4
140°-150°	193.4	3.3
150°-160°	162.9	2.8
160°-170°	108.4	1.9
170°-180°	38.0	0.6
0°-30°	1796.4	30.7
0°-40°	2623.4	44.8
0°-60°	4008.4	68.4
0°-90°	4748.8	81.0
90°-120°	237.0	4.0
90°-150°	802.3	13.7
90°-180°	1112.0	19.0
0°-180°	5860.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2954	2954	2954	2954	2954	
5°	3721	3512	2969	2392	2198	355
15°	2744	3485	2840	1566	1366	758
25°	1368	2035	2572	1182	1092	646
35°	992	1234	2145	955	898	624
45°	784	884	1586	755	759	607
55°	602	638	1003	569	615	538
65°	402	419	550	389	437	399
75°	206	212	245	206	230	216
85°	45	51	48	51	52	50
90°	10	8	0	8	10	7
95°	25	23	19	23	25	25
105°	75	74	71	74	75	79
115°	134	134	134	134	134	133
125°	194	196	196	196	194	173
135°	254	256	254	256	254	195
145°	308	310	308	310	308	193
155°	353	354	353	354	353	162
165°	384	384	385	384	384	108
175°	399	399	400	399	399	38
180°	401	401	401	401	401	



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6
2.5°	3329.1	3325.7	3322.2	3305.1	3288.0	3279.8	3271.5	3246.9	3222.2	3194.8	3167.4
5°	3721.1	3730.7	3740.3	3729.3	3718.3	3684.8	3651.2	3606.6	3562.1	3512.1	3462.0
7.5°	3902.0	3907.5	3913.0	3906.1	3899.2	3890.3	3881.4	3841.7	3801.9	3750.5	3699.1
10°	3714.2	3726.6	3738.9	3765.6	3792.3	3822.5	3852.6	3847.2	3841.7	3826.6	3811.5
12.5°	3301.7	3316.8	3331.8	3385.3	3438.7	3507.3	3575.8	3634.7	3693.7	3734.8	3775.9
15°	2743.9	2785.7	2827.5	2876.1	2924.8	3025.5	3126.3	3250.3	3374.3	3484.7	3595.0
17.5°	2260.1	2275.8	2291.6	2343.7	2395.7	2522.5	2649.3	2792.5	2935.7	3118.7	3301.7
20°	1859.9	1874.2	1888.6	1957.2	2025.7	2125.1	2224.4	2385.5	2546.5	2743.2	2939.9
22.5°	1562.4	1585.1	1607.7	1646.0	1684.4	1779.7	1874.9	2018.2	2161.4	2378.6	2595.8
25°	1367.8	1384.3	1400.7	1424.0	1447.3	1523.4	1599.4	1717.3	1835.2	2034.6	2234.0
27.5°	1234.9	1241.7	1248.6	1271.9	1295.2	1344.5	1393.9	1495.3	1596.7	1766.0	1935.2
30°	1130.7	1135.5	1140.3	1160.9	1181.4	1215.0	1248.6	1321.9	1395.2	1544.6	1694.0
32.5°	1058.1	1061.5	1064.9	1080.7	1096.4	1120.4	1144.4	1197.9	1251.3	1374.7	1498.0
35°	992.3	994.3	996.4	1008.0	1019.7	1037.5	1055.3	1095.8	1136.2	1233.5	1330.8
37.5°	934.7	937.5	940.2	947.1	953.9	969.7	985.4	1017.6	1049.9	1124.5	1199.2
40°	878.5	883.3	888.1	892.9	897.7	910.7	923.8	948.4	973.1	1034.8	1096.4
42.5°	830.6	835.4	840.2	842.2	844.3	851.8	859.3	882.0	904.6	950.5	996.4
45°	784.0	786.0	788.1	790.1	792.2	798.4	804.5	824.4	844.3	884.0	923.8
47.5°	741.5	741.5	741.5	742.8	744.2	749.7	755.2	769.6	784.0	814.8	845.6
50°	700.4	700.4	700.4	698.3	696.2	699.7	703.1	714.1	725.0	752.4	779.8
52.5°	651.0	651.0	651.0	651.7	652.4	652.4	652.4	662.0	671.6	696.2	720.9
55°	601.7	604.4	607.2	605.1	603.0	604.4	605.8	612.0	618.1	638.0	657.9
57.5°	552.3	553.7	555.1	554.4	553.7	554.4	555.1	560.6	566.0	581.1	596.2
60°	505.7	505.7	505.7	504.4	503.0	504.4	505.7	508.5	511.2	524.9	538.6
62.5°	453.7	454.3	455.0	455.7	456.4	455.0	453.7	457.1	460.5	470.8	481.1
65°	401.6	402.3	402.9	405.0	407.1	405.7	404.3	407.7	411.2	418.7	426.2
67.5°	355.0	353.6	352.2	352.9	353.6	355.7	357.7	358.4	359.1	367.3	375.5
70°	300.2	301.5	302.9	302.2	301.5	302.2	302.9	305.0	307.0	313.2	319.3
72.5°	250.8	251.5	252.2	252.2	252.2	253.6	254.9	257.0	259.0	262.5	265.9
75°	205.6	205.6	205.6	207.0	208.3	209.0	209.7	209.7	209.7	212.4	215.2
77.5°	156.2	159.7	163.1	162.4	161.7	163.1	164.5	166.5	168.6	169.9	171.3
80°	113.8	113.8	113.8	114.4	115.1	117.2	119.2	120.6	122.0	124.7	127.5
82.5°	72.6	73.3	74.0	76.1	78.1	79.5	80.9	82.9	85.0	85.0	85.0
85°	45.2	43.9	42.5	43.9	45.2	46.6	48.0	48.7	49.3	50.7	52.1
87.5°	21.9	21.9	21.9	21.9	21.9	22.6	23.3	23.3	23.3	23.3	23.3
90°	9.5	9.3	9.2	9.0	8.9	8.7	8.4	8.1	7.8	7.6	6.7
92.5°	13.6	13.7	13.8	14.0	14.1	14.1	13.9	13.7	13.4	13.2	12.8
95°	24.6	24.6	24.6	24.6	24.6	24.4	24.2	23.9	23.6	23.3	22.8
97.5°	35.3	35.4	35.4	35.5	35.6	35.4	35.1	34.7	34.4	34.0	33.6
100°	47.9	47.8	47.6	47.5	47.3	47.2	47.0	46.7	46.5	46.3	46.0
102.5°	60.8	60.9	61.0	61.0	61.1	61.0	60.8	60.6	60.4	60.2	59.7
105°	75.0	74.9	74.7	74.6	74.4	74.4	74.4	74.4	74.4	74.4	73.7
107.5°	89.5	89.6	89.6	89.7	89.8	89.7	89.5	89.3	89.1	88.9	88.6
110°	104.3	104.4	104.6	104.7	104.9	104.8	104.5	104.2	104.0	103.7	103.5



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	120.1	120.1	120.1	120.1	120.1	119.9	119.5	119.2	118.8	118.5	118.5
115°	134.2	134.3	134.4	134.5	134.5	134.5	134.5	134.4	134.3	134.2	134.4
117.5°	148.7	148.9	149.2	149.4	149.6	149.7	149.7	149.7	149.7	149.7	149.8
120°	164.2	164.3	164.5	164.6	164.7	164.8	164.9	165.0	165.1	165.1	165.5
122.5°	179.0	179.2	179.4	179.6	179.8	180.0	180.3	180.5	180.7	180.9	181.0
125°	193.8	194.1	194.4	194.6	194.9	195.2	195.5	195.8	196.0	196.3	196.5
127.5°	208.6	208.9	209.2	209.5	209.7	210.1	210.5	210.9	211.3	211.8	211.9
130°	223.1	223.6	224.1	224.6	225.1	225.5	225.7	226.0	226.3	226.6	226.8
132.5°	238.2	238.6	238.9	239.3	239.6	240.0	240.3	240.7	241.0	241.4	241.5
135°	254.0	254.1	254.3	254.4	254.5	254.8	255.0	255.3	255.6	255.9	255.9
137.5°	267.9	268.1	268.3	268.5	268.7	269.0	269.3	269.7	270.0	270.4	270.2
140°	281.4	281.9	282.4	282.9	283.4	283.6	283.7	283.8	283.9	283.9	283.9
142.5°	295.3	295.6	296.0	296.3	296.7	296.9	297.0	297.0	297.1	297.2	297.0
145°	308.5	308.8	309.1	309.3	309.6	309.8	309.9	309.9	310.0	310.1	309.9
147.5°	320.5	320.9	321.3	321.7	322.2	322.4	322.4	322.4	322.4	322.4	322.2
150°	331.8	332.2	332.7	333.1	333.5	333.7	333.7	333.7	333.7	333.7	333.6
152.5°	342.9	343.2	343.6	343.9	344.3	344.4	344.2	344.1	343.9	343.8	343.7
155°	352.6	353.1	353.6	354.1	354.6	354.7	354.4	354.1	353.8	353.6	353.5
157.5°	361.8	362.2	362.6	363.0	363.4	363.5	363.2	363.0	362.7	362.4	362.3
160°	370.6	370.9	371.1	371.4	371.7	371.7	371.3	371.0	370.6	370.3	370.3
162.5°	377.2	377.7	378.2	378.7	379.2	379.2	378.9	378.5	378.2	377.8	377.8
165°	383.5	384.0	384.5	385.0	385.5	385.5	385.1	384.7	384.2	383.8	383.8
167.5°	389.2	389.6	390.0	390.4	390.9	390.9	390.4	390.0	389.6	389.2	389.1
170°	393.3	393.8	394.3	394.7	395.2	395.2	394.7	394.3	393.8	393.3	393.3
172.5°	396.4	396.9	397.4	397.9	398.4	398.4	398.0	397.6	397.2	396.7	396.7
175°	398.6	399.1	399.6	400.1	400.6	400.6	400.2	399.8	399.4	398.9	398.9
177.5°	399.9	400.4	400.9	401.4	401.9	401.9	401.5	401.0	400.6	400.2	400.2
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6
2.5°	3159.1	3150.9	3120.8	3090.6	3056.4	3022.1	2996.7	2971.4	2933.7	2896.0	2865.2
5°	3423.7	3385.3	3321.6	3257.8	3171.5	3085.1	3026.9	2968.6	2890.5	2812.4	2750.0
7.5°	3633.4	3567.6	3478.5	3389.4	3276.3	3163.3	3056.4	2949.4	2830.2	2711.0	2613.7
10°	3767.0	3722.4	3619.7	3516.9	3365.4	3214.0	3064.6	2915.2	2761.7	2608.2	2479.3
12.5°	3780.0	3784.1	3689.6	3595.0	3423.7	3252.3	3070.7	2889.1	2695.9	2502.6	2352.6
15°	3665.6	3736.2	3684.1	3632.0	3459.3	3286.6	3063.2	2839.8	2617.1	2394.4	2221.0
17.5°	3453.1	3604.6	3612.1	3619.7	3447.0	3274.3	3026.9	2779.5	2527.3	2275.1	2092.8
20°	3163.3	3386.7	3463.4	3540.2	3399.7	3259.2	2993.3	2727.4	2445.1	2162.7	1971.6
22.5°	2867.2	3138.6	3279.1	3419.6	3315.4	3211.2	2928.2	2645.2	2347.1	2049.0	1855.1
25°	2530.1	2826.1	3042.0	3257.8	3194.1	3130.4	2851.5	2572.5	2255.3	1938.0	1739.9
27.5°	2236.1	2536.9	2797.3	3057.7	3044.0	3030.3	2753.5	2476.6	2151.8	1827.0	1635.8
30°	1974.3	2254.6	2545.8	2837.1	2870.6	2904.2	2637.0	2369.7	2044.2	1718.7	1534.3
32.5°	1742.7	1987.3	2299.8	2612.3	2678.1	2743.9	2502.6	2261.4	1939.3	1617.3	1439.8
35°	1552.8	1774.9	2087.4	2399.9	2482.1	2564.3	2354.6	2144.9	1831.1	1517.2	1347.9
37.5°	1385.0	1570.7	1875.6	2180.6	2281.3	2382.0	2194.3	2006.5	1712.5	1418.5	1263.0
40°	1245.8	1395.2	1675.5	1955.8	2072.3	2188.8	2033.9	1879.0	1600.1	1321.2	1178.0
42.5°	1129.3	1262.3	1516.5	1770.8	1882.5	1994.2	1863.3	1732.4	1484.3	1236.2	1105.4
45°	1030.0	1136.2	1367.1	1598.1	1704.3	1810.5	1698.1	1585.7	1367.1	1148.5	1026.6
47.5°	936.8	1027.9	1225.3	1422.6	1517.2	1611.8	1524.1	1436.3	1251.3	1066.3	956.0
50°	853.2	926.5	1099.2	1271.9	1354.1	1436.3	1358.9	1281.5	1129.3	977.2	881.3
52.5°	780.5	840.2	984.7	1129.3	1199.9	1270.5	1204.0	1137.6	1017.0	896.3	812.7
55°	708.6	759.3	884.7	1010.1	1058.1	1106.0	1054.6	1003.3	905.9	808.6	738.0
57.5°	641.4	686.7	789.4	892.2	929.2	966.2	919.6	873.0	799.7	726.4	667.5
60°	575.6	612.6	698.3	784.0	806.6	829.2	791.5	753.8	702.4	651.0	598.3
62.5°	514.6	548.2	612.0	675.7	690.8	705.8	677.1	648.3	609.2	570.2	529.0
65°	451.6	477.0	529.0	581.1	590.7	600.3	575.0	549.6	520.1	490.7	460.5
67.5°	393.4	411.2	453.7	496.1	496.8	497.5	477.0	456.4	440.0	423.5	399.5
70°	336.5	353.6	381.7	409.8	410.5	411.2	394.7	378.3	365.9	353.6	335.8
72.5°	278.2	290.6	311.8	333.0	331.7	330.3	320.0	309.7	300.2	290.6	277.5
75°	225.5	235.7	250.1	264.5	260.4	256.3	250.8	245.3	237.1	228.9	220.7
77.5°	177.5	183.7	191.9	200.1	197.4	194.6	189.8	185.0	178.9	172.7	169.3
80°	130.2	132.9	138.4	143.9	142.5	141.2	135.7	130.2	128.8	127.5	122.7
82.5°	88.4	91.8	93.2	94.6	93.9	93.2	89.1	85.0	83.6	82.2	81.5
85°	52.8	53.5	54.1	54.8	52.8	50.7	49.3	48.0	48.0	48.0	47.3
87.5°	24.0	24.7	24.7	24.7	24.0	23.3	21.9	20.6	21.2	21.9	21.9
90°	5.7	4.8	3.9	3.1	2.4	1.7	1.0	0.3	1.0	1.7	2.4
92.5°	12.4	12.0	11.6	11.1	10.7	10.3	9.9	9.5	9.9	10.3	10.7
95°	22.2	21.6	21.1	20.6	20.1	19.6	19.1	18.6	19.1	19.6	20.1
97.5°	33.2	32.8	32.4	32.0	31.6	31.3	30.9	30.6	30.9	31.3	31.6
100°	45.6	45.3	44.9	44.5	44.1	43.7	43.3	42.9	43.3	43.7	44.1
102.5°	59.2	58.7	58.2	57.9	57.7	57.5	57.2	57.0	57.2	57.5	57.7
105°	73.1	72.5	71.8	71.5	71.3	71.2	71.0	70.9	71.0	71.2	71.3
107.5°	88.3	88.0	87.7	87.6	87.5	87.4	87.4	87.3	87.4	87.4	87.5
110°	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.4	102.6	102.7	102.8



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.5	118.5	118.5	118.5	118.4	118.3	118.2	118.2	118.2	118.3	118.4
115°	134.5	134.7	134.8	134.8	134.6	134.3	134.1	133.9	134.1	134.3	134.6
117.5°	150.0	150.1	150.2	150.3	150.2	150.1	150.1	150.0	150.1	150.1	150.2
120°	165.8	166.2	166.5	166.5	166.1	165.6	165.2	164.8	165.2	165.6	166.1
122.5°	181.2	181.3	181.4	181.4	181.1	180.8	180.5	180.3	180.5	180.8	181.1
125°	196.6	196.7	196.9	196.8	196.6	196.4	196.2	196.0	196.2	196.4	196.6
127.5°	212.0	212.2	212.3	212.2	211.8	211.3	210.9	210.5	210.9	211.3	211.8
130°	227.0	227.2	227.4	227.2	226.7	226.1	225.6	225.0	225.6	226.1	226.7
132.5°	241.7	241.8	241.9	241.7	241.2	240.6	240.1	239.5	240.1	240.6	241.2
135°	256.0	256.1	256.2	256.0	255.6	255.1	254.7	254.3	254.7	255.1	255.6
137.5°	270.0	269.7	269.5	269.3	268.9	268.6	268.2	267.9	268.2	268.6	268.9
140°	283.8	283.7	283.6	283.4	283.1	282.7	282.4	282.0	282.4	282.7	283.1
142.5°	296.9	296.7	296.6	296.4	296.0	295.7	295.3	295.0	295.3	295.7	296.0
145°	309.7	309.5	309.2	309.1	308.9	308.8	308.6	308.5	308.6	308.8	308.9
147.5°	322.0	321.7	321.5	321.3	321.0	320.7	320.4	320.2	320.4	320.7	321.0
150°	333.4	333.3	333.2	333.0	332.9	332.7	332.6	332.5	332.6	332.7	332.9
152.5°	343.7	343.6	343.5	343.4	343.2	343.0	342.7	342.5	342.7	343.0	343.2
155°	353.4	353.4	353.3	353.3	353.3	353.3	353.3	353.3	353.3	353.3	353.3
157.5°	362.3	362.2	362.1	362.1	362.2	362.3	362.3	362.4	362.3	362.3	362.2
160°	370.3	370.3	370.3	370.3	370.5	370.6	370.8	370.9	370.8	370.6	370.5
162.5°	377.7	377.6	377.6	377.6	377.8	378.0	378.3	378.5	378.3	378.0	377.8
165°	383.8	383.8	383.8	383.9	384.1	384.3	384.6	384.8	384.6	384.3	384.1
167.5°	389.0	389.0	388.9	389.0	389.3	389.6	389.8	390.1	389.8	389.6	389.3
170°	393.3	393.3	393.3	393.4	393.7	394.0	394.3	394.5	394.3	394.0	393.7
172.5°	396.7	396.7	396.7	396.9	397.2	397.4	397.7	398.0	397.7	397.4	397.2
175°	398.9	398.9	398.9	399.1	399.4	399.6	399.9	400.2	399.9	399.6	399.4
177.5°	400.2	400.2	400.2	400.3	400.6	400.9	401.2	401.5	401.2	400.9	400.6
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6	2953.6
2.5°	2834.3	2807.6	2780.9	2760.3	2739.8	2704.8	2669.9	2661.6	2653.4	2641.8	2630.1
5°	2687.7	2621.9	2556.1	2497.2	2438.2	2392.3	2346.4	2316.2	2286.1	2264.2	2242.2
7.5°	2516.4	2417.7	2319.0	2249.1	2179.2	2112.7	2046.2	2025.0	2003.8	1975.0	1946.2
10°	2350.5	2241.6	2132.6	2041.5	1950.3	1885.2	1820.1	1794.1	1768.0	1731.7	1695.4
12.5°	2202.5	2083.3	1964.0	1872.2	1780.4	1717.3	1654.3	1616.6	1578.9	1558.3	1537.8
15°	2047.6	1920.2	1792.7	1707.7	1622.7	1565.9	1509.0	1476.1	1443.2	1423.3	1403.5
17.5°	1910.6	1784.5	1658.4	1576.8	1495.3	1443.2	1391.1	1362.3	1333.6	1318.5	1303.4
20°	1780.4	1657.0	1533.7	1454.2	1374.7	1332.2	1289.7	1271.2	1252.7	1240.4	1228.0
22.5°	1661.1	1539.8	1418.5	1350.7	1282.8	1248.6	1214.3	1201.3	1188.3	1178.0	1167.7
25°	1541.9	1433.6	1325.3	1267.8	1210.2	1182.1	1154.0	1141.0	1128.0	1117.7	1107.4
27.5°	1444.6	1341.1	1237.6	1188.3	1138.9	1117.0	1095.1	1084.8	1074.5	1064.9	1055.3
30°	1350.0	1257.5	1165.0	1122.5	1080.0	1060.1	1040.3	1030.0	1019.7	1010.8	1001.9
32.5°	1262.3	1182.8	1103.3	1064.2	1025.2	1008.7	992.3	980.0	967.6	960.8	953.9
35°	1178.7	1107.4	1036.1	1003.9	971.7	955.3	938.8	928.6	918.3	912.8	907.3
37.5°	1107.4	1043.7	980.0	949.1	918.3	902.5	886.8	877.8	868.9	866.9	864.8
40°	1034.8	980.0	925.1	895.0	864.8	851.1	837.4	831.9	826.4	825.1	823.7
42.5°	974.5	921.0	867.6	840.2	812.7	801.1	789.4	786.7	784.0	786.0	788.1
45°	904.6	860.0	815.5	790.1	764.8	755.2	745.6	743.5	741.5	745.6	749.7
47.5°	845.6	804.5	763.4	739.4	715.4	708.6	701.7	701.0	700.4	705.8	711.3
50°	785.3	745.6	705.8	686.7	667.5	661.3	655.1	657.2	659.2	668.1	677.1
52.5°	729.1	692.1	655.1	637.3	619.5	615.4	611.3	616.1	620.9	630.5	640.1
55°	667.5	633.9	600.3	586.6	572.9	568.8	564.7	574.3	583.9	592.8	601.7
57.5°	608.5	579.1	549.6	537.3	524.9	524.2	523.6	532.5	541.4	551.0	560.6
60°	545.5	520.8	496.1	486.5	477.0	478.3	479.7	490.0	500.3	507.8	515.3
62.5°	487.9	467.4	446.8	437.9	429.0	432.4	435.8	446.1	456.4	465.3	474.2
65°	430.4	413.2	396.1	389.9	383.8	388.6	393.4	402.3	411.2	417.3	423.5
67.5°	375.5	361.1	346.8	342.0	337.2	342.0	346.8	355.7	364.6	370.7	376.9
70°	318.0	306.3	294.7	291.2	287.8	293.3	298.8	306.3	313.9	320.0	326.2
72.5°	264.5	255.6	246.7	246.0	245.3	250.1	254.9	262.5	270.0	274.1	278.2
75°	212.4	207.6	202.8	202.2	201.5	206.3	211.1	215.2	219.3	222.7	226.1
77.5°	165.8	161.7	157.6	158.3	159.0	162.4	165.8	169.9	174.1	176.1	178.2
80°	117.9	116.5	115.1	116.5	117.9	120.6	123.4	126.1	128.8	130.2	131.6
82.5°	80.9	79.5	78.1	80.2	82.2	84.3	86.3	88.4	90.5	91.1	91.8
85°	46.6	48.7	50.7	50.7	50.7	51.4	52.1	52.8	53.5	52.8	52.1
87.5°	21.9	22.6	23.3	23.3	23.3	24.0	24.7	24.7	24.7	24.0	23.3
90°	3.1	3.9	4.8	5.7	6.7	7.6	7.8	8.1	8.4	8.7	8.9
92.5°	11.1	11.6	12.0	12.4	12.8	13.2	13.4	13.7	13.9	14.1	14.1
95°	20.6	21.1	21.6	22.2	22.8	23.3	23.6	23.9	24.2	24.4	24.6
97.5°	32.0	32.4	32.8	33.2	33.6	34.0	34.4	34.7	35.1	35.4	35.6
100°	44.5	44.9	45.3	45.6	46.0	46.3	46.5	46.7	47.0	47.2	47.3
102.5°	57.9	58.2	58.7	59.2	59.7	60.2	60.4	60.6	60.8	61.0	61.1
105°	71.5	71.8	72.5	73.1	73.7	74.4	74.4	74.4	74.4	74.4	74.4
107.5°	87.6	87.7	88.0	88.3	88.6	88.9	89.1	89.3	89.5	89.7	89.8
110°	103.0	103.1	103.3	103.4	103.5	103.7	104.0	104.2	104.5	104.8	104.9



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	118.5	118.5	118.5	118.5	118.5	118.5	118.8	119.2	119.5	119.9	120.1
115°	134.8	134.8	134.7	134.5	134.4	134.2	134.3	134.4	134.5	134.5	134.5
117.5°	150.3	150.2	150.1	150.0	149.8	149.7	149.7	149.7	149.7	149.7	149.6
120°	166.5	166.5	166.2	165.8	165.5	165.1	165.1	165.0	164.9	164.8	164.7
122.5°	181.4	181.4	181.3	181.2	181.0	180.9	180.7	180.5	180.3	180.0	179.8
125°	196.8	196.9	196.7	196.6	196.5	196.3	196.0	195.8	195.5	195.2	194.9
127.5°	212.2	212.3	212.2	212.0	211.9	211.8	211.3	210.9	210.5	210.1	209.7
130°	227.2	227.4	227.2	227.0	226.8	226.6	226.3	226.0	225.7	225.5	225.1
132.5°	241.7	241.9	241.8	241.7	241.5	241.4	241.0	240.7	240.3	240.0	239.6
135°	256.0	256.2	256.1	256.0	255.9	255.9	255.6	255.3	255.0	254.8	254.5
137.5°	269.3	269.5	269.7	270.0	270.2	270.4	270.0	269.7	269.3	269.0	268.7
140°	283.4	283.6	283.7	283.8	283.9	283.9	283.9	283.8	283.7	283.6	283.4
142.5°	296.4	296.6	296.7	296.9	297.0	297.2	297.1	297.0	297.0	296.9	296.7
145°	309.1	309.2	309.5	309.7	309.9	310.1	310.0	309.9	309.9	309.8	309.6
147.5°	321.3	321.5	321.7	322.0	322.2	322.4	322.4	322.4	322.4	322.4	322.2
150°	333.0	333.2	333.3	333.4	333.6	333.7	333.7	333.7	333.7	333.7	333.5
152.5°	343.4	343.5	343.6	343.7	343.7	343.8	343.9	344.1	344.2	344.4	344.3
155°	353.3	353.3	353.4	353.4	353.5	353.6	353.8	354.1	354.4	354.7	354.6
157.5°	362.1	362.1	362.2	362.3	362.3	362.4	362.7	363.0	363.2	363.5	363.4
160°	370.3	370.3	370.3	370.3	370.3	370.3	370.6	371.0	371.3	371.7	371.7
162.5°	377.6	377.6	377.6	377.7	377.8	377.8	378.2	378.5	378.9	379.2	379.2
165°	383.9	383.8	383.8	383.8	383.8	383.8	384.2	384.7	385.1	385.5	385.5
167.5°	389.0	388.9	389.0	389.0	389.1	389.2	389.6	390.0	390.4	390.9	390.9
170°	393.4	393.3	393.3	393.3	393.3	393.3	393.8	394.3	394.7	395.2	395.2
172.5°	396.9	396.7	396.7	396.7	396.7	396.7	397.2	397.6	398.0	398.4	398.4
175°	399.1	398.9	398.9	398.9	398.9	398.9	399.4	399.8	400.2	400.6	400.6
177.5°	400.3	400.2	400.2	400.2	400.2	400.2	400.6	401.0	401.5	401.9	401.9
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2953.6	2953.6	2953.6	2953.6
2.5°	2625.3	2620.5	2601.3	2582.1
5°	2225.8	2209.3	2203.9	2198.4
7.5°	1944.8	1943.5	1914.7	1885.9
10°	1697.4	1699.5	1673.5	1647.4
12.5°	1520.6	1503.5	1501.5	1499.4
15°	1387.7	1371.9	1369.2	1366.5
17.5°	1293.8	1284.2	1281.5	1278.7
20°	1222.5	1217.1	1212.3	1207.5
22.5°	1160.9	1154.0	1149.9	1145.8
25°	1101.2	1095.1	1093.7	1092.3
27.5°	1047.8	1040.3	1040.3	1040.3
30°	997.1	992.3	990.2	988.2
32.5°	949.8	945.7	945.7	945.7
35°	905.3	903.2	900.5	897.7
37.5°	864.8	864.8	863.5	862.1
40°	825.8	827.8	827.8	827.8
42.5°	790.1	792.2	792.2	792.2
45°	753.1	756.6	757.9	759.3
47.5°	716.8	722.3	723.7	725.0
50°	681.2	685.3	686.0	686.7
52.5°	644.8	649.6	653.1	656.5
55°	606.5	611.3	613.3	615.4
57.5°	565.4	570.2	570.8	571.5
60°	520.1	524.9	526.3	527.7
62.5°	477.0	479.7	481.1	482.4
65°	427.6	431.7	434.5	437.2
67.5°	380.3	383.8	383.8	383.8
70°	327.6	328.9	331.0	333.0
72.5°	278.9	279.6	279.6	279.6
75°	227.5	228.9	229.6	230.3
77.5°	178.9	179.5	179.5	179.5
80°	130.9	130.2	130.2	130.2
82.5°	89.8	87.7	87.7	87.7
85°	51.4	50.7	51.4	52.1
87.5°	23.3	23.3	23.3	23.3
90°	9.0	9.2	9.3	9.5
92.5°	14.0	13.8	13.7	13.6
95°	24.6	24.6	24.6	24.6
97.5°	35.5	35.4	35.4	35.3
100°	47.5	47.6	47.8	47.9
102.5°	61.0	61.0	60.9	60.8
105°	74.6	74.7	74.9	75.0
107.5°	89.7	89.6	89.6	89.5
110°	104.7	104.6	104.4	104.3



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	120.1	120.1	120.1	120.1
115°	134.5	134.4	134.3	134.2
117.5°	149.4	149.2	148.9	148.7
120°	164.6	164.5	164.3	164.2
122.5°	179.6	179.4	179.2	179.0
125°	194.6	194.4	194.1	193.8
127.5°	209.5	209.2	208.9	208.6
130°	224.6	224.1	223.6	223.1
132.5°	239.3	238.9	238.6	238.2
135°	254.4	254.3	254.1	254.0
137.5°	268.5	268.3	268.1	267.9
140°	282.9	282.4	281.9	281.4
142.5°	296.3	296.0	295.6	295.3
145°	309.3	309.1	308.8	308.5
147.5°	321.7	321.3	320.9	320.5
150°	333.1	332.7	332.2	331.8
152.5°	343.9	343.6	343.2	342.9
155°	354.1	353.6	353.1	352.6
157.5°	363.0	362.6	362.2	361.8
160°	371.4	371.1	370.9	370.6
162.5°	378.7	378.2	377.7	377.2
165°	385.0	384.5	384.0	383.5
167.5°	390.4	390.0	389.6	389.2
170°	394.7	394.3	393.8	393.3
172.5°	397.9	397.4	396.9	396.4
175°	400.1	399.6	399.1	398.6
177.5°	401.4	400.9	400.4	399.9
180°	401.2	401.2	401.2	401.2



TEST NUMBER: P831256

CATALOG NUMBER: S123DIP-S1165D365U940-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.12	19.28	18.76	19.93	20.68	20.36	21.52	21.00	22.17	22.92
	3H	19.79	20.83	20.44	21.49	22.27	21.80	22.84	22.46	23.50	24.29
	4H	20.38	21.36	21.06	22.03	22.83	22.27	23.24	22.94	23.92	24.72
	6H	20.76	21.67	21.45	22.35	23.16	22.56	23.46	23.24	24.14	24.95
	8H	20.87	21.73	21.57	22.43	23.25	22.63	23.49	23.33	24.19	25.00
	12H	20.92	21.74	21.63	22.44	23.28	22.65	23.47	23.36	24.17	25.01
4H	2H	18.73	19.71	19.41	20.38	21.18	20.55	21.53	21.23	22.21	23.00
	3H	20.58	21.40	21.27	22.11	22.92	22.20	23.01	22.89	23.72	24.54
	4H	21.29	22.03	22.00	22.75	23.59	22.79	23.53	23.50	24.25	25.09
	6H	21.78	22.42	22.51	23.16	24.02	23.21	23.85	23.94	24.59	25.45
	8H	21.93	22.52	22.66	23.26	24.13	23.33	23.93	24.06	24.66	25.53
	12H	22.01	22.54	22.76	23.30	24.17	23.39	23.92	24.14	24.69	25.56
8H	4H	21.58	22.18	22.31	22.91	23.78	22.92	23.52	23.65	24.25	25.12
	6H	22.18	22.67	22.94	23.45	24.32	23.43	23.93	24.20	24.71	25.58
	8H	22.39	22.83	23.16	23.61	24.49	23.61	24.05	24.39	24.83	25.72
	12H	22.52	22.91	23.30	23.68	24.63	23.73	24.12	24.51	24.89	25.83
12H	4H	21.59	22.13	22.35	22.89	23.76	22.91	23.44	23.66	24.20	25.08
	6H	22.23	22.67	23.01	23.45	24.34	23.45	23.89	24.22	24.67	25.55
	8H	22.48	22.86	23.25	23.63	24.58	23.66	24.05	24.44	24.82	25.76