

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332533-927

Luminaire Tested: **S124DIP-S350D1205U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332533-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D1205U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4506.0 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332533-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332533-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	31	30	29	22
2	84	77	71	66	75	69	64	60	54	50	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	54	43	35	30	48	38	32	27	30	26	22	23	20	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332533-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	1.0
10°-20°	124.2	2.8
20°-30°	182.8	4.1
30°-40°	212.5	4.7
40°-50°	212.5	4.7
50°-60°	185.9	4.1
60°-70°	138.0	3.1
70°-80°	78.4	1.7
80°-90°	26.2	0.6
90°-100°	78.5	1.7
100°-110°	232.5	5.2
110°-120°	394.6	8.8
120°-130°	520.4	11.5
130°-140°	584.4	13.0
140°-150°	574.3	12.7
150°-160°	483.0	10.7
160°-170°	321.4	7.1
170°-180°	112.5	2.5
0°-30°	351.0	7.8
0°-40°	563.5	12.5
0°-60°	961.8	21.3
0°-90°	1204.4	26.7
90°-120°	705.6	15.7
90°-150°	2384.7	52.9
90°-180°	3302.0	73.3
0°-180°	4506.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	3	13	20	26	28	5
95°	55	63	70	73	73	61
105°	214	216	219	222	225	228
115°	401	401	399	398	398	396
125°	584	584	584	582	580	521
135°	754	759	759	757	755	583
145°	916	919	920	919	917	573
155°	1049	1049	1048	1052	1048	483
165°	1142	1139	1138	1143	1139	322
175°	1188	1184	1183	1188	1183	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P332533-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.3	8.7	9.1	9.5	9.9	10.2	10.5	10.7	11.0	11.2	11.5
90°	2.8	5.0	7.3	9.5	11.7	13.7	15.4	17.0	18.6	20.3	21.5
92.5°	19.7	22.3	24.9	27.4	30.0	31.8	33.0	34.1	35.3	36.4	37.2
95°	55.2	57.0	58.9	60.8	62.6	64.2	65.7	67.1	68.5	69.9	70.6
97.5°	96.5	97.9	99.4	100.8	102.3	103.9	105.6	107.3	108.9	110.6	111.4
100°	128.9	129.7	130.5	131.3	132.1	133.5	135.3	137.1	138.9	140.9	141.2
102.5°	162.7	163.0	163.3	163.7	164.1	165.0	166.7	168.4	170.1	171.7	172.3
105°	214.4	214.7	214.8	215.1	215.2	215.8	216.6	217.4	218.2	219.0	219.7
107.5°	268.7	269.0	269.3	269.5	269.7	269.9	270.1	270.1	270.3	270.4	271.0
110°	305.5	305.9	306.3	306.8	307.2	307.3	307.1	306.9	306.7	306.5	306.1



TEST NUMBER: P332533-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.8	344.0	344.0	344.1	344.2	344.0	343.6	343.3	342.9	342.5	342.5
115°	401.2	401.2	401.2	401.2	401.2	401.1	400.7	400.3	399.8	399.4	399.3
117.5°	455.4	455.6	455.7	455.9	456.1	456.0	455.7	455.4	455.1	454.9	454.2
120°	491.5	492.3	493.1	493.9	494.7	494.9	494.2	493.6	493.0	492.4	491.4
122.5°	529.0	529.3	529.7	530.0	530.4	530.4	530.0	529.8	529.5	529.2	528.5
125°	584.4	584.4	584.4	584.4	584.4	584.3	584.2	583.9	583.7	583.5	583.1
127.5°	634.7	635.3	635.9	636.5	637.2	637.3	636.9	636.6	636.3	636.0	635.6
130°	670.0	670.7	671.2	671.8	672.5	672.8	672.8	672.8	672.8	672.8	672.4
132.5°	706.1	706.5	707.0	707.4	707.9	708.1	707.9	707.7	707.6	707.4	706.9
135°	753.8	755.0	756.2	757.5	758.7	759.3	759.3	759.3	759.3	759.3	758.9
137.5°	805.6	806.3	806.8	807.4	807.9	808.4	808.7	809.1	809.4	809.7	809.2
140°	840.3	840.7	841.1	841.5	841.9	842.1	842.1	842.1	842.1	842.1	841.9
142.5°	872.0	872.4	872.7	873.1	873.6	873.7	873.5	873.4	873.2	873.1	873.0
145°	915.8	916.6	917.4	918.2	919.0	919.6	919.7	920.0	920.1	920.4	920.1
147.5°	959.2	960.2	961.2	962.1	963.1	963.5	963.4	963.2	963.1	962.9	962.7
150°	985.7	986.5	987.4	988.2	989.0	989.4	989.4	989.4	989.4	989.4	989.4
152.5°	1010.7	1011.2	1011.7	1012.2	1012.7	1013.0	1013.2	1013.4	1013.5	1013.7	1014.2
155°	1049.2	1049.2	1049.2	1049.2	1049.2	1049.1	1048.9	1048.7	1048.5	1048.3	1049.1
157.5°	1081.6	1081.2	1080.9	1080.5	1080.1	1079.9	1079.9	1079.8	1079.8	1079.7	1080.4
160°	1100.7	1100.6	1100.3	1100.1	1099.9	1099.7	1099.5	1099.3	1099.1	1098.9	1099.5
162.5°	1118.4	1117.8	1117.4	1116.8	1116.3	1115.9	1115.7	1115.6	1115.3	1115.1	1116.2
165°	1142.2	1141.5	1140.9	1140.3	1139.7	1139.2	1138.8	1138.4	1138.0	1137.6	1138.8
167.5°	1160.4	1159.5	1158.6	1157.8	1157.0	1156.5	1156.6	1156.6	1156.7	1156.7	1157.9
170°	1170.7	1169.7	1168.6	1167.6	1166.6	1166.2	1166.4	1166.6	1166.8	1167.0	1168.2
172.5°	1178.1	1177.2	1176.3	1175.4	1174.6	1174.2	1174.3	1174.3	1174.3	1174.4	1175.8
175°	1188.2	1187.2	1186.1	1185.1	1184.1	1183.4	1183.3	1183.0	1182.9	1182.6	1184.1
177.5°	1191.5	1190.6	1189.9	1189.1	1188.2	1187.8	1187.8	1187.8	1187.8	1187.8	1189.0
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P332533-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	11.7	12.0	12.2	12.4	12.4	12.6	12.7	12.8
90°	22.7	23.9	25.2	26.0	26.4	26.8	27.2	27.6
92.5°	37.9	38.7	39.4	39.8	40.2	40.4	40.6	40.9
95°	71.1	71.8	72.4	72.7	72.7	72.7	72.7	72.7
97.5°	112.1	112.8	113.6	113.9	113.9	113.9	113.9	113.9
100°	141.6	142.0	142.4	142.7	142.7	142.7	142.7	142.7
102.5°	172.9	173.5	174.0	174.4	174.6	174.8	174.9	175.1
105°	220.3	220.9	221.5	222.1	222.8	223.3	223.9	224.6
107.5°	271.6	272.1	272.7	273.0	272.9	272.9	272.8	272.8
110°	305.6	305.2	304.8	304.9	305.5	306.2	306.8	307.4



TEST NUMBER: P332533-927

CATALOG NUMBER: S124DIP-S350D1205U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.4	342.3	342.2	342.2	342.4	342.5	342.6	342.8
115°	399.0	398.8	398.6	398.4	398.2	398.0	397.8	397.6
117.5°	453.4	452.7	452.0	451.5	451.1	450.7	450.3	449.9
120°	490.4	489.3	488.3	488.0	488.4	488.8	489.3	489.6
122.5°	527.8	527.1	526.4	525.7	525.0	524.3	523.5	522.8
125°	582.7	582.3	581.9	581.5	581.1	580.7	580.2	579.8
127.5°	635.2	634.8	634.3	634.0	633.7	633.3	633.0	632.6
130°	671.9	671.5	671.1	670.5	669.7	668.9	668.0	667.3
132.5°	706.5	706.2	705.8	705.4	705.0	704.7	704.4	704.1
135°	758.5	758.0	757.6	757.2	756.5	755.9	755.3	754.7
137.5°	808.7	808.1	807.6	807.4	807.6	807.6	807.8	807.9
140°	841.7	841.5	841.3	841.1	840.9	840.7	840.5	840.3
142.5°	873.0	872.9	872.9	872.8	872.8	872.7	872.7	872.7
145°	920.0	919.7	919.6	919.1	918.5	917.9	917.3	916.7
147.5°	962.6	962.4	962.2	962.0	961.9	961.6	961.4	961.2
150°	989.4	989.4	989.4	989.3	989.0	988.9	988.6	988.5
152.5°	1014.6	1015.2	1015.7	1015.7	1015.1	1014.5	1014.0	1013.5
155°	1050.0	1050.8	1051.5	1051.5	1050.8	1050.0	1049.1	1048.3
157.5°	1081.0	1081.6	1082.2	1082.2	1081.5	1080.8	1080.1	1079.4
160°	1100.1	1100.7	1101.4	1101.1	1100.1	1099.1	1098.1	1097.1
162.5°	1117.3	1118.4	1119.5	1119.6	1118.6	1117.5	1116.5	1115.5
165°	1140.0	1141.2	1142.5	1142.6	1141.9	1141.1	1140.2	1139.4
167.5°	1159.1	1160.4	1161.6	1161.6	1160.3	1159.0	1157.8	1156.5
170°	1169.5	1170.7	1172.0	1171.8	1170.4	1168.9	1167.5	1166.1
172.5°	1177.2	1178.5	1180.0	1180.0	1178.5	1177.0	1175.6	1174.2
175°	1185.5	1186.9	1188.4	1188.4	1186.9	1185.5	1184.1	1182.6
177.5°	1190.1	1191.3	1192.4	1192.3	1191.0	1189.7	1188.4	1187.1
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0

(END OF REPORT)