

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332061-940

Luminaire Tested: **S123DIP-S1165D585U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332061-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6037.7 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332061-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332061-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	62	59	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	51	48	45	42
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	27
7	61	48	40	34	58	46	38	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	32	27	24	22
9	53	40	32	27	50	39	31	26	35	29	25	32	27	23	29	25	22	19
10	50	37	30	25	47	35	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17546	17546	17546
5°	17629	17386	17507
10°	17511	17235	17343
15°	17307	17041	17072
20°	17068	16763	16778
25°	16747	16431	16397
30°	16394	16063	15940
35°	16025	15674	15471
40°	15638	15244	15008
45°	15213	14850	14487
50°	14788	14364	13966
55°	14230	13863	13440
60°	13670	13276	12854
65°	13173	12638	12246
70°	12441	11909	11383
75°	11366	10959	10493
80°	10253	9819	9732
85°	9003	8657	8312



TEST NUMBER: P332061-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.6	2.5
10°-20°	433.6	7.2
20°-30°	640.5	10.6
30°-40°	748.2	12.4
40°-50°	752.2	12.5
50°-60°	660.7	10.9
60°-70°	492.2	8.2
70°-80°	280.4	4.6
80°-90°	82.4	1.4
90°-100°	42.2	0.7
100°-110°	126.2	2.1
110°-120°	214.7	3.6
120°-130°	282.4	4.7
130°-140°	317.5	5.3
140°-150°	312.1	5.2
150°-160°	262.7	4.4
160°-170°	174.9	2.9
170°-180°	61.2	1.0
0°-30°	1227.6	20.3
0°-40°	1975.8	32.7
0°-60°	3388.7	56.1
0°-90°	4243.8	70.3
90°-120°	383.2	6.3
90°-150°	1295.1	21.5
90°-180°	1794.0	29.7
0°-180°	6037.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1630	1630	1630	1630	1630	
5°	1632	1624	1609	1622	1620	155
15°	1553	1547	1529	1539	1532	438
25°	1410	1401	1384	1385	1381	649
35°	1220	1211	1193	1185	1177	763
45°	999	993	976	959	952	771
55°	758	756	739	724	716	679
65°	517	510	496	485	481	510
75°	273	268	264	257	252	292
85°	73	70	70	67	67	80
90°	0	6	12	14	15	6
95°	30	34	38	40	40	34
105°	114	116	120	120	121	123
115°	216	218	217	217	217	214
125°	316	318	317	315	313	282
135°	410	413	413	411	410	316
145°	498	499	500	500	498	311
155°	570	570	571	572	569	262
165°	621	620	620	622	619	175
175°	646	644	644	647	643	61
180°	648	648	648	648	648	



TEST NUMBER: P332061-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1635.8	1634.8	1633.8	1632.8	1631.7	1629.9	1627.2	1624.4	1621.7	1618.9	1621.4
5°	1631.6	1630.0	1628.4	1626.9	1625.3	1622.8	1619.4	1616.0	1612.6	1609.1	1612.2
7.5°	1615.6	1614.0	1612.5	1610.9	1609.4	1606.8	1603.2	1599.7	1596.2	1592.6	1595.4
10°	1602.1	1600.5	1599.0	1597.4	1595.9	1593.1	1589.0	1585.0	1580.9	1576.9	1579.7
12.5°	1584.2	1582.9	1581.5	1580.3	1579.0	1576.4	1572.6	1568.8	1565.0	1561.2	1563.3
15°	1553.1	1551.8	1550.6	1549.3	1548.1	1545.4	1541.4	1537.3	1533.3	1529.2	1531.7
17.5°	1516.9	1515.3	1513.7	1512.1	1510.4	1507.6	1503.5	1499.5	1495.4	1491.4	1493.2
20°	1490.0	1488.1	1486.2	1484.3	1482.6	1479.5	1475.5	1471.5	1467.4	1463.4	1464.6
22.5°	1459.7	1457.9	1456.0	1454.1	1452.2	1449.3	1445.2	1441.2	1437.2	1433.1	1434.0
25°	1410.1	1408.2	1406.3	1404.4	1402.7	1399.6	1395.6	1391.6	1387.5	1383.5	1383.8
27.5°	1357.1	1355.3	1353.5	1351.7	1349.9	1346.8	1342.5	1338.1	1333.7	1329.4	1329.6
30°	1319.0	1317.4	1315.9	1314.3	1312.8	1309.8	1305.5	1301.1	1296.7	1292.4	1292.4
32.5°	1280.9	1278.8	1276.8	1274.7	1272.6	1269.9	1266.6	1263.2	1259.8	1256.5	1254.7
35°	1219.5	1217.6	1215.8	1213.9	1212.0	1209.1	1205.0	1201.0	1196.9	1192.8	1191.0
37.5°	1156.6	1154.3	1151.9	1149.6	1147.2	1144.0	1139.9	1135.8	1131.7	1127.5	1125.2
40°	1112.9	1111.1	1109.2	1107.3	1105.5	1102.3	1098.0	1093.6	1089.2	1084.9	1082.4
42.5°	1069.2	1067.1	1065.0	1062.8	1060.7	1057.5	1053.1	1048.7	1044.4	1040.1	1037.6
45°	999.4	998.2	996.9	995.7	994.4	991.8	987.7	983.6	979.6	975.5	971.9
47.5°	930.1	928.4	926.6	924.7	922.9	920.2	916.3	912.5	908.7	904.9	901.3
50°	883.1	881.5	879.9	878.4	876.8	874.1	870.0	865.9	861.8	857.8	854.4
52.5°	833.7	832.7	831.6	830.5	829.5	826.8	822.5	818.2	814.0	809.6	806.6
55°	758.3	758.0	757.7	757.4	757.1	754.9	750.8	746.8	742.7	738.7	735.3
57.5°	686.5	685.5	684.4	683.4	682.3	680.2	676.9	673.7	670.5	667.2	664.1
60°	635.0	634.6	634.4	634.0	633.7	631.7	627.9	624.2	620.5	616.7	613.9
62.5°	589.0	588.2	587.4	586.6	585.8	583.4	579.7	576.0	572.3	568.6	565.7
65°	517.2	515.7	514.1	512.6	511.0	508.6	505.5	502.4	499.3	496.2	493.7
67.5°	441.2	439.9	438.5	437.1	435.8	433.9	431.5	429.2	426.8	424.5	422.2
70°	395.3	393.4	391.6	389.7	387.8	385.9	384.1	382.2	380.3	378.4	376.3
72.5°	347.1	345.7	344.3	343.0	341.6	339.8	337.7	335.6	333.5	331.4	329.4
75°	273.3	272.1	270.8	269.6	268.3	267.2	266.4	265.4	264.5	263.5	262.0
77.5°	208.0	207.3	206.6	206.0	205.3	204.4	203.2	202.2	201.0	199.9	198.9
80°	165.4	164.4	163.5	162.6	161.7	160.9	160.2	159.6	159.0	158.4	158.1
82.5°	123.9	123.7	123.5	123.3	123.1	123.0	122.9	122.8	122.6	122.5	122.0
85°	72.9	72.2	71.6	71.0	70.4	70.1	70.1	70.1	70.1	70.1	69.5
87.5°	29.2	28.7	28.2	27.7	27.2	26.9	27.0	27.0	27.1	27.1	26.9
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	12.3	13.1	13.8	14.6	15.4	16.2	17.0	17.8	18.7	19.5	19.9
95°	30.1	30.8	31.6	32.4	33.2	34.1	35.0	35.8	36.7	37.6	38.1
97.5°	53.3	53.9	54.5	55.1	55.6	56.3	56.9	57.6	58.2	58.9	59.4
100°	69.2	69.8	70.5	71.2	71.9	72.5	73.0	73.7	74.2	74.7	75.1
102.5°	87.5	87.9	88.3	88.7	89.1	89.7	90.4	91.2	91.9	92.6	93.0
105°	114.4	114.7	114.9	115.1	115.4	115.9	117.0	118.0	119.0	120.0	120.0
107.5°	145.8	145.9	146.1	146.2	146.3	146.6	147.0	147.4	147.8	148.2	148.6
110°	165.3	165.5	165.8	165.9	166.2	166.4	166.7	166.9	167.1	167.4	167.8



TEST NUMBER: P332061-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	185.7	185.7	185.9	186.0	186.2	186.3	186.4	186.4	186.5	186.5	187.0
115°	216.2	216.5	216.9	217.2	217.5	217.6	217.3	217.1	216.9	216.7	216.8
117.5°	246.9	247.1	247.4	247.5	247.8	247.7	247.4	247.2	246.9	246.6	246.6
120°	266.0	266.7	267.3	268.0	268.8	268.8	268.2	267.7	267.1	266.5	266.4
122.5°	286.0	286.4	287.0	287.4	287.9	288.0	287.8	287.5	287.1	286.9	286.6
125°	316.4	316.7	317.0	317.4	317.7	317.8	317.5	317.4	317.1	316.9	316.4
127.5°	344.5	345.2	345.9	346.6	347.3	347.6	347.3	347.1	346.8	346.6	346.0
130°	363.2	364.1	365.0	365.9	366.8	367.0	366.8	366.4	366.0	365.7	365.2
132.5°	381.8	382.8	383.7	384.6	385.5	385.8	385.6	385.3	385.0	384.9	384.2
135°	410.5	411.2	411.8	412.5	413.1	413.5	413.3	413.2	413.1	413.0	412.6
137.5°	436.9	437.5	438.0	438.6	439.2	439.6	439.9	440.1	440.5	440.8	440.3
140°	455.2	455.8	456.4	456.9	457.4	457.8	457.9	458.1	458.2	458.3	458.2
142.5°	471.9	472.4	473.1	473.6	474.1	474.6	474.7	474.9	475.2	475.4	475.3
145°	497.9	498.2	498.4	498.6	498.8	499.1	499.4	499.8	500.2	500.5	500.3
147.5°	520.8	521.1	521.6	521.9	522.4	522.7	523.1	523.3	523.7	524.0	524.0
150°	536.6	536.8	537.1	537.3	537.5	537.7	538.0	538.1	538.4	538.6	538.6
152.5°	549.7	549.9	550.3	550.5	550.9	551.1	551.3	551.3	551.5	551.6	551.8
155°	570.2	570.2	570.2	570.2	570.2	570.2	570.3	570.4	570.6	570.7	571.1
157.5°	587.6	587.5	587.4	587.3	587.1	587.1	587.2	587.3	587.4	587.5	587.9
160°	598.6	598.4	598.2	598.0	597.7	597.6	597.6	597.6	597.6	597.6	598.2
162.5°	608.4	608.1	607.8	607.4	607.2	607.1	607.2	607.3	607.3	607.4	608.0
165°	621.0	620.7	620.4	620.0	619.6	619.5	619.5	619.5	619.5	619.5	620.2
167.5°	631.1	630.6	630.2	629.7	629.3	629.1	629.2	629.3	629.4	629.5	630.2
170°	636.8	636.3	635.9	635.4	635.0	634.7	634.7	634.7	634.7	634.7	635.5
172.5°	641.2	640.8	640.3	639.9	639.4	639.3	639.3	639.3	639.3	639.3	640.0
175°	646.0	645.5	645.1	644.6	644.2	643.9	643.9	643.9	643.9	643.9	644.6
177.5°	647.9	647.6	647.2	646.8	646.4	646.2	646.2	646.2	646.2	646.2	646.8
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332061-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1623.9	1626.4	1628.9	1630.0	1629.8	1629.5	1629.2	1629.1
5°	1615.3	1618.5	1621.6	1622.8	1622.2	1621.6	1621.0	1620.3
7.5°	1598.2	1601.0	1603.8	1605.0	1604.6	1604.3	1603.9	1603.6
10°	1582.5	1585.3	1588.1	1589.2	1588.6	1588.0	1587.3	1586.7
12.5°	1565.3	1567.4	1569.4	1570.3	1569.9	1569.5	1569.1	1568.8
15°	1534.2	1536.7	1539.2	1539.5	1537.7	1535.8	1533.9	1532.0
17.5°	1494.9	1496.6	1498.3	1498.9	1498.3	1497.5	1496.8	1496.2
20°	1465.9	1467.1	1468.4	1468.5	1467.6	1466.6	1465.7	1464.7
22.5°	1435.1	1436.1	1437.1	1437.0	1435.8	1434.6	1433.4	1432.3
25°	1384.1	1384.4	1384.7	1384.4	1383.5	1382.5	1381.6	1380.6
27.5°	1329.9	1330.1	1330.3	1329.9	1328.7	1327.5	1326.3	1325.2
30°	1292.4	1292.4	1292.4	1291.3	1289.1	1286.9	1284.7	1282.5
32.5°	1252.9	1251.2	1249.5	1248.0	1246.9	1245.6	1244.5	1243.3
35°	1189.1	1187.2	1185.4	1183.7	1182.1	1180.5	1178.9	1177.4
37.5°	1123.0	1120.8	1118.6	1117.0	1115.9	1114.9	1113.9	1112.9
40°	1080.0	1077.5	1075.0	1073.1	1071.8	1070.6	1069.3	1068.1
42.5°	1035.1	1032.6	1030.1	1028.2	1027.0	1025.7	1024.5	1023.2
45°	968.1	964.4	960.6	958.0	956.4	954.8	953.3	951.7
47.5°	897.6	893.9	890.2	887.7	886.4	884.9	883.6	882.3
50°	851.0	847.6	844.1	841.5	839.6	837.8	835.9	834.0
52.5°	803.8	800.8	797.9	795.5	793.6	791.8	789.9	788.0
55°	731.8	728.4	725.0	722.5	720.9	719.3	717.8	716.2
57.5°	661.1	658.1	655.0	652.6	650.8	649.0	647.1	645.3
60°	611.2	608.3	605.6	603.3	601.8	600.2	598.7	597.1
62.5°	562.9	560.1	557.3	555.4	554.3	553.2	552.2	551.2
65°	491.2	488.7	486.2	484.6	483.6	482.7	481.7	480.8
67.5°	420.1	417.9	415.7	413.9	412.7	411.3	410.0	408.8
70°	374.1	371.9	369.7	367.8	366.3	364.7	363.2	361.7
72.5°	327.5	325.6	323.6	322.3	321.5	320.7	319.9	319.1
75°	260.4	258.9	257.3	256.0	255.1	254.1	253.2	252.3
77.5°	197.8	196.7	195.6	195.1	195.1	195.1	195.1	195.1
80°	157.7	157.5	157.1	157.0	157.0	157.0	157.0	157.0
82.5°	121.4	120.8	120.3	119.8	119.6	119.4	119.1	118.9
85°	68.8	68.2	67.6	67.3	67.3	67.3	67.3	67.3
87.5°	26.8	26.7	26.5	26.4	26.5	26.5	26.6	26.6
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	20.2	20.6	21.0	21.1	21.0	20.8	20.7	20.5
95°	38.5	39.0	39.4	39.7	39.7	39.7	39.7	39.7
97.5°	59.9	60.5	61.0	61.2	61.2	61.1	61.1	61.0
100°	75.4	75.8	76.2	76.4	76.6	76.9	77.0	77.3
102.5°	93.4	93.7	94.0	94.2	94.2	94.1	94.1	94.0
105°	120.0	120.0	120.0	120.1	120.4	120.6	120.8	121.1
107.5°	148.9	149.3	149.6	149.8	149.6	149.5	149.4	149.3
110°	168.3	168.7	169.2	169.2	169.1	168.8	168.6	168.4



TEST NUMBER: P332061-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	187.5	188.1	188.6	188.9	188.9	188.8	188.8	188.7
115°	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7
117.5°	246.6	246.5	246.5	246.3	246.0	245.7	245.4	245.0
120°	266.3	266.2	266.1	265.9	265.6	265.5	265.2	265.0
122.5°	286.2	286.0	285.7	285.3	285.1	284.7	284.5	284.1
125°	315.9	315.5	315.0	314.6	314.1	313.7	313.3	312.8
127.5°	345.3	344.6	344.0	343.5	343.0	342.4	341.9	341.3
130°	364.8	364.4	363.9	363.3	362.5	361.7	360.9	360.1
132.5°	383.7	383.2	382.6	382.1	381.5	380.8	380.2	379.6
135°	412.1	411.6	411.2	410.8	410.6	410.4	410.2	409.9
137.5°	439.8	439.3	438.9	438.5	438.0	437.6	437.1	436.7
140°	458.1	457.9	457.8	457.4	456.6	455.8	455.0	454.2
142.5°	475.1	475.0	474.9	474.6	473.9	473.3	472.7	472.1
145°	500.2	500.2	500.1	499.7	499.3	498.8	498.4	497.9
147.5°	524.0	524.0	524.0	523.6	523.0	522.3	521.7	520.9
150°	538.6	538.6	538.6	538.3	537.6	536.9	536.3	535.6
152.5°	552.1	552.2	552.4	552.1	551.6	551.0	550.5	549.8
155°	571.6	572.0	572.5	572.3	571.5	570.7	570.0	569.2
157.5°	588.4	588.9	589.3	589.2	588.6	588.0	587.4	586.7
160°	598.8	599.3	599.9	599.9	599.5	599.1	598.6	598.2
162.5°	608.5	609.1	609.7	609.6	608.9	608.1	607.4	606.7
165°	620.9	621.5	622.2	622.1	621.3	620.5	619.8	619.0
167.5°	630.9	631.6	632.3	632.3	631.6	630.9	630.2	629.5
170°	636.3	637.1	637.9	637.9	637.1	636.3	635.5	634.7
172.5°	640.6	641.3	642.0	642.0	641.2	640.4	639.6	638.8
175°	645.2	646.0	646.7	646.6	645.8	645.0	644.2	643.4
177.5°	647.4	647.9	648.5	648.4	647.7	647.1	646.5	645.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5

(END OF REPORT)