

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332064-940

Luminaire Tested: **S123DIP-S1165D805U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332064-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6827.4 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55				
2	93	85	79	74	87	80	75	70	71	67	63	62	59	57	55	52	50	46				
3	85	75	68	62	79	71	64	59	63	58	54	55	52	48	49	46	43	40				
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34				
5	71	60	51	45	67	56	49	44	50	44	40	45	40	36	39	36	33	30				
6	66	54	45	40	62	51	43	38	45	39	35	40	36	32	36	32	29	26				
7	61	49	40	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23				
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21				
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19				
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15569	15569	15569	15569
5°	18567	15637	13857	15637
10°	23240	15557	12516	15557
15°	28505	15432	11652	15432
20°	33956	15237	11094	15237
25°	36056	14998	10969	14998
30°	30904	14825	11028	14825
35°	21494	14578	11143	14578
40°	16190	14289	11108	14289
45°	13443	13857	10966	13857
50°	12042	12980	10868	12980
55°	11258	12033	10732	12033
60°	10559	11044	10622	11044
65°	9926	10068	10282	10068
70°	9309	8954	9791	8954
75°	8339	7839	8979	7839
80°	7296	6428	7736	6428
85°	5718	4668	5199	4668



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.5	2.1
10°-20°	456.9	6.7
20°-30°	766.8	11.2
30°-40°	868.3	12.7
40°-50°	778.6	11.4
50°-60°	628.3	9.2
60°-70°	437.9	6.4
70°-80°	230.1	3.4
80°-90°	58.9	0.9
90°-100°	57.8	0.8
100°-110°	173.1	2.5
110°-120°	294.3	4.3
120°-130°	387.1	5.7
130°-140°	435.1	6.4
140°-150°	427.7	6.3
150°-160°	360.1	5.3
160°-170°	239.7	3.5
170°-180°	83.9	1.2
0°-30°	1366.2	20.0
0°-40°	2234.5	32.7
0°-60°	3641.5	53.3
0°-90°	4368.4	64.0
90°-120°	525.2	7.7
90°-150°	1775.2	26.0
90°-180°	2459.0	36.0
0°-180°	6827.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1446	1446	1446	1446	1446	
5°	1718	1447	1282	1447	1718	178
15°	2558	1385	1046	1385	2558	739
25°	3036	1263	924	1263	3036	1331
35°	1636	1109	848	1109	1636	1063
45°	883	910	720	910	883	699
55°	600	641	572	641	600	538
65°	390	395	404	395	390	388
75°	200	188	216	188	200	215
85°	46	38	42	38	46	55
90°	21	1	21	1	21	12
95°	54	41	54	41	54	56
105°	166	157	166	157	166	176
115°	297	296	297	296	297	294
125°	429	434	429	434	429	383
135°	562	563	562	563	562	432
145°	682	682	682	682	682	426
155°	780	782	780	782	780	359
165°	848	851	848	851	848	239
175°	882	885	882	885	882	84
180°	888	888	888	888	888	



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1535.1	1533.9	1531.2	1533.4	1528.9	1522.7	1522.2	1516.5	1500.3	1499.1	1494.7
5°	1718.4	1712.8	1712.1	1711.4	1701.6	1688.3	1663.0	1660.9	1627.3	1610.4	1590.2
7.5°	1955.8	1958.7	1948.6	1939.6	1909.6	1889.8	1862.8	1828.2	1786.8	1744.9	1717.0
10°	2126.3	2149.4	2120.7	2101.0	2082.9	2048.4	2008.6	1958.7	1909.0	1850.8	1806.7
12.5°	2309.1	2320.4	2314.6	2296.2	2267.8	2215.5	2144.7	2090.0	2044.2	1947.3	1908.2
15°	2558.0	2600.8	2573.4	2510.3	2511.7	2461.9	2369.5	2267.8	2213.9	2129.0	2013.5
17.5°	2823.2	2828.5	2816.8	2764.3	2729.3	2660.9	2575.5	2478.1	2368.7	2266.2	2143.5
20°	2964.4	2960.2	2935.7	2908.4	2848.1	2794.9	2701.6	2593.0	2452.8	2352.0	2218.0
22.5°	3043.0	3035.9	3024.3	3001.4	2951.3	2894.0	2810.4	2691.7	2558.2	2419.2	2264.6
25°	3035.9	3045.0	3046.4	3040.1	3022.6	2988.3	2922.4	2827.8	2694.7	2516.0	2354.7
27.5°	2761.2	2774.1	2811.6	2844.7	2881.9	2919.7	2914.6	2867.7	2769.2	2614.9	2417.8
30°	2486.4	2458.4	2527.8	2615.5	2675.0	2780.1	2839.0	2842.5	2787.1	2654.7	2462.6
32.5°	2105.2	2136.1	2166.8	2274.6	2404.8	2522.8	2640.0	2734.3	2745.1	2656.9	2489.0
35°	1635.7	1674.3	1730.3	1786.4	1926.5	2047.1	2253.1	2432.5	2575.5	2594.4	2491.4
37.5°	1318.1	1337.1	1372.6	1428.8	1520.5	1663.5	1822.8	2049.6	2256.7	2410.8	2417.5
40°	1152.2	1157.7	1197.7	1240.5	1314.7	1432.4	1576.1	1776.6	2024.6	2239.8	2329.5
42.5°	1027.7	1040.0	1056.9	1098.1	1157.2	1245.8	1379.4	1545.0	1772.4	2020.0	2195.5
45°	883.1	897.1	907.6	934.9	977.0	1036.5	1129.7	1281.1	1454.2	1709.9	1946.2
47.5°	787.5	788.5	796.4	817.0	845.6	890.3	956.2	1053.5	1212.4	1419.9	1662.3
50°	719.1	730.2	733.1	749.1	771.6	804.5	859.2	941.9	1072.3	1254.5	1477.3
52.5°	670.8	674.2	682.1	693.7	713.3	739.0	786.3	851.0	953.4	1108.7	1313.6
55°	599.9	599.9	607.6	616.7	627.9	651.0	682.6	730.2	808.1	928.5	1098.1
57.5°	534.3	537.8	543.2	546.1	555.6	570.9	597.3	633.4	691.4	784.2	919.1
60°	490.5	496.9	496.1	501.8	510.2	522.1	544.6	574.0	625.8	700.1	813.7
62.5°	452.5	452.0	451.9	458.6	467.0	478.4	492.9	518.4	562.5	628.4	725.1
65°	389.7	388.3	393.2	397.3	400.2	408.6	419.8	442.2	471.6	520.7	595.7
67.5°	333.9	329.8	332.4	333.9	338.7	345.2	355.7	369.6	393.0	432.4	488.9
70°	295.8	292.2	291.5	292.9	297.1	302.0	309.8	323.1	344.8	376.3	417.7
72.5°	256.5	254.1	254.0	257.1	259.0	262.3	267.7	279.9	297.1	320.8	359.4
75°	200.5	200.5	200.5	201.2	203.2	206.1	210.3	216.5	229.9	246.6	272.6
77.5°	150.3	150.1	149.3	149.1	152.2	153.5	154.4	160.3	167.7	179.1	198.0
80°	117.7	114.2	115.7	117.7	119.1	119.8	122.0	123.3	129.7	136.0	149.3
82.5°	87.5	84.5	84.8	88.0	88.3	89.0	91.1	93.1	95.4	101.2	108.3
85°	46.3	46.3	47.0	47.0	47.6	47.0	49.0	49.8	49.8	53.2	57.4
87.5°	21.0	19.8	20.3	20.8	20.2	20.7	21.1	21.6	21.9	22.4	22.6
90°	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0	17.4	16.8	14.7
92.5°	28.2	28.4	28.5	28.7	28.9	28.7	28.3	27.7	27.3	26.8	25.6
95°	54.4	54.4	54.4	54.4	54.4	54.0	53.4	52.8	52.3	51.6	50.4
97.5°	83.6	83.7	83.8	83.8	83.9	83.6	82.8	82.1	81.4	80.7	79.8
100°	105.9	105.7	105.3	105.0	104.8	104.3	103.9	103.4	103.0	102.5	101.7
102.5°	128.9	128.9	128.9	129.0	129.1	128.9	128.4	128.0	127.5	127.1	126.0
105°	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5	164.5	164.5	163.2
107.5°	204.6	204.7	204.9	205.1	205.3	205.2	204.6	204.1	203.7	203.1	202.6
110°	230.8	231.0	231.4	231.7	232.0	231.8	231.2	230.6	230.0	229.3	229.1



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.7	258.7	258.8	258.9	258.9	258.6	257.8	257.1	256.4	255.6	255.6
115°	297.0	297.1	297.3	297.5	297.7	297.7	297.5	297.3	297.1	297.0	297.3
117.5°	335.9	336.4	336.8	337.2	337.6	337.9	337.9	338.0	338.0	338.0	338.4
120°	363.2	363.6	363.8	364.2	364.4	364.7	364.9	365.0	365.2	365.3	366.1
122.5°	389.4	389.9	390.3	390.7	391.2	391.6	392.0	392.4	392.8	393.2	393.6
125°	428.7	429.4	430.0	430.6	431.2	431.9	432.5	433.1	433.7	434.4	434.6
127.5°	468.0	468.7	469.4	470.1	470.8	471.6	472.4	473.3	474.2	475.0	475.4
130°	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.1	500.6	501.2	501.8
132.5°	520.4	521.2	522.0	522.9	523.7	524.5	525.2	526.0	526.7	527.4	527.8
135°	562.0	562.2	562.6	562.8	563.2	563.7	564.3	564.9	565.5	566.1	566.2
137.5°	598.6	599.2	599.8	600.4	600.9	601.5	602.3	602.9	603.5	604.1	603.8
140°	622.6	623.7	624.7	625.8	627.0	627.5	627.7	627.9	628.0	628.1	628.0
142.5°	647.1	647.9	648.8	649.6	650.5	650.9	651.1	651.3	651.4	651.6	651.3
145°	682.5	683.1	683.8	684.4	685.0	685.4	685.5	685.7	685.9	686.0	685.5
147.5°	714.1	715.0	715.9	716.8	717.7	718.3	718.3	718.3	718.3	718.3	717.8
150°	734.1	735.0	736.0	736.9	737.9	738.3	738.3	738.3	738.3	738.3	738.0
152.5°	753.7	754.5	755.3	756.1	756.9	757.2	756.9	756.6	756.4	756.2	756.0
155°	780.2	781.2	782.3	783.4	784.4	784.7	784.1	783.5	782.8	782.2	782.1
157.5°	804.2	805.1	806.0	806.9	807.7	807.8	807.2	806.6	805.9	805.2	805.1
160°	819.8	820.5	821.1	821.7	822.3	822.2	821.5	820.7	819.9	819.2	819.2
162.5°	831.6	832.6	833.6	834.6	835.5	835.7	834.9	834.1	833.3	832.6	832.4
165°	848.5	849.5	850.6	851.8	852.8	852.9	851.9	851.0	850.1	849.2	849.2
167.5°	862.8	863.8	864.8	865.7	866.7	866.7	865.7	864.8	863.8	862.8	862.7
170°	870.0	871.2	872.3	873.3	874.4	874.4	873.3	872.3	871.2	870.0	870.0
172.5°	875.7	876.7	877.8	878.9	880.0	880.0	879.1	878.2	877.2	876.2	876.2
175°	881.9	883.0	884.1	885.2	886.3	886.4	885.4	884.5	883.6	882.6	882.6
177.5°	885.3	886.2	887.0	887.9	888.8	888.8	888.1	887.3	886.5	885.8	885.8
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1491.3	1486.8	1482.4	1474.5	1467.8	1458.2	1455.5	1452.1	1442.0	1433.1	1426.3
5°	1582.4	1565.6	1541.1	1518.7	1500.5	1476.0	1461.9	1447.2	1426.1	1407.2	1391.8
7.5°	1677.8	1644.7	1606.5	1565.3	1527.0	1490.0	1460.1	1433.4	1404.0	1376.1	1354.4
10°	1753.5	1705.8	1652.5	1595.1	1546.0	1498.3	1458.4	1423.3	1385.5	1352.5	1325.3
12.5°	1839.8	1769.2	1695.7	1625.9	1567.9	1501.7	1453.3	1408.8	1365.9	1326.2	1295.6
15°	1942.0	1852.3	1765.3	1669.4	1581.0	1498.3	1440.9	1384.8	1335.1	1294.4	1255.2
17.5°	2035.1	1933.4	1818.9	1702.1	1595.6	1497.5	1417.0	1353.7	1291.5	1241.7	1202.6
20°	2087.8	1972.1	1842.5	1721.2	1603.5	1494.2	1405.9	1330.2	1262.8	1210.3	1166.2
22.5°	2133.2	1997.9	1863.8	1734.1	1602.9	1485.1	1385.1	1307.2	1234.3	1182.9	1135.9
25°	2180.2	2018.4	1883.8	1731.7	1585.3	1463.3	1351.2	1262.8	1190.0	1129.7	1081.4
27.5°	2220.6	2017.0	1857.3	1693.7	1557.5	1435.3	1315.5	1220.8	1143.4	1078.0	1028.9
30°	2247.5	2019.7	1829.8	1667.9	1530.6	1404.4	1288.1	1192.8	1111.5	1044.9	998.6
32.5°	2264.3	2018.0	1804.6	1632.1	1488.0	1376.4	1258.4	1159.7	1076.2	1010.8	966.2
35°	2274.1	2005.7	1761.1	1557.9	1419.2	1310.5	1211.7	1109.4	1021.8	960.8	910.3
37.5°	2254.5	1979.8	1710.7	1486.4	1334.5	1227.5	1144.4	1057.2	973.4	906.3	862.8
40°	2223.7	1963.0	1671.4	1436.0	1276.2	1173.1	1102.4	1016.9	934.2	870.4	829.7
42.5°	2164.8	1928.8	1628.3	1379.9	1215.7	1112.6	1047.4	976.0	897.8	837.9	797.3
45°	2021.2	1854.3	1563.5	1295.8	1126.2	1019.7	962.2	910.3	839.5	781.4	746.4
47.5°	1821.9	1742.4	1469.9	1207.1	1032.9	930.4	870.7	828.9	777.2	730.2	696.6
50°	1683.4	1650.4	1406.5	1146.6	970.6	870.4	813.0	775.1	738.0	691.0	660.1
52.5°	1523.6	1543.9	1332.6	1083.7	907.3	808.8	754.7	724.6	690.9	652.3	625.4
55°	1298.6	1372.2	1204.7	978.3	813.0	719.1	667.9	641.2	621.6	592.9	569.8
57.5°	1088.0	1181.6	1066.5	869.7	720.3	639.3	590.2	561.2	548.6	533.6	515.4
60°	963.0	1055.4	967.9	796.8	658.1	580.9	537.5	513.0	500.3	489.9	474.5
62.5°	851.3	944.9	871.4	722.8	596.9	525.5	487.6	463.7	453.9	448.4	435.2
65°	698.0	778.6	729.5	607.6	509.5	446.4	412.1	395.3	386.1	384.1	375.7
67.5°	568.1	629.5	593.7	504.0	426.8	372.3	343.1	328.9	321.8	321.1	314.8
70°	482.9	540.3	513.0	431.7	365.2	322.4	297.1	284.5	280.4	279.6	276.2
72.5°	416.7	456.8	435.1	367.2	315.8	277.0	258.4	245.3	240.5	241.5	239.2
75°	308.4	338.5	325.9	278.9	237.6	212.3	196.9	188.5	184.3	186.5	183.6
77.5°	221.9	240.9	229.6	197.1	171.6	153.4	142.0	136.8	133.0	132.9	131.6
80°	167.5	178.7	172.4	152.8	131.8	116.4	107.2	103.7	101.7	100.9	100.2
82.5°	119.3	128.9	121.4	107.9	93.6	84.4	79.2	74.5	73.0	73.5	72.8
85°	60.3	63.8	61.0	52.5	47.0	42.7	39.9	37.8	36.5	37.2	35.8
87.5°	23.3	23.5	21.4	18.7	17.3	15.3	15.1	13.6	12.8	13.1	12.8
90°	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7	2.2	3.8	5.4
92.5°	24.5	23.4	22.2	21.0	20.1	19.0	17.9	16.9	17.9	19.0	20.1
95°	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1	42.2	43.3	44.4
97.5°	78.9	78.0	77.1	76.3	75.4	74.6	73.8	73.0	73.8	74.6	75.4
100°	100.9	100.1	99.4	98.5	97.6	96.7	95.8	94.8	95.8	96.7	97.6
102.5°	125.0	123.9	123.0	122.2	121.6	121.0	120.5	119.9	120.5	121.0	121.6
105°	161.8	160.3	159.0	158.1	157.8	157.5	157.2	156.9	157.2	157.5	157.8
107.5°	202.1	201.5	200.9	200.5	200.4	200.2	200.0	199.8	200.0	200.2	200.4
110°	228.7	228.5	228.1	227.8	227.5	227.2	226.9	226.6	226.9	227.2	227.5



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	255.5	255.4	255.3	255.2	255.0	254.9	254.7	254.5	254.7	254.9	255.0
115°	297.7	297.9	298.3	298.2	297.7	297.2	296.8	296.3	296.8	297.2	297.7
117.5°	338.8	339.2	339.6	339.7	339.3	339.0	338.8	338.4	338.8	339.0	339.3
120°	366.8	367.7	368.5	368.4	367.4	366.5	365.5	364.6	365.5	366.5	367.4
122.5°	394.0	394.4	394.8	394.7	394.0	393.3	392.6	392.0	392.6	393.3	394.0
125°	435.0	435.2	435.6	435.5	435.1	434.5	434.1	433.6	434.1	434.5	435.1
127.5°	475.7	476.1	476.4	476.1	475.1	474.1	473.1	472.2	473.1	474.1	475.1
130°	502.2	502.7	503.1	502.7	501.5	500.2	499.0	497.8	499.0	500.2	501.5
132.5°	528.2	528.5	528.9	528.4	527.2	525.9	524.7	523.4	524.7	525.9	527.2
135°	566.4	566.6	566.8	566.3	565.4	564.5	563.6	562.6	563.6	564.5	565.4
137.5°	603.3	603.0	602.5	602.0	601.2	600.4	599.7	598.9	599.7	600.4	601.2
140°	627.9	627.7	627.5	627.1	626.3	625.5	624.7	623.9	624.7	625.5	626.3
142.5°	651.0	650.8	650.5	650.0	649.2	648.4	647.6	646.8	647.6	648.4	649.2
145°	685.1	684.7	684.1	683.8	683.5	683.1	682.9	682.5	682.9	683.1	683.5
147.5°	717.4	716.9	716.5	716.0	715.4	714.9	714.3	713.8	714.3	714.9	715.4
150°	737.7	737.4	737.1	736.7	736.5	736.1	735.8	735.5	735.8	736.1	736.5
152.5°	755.8	755.6	755.5	755.1	754.7	754.2	753.8	753.4	753.8	754.2	754.7
155°	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5	781.5	781.5	781.5
157.5°	805.0	804.9	804.8	804.8	804.9	805.1	805.3	805.5	805.3	805.1	804.9
160°	819.2	819.2	819.2	819.3	819.7	819.9	820.3	820.6	820.3	819.9	819.7
162.5°	832.3	832.2	832.1	832.2	832.7	833.1	833.6	833.9	833.6	833.1	832.7
165°	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.2	850.8	850.3	849.9
167.5°	862.6	862.5	862.4	862.6	863.2	863.8	864.4	865.0	864.4	863.8	863.2
170°	870.0	870.0	870.0	870.4	871.0	871.6	872.3	872.9	872.3	871.6	871.0
172.5°	876.2	876.2	876.2	876.6	877.2	877.8	878.4	879.0	878.4	877.8	877.2
175°	882.6	882.6	882.6	883.0	883.6	884.2	884.8	885.4	884.8	884.2	883.6
177.5°	885.8	885.8	885.8	886.1	886.5	887.1	887.6	888.1	887.6	887.1	886.5
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1422.4	1418.4	1412.8	1404.4	1397.7	1387.1	1387.1	1388.8	1388.8	1388.2	1387.1
5°	1379.2	1368.7	1356.1	1341.4	1326.0	1310.5	1307.7	1302.1	1297.9	1295.1	1291.6
7.5°	1333.6	1315.0	1296.6	1276.0	1257.2	1241.7	1230.9	1221.9	1216.2	1210.1	1205.5
10°	1302.8	1279.7	1257.9	1236.3	1212.4	1193.5	1181.6	1173.1	1166.9	1161.3	1158.4
12.5°	1266.4	1239.9	1215.9	1195.3	1169.2	1149.8	1138.4	1134.4	1127.0	1115.3	1109.1
15°	1213.1	1188.6	1159.8	1128.3	1115.7	1091.9	1078.5	1072.3	1068.0	1058.9	1056.1
17.5°	1167.5	1135.4	1103.2	1079.7	1056.2	1036.9	1029.5	1021.6	1016.0	1008.6	1006.4
20°	1131.1	1102.4	1072.9	1047.8	1023.1	1002.2	995.9	990.2	984.6	981.1	978.3
22.5°	1094.1	1065.4	1041.0	1017.4	991.2	977.5	970.6	964.5	960.6	958.1	955.4
25°	1042.1	1016.9	989.5	968.5	947.5	938.3	934.2	930.7	927.9	924.3	923.6
27.5°	995.6	968.1	945.9	926.3	911.2	903.7	899.6	897.9	898.5	899.7	900.5
30°	960.8	935.6	917.4	900.5	886.5	879.5	878.8	878.8	881.6	882.3	883.7
32.5°	928.9	908.1	889.9	873.6	863.0	858.2	860.9	860.9	863.1	865.0	867.5
35°	882.3	864.1	850.1	836.1	827.0	829.0	830.5	831.9	835.4	839.5	842.4
37.5°	837.9	822.1	807.4	796.6	792.4	796.1	799.5	802.5	806.5	809.8	812.5
40°	805.9	794.0	780.0	770.2	771.6	773.7	776.5	780.0	783.5	785.6	788.5
42.5°	776.2	763.8	753.1	744.9	746.9	749.6	751.3	753.1	757.2	761.0	762.6
45°	730.9	721.1	711.3	706.4	707.8	709.3	710.6	712.7	716.2	719.1	719.7
47.5°	680.1	673.2	666.6	661.8	664.1	663.5	665.4	669.9	670.9	672.6	676.5
50°	647.6	641.2	633.6	632.1	632.1	632.1	632.8	638.5	638.5	641.2	644.1
52.5°	611.7	607.6	602.7	600.2	599.1	599.1	602.0	604.8	605.9	609.8	612.7
55°	558.6	554.4	550.1	548.0	546.6	548.0	553.7	555.0	558.6	560.6	562.8
57.5°	503.2	500.0	496.6	495.4	495.2	497.0	500.1	504.3	505.2	511.6	514.8
60°	466.7	461.8	459.1	459.1	457.6	464.0	462.5	469.6	470.9	475.2	480.1
62.5°	429.2	422.6	421.5	421.5	423.5	425.3	427.2	430.3	433.9	439.3	443.1
65°	368.6	365.2	370.1	369.3	367.9	372.1	372.1	375.7	379.9	384.8	392.4
67.5°	311.3	309.5	309.9	309.9	312.0	314.4	316.4	319.4	324.5	329.7	334.7
70°	272.6	274.7	271.3	274.0	276.2	276.8	278.2	282.4	288.0	291.5	297.1
72.5°	235.1	234.9	235.3	236.5	238.5	239.8	241.2	246.0	252.2	255.1	259.6
75°	180.8	180.1	182.2	182.2	185.7	187.1	188.5	190.6	196.3	200.5	203.9
77.5°	132.1	132.9	132.4	134.8	133.8	134.1	138.5	140.6	141.2	149.5	151.2
80°	99.5	100.9	101.7	102.3	103.0	101.7	106.6	108.6	108.6	113.5	117.0
82.5°	71.5	72.3	74.2	74.8	75.0	76.4	76.8	78.4	80.1	82.1	86.8
85°	35.8	37.8	38.5	37.8	38.5	37.2	39.2	39.9	40.7	40.7	40.7
87.5°	12.6	13.5	13.4	14.4	14.2	15.2	15.2	14.3	14.4	16.1	14.0
90°	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0	18.5	19.2	19.7
92.5°	21.0	22.2	23.4	24.5	25.6	26.8	27.3	27.7	28.3	28.7	28.9
95°	45.5	46.6	47.9	49.1	50.4	51.6	52.3	52.8	53.4	54.0	54.4
97.5°	76.3	77.1	78.0	78.9	79.8	80.7	81.4	82.1	82.8	83.6	83.9
100°	98.5	99.4	100.1	100.9	101.7	102.5	103.0	103.4	103.9	104.3	104.8
102.5°	122.2	123.0	123.9	125.0	126.0	127.1	127.5	128.0	128.4	128.9	129.1
105°	158.1	159.0	160.3	161.8	163.2	164.5	164.5	164.5	164.5	164.5	164.7
107.5°	200.5	200.9	201.5	202.1	202.6	203.1	203.7	204.1	204.6	205.2	205.3
110°	227.8	228.1	228.5	228.7	229.1	229.3	230.0	230.6	231.2	231.8	232.0



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.2	255.3	255.4	255.5	255.6	255.6	256.4	257.1	257.8	258.6	258.9
115°	298.2	298.3	297.9	297.7	297.3	297.0	297.1	297.3	297.5	297.7	297.7
117.5°	339.7	339.6	339.2	338.8	338.4	338.0	338.0	338.0	337.9	337.9	337.6
120°	368.4	368.5	367.7	366.8	366.1	365.3	365.2	365.0	364.9	364.7	364.4
122.5°	394.7	394.8	394.4	394.0	393.6	393.2	392.8	392.4	392.0	391.6	391.2
125°	435.5	435.6	435.2	435.0	434.6	434.4	433.7	433.1	432.5	431.9	431.2
127.5°	476.1	476.4	476.1	475.7	475.4	475.0	474.2	473.3	472.4	471.6	470.8
130°	502.7	503.1	502.7	502.2	501.8	501.2	500.6	500.1	499.4	498.8	497.9
132.5°	528.4	528.9	528.5	528.2	527.8	527.4	526.7	526.0	525.2	524.5	523.7
135°	566.3	566.8	566.6	566.4	566.2	566.1	565.5	564.9	564.3	563.7	563.2
137.5°	602.0	602.5	603.0	603.3	603.8	604.1	603.5	602.9	602.3	601.5	600.9
140°	627.1	627.5	627.7	627.9	628.0	628.1	628.0	627.9	627.7	627.5	627.0
142.5°	650.0	650.5	650.8	651.0	651.3	651.6	651.4	651.3	651.1	650.9	650.5
145°	683.8	684.1	684.7	685.1	685.5	686.0	685.9	685.7	685.5	685.4	685.0
147.5°	716.0	716.5	716.9	717.4	717.8	718.3	718.3	718.3	718.3	718.3	717.7
150°	736.7	737.1	737.4	737.7	738.0	738.3	738.3	738.3	738.3	738.3	737.9
152.5°	755.1	755.5	755.6	755.8	756.0	756.2	756.4	756.6	756.9	757.2	756.9
155°	781.5	781.6	781.8	781.9	782.1	782.2	782.8	783.5	784.1	784.7	784.4
157.5°	804.8	804.8	804.9	805.0	805.1	805.2	805.9	806.6	807.2	807.8	807.7
160°	819.3	819.2	819.2	819.2	819.2	819.2	819.9	820.7	821.5	822.2	822.3
162.5°	832.2	832.1	832.2	832.3	832.4	832.6	833.3	834.1	834.9	835.7	835.5
165°	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0	851.9	852.9	852.8
167.5°	862.6	862.4	862.5	862.6	862.7	862.8	863.8	864.8	865.7	866.7	866.7
170°	870.4	870.0	870.0	870.0	870.0	870.0	871.2	872.3	873.3	874.4	874.4
172.5°	876.6	876.2	876.2	876.2	876.2	876.2	877.2	878.2	879.1	880.0	880.0
175°	883.0	882.6	882.6	882.6	882.6	882.6	883.6	884.5	885.4	886.4	886.3
177.5°	886.1	885.8	885.8	885.8	885.8	885.8	886.5	887.3	888.1	888.8	888.8
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1383.1	1382.6	1386.5	1383.7	1386.5	1382.6	1383.1	1387.1	1388.2	1388.8	1388.8
5°	1287.4	1289.5	1282.5	1282.5	1282.5	1289.5	1287.4	1291.6	1295.1	1297.9	1302.1
7.5°	1202.2	1199.1	1199.4	1195.6	1199.4	1199.1	1202.2	1205.5	1210.1	1216.2	1221.9
10°	1150.0	1145.8	1144.4	1145.1	1144.4	1145.8	1150.0	1158.4	1161.3	1166.9	1173.1
12.5°	1106.9	1106.0	1096.8	1096.9	1096.8	1106.0	1106.9	1109.1	1115.3	1127.0	1134.4
15°	1056.1	1042.9	1041.4	1045.6	1041.4	1042.9	1056.1	1056.1	1058.9	1068.0	1072.3
17.5°	1005.2	998.3	998.6	996.6	998.6	998.3	1005.2	1006.4	1008.6	1016.0	1021.6
20°	978.3	974.1	973.4	968.5	973.4	974.1	978.3	978.3	981.1	984.6	990.2
22.5°	953.7	952.3	952.7	947.3	952.7	952.3	953.7	955.4	958.1	960.6	964.5
25°	923.0	926.5	923.6	923.6	923.6	926.5	923.0	923.6	924.3	927.9	930.7
27.5°	902.2	902.1	900.7	900.7	900.7	902.1	902.2	900.5	899.7	898.5	897.9
30°	886.5	885.8	887.3	887.3	887.3	885.8	886.5	883.7	882.3	881.6	878.8
32.5°	870.8	871.8	872.1	872.6	872.1	871.8	870.8	867.5	865.0	863.1	860.9
35°	846.6	847.3	849.4	848.0	849.4	847.3	846.6	842.4	839.5	835.4	831.9
37.5°	813.8	817.0	816.3	817.4	816.3	817.0	813.8	812.5	809.8	806.5	802.5
40°	789.1	791.2	790.5	790.5	790.5	791.2	789.1	788.5	785.6	783.5	780.0
42.5°	763.9	765.4	763.6	762.5	763.6	765.4	763.9	762.6	761.0	757.2	753.1
45°	722.6	721.1	723.3	720.4	723.3	721.1	722.6	719.7	719.1	716.2	712.7
47.5°	676.3	677.7	678.2	680.4	678.2	677.7	676.3	676.5	672.6	670.9	669.9
50°	645.4	649.6	649.6	649.0	649.6	649.6	645.4	644.1	641.2	638.5	638.5
52.5°	615.2	617.2	619.9	619.8	619.9	617.2	615.2	612.7	609.8	605.9	604.8
55°	568.4	569.8	571.1	571.9	571.1	569.8	568.4	562.8	560.6	558.6	555.0
57.5°	519.9	519.3	522.6	523.6	522.6	519.3	519.9	514.8	511.6	505.2	504.3
60°	485.6	485.6	491.2	493.4	491.2	485.6	485.6	480.1	475.2	470.9	469.6
62.5°	449.2	451.5	457.1	454.1	457.1	451.5	449.2	443.1	439.3	433.9	430.3
65°	395.9	401.5	400.8	403.7	400.8	401.5	395.9	392.4	384.8	379.9	375.7
67.5°	340.3	343.8	348.8	349.3	348.8	343.8	340.3	334.7	329.7	324.5	319.4
70°	302.7	306.2	309.1	311.1	309.1	306.2	302.7	297.1	291.5	288.0	282.4
72.5°	266.4	268.1	274.8	271.9	274.8	268.1	266.4	259.6	255.1	252.2	246.0
75°	208.8	213.7	217.9	215.9	217.9	213.7	208.8	203.9	200.5	196.3	190.6
77.5°	154.4	159.3	161.3	159.5	161.3	159.3	154.4	151.2	149.5	141.2	140.6
80°	122.0	121.3	125.5	124.8	125.5	121.3	122.0	117.0	113.5	108.6	108.6
82.5°	89.4	88.7	90.7	91.1	90.7	88.7	89.4	86.8	82.1	80.1	78.4
85°	43.4	45.6	42.7	42.1	42.7	45.6	43.4	40.7	40.7	40.7	39.9
87.5°	14.1	14.2	13.6	13.2	13.6	14.2	14.1	14.0	16.1	14.4	14.3
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0
92.5°	28.7	28.5	28.4	28.2	28.4	28.5	28.7	28.9	28.7	28.3	27.7
95°	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.0	53.4	52.8
97.5°	83.8	83.8	83.7	83.6	83.7	83.8	83.8	83.9	83.6	82.8	82.1
100°	105.0	105.3	105.7	105.9	105.7	105.3	105.0	104.8	104.3	103.9	103.4
102.5°	129.0	128.9	128.9	128.9	128.9	128.9	129.0	129.1	128.9	128.4	128.0
105°	165.0	165.3	165.6	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5
107.5°	205.1	204.9	204.7	204.6	204.7	204.9	205.1	205.3	205.2	204.6	204.1
110°	231.7	231.4	231.0	230.8	231.0	231.4	231.7	232.0	231.8	231.2	230.6



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	258.9	258.8	258.7	258.7	258.7	258.8	258.9	258.9	258.6	257.8	257.1
115°	297.5	297.3	297.1	297.0	297.1	297.3	297.5	297.7	297.7	297.5	297.3
117.5°	337.2	336.8	336.4	335.9	336.4	336.8	337.2	337.6	337.9	337.9	338.0
120°	364.2	363.8	363.6	363.2	363.6	363.8	364.2	364.4	364.7	364.9	365.0
122.5°	390.7	390.3	389.9	389.4	389.9	390.3	390.7	391.2	391.6	392.0	392.4
125°	430.6	430.0	429.4	428.7	429.4	430.0	430.6	431.2	431.9	432.5	433.1
127.5°	470.1	469.4	468.7	468.0	468.7	469.4	470.1	470.8	471.6	472.4	473.3
130°	496.9	495.8	494.7	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.1
132.5°	522.9	522.0	521.2	520.4	521.2	522.0	522.9	523.7	524.5	525.2	526.0
135°	562.8	562.6	562.2	562.0	562.2	562.6	562.8	563.2	563.7	564.3	564.9
137.5°	600.4	599.8	599.2	598.6	599.2	599.8	600.4	600.9	601.5	602.3	602.9
140°	625.8	624.7	623.7	622.6	623.7	624.7	625.8	627.0	627.5	627.7	627.9
142.5°	649.6	648.8	647.9	647.1	647.9	648.8	649.6	650.5	650.9	651.1	651.3
145°	684.4	683.8	683.1	682.5	683.1	683.8	684.4	685.0	685.4	685.5	685.7
147.5°	716.8	715.9	715.0	714.1	715.0	715.9	716.8	717.7	718.3	718.3	718.3
150°	736.9	736.0	735.0	734.1	735.0	736.0	736.9	737.9	738.3	738.3	738.3
152.5°	756.1	755.3	754.5	753.7	754.5	755.3	756.1	756.9	757.2	756.9	756.6
155°	783.4	782.3	781.2	780.2	781.2	782.3	783.4	784.4	784.7	784.1	783.5
157.5°	806.9	806.0	805.1	804.2	805.1	806.0	806.9	807.7	807.8	807.2	806.6
160°	821.7	821.1	820.5	819.8	820.5	821.1	821.7	822.3	822.2	821.5	820.7
162.5°	834.6	833.6	832.6	831.6	832.6	833.6	834.6	835.5	835.7	834.9	834.1
165°	851.8	850.6	849.5	848.5	849.5	850.6	851.8	852.8	852.9	851.9	851.0
167.5°	865.7	864.8	863.8	862.8	863.8	864.8	865.7	866.7	866.7	865.7	864.8
170°	873.3	872.3	871.2	870.0	871.2	872.3	873.3	874.4	874.4	873.3	872.3
172.5°	878.9	877.8	876.7	875.7	876.7	877.8	878.9	880.0	880.0	879.1	878.2
175°	885.2	884.1	883.0	881.9	883.0	884.1	885.2	886.3	886.4	885.4	884.5
177.5°	887.9	887.0	886.2	885.3	886.2	887.0	887.9	888.8	888.8	888.1	887.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1387.1	1387.1	1397.7	1404.4	1412.8	1418.4	1422.4	1426.3	1433.1	1442.0	1452.1
5°	1307.7	1310.5	1326.0	1341.4	1356.1	1368.7	1379.2	1391.8	1407.2	1426.1	1447.2
7.5°	1230.9	1241.7	1257.2	1276.0	1296.6	1315.0	1333.6	1354.4	1376.1	1404.0	1433.4
10°	1181.6	1193.5	1212.4	1236.3	1257.9	1279.7	1302.8	1325.3	1352.5	1385.5	1423.3
12.5°	1138.4	1149.8	1169.2	1195.3	1215.9	1239.9	1266.4	1295.6	1326.2	1365.9	1408.8
15°	1078.5	1091.9	1115.7	1128.3	1159.8	1188.6	1213.1	1255.2	1294.4	1335.1	1384.8
17.5°	1029.5	1036.9	1056.2	1079.7	1103.2	1135.4	1167.5	1202.6	1241.7	1291.5	1353.7
20°	995.9	1002.2	1023.1	1047.8	1072.9	1102.4	1131.1	1166.2	1210.3	1262.8	1330.2
22.5°	970.6	977.5	991.2	1017.4	1041.0	1065.4	1094.1	1135.9	1182.9	1234.3	1307.2
25°	934.2	938.3	947.5	968.5	989.5	1016.9	1042.1	1081.4	1129.7	1190.0	1262.8
27.5°	899.6	903.7	911.2	926.3	945.9	968.1	995.6	1028.9	1078.0	1143.4	1220.8
30°	878.8	879.5	886.5	900.5	917.4	935.6	960.8	998.6	1044.9	1111.5	1192.8
32.5°	860.9	858.2	863.0	873.6	889.9	908.1	928.9	966.2	1010.8	1076.2	1159.7
35°	830.5	829.0	827.0	836.1	850.1	864.1	882.3	910.3	960.8	1021.8	1109.4
37.5°	799.5	796.1	792.4	796.6	807.4	822.1	837.9	862.8	906.3	973.4	1057.2
40°	776.5	773.7	771.6	770.2	780.0	794.0	805.9	829.7	870.4	934.2	1016.9
42.5°	751.3	749.6	746.9	744.9	753.1	763.8	776.2	797.3	837.9	897.8	976.0
45°	710.6	709.3	707.8	706.4	711.3	721.1	730.9	746.4	781.4	839.5	910.3
47.5°	665.4	663.5	664.1	661.8	666.6	673.2	680.1	696.6	730.2	777.2	828.9
50°	632.8	632.1	632.1	632.1	633.6	641.2	647.6	660.1	691.0	738.0	775.1
52.5°	602.0	599.1	599.1	600.2	602.7	607.6	611.7	625.4	652.3	690.9	724.6
55°	553.7	548.0	546.6	548.0	550.1	554.4	558.6	569.8	592.9	621.6	641.2
57.5°	500.1	497.0	495.2	495.4	496.6	500.0	503.2	515.4	533.6	548.6	561.2
60°	462.5	464.0	457.6	459.1	459.1	461.8	466.7	474.5	489.9	500.3	513.0
62.5°	427.2	425.3	423.5	421.5	421.5	422.6	429.2	435.2	448.4	453.9	463.7
65°	372.1	372.1	367.9	369.3	370.1	365.2	368.6	375.7	384.1	386.1	395.3
67.5°	316.4	314.4	312.0	309.9	309.9	309.5	311.3	314.8	321.1	321.8	328.9
70°	278.2	276.8	276.2	274.0	271.3	274.7	272.6	276.2	279.6	280.4	284.5
72.5°	241.2	239.8	238.5	236.5	235.3	234.9	235.1	239.2	241.5	240.5	245.3
75°	188.5	187.1	185.7	182.2	182.2	180.1	180.8	183.6	186.5	184.3	188.5
77.5°	138.5	134.1	133.8	134.8	132.4	132.9	132.1	131.6	132.9	133.0	136.8
80°	106.6	101.7	103.0	102.3	101.7	100.9	99.5	100.2	100.9	101.7	103.7
82.5°	76.8	76.4	75.0	74.8	74.2	72.3	71.5	72.8	73.5	73.0	74.5
85°	39.2	37.2	38.5	37.8	38.5	37.8	35.8	35.8	37.2	36.5	37.8
87.5°	15.2	15.2	14.2	14.4	13.4	13.5	12.6	12.8	13.1	12.8	13.6
90°	17.4	16.8	14.7	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7
92.5°	27.3	26.8	25.6	24.5	23.4	22.2	21.0	20.1	19.0	17.9	16.9
95°	52.3	51.6	50.4	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1
97.5°	81.4	80.7	79.8	78.9	78.0	77.1	76.3	75.4	74.6	73.8	73.0
100°	103.0	102.5	101.7	100.9	100.1	99.4	98.5	97.6	96.7	95.8	94.8
102.5°	127.5	127.1	126.0	125.0	123.9	123.0	122.2	121.6	121.0	120.5	119.9
105°	164.5	164.5	163.2	161.8	160.3	159.0	158.1	157.8	157.5	157.2	156.9
107.5°	203.7	203.1	202.6	202.1	201.5	200.9	200.5	200.4	200.2	200.0	199.8
110°	230.0	229.3	229.1	228.7	228.5	228.1	227.8	227.5	227.2	226.9	226.6



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	256.4	255.6	255.6	255.5	255.4	255.3	255.2	255.0	254.9	254.7	254.5
115°	297.1	297.0	297.3	297.7	297.9	298.3	298.2	297.7	297.2	296.8	296.3
117.5°	338.0	338.0	338.4	338.8	339.2	339.6	339.7	339.3	339.0	338.8	338.4
120°	365.2	365.3	366.1	366.8	367.7	368.5	368.4	367.4	366.5	365.5	364.6
122.5°	392.8	393.2	393.6	394.0	394.4	394.8	394.7	394.0	393.3	392.6	392.0
125°	433.7	434.4	434.6	435.0	435.2	435.6	435.5	435.1	434.5	434.1	433.6
127.5°	474.2	475.0	475.4	475.7	476.1	476.4	476.1	475.1	474.1	473.1	472.2
130°	500.6	501.2	501.8	502.2	502.7	503.1	502.7	501.5	500.2	499.0	497.8
132.5°	526.7	527.4	527.8	528.2	528.5	528.9	528.4	527.2	525.9	524.7	523.4
135°	565.5	566.1	566.2	566.4	566.6	566.8	566.3	565.4	564.5	563.6	562.6
137.5°	603.5	604.1	603.8	603.3	603.0	602.5	602.0	601.2	600.4	599.7	598.9
140°	628.0	628.1	628.0	627.9	627.7	627.5	627.1	626.3	625.5	624.7	623.9
142.5°	651.4	651.6	651.3	651.0	650.8	650.5	650.0	649.2	648.4	647.6	646.8
145°	685.9	686.0	685.5	685.1	684.7	684.1	683.8	683.5	683.1	682.9	682.5
147.5°	718.3	718.3	717.8	717.4	716.9	716.5	716.0	715.4	714.9	714.3	713.8
150°	738.3	738.3	738.0	737.7	737.4	737.1	736.7	736.5	736.1	735.8	735.5
152.5°	756.4	756.2	756.0	755.8	755.6	755.5	755.1	754.7	754.2	753.8	753.4
155°	782.8	782.2	782.1	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5
157.5°	805.9	805.2	805.1	805.0	804.9	804.8	804.8	804.9	805.1	805.3	805.5
160°	819.9	819.2	819.2	819.2	819.2	819.2	819.3	819.7	819.9	820.3	820.6
162.5°	833.3	832.6	832.4	832.3	832.2	832.1	832.2	832.7	833.1	833.6	833.9
165°	850.1	849.2	849.2	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.2
167.5°	863.8	862.8	862.7	862.6	862.5	862.4	862.6	863.2	863.8	864.4	865.0
170°	871.2	870.0	870.0	870.0	870.0	870.0	870.4	871.0	871.6	872.3	872.9
172.5°	877.2	876.2	876.2	876.2	876.2	876.2	876.6	877.2	877.8	878.4	879.0
175°	883.6	882.6	882.6	882.6	882.6	882.6	883.0	883.6	884.2	884.8	885.4
177.5°	886.5	885.8	885.8	885.8	885.8	885.8	886.1	886.5	887.1	887.6	888.1
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1455.5	1458.2	1467.8	1474.5	1482.4	1486.8	1491.3	1494.7	1499.1	1500.3	1516.5
5°	1461.9	1476.0	1500.5	1518.7	1541.1	1565.6	1582.4	1590.2	1610.4	1627.3	1660.9
7.5°	1460.1	1490.0	1527.0	1565.3	1606.5	1644.7	1677.8	1717.0	1744.9	1786.8	1828.2
10°	1458.4	1498.3	1546.0	1595.1	1652.5	1705.8	1753.5	1806.7	1850.8	1909.0	1958.7
12.5°	1453.3	1501.7	1567.9	1625.9	1695.7	1769.2	1839.8	1908.2	1947.3	2044.2	2090.0
15°	1440.9	1498.3	1581.0	1669.4	1765.3	1852.3	1942.0	2013.5	2129.0	2213.9	2267.8
17.5°	1417.0	1497.5	1595.6	1702.1	1818.9	1933.4	2035.1	2143.5	2266.2	2368.7	2478.1
20°	1405.9	1494.2	1603.5	1721.2	1842.5	1972.1	2087.8	2218.0	2352.0	2452.8	2593.0
22.5°	1385.1	1485.1	1602.9	1734.1	1863.8	1997.9	2133.2	2264.6	2419.2	2558.2	2691.7
25°	1351.2	1463.3	1585.3	1731.7	1883.8	2018.4	2180.2	2354.7	2516.0	2694.7	2827.8
27.5°	1315.5	1435.3	1557.5	1693.7	1857.3	2017.0	2220.6	2417.8	2614.9	2769.2	2867.7
30°	1288.1	1404.4	1530.6	1667.9	1829.8	2019.7	2247.5	2462.6	2654.7	2787.1	2842.5
32.5°	1258.4	1376.4	1488.0	1632.1	1804.6	2018.0	2264.3	2489.0	2656.9	2745.1	2734.3
35°	1211.7	1310.5	1419.2	1557.9	1761.1	2005.7	2274.1	2491.4	2594.4	2575.5	2432.5
37.5°	1144.4	1227.5	1334.5	1486.4	1710.7	1979.8	2254.5	2417.5	2410.8	2256.7	2049.6
40°	1102.4	1173.1	1276.2	1436.0	1671.4	1963.0	2223.7	2329.5	2239.8	2024.6	1776.6
42.5°	1047.4	1112.6	1215.7	1379.9	1628.3	1928.8	2164.8	2195.5	2020.0	1772.4	1545.0
45°	962.2	1019.7	1126.2	1295.8	1563.5	1854.3	2021.2	1946.2	1709.9	1454.2	1281.1
47.5°	870.7	930.4	1032.9	1207.1	1469.9	1742.4	1821.9	1662.3	1419.9	1212.4	1053.5
50°	813.0	870.4	970.6	1146.6	1406.5	1650.4	1683.4	1477.3	1254.5	1072.3	941.9
52.5°	754.7	808.8	907.3	1083.7	1332.6	1543.9	1523.6	1313.6	1108.7	953.4	851.0
55°	667.9	719.1	813.0	978.3	1204.7	1372.2	1298.6	1098.1	928.5	808.1	730.2
57.5°	590.2	639.3	720.3	869.7	1066.5	1181.6	1088.0	919.1	784.2	691.4	633.4
60°	537.5	580.9	658.1	796.8	967.9	1055.4	963.0	813.7	700.1	625.8	574.0
62.5°	487.6	525.5	596.9	722.8	871.4	944.9	851.3	725.1	628.4	562.5	518.4
65°	412.1	446.4	509.5	607.6	729.5	778.6	698.0	595.7	520.7	471.6	442.2
67.5°	343.1	372.3	426.8	504.0	593.7	629.5	568.1	488.9	432.4	393.0	369.6
70°	297.1	322.4	365.2	431.7	513.0	540.3	482.9	417.7	376.3	344.8	323.1
72.5°	258.4	277.0	315.8	367.2	435.1	456.8	416.7	359.4	320.8	297.1	279.9
75°	196.9	212.3	237.6	278.9	325.9	338.5	308.4	272.6	246.6	229.9	216.5
77.5°	142.0	153.4	171.6	197.1	229.6	240.9	221.9	198.0	179.1	167.7	160.3
80°	107.2	116.4	131.8	152.8	172.4	178.7	167.5	149.3	136.0	129.7	123.3
82.5°	79.2	84.4	93.6	107.9	121.4	128.9	119.3	108.3	101.2	95.4	93.1
85°	39.9	42.7	47.0	52.5	61.0	63.8	60.3	57.4	53.2	49.8	49.8
87.5°	15.1	15.3	17.3	18.7	21.4	23.5	23.3	22.6	22.4	21.9	21.6
90°	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0
92.5°	17.9	19.0	20.1	21.0	22.2	23.4	24.5	25.6	26.8	27.3	27.7
95°	42.2	43.3	44.4	45.5	46.6	47.9	49.1	50.4	51.6	52.3	52.8
97.5°	73.8	74.6	75.4	76.3	77.1	78.0	78.9	79.8	80.7	81.4	82.1
100°	95.8	96.7	97.6	98.5	99.4	100.1	100.9	101.7	102.5	103.0	103.4
102.5°	120.5	121.0	121.6	122.2	123.0	123.9	125.0	126.0	127.1	127.5	128.0
105°	157.2	157.5	157.8	158.1	159.0	160.3	161.8	163.2	164.5	164.5	164.5
107.5°	200.0	200.2	200.4	200.5	200.9	201.5	202.1	202.6	203.1	203.7	204.1
110°	226.9	227.2	227.5	227.8	228.1	228.5	228.7	229.1	229.3	230.0	230.6



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	254.7	254.9	255.0	255.2	255.3	255.4	255.5	255.6	255.6	256.4	257.1
115°	296.8	297.2	297.7	298.2	298.3	297.9	297.7	297.3	297.0	297.1	297.3
117.5°	338.8	339.0	339.3	339.7	339.6	339.2	338.8	338.4	338.0	338.0	338.0
120°	365.5	366.5	367.4	368.4	368.5	367.7	366.8	366.1	365.3	365.2	365.0
122.5°	392.6	393.3	394.0	394.7	394.8	394.4	394.0	393.6	393.2	392.8	392.4
125°	434.1	434.5	435.1	435.5	435.6	435.2	435.0	434.6	434.4	433.7	433.1
127.5°	473.1	474.1	475.1	476.1	476.4	476.1	475.7	475.4	475.0	474.2	473.3
130°	499.0	500.2	501.5	502.7	503.1	502.7	502.2	501.8	501.2	500.6	500.1
132.5°	524.7	525.9	527.2	528.4	528.9	528.5	528.2	527.8	527.4	526.7	526.0
135°	563.6	564.5	565.4	566.3	566.8	566.6	566.4	566.2	566.1	565.5	564.9
137.5°	599.7	600.4	601.2	602.0	602.5	603.0	603.3	603.8	604.1	603.5	602.9
140°	624.7	625.5	626.3	627.1	627.5	627.7	627.9	628.0	628.1	628.0	627.9
142.5°	647.6	648.4	649.2	650.0	650.5	650.8	651.0	651.3	651.6	651.4	651.3
145°	682.9	683.1	683.5	683.8	684.1	684.7	685.1	685.5	686.0	685.9	685.7
147.5°	714.3	714.9	715.4	716.0	716.5	716.9	717.4	717.8	718.3	718.3	718.3
150°	735.8	736.1	736.5	736.7	737.1	737.4	737.7	738.0	738.3	738.3	738.3
152.5°	753.8	754.2	754.7	755.1	755.5	755.6	755.8	756.0	756.2	756.4	756.6
155°	781.5	781.5	781.5	781.5	781.6	781.8	781.9	782.1	782.2	782.8	783.5
157.5°	805.3	805.1	804.9	804.8	804.8	804.9	805.0	805.1	805.2	805.9	806.6
160°	820.3	819.9	819.7	819.3	819.2	819.2	819.2	819.2	819.2	819.9	820.7
162.5°	833.6	833.1	832.7	832.2	832.1	832.2	832.3	832.4	832.6	833.3	834.1
165°	850.8	850.3	849.9	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0
167.5°	864.4	863.8	863.2	862.6	862.4	862.5	862.6	862.7	862.8	863.8	864.8
170°	872.3	871.6	871.0	870.4	870.0	870.0	870.0	870.0	870.0	871.2	872.3
172.5°	878.4	877.8	877.2	876.6	876.2	876.2	876.2	876.2	876.2	877.2	878.2
175°	884.8	884.2	883.6	883.0	882.6	882.6	882.6	882.6	882.6	883.6	884.5
177.5°	887.6	887.1	886.5	886.1	885.8	885.8	885.8	885.8	885.8	886.5	887.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1522.2	1522.7	1528.9	1533.4	1531.2	1533.9	1535.1
5°	1663.0	1688.3	1701.6	1711.4	1712.1	1712.8	1718.4
7.5°	1862.8	1889.8	1909.6	1939.6	1948.6	1958.7	1955.8
10°	2008.6	2048.4	2082.9	2101.0	2120.7	2149.4	2126.3
12.5°	2144.7	2215.5	2267.8	2296.2	2314.6	2320.4	2309.1
15°	2369.5	2461.9	2511.7	2510.3	2573.4	2600.8	2558.0
17.5°	2575.5	2660.9	2729.3	2764.3	2816.8	2828.5	2823.2
20°	2701.6	2794.9	2848.1	2908.4	2935.7	2960.2	2964.4
22.5°	2810.4	2894.0	2951.3	3001.4	3024.3	3035.9	3043.0
25°	2922.4	2988.3	3022.6	3040.1	3046.4	3045.0	3035.9
27.5°	2914.6	2919.7	2881.9	2844.7	2811.6	2774.1	2761.2
30°	2839.0	2780.1	2675.0	2615.5	2527.8	2458.4	2486.4
32.5°	2640.0	2522.8	2404.8	2274.6	2166.8	2136.1	2105.2
35°	2253.1	2047.1	1926.5	1786.4	1730.3	1674.3	1635.7
37.5°	1822.8	1663.5	1520.5	1428.8	1372.6	1337.1	1318.1
40°	1576.1	1432.4	1314.7	1240.5	1197.7	1157.7	1152.2
42.5°	1379.4	1245.8	1157.2	1098.1	1056.9	1040.0	1027.7
45°	1129.7	1036.5	977.0	934.9	907.6	897.1	883.1
47.5°	956.2	890.3	845.6	817.0	796.4	788.5	787.5
50°	859.2	804.5	771.6	749.1	733.1	730.2	719.1
52.5°	786.3	739.0	713.3	693.7	682.1	674.2	670.8
55°	682.6	651.0	627.9	616.7	607.6	599.9	599.9
57.5°	597.3	570.9	555.6	546.1	543.2	537.8	534.3
60°	544.6	522.1	510.2	501.8	496.1	496.9	490.5
62.5°	492.9	478.4	467.0	458.6	451.9	452.0	452.5
65°	419.8	408.6	400.2	397.3	393.2	388.3	389.7
67.5°	355.7	345.2	338.7	333.9	332.4	329.8	333.9
70°	309.8	302.0	297.1	292.9	291.5	292.2	295.8
72.5°	267.7	262.3	259.0	257.1	254.0	254.1	256.5
75°	210.3	206.1	203.2	201.2	200.5	200.5	200.5
77.5°	154.4	153.5	152.2	149.1	149.3	150.1	150.3
80°	122.0	119.8	119.1	117.7	115.7	114.2	117.7
82.5°	91.1	89.0	88.3	88.0	84.8	84.5	87.5
85°	49.0	47.0	47.6	47.0	47.0	46.3	46.3
87.5°	21.1	20.7	20.2	20.8	20.3	19.8	21.0
90°	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	28.3	28.7	28.9	28.7	28.5	28.4	28.2
95°	53.4	54.0	54.4	54.4	54.4	54.4	54.4
97.5°	82.8	83.6	83.9	83.8	83.8	83.7	83.6
100°	103.9	104.3	104.8	105.0	105.3	105.7	105.9
102.5°	128.4	128.9	129.1	129.0	128.9	128.9	128.9
105°	164.5	164.5	164.7	165.0	165.3	165.6	165.9
107.5°	204.6	205.2	205.3	205.1	204.9	204.7	204.6
110°	231.2	231.8	232.0	231.7	231.4	231.0	230.8



TEST NUMBER: P332064-940

CATALOG NUMBER: S123DIP-S1165D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	257.8	258.6	258.9	258.9	258.8	258.7	258.7
115°	297.5	297.7	297.7	297.5	297.3	297.1	297.0
117.5°	337.9	337.9	337.6	337.2	336.8	336.4	335.9
120°	364.9	364.7	364.4	364.2	363.8	363.6	363.2
122.5°	392.0	391.6	391.2	390.7	390.3	389.9	389.4
125°	432.5	431.9	431.2	430.6	430.0	429.4	428.7
127.5°	472.4	471.6	470.8	470.1	469.4	468.7	468.0
130°	499.4	498.8	497.9	496.9	495.8	494.7	493.6
132.5°	525.2	524.5	523.7	522.9	522.0	521.2	520.4
135°	564.3	563.7	563.2	562.8	562.6	562.2	562.0
137.5°	602.3	601.5	600.9	600.4	599.8	599.2	598.6
140°	627.7	627.5	627.0	625.8	624.7	623.7	622.6
142.5°	651.1	650.9	650.5	649.6	648.8	647.9	647.1
145°	685.5	685.4	685.0	684.4	683.8	683.1	682.5
147.5°	718.3	718.3	717.7	716.8	715.9	715.0	714.1
150°	738.3	738.3	737.9	736.9	736.0	735.0	734.1
152.5°	756.9	757.2	756.9	756.1	755.3	754.5	753.7
155°	784.1	784.7	784.4	783.4	782.3	781.2	780.2
157.5°	807.2	807.8	807.7	806.9	806.0	805.1	804.2
160°	821.5	822.2	822.3	821.7	821.1	820.5	819.8
162.5°	834.9	835.7	835.5	834.6	833.6	832.6	831.6
165°	851.9	852.9	852.8	851.8	850.6	849.5	848.5
167.5°	865.7	866.7	866.7	865.7	864.8	863.8	862.8
170°	873.3	874.4	874.4	873.3	872.3	871.2	870.0
172.5°	879.1	880.0	880.0	878.9	877.8	876.7	875.7
175°	885.4	886.4	886.3	885.2	884.1	883.0	881.9
177.5°	888.1	888.8	888.8	887.9	887.0	886.2	885.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5

(END OF REPORT)