

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331899-940

Luminaire Tested: **S123DIP-S340D1025U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331899-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4400.2 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331899-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331899-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31
2	85	77	71	67	75	69	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19
5	65	53	45	40	58	48	41	36	38	33	29	29	25	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P331899-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	1.0
10°-20°	128.5	2.9
20°-30°	189.9	4.3
30°-40°	221.8	5.0
40°-50°	223.0	5.1
50°-60°	195.8	4.5
60°-70°	145.9	3.3
70°-80°	83.1	1.9
80°-90°	27.2	0.6
90°-100°	73.8	1.7
100°-110°	220.9	5.0
110°-120°	375.8	8.5
120°-130°	494.3	11.2
130°-140°	555.6	12.6
140°-150°	546.1	12.4
150°-160°	459.7	10.4
160°-170°	306.0	7.0
170°-180°	107.2	2.4
0°-30°	363.9	8.3
0°-40°	585.7	13.3
0°-60°	1004.5	22.8
0°-90°	1260.7	28.7
90°-120°	670.6	15.2
90°-150°	2266.5	51.5
90°-180°	3139.0	71.3
0°-180°	4400.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	1	10	21	25	27	4
95°	52	59	66	69	70	59
105°	200	202	210	210	212	214
115°	378	381	379	380	379	374
125°	554	556	555	551	547	494
135°	718	723	723	719	718	553
145°	871	873	876	875	871	544
155°	998	998	999	1002	996	459
165°	1087	1084	1084	1089	1083	306
175°	1130	1127	1127	1132	1126	107
180°	1133	1133	1133	1133	1133	



TEST NUMBER: P331899-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.8	9.0	9.2	9.4	9.5	9.8	10.3	10.7	11.1	11.6	11.7
90°	0.9	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1
92.5°	21.6	22.9	24.3	25.6	26.9	28.4	29.8	31.2	32.7	34.2	34.8
95°	52.5	53.9	55.3	56.7	58.1	59.6	61.1	62.7	64.3	65.9	66.7
97.5°	93.3	94.3	95.3	96.4	97.4	98.4	99.6	100.8	101.9	103.1	104.0
100°	121.1	122.3	123.4	124.6	125.8	126.9	127.9	128.9	129.8	130.8	131.4
102.5°	153.1	153.8	154.5	155.2	156.0	156.9	158.3	159.5	160.9	162.2	162.7
105°	200.3	200.6	201.1	201.4	201.9	203.0	204.7	206.5	208.3	210.1	210.1
107.5°	255.1	255.4	255.6	255.8	256.1	256.5	257.3	258.0	258.7	259.4	260.0
110°	289.3	289.7	290.1	290.4	290.9	291.2	291.7	292.0	292.5	292.8	293.6



TEST NUMBER: P331899-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	324.9	325.1	325.4	325.6	325.8	326.0	326.1	326.2	326.3	326.3	327.3
115°	378.3	378.9	379.5	380.0	380.7	380.8	380.4	380.0	379.6	379.2	379.4
117.5°	432.0	432.5	432.8	433.3	433.6	433.5	433.1	432.6	432.0	431.5	431.5
120°	465.6	466.7	467.9	469.1	470.3	470.4	469.4	468.4	467.4	466.5	466.2
122.5°	500.4	501.3	502.1	503.0	503.9	504.1	503.5	503.0	502.6	502.0	501.5
125°	553.7	554.3	554.8	555.4	556.0	556.2	555.7	555.4	554.9	554.6	553.8
127.5°	602.8	604.0	605.3	606.5	607.9	608.2	607.8	607.4	607.0	606.5	605.4
130°	635.5	637.1	638.7	640.2	641.9	642.4	641.8	641.1	640.6	640.0	639.2
132.5°	668.3	669.9	671.5	673.1	674.7	675.2	674.8	674.3	673.9	673.4	672.5
135°	718.4	719.5	720.7	721.8	723.1	723.5	723.4	723.2	723.0	722.7	722.0
137.5°	764.6	765.6	766.6	767.6	768.6	769.3	769.8	770.3	770.9	771.3	770.5
140°	796.7	797.6	798.6	799.6	800.6	801.2	801.4	801.6	801.8	802.0	801.8
142.5°	825.8	826.8	827.9	828.8	829.8	830.5	830.8	831.2	831.5	831.9	831.7
145°	871.4	871.8	872.2	872.6	873.0	873.5	874.1	874.7	875.3	875.8	875.7
147.5°	911.3	912.0	912.8	913.5	914.2	914.8	915.3	915.9	916.4	917.0	917.0
150°	939.1	939.5	939.9	940.2	940.7	941.0	941.5	941.8	942.3	942.6	942.6
152.5°	961.9	962.4	963.0	963.5	964.0	964.5	964.7	964.9	965.2	965.5	965.7
155°	997.8	997.8	997.8	997.8	997.8	997.9	998.1	998.3	998.5	998.7	999.5
157.5°	1028.4	1028.2	1028.0	1027.7	1027.5	1027.4	1027.6	1027.8	1028.0	1028.1	1028.9
160°	1047.7	1047.2	1046.9	1046.5	1046.1	1045.9	1045.9	1045.9	1045.9	1045.9	1046.9
162.5°	1064.8	1064.2	1063.6	1063.1	1062.6	1062.4	1062.5	1062.7	1062.8	1063.0	1064.0
165°	1086.8	1086.2	1085.7	1085.0	1084.5	1084.1	1084.1	1084.1	1084.1	1084.1	1085.3
167.5°	1104.5	1103.7	1102.9	1102.1	1101.3	1101.0	1101.2	1101.3	1101.4	1101.6	1102.9
170°	1114.5	1113.7	1112.9	1112.1	1111.3	1110.9	1110.9	1110.9	1110.9	1110.9	1112.2
172.5°	1122.2	1121.5	1120.7	1119.9	1119.1	1118.7	1118.7	1118.7	1118.7	1118.7	1119.9
175°	1130.4	1129.6	1128.8	1128.1	1127.3	1126.9	1126.9	1126.9	1126.9	1126.9	1128.1
177.5°	1133.8	1133.2	1132.6	1131.9	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1131.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P331899-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	11.8	11.9	11.9	12.0	12.1	12.1	12.2	12.3
90°	22.9	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	35.5	36.1	36.7	36.9	36.6	36.5	36.2	35.9
95°	67.4	68.2	69.0	69.5	69.5	69.5	69.5	69.5
97.5°	104.9	105.8	106.7	107.1	107.1	107.0	106.9	106.8
100°	132.1	132.6	133.2	133.8	134.1	134.5	134.9	135.3
102.5°	163.4	164.0	164.5	164.8	164.7	164.6	164.6	164.5
105°	210.1	210.1	210.1	210.3	210.6	211.1	211.4	211.9
107.5°	260.6	261.3	261.9	262.1	261.9	261.6	261.4	261.2
110°	294.4	295.2	296.0	296.2	295.8	295.4	295.1	294.6



TEST NUMBER: P331899-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	328.2	329.1	330.1	330.6	330.5	330.4	330.3	330.2
115°	379.6	379.8	380.0	380.0	379.8	379.6	379.4	379.2
117.5°	431.4	431.4	431.4	431.1	430.5	430.0	429.4	428.8
120°	466.0	465.8	465.7	465.3	464.9	464.6	464.1	463.8
122.5°	501.0	500.5	500.0	499.4	498.9	498.3	497.8	497.2
125°	552.9	552.1	551.3	550.5	549.8	549.0	548.2	547.4
127.5°	604.3	603.2	602.1	601.1	600.2	599.2	598.3	597.4
130°	638.4	637.6	636.9	635.7	634.4	632.9	631.6	630.2
132.5°	671.5	670.7	669.7	668.7	667.6	666.6	665.5	664.4
135°	721.2	720.4	719.6	719.0	718.6	718.2	717.8	717.5
137.5°	769.7	768.9	768.0	767.2	766.5	765.7	765.0	764.3
140°	801.6	801.4	801.2	800.4	799.1	797.6	796.3	794.9
142.5°	831.5	831.3	831.1	830.5	829.4	828.3	827.2	826.2
145°	875.5	875.3	875.0	874.6	873.8	873.0	872.2	871.4
147.5°	917.0	917.0	917.0	916.4	915.3	914.0	912.8	911.7
150°	942.6	942.6	942.6	942.0	940.8	939.7	938.4	937.3
152.5°	966.1	966.3	966.7	966.3	965.3	964.3	963.2	962.2
155°	1000.3	1001.1	1001.8	1001.6	1000.2	998.8	997.4	996.0
157.5°	1029.7	1030.6	1031.4	1031.3	1030.2	1029.0	1028.0	1026.8
160°	1047.8	1048.8	1049.8	1049.9	1049.2	1048.4	1047.6	1046.8
162.5°	1065.0	1066.0	1066.9	1066.8	1065.5	1064.3	1063.0	1061.8
165°	1086.5	1087.7	1088.9	1088.8	1087.4	1086.0	1084.7	1083.3
167.5°	1104.0	1105.3	1106.5	1106.5	1105.3	1104.0	1102.9	1101.6
170°	1113.7	1115.0	1116.4	1116.4	1115.0	1113.7	1112.2	1110.9
172.5°	1121.1	1122.4	1123.6	1123.6	1122.1	1120.8	1119.4	1117.9
175°	1129.3	1130.4	1131.7	1131.5	1130.2	1128.7	1127.4	1126.0
177.5°	1132.9	1133.8	1134.8	1134.7	1133.6	1132.5	1131.4	1130.2
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1

(END OF REPORT)