

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331901-940

Luminaire Tested: **S123DIP-S340D1195U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331901-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5550.4 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	59	53	49	47	38	36	34	25	24	23	17
3	76	67	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	8
8	50	39	31	26	45	35	28	24	27	22	19	20	17	15	13	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	11	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4614	4614	4614	4614
5°	5503	4635	4107	4635
10°	6889	4612	3711	4612
15°	8449	4574	3455	4574
20°	10065	4517	3289	4517
25°	10688	4445	3252	4445
30°	9161	4395	3269	4395
35°	6370	4322	3303	4322
40°	4799	4235	3292	4235
45°	3984	4107	3252	4107
50°	3569	3848	3220	3848
55°	3337	3567	3181	3567
60°	3130	3272	3147	3272
65°	2942	2985	3049	2985
70°	2760	2656	2902	2656
75°	2470	2325	2662	2325
80°	2163	1909	2294	1909
85°	1692	1383	1544	1383



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	0.8
10°-20°	135.4	2.4
20°-30°	227.3	4.1
30°-40°	257.4	4.6
40°-50°	230.8	4.2
50°-60°	186.3	3.4
60°-70°	129.8	2.3
70°-80°	68.2	1.2
80°-90°	20.6	0.4
90°-100°	50.7	0.9
100°-110°	241.6	4.4
110°-120°	580.4	10.5
120°-130°	739.1	13.3
130°-140°	789.7	14.2
140°-150°	738.4	13.3
150°-160°	595.6	10.7
160°-170°	384.4	6.9
170°-180°	132.5	2.4
0°-30°	405.0	7.3
0°-40°	662.4	11.9
0°-60°	1079.4	19.4
0°-90°	1298.0	23.4
90°-120°	872.7	15.7
90°-150°	3139.9	56.6
90°-180°	4252.0	76.6
0°-180°	5550.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	429	429	429	429	429	
5°	509	429	380	429	509	53
15°	758	410	310	410	758	219
25°	900	374	274	374	900	395
35°	485	329	251	329	485	315
45°	262	270	214	270	262	207
55°	178	190	170	190	178	160
65°	116	117	120	117	116	115
75°	59	56	64	56	59	64
85°	14	11	12	11	14	17
90°	31	1	31	1	31	15
95°	39	63	39	63	39	33
105°	46	309	46	309	46	104
115°	609	579	609	579	609	563
125°	833	816	833	816	833	744
135°	1027	1016	1027	1016	1027	792
145°	1184	1173	1184	1173	1184	739
155°	1290	1292	1290	1292	1290	595
165°	1359	1362	1359	1362	1359	384
175°	1389	1394	1389	1394	1389	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	455.0	454.7	453.9	454.5	453.2	451.4	451.2	449.5	444.7	444.4	443.1
5°	509.3	507.7	507.5	507.3	504.4	500.4	492.9	492.3	482.3	477.4	471.4
7.5°	579.8	580.6	577.6	575.0	566.1	560.2	552.1	541.9	529.7	517.2	509.0
10°	630.3	637.1	628.7	622.8	617.4	607.3	595.4	580.6	565.9	548.7	535.6
12.5°	684.5	687.8	686.1	680.6	672.3	656.7	635.8	619.5	605.9	577.2	565.6
15°	758.2	770.9	762.8	744.1	744.5	729.8	702.4	672.3	656.2	631.1	596.8
17.5°	836.9	838.4	835.0	819.4	809.0	788.7	763.4	734.6	702.1	671.7	635.3
20°	878.7	877.4	870.2	862.1	844.3	828.5	800.8	768.7	727.1	697.1	657.5
22.5°	902.0	899.9	896.4	889.7	874.9	857.9	833.0	797.9	758.3	717.1	671.3
25°	899.9	902.6	903.0	901.2	896.0	885.8	866.3	838.2	798.8	745.7	698.0
27.5°	818.5	822.3	833.4	843.3	854.3	865.5	864.0	850.1	820.8	775.1	716.7
30°	737.1	728.7	749.3	775.3	792.9	824.1	841.5	842.6	826.2	786.9	730.0
32.5°	624.0	633.2	642.3	674.2	712.8	747.8	782.6	810.5	813.7	787.6	737.8
35°	484.8	496.3	512.9	529.5	571.1	606.8	667.9	721.0	763.4	769.0	738.5
37.5°	390.7	396.4	406.9	423.6	450.7	493.1	540.3	607.5	669.0	714.6	716.6
40°	341.5	343.2	355.0	367.7	389.7	424.6	467.2	526.6	600.1	664.0	690.5
42.5°	304.6	308.3	313.3	325.5	343.0	369.3	408.8	458.0	525.4	598.8	650.8
45°	261.7	265.9	269.0	277.1	289.6	307.3	334.8	379.8	431.1	506.8	576.8
47.5°	233.4	233.7	236.0	242.2	250.7	263.9	283.5	312.3	359.4	420.9	492.8
50°	213.1	216.4	217.3	222.0	228.7	238.4	254.7	279.2	317.8	371.8	437.9
52.5°	198.9	199.8	202.2	205.6	211.4	219.0	233.1	252.3	282.6	328.7	389.4
55°	177.8	177.8	180.1	182.8	186.1	193.0	202.3	216.4	239.5	275.3	325.6
57.5°	158.4	159.4	161.0	161.8	164.7	169.2	177.0	187.8	204.9	232.5	272.4
60°	145.4	147.3	147.0	148.7	151.2	154.8	161.4	170.1	185.5	207.5	241.2
62.5°	134.1	134.0	133.9	136.0	138.4	141.8	146.2	153.6	166.7	186.3	214.9
65°	115.5	115.1	116.5	117.8	118.6	121.1	124.4	131.1	139.8	154.4	176.6
67.5°	99.0	97.7	98.5	99.0	100.4	102.4	105.5	109.6	116.5	128.1	144.9
70°	87.7	86.6	86.4	86.9	88.1	89.5	91.8	95.8	102.2	111.6	123.8
72.5°	76.1	75.3	75.3	76.2	76.8	77.8	79.4	82.9	88.1	95.1	106.6
75°	59.4	59.4	59.4	59.7	60.3	61.1	62.3	64.2	68.1	73.1	80.8
77.5°	44.5	44.5	44.2	44.2	45.1	45.5	45.7	47.5	49.8	53.1	58.7
80°	34.9	33.9	34.2	34.9	35.3	35.5	36.1	36.6	38.4	40.3	44.2
82.5°	25.9	25.1	25.1	26.1	26.2	26.4	27.0	27.6	28.3	30.0	32.1
85°	13.7	13.7	13.9	13.9	14.1	13.9	14.5	14.7	14.7	15.8	17.0
87.5°	11.2	10.8	10.9	11.0	10.7	10.7	10.7	10.7	10.6	10.6	10.2
90°	31.1	30.6	30.1	29.7	29.2	28.5	27.6	26.7	25.8	24.9	21.8
92.5°	34.4	34.2	33.9	33.5	33.3	32.5	30.9	29.4	28.0	26.5	24.3
95°	39.3	39.3	39.3	39.3	39.3	38.5	36.9	35.3	33.7	32.1	29.6
97.5°	42.7	42.4	42.3	42.0	41.7	40.8	38.9	37.0	35.2	33.3	49.9
100°	43.5	43.2	43.1	42.8	42.6	41.6	39.7	37.9	36.0	34.2	70.1
102.5°	44.3	44.0	43.5	43.1	42.7	45.3	51.0	56.7	62.4	68.1	107.4
105°	45.6	45.1	44.7	44.2	43.8	63.8	104.6	145.3	186.1	226.9	247.6
107.5°	143.2	173.9	204.6	235.3	266.0	296.3	326.2	356.1	385.9	415.9	412.6
110°	284.9	317.8	350.7	383.7	416.6	436.8	444.4	452.0	459.7	467.3	464.7



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.7	495.7	502.7	509.6	516.6	520.0	519.9	519.7	519.6	519.4	516.9
115°	609.1	608.2	607.3	606.4	605.5	603.9	601.5	599.2	597.0	594.7	592.6
117.5°	676.7	676.5	676.4	676.2	676.0	674.9	673.2	671.3	669.4	667.6	666.6
120°	723.1	723.1	723.1	723.1	723.1	722.2	720.3	718.5	716.7	714.8	714.2
122.5°	768.7	768.6	768.3	768.1	767.9	767.2	766.0	764.6	763.4	762.1	761.2
125°	832.9	832.5	832.1	831.5	831.1	830.6	830.2	829.7	829.3	828.8	827.9
127.5°	894.7	895.2	895.6	896.1	896.5	896.3	895.6	894.9	894.2	893.4	892.3
130°	934.5	935.0	935.4	935.9	936.3	936.1	935.1	934.2	933.4	932.4	931.5
132.5°	970.9	971.6	972.2	972.9	973.5	973.4	972.5	971.5	970.6	969.7	968.9
135°	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7	1025.7
137.5°	1079.1	1079.6	1080.0	1080.5	1080.9	1080.6	1079.5	1078.4	1077.3	1076.2	1075.7
140°	1110.6	1111.1	1111.5	1112.0	1112.4	1112.2	1111.3	1110.4	1109.5	1108.5	1107.9
142.5°	1139.6	1140.2	1140.9	1141.6	1142.2	1142.1	1141.4	1140.7	1140.0	1139.2	1138.5
145°	1184.1	1184.1	1184.1	1184.1	1184.1	1183.9	1183.5	1183.0	1182.5	1182.1	1181.6
147.5°	1217.3	1218.3	1219.4	1220.5	1221.6	1221.8	1221.4	1220.9	1220.5	1219.9	1219.5
150°	1242.2	1242.9	1243.6	1244.2	1244.9	1245.0	1244.6	1244.1	1243.7	1243.2	1242.8
152.5°	1262.0	1263.1	1264.2	1265.2	1266.3	1266.4	1265.6	1264.7	1263.9	1263.1	1262.8
155°	1289.9	1291.2	1292.6	1294.0	1295.3	1295.5	1294.3	1293.2	1292.0	1290.8	1290.7
157.5°	1313.2	1315.0	1316.8	1318.7	1320.4	1320.6	1319.2	1317.9	1316.5	1315.1	1315.4
160°	1328.1	1329.7	1331.4	1333.0	1334.6	1334.7	1333.3	1331.9	1330.6	1329.2	1329.5
162.5°	1342.2	1343.6	1345.1	1346.5	1347.9	1347.9	1346.3	1344.8	1343.2	1341.6	1341.8
165°	1359.2	1360.8	1362.4	1364.1	1365.7	1365.6	1363.7	1361.9	1360.0	1358.2	1358.4
167.5°	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5	1371.5
170°	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9	1378.9
172.5°	1383.0	1385.1	1387.1	1389.1	1391.2	1391.2	1389.4	1387.6	1385.7	1383.8	1383.7
175°	1389.3	1391.2	1392.9	1394.8	1396.6	1396.8	1395.2	1393.6	1392.0	1390.3	1390.1
177.5°	1391.2	1392.9	1394.8	1396.7	1398.5	1398.6	1397.2	1395.7	1394.3	1392.8	1392.6
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	442.0	440.8	439.4	437.1	435.1	432.3	431.4	430.4	427.4	424.8	422.8
5°	469.0	464.0	456.8	450.1	444.8	437.5	433.4	429.0	422.8	417.1	412.6
7.5°	497.3	487.5	476.2	464.0	452.6	441.7	432.8	424.9	416.2	408.0	401.4
10°	519.8	505.6	489.8	472.8	458.3	444.2	432.3	422.0	410.7	400.9	392.8
12.5°	545.4	524.4	502.7	482.0	464.8	445.1	430.8	417.6	404.8	393.2	384.1
15°	575.6	549.0	523.3	494.8	468.7	444.2	427.1	410.5	395.7	383.7	372.0
17.5°	603.2	573.1	539.1	504.5	473.0	443.9	420.1	401.3	382.8	368.1	356.5
20°	618.8	584.6	546.2	510.2	475.3	442.9	416.7	394.3	374.3	358.7	345.7
22.5°	632.3	592.2	552.4	514.0	475.1	440.2	410.5	387.4	365.9	350.6	336.7
25°	646.3	598.2	558.4	513.4	469.9	433.7	400.6	374.3	352.8	334.8	320.6
27.5°	658.3	597.9	550.5	502.0	461.6	425.4	389.9	361.9	338.9	319.5	305.0
30°	666.2	598.7	542.4	494.5	453.7	416.3	381.8	353.6	329.5	309.8	296.0
32.5°	671.2	598.2	534.9	483.8	441.0	408.0	373.0	343.8	319.0	299.6	286.4
35°	674.1	594.5	522.0	461.8	420.7	388.4	359.2	328.9	302.9	284.8	269.8
37.5°	668.2	586.8	507.1	440.6	395.6	363.9	339.2	313.4	288.6	268.7	255.7
40°	659.2	581.8	495.4	425.6	378.3	347.8	326.8	301.4	276.9	258.0	245.9
42.5°	641.7	571.8	482.7	409.0	360.3	329.8	310.5	289.3	266.1	248.3	236.3
45°	599.1	549.7	463.4	384.1	333.9	302.3	285.3	269.8	248.9	231.7	221.2
47.5°	540.0	516.5	435.7	357.8	306.1	275.8	258.1	245.8	230.4	216.4	206.5
50°	499.0	489.2	417.0	339.8	287.8	258.0	240.9	229.8	218.7	204.8	195.7
52.5°	451.7	457.6	395.0	321.3	268.9	239.7	223.7	214.8	204.8	193.3	185.4
55°	385.0	406.7	357.1	290.0	240.9	213.1	198.0	190.1	184.2	175.8	168.9
57.5°	322.5	350.3	316.1	257.8	213.5	189.5	175.0	166.4	162.6	158.2	152.8
60°	285.4	312.8	286.9	236.2	195.1	172.2	159.3	152.0	148.3	145.2	140.6
62.5°	252.4	280.1	258.3	214.3	176.9	155.8	144.5	137.4	134.6	133.0	129.0
65°	206.9	230.8	216.2	180.1	151.1	132.3	122.2	117.2	114.5	113.9	111.4
67.5°	168.4	186.5	176.0	149.4	126.5	110.4	101.7	97.5	95.4	95.1	93.3
70°	143.1	160.2	152.0	128.0	108.3	95.6	88.1	84.4	83.1	82.9	81.9
72.5°	123.5	135.4	128.9	108.9	93.6	82.1	76.6	72.7	71.3	71.6	70.9
75°	91.4	100.3	96.6	82.7	70.4	63.0	58.4	55.9	54.7	55.3	54.4
77.5°	65.8	71.4	68.0	58.4	50.8	45.5	42.1	40.6	39.4	39.4	39.1
80°	49.7	53.0	51.1	45.3	39.1	34.5	31.7	30.8	30.1	29.9	29.7
82.5°	35.4	38.2	35.9	32.0	27.7	25.0	23.5	22.1	21.7	21.8	21.6
85°	17.8	18.9	18.1	15.6	13.9	12.7	11.9	11.2	10.8	11.0	10.6
87.5°	9.9	9.5	8.4	7.2	6.4	5.4	5.0	4.2	4.3	4.8	5.1
90°	18.9	15.9	12.9	10.3	7.9	5.6	3.3	1.1	3.3	5.6	7.9
92.5°	22.0	19.8	17.5	16.7	17.3	18.0	18.6	19.3	18.6	18.0	17.3
95°	27.0	24.5	22.0	25.4	34.9	44.3	53.8	63.2	53.8	44.3	34.9
97.5°	66.5	83.1	99.7	110.0	114.3	118.5	122.8	127.0	122.8	118.5	114.3
100°	106.0	142.0	177.8	193.5	188.9	184.3	179.7	175.0	179.7	184.3	188.9
102.5°	146.6	185.8	225.1	243.1	239.7	236.4	233.1	229.8	233.1	236.4	239.7
105°	268.3	289.0	309.8	318.9	316.3	313.8	311.3	308.7	311.3	313.8	316.3
107.5°	409.3	406.1	402.8	400.1	398.1	396.1	394.0	392.0	394.0	396.1	398.1
110°	462.2	459.7	457.1	455.0	453.1	451.2	449.4	447.5	449.4	451.2	453.1



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	514.4	511.8	509.3	507.2	505.6	503.9	502.2	500.6	502.2	503.9	505.6
115°	590.5	588.4	586.4	584.6	583.3	581.8	580.5	579.2	580.5	581.8	583.3
117.5°	665.5	664.4	663.3	662.0	660.3	658.5	656.8	655.1	656.8	658.5	660.3
120°	713.5	712.7	712.1	710.7	708.6	706.6	704.5	702.4	704.5	706.6	708.6
122.5°	760.4	759.5	758.6	757.3	755.5	753.9	752.2	750.5	752.2	753.9	755.5
125°	827.0	826.0	825.1	823.8	821.9	820.0	818.2	816.4	818.2	820.0	821.9
127.5°	891.3	890.1	889.0	887.5	885.7	883.9	882.0	880.2	882.0	883.9	885.7
130°	930.6	929.6	928.7	927.3	925.5	923.6	921.9	920.0	921.9	923.6	925.5
132.5°	968.2	967.5	966.7	965.5	963.6	961.8	959.9	958.1	959.9	961.8	963.6
135°	1024.8	1024.0	1023.0	1021.8	1020.5	1019.0	1017.7	1016.3	1017.7	1019.0	1020.5
137.5°	1075.2	1074.7	1074.2	1073.1	1071.3	1069.5	1067.8	1066.0	1067.8	1069.5	1071.3
140°	1107.1	1106.4	1105.7	1104.7	1103.3	1102.0	1100.5	1099.2	1100.5	1102.0	1103.3
142.5°	1137.8	1137.1	1136.4	1135.4	1134.0	1132.7	1131.2	1129.9	1131.2	1132.7	1134.0
145°	1181.2	1180.7	1180.3	1179.2	1177.6	1176.0	1174.4	1172.8	1174.4	1176.0	1177.6
147.5°	1219.1	1218.6	1218.2	1217.4	1216.3	1215.3	1214.2	1213.2	1214.2	1215.3	1216.3
150°	1242.2	1241.8	1241.4	1240.8	1240.1	1239.4	1238.7	1238.1	1238.7	1239.4	1240.1
152.5°	1262.6	1262.2	1261.9	1261.7	1261.3	1261.1	1260.7	1260.4	1260.7	1261.1	1261.3
155°	1290.4	1290.1	1289.9	1290.0	1290.5	1290.9	1291.5	1291.9	1291.5	1290.9	1290.5
157.5°	1315.5	1315.8	1316.0	1316.2	1316.2	1316.3	1316.3	1316.3	1316.3	1316.3	1316.2
160°	1329.6	1329.9	1330.1	1330.3	1330.6	1330.8	1331.1	1331.2	1331.1	1330.8	1330.6
162.5°	1342.1	1342.3	1342.6	1342.9	1343.5	1344.2	1344.8	1345.3	1344.8	1344.2	1343.5
165°	1358.6	1358.9	1359.1	1359.6	1360.3	1360.9	1361.6	1362.4	1361.6	1360.9	1360.3
167.5°	1371.5	1371.5	1371.5	1371.9	1372.9	1373.8	1374.7	1375.6	1374.7	1373.8	1372.9
170°	1378.9	1378.9	1378.9	1379.4	1380.3	1381.3	1382.2	1383.0	1382.2	1381.3	1380.3
172.5°	1383.5	1383.3	1383.1	1383.6	1384.7	1385.8	1387.0	1388.0	1387.0	1385.8	1384.7
175°	1389.8	1389.6	1389.4	1389.8	1391.0	1392.1	1393.3	1394.5	1393.3	1392.1	1391.0
177.5°	1392.4	1392.2	1392.0	1392.4	1393.4	1394.3	1395.2	1396.2	1395.2	1394.3	1393.4
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	421.6	420.4	418.8	416.3	414.3	411.2	411.2	411.6	411.6	411.5	411.2
5°	408.8	405.7	402.0	397.6	393.1	388.4	387.6	385.9	384.8	383.9	382.9
7.5°	395.3	389.8	384.3	378.3	372.6	368.1	364.9	362.2	360.5	358.6	357.3
10°	386.2	379.3	372.9	366.5	359.4	353.7	350.3	347.8	345.9	344.2	343.4
12.5°	375.4	367.6	360.4	354.3	346.6	340.8	337.4	336.3	334.1	330.6	328.8
15°	359.6	352.3	343.8	334.5	330.7	323.7	319.7	317.8	316.6	313.9	313.1
17.5°	346.1	336.6	327.0	320.0	313.1	307.4	305.1	302.8	301.2	299.0	298.3
20°	335.3	326.8	318.1	310.6	303.3	297.0	295.2	293.6	291.9	290.9	290.0
22.5°	324.3	315.8	308.5	301.6	293.8	289.7	287.8	285.9	284.7	284.0	283.2
25°	308.9	301.4	293.3	287.1	280.9	278.1	276.9	275.9	275.0	274.0	273.8
27.5°	295.2	287.0	280.4	274.6	270.1	267.9	266.6	266.2	266.4	266.7	267.0
30°	284.8	277.3	272.0	267.0	262.8	260.7	260.5	260.5	261.4	261.5	262.0
32.5°	275.4	269.2	263.8	259.0	255.8	254.4	255.2	255.2	255.8	256.4	257.2
35°	261.5	256.1	252.0	247.8	245.1	245.8	246.2	246.6	247.6	248.9	249.7
37.5°	248.3	243.7	239.3	236.1	234.9	235.9	237.0	237.8	239.1	240.0	240.9
40°	238.9	235.3	231.2	228.3	228.7	229.3	230.2	231.2	232.3	232.9	233.7
42.5°	230.1	226.4	223.2	220.8	221.4	222.2	222.7	223.2	224.4	225.6	226.0
45°	216.7	213.7	210.9	209.4	209.8	210.3	210.6	211.2	212.3	213.1	213.4
47.5°	201.6	199.6	197.6	196.2	196.9	196.7	197.2	198.6	198.9	199.4	200.5
50°	192.0	190.1	187.8	187.3	187.3	187.3	187.6	189.2	189.2	190.1	190.9
52.5°	181.3	180.1	178.7	177.9	177.5	177.5	178.4	179.2	179.6	180.7	181.6
55°	165.6	164.3	163.1	162.5	162.0	162.5	164.1	164.5	165.6	166.2	166.8
57.5°	149.2	148.2	147.2	146.9	146.8	147.3	148.2	149.5	149.7	151.7	152.6
60°	138.4	136.9	136.1	136.1	135.6	137.5	137.1	139.2	139.6	140.9	142.3
62.5°	127.2	125.3	124.9	124.9	125.6	126.1	126.6	127.5	128.7	130.2	131.3
65°	109.2	108.3	109.7	109.5	109.1	110.3	110.3	111.4	112.6	114.0	116.4
67.5°	92.3	91.8	91.8	91.8	92.5	93.2	93.8	94.7	96.2	97.7	99.2
70°	80.8	81.4	80.4	81.2	81.9	82.0	82.5	83.7	85.3	86.4	88.1
72.5°	69.6	69.6	69.7	70.1	70.7	71.1	71.5	72.9	74.7	75.6	77.0
75°	53.6	53.4	54.0	54.0	55.0	55.5	55.9	56.5	58.1	59.4	60.5
77.5°	39.1	39.4	39.2	39.9	39.7	39.8	41.0	41.6	41.8	44.3	44.9
80°	29.5	29.9	30.1	30.3	30.5	30.1	31.6	32.2	32.2	33.6	34.7
82.5°	21.2	21.4	21.9	22.2	22.2	22.6	22.7	23.2	23.7	24.3	25.7
85°	10.6	11.2	11.4	11.2	11.4	11.0	11.6	11.9	12.0	12.0	12.0
87.5°	5.4	6.1	6.5	7.2	7.7	8.5	8.6	8.5	8.6	9.4	8.8
90°	10.3	12.9	15.9	18.9	21.8	24.9	25.8	26.7	27.6	28.5	29.2
92.5°	16.7	17.5	19.8	22.0	24.3	26.5	28.0	29.4	30.9	32.5	33.3
95°	25.4	22.0	24.5	27.0	29.6	32.1	33.7	35.3	36.9	38.5	39.3
97.5°	110.0	99.7	83.1	66.5	49.9	33.3	35.2	37.0	38.9	40.8	41.7
100°	193.5	177.8	142.0	106.0	70.1	34.2	36.0	37.9	39.7	41.6	42.6
102.5°	243.1	225.1	185.8	146.6	107.4	68.1	62.4	56.7	51.0	45.3	42.7
105°	318.9	309.8	289.0	268.3	247.6	226.9	186.1	145.3	104.6	63.8	43.8
107.5°	400.1	402.8	406.1	409.3	412.6	415.9	385.9	356.1	326.2	296.3	266.0
110°	455.0	457.1	459.7	462.2	464.7	467.3	459.7	452.0	444.4	436.8	416.6



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	507.2	509.3	511.8	514.4	516.9	519.4	519.6	519.7	519.9	520.0	516.6
115°	584.6	586.4	588.4	590.5	592.6	594.7	597.0	599.2	601.5	603.9	605.5
117.5°	662.0	663.3	664.4	665.5	666.6	667.6	669.4	671.3	673.2	674.9	676.0
120°	710.7	712.1	712.7	713.5	714.2	714.8	716.7	718.5	720.3	722.2	723.1
122.5°	757.3	758.6	759.5	760.4	761.2	762.1	763.4	764.6	766.0	767.2	767.9
125°	823.8	825.1	826.0	827.0	827.9	828.8	829.3	829.7	830.2	830.6	831.1
127.5°	887.5	889.0	890.1	891.3	892.3	893.4	894.2	894.9	895.6	896.3	896.5
130°	927.3	928.7	929.6	930.6	931.5	932.4	933.4	934.2	935.1	936.1	936.3
132.5°	965.5	966.7	967.5	968.2	968.9	969.7	970.6	971.5	972.5	973.4	973.5
135°	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5
137.5°	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3	1078.4	1079.5	1080.6	1080.9
140°	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5	1110.4	1111.3	1112.2	1112.4
142.5°	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0	1140.7	1141.4	1142.1	1142.2
145°	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5	1183.0	1183.5	1183.9	1184.1
147.5°	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5	1220.9	1221.4	1221.8	1221.6
150°	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7	1244.1	1244.6	1245.0	1244.9
152.5°	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9	1264.7	1265.6	1266.4	1266.3
155°	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0	1293.2	1294.3	1295.5	1295.3
157.5°	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5	1317.9	1319.2	1320.6	1320.4
160°	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6	1331.9	1333.3	1334.7	1334.6
162.5°	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2	1344.8	1346.3	1347.9	1347.9
165°	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0	1361.9	1363.7	1365.6	1365.7
167.5°	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9
170°	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3
172.5°	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7	1387.6	1389.4	1391.2	1391.2
175°	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0	1393.6	1395.2	1396.8	1396.6
177.5°	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3	1395.7	1397.2	1398.6	1398.5
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	410.0	409.8	411.0	410.2	411.0	409.8	410.0	411.2	411.5	411.6	411.6
5°	381.7	382.3	380.1	380.1	380.1	382.3	381.7	382.9	383.9	384.8	385.9
7.5°	356.3	355.4	355.5	354.4	355.5	355.4	356.3	357.3	358.6	360.5	362.2
10°	340.9	339.7	339.2	339.5	339.2	339.7	340.9	343.4	344.2	345.9	347.8
12.5°	328.1	327.9	325.1	325.1	325.1	327.9	328.1	328.8	330.6	334.1	336.3
15°	313.1	309.2	308.7	310.0	308.7	309.2	313.1	313.1	313.9	316.6	317.8
17.5°	298.0	295.9	296.0	295.4	296.0	295.9	298.0	298.3	299.0	301.2	302.8
20°	290.0	288.7	288.6	287.1	288.6	288.7	290.0	290.0	290.9	291.9	293.6
22.5°	282.7	282.3	282.4	280.8	282.4	282.3	282.7	283.2	284.0	284.7	285.9
25°	273.6	274.6	273.8	273.8	273.8	274.6	273.6	273.8	274.0	275.0	275.9
27.5°	267.4	267.4	267.0	267.0	267.0	267.4	267.4	267.0	266.7	266.4	266.2
30°	262.8	262.6	263.0	263.0	263.0	262.6	262.8	262.0	261.5	261.4	260.5
32.5°	258.2	258.4	258.5	258.7	258.5	258.4	258.2	257.2	256.4	255.8	255.2
35°	250.9	251.2	251.8	251.4	251.8	251.2	250.9	249.7	248.9	247.6	246.6
37.5°	241.2	242.2	242.0	242.3	242.0	242.2	241.2	240.9	240.0	239.1	237.8
40°	233.9	234.5	234.3	234.3	234.3	234.5	233.9	233.7	232.9	232.3	231.2
42.5°	226.4	226.9	226.3	226.0	226.3	226.9	226.4	226.0	225.6	224.4	223.2
45°	214.2	213.7	214.4	213.6	214.4	213.7	214.2	213.4	213.1	212.3	211.2
47.5°	200.5	200.9	201.1	201.7	201.1	200.9	200.5	200.5	199.4	198.9	198.6
50°	191.4	192.6	192.6	192.3	192.6	192.6	191.4	190.9	190.1	189.2	189.2
52.5°	182.4	182.9	183.8	183.7	183.8	182.9	182.4	181.6	180.7	179.6	179.2
55°	168.4	168.9	169.3	169.5	169.3	168.9	168.4	166.8	166.2	165.6	164.5
57.5°	154.1	153.9	154.9	155.2	154.9	153.9	154.1	152.6	151.7	149.7	149.5
60°	143.9	143.9	145.6	146.2	145.6	143.9	143.9	142.3	140.9	139.6	139.2
62.5°	133.1	133.8	135.5	134.6	135.5	133.8	133.1	131.3	130.2	128.7	127.5
65°	117.3	119.0	118.9	119.7	118.9	119.0	117.3	116.4	114.0	112.6	111.4
67.5°	100.9	101.9	103.4	103.5	103.4	101.9	100.9	99.2	97.7	96.2	94.7
70°	89.7	90.8	91.6	92.2	91.6	90.8	89.7	88.1	86.4	85.3	83.7
72.5°	78.9	79.5	81.5	80.6	81.5	79.5	78.9	77.0	75.6	74.7	72.9
75°	61.9	63.4	64.6	64.0	64.6	63.4	61.9	60.5	59.4	58.1	56.5
77.5°	45.7	47.3	47.8	47.3	47.8	47.3	45.7	44.9	44.3	41.8	41.6
80°	36.1	35.9	37.2	37.0	37.2	35.9	36.1	34.7	33.6	32.2	32.2
82.5°	26.5	26.3	26.8	27.0	26.8	26.3	26.5	25.7	24.3	23.7	23.2
85°	12.8	13.5	12.7	12.5	12.7	13.5	12.8	12.0	12.0	12.0	11.9
87.5°	8.9	9.0	8.9	8.9	8.9	9.0	8.9	8.8	9.4	8.6	8.5
90°	29.7	30.1	30.6	31.1	30.6	30.1	29.7	29.2	28.5	27.6	26.7
92.5°	33.5	33.9	34.2	34.4	34.2	33.9	33.5	33.3	32.5	30.9	29.4
95°	39.3	39.3	39.3	39.3	39.3	39.3	39.3	39.3	38.5	36.9	35.3
97.5°	42.0	42.3	42.4	42.7	42.4	42.3	42.0	41.7	40.8	38.9	37.0
100°	42.8	43.1	43.2	43.5	43.2	43.1	42.8	42.6	41.6	39.7	37.9
102.5°	43.1	43.5	44.0	44.3	44.0	43.5	43.1	42.7	45.3	51.0	56.7
105°	44.2	44.7	45.1	45.6	45.1	44.7	44.2	43.8	63.8	104.6	145.3
107.5°	235.3	204.6	173.9	143.2	173.9	204.6	235.3	266.0	296.3	326.2	356.1
110°	383.7	350.7	317.8	284.9	317.8	350.7	383.7	416.6	436.8	444.4	452.0



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	509.6	502.7	495.7	488.7	495.7	502.7	509.6	516.6	520.0	519.9	519.7
115°	606.4	607.3	608.2	609.1	608.2	607.3	606.4	605.5	603.9	601.5	599.2
117.5°	676.2	676.4	676.5	676.7	676.5	676.4	676.2	676.0	674.9	673.2	671.3
120°	723.1	723.1	723.1	723.1	723.1	723.1	723.1	723.1	722.2	720.3	718.5
122.5°	768.1	768.3	768.6	768.7	768.6	768.3	768.1	767.9	767.2	766.0	764.6
125°	831.5	832.1	832.5	832.9	832.5	832.1	831.5	831.1	830.6	830.2	829.7
127.5°	896.1	895.6	895.2	894.7	895.2	895.6	896.1	896.5	896.3	895.6	894.9
130°	935.9	935.4	935.0	934.5	935.0	935.4	935.9	936.3	936.1	935.1	934.2
132.5°	972.9	972.2	971.6	970.9	971.6	972.2	972.9	973.5	973.4	972.5	971.5
135°	1028.8	1028.1	1027.3	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1
137.5°	1080.5	1080.0	1079.6	1079.1	1079.6	1080.0	1080.5	1080.9	1080.6	1079.5	1078.4
140°	1112.0	1111.5	1111.1	1110.6	1111.1	1111.5	1112.0	1112.4	1112.2	1111.3	1110.4
142.5°	1141.6	1140.9	1140.2	1139.6	1140.2	1140.9	1141.6	1142.2	1142.1	1141.4	1140.7
145°	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1183.9	1183.5	1183.0
147.5°	1220.5	1219.4	1218.3	1217.3	1218.3	1219.4	1220.5	1221.6	1221.8	1221.4	1220.9
150°	1244.2	1243.6	1242.9	1242.2	1242.9	1243.6	1244.2	1244.9	1245.0	1244.6	1244.1
152.5°	1265.2	1264.2	1263.1	1262.0	1263.1	1264.2	1265.2	1266.3	1266.4	1265.6	1264.7
155°	1294.0	1292.6	1291.2	1289.9	1291.2	1292.6	1294.0	1295.3	1295.5	1294.3	1293.2
157.5°	1318.7	1316.8	1315.0	1313.2	1315.0	1316.8	1318.7	1320.4	1320.6	1319.2	1317.9
160°	1333.0	1331.4	1329.7	1328.1	1329.7	1331.4	1333.0	1334.6	1334.7	1333.3	1331.9
162.5°	1346.5	1345.1	1343.6	1342.2	1343.6	1345.1	1346.5	1347.9	1347.9	1346.3	1344.8
165°	1364.1	1362.4	1360.8	1359.2	1360.8	1362.4	1364.1	1365.7	1365.6	1363.7	1361.9
167.5°	1377.0	1375.1	1373.3	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1
170°	1384.5	1382.6	1380.7	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6
172.5°	1389.1	1387.1	1385.1	1383.0	1385.1	1387.1	1389.1	1391.2	1391.2	1389.4	1387.6
175°	1394.8	1392.9	1391.2	1389.3	1391.2	1392.9	1394.8	1396.6	1396.8	1395.2	1393.6
177.5°	1396.7	1394.8	1392.9	1391.2	1392.9	1394.8	1396.7	1398.5	1398.6	1397.2	1395.7
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	411.2	411.2	414.3	416.3	418.8	420.4	421.6	422.8	424.8	427.4	430.4
5°	387.6	388.4	393.1	397.6	402.0	405.7	408.8	412.6	417.1	422.8	429.0
7.5°	364.9	368.1	372.6	378.3	384.3	389.8	395.3	401.4	408.0	416.2	424.9
10°	350.3	353.7	359.4	366.5	372.9	379.3	386.2	392.8	400.9	410.7	422.0
12.5°	337.4	340.8	346.6	354.3	360.4	367.6	375.4	384.1	393.2	404.8	417.6
15°	319.7	323.7	330.7	334.5	343.8	352.3	359.6	372.0	383.7	395.7	410.5
17.5°	305.1	307.4	313.1	320.0	327.0	336.6	346.1	356.5	368.1	382.8	401.3
20°	295.2	297.0	303.3	310.6	318.1	326.8	335.3	345.7	358.7	374.3	394.3
22.5°	287.8	289.7	293.8	301.6	308.5	315.8	324.3	336.7	350.6	365.9	387.4
25°	276.9	278.1	280.9	287.1	293.3	301.4	308.9	320.6	334.8	352.8	374.3
27.5°	266.6	267.9	270.1	274.6	280.4	287.0	295.2	305.0	319.5	338.9	361.9
30°	260.5	260.7	262.8	267.0	272.0	277.3	284.8	296.0	309.8	329.5	353.6
32.5°	255.2	254.4	255.8	259.0	263.8	269.2	275.4	286.4	299.6	319.0	343.8
35°	246.2	245.8	245.1	247.8	252.0	256.1	261.5	269.8	284.8	302.9	328.9
37.5°	237.0	235.9	234.9	236.1	239.3	243.7	248.3	255.7	268.7	288.6	313.4
40°	230.2	229.3	228.7	228.3	231.2	235.3	238.9	245.9	258.0	276.9	301.4
42.5°	222.7	222.2	221.4	220.8	223.2	226.4	230.1	236.3	248.3	266.1	289.3
45°	210.6	210.3	209.8	209.4	210.9	213.7	216.7	221.2	231.7	248.9	269.8
47.5°	197.2	196.7	196.9	196.2	197.6	199.6	201.6	206.5	216.4	230.4	245.8
50°	187.6	187.3	187.3	187.3	187.8	190.1	192.0	195.7	204.8	218.7	229.8
52.5°	178.4	177.5	177.5	177.9	178.7	180.1	181.3	185.4	193.3	204.8	214.8
55°	164.1	162.5	162.0	162.5	163.1	164.3	165.6	168.9	175.8	184.2	190.1
57.5°	148.2	147.3	146.8	146.9	147.2	148.2	149.2	152.8	158.2	162.6	166.4
60°	137.1	137.5	135.6	136.1	136.1	136.9	138.4	140.6	145.2	148.3	152.0
62.5°	126.6	126.1	125.6	124.9	124.9	125.3	127.2	129.0	133.0	134.6	137.4
65°	110.3	110.3	109.1	109.5	109.7	108.3	109.2	111.4	113.9	114.5	117.2
67.5°	93.8	93.2	92.5	91.8	91.8	91.8	92.3	93.3	95.1	95.4	97.5
70°	82.5	82.0	81.9	81.2	80.4	81.4	80.8	81.9	82.9	83.1	84.4
72.5°	71.5	71.1	70.7	70.1	69.7	69.6	69.6	70.9	71.6	71.3	72.7
75°	55.9	55.5	55.0	54.0	54.0	53.4	53.6	54.4	55.3	54.7	55.9
77.5°	41.0	39.8	39.7	39.9	39.2	39.4	39.1	39.1	39.4	39.4	40.6
80°	31.6	30.1	30.5	30.3	30.1	29.9	29.5	29.7	29.9	30.1	30.8
82.5°	22.7	22.6	22.2	22.2	21.9	21.4	21.2	21.6	21.8	21.7	22.1
85°	11.6	11.0	11.4	11.2	11.4	11.2	10.6	10.6	11.0	10.8	11.2
87.5°	8.6	8.5	7.7	7.2	6.5	6.1	5.4	5.1	4.8	4.3	4.2
90°	25.8	24.9	21.8	18.9	15.9	12.9	10.3	7.9	5.6	3.3	1.1
92.5°	28.0	26.5	24.3	22.0	19.8	17.5	16.7	17.3	18.0	18.6	19.3
95°	33.7	32.1	29.6	27.0	24.5	22.0	25.4	34.9	44.3	53.8	63.2
97.5°	35.2	33.3	49.9	66.5	83.1	99.7	110.0	114.3	118.5	122.8	127.0
100°	36.0	34.2	70.1	106.0	142.0	177.8	193.5	188.9	184.3	179.7	175.0
102.5°	62.4	68.1	107.4	146.6	185.8	225.1	243.1	239.7	236.4	233.1	229.8
105°	186.1	226.9	247.6	268.3	289.0	309.8	318.9	316.3	313.8	311.3	308.7
107.5°	385.9	415.9	412.6	409.3	406.1	402.8	400.1	398.1	396.1	394.0	392.0
110°	459.7	467.3	464.7	462.2	459.7	457.1	455.0	453.1	451.2	449.4	447.5



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	519.6	519.4	516.9	514.4	511.8	509.3	507.2	505.6	503.9	502.2	500.6
115°	597.0	594.7	592.6	590.5	588.4	586.4	584.6	583.3	581.8	580.5	579.2
117.5°	669.4	667.6	666.6	665.5	664.4	663.3	662.0	660.3	658.5	656.8	655.1
120°	716.7	714.8	714.2	713.5	712.7	712.1	710.7	708.6	706.6	704.5	702.4
122.5°	763.4	762.1	761.2	760.4	759.5	758.6	757.3	755.5	753.9	752.2	750.5
125°	829.3	828.8	827.9	827.0	826.0	825.1	823.8	821.9	820.0	818.2	816.4
127.5°	894.2	893.4	892.3	891.3	890.1	889.0	887.5	885.7	883.9	882.0	880.2
130°	933.4	932.4	931.5	930.6	929.6	928.7	927.3	925.5	923.6	921.9	920.0
132.5°	970.6	969.7	968.9	968.2	967.5	966.7	965.5	963.6	961.8	959.9	958.1
135°	1027.3	1026.7	1025.7	1024.8	1024.0	1023.0	1021.8	1020.5	1019.0	1017.7	1016.3
137.5°	1077.3	1076.2	1075.7	1075.2	1074.7	1074.2	1073.1	1071.3	1069.5	1067.8	1066.0
140°	1109.5	1108.5	1107.9	1107.1	1106.4	1105.7	1104.7	1103.3	1102.0	1100.5	1099.2
142.5°	1140.0	1139.2	1138.5	1137.8	1137.1	1136.4	1135.4	1134.0	1132.7	1131.2	1129.9
145°	1182.5	1182.1	1181.6	1181.2	1180.7	1180.3	1179.2	1177.6	1176.0	1174.4	1172.8
147.5°	1220.5	1219.9	1219.5	1219.1	1218.6	1218.2	1217.4	1216.3	1215.3	1214.2	1213.2
150°	1243.7	1243.2	1242.8	1242.2	1241.8	1241.4	1240.8	1240.1	1239.4	1238.7	1238.1
152.5°	1263.9	1263.1	1262.8	1262.6	1262.2	1261.9	1261.7	1261.3	1261.1	1260.7	1260.4
155°	1292.0	1290.8	1290.7	1290.4	1290.1	1289.9	1290.0	1290.5	1290.9	1291.5	1291.9
157.5°	1316.5	1315.1	1315.4	1315.5	1315.8	1316.0	1316.2	1316.2	1316.3	1316.3	1316.3
160°	1330.6	1329.2	1329.5	1329.6	1329.9	1330.1	1330.3	1330.6	1330.8	1331.1	1331.2
162.5°	1343.2	1341.6	1341.8	1342.1	1342.3	1342.6	1342.9	1343.5	1344.2	1344.8	1345.3
165°	1360.0	1358.2	1358.4	1358.6	1358.9	1359.1	1359.6	1360.3	1360.9	1361.6	1362.4
167.5°	1373.3	1371.5	1371.5	1371.5	1371.5	1371.5	1371.9	1372.9	1373.8	1374.7	1375.6
170°	1380.7	1378.9	1378.9	1378.9	1378.9	1378.9	1379.4	1380.3	1381.3	1382.2	1383.0
172.5°	1385.7	1383.8	1383.7	1383.5	1383.3	1383.1	1383.6	1384.7	1385.8	1387.0	1388.0
175°	1392.0	1390.3	1390.1	1389.8	1389.6	1389.4	1389.8	1391.0	1392.1	1393.3	1394.5
177.5°	1394.3	1392.8	1392.6	1392.4	1392.2	1392.0	1392.4	1393.4	1394.3	1395.2	1396.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	431.4	432.3	435.1	437.1	439.4	440.8	442.0	443.1	444.4	444.7	449.5
5°	433.4	437.5	444.8	450.1	456.8	464.0	469.0	471.4	477.4	482.3	492.3
7.5°	432.8	441.7	452.6	464.0	476.2	487.5	497.3	509.0	517.2	529.7	541.9
10°	432.3	444.2	458.3	472.8	489.8	505.6	519.8	535.6	548.7	565.9	580.6
12.5°	430.8	445.1	464.8	482.0	502.7	524.4	545.4	565.6	577.2	605.9	619.5
15°	427.1	444.2	468.7	494.8	523.3	549.0	575.6	596.8	631.1	656.2	672.3
17.5°	420.1	443.9	473.0	504.5	539.1	573.1	603.2	635.3	671.7	702.1	734.6
20°	416.7	442.9	475.3	510.2	546.2	584.6	618.8	657.5	697.1	727.1	768.7
22.5°	410.5	440.2	475.1	514.0	552.4	592.2	632.3	671.3	717.1	758.3	797.9
25°	400.6	433.7	469.9	513.4	558.4	598.2	646.3	698.0	745.7	798.8	838.2
27.5°	389.9	425.4	461.6	502.0	550.5	597.9	658.3	716.7	775.1	820.8	850.1
30°	381.8	416.3	453.7	494.5	542.4	598.7	666.2	730.0	786.9	826.2	842.6
32.5°	373.0	408.0	441.0	483.8	534.9	598.2	671.2	737.8	787.6	813.7	810.5
35°	359.2	388.4	420.7	461.8	522.0	594.5	674.1	738.5	769.0	763.4	721.0
37.5°	339.2	363.9	395.6	440.6	507.1	586.8	668.2	716.6	714.6	669.0	607.5
40°	326.8	347.8	378.3	425.6	495.4	581.8	659.2	690.5	664.0	600.1	526.6
42.5°	310.5	329.8	360.3	409.0	482.7	571.8	641.7	650.8	598.8	525.4	458.0
45°	285.3	302.3	333.9	384.1	463.4	549.7	599.1	576.8	506.8	431.1	379.8
47.5°	258.1	275.8	306.1	357.8	435.7	516.5	540.0	492.8	420.9	359.4	312.3
50°	240.9	258.0	287.8	339.8	417.0	489.2	499.0	437.9	371.8	317.8	279.2
52.5°	223.7	239.7	268.9	321.3	395.0	457.6	451.7	389.4	328.7	282.6	252.3
55°	198.0	213.1	240.9	290.0	357.1	406.7	385.0	325.6	275.3	239.5	216.4
57.5°	175.0	189.5	213.5	257.8	316.1	350.3	322.5	272.4	232.5	204.9	187.8
60°	159.3	172.2	195.1	236.2	286.9	312.8	285.4	241.2	207.5	185.5	170.1
62.5°	144.5	155.8	176.9	214.3	258.3	280.1	252.4	214.9	186.3	166.7	153.6
65°	122.2	132.3	151.1	180.1	216.2	230.8	206.9	176.6	154.4	139.8	131.1
67.5°	101.7	110.4	126.5	149.4	176.0	186.5	168.4	144.9	128.1	116.5	109.6
70°	88.1	95.6	108.3	128.0	152.0	160.2	143.1	123.8	111.6	102.2	95.8
72.5°	76.6	82.1	93.6	108.9	128.9	135.4	123.5	106.6	95.1	88.1	82.9
75°	58.4	63.0	70.4	82.7	96.6	100.3	91.4	80.8	73.1	68.1	64.2
77.5°	42.1	45.5	50.8	58.4	68.0	71.4	65.8	58.7	53.1	49.8	47.5
80°	31.7	34.5	39.1	45.3	51.1	53.0	49.7	44.2	40.3	38.4	36.6
82.5°	23.5	25.0	27.7	32.0	35.9	38.2	35.4	32.1	30.0	28.3	27.6
85°	11.9	12.7	13.9	15.6	18.1	18.9	17.8	17.0	15.8	14.7	14.7
87.5°	5.0	5.4	6.4	7.2	8.4	9.5	9.9	10.2	10.6	10.6	10.7
90°	3.3	5.6	7.9	10.3	12.9	15.9	18.9	21.8	24.9	25.8	26.7
92.5°	18.6	18.0	17.3	16.7	17.5	19.8	22.0	24.3	26.5	28.0	29.4
95°	53.8	44.3	34.9	25.4	22.0	24.5	27.0	29.6	32.1	33.7	35.3
97.5°	122.8	118.5	114.3	110.0	99.7	83.1	66.5	49.9	33.3	35.2	37.0
100°	179.7	184.3	188.9	193.5	177.8	142.0	106.0	70.1	34.2	36.0	37.9
102.5°	233.1	236.4	239.7	243.1	225.1	185.8	146.6	107.4	68.1	62.4	56.7
105°	311.3	313.8	316.3	318.9	309.8	289.0	268.3	247.6	226.9	186.1	145.3
107.5°	394.0	396.1	398.1	400.1	402.8	406.1	409.3	412.6	415.9	385.9	356.1
110°	449.4	451.2	453.1	455.0	457.1	459.7	462.2	464.7	467.3	459.7	452.0



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	502.2	503.9	505.6	507.2	509.3	511.8	514.4	516.9	519.4	519.6	519.7
115°	580.5	581.8	583.3	584.6	586.4	588.4	590.5	592.6	594.7	597.0	599.2
117.5°	656.8	658.5	660.3	662.0	663.3	664.4	665.5	666.6	667.6	669.4	671.3
120°	704.5	706.6	708.6	710.7	712.1	712.7	713.5	714.2	714.8	716.7	718.5
122.5°	752.2	753.9	755.5	757.3	758.6	759.5	760.4	761.2	762.1	763.4	764.6
125°	818.2	820.0	821.9	823.8	825.1	826.0	827.0	827.9	828.8	829.3	829.7
127.5°	882.0	883.9	885.7	887.5	889.0	890.1	891.3	892.3	893.4	894.2	894.9
130°	921.9	923.6	925.5	927.3	928.7	929.6	930.6	931.5	932.4	933.4	934.2
132.5°	959.9	961.8	963.6	965.5	966.7	967.5	968.2	968.9	969.7	970.6	971.5
135°	1017.7	1019.0	1020.5	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3	1028.1
137.5°	1067.8	1069.5	1071.3	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3	1078.4
140°	1100.5	1102.0	1103.3	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5	1110.4
142.5°	1131.2	1132.7	1134.0	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0	1140.7
145°	1174.4	1176.0	1177.6	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5	1183.0
147.5°	1214.2	1215.3	1216.3	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5	1220.9
150°	1238.7	1239.4	1240.1	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7	1244.1
152.5°	1260.7	1261.1	1261.3	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9	1264.7
155°	1291.5	1290.9	1290.5	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0	1293.2
157.5°	1316.3	1316.3	1316.2	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5	1317.9
160°	1331.1	1330.8	1330.6	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6	1331.9
162.5°	1344.8	1344.2	1343.5	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2	1344.8
165°	1361.6	1360.9	1360.3	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0	1361.9
167.5°	1374.7	1373.8	1372.9	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3	1375.1
170°	1382.2	1381.3	1380.3	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7	1382.6
172.5°	1387.0	1385.8	1384.7	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7	1387.6
175°	1393.3	1392.1	1391.0	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0	1393.6
177.5°	1395.2	1394.3	1393.4	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3	1395.7
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	451.2	451.4	453.2	454.5	453.9	454.7	455.0
5°	492.9	500.4	504.4	507.3	507.5	507.7	509.3
7.5°	552.1	560.2	566.1	575.0	577.6	580.6	579.8
10°	595.4	607.3	617.4	622.8	628.7	637.1	630.3
12.5°	635.8	656.7	672.3	680.6	686.1	687.8	684.5
15°	702.4	729.8	744.5	744.1	762.8	770.9	758.2
17.5°	763.4	788.7	809.0	819.4	835.0	838.4	836.9
20°	800.8	828.5	844.3	862.1	870.2	877.4	878.7
22.5°	833.0	857.9	874.9	889.7	896.4	899.9	902.0
25°	866.3	885.8	896.0	901.2	903.0	902.6	899.9
27.5°	864.0	865.5	854.3	843.3	833.4	822.3	818.5
30°	841.5	824.1	792.9	775.3	749.3	728.7	737.1
32.5°	782.6	747.8	712.8	674.2	642.3	633.2	624.0
35°	667.9	606.8	571.1	529.5	512.9	496.3	484.8
37.5°	540.3	493.1	450.7	423.6	406.9	396.4	390.7
40°	467.2	424.6	389.7	367.7	355.0	343.2	341.5
42.5°	408.8	369.3	343.0	325.5	313.3	308.3	304.6
45°	334.8	307.3	289.6	277.1	269.0	265.9	261.7
47.5°	283.5	263.9	250.7	242.2	236.0	233.7	233.4
50°	254.7	238.4	228.7	222.0	217.3	216.4	213.1
52.5°	233.1	219.0	211.4	205.6	202.2	199.8	198.9
55°	202.3	193.0	186.1	182.8	180.1	177.8	177.8
57.5°	177.0	169.2	164.7	161.8	161.0	159.4	158.4
60°	161.4	154.8	151.2	148.7	147.0	147.3	145.4
62.5°	146.2	141.8	138.4	136.0	133.9	134.0	134.1
65°	124.4	121.1	118.6	117.8	116.5	115.1	115.5
67.5°	105.5	102.4	100.4	99.0	98.5	97.7	99.0
70°	91.8	89.5	88.1	86.9	86.4	86.6	87.7
72.5°	79.4	77.8	76.8	76.2	75.3	75.3	76.1
75°	62.3	61.1	60.3	59.7	59.4	59.4	59.4
77.5°	45.7	45.5	45.1	44.2	44.2	44.5	44.5
80°	36.1	35.5	35.3	34.9	34.2	33.9	34.9
82.5°	27.0	26.4	26.2	26.1	25.1	25.1	25.9
85°	14.5	13.9	14.1	13.9	13.9	13.7	13.7
87.5°	10.7	10.7	10.7	11.0	10.9	10.8	11.2
90°	27.6	28.5	29.2	29.7	30.1	30.6	31.1
92.5°	30.9	32.5	33.3	33.5	33.9	34.2	34.4
95°	36.9	38.5	39.3	39.3	39.3	39.3	39.3
97.5°	38.9	40.8	41.7	42.0	42.3	42.4	42.7
100°	39.7	41.6	42.6	42.8	43.1	43.2	43.5
102.5°	51.0	45.3	42.7	43.1	43.5	44.0	44.3
105°	104.6	63.8	43.8	44.2	44.7	45.1	45.6
107.5°	326.2	296.3	266.0	235.3	204.6	173.9	143.2
110°	444.4	436.8	416.6	383.7	350.7	317.8	284.9



TEST NUMBER: P331901-940

CATALOG NUMBER: S123DIP-S340D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	519.9	520.0	516.6	509.6	502.7	495.7	488.7
115°	601.5	603.9	605.5	606.4	607.3	608.2	609.1
117.5°	673.2	674.9	676.0	676.2	676.4	676.5	676.7
120°	720.3	722.2	723.1	723.1	723.1	723.1	723.1
122.5°	766.0	767.2	767.9	768.1	768.3	768.6	768.7
125°	830.2	830.6	831.1	831.5	832.1	832.5	832.9
127.5°	895.6	896.3	896.5	896.1	895.6	895.2	894.7
130°	935.1	936.1	936.3	935.9	935.4	935.0	934.5
132.5°	972.5	973.4	973.5	972.9	972.2	971.6	970.9
135°	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7
137.5°	1079.5	1080.6	1080.9	1080.5	1080.0	1079.6	1079.1
140°	1111.3	1112.2	1112.4	1112.0	1111.5	1111.1	1110.6
142.5°	1141.4	1142.1	1142.2	1141.6	1140.9	1140.2	1139.6
145°	1183.5	1183.9	1184.1	1184.1	1184.1	1184.1	1184.1
147.5°	1221.4	1221.8	1221.6	1220.5	1219.4	1218.3	1217.3
150°	1244.6	1245.0	1244.9	1244.2	1243.6	1242.9	1242.2
152.5°	1265.6	1266.4	1266.3	1265.2	1264.2	1263.1	1262.0
155°	1294.3	1295.5	1295.3	1294.0	1292.6	1291.2	1289.9
157.5°	1319.2	1320.6	1320.4	1318.7	1316.8	1315.0	1313.2
160°	1333.3	1334.7	1334.6	1333.0	1331.4	1329.7	1328.1
162.5°	1346.3	1347.9	1347.9	1346.5	1345.1	1343.6	1342.2
165°	1363.7	1365.6	1365.7	1364.1	1362.4	1360.8	1359.2
167.5°	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5
170°	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9
172.5°	1389.4	1391.2	1391.2	1389.1	1387.1	1385.1	1383.0
175°	1395.2	1396.8	1396.6	1394.8	1392.9	1391.2	1389.3
177.5°	1397.2	1398.6	1398.5	1396.7	1394.8	1392.9	1391.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5

(END OF REPORT)