

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332515-927

Luminaire Tested: **S124DIP-S350D810U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332515-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D810U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3425.0 lumens  
Efficiency: N/A  
Efficacy: 109.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332515-927

CATALOG NUMBER: S124DIP-S350D810U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332515-927

CATALOG NUMBER: S124DIP-S350D810U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	29				
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25				
3	78	69	62	56	71	63	57	52	51	46	43	40	36	34	29	27	26	21				
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18				
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16				
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14				
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12				
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11				
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10				
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3777	3777	3777
5°	3789	3743	3771
10°	3765	3713	3731
15°	3719	3661	3670
20°	3660	3594	3598
25°	3591	3520	3510
30°	3506	3432	3402
35°	3418	3341	3297
40°	3327	3236	3177
45°	3232	3134	3075
50°	3127	3042	2948
55°	3013	2923	2829
60°	2900	2792	2706
65°	2772	2665	2558
70°	2629	2497	2398
75°	2408	2293	2233
80°	2143	2060	2004
85°	1880	1806	1769



TEST NUMBER: P332515-927

CATALOG NUMBER: S124DIP-S350D810U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.1	1.3
10°-20°	124.2	3.6
20°-30°	182.8	5.3
30°-40°	212.5	6.2
40°-50°	212.5	6.2
50°-60°	185.9	5.4
60°-70°	138.0	4.0
70°-80°	78.4	2.3
80°-90°	25.0	0.7
90°-100°	52.8	1.5
100°-110°	156.5	4.6
110°-120°	265.6	7.8
120°-130°	350.2	10.2
130°-140°	393.3	11.5
140°-150°	386.4	11.3
150°-160°	325.0	9.5
160°-170°	216.2	6.3
170°-180°	75.7	2.2
0°-30°	351.0	10.2
0°-40°	563.5	16.5
0°-60°	961.8	28.1
0°-90°	1203.3	35.1
90°-120°	474.9	13.9
90°-150°	1604.7	46.9
90°-180°	2222.0	64.9
0°-180°	3425.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	466	465	44
15°	445	443	438	440	439	125
25°	403	400	395	396	394	185
35°	347	344	339	336	334	217
45°	283	280	274	270	269	218
55°	214	213	208	203	201	192
65°	145	143	140	136	134	144
75°	77	75	74	72	72	82
85°	20	20	20	20	19	22
90°	2	9	14	17	19	3
95°	37	43	47	49	49	41
105°	144	145	147	149	151	153
115°	270	270	269	268	268	266
125°	393	393	393	391	390	350
135°	507	511	511	510	508	392
145°	616	619	619	619	617	386
155°	706	706	705	708	705	325
165°	769	767	766	769	767	217
175°	800	797	796	800	796	76
180°	801	801	801	801	801	



TEST NUMBER: P332515-927

CATALOG NUMBER: S124DIP-S350D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	469.1	469.0	468.7	468.6	468.3	467.9	467.1	466.4	465.7	464.9	465.6
5°	467.5	467.2	466.9	466.6	466.3	465.6	464.7	463.8	462.9	461.9	462.9
7.5°	463.3	462.9	462.6	462.2	461.9	461.2	460.2	459.2	458.2	457.2	457.9
10°	459.3	459.0	458.7	458.4	458.0	457.3	456.2	455.1	454.1	453.0	453.6
12.5°	454.2	453.9	453.6	453.2	452.9	452.2	451.0	449.9	448.7	447.6	448.3
15°	445.0	444.7	444.4	444.1	443.8	443.0	441.7	440.5	439.2	438.0	438.5
17.5°	434.0	433.6	433.2	432.8	432.4	431.6	430.4	429.2	428.0	426.8	427.1
20°	426.0	425.6	425.2	424.7	424.3	423.5	422.2	421.0	419.7	418.4	418.7
22.5°	417.2	416.7	416.1	415.6	415.0	414.2	412.9	411.7	410.4	409.2	409.6
25°	403.1	402.5	402.0	401.3	400.8	399.9	398.7	397.5	396.4	395.2	395.3
27.5°	386.9	386.3	385.7	385.1	384.5	383.7	382.5	381.5	380.4	379.3	379.1
30°	376.1	375.4	374.8	374.1	373.4	372.6	371.5	370.3	369.3	368.2	367.9
32.5°	364.7	364.1	363.5	362.9	362.3	361.4	360.3	359.1	358.0	356.8	356.4
35°	346.8	346.3	345.7	345.1	344.5	343.6	342.5	341.3	340.2	339.0	338.4
37.5°	328.0	327.5	326.9	326.5	325.9	325.0	323.8	322.5	321.2	320.0	319.3
40°	315.7	315.1	314.4	313.7	313.1	312.1	310.9	309.6	308.3	307.1	306.3
42.5°	302.5	302.1	301.7	301.3	301.0	300.0	298.7	297.2	295.9	294.5	293.5
45°	283.1	282.5	281.9	281.4	280.7	279.8	278.5	277.1	275.8	274.5	273.5
47.5°	262.8	262.4	262.0	261.6	261.2	260.4	259.1	257.9	256.7	255.4	254.4
50°	249.0	248.7	248.3	248.0	247.6	246.9	245.7	244.5	243.4	242.2	241.1
52.5°	235.5	235.0	234.6	234.2	233.9	233.1	231.8	230.6	229.3	228.1	227.1
55°	214.1	213.9	213.6	213.3	213.1	212.4	211.2	210.1	208.9	207.7	206.8
57.5°	193.7	193.5	193.1	192.9	192.6	191.9	190.7	189.6	188.4	187.3	186.3
60°	179.6	179.2	178.8	178.3	177.9	177.2	176.1	175.0	174.0	172.9	172.1
62.5°	165.8	165.5	165.1	164.8	164.4	163.7	162.5	161.4	160.2	159.1	158.4
65°	145.1	144.7	144.3	143.9	143.5	142.8	142.0	141.2	140.3	139.5	138.6
67.5°	124.3	123.9	123.5	123.1	122.7	122.2	121.4	120.6	119.8	118.9	118.1
70°	111.4	110.7	110.2	109.6	109.0	108.4	107.7	107.1	106.4	105.8	105.0
72.5°	97.6	97.0	96.4	95.9	95.2	94.7	94.1	93.6	93.1	92.5	92.0
75°	77.2	76.8	76.4	76.0	75.6	75.2	74.8	74.3	73.9	73.5	73.2
77.5°	57.8	57.7	57.4	57.3	57.1	56.8	56.5	56.1	55.7	55.4	55.2
80°	46.1	45.9	45.6	45.4	45.2	44.9	44.8	44.6	44.4	44.3	44.0
82.5°	34.7	34.6	34.5	34.4	34.2	34.1	34.1	34.1	34.1	34.1	34.0
85°	20.3	20.3	20.3	20.3	20.3	20.2	20.0	19.8	19.6	19.5	19.5
87.5°	8.2	8.4	8.6	8.9	9.1	9.3	9.4	9.6	9.7	9.9	10.1
90°	1.8	3.4	4.9	6.4	7.9	9.2	10.3	11.4	12.5	13.6	14.4
92.5°	13.2	15.0	16.7	18.5	20.2	21.5	22.2	23.0	23.8	24.6	25.0
95°	37.2	38.4	39.6	40.9	42.1	43.3	44.2	45.2	46.1	47.1	47.5
97.5°	64.9	65.9	66.9	67.9	68.8	69.9	71.1	72.2	73.3	74.5	74.9
100°	86.7	87.2	87.8	88.3	88.9	89.8	91.0	92.3	93.5	94.7	95.1
102.5°	109.5	109.7	110.0	110.2	110.4	111.1	112.2	113.3	114.5	115.6	116.0
105°	144.3	144.4	144.6	144.7	144.9	145.2	145.8	146.3	146.9	147.4	147.8
107.5°	180.9	181.0	181.2	181.3	181.5	181.6	181.7	181.8	181.9	182.0	182.4
110°	205.7	205.9	206.1	206.4	206.7	206.8	206.7	206.5	206.4	206.2	206.0



TEST NUMBER: P332515-927

CATALOG NUMBER: S124DIP-S350D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.4	231.4	231.5	231.6	231.6	231.5	231.2	231.0	230.8	230.5	230.4
115°	270.1	270.1	270.1	270.1	270.1	269.9	269.6	269.3	269.0	268.8	268.6
117.5°	306.4	306.6	306.7	306.7	306.9	306.8	306.7	306.4	306.3	306.1	305.6
120°	330.7	331.3	331.8	332.4	333.0	333.0	332.6	332.2	331.8	331.4	330.7
122.5°	356.0	356.2	356.4	356.6	356.9	356.9	356.7	356.5	356.3	356.1	355.6
125°	393.2	393.2	393.2	393.2	393.2	393.2	393.1	392.9	392.8	392.7	392.4
127.5°	427.1	427.5	427.9	428.3	428.7	428.8	428.6	428.4	428.2	427.9	427.7
130°	450.8	451.3	451.7	452.1	452.5	452.7	452.7	452.7	452.7	452.7	452.4
132.5°	475.2	475.5	475.8	476.0	476.3	476.4	476.3	476.3	476.1	476.0	475.7
135°	507.2	508.0	508.9	509.7	510.6	511.0	511.0	511.0	511.0	511.0	510.6
137.5°	542.2	542.6	542.9	543.3	543.7	544.0	544.2	544.5	544.6	544.9	544.5
140°	565.5	565.7	566.0	566.3	566.6	566.6	566.6	566.6	566.6	566.6	566.6
142.5°	586.8	587.0	587.3	587.6	587.9	588.0	587.8	587.7	587.6	587.5	587.5
145°	616.2	616.8	617.3	617.9	618.5	618.8	618.9	619.0	619.2	619.3	619.2
147.5°	645.5	646.1	646.7	647.5	648.1	648.4	648.2	648.2	648.0	647.9	647.8
150°	663.3	663.8	664.4	665.0	665.5	665.7	665.7	665.7	665.7	665.7	665.7
152.5°	680.2	680.5	680.8	681.1	681.4	681.7	681.8	681.9	682.0	682.1	682.5
155°	706.0	706.0	706.0	706.0	706.0	705.9	705.8	705.7	705.5	705.4	705.9
157.5°	727.9	727.5	727.3	727.1	726.8	726.7	726.7	726.7	726.6	726.6	727.0
160°	740.7	740.5	740.5	740.3	740.1	740.0	739.9	739.7	739.6	739.5	739.9
162.5°	752.6	752.3	751.9	751.5	751.1	750.9	750.8	750.7	750.5	750.4	751.1
165°	768.6	768.2	767.8	767.3	766.9	766.6	766.3	766.0	765.7	765.5	766.3
167.5°	780.9	780.2	779.7	779.1	778.6	778.2	778.2	778.3	778.3	778.3	779.2
170°	787.7	787.1	786.4	785.7	785.1	784.7	784.9	785.1	785.1	785.3	786.1
172.5°	792.7	792.2	791.5	791.0	790.4	790.1	790.2	790.2	790.2	790.3	791.2
175°	799.5	798.8	798.1	797.5	796.8	796.4	796.2	796.1	796.0	795.8	796.8
177.5°	801.8	801.2	800.7	800.1	799.5	799.3	799.3	799.3	799.3	799.3	800.0
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7



TEST NUMBER: P332515-927

CATALOG NUMBER: S124DIP-S350D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9
2.5°	466.3	467.0	467.6	467.9	467.9	467.8	467.7	467.6
5°	463.8	464.7	465.6	466.0	465.8	465.6	465.5	465.3
7.5°	458.6	459.4	460.1	460.4	460.3	460.2	460.1	460.0
10°	454.3	455.0	455.7	455.9	455.7	455.5	455.3	455.2
12.5°	449.0	449.7	450.5	450.8	450.5	450.3	450.0	449.8
15°	438.9	439.4	440.0	440.1	439.8	439.6	439.3	439.1
17.5°	427.5	427.8	428.1	428.2	428.0	427.9	427.7	427.5
20°	419.0	419.2	419.5	419.5	419.3	419.1	419.0	418.8
22.5°	410.0	410.5	411.0	411.1	410.7	410.4	410.1	409.9
25°	395.4	395.5	395.5	395.5	395.1	394.7	394.4	394.1
27.5°	378.9	378.7	378.5	378.2	377.8	377.4	376.9	376.5
30°	367.6	367.3	366.9	366.5	366.1	365.7	365.3	364.9
32.5°	356.0	355.6	355.2	354.8	354.4	353.9	353.6	353.2
35°	337.8	337.2	336.6	336.1	335.7	335.3	334.9	334.5
37.5°	318.7	318.1	317.4	316.9	316.3	315.8	315.2	314.7
40°	305.5	304.6	303.8	303.2	302.7	302.3	301.9	301.5
42.5°	292.6	291.6	290.7	290.0	289.7	289.5	289.1	288.9
45°	272.7	271.7	270.8	270.2	270.0	269.7	269.5	269.3
47.5°	253.3	252.3	251.3	250.5	249.9	249.2	248.6	248.0
50°	239.9	238.8	237.6	236.7	236.2	235.8	235.2	234.7
52.5°	226.1	225.1	224.0	223.2	222.5	221.9	221.3	220.6
55°	205.7	204.7	203.7	203.0	202.5	202.0	201.5	201.0
57.5°	185.4	184.4	183.5	182.8	182.3	181.8	181.3	180.8
60°	171.3	170.6	169.8	169.3	168.9	168.4	168.0	167.6
62.5°	157.7	157.0	156.3	155.7	155.3	155.0	154.6	154.1
65°	137.8	137.0	136.2	135.5	135.1	134.7	134.3	133.9
67.5°	117.3	116.5	115.7	115.3	115.2	115.0	114.9	114.8
70°	104.4	103.8	103.1	102.6	102.3	102.1	101.9	101.6
72.5°	91.5	90.9	90.4	90.0	89.8	89.5	89.3	89.0
75°	72.8	72.5	72.2	71.9	71.9	71.8	71.7	71.6
77.5°	55.1	55.1	55.0	54.8	54.6	54.3	54.1	53.9
80°	43.9	43.7	43.6	43.5	43.3	43.3	43.2	43.1
82.5°	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2
85°	19.5	19.5	19.5	19.5	19.4	19.3	19.2	19.1
87.5°	10.2	10.5	10.6	10.7	10.8	10.8	10.9	10.9
90°	15.3	16.1	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	25.5	26.0	26.5	26.9	27.0	27.2	27.3	27.5
95°	47.9	48.3	48.7	49.0	49.0	49.0	49.0	49.0
97.5°	75.4	75.9	76.4	76.7	76.7	76.7	76.7	76.7
100°	95.3	95.6	95.9	96.0	96.0	96.0	96.0	96.0
102.5°	116.4	116.7	117.1	117.3	117.5	117.6	117.7	117.8
105°	148.2	148.6	149.0	149.5	149.9	150.3	150.7	151.1
107.5°	182.8	183.1	183.5	183.7	183.6	183.6	183.6	183.5
110°	205.7	205.4	205.1	205.2	205.7	206.0	206.4	206.8





TEST NUMBER: P332515-927

CATALOG NUMBER: S124DIP-S350D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.4	230.4	230.3	230.3	230.4	230.4	230.5	230.6
115°	268.5	268.4	268.2	268.1	268.0	267.8	267.7	267.5
117.5°	305.1	304.7	304.2	303.8	303.6	303.2	303.0	302.7
120°	329.9	329.2	328.6	328.4	328.7	328.9	329.2	329.5
122.5°	355.1	354.7	354.3	353.8	353.2	352.8	352.3	351.8
125°	392.1	391.8	391.6	391.3	391.0	390.7	390.5	390.1
127.5°	427.4	427.1	426.8	426.6	426.4	426.2	426.0	425.7
130°	452.2	451.9	451.6	451.2	450.7	450.1	449.6	449.0
132.5°	475.5	475.2	474.9	474.7	474.4	474.2	474.0	473.8
135°	510.4	510.1	509.8	509.5	509.1	508.7	508.3	507.9
137.5°	544.2	543.8	543.4	543.3	543.4	543.4	543.5	543.7
140°	566.4	566.3	566.1	566.0	565.9	565.7	565.5	565.5
142.5°	587.4	587.4	587.4	587.3	587.3	587.3	587.2	587.2
145°	619.0	618.9	618.8	618.5	618.1	617.7	617.3	616.9
147.5°	647.7	647.6	647.5	647.4	647.2	647.1	647.0	646.8
150°	665.7	665.7	665.7	665.7	665.6	665.4	665.3	665.1
152.5°	682.8	683.1	683.4	683.4	683.1	682.7	682.4	682.0
155°	706.5	707.0	707.6	707.6	707.0	706.5	705.9	705.4
157.5°	727.4	727.9	728.3	728.2	727.8	727.3	726.8	726.4
160°	740.3	740.7	741.1	741.0	740.3	739.6	738.9	738.2
162.5°	751.9	752.6	753.4	753.4	752.7	752.0	751.3	750.6
165°	767.1	767.9	768.8	768.9	768.3	767.8	767.2	766.8
167.5°	780.0	780.9	781.6	781.6	780.8	779.9	779.1	778.2
170°	787.0	787.7	788.6	788.5	787.6	786.6	785.6	784.7
172.5°	792.1	793.1	794.0	794.0	793.1	792.0	791.1	790.1
175°	797.7	798.7	799.7	799.7	798.7	797.7	796.8	795.8
177.5°	800.8	801.6	802.4	802.3	801.5	800.6	799.7	798.8
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7

(END OF REPORT)