

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332541-927

Luminaire Tested: **S124DIP-S575D365U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332541-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S575D365U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3133.1 lumens  
Efficiency: N/A  
Efficacy: 113.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332541-927

CATALOG NUMBER: S124DIP-S575D365U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332541-927

CATALOG NUMBER: S124DIP-S575D365U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6211	6211	6211
5°	6229	6155	6199
10°	6190	6105	6135
15°	6115	6018	6033
20°	6016	5910	5916
25°	5903	5787	5770
30°	5764	5643	5591
35°	5619	5492	5419
40°	5469	5321	5223
45°	5313	5151	5053
50°	5141	5001	4847
55°	4954	4807	4650
60°	4766	4589	4448
65°	4556	4380	4204
70°	4322	4102	3944
75°	3961	3768	3671
80°	3524	3380	3296
85°	3084	2973	2908



TEST NUMBER: P332541-927

CATALOG NUMBER: S124DIP-S575D365U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.5	2.3
10°-20°	204.1	6.5
20°-30°	300.5	9.6
30°-40°	349.3	11.1
40°-50°	349.3	11.1
50°-60°	305.5	9.8
60°-70°	226.9	7.2
70°-80°	128.9	4.1
80°-90°	38.3	1.2
90°-100°	12.8	0.4
100°-110°	81.6	2.6
110°-120°	156.1	5.0
120°-130°	198.2	6.3
130°-140°	212.1	6.8
140°-150°	198.3	6.3
150°-160°	159.9	5.1
160°-170°	103.2	3.3
170°-180°	35.6	1.1
0°-30°	577.0	18.4
0°-40°	926.3	29.6
0°-60°	1581.2	50.5
0°-90°	1975.3	63.0
90°-120°	250.6	8.0
90°-150°	859.2	27.4
90°-180°	1158.0	37.0
0°-180°	3133.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	760	766	765	73
15°	732	729	720	723	722	206
25°	663	658	650	650	648	305
35°	570	566	557	553	550	356
45°	465	461	451	445	443	359
55°	352	350	342	334	330	315
65°	238	235	229	223	220	236
75°	127	124	121	118	118	135
85°	33	33	32	32	31	37
90°	1	4	6	8	8	3
95°	15	6	6	8	8	20
105°	84	86	87	89	80	88
115°	157	158	158	158	158	155
125°	221	222	222	222	223	197
135°	274	274	275	276	276	211
145°	316	317	317	317	318	198
155°	347	347	346	347	347	160
165°	366	365	364	366	364	103
175°	374	373	373	375	372	36
180°	374	374	374	374	374	



TEST NUMBER: P332541-927

CATALOG NUMBER: S124DIP-S575D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	771.3	771.0	770.6	770.3	770.0	769.2	768.0	766.8	765.6	764.4	765.5
5°	768.7	768.2	767.6	767.1	766.5	765.5	764.0	762.5	761.0	759.5	761.0
7.5°	761.5	761.0	760.5	759.9	759.4	758.3	756.6	754.9	753.2	751.5	752.8
10°	755.1	754.6	754.1	753.5	753.0	751.8	750.0	748.2	746.5	744.7	745.8
12.5°	746.8	746.2	745.7	745.1	744.6	743.4	741.5	739.6	737.7	735.8	737.0
15°	731.7	731.2	730.6	730.1	729.5	728.3	726.2	724.1	722.1	720.0	720.8
17.5°	713.6	712.9	712.3	711.5	710.8	709.6	707.6	705.7	703.7	701.8	702.3
20°	700.3	699.6	698.9	698.2	697.5	696.2	694.1	692.1	690.0	687.9	688.3
22.5°	686.0	685.1	684.2	683.3	682.4	680.9	678.8	676.8	674.7	672.6	673.4
25°	662.7	661.7	660.8	659.8	658.9	657.4	655.5	653.6	651.6	649.7	649.9
27.5°	636.0	635.1	634.1	633.1	632.1	630.7	628.9	627.2	625.3	623.6	623.3
30°	618.3	617.2	616.1	615.0	613.9	612.4	610.7	608.9	607.1	605.4	604.8
32.5°	599.5	598.6	597.5	596.6	595.6	594.1	592.3	590.4	588.5	586.6	586.0
35°	570.2	569.3	568.3	567.4	566.4	564.9	563.0	561.1	559.2	557.3	556.3
37.5°	539.2	538.4	537.5	536.6	535.8	534.3	532.3	530.2	528.1	526.1	525.1
40°	519.0	517.9	516.8	515.8	514.7	513.1	511.0	509.0	506.9	504.9	503.5
42.5°	497.3	496.7	496.1	495.4	494.7	493.2	491.0	488.7	486.4	484.2	482.6
45°	465.4	464.5	463.5	462.6	461.6	460.0	457.8	455.6	453.4	451.2	449.7
47.5°	432.0	431.3	430.7	430.0	429.4	428.0	426.0	424.0	421.9	419.9	418.2
50°	409.3	408.8	408.2	407.7	407.1	405.9	404.0	402.0	400.1	398.2	396.3
52.5°	387.1	386.5	385.8	385.2	384.5	383.2	381.1	379.1	377.1	375.0	373.4
55°	352.0	351.6	351.2	350.8	350.4	349.2	347.3	345.3	343.4	341.5	339.8
57.5°	318.5	318.0	317.5	317.0	316.6	315.4	313.5	311.6	309.7	307.8	306.3
60°	295.2	294.6	293.9	293.2	292.6	291.3	289.5	287.7	286.0	284.2	283.0
62.5°	272.6	272.0	271.4	270.8	270.3	269.0	267.2	265.3	263.4	261.5	260.4
65°	238.5	237.9	237.2	236.5	235.8	234.8	233.5	232.0	230.7	229.3	227.9
67.5°	204.3	203.7	203.0	202.4	201.8	200.8	199.5	198.2	196.9	195.5	194.2
70°	183.1	182.1	181.2	180.2	179.3	178.2	177.1	176.0	174.9	173.8	172.8
72.5°	160.4	159.5	158.5	157.5	156.5	155.7	154.8	153.9	153.0	152.1	151.2
75°	127.0	126.3	125.6	124.9	124.2	123.6	122.9	122.2	121.5	120.8	120.3
77.5°	95.1	94.7	94.4	94.2	93.9	93.4	92.8	92.2	91.6	91.0	90.8
80°	75.8	75.4	75.0	74.6	74.1	73.8	73.6	73.3	73.0	72.7	72.5
82.5°	57.1	56.9	56.7	56.5	56.3	56.2	56.2	56.1	56.0	56.0	55.8
85°	33.3	33.3	33.3	33.3	33.3	33.1	32.9	32.6	32.3	32.1	32.1
87.5°	13.0	13.0	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.2
90°	0.9	1.5	2.2	2.9	3.6	4.2	4.7	5.1	5.6	6.2	6.5
92.5°	3.6	3.6	3.6	3.6	3.6	4.0	4.4	4.9	5.5	5.9	6.3
95°	15.4	13.3	11.2	9.0	7.0	5.9	5.9	6.0	6.1	6.2	6.5
97.5°	32.7	34.0	35.3	36.7	37.9	35.2	28.2	21.3	14.3	7.4	7.4
100°	45.9	47.1	48.2	49.3	50.4	46.7	38.1	29.5	20.9	12.4	11.2
102.5°	60.7	61.6	62.3	63.1	64.0	63.8	62.7	61.6	60.4	59.3	47.9
105°	84.3	84.6	85.0	85.4	85.8	86.1	86.4	86.7	87.1	87.4	87.9
107.5°	106.2	106.3	106.5	106.7	106.9	107.2	107.7	108.1	108.4	108.9	109.2
110°	121.0	121.1	121.3	121.5	121.7	122.0	122.3	122.7	123.1	123.5	123.6



TEST NUMBER: P332541-927

CATALOG NUMBER: S124DIP-S575D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	135.3	135.6	135.9	136.3	136.7	136.9	137.0	137.2	137.4	137.6	137.5
115°	157.3	157.6	157.7	157.9	158.1	158.1	158.1	158.0	158.0	157.9	158.0
117.5°	177.2	177.4	177.7	178.0	178.2	178.4	178.6	178.7	178.8	179.0	179.0
120°	190.7	190.9	191.2	191.4	191.6	191.7	191.7	191.6	191.5	191.5	191.6
122.5°	203.2	203.4	203.5	203.7	203.8	203.9	204.0	204.1	204.1	204.3	204.3
125°	221.2	221.4	221.7	221.9	222.2	222.2	222.1	222.0	221.9	221.7	221.9
127.5°	238.2	238.3	238.3	238.4	238.4	238.6	238.9	239.2	239.5	239.8	239.7
130°	249.1	249.2	249.3	249.4	249.5	249.5	249.7	249.9	250.1	250.3	250.3
132.5°	259.3	259.4	259.4	259.6	259.7	259.8	260.1	260.3	260.5	260.8	260.9
135°	274.3	274.3	274.3	274.2	274.1	274.2	274.5	274.7	275.0	275.2	275.4
137.5°	287.7	287.8	287.8	287.8	287.9	288.0	288.3	288.5	288.8	289.1	289.2
140°	296.5	296.6	296.8	296.8	297.0	297.1	297.2	297.4	297.5	297.6	297.8
142.5°	304.4	304.5	304.8	305.0	305.2	305.4	305.5	305.5	305.6	305.7	305.8
145°	316.4	316.6	316.7	317.0	317.1	317.2	317.2	317.2	317.2	317.2	317.3
147.5°	325.9	326.3	326.6	327.0	327.3	327.5	327.4	327.3	327.3	327.3	327.3
150°	332.9	333.1	333.4	333.7	333.9	334.0	333.9	333.8	333.7	333.7	333.7
152.5°	338.7	338.9	339.1	339.3	339.5	339.5	339.5	339.3	339.2	339.1	339.2
155°	346.9	347.0	347.0	347.1	347.1	347.1	346.9	346.7	346.5	346.3	346.6
157.5°	353.8	353.7	353.7	353.6	353.6	353.5	353.3	353.1	352.8	352.7	353.0
160°	357.8	357.6	357.4	357.3	357.0	357.0	356.9	356.8	356.7	356.6	357.0
162.5°	361.4	361.2	360.9	360.7	360.4	360.3	360.2	360.1	360.1	360.0	360.4
165°	365.9	365.6	365.3	365.0	364.6	364.5	364.5	364.5	364.5	364.5	365.0
167.5°	369.5	369.2	368.8	368.5	368.2	368.0	368.0	368.0	367.9	367.9	368.4
170°	371.5	371.1	370.7	370.4	370.0	369.9	369.9	370.0	370.0	370.1	370.6
172.5°	372.9	372.5	372.1	371.8	371.4	371.2	371.3	371.4	371.4	371.5	371.9
175°	374.3	373.9	373.6	373.2	372.8	372.6	372.7	372.8	372.9	372.9	373.5
177.5°	375.0	374.6	374.3	373.9	373.6	373.4	373.6	373.7	373.8	373.8	374.3
180°	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3



TEST NUMBER: P332541-927

CATALOG NUMBER: S124DIP-S575D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	766.6	767.7	768.8	769.3	769.1	769.1	769.0	768.8
5°	762.5	764.0	765.5	766.1	765.8	765.6	765.2	765.0
7.5°	754.0	755.2	756.4	756.9	756.8	756.6	756.5	756.2
10°	746.9	748.0	749.1	749.5	749.2	748.9	748.6	748.4
12.5°	738.2	739.4	740.6	741.0	740.6	740.2	739.9	739.5
15°	721.7	722.5	723.3	723.5	723.1	722.7	722.2	721.8
17.5°	702.8	703.3	703.9	703.9	703.7	703.4	703.1	702.9
20°	688.8	689.2	689.6	689.7	689.4	689.1	688.9	688.6
22.5°	674.1	674.9	675.7	675.7	675.3	674.8	674.3	673.8
25°	650.0	650.1	650.3	650.1	649.5	649.0	648.4	647.8
27.5°	623.0	622.6	622.3	621.8	621.1	620.4	619.7	619.0
30°	604.3	603.7	603.2	602.5	601.8	601.2	600.5	599.8
32.5°	585.3	584.6	584.0	583.3	582.7	581.9	581.2	580.6
35°	555.3	554.4	553.4	552.6	551.9	551.2	550.6	549.9
37.5°	524.0	522.9	521.9	520.9	520.1	519.1	518.2	517.3
40°	502.2	500.7	499.4	498.4	497.6	497.0	496.3	495.6
42.5°	481.0	479.3	477.8	476.7	476.3	475.9	475.4	474.9
45°	448.2	446.7	445.2	444.3	443.9	443.5	443.0	442.6
47.5°	416.5	414.8	413.1	411.8	410.7	409.6	408.6	407.6
50°	394.3	392.4	390.5	389.2	388.3	387.5	386.7	385.9
52.5°	371.6	369.9	368.3	366.9	365.8	364.8	363.8	362.7
55°	338.3	336.6	334.9	333.7	332.9	332.1	331.2	330.4
57.5°	304.8	303.2	301.6	300.4	299.6	298.8	298.0	297.2
60°	281.7	280.5	279.2	278.3	277.6	276.9	276.2	275.5
62.5°	259.3	258.1	257.0	256.1	255.4	254.8	254.1	253.3
65°	226.6	225.2	223.9	222.8	222.1	221.4	220.8	220.1
67.5°	192.9	191.6	190.3	189.5	189.3	189.2	188.9	188.8
70°	171.7	170.6	169.4	168.7	168.3	167.9	167.5	167.1
72.5°	150.4	149.5	148.6	148.0	147.6	147.2	146.8	146.3
75°	119.7	119.1	118.7	118.3	118.1	118.0	117.9	117.7
77.5°	90.6	90.5	90.3	90.1	89.7	89.4	89.0	88.6
80°	72.2	71.9	71.6	71.5	71.3	71.1	71.1	70.9
82.5°	55.6	55.5	55.3	55.1	55.1	54.9	54.7	54.6
85°	32.1	32.1	32.1	32.0	31.8	31.7	31.6	31.4
87.5°	13.2	13.3	13.4	13.4	13.5	13.5	13.5	13.5
90°	6.9	7.3	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	6.7	7.1	7.4	7.6	7.7	7.7	7.7	7.8
95°	6.9	7.3	7.7	7.8	7.9	8.0	8.1	8.1
97.5°	7.4	7.5	7.5	7.6	7.7	7.7	7.8	7.8
100°	10.2	9.1	8.1	7.6	7.7	7.7	7.8	7.8
102.5°	36.5	25.1	13.7	8.0	8.0	8.0	8.1	8.1
105°	88.5	89.0	89.6	88.7	86.5	84.3	82.0	79.8
107.5°	109.5	109.7	110.0	110.3	110.5	110.7	111.0	111.2
110°	123.7	123.8	124.0	124.1	124.3	124.5	124.7	124.8





TEST NUMBER: P332541-927

CATALOG NUMBER: S124DIP-S575D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.5	137.5	137.4	137.6	137.8	138.1	138.3	138.6
115°	158.1	158.3	158.4	158.4	158.4	158.4	158.4	158.4
117.5°	178.9	178.9	178.9	178.8	178.8	178.8	178.8	178.7
120°	191.7	191.9	192.0	192.0	191.9	191.7	191.6	191.5
122.5°	204.4	204.5	204.5	204.5	204.4	204.3	204.1	204.1
125°	222.1	222.3	222.4	222.6	222.7	222.8	222.8	222.8
127.5°	239.7	239.6	239.6	239.6	239.6	239.5	239.4	239.4
130°	250.4	250.5	250.6	250.6	250.6	250.6	250.6	250.6
132.5°	260.9	261.0	261.1	261.1	261.0	260.9	260.9	260.9
135°	275.4	275.6	275.7	275.8	275.9	276.1	276.2	276.3
137.5°	289.4	289.5	289.6	289.7	289.6	289.6	289.5	289.5
140°	297.9	298.2	298.3	298.5	298.6	298.6	298.7	298.7
142.5°	305.9	306.1	306.2	306.3	306.3	306.3	306.3	306.3
145°	317.3	317.4	317.4	317.5	317.7	317.8	317.9	318.1
147.5°	327.3	327.4	327.4	327.5	327.6	327.6	327.6	327.7
150°	333.7	333.7	333.7	333.7	333.8	333.9	333.9	334.0
152.5°	339.3	339.4	339.5	339.5	339.5	339.5	339.5	339.4
155°	346.8	347.1	347.3	347.4	347.1	347.0	346.8	346.6
157.5°	353.3	353.6	353.9	353.9	353.6	353.3	353.0	352.7
160°	357.4	357.8	358.1	358.1	357.8	357.4	357.0	356.6
162.5°	360.8	361.2	361.6	361.5	361.1	360.7	360.2	359.8
165°	365.5	366.0	366.5	366.5	365.9	365.4	364.8	364.2
167.5°	369.0	369.6	370.0	370.0	369.4	368.8	368.1	367.6
170°	371.1	371.6	372.1	372.0	371.5	370.8	370.2	369.6
172.5°	372.5	373.0	373.4	373.4	372.7	372.0	371.4	370.7
175°	374.1	374.6	375.2	375.1	374.3	373.6	372.8	372.1
177.5°	374.7	375.1	375.5	375.3	374.8	374.1	373.6	373.0
180°	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3

(END OF REPORT)