

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331875-940

Luminaire Tested: **S123DIP-S340D585U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331875-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3089.9 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																												
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42	36																												
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30																												
3	80	71	64	58	73	65	59	54	54	49	46	44	41	38	34	32	30	26																												
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22																												
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20																												
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20	17																												
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																												
8	53	41	34	28	48	38	31	27	32	27	23	26	22	20	21	18	16	14																												
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12																												
10	46	34	27	23	42	32	25	21	27	22	18	22	19	16	18	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4614	4614	4614	4614
5°	5503	4635	4107	4635
10°	6889	4612	3711	4612
15°	8449	4574	3455	4574
20°	10065	4517	3289	4517
25°	10688	4445	3252	4445
30°	9161	4395	3269	4395
35°	6370	4322	3303	4322
40°	4799	4235	3292	4235
45°	3984	4107	3252	4107
50°	3569	3848	3220	3848
55°	3337	3567	3181	3567
60°	3130	3272	3147	3272
65°	2942	2985	3049	2985
70°	2760	2656	2902	2656
75°	2470	2325	2662	2325
80°	2163	1909	2294	1909
85°	1692	1383	1544	1383



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	1.4
10°-20°	135.4	4.4
20°-30°	227.3	7.4
30°-40°	257.4	8.3
40°-50°	230.8	7.5
50°-60°	186.3	6.0
60°-70°	129.8	4.2
70°-80°	68.2	2.2
80°-90°	18.6	0.6
90°-100°	42.2	1.4
100°-110°	126.2	4.1
110°-120°	214.7	6.9
120°-130°	282.4	9.1
130°-140°	317.5	10.3
140°-150°	312.1	10.1
150°-160°	262.7	8.5
160°-170°	174.9	5.7
170°-180°	61.2	2.0
0°-30°	405.0	13.1
0°-40°	662.4	21.4
0°-60°	1079.4	34.9
0°-90°	1296.0	41.9
90°-120°	383.2	12.4
90°-150°	1295.1	41.9
90°-180°	1794.0	58.1
0°-180°	3089.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	429	429	429	429	429	
5°	509	429	380	429	509	53
15°	758	410	310	410	758	219
25°	900	374	274	374	900	395
35°	485	329	251	329	485	315
45°	262	270	214	270	262	207
55°	178	190	170	190	178	160
65°	116	117	120	117	116	115
75°	59	56	64	56	59	64
85°	14	11	12	11	14	17
90°	15	0	15	0	15	8
95°	40	30	40	30	40	41
105°	121	114	121	114	121	128
115°	217	216	217	216	217	215
125°	313	316	313	316	313	280
135°	410	410	410	410	410	315
145°	498	498	498	498	498	311
155°	569	570	569	570	569	262
165°	619	621	619	621	619	175
175°	643	646	643	646	643	61
180°	648	648	648	648	648	



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	455.0	454.7	453.9	454.5	453.2	451.4	451.2	449.5	444.7	444.4	443.1
5°	509.3	507.7	507.5	507.3	504.4	500.4	492.9	492.3	482.3	477.4	471.4
7.5°	579.8	580.6	577.6	575.0	566.1	560.2	552.1	541.9	529.7	517.2	509.0
10°	630.3	637.1	628.7	622.8	617.4	607.3	595.4	580.6	565.9	548.7	535.6
12.5°	684.5	687.8	686.1	680.6	672.3	656.7	635.8	619.5	605.9	577.2	565.6
15°	758.2	770.9	762.8	744.1	744.5	729.8	702.4	672.3	656.2	631.1	596.8
17.5°	836.9	838.4	835.0	819.4	809.0	788.7	763.4	734.6	702.1	671.7	635.3
20°	878.7	877.4	870.2	862.1	844.3	828.5	800.8	768.7	727.1	697.1	657.5
22.5°	902.0	899.9	896.4	889.7	874.9	857.9	833.0	797.9	758.3	717.1	671.3
25°	899.9	902.6	903.0	901.2	896.0	885.8	866.3	838.2	798.8	745.7	698.0
27.5°	818.5	822.3	833.4	843.3	854.3	865.5	864.0	850.1	820.8	775.1	716.7
30°	737.1	728.7	749.3	775.3	792.9	824.1	841.5	842.6	826.2	786.9	730.0
32.5°	624.0	633.2	642.3	674.2	712.8	747.8	782.6	810.5	813.7	787.6	737.8
35°	484.8	496.3	512.9	529.5	571.1	606.8	667.9	721.0	763.4	769.0	738.5
37.5°	390.7	396.4	406.9	423.6	450.7	493.1	540.3	607.5	669.0	714.6	716.6
40°	341.5	343.2	355.0	367.7	389.7	424.6	467.2	526.6	600.1	664.0	690.5
42.5°	304.6	308.3	313.3	325.5	343.0	369.3	408.8	458.0	525.4	598.8	650.8
45°	261.7	265.9	269.0	277.1	289.6	307.3	334.8	379.8	431.1	506.8	576.8
47.5°	233.4	233.7	236.0	242.2	250.7	263.9	283.5	312.3	359.4	420.9	492.8
50°	213.1	216.4	217.3	222.0	228.7	238.4	254.7	279.2	317.8	371.8	437.9
52.5°	198.9	199.8	202.2	205.6	211.4	219.0	233.1	252.3	282.6	328.7	389.4
55°	177.8	177.8	180.1	182.8	186.1	193.0	202.3	216.4	239.5	275.3	325.6
57.5°	158.4	159.4	161.0	161.8	164.7	169.2	177.0	187.8	204.9	232.5	272.4
60°	145.4	147.3	147.0	148.7	151.2	154.8	161.4	170.1	185.5	207.5	241.2
62.5°	134.1	134.0	133.9	136.0	138.4	141.8	146.2	153.6	166.7	186.3	214.9
65°	115.5	115.1	116.5	117.8	118.6	121.1	124.4	131.1	139.8	154.4	176.6
67.5°	99.0	97.7	98.5	99.0	100.4	102.4	105.5	109.6	116.5	128.1	144.9
70°	87.7	86.6	86.4	86.9	88.1	89.5	91.8	95.8	102.2	111.6	123.8
72.5°	76.1	75.3	75.3	76.2	76.8	77.8	79.4	82.9	88.1	95.1	106.6
75°	59.4	59.4	59.4	59.7	60.3	61.1	62.3	64.2	68.1	73.1	80.8
77.5°	44.5	44.5	44.2	44.2	45.1	45.5	45.7	47.5	49.8	53.1	58.7
80°	34.9	33.9	34.2	34.9	35.3	35.5	36.1	36.6	38.4	40.3	44.2
82.5°	25.9	25.1	25.1	26.1	26.2	26.4	27.0	27.6	28.3	30.0	32.1
85°	13.7	13.7	13.9	13.9	14.1	13.9	14.5	14.7	14.7	15.8	17.0
87.5°	8.0	7.7	7.8	7.9	7.7	7.8	7.8	7.9	8.0	8.1	7.9
90°	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1	12.7	12.2	10.7
92.5°	20.5	20.7	20.8	21.0	21.1	21.0	20.6	20.2	19.9	19.5	18.7
95°	39.7	39.7	39.7	39.7	39.7	39.4	39.0	38.5	38.1	37.6	36.7
97.5°	61.0	61.1	61.1	61.2	61.2	61.0	60.5	59.9	59.4	58.9	58.2
100°	77.3	77.0	76.9	76.6	76.4	76.2	75.8	75.4	75.1	74.7	74.2
102.5°	94.0	94.1	94.1	94.2	94.2	94.0	93.7	93.4	93.0	92.6	91.9
105°	121.1	120.8	120.6	120.4	120.1	120.0	120.0	120.0	120.0	120.0	119.0
107.5°	149.3	149.4	149.5	149.6	149.8	149.6	149.3	148.9	148.6	148.2	147.8
110°	168.4	168.6	168.8	169.1	169.2	169.2	168.7	168.3	167.8	167.4	167.1



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.7	188.8	188.8	188.9	188.9	188.6	188.1	187.5	187.0	186.5	186.5
115°	216.7	216.8	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7	216.9
117.5°	245.0	245.4	245.7	246.0	246.3	246.5	246.5	246.6	246.6	246.6	246.9
120°	265.0	265.2	265.5	265.6	265.9	266.1	266.2	266.3	266.4	266.5	267.1
122.5°	284.1	284.5	284.7	285.1	285.3	285.7	286.0	286.2	286.6	286.9	287.1
125°	312.8	313.3	313.7	314.1	314.6	315.0	315.5	315.9	316.4	316.9	317.1
127.5°	341.3	341.9	342.4	343.0	343.5	344.0	344.6	345.3	346.0	346.6	346.8
130°	360.1	360.9	361.7	362.5	363.3	363.9	364.4	364.8	365.2	365.7	366.0
132.5°	379.6	380.2	380.8	381.5	382.1	382.6	383.2	383.7	384.2	384.9	385.0
135°	409.9	410.2	410.4	410.6	410.8	411.2	411.6	412.1	412.6	413.0	413.1
137.5°	436.7	437.1	437.6	438.0	438.5	438.9	439.3	439.8	440.3	440.8	440.5
140°	454.2	455.0	455.8	456.6	457.4	457.8	457.9	458.1	458.2	458.3	458.2
142.5°	472.1	472.7	473.3	473.9	474.6	474.9	475.0	475.1	475.3	475.4	475.2
145°	497.9	498.4	498.8	499.3	499.7	500.1	500.2	500.2	500.3	500.5	500.2
147.5°	520.9	521.7	522.3	523.0	523.6	524.0	524.0	524.0	524.0	524.0	523.7
150°	535.6	536.3	536.9	537.6	538.3	538.6	538.6	538.6	538.6	538.6	538.4
152.5°	549.8	550.5	551.0	551.6	552.1	552.4	552.2	552.1	551.8	551.6	551.5
155°	569.2	570.0	570.7	571.5	572.3	572.5	572.0	571.6	571.1	570.7	570.6
157.5°	586.7	587.4	588.0	588.6	589.2	589.3	588.9	588.4	587.9	587.5	587.4
160°	598.2	598.6	599.1	599.5	599.9	599.9	599.3	598.8	598.2	597.6	597.6
162.5°	606.7	607.4	608.1	608.9	609.6	609.7	609.1	608.5	608.0	607.4	607.3
165°	619.0	619.8	620.5	621.3	622.1	622.2	621.5	620.9	620.2	619.5	619.5
167.5°	629.5	630.2	630.9	631.6	632.3	632.3	631.6	630.9	630.2	629.5	629.4
170°	634.7	635.5	636.3	637.1	637.9	637.9	637.1	636.3	635.5	634.7	634.7
172.5°	638.8	639.6	640.4	641.2	642.0	642.0	641.3	640.6	640.0	639.3	639.3
175°	643.4	644.2	645.0	645.8	646.6	646.7	646.0	645.2	644.6	643.9	643.9
177.5°	645.9	646.5	647.1	647.7	648.4	648.5	647.9	647.4	646.8	646.2	646.2
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	442.0	440.8	439.4	437.1	435.1	432.3	431.4	430.4	427.4	424.8	422.8
5°	469.0	464.0	456.8	450.1	444.8	437.5	433.4	429.0	422.8	417.1	412.6
7.5°	497.3	487.5	476.2	464.0	452.6	441.7	432.8	424.9	416.2	408.0	401.4
10°	519.8	505.6	489.8	472.8	458.3	444.2	432.3	422.0	410.7	400.9	392.8
12.5°	545.4	524.4	502.7	482.0	464.8	445.1	430.8	417.6	404.8	393.2	384.1
15°	575.6	549.0	523.3	494.8	468.7	444.2	427.1	410.5	395.7	383.7	372.0
17.5°	603.2	573.1	539.1	504.5	473.0	443.9	420.1	401.3	382.8	368.1	356.5
20°	618.8	584.6	546.2	510.2	475.3	442.9	416.7	394.3	374.3	358.7	345.7
22.5°	632.3	592.2	552.4	514.0	475.1	440.2	410.5	387.4	365.9	350.6	336.7
25°	646.3	598.2	558.4	513.4	469.9	433.7	400.6	374.3	352.8	334.8	320.6
27.5°	658.3	597.9	550.5	502.0	461.6	425.4	389.9	361.9	338.9	319.5	305.0
30°	666.2	598.7	542.4	494.5	453.7	416.3	381.8	353.6	329.5	309.8	296.0
32.5°	671.2	598.2	534.9	483.8	441.0	408.0	373.0	343.8	319.0	299.6	286.4
35°	674.1	594.5	522.0	461.8	420.7	388.4	359.2	328.9	302.9	284.8	269.8
37.5°	668.2	586.8	507.1	440.6	395.6	363.9	339.2	313.4	288.6	268.7	255.7
40°	659.2	581.8	495.4	425.6	378.3	347.8	326.8	301.4	276.9	258.0	245.9
42.5°	641.7	571.8	482.7	409.0	360.3	329.8	310.5	289.3	266.1	248.3	236.3
45°	599.1	549.7	463.4	384.1	333.9	302.3	285.3	269.8	248.9	231.7	221.2
47.5°	540.0	516.5	435.7	357.8	306.1	275.8	258.1	245.8	230.4	216.4	206.5
50°	499.0	489.2	417.0	339.8	287.8	258.0	240.9	229.8	218.7	204.8	195.7
52.5°	451.7	457.6	395.0	321.3	268.9	239.7	223.7	214.8	204.8	193.3	185.4
55°	385.0	406.7	357.1	290.0	240.9	213.1	198.0	190.1	184.2	175.8	168.9
57.5°	322.5	350.3	316.1	257.8	213.5	189.5	175.0	166.4	162.6	158.2	152.8
60°	285.4	312.8	286.9	236.2	195.1	172.2	159.3	152.0	148.3	145.2	140.6
62.5°	252.4	280.1	258.3	214.3	176.9	155.8	144.5	137.4	134.6	133.0	129.0
65°	206.9	230.8	216.2	180.1	151.1	132.3	122.2	117.2	114.5	113.9	111.4
67.5°	168.4	186.5	176.0	149.4	126.5	110.4	101.7	97.5	95.4	95.1	93.3
70°	143.1	160.2	152.0	128.0	108.3	95.6	88.1	84.4	83.1	82.9	81.9
72.5°	123.5	135.4	128.9	108.9	93.6	82.1	76.6	72.7	71.3	71.6	70.9
75°	91.4	100.3	96.6	82.7	70.4	63.0	58.4	55.9	54.7	55.3	54.4
77.5°	65.8	71.4	68.0	58.4	50.8	45.5	42.1	40.6	39.4	39.4	39.1
80°	49.7	53.0	51.1	45.3	39.1	34.5	31.7	30.8	30.1	29.9	29.7
82.5°	35.4	38.2	35.9	32.0	27.7	25.0	23.5	22.1	21.7	21.8	21.6
85°	17.8	18.9	18.1	15.6	13.9	12.7	11.9	11.2	10.8	11.0	10.6
87.5°	8.0	7.8	7.0	6.2	5.6	4.9	4.6	4.1	4.0	4.2	4.3
90°	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5	1.6	2.8	3.9
92.5°	17.8	17.0	16.2	15.4	14.6	13.8	13.1	12.3	13.1	13.8	14.6
95°	35.8	35.0	34.1	33.2	32.4	31.6	30.8	30.1	30.8	31.6	32.4
97.5°	57.6	56.9	56.3	55.6	55.1	54.5	53.9	53.3	53.9	54.5	55.1
100°	73.7	73.0	72.5	71.9	71.2	70.5	69.8	69.2	69.8	70.5	71.2
102.5°	91.2	90.4	89.7	89.1	88.7	88.3	87.9	87.5	87.9	88.3	88.7
105°	118.0	117.0	115.9	115.4	115.1	114.9	114.7	114.4	114.7	114.9	115.1
107.5°	147.4	147.0	146.6	146.3	146.2	146.1	145.9	145.8	145.9	146.1	146.2
110°	166.9	166.7	166.4	166.2	165.9	165.8	165.5	165.3	165.5	165.8	165.9



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	186.4	186.4	186.3	186.2	186.0	185.9	185.7	185.7	185.7	185.9	186.0
115°	217.1	217.3	217.6	217.5	217.2	216.9	216.5	216.2	216.5	216.9	217.2
117.5°	247.2	247.4	247.7	247.8	247.5	247.4	247.1	246.9	247.1	247.4	247.5
120°	267.7	268.2	268.8	268.8	268.0	267.3	266.7	266.0	266.7	267.3	268.0
122.5°	287.5	287.8	288.0	287.9	287.4	287.0	286.4	286.0	286.4	287.0	287.4
125°	317.4	317.5	317.8	317.7	317.4	317.0	316.7	316.4	316.7	317.0	317.4
127.5°	347.1	347.3	347.6	347.3	346.6	345.9	345.2	344.5	345.2	345.9	346.6
130°	366.4	366.8	367.0	366.8	365.9	365.0	364.1	363.2	364.1	365.0	365.9
132.5°	385.3	385.6	385.8	385.5	384.6	383.7	382.8	381.8	382.8	383.7	384.6
135°	413.2	413.3	413.5	413.1	412.5	411.8	411.2	410.5	411.2	411.8	412.5
137.5°	440.1	439.9	439.6	439.2	438.6	438.0	437.5	436.9	437.5	438.0	438.6
140°	458.1	457.9	457.8	457.4	456.9	456.4	455.8	455.2	455.8	456.4	456.9
142.5°	474.9	474.7	474.6	474.1	473.6	473.1	472.4	471.9	472.4	473.1	473.6
145°	499.8	499.4	499.1	498.8	498.6	498.4	498.2	497.9	498.2	498.4	498.6
147.5°	523.3	523.1	522.7	522.4	521.9	521.6	521.1	520.8	521.1	521.6	521.9
150°	538.1	538.0	537.7	537.5	537.3	537.1	536.8	536.6	536.8	537.1	537.3
152.5°	551.3	551.3	551.1	550.9	550.5	550.3	549.9	549.7	549.9	550.3	550.5
155°	570.4	570.3	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
157.5°	587.3	587.2	587.1	587.1	587.3	587.4	587.5	587.6	587.5	587.4	587.3
160°	597.6	597.6	597.6	597.7	598.0	598.2	598.4	598.6	598.4	598.2	598.0
162.5°	607.3	607.2	607.1	607.2	607.4	607.8	608.1	608.4	608.1	607.8	607.4
165°	619.5	619.5	619.5	619.6	620.0	620.4	620.7	621.0	620.7	620.4	620.0
167.5°	629.3	629.2	629.1	629.3	629.7	630.2	630.6	631.1	630.6	630.2	629.7
170°	634.7	634.7	634.7	635.0	635.4	635.9	636.3	636.8	636.3	635.9	635.4
172.5°	639.3	639.3	639.3	639.4	639.9	640.3	640.8	641.2	640.8	640.3	639.9
175°	643.9	643.9	643.9	644.2	644.6	645.1	645.5	646.0	645.5	645.1	644.6
177.5°	646.2	646.2	646.2	646.4	646.8	647.2	647.6	647.9	647.6	647.2	646.8
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	421.6	420.4	418.8	416.3	414.3	411.2	411.2	411.6	411.6	411.5	411.2
5°	408.8	405.7	402.0	397.6	393.1	388.4	387.6	385.9	384.8	383.9	382.9
7.5°	395.3	389.8	384.3	378.3	372.6	368.1	364.9	362.2	360.5	358.6	357.3
10°	386.2	379.3	372.9	366.5	359.4	353.7	350.3	347.8	345.9	344.2	343.4
12.5°	375.4	367.6	360.4	354.3	346.6	340.8	337.4	336.3	334.1	330.6	328.8
15°	359.6	352.3	343.8	334.5	330.7	323.7	319.7	317.8	316.6	313.9	313.1
17.5°	346.1	336.6	327.0	320.0	313.1	307.4	305.1	302.8	301.2	299.0	298.3
20°	335.3	326.8	318.1	310.6	303.3	297.0	295.2	293.6	291.9	290.9	290.0
22.5°	324.3	315.8	308.5	301.6	293.8	289.7	287.8	285.9	284.7	284.0	283.2
25°	308.9	301.4	293.3	287.1	280.9	278.1	276.9	275.9	275.0	274.0	273.8
27.5°	295.2	287.0	280.4	274.6	270.1	267.9	266.6	266.2	266.4	266.7	267.0
30°	284.8	277.3	272.0	267.0	262.8	260.7	260.5	260.5	261.4	261.5	262.0
32.5°	275.4	269.2	263.8	259.0	255.8	254.4	255.2	255.2	255.8	256.4	257.2
35°	261.5	256.1	252.0	247.8	245.1	245.8	246.2	246.6	247.6	248.9	249.7
37.5°	248.3	243.7	239.3	236.1	234.9	235.9	237.0	237.8	239.1	240.0	240.9
40°	238.9	235.3	231.2	228.3	228.7	229.3	230.2	231.2	232.3	232.9	233.7
42.5°	230.1	226.4	223.2	220.8	221.4	222.2	222.7	223.2	224.4	225.6	226.0
45°	216.7	213.7	210.9	209.4	209.8	210.3	210.6	211.2	212.3	213.1	213.4
47.5°	201.6	199.6	197.6	196.2	196.9	196.7	197.2	198.6	198.9	199.4	200.5
50°	192.0	190.1	187.8	187.3	187.3	187.3	187.6	189.2	189.2	190.1	190.9
52.5°	181.3	180.1	178.7	177.9	177.5	177.5	178.4	179.2	179.6	180.7	181.6
55°	165.6	164.3	163.1	162.5	162.0	162.5	164.1	164.5	165.6	166.2	166.8
57.5°	149.2	148.2	147.2	146.9	146.8	147.3	148.2	149.5	149.7	151.7	152.6
60°	138.4	136.9	136.1	136.1	135.6	137.5	137.1	139.2	139.6	140.9	142.3
62.5°	127.2	125.3	124.9	124.9	125.6	126.1	126.6	127.5	128.7	130.2	131.3
65°	109.2	108.3	109.7	109.5	109.1	110.3	110.3	111.4	112.6	114.0	116.4
67.5°	92.3	91.8	91.8	91.8	92.5	93.2	93.8	94.7	96.2	97.7	99.2
70°	80.8	81.4	80.4	81.2	81.9	82.0	82.5	83.7	85.3	86.4	88.1
72.5°	69.6	69.6	69.7	70.1	70.7	71.1	71.5	72.9	74.7	75.6	77.0
75°	53.6	53.4	54.0	54.0	55.0	55.5	55.9	56.5	58.1	59.4	60.5
77.5°	39.1	39.4	39.2	39.9	39.7	39.8	41.0	41.6	41.8	44.3	44.9
80°	29.5	29.9	30.1	30.3	30.5	30.1	31.6	32.2	32.2	33.6	34.7
82.5°	21.2	21.4	21.9	22.2	22.2	22.6	22.7	23.2	23.7	24.3	25.7
85°	10.6	11.2	11.4	11.2	11.4	11.0	11.6	11.9	12.0	12.0	12.0
87.5°	4.4	4.7	4.9	5.4	5.4	6.0	6.1	5.8	5.9	6.4	5.9
90°	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1	13.6	14.0	14.4
92.5°	15.4	16.2	17.0	17.8	18.7	19.5	19.9	20.2	20.6	21.0	21.1
95°	33.2	34.1	35.0	35.8	36.7	37.6	38.1	38.5	39.0	39.4	39.7
97.5°	55.6	56.3	56.9	57.6	58.2	58.9	59.4	59.9	60.5	61.0	61.2
100°	71.9	72.5	73.0	73.7	74.2	74.7	75.1	75.4	75.8	76.2	76.4
102.5°	89.1	89.7	90.4	91.2	91.9	92.6	93.0	93.4	93.7	94.0	94.2
105°	115.4	115.9	117.0	118.0	119.0	120.0	120.0	120.0	120.0	120.0	120.1
107.5°	146.3	146.6	147.0	147.4	147.8	148.2	148.6	148.9	149.3	149.6	149.8
110°	166.2	166.4	166.7	166.9	167.1	167.4	167.8	168.3	168.7	169.2	169.2



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	186.2	186.3	186.4	186.4	186.5	186.5	187.0	187.5	188.1	188.6	188.9
115°	217.5	217.6	217.3	217.1	216.9	216.7	216.8	216.9	217.0	217.1	217.1
117.5°	247.8	247.7	247.4	247.2	246.9	246.6	246.6	246.6	246.5	246.5	246.3
120°	268.8	268.8	268.2	267.7	267.1	266.5	266.4	266.3	266.2	266.1	265.9
122.5°	287.9	288.0	287.8	287.5	287.1	286.9	286.6	286.2	286.0	285.7	285.3
125°	317.7	317.8	317.5	317.4	317.1	316.9	316.4	315.9	315.5	315.0	314.6
127.5°	347.3	347.6	347.3	347.1	346.8	346.6	346.0	345.3	344.6	344.0	343.5
130°	366.8	367.0	366.8	366.4	366.0	365.7	365.2	364.8	364.4	363.9	363.3
132.5°	385.5	385.8	385.6	385.3	385.0	384.9	384.2	383.7	383.2	382.6	382.1
135°	413.1	413.5	413.3	413.2	413.1	413.0	412.6	412.1	411.6	411.2	410.8
137.5°	439.2	439.6	439.9	440.1	440.5	440.8	440.3	439.8	439.3	438.9	438.5
140°	457.4	457.8	457.9	458.1	458.2	458.3	458.2	458.1	457.9	457.8	457.4
142.5°	474.1	474.6	474.7	474.9	475.2	475.4	475.3	475.1	475.0	474.9	474.6
145°	498.8	499.1	499.4	499.8	500.2	500.5	500.3	500.2	500.2	500.1	499.7
147.5°	522.4	522.7	523.1	523.3	523.7	524.0	524.0	524.0	524.0	524.0	523.6
150°	537.5	537.7	538.0	538.1	538.4	538.6	538.6	538.6	538.6	538.6	538.3
152.5°	550.9	551.1	551.3	551.3	551.5	551.6	551.8	552.1	552.2	552.4	552.1
155°	570.2	570.2	570.3	570.4	570.6	570.7	571.1	571.6	572.0	572.5	572.3
157.5°	587.1	587.1	587.2	587.3	587.4	587.5	587.9	588.4	588.9	589.3	589.2
160°	597.7	597.6	597.6	597.6	597.6	597.6	598.2	598.8	599.3	599.9	599.9
162.5°	607.2	607.1	607.2	607.3	607.3	607.4	608.0	608.5	609.1	609.7	609.6
165°	619.6	619.5	619.5	619.5	619.5	619.5	620.2	620.9	621.5	622.2	622.1
167.5°	629.3	629.1	629.2	629.3	629.4	629.5	630.2	630.9	631.6	632.3	632.3
170°	635.0	634.7	634.7	634.7	634.7	634.7	635.5	636.3	637.1	637.9	637.9
172.5°	639.4	639.3	639.3	639.3	639.3	639.3	640.0	640.6	641.3	642.0	642.0
175°	644.2	643.9	643.9	643.9	643.9	643.9	644.6	645.2	646.0	646.7	646.6
177.5°	646.4	646.2	646.2	646.2	646.2	646.2	646.8	647.4	647.9	648.5	648.4
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	410.0	409.8	411.0	410.2	411.0	409.8	410.0	411.2	411.5	411.6	411.6
5°	381.7	382.3	380.1	380.1	380.1	382.3	381.7	382.9	383.9	384.8	385.9
7.5°	356.3	355.4	355.5	354.4	355.5	355.4	356.3	357.3	358.6	360.5	362.2
10°	340.9	339.7	339.2	339.5	339.2	339.7	340.9	343.4	344.2	345.9	347.8
12.5°	328.1	327.9	325.1	325.1	325.1	327.9	328.1	328.8	330.6	334.1	336.3
15°	313.1	309.2	308.7	310.0	308.7	309.2	313.1	313.1	313.9	316.6	317.8
17.5°	298.0	295.9	296.0	295.4	296.0	295.9	298.0	298.3	299.0	301.2	302.8
20°	290.0	288.7	288.6	287.1	288.6	288.7	290.0	290.0	290.9	291.9	293.6
22.5°	282.7	282.3	282.4	280.8	282.4	282.3	282.7	283.2	284.0	284.7	285.9
25°	273.6	274.6	273.8	273.8	273.8	274.6	273.6	273.8	274.0	275.0	275.9
27.5°	267.4	267.4	267.0	267.0	267.0	267.4	267.4	267.0	266.7	266.4	266.2
30°	262.8	262.6	263.0	263.0	263.0	262.6	262.8	262.0	261.5	261.4	260.5
32.5°	258.2	258.4	258.5	258.7	258.5	258.4	258.2	257.2	256.4	255.8	255.2
35°	250.9	251.2	251.8	251.4	251.8	251.2	250.9	249.7	248.9	247.6	246.6
37.5°	241.2	242.2	242.0	242.3	242.0	242.2	241.2	240.9	240.0	239.1	237.8
40°	233.9	234.5	234.3	234.3	234.3	234.5	233.9	233.7	232.9	232.3	231.2
42.5°	226.4	226.9	226.3	226.0	226.3	226.9	226.4	226.0	225.6	224.4	223.2
45°	214.2	213.7	214.4	213.6	214.4	213.7	214.2	213.4	213.1	212.3	211.2
47.5°	200.5	200.9	201.1	201.7	201.1	200.9	200.5	200.5	199.4	198.9	198.6
50°	191.4	192.6	192.6	192.3	192.6	192.6	191.4	190.9	190.1	189.2	189.2
52.5°	182.4	182.9	183.8	183.7	183.8	182.9	182.4	181.6	180.7	179.6	179.2
55°	168.4	168.9	169.3	169.5	169.3	168.9	168.4	166.8	166.2	165.6	164.5
57.5°	154.1	153.9	154.9	155.2	154.9	153.9	154.1	152.6	151.7	149.7	149.5
60°	143.9	143.9	145.6	146.2	145.6	143.9	143.9	142.3	140.9	139.6	139.2
62.5°	133.1	133.8	135.5	134.6	135.5	133.8	133.1	131.3	130.2	128.7	127.5
65°	117.3	119.0	118.9	119.7	118.9	119.0	117.3	116.4	114.0	112.6	111.4
67.5°	100.9	101.9	103.4	103.5	103.4	101.9	100.9	99.2	97.7	96.2	94.7
70°	89.7	90.8	91.6	92.2	91.6	90.8	89.7	88.1	86.4	85.3	83.7
72.5°	78.9	79.5	81.5	80.6	81.5	79.5	78.9	77.0	75.6	74.7	72.9
75°	61.9	63.4	64.6	64.0	64.6	63.4	61.9	60.5	59.4	58.1	56.5
77.5°	45.7	47.3	47.8	47.3	47.8	47.3	45.7	44.9	44.3	41.8	41.6
80°	36.1	35.9	37.2	37.0	37.2	35.9	36.1	34.7	33.6	32.2	32.2
82.5°	26.5	26.3	26.8	27.0	26.8	26.3	26.5	25.7	24.3	23.7	23.2
85°	12.8	13.5	12.7	12.5	12.7	13.5	12.8	12.0	12.0	12.0	11.9
87.5°	5.9	6.0	5.8	5.7	5.8	6.0	5.9	5.9	6.4	5.9	5.8
90°	14.6	14.8	15.1	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1
92.5°	21.0	20.8	20.7	20.5	20.7	20.8	21.0	21.1	21.0	20.6	20.2
95°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.4	39.0	38.5
97.5°	61.2	61.1	61.1	61.0	61.1	61.1	61.2	61.2	61.0	60.5	59.9
100°	76.6	76.9	77.0	77.3	77.0	76.9	76.6	76.4	76.2	75.8	75.4
102.5°	94.2	94.1	94.1	94.0	94.1	94.1	94.2	94.2	94.0	93.7	93.4
105°	120.4	120.6	120.8	121.1	120.8	120.6	120.4	120.1	120.0	120.0	120.0
107.5°	149.6	149.5	149.4	149.3	149.4	149.5	149.6	149.8	149.6	149.3	148.9
110°	169.1	168.8	168.6	168.4	168.6	168.8	169.1	169.2	169.2	168.7	168.3



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	188.9	188.8	188.8	188.7	188.8	188.8	188.9	188.9	188.6	188.1	187.5
115°	217.0	216.9	216.8	216.7	216.8	216.9	217.0	217.1	217.1	217.0	216.9
117.5°	246.0	245.7	245.4	245.0	245.4	245.7	246.0	246.3	246.5	246.5	246.6
120°	265.6	265.5	265.2	265.0	265.2	265.5	265.6	265.9	266.1	266.2	266.3
122.5°	285.1	284.7	284.5	284.1	284.5	284.7	285.1	285.3	285.7	286.0	286.2
125°	314.1	313.7	313.3	312.8	313.3	313.7	314.1	314.6	315.0	315.5	315.9
127.5°	343.0	342.4	341.9	341.3	341.9	342.4	343.0	343.5	344.0	344.6	345.3
130°	362.5	361.7	360.9	360.1	360.9	361.7	362.5	363.3	363.9	364.4	364.8
132.5°	381.5	380.8	380.2	379.6	380.2	380.8	381.5	382.1	382.6	383.2	383.7
135°	410.6	410.4	410.2	409.9	410.2	410.4	410.6	410.8	411.2	411.6	412.1
137.5°	438.0	437.6	437.1	436.7	437.1	437.6	438.0	438.5	438.9	439.3	439.8
140°	456.6	455.8	455.0	454.2	455.0	455.8	456.6	457.4	457.8	457.9	458.1
142.5°	473.9	473.3	472.7	472.1	472.7	473.3	473.9	474.6	474.9	475.0	475.1
145°	499.3	498.8	498.4	497.9	498.4	498.8	499.3	499.7	500.1	500.2	500.2
147.5°	523.0	522.3	521.7	520.9	521.7	522.3	523.0	523.6	524.0	524.0	524.0
150°	537.6	536.9	536.3	535.6	536.3	536.9	537.6	538.3	538.6	538.6	538.6
152.5°	551.6	551.0	550.5	549.8	550.5	551.0	551.6	552.1	552.4	552.2	552.1
155°	571.5	570.7	570.0	569.2	570.0	570.7	571.5	572.3	572.5	572.0	571.6
157.5°	588.6	588.0	587.4	586.7	587.4	588.0	588.6	589.2	589.3	588.9	588.4
160°	599.5	599.1	598.6	598.2	598.6	599.1	599.5	599.9	599.9	599.3	598.8
162.5°	608.9	608.1	607.4	606.7	607.4	608.1	608.9	609.6	609.7	609.1	608.5
165°	621.3	620.5	619.8	619.0	619.8	620.5	621.3	622.1	622.2	621.5	620.9
167.5°	631.6	630.9	630.2	629.5	630.2	630.9	631.6	632.3	632.3	631.6	630.9
170°	637.1	636.3	635.5	634.7	635.5	636.3	637.1	637.9	637.9	637.1	636.3
172.5°	641.2	640.4	639.6	638.8	639.6	640.4	641.2	642.0	642.0	641.3	640.6
175°	645.8	645.0	644.2	643.4	644.2	645.0	645.8	646.6	646.7	646.0	645.2
177.5°	647.7	647.1	646.5	645.9	646.5	647.1	647.7	648.4	648.5	647.9	647.4
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	411.2	411.2	414.3	416.3	418.8	420.4	421.6	422.8	424.8	427.4	430.4
5°	387.6	388.4	393.1	397.6	402.0	405.7	408.8	412.6	417.1	422.8	429.0
7.5°	364.9	368.1	372.6	378.3	384.3	389.8	395.3	401.4	408.0	416.2	424.9
10°	350.3	353.7	359.4	366.5	372.9	379.3	386.2	392.8	400.9	410.7	422.0
12.5°	337.4	340.8	346.6	354.3	360.4	367.6	375.4	384.1	393.2	404.8	417.6
15°	319.7	323.7	330.7	334.5	343.8	352.3	359.6	372.0	383.7	395.7	410.5
17.5°	305.1	307.4	313.1	320.0	327.0	336.6	346.1	356.5	368.1	382.8	401.3
20°	295.2	297.0	303.3	310.6	318.1	326.8	335.3	345.7	358.7	374.3	394.3
22.5°	287.8	289.7	293.8	301.6	308.5	315.8	324.3	336.7	350.6	365.9	387.4
25°	276.9	278.1	280.9	287.1	293.3	301.4	308.9	320.6	334.8	352.8	374.3
27.5°	266.6	267.9	270.1	274.6	280.4	287.0	295.2	305.0	319.5	338.9	361.9
30°	260.5	260.7	262.8	267.0	272.0	277.3	284.8	296.0	309.8	329.5	353.6
32.5°	255.2	254.4	255.8	259.0	263.8	269.2	275.4	286.4	299.6	319.0	343.8
35°	246.2	245.8	245.1	247.8	252.0	256.1	261.5	269.8	284.8	302.9	328.9
37.5°	237.0	235.9	234.9	236.1	239.3	243.7	248.3	255.7	268.7	288.6	313.4
40°	230.2	229.3	228.7	228.3	231.2	235.3	238.9	245.9	258.0	276.9	301.4
42.5°	222.7	222.2	221.4	220.8	223.2	226.4	230.1	236.3	248.3	266.1	289.3
45°	210.6	210.3	209.8	209.4	210.9	213.7	216.7	221.2	231.7	248.9	269.8
47.5°	197.2	196.7	196.9	196.2	197.6	199.6	201.6	206.5	216.4	230.4	245.8
50°	187.6	187.3	187.3	187.3	187.8	190.1	192.0	195.7	204.8	218.7	229.8
52.5°	178.4	177.5	177.5	177.9	178.7	180.1	181.3	185.4	193.3	204.8	214.8
55°	164.1	162.5	162.0	162.5	163.1	164.3	165.6	168.9	175.8	184.2	190.1
57.5°	148.2	147.3	146.8	146.9	147.2	148.2	149.2	152.8	158.2	162.6	166.4
60°	137.1	137.5	135.6	136.1	136.1	136.9	138.4	140.6	145.2	148.3	152.0
62.5°	126.6	126.1	125.6	124.9	124.9	125.3	127.2	129.0	133.0	134.6	137.4
65°	110.3	110.3	109.1	109.5	109.7	108.3	109.2	111.4	113.9	114.5	117.2
67.5°	93.8	93.2	92.5	91.8	91.8	91.8	92.3	93.3	95.1	95.4	97.5
70°	82.5	82.0	81.9	81.2	80.4	81.4	80.8	81.9	82.9	83.1	84.4
72.5°	71.5	71.1	70.7	70.1	69.7	69.6	69.6	70.9	71.6	71.3	72.7
75°	55.9	55.5	55.0	54.0	54.0	53.4	53.6	54.4	55.3	54.7	55.9
77.5°	41.0	39.8	39.7	39.9	39.2	39.4	39.1	39.1	39.4	39.4	40.6
80°	31.6	30.1	30.5	30.3	30.1	29.9	29.5	29.7	29.9	30.1	30.8
82.5°	22.7	22.6	22.2	22.2	21.9	21.4	21.2	21.6	21.8	21.7	22.1
85°	11.6	11.0	11.4	11.2	11.4	11.2	10.6	10.6	11.0	10.8	11.2
87.5°	6.1	6.0	5.4	5.4	4.9	4.7	4.4	4.3	4.2	4.0	4.1
90°	12.7	12.2	10.7	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5
92.5°	19.9	19.5	18.7	17.8	17.0	16.2	15.4	14.6	13.8	13.1	12.3
95°	38.1	37.6	36.7	35.8	35.0	34.1	33.2	32.4	31.6	30.8	30.1
97.5°	59.4	58.9	58.2	57.6	56.9	56.3	55.6	55.1	54.5	53.9	53.3
100°	75.1	74.7	74.2	73.7	73.0	72.5	71.9	71.2	70.5	69.8	69.2
102.5°	93.0	92.6	91.9	91.2	90.4	89.7	89.1	88.7	88.3	87.9	87.5
105°	120.0	120.0	119.0	118.0	117.0	115.9	115.4	115.1	114.9	114.7	114.4
107.5°	148.6	148.2	147.8	147.4	147.0	146.6	146.3	146.2	146.1	145.9	145.8
110°	167.8	167.4	167.1	166.9	166.7	166.4	166.2	165.9	165.8	165.5	165.3



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	187.0	186.5	186.5	186.4	186.4	186.3	186.2	186.0	185.9	185.7	185.7
115°	216.8	216.7	216.9	217.1	217.3	217.6	217.5	217.2	216.9	216.5	216.2
117.5°	246.6	246.6	246.9	247.2	247.4	247.7	247.8	247.5	247.4	247.1	246.9
120°	266.4	266.5	267.1	267.7	268.2	268.8	268.8	268.0	267.3	266.7	266.0
122.5°	286.6	286.9	287.1	287.5	287.8	288.0	287.9	287.4	287.0	286.4	286.0
125°	316.4	316.9	317.1	317.4	317.5	317.8	317.7	317.4	317.0	316.7	316.4
127.5°	346.0	346.6	346.8	347.1	347.3	347.6	347.3	346.6	345.9	345.2	344.5
130°	365.2	365.7	366.0	366.4	366.8	367.0	366.8	365.9	365.0	364.1	363.2
132.5°	384.2	384.9	385.0	385.3	385.6	385.8	385.5	384.6	383.7	382.8	381.8
135°	412.6	413.0	413.1	413.2	413.3	413.5	413.1	412.5	411.8	411.2	410.5
137.5°	440.3	440.8	440.5	440.1	439.9	439.6	439.2	438.6	438.0	437.5	436.9
140°	458.2	458.3	458.2	458.1	457.9	457.8	457.4	456.9	456.4	455.8	455.2
142.5°	475.3	475.4	475.2	474.9	474.7	474.6	474.1	473.6	473.1	472.4	471.9
145°	500.3	500.5	500.2	499.8	499.4	499.1	498.8	498.6	498.4	498.2	497.9
147.5°	524.0	524.0	523.7	523.3	523.1	522.7	522.4	521.9	521.6	521.1	520.8
150°	538.6	538.6	538.4	538.1	538.0	537.7	537.5	537.3	537.1	536.8	536.6
152.5°	551.8	551.6	551.5	551.3	551.3	551.1	550.9	550.5	550.3	549.9	549.7
155°	571.1	570.7	570.6	570.4	570.3	570.2	570.2	570.2	570.2	570.2	570.2
157.5°	587.9	587.5	587.4	587.3	587.2	587.1	587.1	587.3	587.4	587.5	587.6
160°	598.2	597.6	597.6	597.6	597.6	597.6	597.7	598.0	598.2	598.4	598.6
162.5°	608.0	607.4	607.3	607.3	607.2	607.1	607.2	607.4	607.8	608.1	608.4
165°	620.2	619.5	619.5	619.5	619.5	619.5	619.6	620.0	620.4	620.7	621.0
167.5°	630.2	629.5	629.4	629.3	629.2	629.1	629.3	629.7	630.2	630.6	631.1
170°	635.5	634.7	634.7	634.7	634.7	634.7	635.0	635.4	635.9	636.3	636.8
172.5°	640.0	639.3	639.3	639.3	639.3	639.3	639.4	639.9	640.3	640.8	641.2
175°	644.6	643.9	643.9	643.9	643.9	643.9	644.2	644.6	645.1	645.5	646.0
177.5°	646.8	646.2	646.2	646.2	646.2	646.2	646.4	646.8	647.2	647.6	647.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	431.4	432.3	435.1	437.1	439.4	440.8	442.0	443.1	444.4	444.7	449.5
5°	433.4	437.5	444.8	450.1	456.8	464.0	469.0	471.4	477.4	482.3	492.3
7.5°	432.8	441.7	452.6	464.0	476.2	487.5	497.3	509.0	517.2	529.7	541.9
10°	432.3	444.2	458.3	472.8	489.8	505.6	519.8	535.6	548.7	565.9	580.6
12.5°	430.8	445.1	464.8	482.0	502.7	524.4	545.4	565.6	577.2	605.9	619.5
15°	427.1	444.2	468.7	494.8	523.3	549.0	575.6	596.8	631.1	656.2	672.3
17.5°	420.1	443.9	473.0	504.5	539.1	573.1	603.2	635.3	671.7	702.1	734.6
20°	416.7	442.9	475.3	510.2	546.2	584.6	618.8	657.5	697.1	727.1	768.7
22.5°	410.5	440.2	475.1	514.0	552.4	592.2	632.3	671.3	717.1	758.3	797.9
25°	400.6	433.7	469.9	513.4	558.4	598.2	646.3	698.0	745.7	798.8	838.2
27.5°	389.9	425.4	461.6	502.0	550.5	597.9	658.3	716.7	775.1	820.8	850.1
30°	381.8	416.3	453.7	494.5	542.4	598.7	666.2	730.0	786.9	826.2	842.6
32.5°	373.0	408.0	441.0	483.8	534.9	598.2	671.2	737.8	787.6	813.7	810.5
35°	359.2	388.4	420.7	461.8	522.0	594.5	674.1	738.5	769.0	763.4	721.0
37.5°	339.2	363.9	395.6	440.6	507.1	586.8	668.2	716.6	714.6	669.0	607.5
40°	326.8	347.8	378.3	425.6	495.4	581.8	659.2	690.5	664.0	600.1	526.6
42.5°	310.5	329.8	360.3	409.0	482.7	571.8	641.7	650.8	598.8	525.4	458.0
45°	285.3	302.3	333.9	384.1	463.4	549.7	599.1	576.8	506.8	431.1	379.8
47.5°	258.1	275.8	306.1	357.8	435.7	516.5	540.0	492.8	420.9	359.4	312.3
50°	240.9	258.0	287.8	339.8	417.0	489.2	499.0	437.9	371.8	317.8	279.2
52.5°	223.7	239.7	268.9	321.3	395.0	457.6	451.7	389.4	328.7	282.6	252.3
55°	198.0	213.1	240.9	290.0	357.1	406.7	385.0	325.6	275.3	239.5	216.4
57.5°	175.0	189.5	213.5	257.8	316.1	350.3	322.5	272.4	232.5	204.9	187.8
60°	159.3	172.2	195.1	236.2	286.9	312.8	285.4	241.2	207.5	185.5	170.1
62.5°	144.5	155.8	176.9	214.3	258.3	280.1	252.4	214.9	186.3	166.7	153.6
65°	122.2	132.3	151.1	180.1	216.2	230.8	206.9	176.6	154.4	139.8	131.1
67.5°	101.7	110.4	126.5	149.4	176.0	186.5	168.4	144.9	128.1	116.5	109.6
70°	88.1	95.6	108.3	128.0	152.0	160.2	143.1	123.8	111.6	102.2	95.8
72.5°	76.6	82.1	93.6	108.9	128.9	135.4	123.5	106.6	95.1	88.1	82.9
75°	58.4	63.0	70.4	82.7	96.6	100.3	91.4	80.8	73.1	68.1	64.2
77.5°	42.1	45.5	50.8	58.4	68.0	71.4	65.8	58.7	53.1	49.8	47.5
80°	31.7	34.5	39.1	45.3	51.1	53.0	49.7	44.2	40.3	38.4	36.6
82.5°	23.5	25.0	27.7	32.0	35.9	38.2	35.4	32.1	30.0	28.3	27.6
85°	11.9	12.7	13.9	15.6	18.1	18.9	17.8	17.0	15.8	14.7	14.7
87.5°	4.6	4.9	5.6	6.2	7.0	7.8	8.0	7.9	8.1	8.0	7.9
90°	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1
92.5°	13.1	13.8	14.6	15.4	16.2	17.0	17.8	18.7	19.5	19.9	20.2
95°	30.8	31.6	32.4	33.2	34.1	35.0	35.8	36.7	37.6	38.1	38.5
97.5°	53.9	54.5	55.1	55.6	56.3	56.9	57.6	58.2	58.9	59.4	59.9
100°	69.8	70.5	71.2	71.9	72.5	73.0	73.7	74.2	74.7	75.1	75.4
102.5°	87.9	88.3	88.7	89.1	89.7	90.4	91.2	91.9	92.6	93.0	93.4
105°	114.7	114.9	115.1	115.4	115.9	117.0	118.0	119.0	120.0	120.0	120.0
107.5°	145.9	146.1	146.2	146.3	146.6	147.0	147.4	147.8	148.2	148.6	148.9
110°	165.5	165.8	165.9	166.2	166.4	166.7	166.9	167.1	167.4	167.8	168.3



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	185.7	185.9	186.0	186.2	186.3	186.4	186.4	186.5	186.5	187.0	187.5
115°	216.5	216.9	217.2	217.5	217.6	217.3	217.1	216.9	216.7	216.8	216.9
117.5°	247.1	247.4	247.5	247.8	247.7	247.4	247.2	246.9	246.6	246.6	246.6
120°	266.7	267.3	268.0	268.8	268.8	268.2	267.7	267.1	266.5	266.4	266.3
122.5°	286.4	287.0	287.4	287.9	288.0	287.8	287.5	287.1	286.9	286.6	286.2
125°	316.7	317.0	317.4	317.7	317.8	317.5	317.4	317.1	316.9	316.4	315.9
127.5°	345.2	345.9	346.6	347.3	347.6	347.3	347.1	346.8	346.6	346.0	345.3
130°	364.1	365.0	365.9	366.8	367.0	366.8	366.4	366.0	365.7	365.2	364.8
132.5°	382.8	383.7	384.6	385.5	385.8	385.6	385.3	385.0	384.9	384.2	383.7
135°	411.2	411.8	412.5	413.1	413.5	413.3	413.2	413.1	413.0	412.6	412.1
137.5°	437.5	438.0	438.6	439.2	439.6	439.9	440.1	440.5	440.8	440.3	439.8
140°	455.8	456.4	456.9	457.4	457.8	457.9	458.1	458.2	458.3	458.2	458.1
142.5°	472.4	473.1	473.6	474.1	474.6	474.7	474.9	475.2	475.4	475.3	475.1
145°	498.2	498.4	498.6	498.8	499.1	499.4	499.8	500.2	500.5	500.3	500.2
147.5°	521.1	521.6	521.9	522.4	522.7	523.1	523.3	523.7	524.0	524.0	524.0
150°	536.8	537.1	537.3	537.5	537.7	538.0	538.1	538.4	538.6	538.6	538.6
152.5°	549.9	550.3	550.5	550.9	551.1	551.3	551.3	551.5	551.6	551.8	552.1
155°	570.2	570.2	570.2	570.2	570.2	570.3	570.4	570.6	570.7	571.1	571.6
157.5°	587.5	587.4	587.3	587.1	587.1	587.2	587.3	587.4	587.5	587.9	588.4
160°	598.4	598.2	598.0	597.7	597.6	597.6	597.6	597.6	597.6	598.2	598.8
162.5°	608.1	607.8	607.4	607.2	607.1	607.2	607.3	607.3	607.4	608.0	608.5
165°	620.7	620.4	620.0	619.6	619.5	619.5	619.5	619.5	619.5	620.2	620.9
167.5°	630.6	630.2	629.7	629.3	629.1	629.2	629.3	629.4	629.5	630.2	630.9
170°	636.3	635.9	635.4	635.0	634.7	634.7	634.7	634.7	634.7	635.5	636.3
172.5°	640.8	640.3	639.9	639.4	639.3	639.3	639.3	639.3	639.3	640.0	640.6
175°	645.5	645.1	644.6	644.2	643.9	643.9	643.9	643.9	643.9	644.6	645.2
177.5°	647.6	647.2	646.8	646.4	646.2	646.2	646.2	646.2	646.2	646.8	647.4
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	451.2	451.4	453.2	454.5	453.9	454.7	455.0
5°	492.9	500.4	504.4	507.3	507.5	507.7	509.3
7.5°	552.1	560.2	566.1	575.0	577.6	580.6	579.8
10°	595.4	607.3	617.4	622.8	628.7	637.1	630.3
12.5°	635.8	656.7	672.3	680.6	686.1	687.8	684.5
15°	702.4	729.8	744.5	744.1	762.8	770.9	758.2
17.5°	763.4	788.7	809.0	819.4	835.0	838.4	836.9
20°	800.8	828.5	844.3	862.1	870.2	877.4	878.7
22.5°	833.0	857.9	874.9	889.7	896.4	899.9	902.0
25°	866.3	885.8	896.0	901.2	903.0	902.6	899.9
27.5°	864.0	865.5	854.3	843.3	833.4	822.3	818.5
30°	841.5	824.1	792.9	775.3	749.3	728.7	737.1
32.5°	782.6	747.8	712.8	674.2	642.3	633.2	624.0
35°	667.9	606.8	571.1	529.5	512.9	496.3	484.8
37.5°	540.3	493.1	450.7	423.6	406.9	396.4	390.7
40°	467.2	424.6	389.7	367.7	355.0	343.2	341.5
42.5°	408.8	369.3	343.0	325.5	313.3	308.3	304.6
45°	334.8	307.3	289.6	277.1	269.0	265.9	261.7
47.5°	283.5	263.9	250.7	242.2	236.0	233.7	233.4
50°	254.7	238.4	228.7	222.0	217.3	216.4	213.1
52.5°	233.1	219.0	211.4	205.6	202.2	199.8	198.9
55°	202.3	193.0	186.1	182.8	180.1	177.8	177.8
57.5°	177.0	169.2	164.7	161.8	161.0	159.4	158.4
60°	161.4	154.8	151.2	148.7	147.0	147.3	145.4
62.5°	146.2	141.8	138.4	136.0	133.9	134.0	134.1
65°	124.4	121.1	118.6	117.8	116.5	115.1	115.5
67.5°	105.5	102.4	100.4	99.0	98.5	97.7	99.0
70°	91.8	89.5	88.1	86.9	86.4	86.6	87.7
72.5°	79.4	77.8	76.8	76.2	75.3	75.3	76.1
75°	62.3	61.1	60.3	59.7	59.4	59.4	59.4
77.5°	45.7	45.5	45.1	44.2	44.2	44.5	44.5
80°	36.1	35.5	35.3	34.9	34.2	33.9	34.9
82.5°	27.0	26.4	26.2	26.1	25.1	25.1	25.9
85°	14.5	13.9	14.1	13.9	13.9	13.7	13.7
87.5°	7.8	7.8	7.7	7.9	7.8	7.7	8.0
90°	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	20.6	21.0	21.1	21.0	20.8	20.7	20.5
95°	39.0	39.4	39.7	39.7	39.7	39.7	39.7
97.5°	60.5	61.0	61.2	61.2	61.1	61.1	61.0
100°	75.8	76.2	76.4	76.6	76.9	77.0	77.3
102.5°	93.7	94.0	94.2	94.2	94.1	94.1	94.0
105°	120.0	120.0	120.1	120.4	120.6	120.8	121.1
107.5°	149.3	149.6	149.8	149.6	149.5	149.4	149.3
110°	168.7	169.2	169.2	169.1	168.8	168.6	168.4



TEST NUMBER: P331875-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	188.1	188.6	188.9	188.9	188.8	188.8	188.7
115°	217.0	217.1	217.1	217.0	216.9	216.8	216.7
117.5°	246.5	246.5	246.3	246.0	245.7	245.4	245.0
120°	266.2	266.1	265.9	265.6	265.5	265.2	265.0
122.5°	286.0	285.7	285.3	285.1	284.7	284.5	284.1
125°	315.5	315.0	314.6	314.1	313.7	313.3	312.8
127.5°	344.6	344.0	343.5	343.0	342.4	341.9	341.3
130°	364.4	363.9	363.3	362.5	361.7	360.9	360.1
132.5°	383.2	382.6	382.1	381.5	380.8	380.2	379.6
135°	411.6	411.2	410.8	410.6	410.4	410.2	409.9
137.5°	439.3	438.9	438.5	438.0	437.6	437.1	436.7
140°	457.9	457.8	457.4	456.6	455.8	455.0	454.2
142.5°	475.0	474.9	474.6	473.9	473.3	472.7	472.1
145°	500.2	500.1	499.7	499.3	498.8	498.4	497.9
147.5°	524.0	524.0	523.6	523.0	522.3	521.7	520.9
150°	538.6	538.6	538.3	537.6	536.9	536.3	535.6
152.5°	552.2	552.4	552.1	551.6	551.0	550.5	549.8
155°	572.0	572.5	572.3	571.5	570.7	570.0	569.2
157.5°	588.9	589.3	589.2	588.6	588.0	587.4	586.7
160°	599.3	599.9	599.9	599.5	599.1	598.6	598.2
162.5°	609.1	609.7	609.6	608.9	608.1	607.4	606.7
165°	621.5	622.2	622.1	621.3	620.5	619.8	619.0
167.5°	631.6	632.3	632.3	631.6	630.9	630.2	629.5
170°	637.1	637.9	637.9	637.1	636.3	635.5	634.7
172.5°	641.3	642.0	642.0	641.2	640.4	639.6	638.8
175°	646.0	646.7	646.6	645.8	645.0	644.2	643.4
177.5°	647.9	648.5	648.4	647.7	647.1	646.5	645.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5

(END OF REPORT)