

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331891-940

Luminaire Tested: **S123DIP-S340D805U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331891-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3851.1 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331891-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331891-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	28	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P331891-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	1.2
10°-20°	128.5	3.3
20°-30°	189.9	4.9
30°-40°	221.8	5.8
40°-50°	223.0	5.8
50°-60°	195.8	5.1
60°-70°	145.9	3.8
70°-80°	83.1	2.2
80°-90°	26.5	0.7
90°-100°	191.7	5.0
100°-110°	542.7	14.1
110°-120°	533.9	13.9
120°-130°	425.8	11.1
130°-140°	335.7	8.7
140°-150°	250.6	6.5
150°-160°	174.7	4.5
160°-170°	102.6	2.7
170°-180°	33.4	0.9
0°-30°	363.9	9.4
0°-40°	585.7	15.2
0°-60°	1004.5	26.1
0°-90°	1260.0	32.7
90°-120°	1268.2	32.9
90°-150°	2280.4	59.2
90°-180°	2591.0	67.3
0°-180°	3851.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	1	8	17	20	20	3
95°	24	77	413	121	81	26
105°	81	120	560	980	887	86
115°	143	178	429	940	1078	141
125°	199	235	400	725	850	176
135°	233	278	395	597	690	180
145°	266	304	390	490	539	166
155°	302	326	377	429	447	139
165°	330	339	361	383	390	93
175°	344	344	346	351	351	33
180°	344	344	344	344	344	



TEST NUMBER: P331891-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.9	9.0	9.0	9.3	9.3	9.5	9.8	10.1	10.4	10.8	10.6
90°	1.4	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8
92.5°	8.6	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9
95°	23.7	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4
97.5°	40.4	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5
100°	51.6	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5
102.5°	63.3	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2
105°	80.9	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6
107.5°	99.5	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2
110°	113.0	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3



TEST NUMBER: P331891-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.2	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6
115°	142.9	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4
117.5°	160.6	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7
120°	172.9	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1
122.5°	183.5	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2
125°	198.7	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7
127.5°	210.3	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3
130°	217.5	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5
132.5°	223.1	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2
135°	232.8	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7
137.5°	242.0	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5
140°	248.2	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5
142.5°	254.9	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0
145°	265.6	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1
147.5°	276.5	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2
150°	283.7	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3
152.5°	291.0	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8
155°	301.8	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1
157.5°	310.5	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6
160°	317.2	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5
162.5°	322.3	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5
165°	329.8	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7
167.5°	335.5	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2
170°	338.9	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2
172.5°	341.1	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3
175°	343.7	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9
177.5°	344.9	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331891-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	10.6	10.7	10.8	11.1	10.9	11.1	11.1	11.1
90°	17.4	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	58.7	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	251.0	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	625.6	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	822.0	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	887.2	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	906.3	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	851.4	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	799.0	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P331891-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	747.1	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	678.3	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	628.6	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	602.4	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	581.8	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	554.2	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	530.3	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	515.2	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	501.2	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	482.4	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	465.3	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	455.2	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	445.8	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	434.4	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	425.0	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	418.3	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	412.1	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	403.0	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	393.2	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	387.6	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	380.9	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	372.3	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	364.7	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	359.7	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	355.3	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	349.3	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	345.5	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)