

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332545-927

Luminaire Tested: **S124DIP-S575D590U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332545-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D590U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3675.5 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56																												
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	52	48																												
2	91	83	77	72	84	78	72	68	67	63	60	57	55	52	49	46	45	40																												
3	83	73	66	60	77	69	62	57	59	55	51	51	47	44	43	41	38	34																												
4	76	65	57	51	70	61	54	49	53	48	43	46	42	38	39	36	33	30																												
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26																												
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23																												
7	60	47	39	34	55	45	37	32	39	33	29	34	29	26	29	26	23	20																												
8	55	43	35	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18																												
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17																												
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	19	17	15																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6006	6006	6006	6006
5°	7074	6022	5315	6022
10°	8470	5996	4786	5996
15°	10021	5935	4395	5935
20°	11159	5874	4046	5874
25°	11339	5782	3805	5782
30°	9648	5695	3730	5695
35°	7418	5552	3730	5552
40°	5782	5385	3800	5385
45°	4820	5134	3863	5134
50°	4243	4828	3995	4828
55°	3887	4460	4155	4460
60°	3643	4130	4350	4130
65°	3391	3761	4510	3761
70°	3099	3397	4612	3397
75°	2770	2991	4557	2991
80°	2320	2450	4412	2450
85°	1714	1769	4224	1769



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	2.0
10°-20°	223.4	6.1
20°-30°	354.3	9.6
30°-40°	394.3	10.7
40°-50°	358.9	9.8
50°-60°	293.3	8.0
60°-70°	209.4	5.7
70°-80°	115.3	3.1
80°-90°	33.2	0.9
90°-100°	38.5	1.0
100°-110°	114.1	3.1
110°-120°	193.7	5.3
120°-130°	255.5	7.0
130°-140°	286.9	7.8
140°-150°	281.9	7.7
150°-160°	237.1	6.5
160°-170°	157.8	4.3
170°-180°	55.2	1.5
0°-30°	650.2	17.7
0°-40°	1044.5	28.4
0°-60°	1696.7	46.2
0°-90°	2054.6	55.9
90°-120°	346.4	9.4
90°-150°	1170.7	31.9
90°-180°	1621.0	44.1
0°-180°	3675.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	744	744	744	744	744	
5°	873	743	656	743	873	89
15°	1199	710	526	710	1199	339
25°	1273	649	427	649	1273	561
35°	753	563	378	563	753	478
45°	422	450	338	450	422	333
55°	276	317	295	317	276	249
65°	178	197	236	197	178	176
75°	89	96	146	96	89	94
85°	18	19	46	19	18	23
90°	14	1	14	1	14	8
95°	36	27	36	27	36	37
105°	110	105	110	105	110	116
115°	195	197	195	197	195	193
125°	285	287	285	287	285	254
135°	370	370	370	370	370	286
145°	450	450	450	450	450	282
155°	515	515	515	515	515	237
165°	559	561	559	561	559	158
175°	581	583	581	583	581	55
180°	584	584	584	584	584	



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	791.9	791.6	789.2	788.7	787.0	784.7	784.3	780.3	772.4	768.7	767.7
5°	872.9	879.1	871.0	869.5	868.5	858.4	853.2	847.0	832.8	824.5	818.0
7.5°	969.6	970.3	966.8	963.9	956.1	947.2	933.9	919.7	902.9	885.3	872.0
10°	1033.2	1035.6	1031.7	1031.0	1015.3	1005.4	985.7	969.1	949.9	928.7	909.3
12.5°	1100.3	1096.8	1094.7	1081.6	1078.6	1060.7	1037.8	1020.6	991.1	966.6	940.8
15°	1199.0	1192.2	1187.9	1169.7	1160.8	1135.8	1111.4	1092.7	1054.2	1017.5	989.7
17.5°	1257.0	1263.7	1253.7	1246.3	1223.1	1205.6	1180.7	1141.3	1111.1	1065.6	1030.5
20°	1298.9	1299.5	1294.0	1286.2	1268.0	1245.9	1218.7	1175.6	1139.5	1094.2	1046.1
22.5°	1310.2	1310.3	1308.0	1300.8	1287.0	1269.0	1241.7	1205.6	1162.0	1112.7	1064.6
25°	1273.0	1271.8	1274.5	1282.5	1277.3	1271.8	1256.0	1229.2	1188.5	1136.4	1084.7
27.5°	1134.6	1143.1	1158.8	1178.5	1197.5	1212.0	1216.1	1210.6	1185.3	1142.5	1088.3
30°	1035.0	1045.5	1057.2	1077.0	1115.2	1137.0	1161.1	1179.2	1169.1	1134.9	1084.3
32.5°	925.5	928.1	945.5	968.0	1003.0	1045.0	1083.2	1120.1	1132.3	1114.4	1072.2
35°	752.7	757.0	775.8	798.0	840.8	892.3	949.7	1000.8	1043.1	1060.0	1038.4
37.5°	614.3	626.6	639.8	663.7	701.5	747.8	807.4	873.5	936.5	978.7	985.8
40°	548.7	556.3	565.9	584.1	616.2	661.8	712.9	788.8	855.6	916.1	935.8
42.5°	496.9	501.4	507.2	523.6	548.1	593.4	640.2	706.9	774.0	846.3	879.3
45°	422.2	426.9	436.7	446.3	464.8	496.2	539.7	594.5	662.0	731.7	792.7
47.5°	368.4	371.4	377.2	387.5	403.1	423.9	459.2	505.0	567.6	635.3	700.3
50°	337.8	340.2	344.9	354.2	366.1	384.7	413.6	456.5	505.5	573.6	637.4
52.5°	313.6	314.7	318.1	324.3	333.9	349.4	373.2	408.6	454.2	514.9	578.5
55°	276.2	277.4	280.5	285.1	293.4	303.3	321.5	348.0	387.8	440.5	495.6
57.5°	245.3	246.2	248.8	250.6	257.5	265.5	279.4	298.3	328.5	373.2	422.5
60°	225.6	225.0	228.1	229.7	234.2	241.1	251.8	270.0	296.2	332.2	377.6
62.5°	206.4	205.5	208.1	210.2	212.8	218.6	227.4	241.6	262.9	295.6	334.7
65°	177.5	176.3	177.8	180.3	182.8	185.8	192.3	204.9	221.9	245.3	275.2
67.5°	148.5	149.9	150.1	151.3	152.7	156.9	161.4	170.3	182.3	201.1	226.3
70°	131.3	131.6	132.8	132.8	133.8	137.4	141.2	146.4	158.1	175.4	196.1
72.5°	114.1	115.3	114.9	115.8	116.5	119.0	121.7	126.7	136.7	149.5	166.9
75°	88.8	89.7	89.7	90.0	90.9	91.8	94.0	97.7	104.8	114.3	126.4
77.5°	64.7	64.9	65.3	66.4	66.4	67.9	69.5	72.4	76.0	82.5	89.8
80°	49.9	50.5	50.2	50.9	50.9	52.1	52.7	56.4	57.9	62.3	68.1
82.5°	36.6	37.2	37.2	38.0	38.5	38.7	39.6	41.1	42.6	46.5	48.9
85°	18.5	19.1	18.5	19.1	20.0	20.4	21.2	21.5	22.8	23.8	25.9
87.5°	8.2	8.9	8.8	9.0	9.4	9.6	9.7	9.3	10.2	10.4	11.2
90°	13.5	13.4	13.2	13.0	12.8	12.4	11.7	11.2	10.5	9.9	9.1
92.5°	20.0	20.0	19.8	19.7	19.6	19.3	19.0	18.6	18.2	17.9	17.3
95°	35.7	35.7	35.7	35.7	35.7	35.6	35.3	34.9	34.6	34.3	33.7
97.5°	55.9	55.9	55.9	55.9	55.9	55.8	55.4	55.1	54.7	54.3	53.5
100°	70.0	70.0	70.0	70.0	70.0	69.9	69.7	69.6	69.3	69.2	68.2
102.5°	86.0	85.9	85.8	85.7	85.6	85.4	85.2	84.8	84.6	84.3	83.5
105°	110.3	110.0	109.6	109.3	109.0	108.8	108.4	108.1	107.8	107.5	107.1
107.5°	134.0	134.0	134.0	134.0	134.0	133.9	133.6	133.3	133.0	132.8	132.7
110°	150.9	150.6	150.3	150.0	149.7	149.6	149.9	150.0	150.3	150.4	150.6



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.3	168.2	168.1	168.1	168.0	168.0	168.0	168.1	168.1	168.2	168.3
115°	195.2	195.3	195.4	195.5	195.6	195.7	195.8	195.9	196.0	196.1	196.3
117.5°	220.9	221.0	221.3	221.4	221.7	221.9	222.3	222.6	222.9	223.3	223.4
120°	240.3	240.2	240.0	239.8	239.6	239.7	240.2	240.7	241.2	241.7	242.0
122.5°	256.7	257.0	257.4	257.7	258.1	258.4	258.8	259.1	259.4	259.8	259.9
125°	284.6	284.9	285.0	285.3	285.4	285.7	285.8	286.1	286.2	286.5	286.5
127.5°	310.6	310.8	310.9	311.1	311.2	311.4	311.6	311.8	312.0	312.2	312.4
130°	327.6	328.0	328.4	328.8	329.2	329.5	329.7	329.9	330.1	330.3	330.3
132.5°	345.6	345.8	345.9	346.1	346.3	346.5	346.7	346.9	347.1	347.3	347.4
135°	370.5	370.8	371.1	371.4	371.7	371.9	372.2	372.3	372.6	372.7	372.7
137.5°	396.6	396.6	396.5	396.4	396.3	396.5	396.7	397.0	397.3	397.5	397.4
140°	412.5	412.6	412.7	412.8	412.9	413.0	413.1	413.2	413.3	413.4	413.4
142.5°	428.4	428.4	428.5	428.5	428.5	428.5	428.6	428.6	428.6	428.6	428.6
145°	450.0	450.3	450.6	450.9	451.2	451.4	451.5	451.6	451.7	451.8	451.7
147.5°	471.9	472.0	472.1	472.2	472.3	472.4	472.5	472.5	472.6	472.7	472.8
150°	485.3	485.4	485.4	485.5	485.7	485.7	485.7	485.7	485.7	485.7	485.7
152.5°	497.6	497.8	498.0	498.4	498.6	498.6	498.4	498.1	497.9	497.6	497.6
155°	514.6	515.0	515.4	515.8	516.3	516.3	515.8	515.4	515.0	514.6	514.8
157.5°	529.9	530.2	530.6	530.9	531.2	531.3	531.0	530.7	530.4	530.0	530.1
160°	538.6	539.1	539.6	540.1	540.6	540.7	540.3	540.1	539.8	539.5	539.6
162.5°	547.6	548.1	548.6	549.1	549.6	549.6	549.1	548.5	548.0	547.4	547.6
165°	559.4	559.8	560.2	560.5	560.9	560.9	560.2	559.7	559.0	558.5	558.6
167.5°	567.8	568.4	569.0	569.7	570.2	570.3	569.7	569.0	568.5	567.8	567.8
170°	572.4	573.1	573.9	574.6	575.3	575.3	574.7	574.1	573.5	572.9	572.8
172.5°	576.5	577.1	577.8	578.5	579.2	579.2	578.6	577.9	577.2	576.6	576.5
175°	580.6	581.3	582.0	582.7	583.4	583.4	582.7	582.0	581.3	580.6	580.7
177.5°	582.7	583.4	584.1	584.7	585.3	585.3	584.8	584.2	583.7	583.1	583.1
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	767.9	764.5	762.1	760.1	754.6	751.5	749.0	745.5	741.6	737.4	732.2
5°	811.6	801.1	793.4	781.6	770.6	761.3	751.8	743.1	732.6	721.3	712.9
7.5°	857.4	841.8	821.8	804.5	785.0	768.0	752.9	737.4	721.2	705.5	691.2
10°	886.5	866.4	844.2	818.0	793.4	771.5	751.1	731.4	712.3	693.2	676.8
12.5°	917.7	892.8	860.0	829.3	801.8	772.5	747.9	723.7	700.7	680.6	661.6
15°	959.8	923.8	885.8	844.9	808.5	774.3	740.7	710.1	684.3	657.7	639.3
17.5°	985.6	941.0	897.7	854.8	810.8	767.6	731.4	696.2	663.8	637.5	614.2
20°	1002.7	958.3	904.4	861.5	809.1	764.7	722.8	683.7	649.7	621.7	597.6
22.5°	1017.5	966.1	912.2	855.8	803.7	756.5	710.7	671.3	636.7	607.1	584.1
25°	1025.5	966.6	908.0	851.9	792.7	737.0	695.4	649.1	612.1	581.0	556.3
27.5°	1026.4	963.4	897.1	834.8	773.7	721.8	669.2	627.9	589.5	556.6	532.9
30°	1023.6	958.0	886.8	819.3	758.0	701.5	655.9	610.9	571.7	539.1	514.4
32.5°	1014.9	946.6	873.5	802.0	738.5	683.3	636.2	593.4	555.2	523.1	497.2
35°	990.0	922.5	844.5	770.2	705.2	649.4	606.9	563.4	525.2	494.7	469.8
37.5°	951.0	889.9	810.7	733.8	669.9	613.9	571.7	532.5	498.0	467.0	441.4
40°	917.0	863.3	783.8	708.9	639.8	586.5	547.1	511.0	476.8	447.5	423.2
42.5°	877.7	831.0	757.6	678.3	611.7	558.2	519.8	487.4	455.1	428.1	403.7
45°	807.9	777.1	708.0	634.6	565.3	514.8	478.1	449.7	422.6	396.1	375.7
47.5°	727.5	712.2	654.0	584.4	518.6	468.7	437.0	410.7	387.0	364.5	346.6
50°	673.4	666.1	615.8	548.7	485.8	438.9	406.9	384.4	364.0	344.3	327.3
52.5°	620.2	620.0	574.6	513.1	455.0	409.8	378.0	357.0	339.4	323.3	308.1
55°	538.8	547.4	512.0	457.1	405.0	364.3	335.6	316.9	304.5	291.3	279.9
57.5°	464.0	478.3	449.1	400.8	357.3	319.8	294.9	280.7	267.6	259.6	251.3
60°	415.2	428.7	405.9	365.3	324.2	292.2	268.5	255.8	244.4	238.8	233.0
62.5°	371.8	383.9	366.9	329.2	293.7	262.8	242.8	230.7	223.0	216.9	213.0
65°	309.7	320.0	305.5	278.1	247.5	222.8	206.5	196.9	189.6	187.1	182.8
67.5°	250.4	259.7	251.8	228.5	204.1	185.4	172.6	163.4	159.1	156.9	153.8
70°	215.2	224.4	216.0	195.7	176.9	161.2	149.2	143.9	139.3	138.4	134.1
72.5°	185.3	191.6	183.2	167.4	151.3	138.0	128.7	123.3	120.8	119.1	116.8
75°	139.0	144.6	139.0	126.7	115.3	106.0	98.0	95.9	93.1	92.1	90.6
77.5°	98.4	103.2	98.9	91.3	82.7	75.6	71.3	68.5	67.9	66.3	67.0
80°	75.2	78.3	74.3	69.1	62.3	57.4	54.3	52.7	50.9	50.2	51.5
82.5°	54.0	55.4	53.3	49.8	44.8	41.5	39.5	37.6	37.3	37.4	37.4
85°	28.0	27.7	27.4	24.3	22.8	20.7	19.4	19.1	18.8	19.4	20.0
87.5°	11.0	11.1	10.7	9.5	8.6	7.6	7.1	6.7	7.1	7.6	8.1
90°	8.3	7.5	6.7	5.8	4.7	3.6	2.5	1.3	2.5	3.6	4.7
92.5°	16.8	16.2	15.6	14.7	13.5	12.2	10.9	9.7	10.9	12.2	13.5
95°	33.0	32.2	31.5	30.7	29.8	28.9	28.0	27.1	28.0	28.9	29.8
97.5°	52.7	51.8	51.0	50.2	49.5	48.8	48.1	47.4	48.1	48.8	49.5
100°	67.3	66.4	65.5	64.9	64.5	64.1	63.7	63.2	63.7	64.1	64.5
102.5°	82.6	81.8	81.0	80.5	80.3	80.2	80.0	79.9	80.0	80.2	80.3
105°	106.7	106.3	105.9	105.7	105.6	105.4	105.4	105.3	105.4	105.4	105.6
107.5°	132.6	132.5	132.5	132.5	132.3	132.1	132.1	131.9	132.1	132.1	132.3
110°	150.7	150.8	150.8	150.8	150.6	150.4	150.2	150.0	150.2	150.4	150.6



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	168.5	168.7	168.9	169.0	168.9	168.9	168.8	168.8	168.8	168.9	168.9
115°	196.5	196.7	196.9	197.0	197.0	197.0	197.0	197.0	197.0	197.0	197.0
117.5°	223.6	223.7	223.9	223.9	223.8	223.7	223.6	223.6	223.6	223.7	223.8
120°	242.3	242.6	243.0	242.9	242.5	242.1	241.7	241.3	241.7	242.1	242.5
122.5°	260.1	260.2	260.4	260.3	260.2	260.0	259.8	259.7	259.8	260.0	260.2
125°	286.7	286.8	286.8	286.9	286.9	286.9	286.9	286.9	286.9	286.9	286.9
127.5°	312.5	312.7	312.8	312.8	312.5	312.2	311.9	311.6	311.9	312.2	312.5
130°	330.3	330.3	330.3	330.1	329.9	329.5	329.2	328.9	329.2	329.5	329.9
132.5°	347.5	347.5	347.6	347.5	347.3	347.1	346.9	346.7	346.9	347.1	347.3
135°	372.7	372.7	372.7	372.5	371.9	371.2	370.7	370.0	370.7	371.2	371.9
137.5°	397.2	397.0	396.9	396.6	396.3	396.1	395.8	395.5	395.8	396.1	396.3
140°	413.4	413.4	413.4	413.3	413.1	412.9	412.7	412.5	412.7	412.9	413.1
142.5°	428.7	428.8	428.9	428.9	428.6	428.5	428.3	428.0	428.3	428.5	428.6
145°	451.6	451.5	451.4	451.1	450.8	450.4	450.0	449.6	450.0	450.4	450.8
147.5°	472.9	472.9	473.0	472.9	472.3	471.8	471.3	470.9	471.3	471.8	472.3
150°	485.7	485.7	485.7	485.5	485.1	484.7	484.3	483.9	484.3	484.7	485.1
152.5°	497.5	497.4	497.3	497.2	496.9	496.7	496.5	496.2	496.5	496.7	496.9
155°	514.8	514.9	515.0	515.1	515.1	515.1	515.1	515.1	515.1	515.1	515.1
157.5°	530.1	530.1	530.1	530.3	530.4	530.6	530.8	531.0	530.8	530.6	530.4
160°	539.7	539.8	539.9	540.0	540.1	540.2	540.3	540.3	540.3	540.2	540.1
162.5°	547.6	547.7	547.8	548.0	548.3	548.5	548.8	549.1	548.8	548.5	548.3
165°	558.9	559.0	559.3	559.5	559.8	560.1	560.4	560.7	560.4	560.1	559.8
167.5°	567.8	567.8	567.8	568.0	568.4	568.8	569.3	569.7	569.3	568.8	568.4
170°	572.7	572.6	572.5	572.7	573.2	573.7	574.3	574.7	574.3	573.7	573.2
172.5°	576.5	576.5	576.5	576.6	577.1	577.5	577.9	578.3	577.9	577.5	577.1
175°	580.8	580.9	581.0	581.3	581.8	582.3	582.8	583.3	582.8	582.3	581.8
177.5°	583.1	583.1	583.1	583.3	583.8	584.2	584.6	584.9	584.6	584.2	583.8
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	729.8	727.5	724.3	719.9	716.2	712.3	711.2	709.8	712.7	710.3	709.6
5°	705.8	699.3	691.0	681.5	676.0	667.9	666.4	663.3	660.2	659.9	656.8
7.5°	680.5	671.0	660.1	650.4	641.4	632.6	626.9	625.7	621.1	618.5	615.4
10°	664.2	652.5	639.8	630.7	620.1	610.9	604.4	600.7	597.6	594.2	591.2
12.5°	645.0	632.6	622.1	612.1	599.7	592.6	582.0	575.6	575.0	575.0	567.0
15°	622.6	610.3	594.2	580.1	573.3	559.8	553.9	546.4	541.9	537.3	533.5
17.5°	597.1	581.7	569.2	552.9	540.0	529.2	521.4	517.0	510.1	503.5	498.8
20°	581.0	564.7	551.4	534.2	520.0	506.8	500.3	494.1	488.9	483.3	478.1
22.5°	564.7	547.6	531.5	514.7	501.5	487.5	481.3	472.9	467.9	464.8	459.5
25°	539.1	520.6	502.1	486.1	472.5	460.2	451.9	445.4	439.8	437.4	434.0
27.5°	511.2	492.8	475.0	456.8	441.4	432.5	425.8	420.9	417.7	414.5	412.9
30°	493.5	474.4	455.3	438.3	424.1	415.2	409.0	405.6	403.1	401.6	400.1
32.5°	475.5	456.6	436.5	421.0	408.4	400.4	395.7	392.3	391.1	390.5	390.0
35°	446.6	427.5	409.0	395.1	383.1	380.0	376.0	374.1	373.6	375.7	376.7
37.5°	418.7	400.9	383.9	370.5	362.6	358.1	356.7	356.8	359.0	360.9	363.1
40°	400.7	383.4	367.4	355.7	348.3	345.5	344.9	346.4	348.9	351.1	353.6
42.5°	383.2	366.1	351.6	340.6	335.5	333.0	333.4	334.9	338.3	341.0	344.7
45°	356.0	341.8	327.6	318.7	314.4	315.0	315.0	317.7	321.2	325.2	329.2
47.5°	330.4	316.1	304.4	296.9	294.7	294.1	295.9	299.5	304.4	309.3	315.0
50°	313.1	299.6	289.4	282.7	280.2	281.1	283.6	286.9	292.8	299.0	304.8
52.5°	295.6	283.3	273.9	267.6	265.9	267.5	270.0	275.4	280.5	287.2	294.2
55°	268.5	258.0	250.6	246.0	245.3	246.3	249.1	254.9	262.3	270.6	277.4
57.5°	241.4	232.7	225.9	222.7	223.0	223.9	228.4	235.4	243.3	252.2	260.9
60°	223.2	215.2	209.6	207.2	207.5	209.3	214.8	221.3	231.2	239.8	249.1
62.5°	205.9	198.8	193.5	191.3	190.9	195.0	200.3	207.0	216.9	226.5	236.5
65°	178.2	172.6	168.3	167.1	167.9	171.0	177.8	186.8	195.1	205.3	215.8
67.5°	151.0	146.5	143.5	144.1	145.2	149.7	155.4	163.1	172.5	183.1	193.5
70°	133.8	129.4	127.0	127.3	129.1	134.7	139.7	147.3	157.5	168.3	176.9
72.5°	116.1	113.2	111.0	112.3	114.1	118.0	124.1	131.8	140.8	150.8	159.9
75°	89.0	89.0	87.9	88.8	91.6	95.2	99.9	107.9	116.8	124.8	132.2
77.5°	66.1	65.4	66.2	67.3	68.9	73.3	78.6	84.4	91.0	99.1	105.2
80°	50.5	50.9	52.4	54.3	54.9	58.2	63.8	69.1	74.3	81.0	86.9
82.5°	37.9	38.3	39.1	41.4	42.1	45.7	49.3	54.5	59.3	63.8	68.7
85°	20.7	20.7	22.2	23.1	24.6	27.1	29.3	32.4	36.7	39.8	44.4
87.5°	9.0	9.3	10.4	11.0	12.0	13.3	13.9	16.8	17.9	19.3	21.5
90°	5.8	6.7	7.5	8.3	9.1	9.9	10.5	11.2	11.7	12.4	12.8
92.5°	14.7	15.6	16.2	16.8	17.3	17.9	18.2	18.6	19.0	19.3	19.6
95°	30.7	31.5	32.2	33.0	33.7	34.3	34.6	34.9	35.3	35.6	35.7
97.5°	50.2	51.0	51.8	52.7	53.5	54.3	54.7	55.1	55.4	55.8	55.9
100°	64.9	65.5	66.4	67.3	68.2	69.2	69.3	69.6	69.7	69.9	70.0
102.5°	80.5	81.0	81.8	82.6	83.5	84.3	84.6	84.8	85.2	85.4	85.6
105°	105.7	105.9	106.3	106.7	107.1	107.5	107.8	108.1	108.4	108.8	109.0
107.5°	132.5	132.5	132.5	132.6	132.7	132.8	133.0	133.3	133.6	133.9	134.0
110°	150.8	150.8	150.8	150.7	150.6	150.4	150.3	150.0	149.9	149.6	149.7



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	169.0	168.9	168.7	168.5	168.3	168.2	168.1	168.1	168.0	168.0	168.0
115°	197.0	196.9	196.7	196.5	196.3	196.1	196.0	195.9	195.8	195.7	195.6
117.5°	223.9	223.9	223.7	223.6	223.4	223.3	222.9	222.6	222.3	221.9	221.7
120°	242.9	243.0	242.6	242.3	242.0	241.7	241.2	240.7	240.2	239.7	239.6
122.5°	260.3	260.4	260.2	260.1	259.9	259.8	259.4	259.1	258.8	258.4	258.1
125°	286.9	286.8	286.8	286.7	286.5	286.5	286.2	286.1	285.8	285.7	285.4
127.5°	312.8	312.8	312.7	312.5	312.4	312.2	312.0	311.8	311.6	311.4	311.2
130°	330.1	330.3	330.3	330.3	330.3	330.3	330.1	329.9	329.7	329.5	329.2
132.5°	347.5	347.6	347.5	347.5	347.4	347.3	347.1	346.9	346.7	346.5	346.3
135°	372.5	372.7	372.7	372.7	372.7	372.7	372.6	372.3	372.2	371.9	371.7
137.5°	396.6	396.9	397.0	397.2	397.4	397.5	397.3	397.0	396.7	396.5	396.3
140°	413.3	413.4	413.4	413.4	413.4	413.4	413.3	413.2	413.1	413.0	412.9
142.5°	428.9	428.9	428.8	428.7	428.6	428.6	428.6	428.6	428.6	428.5	428.5
145°	451.1	451.4	451.5	451.6	451.7	451.8	451.7	451.6	451.5	451.4	451.2
147.5°	472.9	473.0	472.9	472.9	472.8	472.7	472.6	472.5	472.5	472.4	472.3
150°	485.5	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7	485.7
152.5°	497.2	497.3	497.4	497.5	497.6	497.6	497.9	498.1	498.4	498.6	498.6
155°	515.1	515.0	514.9	514.8	514.8	514.6	515.0	515.4	515.8	516.3	516.3
157.5°	530.3	530.1	530.1	530.1	530.1	530.0	530.4	530.7	531.0	531.3	531.2
160°	540.0	539.9	539.8	539.7	539.6	539.5	539.8	540.1	540.3	540.7	540.6
162.5°	548.0	547.8	547.7	547.6	547.6	547.4	548.0	548.5	549.1	549.6	549.6
165°	559.5	559.3	559.0	558.9	558.6	558.5	559.0	559.7	560.2	560.9	560.9
167.5°	568.0	567.8	567.8	567.8	567.8	567.8	568.5	569.0	569.7	570.3	570.2
170°	572.7	572.5	572.6	572.7	572.8	572.9	573.5	574.1	574.7	575.3	575.3
172.5°	576.6	576.5	576.5	576.5	576.5	576.6	577.2	577.9	578.6	579.2	579.2
175°	581.3	581.0	580.9	580.8	580.7	580.6	581.3	582.0	582.7	583.4	583.4
177.5°	583.3	583.1	583.1	583.1	583.1	583.1	583.7	584.2	584.8	585.3	585.3
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	709.0	708.5	706.8	706.5	706.8	708.5	709.0	709.6	710.3	712.7	709.8
5°	655.0	653.5	652.5	655.9	652.5	653.5	655.0	656.8	659.9	660.2	663.3
7.5°	614.3	613.0	610.3	609.4	610.3	613.0	614.3	615.4	618.5	621.1	625.7
10°	588.1	586.8	584.4	583.8	584.4	586.8	588.1	591.2	594.2	597.6	600.7
12.5°	562.9	560.5	560.0	560.6	560.0	560.5	562.9	567.0	575.0	575.0	575.6
15°	529.5	528.3	524.9	525.9	524.9	528.3	529.5	533.5	537.3	541.9	546.4
17.5°	496.6	495.1	491.0	494.6	491.0	495.1	496.6	498.8	503.5	510.1	517.0
20°	475.9	473.4	471.3	471.0	471.3	473.4	475.9	478.1	483.3	488.9	494.1
22.5°	456.1	453.9	453.8	451.7	453.8	453.9	456.1	459.5	464.8	467.9	472.9
25°	431.5	429.4	428.7	427.2	428.7	429.4	431.5	434.0	437.4	439.8	445.4
27.5°	412.6	411.5	410.4	410.9	410.4	411.5	412.6	412.9	414.5	417.7	420.9
30°	401.0	400.7	400.1	400.1	400.1	400.7	401.0	400.1	401.6	403.1	405.6
32.5°	391.4	391.3	391.7	391.7	391.7	391.3	391.4	390.0	390.5	391.1	392.3
35°	377.9	378.8	379.5	378.5	379.5	378.8	377.9	376.7	375.7	373.6	374.1
37.5°	365.7	366.6	367.5	368.5	367.5	366.6	365.7	363.1	360.9	359.0	356.8
40°	356.3	358.5	359.1	360.6	359.1	358.5	356.3	353.6	351.1	348.9	346.4
42.5°	347.5	349.8	351.4	351.7	351.4	349.8	347.5	344.7	341.0	338.3	334.9
45°	333.8	336.3	338.4	338.4	338.4	336.3	333.8	329.2	325.2	321.2	317.7
47.5°	319.7	323.3	325.4	326.0	325.4	323.3	319.7	315.0	309.3	304.4	299.5
50°	310.1	314.4	316.6	318.1	316.6	314.4	310.1	304.8	299.0	292.8	286.9
52.5°	300.7	305.0	307.9	308.7	307.9	305.0	300.7	294.2	287.2	280.5	275.4
55°	284.5	290.7	294.1	295.2	294.1	290.7	284.5	277.4	270.6	262.3	254.9
57.5°	269.2	274.9	278.8	279.7	278.8	274.9	269.2	260.9	252.2	243.3	235.4
60°	257.4	263.6	268.5	269.4	268.5	263.6	257.4	249.1	239.8	231.2	221.3
62.5°	245.3	251.7	256.1	258.6	256.1	251.7	245.3	236.5	226.5	216.9	207.0
65°	224.4	230.8	235.2	236.1	235.2	230.8	224.4	215.8	205.3	195.1	186.8
67.5°	201.6	208.0	210.9	212.7	210.9	208.0	201.6	193.5	183.1	172.5	163.1
70°	185.5	190.8	193.8	195.4	193.8	190.8	185.5	176.9	168.3	157.5	147.3
72.5°	167.3	172.8	176.3	176.7	176.3	172.8	167.3	159.9	150.8	140.8	131.8
75°	139.3	144.3	146.1	146.1	146.1	144.3	139.3	132.2	124.8	116.8	107.9
77.5°	110.3	112.8	115.2	115.7	115.2	112.8	110.3	105.2	99.1	91.0	84.4
80°	91.6	93.1	94.9	94.9	94.9	93.1	91.6	86.9	81.0	74.3	69.1
82.5°	72.3	73.6	75.4	75.2	75.4	73.6	72.3	68.7	63.8	59.3	54.5
85°	43.7	46.6	46.3	45.6	46.3	46.6	43.7	44.4	39.8	36.7	32.4
87.5°	22.3	22.6	23.4	23.9	23.4	22.6	22.3	21.5	19.3	17.9	16.8
90°	13.0	13.2	13.4	13.5	13.4	13.2	13.0	12.8	12.4	11.7	11.2
92.5°	19.7	19.8	20.0	20.0	20.0	19.8	19.7	19.6	19.3	19.0	18.6
95°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.6	35.3	34.9
97.5°	55.9	55.9	55.9	55.9	55.9	55.9	55.9	55.9	55.8	55.4	55.1
100°	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0	69.9	69.7	69.6
102.5°	85.7	85.8	85.9	86.0	85.9	85.8	85.7	85.6	85.4	85.2	84.8
105°	109.3	109.6	110.0	110.3	110.0	109.6	109.3	109.0	108.8	108.4	108.1
107.5°	134.0	134.0	134.0	134.0	134.0	134.0	134.0	134.0	133.9	133.6	133.3
110°	150.0	150.3	150.6	150.9	150.6	150.3	150.0	149.7	149.6	149.9	150.0



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	168.1	168.1	168.2	168.3	168.2	168.1	168.1	168.0	168.0	168.0	168.1
115°	195.5	195.4	195.3	195.2	195.3	195.4	195.5	195.6	195.7	195.8	195.9
117.5°	221.4	221.3	221.0	220.9	221.0	221.3	221.4	221.7	221.9	222.3	222.6
120°	239.8	240.0	240.2	240.3	240.2	240.0	239.8	239.6	239.7	240.2	240.7
122.5°	257.7	257.4	257.0	256.7	257.0	257.4	257.7	258.1	258.4	258.8	259.1
125°	285.3	285.0	284.9	284.6	284.9	285.0	285.3	285.4	285.7	285.8	286.1
127.5°	311.1	310.9	310.8	310.6	310.8	310.9	311.1	311.2	311.4	311.6	311.8
130°	328.8	328.4	328.0	327.6	328.0	328.4	328.8	329.2	329.5	329.7	329.9
132.5°	346.1	345.9	345.8	345.6	345.8	345.9	346.1	346.3	346.5	346.7	346.9
135°	371.4	371.1	370.8	370.5	370.8	371.1	371.4	371.7	371.9	372.2	372.3
137.5°	396.4	396.5	396.6	396.6	396.6	396.5	396.4	396.3	396.5	396.7	397.0
140°	412.8	412.7	412.6	412.5	412.6	412.7	412.8	412.9	413.0	413.1	413.2
142.5°	428.5	428.5	428.4	428.4	428.4	428.5	428.5	428.5	428.5	428.6	428.6
145°	450.9	450.6	450.3	450.0	450.3	450.6	450.9	451.2	451.4	451.5	451.6
147.5°	472.2	472.1	472.0	471.9	472.0	472.1	472.2	472.3	472.4	472.5	472.5
150°	485.5	485.4	485.4	485.3	485.4	485.4	485.5	485.7	485.7	485.7	485.7
152.5°	498.4	498.0	497.8	497.6	497.8	498.0	498.4	498.6	498.6	498.4	498.1
155°	515.8	515.4	515.0	514.6	515.0	515.4	515.8	516.3	516.3	515.8	515.4
157.5°	530.9	530.6	530.2	529.9	530.2	530.6	530.9	531.2	531.3	531.0	530.7
160°	540.1	539.6	539.1	538.6	539.1	539.6	540.1	540.6	540.7	540.3	540.1
162.5°	549.1	548.6	548.1	547.6	548.1	548.6	549.1	549.6	549.6	549.1	548.5
165°	560.5	560.2	559.8	559.4	559.8	560.2	560.5	560.9	560.9	560.2	559.7
167.5°	569.7	569.0	568.4	567.8	568.4	569.0	569.7	570.2	570.3	569.7	569.0
170°	574.6	573.9	573.1	572.4	573.1	573.9	574.6	575.3	575.3	574.7	574.1
172.5°	578.5	577.8	577.1	576.5	577.1	577.8	578.5	579.2	579.2	578.6	577.9
175°	582.7	582.0	581.3	580.6	581.3	582.0	582.7	583.4	583.4	582.7	582.0
177.5°	584.7	584.1	583.4	582.7	583.4	584.1	584.7	585.3	585.3	584.8	584.2
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	711.2	712.3	716.2	719.9	724.3	727.5	729.8	732.2	737.4	741.6	745.5
5°	666.4	667.9	676.0	681.5	691.0	699.3	705.8	712.9	721.3	732.6	743.1
7.5°	626.9	632.6	641.4	650.4	660.1	671.0	680.5	691.2	705.5	721.2	737.4
10°	604.4	610.9	620.1	630.7	639.8	652.5	664.2	676.8	693.2	712.3	731.4
12.5°	582.0	592.6	599.7	612.1	622.1	632.6	645.0	661.6	680.6	700.7	723.7
15°	553.9	559.8	573.3	580.1	594.2	610.3	622.6	639.3	657.7	684.3	710.1
17.5°	521.4	529.2	540.0	552.9	569.2	581.7	597.1	614.2	637.5	663.8	696.2
20°	500.3	506.8	520.0	534.2	551.4	564.7	581.0	597.6	621.7	649.7	683.7
22.5°	481.3	487.5	501.5	514.7	531.5	547.6	564.7	584.1	607.1	636.7	671.3
25°	451.9	460.2	472.5	486.1	502.1	520.6	539.1	556.3	581.0	612.1	649.1
27.5°	425.8	432.5	441.4	456.8	475.0	492.8	511.2	532.9	556.6	589.5	627.9
30°	409.0	415.2	424.1	438.3	455.3	474.4	493.5	514.4	539.1	571.7	610.9
32.5°	395.7	400.4	408.4	421.0	436.5	456.6	475.5	497.2	523.1	555.2	593.4
35°	376.0	380.0	383.1	395.1	409.0	427.5	446.6	469.8	494.7	525.2	563.4
37.5°	356.7	358.1	362.6	370.5	383.9	400.9	418.7	441.4	467.0	498.0	532.5
40°	344.9	345.5	348.3	355.7	367.4	383.4	400.7	423.2	447.5	476.8	511.0
42.5°	333.4	333.0	335.5	340.6	351.6	366.1	383.2	403.7	428.1	455.1	487.4
45°	315.0	315.0	314.4	318.7	327.6	341.8	356.0	375.7	396.1	422.6	449.7
47.5°	295.9	294.1	294.7	296.9	304.4	316.1	330.4	346.6	364.5	387.0	410.7
50°	283.6	281.1	280.2	282.7	289.4	299.6	313.1	327.3	344.3	364.0	384.4
52.5°	270.0	267.5	265.9	267.6	273.9	283.3	295.6	308.1	323.3	339.4	357.0
55°	249.1	246.3	245.3	246.0	250.6	258.0	268.5	279.9	291.3	304.5	316.9
57.5°	228.4	223.9	223.0	222.7	225.9	232.7	241.4	251.3	259.6	267.6	280.7
60°	214.8	209.3	207.5	207.2	209.6	215.2	223.2	233.0	238.8	244.4	255.8
62.5°	200.3	195.0	190.9	191.3	193.5	198.8	205.9	213.0	216.9	223.0	230.7
65°	177.8	171.0	167.9	167.1	168.3	172.6	178.2	182.8	187.1	189.6	196.9
67.5°	155.4	149.7	145.2	144.1	143.5	146.5	151.0	153.8	156.9	159.1	163.4
70°	139.7	134.7	129.1	127.3	127.0	129.4	133.8	134.1	138.4	139.3	143.9
72.5°	124.1	118.0	114.1	112.3	111.0	113.2	116.1	116.8	119.1	120.8	123.3
75°	99.9	95.2	91.6	88.8	87.9	89.0	89.0	90.6	92.1	93.1	95.9
77.5°	78.6	73.3	68.9	67.3	66.2	65.4	66.1	67.0	66.3	67.9	68.5
80°	63.8	58.2	54.9	54.3	52.4	50.9	50.5	51.5	50.2	50.9	52.7
82.5°	49.3	45.7	42.1	41.4	39.1	38.3	37.9	37.4	37.4	37.3	37.6
85°	29.3	27.1	24.6	23.1	22.2	20.7	20.7	20.0	19.4	18.8	19.1
87.5°	13.9	13.3	12.0	11.0	10.4	9.3	9.0	8.1	7.6	7.1	6.7
90°	10.5	9.9	9.1	8.3	7.5	6.7	5.8	4.7	3.6	2.5	1.3
92.5°	18.2	17.9	17.3	16.8	16.2	15.6	14.7	13.5	12.2	10.9	9.7
95°	34.6	34.3	33.7	33.0	32.2	31.5	30.7	29.8	28.9	28.0	27.1
97.5°	54.7	54.3	53.5	52.7	51.8	51.0	50.2	49.5	48.8	48.1	47.4
100°	69.3	69.2	68.2	67.3	66.4	65.5	64.9	64.5	64.1	63.7	63.2
102.5°	84.6	84.3	83.5	82.6	81.8	81.0	80.5	80.3	80.2	80.0	79.9
105°	107.8	107.5	107.1	106.7	106.3	105.9	105.7	105.6	105.4	105.4	105.3
107.5°	133.0	132.8	132.7	132.6	132.5	132.5	132.5	132.3	132.1	132.1	131.9
110°	150.3	150.4	150.6	150.7	150.8	150.8	150.8	150.6	150.4	150.2	150.0



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	168.1	168.2	168.3	168.5	168.7	168.9	169.0	168.9	168.9	168.8	168.8
115°	196.0	196.1	196.3	196.5	196.7	196.9	197.0	197.0	197.0	197.0	197.0
117.5°	222.9	223.3	223.4	223.6	223.7	223.9	223.9	223.8	223.7	223.6	223.6
120°	241.2	241.7	242.0	242.3	242.6	243.0	242.9	242.5	242.1	241.7	241.3
122.5°	259.4	259.8	259.9	260.1	260.2	260.4	260.3	260.2	260.0	259.8	259.7
125°	286.2	286.5	286.5	286.7	286.8	286.8	286.9	286.9	286.9	286.9	286.9
127.5°	312.0	312.2	312.4	312.5	312.7	312.8	312.8	312.5	312.2	311.9	311.6
130°	330.1	330.3	330.3	330.3	330.3	330.3	330.1	329.9	329.5	329.2	328.9
132.5°	347.1	347.3	347.4	347.5	347.5	347.6	347.5	347.3	347.1	346.9	346.7
135°	372.6	372.7	372.7	372.7	372.7	372.7	372.5	371.9	371.2	370.7	370.0
137.5°	397.3	397.5	397.4	397.2	397.0	396.9	396.6	396.3	396.1	395.8	395.5
140°	413.3	413.4	413.4	413.4	413.4	413.4	413.3	413.1	412.9	412.7	412.5
142.5°	428.6	428.6	428.6	428.7	428.8	428.9	428.9	428.6	428.5	428.3	428.0
145°	451.7	451.8	451.7	451.6	451.5	451.4	451.1	450.8	450.4	450.0	449.6
147.5°	472.6	472.7	472.8	472.9	472.9	473.0	472.9	472.3	471.8	471.3	470.9
150°	485.7	485.7	485.7	485.7	485.7	485.7	485.5	485.1	484.7	484.3	483.9
152.5°	497.9	497.6	497.6	497.5	497.4	497.3	497.2	496.9	496.7	496.5	496.2
155°	515.0	514.6	514.8	514.8	514.9	515.0	515.1	515.1	515.1	515.1	515.1
157.5°	530.4	530.0	530.1	530.1	530.1	530.1	530.3	530.4	530.6	530.8	531.0
160°	539.8	539.5	539.6	539.7	539.8	539.9	540.0	540.1	540.2	540.3	540.3
162.5°	548.0	547.4	547.6	547.6	547.7	547.8	548.0	548.3	548.5	548.8	549.1
165°	559.0	558.5	558.6	558.9	559.0	559.3	559.5	559.8	560.1	560.4	560.7
167.5°	568.5	567.8	567.8	567.8	567.8	567.8	568.0	568.4	568.8	569.3	569.7
170°	573.5	572.9	572.8	572.7	572.6	572.5	572.7	573.2	573.7	574.3	574.7
172.5°	577.2	576.6	576.5	576.5	576.5	576.5	576.6	577.1	577.5	577.9	578.3
175°	581.3	580.6	580.7	580.8	580.9	581.0	581.3	581.8	582.3	582.8	583.3
177.5°	583.7	583.1	583.1	583.1	583.1	583.1	583.3	583.8	584.2	584.6	584.9
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	749.0	751.5	754.6	760.1	762.1	764.5	767.9	767.7	768.7	772.4	780.3
5°	751.8	761.3	770.6	781.6	793.4	801.1	811.6	818.0	824.5	832.8	847.0
7.5°	752.9	768.0	785.0	804.5	821.8	841.8	857.4	872.0	885.3	902.9	919.7
10°	751.1	771.5	793.4	818.0	844.2	866.4	886.5	909.3	928.7	949.9	969.1
12.5°	747.9	772.5	801.8	829.3	860.0	892.8	917.7	940.8	966.6	991.1	1020.6
15°	740.7	774.3	808.5	844.9	885.8	923.8	959.8	989.7	1017.5	1054.2	1092.7
17.5°	731.4	767.6	810.8	854.8	897.7	941.0	985.6	1030.5	1065.6	1111.1	1141.3
20°	722.8	764.7	809.1	861.5	904.4	958.3	1002.7	1046.1	1094.2	1139.5	1175.6
22.5°	710.7	756.5	803.7	855.8	912.2	966.1	1017.5	1064.6	1112.7	1162.0	1205.6
25°	695.4	737.0	792.7	851.9	908.0	966.6	1025.5	1084.7	1136.4	1188.5	1229.2
27.5°	669.2	721.8	773.7	834.8	897.1	963.4	1026.4	1088.3	1142.5	1185.3	1210.6
30°	655.9	701.5	758.0	819.3	886.8	958.0	1023.6	1084.3	1134.9	1169.1	1179.2
32.5°	636.2	683.3	738.5	802.0	873.5	946.6	1014.9	1072.2	1114.4	1132.3	1120.1
35°	606.9	649.4	705.2	770.2	844.5	922.5	990.0	1038.4	1060.0	1043.1	1000.8
37.5°	571.7	613.9	669.9	733.8	810.7	889.9	951.0	985.8	978.7	936.5	873.5
40°	547.1	586.5	639.8	708.9	783.8	863.3	917.0	935.8	916.1	855.6	788.8
42.5°	519.8	558.2	611.7	678.3	757.6	831.0	877.7	879.3	846.3	774.0	706.9
45°	478.1	514.8	565.3	634.6	708.0	777.1	807.9	792.7	731.7	662.0	594.5
47.5°	437.0	468.7	518.6	584.4	654.0	712.2	727.5	700.3	635.3	567.6	505.0
50°	406.9	438.9	485.8	548.7	615.8	666.1	673.4	637.4	573.6	505.5	456.5
52.5°	378.0	409.8	455.0	513.1	574.6	620.0	620.2	578.5	514.9	454.2	408.6
55°	335.6	364.3	405.0	457.1	512.0	547.4	538.8	495.6	440.5	387.8	348.0
57.5°	294.9	319.8	357.3	400.8	449.1	478.3	464.0	422.5	373.2	328.5	298.3
60°	268.5	292.2	324.2	365.3	405.9	428.7	415.2	377.6	332.2	296.2	270.0
62.5°	242.8	262.8	293.7	329.2	366.9	383.9	371.8	334.7	295.6	262.9	241.6
65°	206.5	222.8	247.5	278.1	305.5	320.0	309.7	275.2	245.3	221.9	204.9
67.5°	172.6	185.4	204.1	228.5	251.8	259.7	250.4	226.3	201.1	182.3	170.3
70°	149.2	161.2	176.9	195.7	216.0	224.4	215.2	196.1	175.4	158.1	146.4
72.5°	128.7	138.0	151.3	167.4	183.2	191.6	185.3	166.9	149.5	136.7	126.7
75°	98.0	106.0	115.3	126.7	139.0	144.6	139.0	126.4	114.3	104.8	97.7
77.5°	71.3	75.6	82.7	91.3	98.9	103.2	98.4	89.8	82.5	76.0	72.4
80°	54.3	57.4	62.3	69.1	74.3	78.3	75.2	68.1	62.3	57.9	56.4
82.5°	39.5	41.5	44.8	49.8	53.3	55.4	54.0	48.9	46.5	42.6	41.1
85°	19.4	20.7	22.8	24.3	27.4	27.7	28.0	25.9	23.8	22.8	21.5
87.5°	7.1	7.6	8.6	9.5	10.7	11.1	11.0	11.2	10.4	10.2	9.3
90°	2.5	3.6	4.7	5.8	6.7	7.5	8.3	9.1	9.9	10.5	11.2
92.5°	10.9	12.2	13.5	14.7	15.6	16.2	16.8	17.3	17.9	18.2	18.6
95°	28.0	28.9	29.8	30.7	31.5	32.2	33.0	33.7	34.3	34.6	34.9
97.5°	48.1	48.8	49.5	50.2	51.0	51.8	52.7	53.5	54.3	54.7	55.1
100°	63.7	64.1	64.5	64.9	65.5	66.4	67.3	68.2	69.2	69.3	69.6
102.5°	80.0	80.2	80.3	80.5	81.0	81.8	82.6	83.5	84.3	84.6	84.8
105°	105.4	105.4	105.6	105.7	105.9	106.3	106.7	107.1	107.5	107.8	108.1
107.5°	132.1	132.1	132.3	132.5	132.5	132.5	132.6	132.7	132.8	133.0	133.3
110°	150.2	150.4	150.6	150.8	150.8	150.8	150.7	150.6	150.4	150.3	150.0



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.8	168.9	168.9	169.0	168.9	168.7	168.5	168.3	168.2	168.1	168.1
115°	197.0	197.0	197.0	197.0	196.9	196.7	196.5	196.3	196.1	196.0	195.9
117.5°	223.6	223.7	223.8	223.9	223.9	223.7	223.6	223.4	223.3	222.9	222.6
120°	241.7	242.1	242.5	242.9	243.0	242.6	242.3	242.0	241.7	241.2	240.7
122.5°	259.8	260.0	260.2	260.3	260.4	260.2	260.1	259.9	259.8	259.4	259.1
125°	286.9	286.9	286.9	286.9	286.8	286.8	286.7	286.5	286.5	286.2	286.1
127.5°	311.9	312.2	312.5	312.8	312.8	312.7	312.5	312.4	312.2	312.0	311.8
130°	329.2	329.5	329.9	330.1	330.3	330.3	330.3	330.3	330.3	330.1	329.9
132.5°	346.9	347.1	347.3	347.5	347.6	347.5	347.5	347.4	347.3	347.1	346.9
135°	370.7	371.2	371.9	372.5	372.7	372.7	372.7	372.7	372.7	372.6	372.3
137.5°	395.8	396.1	396.3	396.6	396.9	397.0	397.2	397.4	397.5	397.3	397.0
140°	412.7	412.9	413.1	413.3	413.4	413.4	413.4	413.4	413.4	413.3	413.2
142.5°	428.3	428.5	428.6	428.9	428.9	428.8	428.7	428.6	428.6	428.6	428.6
145°	450.0	450.4	450.8	451.1	451.4	451.5	451.6	451.7	451.8	451.7	451.6
147.5°	471.3	471.8	472.3	472.9	473.0	472.9	472.9	472.8	472.7	472.6	472.5
150°	484.3	484.7	485.1	485.5	485.7	485.7	485.7	485.7	485.7	485.7	485.7
152.5°	496.5	496.7	496.9	497.2	497.3	497.4	497.5	497.6	497.6	497.9	498.1
155°	515.1	515.1	515.1	515.1	515.0	514.9	514.8	514.8	514.6	515.0	515.4
157.5°	530.8	530.6	530.4	530.3	530.1	530.1	530.1	530.1	530.0	530.4	530.7
160°	540.3	540.2	540.1	540.0	539.9	539.8	539.7	539.6	539.5	539.8	540.1
162.5°	548.8	548.5	548.3	548.0	547.8	547.7	547.6	547.6	547.4	548.0	548.5
165°	560.4	560.1	559.8	559.5	559.3	559.0	558.9	558.6	558.5	559.0	559.7
167.5°	569.3	568.8	568.4	568.0	567.8	567.8	567.8	567.8	567.8	568.5	569.0
170°	574.3	573.7	573.2	572.7	572.5	572.6	572.7	572.8	572.9	573.5	574.1
172.5°	577.9	577.5	577.1	576.6	576.5	576.5	576.5	576.5	576.6	577.2	577.9
175°	582.8	582.3	581.8	581.3	581.0	580.9	580.8	580.7	580.6	581.3	582.0
177.5°	584.6	584.2	583.8	583.3	583.1	583.1	583.1	583.1	583.1	583.7	584.2
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	744.0	744.0	744.0	744.0	744.0	744.0	744.0
2.5°	784.3	784.7	787.0	788.7	789.2	791.6	791.9
5°	853.2	858.4	868.5	869.5	871.0	879.1	872.9
7.5°	933.9	947.2	956.1	963.9	966.8	970.3	969.6
10°	985.7	1005.4	1015.3	1031.0	1031.7	1035.6	1033.2
12.5°	1037.8	1060.7	1078.6	1081.6	1094.7	1096.8	1100.3
15°	1111.4	1135.8	1160.8	1169.7	1187.9	1192.2	1199.0
17.5°	1180.7	1205.6	1223.1	1246.3	1253.7	1263.7	1257.0
20°	1218.7	1245.9	1268.0	1286.2	1294.0	1299.5	1298.9
22.5°	1241.7	1269.0	1287.0	1300.8	1308.0	1310.3	1310.2
25°	1256.0	1271.8	1277.3	1282.5	1274.5	1271.8	1273.0
27.5°	1216.1	1212.0	1197.5	1178.5	1158.8	1143.1	1134.6
30°	1161.1	1137.0	1115.2	1077.0	1057.2	1045.5	1035.0
32.5°	1083.2	1045.0	1003.0	968.0	945.5	928.1	925.5
35°	949.7	892.3	840.8	798.0	775.8	757.0	752.7
37.5°	807.4	747.8	701.5	663.7	639.8	626.6	614.3
40°	712.9	661.8	616.2	584.1	565.9	556.3	548.7
42.5°	640.2	593.4	548.1	523.6	507.2	501.4	496.9
45°	539.7	496.2	464.8	446.3	436.7	426.9	422.2
47.5°	459.2	423.9	403.1	387.5	377.2	371.4	368.4
50°	413.6	384.7	366.1	354.2	344.9	340.2	337.8
52.5°	373.2	349.4	333.9	324.3	318.1	314.7	313.6
55°	321.5	303.3	293.4	285.1	280.5	277.4	276.2
57.5°	279.4	265.5	257.5	250.6	248.8	246.2	245.3
60°	251.8	241.1	234.2	229.7	228.1	225.0	225.6
62.5°	227.4	218.6	212.8	210.2	208.1	205.5	206.4
65°	192.3	185.8	182.8	180.3	177.8	176.3	177.5
67.5°	161.4	156.9	152.7	151.3	150.1	149.9	148.5
70°	141.2	137.4	133.8	132.8	132.8	131.6	131.3
72.5°	121.7	119.0	116.5	115.8	114.9	115.3	114.1
75°	94.0	91.8	90.9	90.0	89.7	89.7	88.8
77.5°	69.5	67.9	66.4	66.4	65.3	64.9	64.7
80°	52.7	52.1	50.9	50.9	50.2	50.5	49.9
82.5°	39.6	38.7	38.5	38.0	37.2	37.2	36.6
85°	21.2	20.4	20.0	19.1	18.5	19.1	18.5
87.5°	9.7	9.6	9.4	9.0	8.8	8.9	8.2
90°	11.7	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	19.0	19.3	19.6	19.7	19.8	20.0	20.0
95°	35.3	35.6	35.7	35.7	35.7	35.7	35.7
97.5°	55.4	55.8	55.9	55.9	55.9	55.9	55.9
100°	69.7	69.9	70.0	70.0	70.0	70.0	70.0
102.5°	85.2	85.4	85.6	85.7	85.8	85.9	86.0
105°	108.4	108.8	109.0	109.3	109.6	110.0	110.3
107.5°	133.6	133.9	134.0	134.0	134.0	134.0	134.0
110°	149.9	149.6	149.7	150.0	150.3	150.6	150.9



TEST NUMBER: P332545-927

CATALOG NUMBER: S124DIP-S575D590U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	168.0	168.0	168.0	168.1	168.1	168.2	168.3
115°	195.8	195.7	195.6	195.5	195.4	195.3	195.2
117.5°	222.3	221.9	221.7	221.4	221.3	221.0	220.9
120°	240.2	239.7	239.6	239.8	240.0	240.2	240.3
122.5°	258.8	258.4	258.1	257.7	257.4	257.0	256.7
125°	285.8	285.7	285.4	285.3	285.0	284.9	284.6
127.5°	311.6	311.4	311.2	311.1	310.9	310.8	310.6
130°	329.7	329.5	329.2	328.8	328.4	328.0	327.6
132.5°	346.7	346.5	346.3	346.1	345.9	345.8	345.6
135°	372.2	371.9	371.7	371.4	371.1	370.8	370.5
137.5°	396.7	396.5	396.3	396.4	396.5	396.6	396.6
140°	413.1	413.0	412.9	412.8	412.7	412.6	412.5
142.5°	428.6	428.5	428.5	428.5	428.5	428.4	428.4
145°	451.5	451.4	451.2	450.9	450.6	450.3	450.0
147.5°	472.5	472.4	472.3	472.2	472.1	472.0	471.9
150°	485.7	485.7	485.7	485.5	485.4	485.4	485.3
152.5°	498.4	498.6	498.6	498.4	498.0	497.8	497.6
155°	515.8	516.3	516.3	515.8	515.4	515.0	514.6
157.5°	531.0	531.3	531.2	530.9	530.6	530.2	529.9
160°	540.3	540.7	540.6	540.1	539.6	539.1	538.6
162.5°	549.1	549.6	549.6	549.1	548.6	548.1	547.6
165°	560.2	560.9	560.9	560.5	560.2	559.8	559.4
167.5°	569.7	570.3	570.2	569.7	569.0	568.4	567.8
170°	574.7	575.3	575.3	574.6	573.9	573.1	572.4
172.5°	578.6	579.2	579.2	578.5	577.8	577.1	576.5
175°	582.7	583.4	583.4	582.7	582.0	581.3	580.6
177.5°	584.8	585.3	585.3	584.7	584.1	583.4	582.7
180°	584.2	584.2	584.2	584.2	584.2	584.2	584.2

(END OF REPORT)