

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331948-940

Luminaire Tested: **S123DIP-S560D1195U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331948-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5982.0 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36				
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30				
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	27	22				
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19				
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17				
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15				
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13				
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12				
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	10				
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7587	7587	7587	7587
5°	9048	7621	6753	7621
10°	11326	7582	6099	7582
15°	13891	7520	5678	7520
20°	16549	7425	5407	7425
25°	17570	7310	5346	7310
30°	15060	7225	5374	7225
35°	10474	7104	5430	7104
40°	7888	6962	5413	6962
45°	6550	6753	5345	6753
50°	5868	6325	5297	6325
55°	5485	5864	5230	5864
60°	5147	5382	5175	5382
65°	4834	4905	5010	4905
70°	4535	4365	4771	4365
75°	4059	3818	4375	3818
80°	3552	3137	3769	3137
85°	2791	2285	2532	2285



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	1.2
10°-20°	222.7	3.7
20°-30°	373.7	6.2
30°-40°	423.1	7.1
40°-50°	379.5	6.3
50°-60°	306.2	5.1
60°-70°	213.4	3.6
70°-80°	112.2	1.9
80°-90°	31.4	0.5
90°-100°	284.8	4.8
100°-110°	806.5	13.5
110°-120°	793.4	13.3
120°-130°	632.8	10.6
130°-140°	498.9	8.3
140°-150°	372.4	6.2
150°-160°	259.6	4.3
160°-170°	152.5	2.5
170°-180°	49.6	0.8
0°-30°	665.8	11.1
0°-40°	1088.9	18.2
0°-60°	1774.6	29.7
0°-90°	2131.5	35.6
90°-120°	1884.7	31.5
90°-150°	3388.9	56.7
90°-180°	3851.0	64.4
0°-180°	5982.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	705	705	705	705	705	
5°	837	705	625	705	837	87
15°	1246	675	510	675	1246	360
25°	1479	616	450	616	1479	649
35°	797	541	413	541	797	518
45°	430	444	351	444	430	340
55°	292	312	279	312	292	262
65°	190	193	197	193	190	189
75°	98	92	105	92	98	105
85°	23	18	20	18	23	27
90°	30	2	30	2	30	17
95°	120	35	120	35	120	217
105°	1318	120	1318	120	1318	1300
115°	1603	212	1603	212	1603	1557
125°	1264	295	1264	295	1264	1145
135°	1025	346	1025	346	1025	795
145°	801	395	801	395	801	509
155°	664	449	664	449	664	310
165°	579	490	579	490	579	166
175°	521	511	521	511	521	51
180°	512	512	512	512	512	



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	748.1	747.5	746.2	747.3	745.0	742.1	741.8	739.0	731.1	730.6	728.4
5°	837.4	834.6	834.4	834.0	829.2	822.7	810.4	809.4	793.0	784.8	774.9
7.5°	953.1	954.6	949.6	945.2	930.6	921.0	907.8	890.9	870.8	850.3	836.7
10°	1036.2	1047.4	1033.4	1023.9	1015.0	998.3	978.8	954.6	930.3	902.0	880.5
12.5°	1125.2	1130.8	1128.0	1118.9	1105.2	1079.7	1045.2	1018.5	996.1	949.0	929.9
15°	1246.5	1267.4	1254.1	1223.3	1224.1	1199.8	1154.7	1105.2	1078.9	1037.5	981.1
17.5°	1375.8	1378.4	1372.7	1347.1	1330.0	1296.7	1255.1	1207.6	1154.3	1104.4	1044.6
20°	1444.7	1442.6	1430.7	1417.3	1387.9	1362.0	1316.5	1263.6	1195.3	1146.1	1080.9
22.5°	1482.9	1479.4	1473.8	1462.7	1438.2	1410.3	1369.6	1311.7	1246.7	1178.9	1103.6
25°	1479.4	1483.9	1484.6	1481.5	1473.0	1456.3	1424.2	1378.0	1313.1	1226.1	1147.5
27.5°	1345.6	1351.8	1370.1	1386.3	1404.4	1422.8	1420.4	1397.5	1349.5	1274.3	1178.2
30°	1211.7	1198.0	1231.9	1274.5	1303.6	1354.8	1383.5	1385.2	1358.3	1293.7	1200.1
32.5°	1025.9	1041.0	1055.9	1108.4	1171.9	1229.4	1286.5	1332.5	1337.7	1294.8	1212.9
35°	797.1	815.9	843.2	870.6	938.9	997.6	1098.0	1185.4	1255.1	1264.3	1214.1
37.5°	642.3	651.7	668.9	696.2	740.9	810.7	888.3	998.8	1099.7	1174.8	1178.1
40°	561.4	564.2	583.6	604.5	640.7	698.0	768.1	865.8	986.7	1091.5	1135.2
42.5°	500.8	506.8	515.1	535.1	563.9	607.1	672.2	753.0	863.7	984.4	1069.9
45°	430.3	437.1	442.3	455.6	476.1	505.1	550.5	624.3	708.6	833.3	948.4
47.5°	383.7	384.2	388.1	398.1	412.1	433.9	466.0	513.4	590.8	691.9	810.1
50°	350.4	355.9	357.2	365.1	376.0	392.1	418.7	459.0	522.5	611.4	720.0
52.5°	326.9	328.5	332.3	338.0	347.6	360.1	383.2	414.7	464.6	540.3	640.2
55°	292.3	292.3	296.1	300.5	306.0	317.3	332.6	355.9	393.8	452.5	535.2
57.5°	260.4	262.1	264.7	266.1	270.7	278.2	291.1	308.7	337.0	382.2	447.9
60°	239.1	242.1	241.8	244.5	248.6	254.4	265.4	279.7	305.0	341.2	396.5
62.5°	220.5	220.3	220.3	223.5	227.6	233.1	240.2	252.6	274.1	306.2	353.3
65°	189.8	189.2	191.6	193.7	195.0	199.1	204.6	215.5	229.9	253.8	290.3
67.5°	162.7	160.7	162.0	162.7	165.1	168.3	173.3	180.1	191.5	210.7	238.3
70°	144.1	142.4	142.0	142.8	144.8	147.2	151.0	157.5	168.0	183.4	203.6
72.5°	125.0	123.9	123.8	125.3	126.3	127.8	130.5	136.4	144.8	156.3	175.1
75°	97.6	97.6	97.6	98.0	99.1	100.4	102.5	105.5	112.0	120.2	132.9
77.5°	73.2	73.1	72.8	72.7	74.2	74.8	75.3	78.1	81.8	87.3	96.5
80°	57.3	55.6	56.4	57.3	58.1	58.4	59.4	60.1	63.2	66.3	72.8
82.5°	42.6	41.2	41.3	42.9	43.1	43.3	44.4	45.4	46.5	49.3	52.8
85°	22.6	22.6	22.9	22.9	23.2	22.9	23.9	24.3	24.3	25.9	28.0
87.5°	14.2	13.9	13.9	14.0	13.9	13.8	13.8	13.9	14.0	14.4	14.1
90°	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9	24.9	25.9	22.8
92.5°	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2	120.2	159.3	175.3
95°	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0	498.3	614.4	547.1
97.5°	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7	1018.6	952.1	697.1
100°	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5	1185.3	981.1	663.1
102.5°	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5	1193.5	927.3	613.3
105°	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8	1130.3	832.9	552.2
107.5°	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2	1019.7	749.7	513.3
110°	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3	950.0	702.4	498.3



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2	889.6	670.9	490.1
115°	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1	816.4	637.1	487.0
117.5°	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1	772.2	617.2	488.8
120°	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1	749.0	608.1	492.1
122.5°	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4	730.0	602.4	497.9
125°	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7	705.5	594.7	506.6
127.5°	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0	684.0	590.9	516.6
130°	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6	672.3	588.4	523.2
132.5°	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9	661.6	587.6	528.2
135°	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9	647.6	586.4	535.7
137.5°	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4	635.3	584.1	540.6
140°	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5	627.9	583.3	543.9
142.5°	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5	621.2	581.7	546.4
145°	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4	612.3	579.2	548.0
147.5°	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6	603.6	575.2	548.0
150°	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6	597.8	571.9	548.0
152.5°	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5	591.2	567.8	545.5
155°	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8	581.2	560.5	542.9
157.5°	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3	570.0	554.1	539.4
160°	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0	562.6	549.1	537.7
162.5°	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1	555.1	544.1	534.4
165°	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2	544.9	536.6	529.4
167.5°	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1	535.2	529.2	524.4
170°	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6	529.4	524.2	521.1
172.5°	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0	523.6	520.0	518.6
175°	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1	517.0	514.9	514.9
177.5°	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4	512.6	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	726.7	724.6	722.4	718.5	715.2	710.6	709.3	707.7	702.8	698.3	695.1
5°	771.2	762.9	751.0	740.0	731.2	719.3	712.4	705.3	695.0	685.8	678.2
7.5°	817.6	801.5	782.9	762.9	744.1	726.0	711.5	698.6	684.2	670.6	660.0
10°	854.5	831.3	805.3	777.3	753.4	730.1	710.7	693.7	675.2	659.2	645.8
12.5°	896.5	862.1	826.3	792.3	764.0	731.8	708.3	686.5	665.7	646.3	631.3
15°	946.4	902.7	860.3	813.5	770.4	730.1	702.1	674.8	650.6	630.8	611.6
17.5°	991.7	942.2	886.4	829.5	777.6	729.8	690.5	659.7	629.4	605.1	586.0
20°	1017.4	961.0	897.9	838.7	781.4	728.1	685.1	648.2	615.5	589.8	568.3
22.5°	1039.6	973.6	908.2	845.1	781.1	723.7	675.0	637.0	601.5	576.4	553.6
25°	1062.5	983.6	918.0	843.9	772.5	713.1	658.4	615.5	579.9	550.5	527.0
27.5°	1082.2	982.9	905.1	825.4	759.0	699.5	641.1	594.9	557.2	525.3	501.4
30°	1095.3	984.3	891.7	812.8	745.9	684.4	627.7	581.3	541.6	509.2	486.7
32.5°	1103.5	983.5	879.4	795.3	725.1	670.7	613.2	565.2	524.4	492.6	470.8
35°	1108.2	977.4	858.3	759.2	691.6	638.6	590.5	540.6	497.9	468.2	443.6
37.5°	1098.7	964.8	833.7	724.3	650.3	598.2	557.7	515.2	474.4	441.7	420.4
40°	1083.6	956.6	814.5	699.8	621.9	571.7	537.3	495.5	455.2	424.2	404.4
42.5°	1055.0	940.0	793.5	672.4	592.4	542.2	510.4	475.6	437.5	408.3	388.5
45°	985.0	903.7	762.0	631.5	548.8	497.0	469.0	443.6	409.1	380.8	363.7
47.5°	887.8	849.1	716.3	588.3	503.4	453.4	424.3	403.9	378.7	355.9	339.5
50°	820.4	804.3	685.5	558.7	473.0	424.2	396.2	377.7	359.6	336.7	321.7
52.5°	742.4	752.3	649.3	528.2	442.1	394.1	367.7	353.1	336.7	317.9	304.8
55°	632.8	668.7	587.1	476.8	396.2	350.4	325.5	312.5	302.9	288.9	277.7
57.5°	530.2	575.8	519.7	423.8	351.0	311.6	287.7	273.5	267.3	260.0	251.2
60°	469.2	514.3	471.6	388.3	320.7	283.1	262.0	250.0	243.9	238.7	231.2
62.5°	414.9	460.5	424.6	352.2	290.9	256.1	237.6	226.0	221.1	218.5	212.0
65°	340.2	379.4	355.5	296.1	248.3	217.6	200.8	192.6	188.2	187.2	183.1
67.5°	276.9	306.7	289.4	245.6	207.9	181.4	167.2	160.2	156.9	156.5	153.4
70°	235.3	263.3	250.0	210.4	177.9	157.1	144.8	138.7	136.6	136.3	134.6
72.5°	203.0	222.6	212.0	179.0	153.9	135.0	125.9	119.5	117.2	117.7	116.5
75°	150.3	165.0	158.8	135.9	115.7	103.4	95.9	91.8	89.8	90.9	89.4
77.5°	108.2	117.4	111.9	96.0	83.6	74.7	69.2	66.7	64.8	64.7	64.1
80°	81.6	87.1	84.0	74.5	64.2	56.7	52.3	50.6	49.5	49.2	48.9
82.5°	58.1	62.8	59.1	52.6	45.7	41.1	38.6	36.4	35.6	35.8	35.5
85°	29.3	31.1	29.7	25.6	22.9	20.9	19.4	18.5	17.7	18.1	17.4
87.5°	14.1	13.7	12.2	10.8	9.8	8.4	7.9	7.0	6.9	7.2	7.6
90°	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1	4.1	6.2	9.4
92.5°	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8	19.1	27.7	35.8
95°	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2	38.3	49.8	67.3
97.5°	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1	61.1	70.0	85.3
100°	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7	77.7	85.0	99.4
102.5°	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1	95.9	102.4	116.0
105°	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2	123.3	129.5	142.0
107.5°	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9	151.1	157.0	169.2
110°	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8	170.9	176.1	187.5



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1	189.2	194.4	205.7
115°	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4	216.5	222.7	233.1
117.5°	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7	243.4	248.6	258.2
120°	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9	260.0	265.2	275.6
122.5°	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7	275.8	281.0	292.1
125°	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2	297.4	303.5	315.0
127.5°	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5	315.6	323.2	334.8
130°	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2	326.4	335.6	348.1
132.5°	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5	335.5	345.6	360.5
135°	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1	350.2	361.6	377.1
137.5°	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7	364.1	375.2	391.8
140°	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8	374.0	384.3	400.9
142.5°	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8	383.2	394.3	409.2
145°	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8	397.8	407.2	422.7
147.5°	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9	412.8	421.9	435.3
150°	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7	422.7	431.0	444.4
152.5°	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5	432.7	441.0	452.7
155°	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6	448.6	454.9	465.2
157.5°	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5	462.3	467.3	476.4
160°	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4	471.4	475.5	483.8
162.5°	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8	478.8	482.1	488.8
165°	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1	489.0	491.1	496.2
167.5°	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6	497.3	498.3	502.3
170°	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5	501.4	502.5	505.6
172.5°	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8	505.6	505.8	508.1
175°	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8	509.7	508.7	510.8
177.5°	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6	511.8	511.0	511.8
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	693.1	691.3	688.5	684.4	681.1	675.9	675.9	676.7	676.7	676.5	675.9
5°	672.1	667.0	660.8	653.7	646.1	638.6	637.3	634.5	632.5	631.2	629.5
7.5°	649.9	640.9	631.9	621.9	612.7	605.1	599.9	595.5	592.6	589.7	587.5
10°	634.9	623.6	613.1	602.4	590.8	581.6	575.8	571.7	568.6	565.9	564.5
12.5°	617.2	604.2	592.5	582.5	569.8	560.3	554.7	552.9	549.2	543.5	540.5
15°	591.2	579.3	565.3	549.8	543.7	532.1	525.6	522.5	520.5	516.0	514.7
17.5°	569.0	553.3	537.6	526.1	514.7	505.3	501.7	497.8	495.2	491.5	490.4
20°	551.3	537.3	522.9	510.6	498.6	488.4	485.3	482.6	479.8	478.1	476.8
22.5°	533.2	519.2	507.3	495.8	483.0	476.4	473.0	470.0	468.1	466.9	465.6
25°	507.8	495.5	482.2	472.0	461.7	457.3	455.2	453.5	452.2	450.5	450.1
27.5°	485.2	471.8	461.0	451.4	444.1	440.3	438.4	437.6	437.8	438.5	438.8
30°	468.2	455.9	447.0	438.8	432.0	428.6	428.3	428.3	429.6	430.0	430.7
32.5°	452.6	442.6	433.6	425.7	420.5	418.2	419.5	419.5	420.6	421.5	422.8
35°	430.0	421.1	414.3	407.4	403.0	404.0	404.7	405.4	407.1	409.1	410.5
37.5°	408.3	400.6	393.5	388.2	386.1	388.0	389.6	391.0	393.1	394.6	395.9
40°	392.7	386.9	380.1	375.3	376.0	377.0	378.4	380.1	381.8	382.8	384.2
42.5°	378.3	372.2	367.0	363.0	364.0	365.3	366.1	367.0	369.0	370.9	371.7
45°	356.2	351.4	346.6	344.3	344.9	345.6	346.3	347.3	349.0	350.4	350.7
47.5°	331.4	328.1	324.9	322.5	323.6	323.3	324.2	326.5	327.0	327.8	329.7
50°	315.6	312.5	308.7	308.1	308.1	308.1	308.4	311.1	311.1	312.5	313.9
52.5°	298.1	296.1	293.7	292.5	291.9	291.9	293.4	294.7	295.2	297.2	298.5
55°	272.2	270.1	268.1	267.1	266.4	267.1	269.8	270.5	272.2	273.2	274.2
57.5°	245.2	243.6	242.0	241.5	241.3	242.2	243.7	245.8	246.2	249.3	250.8
60°	227.5	225.1	223.7	223.7	223.0	226.0	225.4	228.8	229.5	231.6	234.0
62.5°	209.1	205.9	205.4	205.4	206.3	207.2	208.2	209.7	211.5	214.1	215.9
65°	179.7	177.9	180.3	179.9	179.3	181.4	181.4	183.1	185.1	187.5	191.3
67.5°	151.7	150.8	151.1	151.1	152.0	153.2	154.2	155.7	158.1	160.7	163.1
70°	132.9	133.8	132.2	133.6	134.6	134.9	135.5	137.6	140.4	142.0	144.8
72.5°	114.6	114.5	114.7	115.2	116.3	116.9	117.5	119.8	122.9	124.3	126.5
75°	88.1	87.7	88.8	88.8	90.5	91.2	91.8	92.9	95.6	97.6	99.4
77.5°	64.4	64.7	64.6	65.7	65.3	65.4	67.5	68.5	68.8	72.9	73.7
80°	48.5	49.2	49.5	49.8	50.2	49.5	51.9	53.0	53.0	55.3	57.1
82.5°	34.9	35.2	36.1	36.5	36.6	37.2	37.5	38.2	39.0	40.0	42.3
85°	17.4	18.5	18.8	18.5	18.8	18.1	19.1	19.4	19.8	19.8	19.8
87.5°	7.8	8.5	8.7	9.6	10.0	10.9	10.7	10.3	10.6	11.6	11.0
90°	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9	26.9	28.0	30.1
92.5°	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2	69.2	61.1	55.7
95°	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0	252.8	197.9	160.6
97.5°	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7	744.7	611.1	487.1
100°	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5	1137.6	1016.4	869.2
102.5°	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5	1315.7	1245.1	1151.8
105°	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8	1450.5	1470.2	1443.2
107.5°	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2	1433.4	1524.2	1561.1
110°	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3	1378.0	1508.5	1581.0



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2	1305.0	1451.3	1544.5
115°	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1	1188.3	1340.6	1453.6
117.5°	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1	1089.7	1226.5	1341.0
120°	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1	1035.0	1159.3	1264.0
122.5°	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4	991.0	1106.3	1203.5
125°	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7	936.6	1036.0	1118.9
127.5°	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0	888.7	978.4	1053.8
130°	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6	858.9	942.8	1013.3
132.5°	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9	830.7	908.8	976.0
135°	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9	790.5	857.8	916.9
137.5°	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4	751.7	809.8	860.9
140°	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5	729.3	779.1	823.7
142.5°	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5	707.8	750.9	789.7
145°	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4	679.7	712.8	742.8
147.5°	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6	658.7	685.5	706.8
150°	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6	645.4	667.2	686.9
152.5°	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5	633.0	652.3	668.7
155°	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8	615.4	631.0	643.4
157.5°	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3	598.2	610.2	619.9
160°	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0	587.5	597.8	605.0
162.5°	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1	575.9	585.3	591.7
165°	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2	559.5	566.7	571.9
167.5°	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1	546.8	551.0	554.7
170°	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6	537.7	541.8	543.9
172.5°	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0	530.2	533.6	534.8
175°	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1	520.0	522.2	522.2
177.5°	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4	514.2	515.1	515.1
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	674.0	673.8	675.6	674.3	675.6	673.8	674.0	675.9	676.5	676.7	676.7
5°	627.4	628.4	625.0	625.0	625.0	628.4	627.4	629.5	631.2	632.5	634.5
7.5°	585.9	584.3	584.5	582.6	584.5	584.3	585.9	587.5	589.7	592.6	595.5
10°	560.4	558.4	557.7	558.0	557.7	558.4	560.4	564.5	565.9	568.6	571.7
12.5°	539.4	539.0	534.5	534.6	534.5	539.0	539.4	540.5	543.5	549.2	552.9
15°	514.7	508.2	507.5	509.5	507.5	508.2	514.7	514.7	516.0	520.5	522.5
17.5°	489.9	486.4	486.7	485.6	486.7	486.4	489.9	490.4	491.5	495.2	497.8
20°	476.8	474.7	474.4	472.0	474.4	474.7	476.8	476.8	478.1	479.8	482.6
22.5°	464.8	464.0	464.2	461.6	464.2	464.0	464.8	465.6	466.9	468.1	470.0
25°	449.8	451.5	450.1	450.1	450.1	451.5	449.8	450.1	450.5	452.2	453.5
27.5°	439.7	439.6	438.9	438.9	438.9	439.6	439.7	438.8	438.5	437.8	437.6
30°	432.0	431.7	432.4	432.4	432.4	431.7	432.0	430.7	430.0	429.6	428.3
32.5°	424.4	424.8	425.0	425.3	425.0	424.8	424.4	422.8	421.5	420.6	419.5
35°	412.6	412.9	413.9	413.2	413.9	412.9	412.6	410.5	409.1	407.1	405.4
37.5°	396.5	398.1	397.8	398.3	397.8	398.1	396.5	395.9	394.6	393.1	391.0
40°	384.6	385.6	385.2	385.2	385.2	385.6	384.6	384.2	382.8	381.8	380.1
42.5°	372.3	373.0	372.1	371.6	372.1	373.0	372.3	371.7	370.9	369.0	367.0
45°	352.1	351.4	352.5	351.1	352.5	351.4	352.1	350.7	350.4	349.0	347.3
47.5°	329.6	330.3	330.6	331.5	330.6	330.3	329.6	329.7	327.8	327.0	326.5
50°	314.5	316.6	316.6	316.3	316.6	316.6	314.5	313.9	312.5	311.1	311.1
52.5°	299.8	300.8	302.1	302.0	302.1	300.8	299.8	298.5	297.2	295.2	294.7
55°	277.0	277.7	278.3	278.7	278.3	277.7	277.0	274.2	273.2	272.2	270.5
57.5°	253.3	253.1	254.7	255.2	254.7	253.1	253.3	250.8	249.3	246.2	245.8
60°	236.7	236.7	239.4	240.4	239.4	236.7	236.7	234.0	231.6	229.5	228.8
62.5°	218.9	220.0	222.7	221.3	222.7	220.0	218.9	215.9	214.1	211.5	209.7
65°	193.0	195.7	195.4	196.7	195.4	195.7	193.0	191.3	187.5	185.1	183.1
67.5°	165.9	167.6	170.0	170.2	170.0	167.6	165.9	163.1	160.7	158.1	155.7
70°	147.6	149.3	150.6	151.6	150.6	149.3	147.6	144.8	142.0	140.4	137.6
72.5°	129.7	130.6	133.9	132.5	133.9	130.6	129.7	126.5	124.3	122.9	119.8
75°	101.7	104.2	106.2	105.2	106.2	104.2	101.7	99.4	97.6	95.6	92.9
77.5°	75.3	77.7	78.6	77.8	78.6	77.7	75.3	73.7	72.9	68.8	68.5
80°	59.4	59.1	61.2	60.8	61.2	59.1	59.4	57.1	55.3	53.0	53.0
82.5°	43.6	43.2	44.2	44.4	44.2	43.2	43.6	42.3	40.0	39.0	38.2
85°	21.1	22.2	20.9	20.5	20.9	22.2	21.1	19.8	19.8	19.8	19.4
87.5°	10.7	11.0	10.9	10.3	10.9	11.0	10.7	11.0	11.6	10.6	10.3
90°	29.0	30.1	31.1	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9
92.5°	53.9	50.7	51.8	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2
95°	140.9	131.6	124.3	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0
97.5°	410.7	364.1	336.1	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7
100°	764.6	688.9	648.5	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5
102.5°	1070.4	1010.6	976.8	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5
105°	1395.5	1356.2	1323.0	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8
107.5°	1561.9	1548.6	1537.5	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2
110°	1610.0	1618.3	1616.2	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1597.6	1623.3	1631.1	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2
115°	1531.2	1576.8	1597.6	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1
117.5°	1422.1	1474.3	1504.1	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1
120°	1345.8	1403.8	1428.7	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1
122.5°	1276.2	1328.4	1355.8	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4
125°	1185.3	1230.8	1256.7	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7
127.5°	1112.9	1151.8	1175.3	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0
130°	1068.2	1105.5	1127.2	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6
132.5°	1027.5	1064.8	1084.1	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9
135°	967.7	998.7	1017.4	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9
137.5°	903.7	935.1	950.8	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4
140°	863.0	892.1	908.6	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5
142.5°	823.2	848.9	863.8	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5
145°	768.7	790.5	798.8	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4
147.5°	726.5	741.2	749.0	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6
150°	702.4	713.8	720.1	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6
152.5°	680.9	691.4	695.2	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5
155°	652.7	661.0	663.1	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8
157.5°	628.0	634.3	635.9	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3
160°	612.3	618.5	618.5	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0
162.5°	596.6	601.9	601.9	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1
165°	576.0	580.1	579.2	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2
167.5°	556.5	559.5	558.4	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1
170°	544.9	547.1	546.0	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6
172.5°	535.0	537.1	535.2	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0
175°	522.2	523.2	522.2	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1
177.5°	514.2	515.1	513.4	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	675.9	675.9	681.1	684.4	688.5	691.3	693.1	695.1	698.3	702.8	707.7
5°	637.3	638.6	646.1	653.7	660.8	667.0	672.1	678.2	685.8	695.0	705.3
7.5°	599.9	605.1	612.7	621.9	631.9	640.9	649.9	660.0	670.6	684.2	698.6
10°	575.8	581.6	590.8	602.4	613.1	623.6	634.9	645.8	659.2	675.2	693.7
12.5°	554.7	560.3	569.8	582.5	592.5	604.2	617.2	631.3	646.3	665.7	686.5
15°	525.6	532.1	543.7	549.8	565.3	579.3	591.2	611.6	630.8	650.6	674.8
17.5°	501.7	505.3	514.7	526.1	537.6	553.3	569.0	586.0	605.1	629.4	659.7
20°	485.3	488.4	498.6	510.6	522.9	537.3	551.3	568.3	589.8	615.5	648.2
22.5°	473.0	476.4	483.0	495.8	507.3	519.2	533.2	553.6	576.4	601.5	637.0
25°	455.2	457.3	461.7	472.0	482.2	495.5	507.8	527.0	550.5	579.9	615.5
27.5°	438.4	440.3	444.1	451.4	461.0	471.8	485.2	501.4	525.3	557.2	594.9
30°	428.3	428.6	432.0	438.8	447.0	455.9	468.2	486.7	509.2	541.6	581.3
32.5°	419.5	418.2	420.5	425.7	433.6	442.6	452.6	470.8	492.6	524.4	565.2
35°	404.7	404.0	403.0	407.4	414.3	421.1	430.0	443.6	468.2	497.9	540.6
37.5°	389.6	388.0	386.1	388.2	393.5	400.6	408.3	420.4	441.7	474.4	515.2
40°	378.4	377.0	376.0	375.3	380.1	386.9	392.7	404.4	424.2	455.2	495.5
42.5°	366.1	365.3	364.0	363.0	367.0	372.2	378.3	388.5	408.3	437.5	475.6
45°	346.3	345.6	344.9	344.3	346.6	351.4	356.2	363.7	380.8	409.1	443.6
47.5°	324.2	323.3	323.6	322.5	324.9	328.1	331.4	339.5	355.9	378.7	403.9
50°	308.4	308.1	308.1	308.1	308.7	312.5	315.6	321.7	336.7	359.6	377.7
52.5°	293.4	291.9	291.9	292.5	293.7	296.1	298.1	304.8	317.9	336.7	353.1
55°	269.8	267.1	266.4	267.1	268.1	270.1	272.2	277.7	288.9	302.9	312.5
57.5°	243.7	242.2	241.3	241.5	242.0	243.6	245.2	251.2	260.0	267.3	273.5
60°	225.4	226.0	223.0	223.7	223.7	225.1	227.5	231.2	238.7	243.9	250.0
62.5°	208.2	207.2	206.3	205.4	205.4	205.9	209.1	212.0	218.5	221.1	226.0
65°	181.4	181.4	179.3	179.9	180.3	177.9	179.7	183.1	187.2	188.2	192.6
67.5°	154.2	153.2	152.0	151.1	151.1	150.8	151.7	153.4	156.5	156.9	160.2
70°	135.5	134.9	134.6	133.6	132.2	133.8	132.9	134.6	136.3	136.6	138.7
72.5°	117.5	116.9	116.3	115.2	114.7	114.5	114.6	116.5	117.7	117.2	119.5
75°	91.8	91.2	90.5	88.8	88.8	87.7	88.1	89.4	90.9	89.8	91.8
77.5°	67.5	65.4	65.3	65.7	64.6	64.7	64.4	64.1	64.7	64.8	66.7
80°	51.9	49.5	50.2	49.8	49.5	49.2	48.5	48.9	49.2	49.5	50.6
82.5°	37.5	37.2	36.6	36.5	36.1	35.2	34.9	35.5	35.8	35.6	36.4
85°	19.1	18.1	18.8	18.5	18.8	18.5	17.4	17.4	18.1	17.7	18.5
87.5°	10.7	10.9	10.0	9.6	8.7	8.5	7.8	7.6	7.2	6.9	7.0
90°	24.9	25.9	22.8	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1
92.5°	120.2	159.3	175.3	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8
95°	498.3	614.4	547.1	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2
97.5°	1018.6	952.1	697.1	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1
100°	1185.3	981.1	663.1	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7
102.5°	1193.5	927.3	613.3	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1
105°	1130.3	832.9	552.2	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2
107.5°	1019.7	749.7	513.3	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9
110°	950.0	702.4	498.3	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	889.6	670.9	490.1	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1
115°	816.4	637.1	487.0	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4
117.5°	772.2	617.2	488.8	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7
120°	749.0	608.1	492.1	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9
122.5°	730.0	602.4	497.9	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7
125°	705.5	594.7	506.6	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2
127.5°	684.0	590.9	516.6	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5
130°	672.3	588.4	523.2	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2
132.5°	661.6	587.6	528.2	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5
135°	647.6	586.4	535.7	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1
137.5°	635.3	584.1	540.6	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7
140°	627.9	583.3	543.9	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8
142.5°	621.2	581.7	546.4	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8
145°	612.3	579.2	548.0	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8
147.5°	603.6	575.2	548.0	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9
150°	597.8	571.9	548.0	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7
152.5°	591.2	567.8	545.5	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5
155°	581.2	560.5	542.9	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6
157.5°	570.0	554.1	539.4	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5
160°	562.6	549.1	537.7	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4
162.5°	555.1	544.1	534.4	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8
165°	544.9	536.6	529.4	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1
167.5°	535.2	529.2	524.4	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6
170°	529.4	524.2	521.1	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5
172.5°	523.6	520.0	518.6	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8
175°	517.0	514.9	514.9	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8
177.5°	512.6	511.8	512.6	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	709.3	710.6	715.2	718.5	722.4	724.6	726.7	728.4	730.6	731.1	739.0
5°	712.4	719.3	731.2	740.0	751.0	762.9	771.2	774.9	784.8	793.0	809.4
7.5°	711.5	726.0	744.1	762.9	782.9	801.5	817.6	836.7	850.3	870.8	890.9
10°	710.7	730.1	753.4	777.3	805.3	831.3	854.5	880.5	902.0	930.3	954.6
12.5°	708.3	731.8	764.0	792.3	826.3	862.1	896.5	929.9	949.0	996.1	1018.5
15°	702.1	730.1	770.4	813.5	860.3	902.7	946.4	981.1	1037.5	1078.9	1105.2
17.5°	690.5	729.8	777.6	829.5	886.4	942.2	991.7	1044.6	1104.4	1154.3	1207.6
20°	685.1	728.1	781.4	838.7	897.9	961.0	1017.4	1080.9	1146.1	1195.3	1263.6
22.5°	675.0	723.7	781.1	845.1	908.2	973.6	1039.6	1103.6	1178.9	1246.7	1311.7
25°	658.4	713.1	772.5	843.9	918.0	983.6	1062.5	1147.5	1226.1	1313.1	1378.0
27.5°	641.1	699.5	759.0	825.4	905.1	982.9	1082.2	1178.2	1274.3	1349.5	1397.5
30°	627.7	684.4	745.9	812.8	891.7	984.3	1095.3	1200.1	1293.7	1358.3	1385.2
32.5°	613.2	670.7	725.1	795.3	879.4	983.5	1103.5	1212.9	1294.8	1337.7	1332.5
35°	590.5	638.6	691.6	759.2	858.3	977.4	1108.2	1214.1	1264.3	1255.1	1185.4
37.5°	557.7	598.2	650.3	724.3	833.7	964.8	1098.7	1178.1	1174.8	1099.7	998.8
40°	537.3	571.7	621.9	699.8	814.5	956.6	1083.6	1135.2	1091.5	986.7	865.8
42.5°	510.4	542.2	592.4	672.4	793.5	940.0	1055.0	1069.9	984.4	863.7	753.0
45°	469.0	497.0	548.8	631.5	762.0	903.7	985.0	948.4	833.3	708.6	624.3
47.5°	424.3	453.4	503.4	588.3	716.3	849.1	887.8	810.1	691.9	590.8	513.4
50°	396.2	424.2	473.0	558.7	685.5	804.3	820.4	720.0	611.4	522.5	459.0
52.5°	367.7	394.1	442.1	528.2	649.3	752.3	742.4	640.2	540.3	464.6	414.7
55°	325.5	350.4	396.2	476.8	587.1	668.7	632.8	535.2	452.5	393.8	355.9
57.5°	287.7	311.6	351.0	423.8	519.7	575.8	530.2	447.9	382.2	337.0	308.7
60°	262.0	283.1	320.7	388.3	471.6	514.3	469.2	396.5	341.2	305.0	279.7
62.5°	237.6	256.1	290.9	352.2	424.6	460.5	414.9	353.3	306.2	274.1	252.6
65°	200.8	217.6	248.3	296.1	355.5	379.4	340.2	290.3	253.8	229.9	215.5
67.5°	167.2	181.4	207.9	245.6	289.4	306.7	276.9	238.3	210.7	191.5	180.1
70°	144.8	157.1	177.9	210.4	250.0	263.3	235.3	203.6	183.4	168.0	157.5
72.5°	125.9	135.0	153.9	179.0	212.0	222.6	203.0	175.1	156.3	144.8	136.4
75°	95.9	103.4	115.7	135.9	158.8	165.0	150.3	132.9	120.2	112.0	105.5
77.5°	69.2	74.7	83.6	96.0	111.9	117.4	108.2	96.5	87.3	81.8	78.1
80°	52.3	56.7	64.2	74.5	84.0	87.1	81.6	72.8	66.3	63.2	60.1
82.5°	38.6	41.1	45.7	52.6	59.1	62.8	58.1	52.8	49.3	46.5	45.4
85°	19.4	20.9	22.9	25.6	29.7	31.1	29.3	28.0	25.9	24.3	24.3
87.5°	7.9	8.4	9.8	10.8	12.2	13.7	14.1	14.1	14.4	14.0	13.9
90°	4.1	6.2	9.4	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9
92.5°	19.1	27.7	35.8	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2
95°	38.3	49.8	67.3	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0
97.5°	61.1	70.0	85.3	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7
100°	77.7	85.0	99.4	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5
102.5°	95.9	102.4	116.0	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5
105°	123.3	129.5	142.0	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8
107.5°	151.1	157.0	169.2	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2
110°	170.9	176.1	187.5	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.2	194.4	205.7	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2
115°	216.5	222.7	233.1	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1
117.5°	243.4	248.6	258.2	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1
120°	260.0	265.2	275.6	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1
122.5°	275.8	281.0	292.1	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4
125°	297.4	303.5	315.0	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7
127.5°	315.6	323.2	334.8	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0
130°	326.4	335.6	348.1	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6
132.5°	335.5	345.6	360.5	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9
135°	350.2	361.6	377.1	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9
137.5°	364.1	375.2	391.8	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4
140°	374.0	384.3	400.9	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5
142.5°	383.2	394.3	409.2	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5
145°	397.8	407.2	422.7	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4
147.5°	412.8	421.9	435.3	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6
150°	422.7	431.0	444.4	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6
152.5°	432.7	441.0	452.7	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5
155°	448.6	454.9	465.2	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8
157.5°	462.3	467.3	476.4	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3
160°	471.4	475.5	483.8	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0
162.5°	478.8	482.1	488.8	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1
165°	489.0	491.1	496.2	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2
167.5°	497.3	498.3	502.3	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1
170°	501.4	502.5	505.6	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6
172.5°	505.6	505.8	508.1	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0
175°	509.7	508.7	510.8	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1
177.5°	511.8	511.0	511.8	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	741.8	742.1	745.0	747.3	746.2	747.5	748.1
5°	810.4	822.7	829.2	834.0	834.4	834.6	837.4
7.5°	907.8	921.0	930.6	945.2	949.6	954.6	953.1
10°	978.8	998.3	1015.0	1023.9	1033.4	1047.4	1036.2
12.5°	1045.2	1079.7	1105.2	1118.9	1128.0	1130.8	1125.2
15°	1154.7	1199.8	1224.1	1223.3	1254.1	1267.4	1246.5
17.5°	1255.1	1296.7	1330.0	1347.1	1372.7	1378.4	1375.8
20°	1316.5	1362.0	1387.9	1417.3	1430.7	1442.6	1444.7
22.5°	1369.6	1410.3	1438.2	1462.7	1473.8	1479.4	1482.9
25°	1424.2	1456.3	1473.0	1481.5	1484.6	1483.9	1479.4
27.5°	1420.4	1422.8	1404.4	1386.3	1370.1	1351.8	1345.6
30°	1383.5	1354.8	1303.6	1274.5	1231.9	1198.0	1211.7
32.5°	1286.5	1229.4	1171.9	1108.4	1055.9	1041.0	1025.9
35°	1098.0	997.6	938.9	870.6	843.2	815.9	797.1
37.5°	888.3	810.7	740.9	696.2	668.9	651.7	642.3
40°	768.1	698.0	640.7	604.5	583.6	564.2	561.4
42.5°	672.2	607.1	563.9	535.1	515.1	506.8	500.8
45°	550.5	505.1	476.1	455.6	442.3	437.1	430.3
47.5°	466.0	433.9	412.1	398.1	388.1	384.2	383.7
50°	418.7	392.1	376.0	365.1	357.2	355.9	350.4
52.5°	383.2	360.1	347.6	338.0	332.3	328.5	326.9
55°	332.6	317.3	306.0	300.5	296.1	292.3	292.3
57.5°	291.1	278.2	270.7	266.1	264.7	262.1	260.4
60°	265.4	254.4	248.6	244.5	241.8	242.1	239.1
62.5°	240.2	233.1	227.6	223.5	220.3	220.3	220.5
65°	204.6	199.1	195.0	193.7	191.6	189.2	189.8
67.5°	173.3	168.3	165.1	162.7	162.0	160.7	162.7
70°	151.0	147.2	144.8	142.8	142.0	142.4	144.1
72.5°	130.5	127.8	126.3	125.3	123.8	123.9	125.0
75°	102.5	100.4	99.1	98.0	97.6	97.6	97.6
77.5°	75.3	74.8	74.2	72.7	72.8	73.1	73.2
80°	59.4	58.4	58.1	57.3	56.4	55.6	57.3
82.5°	44.4	43.3	43.1	42.9	41.3	41.2	42.6
85°	23.9	22.9	23.2	22.9	22.9	22.6	22.6
87.5°	13.8	13.8	13.9	14.0	13.9	13.9	14.2
90°	26.9	28.0	30.1	29.0	30.1	31.1	30.1
92.5°	69.2	61.1	55.7	53.9	50.7	51.8	49.9
95°	252.8	197.9	160.6	140.9	131.6	124.3	120.2
97.5°	744.7	611.1	487.1	410.7	364.1	336.1	327.2
100°	1137.6	1016.4	869.2	764.6	688.9	648.5	649.6
102.5°	1315.7	1245.1	1151.8	1070.4	1010.6	976.8	953.0
105°	1450.5	1470.2	1443.2	1395.5	1356.2	1323.0	1317.9
107.5°	1433.4	1524.2	1561.1	1561.9	1548.6	1537.5	1527.9
110°	1378.0	1508.5	1581.0	1610.0	1618.3	1616.2	1614.2



TEST NUMBER: P331948-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1305.0	1451.3	1544.5	1597.6	1623.3	1631.1	1631.6
115°	1188.3	1340.6	1453.6	1531.2	1576.8	1597.6	1602.8
117.5°	1089.7	1226.5	1341.0	1422.1	1474.3	1504.1	1511.2
120°	1035.0	1159.3	1264.0	1345.8	1403.8	1428.7	1434.9
122.5°	991.0	1106.3	1203.5	1276.2	1328.4	1355.8	1363.6
125°	936.6	1036.0	1118.9	1185.3	1230.8	1256.7	1264.0
127.5°	888.7	978.4	1053.8	1112.9	1151.8	1175.3	1181.9
130°	858.9	942.8	1013.3	1068.2	1105.5	1127.2	1135.5
132.5°	830.7	908.8	976.0	1027.5	1064.8	1084.1	1089.9
135°	790.5	857.8	916.9	967.7	998.7	1017.4	1024.7
137.5°	751.7	809.8	860.9	903.7	935.1	950.8	955.6
140°	729.3	779.1	823.7	863.0	892.1	908.6	907.6
142.5°	707.8	750.9	789.7	823.2	848.9	863.8	862.8
145°	679.7	712.8	742.8	768.7	790.5	798.8	800.8
147.5°	658.7	685.5	706.8	726.5	741.2	749.0	749.8
150°	645.4	667.2	686.9	702.4	713.8	720.1	720.1
152.5°	633.0	652.3	668.7	680.9	691.4	695.2	695.2
155°	615.4	631.0	643.4	652.7	661.0	663.1	664.1
157.5°	598.2	610.2	619.9	628.0	634.3	635.9	635.7
160°	587.5	597.8	605.0	612.3	618.5	618.5	617.5
162.5°	575.9	585.3	591.7	596.6	601.9	601.9	600.9
165°	559.5	566.7	571.9	576.0	580.1	579.2	579.2
167.5°	546.8	551.0	554.7	556.5	559.5	558.4	558.4
170°	537.7	541.8	543.9	544.9	547.1	546.0	546.0
172.5°	530.2	533.6	534.8	535.0	537.1	535.2	534.4
175°	520.0	522.2	522.2	522.2	523.2	522.2	521.1
177.5°	514.2	515.1	515.1	514.2	515.1	513.4	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8

(END OF REPORT)