

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332606-927

Luminaire Tested: **S124DIP-S795D810U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332606-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S795D810U927-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4993.3 lumens  
Efficiency: N/A  
Efficacy: 108.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332606-927

CATALOG NUMBER: S124DIP-S795D810U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332606-927

CATALOG NUMBER: S124DIP-S795D810U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	52	50	45
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	38	36	32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8490	8490	8490
5°	8515	8413	8474
10°	8461	8344	8385
15°	8359	8226	8247
20°	8223	8079	8086
25°	8068	7911	7888
30°	7879	7713	7643
35°	7681	7508	7407
40°	7477	7273	7140
45°	7263	7042	6907
50°	7027	6836	6625
55°	6773	6570	6356
60°	6516	6273	6082
65°	6229	5989	5746
70°	5908	5611	5391
75°	5415	5153	5022
80°	4816	4621	4505
85°	4215	4057	3974



TEST NUMBER: P332606-927

CATALOG NUMBER: S124DIP-S795D810U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.0	2.0
10°-20°	279.0	5.6
20°-30°	410.7	8.2
30°-40°	477.4	9.6
40°-50°	477.5	9.6
50°-60°	417.6	8.4
60°-70°	310.2	6.2
70°-80°	176.2	3.5
80°-90°	52.6	1.1
90°-100°	227.7	4.6
100°-110°	474.0	9.5
110°-120°	424.5	8.5
120°-130°	357.1	7.2
130°-140°	297.7	6.0
140°-150°	227.5	4.6
150°-160°	159.9	3.2
160°-170°	94.0	1.9
170°-180°	30.6	0.6
0°-30°	788.7	15.8
0°-40°	1266.2	25.4
0°-60°	2161.3	43.3
0°-90°	2700.3	54.1
90°-120°	1126.2	22.6
90°-150°	2008.5	40.2
90°-180°	2293.0	45.9
0°-180°	4993.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1052	1052	1052	1052	1052	
5°	1051	1047	1038	1047	1046	100
15°	1000	996	984	989	987	282
25°	906	900	888	889	886	417
35°	779	773	762	756	752	487
45°	636	630	617	608	605	490
55°	481	478	467	457	452	431
65°	326	322	314	305	301	323
75°	174	169	165	162	161	184
85°	46	45	44	44	43	50
90°	1	5	11	12	13	4
95°	20	64	505	250	151	23
105°	72	105	406	875	872	77
115°	128	160	362	696	837	127
125°	178	211	360	592	668	158
135°	211	251	357	526	597	163
145°	243	279	356	444	488	153
155°	277	299	346	392	408	128
165°	302	311	331	351	356	85
175°	315	315	318	322	321	30
180°	315	315	315	315	315	



TEST NUMBER: P332606-927

CATALOG NUMBER: S124DIP-S795D810U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1054.3	1053.8	1053.4	1053.0	1052.5	1051.5	1049.8	1048.1	1046.5	1044.9	1046.3
5°	1050.8	1050.0	1049.2	1048.5	1047.7	1046.3	1044.3	1042.2	1040.1	1038.1	1040.1
7.5°	1041.0	1040.2	1039.5	1038.7	1038.0	1036.5	1034.2	1031.9	1029.6	1027.3	1029.0
10°	1032.2	1031.5	1030.7	1030.0	1029.2	1027.6	1025.2	1022.8	1020.3	1017.9	1019.4
12.5°	1020.7	1020.0	1019.2	1018.5	1017.8	1016.1	1013.5	1010.9	1008.4	1005.8	1007.4
15°	1000.2	999.4	998.7	997.9	997.2	995.5	992.6	989.8	987.0	984.2	985.3
17.5°	975.4	974.5	973.5	972.6	971.7	969.9	967.3	964.6	961.9	959.3	960.0
20°	957.2	956.2	955.4	954.4	953.5	951.6	948.8	945.9	943.2	940.4	941.0
22.5°	937.7	936.4	935.2	934.0	932.7	930.7	927.9	925.1	922.3	919.5	920.5
25°	905.8	904.5	903.2	901.9	900.6	898.6	896.0	893.3	890.7	888.1	888.3
27.5°	869.4	868.1	866.7	865.4	864.0	862.1	859.7	857.3	854.8	852.4	851.9
30°	845.2	843.7	842.2	840.7	839.2	837.2	834.7	832.3	829.9	827.4	826.7
32.5°	819.5	818.2	816.8	815.5	814.1	812.1	809.6	807.0	804.5	801.8	801.0
35°	779.4	778.1	776.8	775.5	774.2	772.2	769.6	767.0	764.4	761.8	760.4
37.5°	737.1	735.9	734.7	733.6	732.3	730.3	727.5	724.7	721.9	719.1	717.6
40°	709.5	708.0	706.5	705.0	703.5	701.3	698.5	695.7	692.9	690.1	688.2
42.5°	679.9	678.9	678.0	677.2	676.2	674.2	671.1	668.0	664.9	661.8	659.7
45°	636.2	634.9	633.6	632.2	631.0	628.8	625.8	622.8	619.8	616.8	614.7
47.5°	590.5	589.6	588.7	587.8	586.9	585.1	582.3	579.6	576.8	574.0	571.6
50°	559.5	558.7	558.0	557.2	556.5	554.8	552.2	549.6	546.9	544.3	541.7
52.5°	529.2	528.3	527.4	526.5	525.5	523.7	520.9	518.2	515.4	512.6	510.3
55°	481.2	480.5	480.0	479.4	478.9	477.3	474.7	472.1	469.4	466.8	464.5
57.5°	435.3	434.7	434.0	433.4	432.8	431.1	428.6	426.0	423.4	420.8	418.7
60°	403.6	402.7	401.7	400.8	399.9	398.2	395.8	393.3	390.9	388.5	386.7
62.5°	372.6	371.9	371.1	370.3	369.5	367.8	365.2	362.6	360.0	357.4	355.9
65°	326.1	325.2	324.2	323.3	322.3	320.9	319.1	317.2	315.3	313.5	311.6
67.5°	279.2	278.4	277.5	276.6	275.8	274.5	272.7	270.8	269.1	267.3	265.5
70°	250.3	249.0	247.6	246.3	245.0	243.6	242.1	240.6	239.1	237.7	236.1
72.5°	219.3	217.9	216.7	215.3	214.0	212.8	211.6	210.3	209.1	207.9	206.8
75°	173.6	172.6	171.7	170.8	169.8	168.9	167.9	167.0	166.1	165.2	164.4
77.5°	129.9	129.5	129.1	128.7	128.3	127.7	126.8	126.0	125.2	124.4	124.1
80°	103.6	103.1	102.5	102.0	101.4	100.9	100.5	100.2	99.8	99.4	99.0
82.5°	78.0	77.8	77.5	77.2	77.0	76.8	76.8	76.7	76.6	76.5	76.3
85°	45.5	45.5	45.5	45.5	45.5	45.3	44.9	44.6	44.2	43.8	43.8
87.5°	17.7	17.7	18.0	18.0	17.9	17.7	18.4	18.2	18.3	18.4	18.3
90°	0.6	1.8	3.7	4.4	5.0	5.0	8.6	8.6	9.9	11.2	10.5
92.5°	7.1	10.3	16.1	23.7	32.7	45.6	77.1	125.1	172.0	196.5	163.7
95°	20.4	22.3	28.5	36.5	51.4	77.4	131.3	232.9	381.0	504.9	519.1
97.5°	36.7	36.7	42.0	49.4	62.2	84.0	125.5	209.4	356.6	531.7	652.1
100°	47.1	47.1	51.4	58.9	70.6	90.5	127.0	197.0	323.4	498.0	656.6
102.5°	57.0	58.0	61.8	68.8	80.0	98.9	131.9	193.5	301.0	455.9	619.4
105°	72.5	74.3	77.4	84.8	96.0	114.0	143.7	195.1	281.9	406.3	551.9
107.5°	89.6	90.8	93.9	101.8	112.5	130.2	157.5	204.3	278.4	378.6	497.4
110°	101.0	102.2	105.3	112.7	123.9	140.6	167.9	211.2	279.3	369.2	470.2



TEST NUMBER: P332606-927

CATALOG NUMBER: S124DIP-S795D810U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.9	113.1	116.7	123.7	134.8	151.5	177.8	218.6	282.3	364.7	454.8
115°	127.6	129.4	133.8	140.0	151.8	168.5	193.3	230.4	288.0	362.3	440.4
117.5°	143.9	145.7	149.6	156.4	167.4	184.7	208.3	242.4	294.1	361.7	434.0
120°	154.9	156.1	160.4	167.2	177.8	195.1	218.6	250.9	298.6	361.7	430.5
122.5°	164.8	166.0	170.3	176.7	188.1	205.0	228.5	258.8	303.0	361.2	426.5
125°	177.8	180.2	183.9	190.8	202.6	219.9	242.2	270.7	309.7	360.5	419.9
127.5°	189.3	191.3	195.7	203.5	215.8	233.3	254.8	281.0	315.1	359.2	411.1
130°	195.7	198.2	203.2	212.5	224.3	242.2	263.2	287.4	319.0	358.6	405.8
132.5°	202.2	204.1	210.6	219.4	232.2	249.1	270.2	293.8	322.5	358.1	400.8
135°	211.2	213.7	219.9	230.4	243.4	259.5	280.0	302.3	327.6	357.4	393.3
137.5°	220.3	222.6	229.4	239.5	252.9	268.3	287.4	308.2	330.7	357.3	386.9
140°	226.7	228.5	235.4	245.9	258.9	273.8	292.4	312.2	333.3	356.8	383.4
142.5°	233.6	235.5	241.9	251.8	264.4	278.8	296.8	315.1	335.3	356.8	380.5
145°	243.4	245.3	251.5	260.2	272.0	285.6	301.7	318.4	336.4	355.5	375.3
147.5°	254.4	255.1	260.5	269.4	279.2	291.5	306.7	321.2	337.0	353.3	370.8
150°	261.4	262.1	267.0	274.4	283.7	295.5	309.1	322.7	337.0	351.8	367.3
152.5°	267.8	268.0	272.9	279.9	288.2	299.0	311.1	323.7	336.0	349.4	363.4
155°	276.9	277.5	281.2	287.4	294.2	303.5	314.0	324.6	334.5	345.6	357.4
157.5°	285.7	285.7	289.1	294.0	299.9	307.2	316.2	324.6	332.9	341.8	351.3
160°	291.1	291.1	293.6	297.9	302.9	309.7	317.1	324.6	331.4	338.8	346.9
162.5°	296.1	295.6	297.5	301.4	305.9	311.2	318.1	324.6	329.9	335.9	342.9
165°	301.7	301.7	302.9	306.0	309.1	312.8	318.4	323.4	327.1	331.4	336.4
167.5°	307.2	306.7	307.2	309.6	311.3	314.2	318.3	321.9	324.1	326.9	330.4
170°	309.7	309.1	309.7	311.6	312.8	314.7	317.7	320.8	322.1	323.9	326.5
172.5°	312.2	311.6	311.7	313.1	313.8	315.1	317.3	319.9	320.1	321.0	323.0
175°	314.7	314.0	314.0	314.7	315.3	315.3	316.6	318.4	317.7	317.7	319.0
177.5°	315.8	315.3	314.8	315.3	315.3	315.3	315.8	316.8	315.8	315.8	316.2
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3



TEST NUMBER: P332606-927

CATALOG NUMBER: S124DIP-S795D810U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1047.8	1049.3	1050.8	1051.5	1051.4	1051.2	1051.1	1050.9
5°	1042.2	1044.3	1046.3	1047.2	1046.8	1046.5	1046.1	1045.7
7.5°	1030.6	1032.3	1033.9	1034.6	1034.4	1034.2	1034.0	1033.7
10°	1020.9	1022.4	1023.9	1024.5	1024.1	1023.7	1023.3	1022.9
12.5°	1009.1	1010.7	1012.3	1012.9	1012.4	1011.9	1011.3	1010.8
15°	986.4	987.5	988.6	989.0	988.4	987.9	987.3	986.7
17.5°	960.7	961.4	962.1	962.3	961.9	961.5	961.2	960.8
20°	941.5	942.1	942.6	942.7	942.3	942.0	941.6	941.2
22.5°	921.5	922.5	923.5	923.7	923.0	922.3	921.6	921.0
25°	888.5	888.7	888.9	888.6	887.9	887.1	886.4	885.6
27.5°	851.5	851.0	850.6	849.9	849.0	848.0	847.1	846.1
30°	825.9	825.2	824.4	823.6	822.7	821.7	820.8	819.9
32.5°	800.0	799.2	798.3	797.3	796.4	795.4	794.5	793.6
35°	759.1	757.8	756.5	755.3	754.4	753.5	752.6	751.6
37.5°	716.2	714.8	713.4	712.1	710.8	709.6	708.4	707.1
40°	686.3	684.5	682.6	681.2	680.2	679.4	678.4	677.5
42.5°	657.4	655.3	653.1	651.7	651.1	650.5	649.8	649.2
45°	612.7	610.6	608.6	607.3	606.7	606.1	605.5	605.0
47.5°	569.3	567.0	564.7	562.8	561.4	560.0	558.6	557.1
50°	539.1	536.5	533.9	532.0	530.8	529.7	528.6	527.5
52.5°	508.0	505.6	503.4	501.5	500.1	498.7	497.3	495.8
55°	462.3	460.1	457.8	456.1	455.0	453.9	452.7	451.6
57.5°	416.5	414.4	412.3	410.7	409.6	408.4	407.4	406.3
60°	385.1	383.4	381.7	380.4	379.5	378.5	377.6	376.7
62.5°	354.3	352.8	351.3	350.1	349.1	348.2	347.3	346.3
65°	309.7	307.8	305.9	304.6	303.6	302.7	301.7	300.8
67.5°	263.7	261.9	260.1	259.0	258.8	258.6	258.3	258.0
70°	234.6	233.1	231.6	230.6	230.0	229.5	228.9	228.4
72.5°	205.6	204.4	203.2	202.3	201.7	201.1	200.6	200.0
75°	163.7	162.9	162.2	161.7	161.5	161.3	161.1	161.0
77.5°	123.9	123.7	123.5	123.1	122.6	122.2	121.7	121.2
80°	98.7	98.3	97.9	97.7	97.4	97.3	97.1	96.9
82.5°	76.0	75.8	75.6	75.4	75.3	75.0	74.9	74.6
85°	43.8	43.8	43.8	43.7	43.6	43.3	43.2	42.9
87.5°	18.4	18.5	18.7	18.7	18.8	18.9	18.8	18.8
90°	11.2	11.8	12.4	12.4	13.0	13.6	13.0	13.0
92.5°	121.7	91.6	72.9	60.4	53.2	49.8	47.7	47.7
95°	459.0	363.0	280.0	219.9	189.6	170.3	159.2	151.1
97.5°	678.1	642.5	581.9	517.2	472.8	435.5	416.8	404.0
100°	747.0	759.4	729.0	683.3	629.3	591.5	573.0	568.0
102.5°	743.5	805.0	813.8	794.7	761.7	734.3	714.7	710.7
105°	693.8	800.9	862.2	887.6	888.9	883.9	875.3	871.6
107.5°	623.1	737.1	823.5	878.7	909.3	923.4	929.6	931.2
110°	580.4	687.5	777.4	845.5	889.5	915.5	926.7	932.2





TEST NUMBER: P332606-927

CATALOG NUMBER: S124DIP-S795D810U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	549.2	644.0	728.8	796.9	846.8	878.4	894.0	903.0
115°	517.8	594.1	666.5	726.0	774.9	812.1	831.9	836.9
117.5°	502.5	565.5	622.5	673.0	714.7	745.9	766.0	769.8
120°	495.5	553.2	602.7	646.7	682.0	709.2	725.3	732.1
122.5°	489.6	545.2	590.3	628.8	658.7	682.0	695.6	702.4
125°	479.4	532.7	575.4	609.5	634.3	652.3	664.0	667.7
127.5°	467.1	517.9	560.5	592.9	617.8	633.8	643.7	647.5
130°	457.2	506.0	548.2	581.0	606.4	621.9	631.8	635.6
132.5°	446.7	492.7	533.9	566.6	591.5	609.0	618.5	622.2
135°	432.4	472.6	510.4	541.4	566.2	583.5	593.4	597.1
137.5°	419.4	453.4	485.3	513.3	536.4	553.5	561.7	566.2
140°	411.9	441.0	468.9	495.0	516.6	530.2	538.9	543.8
142.5°	405.0	430.6	454.6	477.1	496.3	508.9	516.6	520.1
145°	395.2	416.3	434.8	452.2	467.7	478.2	484.4	487.5
147.5°	387.1	403.9	418.7	432.4	443.8	452.8	457.5	458.6
150°	382.1	396.4	408.8	419.9	429.9	437.9	441.6	442.3
152.5°	376.8	389.0	400.4	409.6	418.0	424.5	426.7	427.4
155°	368.5	378.5	387.8	395.2	401.4	406.3	408.2	408.2
157.5°	359.7	368.0	375.9	381.8	386.5	390.2	391.3	391.3
160°	354.3	361.2	368.0	372.9	376.6	380.3	381.0	381.0
162.5°	348.9	354.7	360.0	364.5	367.2	370.9	371.5	371.1
165°	341.3	345.0	349.4	352.4	354.9	357.4	356.8	356.2
167.5°	334.0	336.8	340.3	342.1	343.4	345.0	344.9	344.4
170°	329.5	331.4	333.9	335.7	337.0	337.5	337.0	337.0
172.5°	325.6	326.9	328.4	329.8	330.5	331.1	330.5	329.5
175°	320.3	320.8	322.1	322.1	322.1	323.4	322.1	320.8
177.5°	316.8	317.3	317.3	317.7	317.3	317.7	316.8	315.8
180°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3

(END OF REPORT)