

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331953-940

Luminaire Tested: **S123DIP-S560D1195U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331953-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1195U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5725.2 lumens  
Efficiency: N/A  
Efficacy: 115.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331953-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331953-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31	25
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	20	16
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P331953-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.8	1.3
10°-20°	211.3	3.7
20°-30°	312.1	5.5
30°-40°	364.6	6.4
40°-50°	366.5	6.4
50°-60°	322.0	5.6
60°-70°	239.9	4.2
70°-80°	136.7	2.4
80°-90°	43.1	0.8
90°-100°	85.9	1.5
100°-110°	257.2	4.5
110°-120°	437.4	7.6
120°-130°	575.3	10.0
130°-140°	646.7	11.3
140°-150°	635.6	11.1
150°-160°	535.1	9.3
160°-170°	356.2	6.2
170°-180°	124.7	2.2
0°-30°	598.2	10.4
0°-40°	962.8	16.8
0°-60°	1651.3	28.8
0°-90°	2071.0	36.2
90°-120°	780.5	13.6
90°-150°	2638.1	46.1
90°-180°	3654.0	63.8
0°-180°	5725.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	1	12	25	29	31	6
95°	61	68	77	81	81	69
105°	233	236	244	245	247	250
115°	440	443	441	442	441	436
125°	644	647	646	641	637	574
135°	836	842	841	837	835	644
145°	1014	1016	1020	1018	1014	633
155°	1162	1162	1162	1166	1159	534
165°	1265	1262	1262	1267	1261	357
175°	1316	1312	1312	1317	1311	125
180°	1319	1319	1319	1319	1319	



TEST NUMBER: P331953-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.4	14.5	14.6	14.7	14.8	15.1	15.6	16.1	16.5	17.0	17.0
90°	1.1	3.3	5.6	7.9	10.3	12.9	15.9	18.9	21.8	24.9	25.8
92.5°	25.1	26.7	28.2	29.8	31.3	33.0	34.7	36.4	38.1	39.8	40.5
95°	61.2	62.8	64.4	66.0	67.6	69.3	71.2	72.9	74.8	76.7	77.6
97.5°	108.6	109.8	111.0	112.2	113.3	114.7	116.0	117.3	118.6	119.9	121.0
100°	140.9	142.3	143.7	145.1	146.4	147.7	148.8	150.0	151.1	152.3	153.0
102.5°	178.2	179.1	179.9	180.7	181.6	182.7	184.2	185.7	187.3	188.8	189.5
105°	233.1	233.5	234.1	234.5	235.0	236.2	238.3	240.4	242.5	244.5	244.5
107.5°	296.9	297.2	297.5	297.7	298.0	298.6	299.4	300.2	301.0	301.9	302.6
110°	336.7	337.2	337.6	338.1	338.6	339.0	339.5	339.9	340.4	340.9	341.8



TEST NUMBER: P331953-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.2	378.4	378.7	379.0	379.2	379.4	379.5	379.6	379.7	379.8	380.9
115°	440.3	441.0	441.7	442.4	443.1	443.2	442.7	442.3	441.8	441.4	441.6
117.5°	502.9	503.4	503.8	504.3	504.7	504.7	504.1	503.5	502.9	502.3	502.2
120°	541.9	543.2	544.7	546.0	547.4	547.5	546.4	545.2	544.0	542.9	542.7
122.5°	582.5	583.4	584.5	585.5	586.6	586.7	586.1	585.5	585.0	584.3	583.7
125°	644.4	645.2	645.8	646.5	647.2	647.3	646.8	646.4	646.0	645.5	644.5
127.5°	701.6	703.1	704.5	706.1	707.5	708.0	707.5	706.9	706.5	706.0	704.7
130°	739.8	741.5	743.4	745.3	747.1	747.7	747.0	746.3	745.6	744.9	744.0
132.5°	777.8	779.7	781.6	783.4	785.2	786.0	785.4	784.9	784.3	783.9	782.7
135°	836.1	837.5	838.8	840.3	841.6	842.2	842.0	841.8	841.5	841.2	840.3
137.5°	890.0	891.1	892.2	893.4	894.6	895.5	896.1	896.6	897.2	897.9	896.9
140°	927.3	928.4	929.6	930.8	931.8	932.6	932.8	933.0	933.3	933.5	933.3
142.5°	961.3	962.4	963.6	964.7	965.9	966.6	967.1	967.5	967.9	968.3	968.0
145°	1014.3	1014.8	1015.2	1015.7	1016.1	1016.7	1017.4	1018.1	1018.8	1019.5	1019.2
147.5°	1060.7	1061.6	1062.4	1063.2	1064.1	1064.8	1065.4	1066.0	1066.7	1067.4	1067.4
150°	1093.1	1093.5	1094.0	1094.4	1094.9	1095.4	1095.8	1096.3	1096.7	1097.2	1097.2
152.5°	1119.5	1120.3	1120.9	1121.5	1122.1	1122.6	1122.8	1123.2	1123.5	1123.7	1124.1
155°	1161.5	1161.5	1161.5	1161.5	1161.5	1161.5	1161.8	1162.0	1162.3	1162.4	1163.4
157.5°	1197.0	1196.8	1196.5	1196.2	1196.0	1195.9	1196.1	1196.3	1196.5	1196.7	1197.7
160°	1219.4	1219.0	1218.5	1218.1	1217.6	1217.4	1217.4	1217.4	1217.4	1217.4	1218.5
162.5°	1239.3	1238.7	1238.1	1237.4	1236.8	1236.5	1236.7	1236.9	1237.1	1237.2	1238.4
165°	1265.1	1264.4	1263.6	1262.9	1262.3	1261.9	1261.9	1261.9	1261.9	1261.9	1263.3
167.5°	1285.6	1284.6	1283.7	1282.8	1281.8	1281.5	1281.7	1281.8	1282.0	1282.2	1283.6
170°	1297.2	1296.2	1295.3	1294.4	1293.4	1293.0	1293.0	1293.0	1293.0	1293.0	1294.6
172.5°	1306.3	1305.4	1304.4	1303.5	1302.6	1302.2	1302.2	1302.2	1302.2	1302.2	1303.6
175°	1315.8	1314.9	1313.9	1313.0	1312.2	1311.6	1311.6	1311.6	1311.6	1311.6	1313.0
177.5°	1319.7	1319.0	1318.3	1317.5	1316.8	1316.4	1316.4	1316.4	1316.4	1316.4	1317.5
180°	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9



TEST NUMBER: P331953-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	17.1	17.2	17.2	17.3	17.4	17.5	17.6	17.7
90°	26.8	27.6	28.5	29.2	29.7	30.1	30.6	31.1
92.5°	41.3	42.0	42.7	43.0	42.7	42.4	42.1	41.8
95°	78.5	79.5	80.3	80.8	80.8	80.8	80.8	80.8
97.5°	122.1	123.1	124.2	124.7	124.6	124.5	124.4	124.3
100°	153.6	154.4	155.1	155.6	156.1	156.6	157.0	157.5
102.5°	190.1	190.8	191.5	191.8	191.7	191.6	191.5	191.5
105°	244.5	244.5	244.5	244.8	245.2	245.7	246.1	246.6
107.5°	303.4	304.2	304.9	305.1	304.8	304.5	304.3	304.0
110°	342.7	343.7	344.6	344.7	344.3	343.8	343.4	343.0





TEST NUMBER: P331953-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.0	383.2	384.2	384.8	384.7	384.6	384.5	384.4
115°	441.8	442.0	442.3	442.3	442.0	441.8	441.6	441.4
117.5°	502.2	502.1	502.1	501.8	501.1	500.4	499.8	499.2
120°	542.4	542.2	542.0	541.6	541.2	540.7	540.3	539.8
122.5°	583.2	582.6	581.9	581.3	580.7	580.1	579.3	578.7
125°	643.6	642.7	641.8	640.9	640.0	639.0	638.1	637.2
127.5°	703.4	702.1	700.8	699.6	698.6	697.5	696.4	695.4
130°	743.1	742.2	741.3	739.9	738.3	736.7	735.1	733.5
132.5°	781.7	780.6	779.4	778.3	777.0	775.8	774.5	773.3
135°	839.5	838.5	837.6	836.9	836.4	836.0	835.5	835.1
137.5°	895.9	894.9	893.9	893.0	892.2	891.4	890.5	889.6
140°	933.0	932.8	932.6	931.7	930.1	928.4	926.8	925.2
142.5°	967.9	967.6	967.4	966.6	965.4	964.1	963.0	961.7
145°	1019.0	1018.8	1018.6	1018.0	1017.1	1016.1	1015.2	1014.3
147.5°	1067.4	1067.4	1067.4	1066.7	1065.2	1063.9	1062.5	1061.1
150°	1097.2	1097.2	1097.2	1096.5	1095.1	1093.8	1092.3	1091.0
152.5°	1124.4	1124.8	1125.2	1124.8	1123.6	1122.4	1121.1	1120.0
155°	1164.3	1165.2	1166.2	1165.8	1164.2	1162.6	1161.0	1159.3
157.5°	1198.5	1199.5	1200.5	1200.3	1199.1	1197.7	1196.5	1195.2
160°	1219.7	1220.8	1222.0	1222.1	1221.2	1220.2	1219.3	1218.4
162.5°	1239.6	1240.7	1241.9	1241.7	1240.2	1238.8	1237.2	1235.8
165°	1264.7	1266.1	1267.5	1267.3	1265.7	1264.1	1262.5	1260.9
167.5°	1285.0	1286.5	1287.9	1287.9	1286.5	1285.0	1283.6	1282.2
170°	1296.2	1297.9	1299.5	1299.5	1297.9	1296.2	1294.6	1293.0
172.5°	1305.0	1306.4	1307.9	1307.8	1306.1	1304.5	1302.9	1301.3
175°	1314.4	1315.8	1317.1	1317.1	1315.5	1313.8	1312.2	1310.6
177.5°	1318.7	1319.7	1320.8	1320.7	1319.5	1318.1	1316.9	1315.6
180°	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9	1318.9

(END OF REPORT)