

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332976-927

Luminaire Tested: **S124RDIP-S1020D1035U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332976-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D1035U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6578.5 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332976-927

CATALOG NUMBER: S124RDIP-S1020D1035U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332976-927

CATALOG NUMBER: S124RDIP-S1020D1035U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50					50			
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43					43			
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	36					36			
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31					31			
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	27					27			
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	23					23			
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21					21			
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	24	21	18					18			
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17					17			
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15					15			
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14					14			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11548	11548	11548
5°	11574	11432	11503
10°	11501	11294	11294
15°	11369	11058	10975
20°	11188	10746	10548
25°	10956	10381	10117
30°	10730	9996	9577
35°	10481	9596	9034
40°	10181	9141	8450
45°	9903	8691	7854
50°	9588	8171	7222
55°	9250	7631	6536
60°	8879	7038	5837
65°	8537	6298	5146
70°	8039	5481	4369
75°	7414	4545	3553
80°	6467	3464	3259
85°	5483	3149	2946



TEST NUMBER: P332976-927

CATALOG NUMBER: S124RDIP-S1020D1035U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.4	2.0
10°-20°	374.7	5.7
20°-30°	541.1	8.2
30°-40°	613.3	9.3
40°-50°	592.3	9.0
50°-60°	492.5	7.5
60°-70°	340.1	5.2
70°-80°	172.4	2.6
80°-90°	47.3	0.7
90°-100°	36.2	0.5
100°-110°	230.6	3.5
110°-120°	441.1	6.7
120°-130°	559.9	8.5
130°-140°	599.1	9.1
140°-150°	560.2	8.5
150°-160°	451.8	6.9
160°-170°	291.4	4.4
170°-180°	100.4	1.5
0°-30°	1050.1	16.0
0°-40°	1663.5	25.3
0°-60°	2748.2	41.8
0°-90°	3307.9	50.3
90°-120°	707.8	10.8
90°-150°	2427.0	36.9
90°-180°	3271.0	49.7
0°-180°	6578.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1430	1430	1430	1430	1430	
5°	1428	1423	1411	1421	1420	135
15°	1360	1349	1323	1321	1313	383
25°	1230	1209	1165	1147	1136	566
35°	1064	1027	974	937	917	664
45°	867	826	761	709	688	669
55°	657	612	542	487	464	588
65°	447	398	330	284	269	441
75°	238	197	146	122	114	251
85°	59	38	34	32	32	67
90°	2	11	17	22	24	5
95°	44	18	17	22	23	56
105°	238	243	247	252	225	249
115°	444	447	446	448	448	437
125°	625	628	626	629	630	558
135°	775	774	777	779	780	597
145°	894	896	896	897	898	558
155°	980	980	978	981	979	452
165°	1034	1030	1030	1035	1029	292
175°	1057	1053	1053	1060	1051	101
180°	1057	1057	1057	1057	1057	



TEST NUMBER: P332976-927

CATALOG NUMBER: S124RDIP-S1020D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1433.9	1433.1	1432.3	1431.6	1430.8	1429.3	1427.2	1425.1	1422.9	1420.8	1422.9
5°	1428.2	1427.3	1426.3	1425.3	1424.3	1422.4	1419.5	1416.6	1413.6	1410.7	1413.2
7.5°	1415.3	1414.3	1413.3	1412.2	1411.2	1408.8	1405.0	1401.2	1397.4	1393.6	1395.2
10°	1403.0	1401.8	1400.6	1399.4	1398.2	1395.3	1391.0	1386.6	1382.2	1377.8	1378.8
12.5°	1387.3	1385.8	1384.4	1383.1	1381.6	1378.3	1373.2	1368.0	1362.9	1357.7	1358.3
15°	1360.3	1358.1	1356.0	1353.8	1351.5	1347.4	1341.3	1335.2	1329.2	1323.1	1322.6
17.5°	1327.7	1324.5	1321.4	1318.2	1315.0	1309.8	1302.5	1295.2	1287.9	1280.6	1279.2
20°	1302.3	1299.1	1295.9	1292.8	1289.6	1283.9	1275.7	1267.3	1259.1	1250.8	1248.9
22.5°	1274.2	1270.7	1267.1	1263.6	1260.0	1253.8	1245.0	1236.1	1227.2	1218.4	1215.4
25°	1230.0	1225.6	1221.2	1216.9	1212.4	1205.3	1195.3	1185.3	1175.4	1165.4	1161.3
27.5°	1183.5	1178.1	1172.6	1167.0	1161.6	1153.5	1142.8	1132.2	1121.5	1110.8	1105.7
30°	1151.1	1145.0	1139.0	1132.9	1126.8	1118.0	1106.6	1095.1	1083.7	1072.3	1066.2
32.5°	1117.0	1110.1	1103.2	1096.4	1089.5	1080.1	1068.3	1056.5	1044.7	1032.8	1025.8
35°	1063.5	1055.7	1047.9	1040.1	1032.4	1022.4	1010.2	998.1	985.9	973.7	965.4
37.5°	1006.3	998.3	990.3	982.2	974.2	963.5	950.0	936.5	923.0	909.5	900.2
40°	966.1	958.0	950.0	941.9	933.9	923.0	909.1	895.2	881.3	867.4	857.2
42.5°	927.5	919.1	910.6	902.2	893.8	882.3	867.9	853.4	839.0	824.5	814.1
45°	867.4	858.5	849.5	840.4	831.4	819.6	805.0	790.4	775.8	761.2	749.3
47.5°	805.5	796.1	786.9	777.6	768.3	756.1	740.8	725.6	710.4	695.3	682.9
50°	763.4	753.9	744.4	734.9	725.4	712.9	697.4	681.8	666.1	650.6	638.4
52.5°	720.5	711.1	701.9	692.6	683.3	670.7	654.7	638.7	622.7	606.8	594.5
55°	657.2	647.5	637.7	628.0	618.2	605.5	589.6	573.8	558.0	542.2	529.5
57.5°	594.5	584.4	574.3	564.1	554.1	541.1	525.6	510.0	494.4	478.9	466.0
60°	549.9	540.1	530.4	520.6	510.9	498.2	482.7	467.1	451.5	435.9	423.3
62.5°	509.5	499.4	489.3	479.1	469.1	456.0	440.0	424.1	408.1	392.1	380.4
65°	446.9	436.4	426.0	415.5	405.0	392.0	376.4	360.8	345.2	329.7	319.2
67.5°	381.8	371.8	361.8	351.7	341.7	329.5	315.0	300.6	286.1	271.6	262.6
70°	340.6	330.4	320.2	310.0	299.8	287.7	273.9	259.9	246.1	232.2	224.2
72.5°	296.8	287.6	278.3	269.1	259.8	248.7	235.6	222.4	209.4	196.3	189.4
75°	237.7	228.7	219.7	210.6	201.7	191.4	180.0	168.6	157.1	145.7	140.1
77.5°	177.7	170.0	162.4	154.7	147.1	138.6	129.4	120.2	110.9	101.6	98.4
80°	139.1	132.1	125.0	118.0	110.9	103.7	96.4	89.1	81.8	74.5	73.8
82.5°	105.8	99.3	92.8	86.3	79.9	74.5	70.4	66.2	62.0	57.8	57.3
85°	59.2	54.3	49.4	44.5	39.7	36.8	36.1	35.4	34.7	34.0	33.4
87.5°	20.6	19.5	18.3	17.1	15.9	15.4	15.5	15.6	15.7	15.8	15.8
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	10.0	10.1	10.1	10.3	10.4	11.2	12.5	13.9	15.4	16.8	17.8
95°	43.5	37.5	31.5	25.6	19.6	16.7	16.9	17.0	17.2	17.4	18.5
97.5°	92.4	96.1	99.8	103.5	107.3	99.3	79.7	60.1	40.5	20.9	21.0
100°	129.7	132.8	136.0	139.2	142.4	131.8	107.6	83.3	59.0	34.8	31.8
102.5°	171.4	173.8	176.1	178.4	180.7	180.3	177.1	174.0	170.8	167.6	135.4
105°	238.1	239.1	240.1	241.2	242.2	243.2	244.1	244.9	245.9	246.8	248.3
107.5°	299.8	300.4	301.0	301.4	302.0	302.9	304.0	305.2	306.4	307.6	308.4
110°	341.7	342.1	342.7	343.2	343.7	344.5	345.5	346.7	347.7	348.7	349.1



TEST NUMBER: P332976-927

CATALOG NUMBER: S124RDIP-S1020D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.1	383.1	384.0	385.0	386.0	386.7	387.1	387.6	388.1	388.6	388.6
115°	444.4	445.0	445.5	446.0	446.6	446.7	446.6	446.4	446.2	446.0	446.4
117.5°	500.6	501.3	502.0	502.7	503.4	503.9	504.3	504.7	505.1	505.5	505.4
120°	538.5	539.2	540.0	540.7	541.4	541.6	541.5	541.3	541.1	540.9	541.3
122.5°	573.9	574.4	574.8	575.2	575.7	576.0	576.2	576.5	576.7	576.9	577.2
125°	624.7	625.4	626.1	626.9	627.6	627.7	627.4	627.0	626.7	626.3	626.9
127.5°	672.8	673.0	673.2	673.4	673.5	674.0	674.9	675.7	676.4	677.2	677.2
130°	703.9	704.0	704.2	704.3	704.5	704.9	705.4	705.9	706.5	707.0	707.2
132.5°	732.3	732.6	732.9	733.2	733.6	734.0	734.7	735.4	736.0	736.7	736.9
135°	775.0	774.8	774.7	774.4	774.3	774.5	775.2	775.9	776.7	777.4	777.7
137.5°	812.8	812.9	812.9	813.0	813.1	813.5	814.3	815.1	815.8	816.6	817.0
140°	837.5	837.8	838.2	838.5	838.8	839.2	839.6	840.0	840.3	840.7	841.1
142.5°	859.6	860.2	860.9	861.5	862.1	862.5	862.8	863.0	863.2	863.4	863.8
145°	893.6	894.1	894.7	895.2	895.7	896.0	896.0	896.0	896.0	896.0	896.2
147.5°	920.7	921.6	922.7	923.6	924.6	925.0	924.8	924.6	924.5	924.3	924.5
150°	940.2	941.0	941.7	942.4	943.1	943.3	943.2	943.0	942.9	942.6	942.6
152.5°	956.7	957.3	957.8	958.4	958.9	959.1	958.8	958.5	958.1	957.8	958.1
155°	979.9	980.0	980.2	980.3	980.5	980.3	979.9	979.3	978.7	978.3	978.9
157.5°	999.3	999.2	999.0	998.9	998.9	998.5	997.9	997.3	996.7	996.1	997.0
160°	1010.7	1010.1	1009.6	1009.1	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5
162.5°	1020.8	1020.1	1019.5	1018.7	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0
165°	1033.6	1032.7	1031.8	1030.9	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0
167.5°	1043.7	1042.8	1041.9	1041.0	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7
170°	1049.4	1048.4	1047.3	1046.2	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9
172.5°	1053.2	1052.2	1051.1	1050.0	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7
175°	1057.3	1056.3	1055.2	1054.2	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9
177.5°	1059.2	1058.2	1057.2	1056.3	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332976-927

CATALOG NUMBER: S124RDIP-S1020D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4	1430.4
2.5°	1425.1	1427.2	1429.3	1430.4	1430.1	1430.0	1429.7	1429.6
5°	1415.6	1418.0	1420.5	1421.4	1420.9	1420.5	1420.0	1419.5
7.5°	1396.8	1398.3	1399.9	1400.3	1399.5	1398.7	1397.9	1397.1
10°	1379.8	1380.8	1381.7	1381.7	1380.8	1379.8	1378.8	1377.8
12.5°	1358.8	1359.5	1360.0	1359.6	1358.3	1356.9	1355.6	1354.2
15°	1322.2	1321.6	1321.1	1320.0	1318.3	1316.6	1314.9	1313.2
17.5°	1277.9	1276.5	1275.2	1273.2	1270.6	1268.0	1265.4	1262.8
20°	1246.9	1245.0	1243.0	1240.5	1237.3	1234.1	1231.0	1227.8
22.5°	1212.5	1209.6	1206.7	1204.0	1201.3	1198.8	1196.2	1193.7
25°	1157.1	1152.9	1148.8	1145.5	1143.1	1140.7	1138.2	1135.8
27.5°	1100.6	1095.5	1090.4	1086.1	1082.6	1079.0	1075.5	1072.1
30°	1060.1	1054.0	1047.9	1042.9	1039.0	1035.1	1031.3	1027.4
32.5°	1018.7	1011.7	1004.6	999.3	995.5	991.8	988.2	984.4
35°	957.1	948.9	940.6	934.3	929.9	925.5	921.1	916.7
37.5°	891.0	881.8	872.5	865.7	861.3	856.9	852.5	848.2
40°	847.0	836.8	826.6	819.3	814.9	810.5	806.1	801.8
42.5°	803.7	793.3	782.8	775.4	770.8	766.2	761.6	757.1
45°	737.4	725.4	713.5	705.4	701.0	696.6	692.2	687.9
47.5°	670.6	658.2	645.8	637.2	632.4	627.6	622.7	618.0
50°	626.2	614.1	601.9	593.5	588.9	584.2	579.6	575.0
52.5°	582.0	569.7	557.3	548.7	543.9	539.1	534.2	529.5
55°	516.8	504.2	491.5	482.9	478.2	473.6	469.1	464.4
57.5°	453.1	440.3	427.5	419.3	415.7	412.3	408.8	405.3
60°	410.6	397.9	385.3	377.0	373.1	369.2	365.4	361.5
62.5°	368.8	357.0	345.4	337.9	334.9	331.8	328.6	325.5
65°	308.7	298.3	287.8	281.1	278.2	275.3	272.4	269.4
67.5°	253.6	244.6	235.6	229.5	226.2	223.1	219.8	216.7
70°	216.1	208.1	200.1	194.8	192.4	190.0	187.5	185.1
72.5°	182.5	175.7	168.8	164.3	162.0	159.8	157.6	155.3
75°	134.5	128.9	123.3	119.8	118.3	116.8	115.3	113.9
77.5°	95.1	91.9	88.6	86.7	86.3	85.9	85.4	85.0
80°	73.0	72.3	71.5	71.1	70.8	70.6	70.3	70.1
82.5°	56.7	56.2	55.7	55.3	55.1	54.8	54.6	54.3
85°	33.0	32.5	32.0	31.8	31.8	31.8	31.8	31.8
87.5°	15.8	15.8	15.8	15.9	16.2	16.5	16.7	17.0
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	18.9	20.0	21.0	21.5	21.6	21.7	21.8	21.9
95°	19.5	20.6	21.6	22.3	22.4	22.6	22.7	22.9
97.5°	21.1	21.2	21.3	21.5	21.6	21.8	21.9	22.2
100°	28.8	25.8	22.8	21.5	21.6	21.8	21.9	22.2
102.5°	103.2	71.0	38.7	22.7	22.7	22.7	22.7	22.8
105°	249.9	251.4	253.0	250.7	244.4	238.1	231.7	225.4
107.5°	309.2	310.0	310.7	311.4	312.1	312.8	313.5	314.1
110°	349.4	349.8	350.1	350.6	351.1	351.6	352.2	352.7





TEST NUMBER: P332976-927

CATALOG NUMBER: S124RDIP-S1020D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	388.5	388.4	388.3	388.6	389.3	390.0	390.6	391.3
115°	446.7	447.1	447.4	447.6	447.6	447.6	447.6	447.6
117.5°	505.3	505.3	505.2	505.2	505.1	505.0	504.9	504.9
120°	541.6	541.9	542.3	542.3	541.9	541.6	541.3	540.9
122.5°	577.4	577.6	577.8	577.7	577.4	577.0	576.7	576.3
125°	627.4	627.9	628.4	628.8	629.0	629.2	629.3	629.5
127.5°	677.1	676.9	676.8	676.7	676.6	676.4	676.3	676.1
130°	707.3	707.5	707.7	707.8	707.8	707.8	707.8	707.8
132.5°	737.0	737.3	737.4	737.4	737.3	737.1	737.0	736.9
135°	778.1	778.4	778.8	779.1	779.5	779.8	780.1	780.5
137.5°	817.4	817.8	818.2	818.2	818.2	818.1	817.9	817.8
140°	841.7	842.2	842.7	843.1	843.3	843.4	843.6	843.8
142.5°	864.2	864.6	865.0	865.1	865.2	865.2	865.3	865.3
145°	896.4	896.5	896.7	897.0	897.3	897.6	898.0	898.3
147.5°	924.6	924.7	924.9	925.0	925.2	925.3	925.6	925.7
150°	942.6	942.6	942.6	942.7	942.9	943.1	943.3	943.4
152.5°	958.4	958.7	958.9	959.0	958.9	958.9	958.7	958.6
155°	979.6	980.3	981.0	981.1	980.6	980.1	979.5	979.1
157.5°	997.9	998.9	999.7	999.7	998.9	997.9	997.0	996.1
160°	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5
162.5°	1019.1	1020.2	1021.2	1021.1	1019.9	1018.7	1017.6	1016.4
165°	1032.5	1033.9	1035.2	1035.1	1033.6	1032.0	1030.4	1028.8
167.5°	1042.2	1043.8	1045.3	1045.2	1043.5	1041.7	1039.9	1038.2
170°	1048.3	1049.6	1051.1	1050.9	1049.2	1047.4	1045.6	1043.9
172.5°	1052.1	1053.4	1054.9	1054.6	1052.7	1050.8	1048.9	1047.0
175°	1056.5	1058.1	1059.7	1059.4	1057.3	1055.2	1053.1	1051.0
177.5°	1058.3	1059.4	1060.6	1060.3	1058.6	1056.9	1055.2	1053.5
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3

(END OF REPORT)