

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332979-927

Luminaire Tested: **S124RDIP-S1020D1205U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332979-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D1205U927-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7246.3 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	58	50	44	63	53	46	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	47	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10973	10973	10973	10973
5°	12729	11006	9728	11006
10°	15057	10958	8682	10958
15°	17393	10857	7460	10857
20°	19365	10717	6747	10717
25°	19991	10580	6263	10580
30°	17500	10414	5972	10414
35°	13623	10168	5797	10168
40°	10215	9886	5702	9886
45°	8066	9435	5651	9435
50°	6810	8913	5488	8913
55°	5935	8341	5195	8341
60°	5339	7745	4598	7745
65°	4707	7104	3954	7104
70°	4239	6437	3567	6437
75°	3553	5705	3041	5705
80°	3003	4863	2850	4863
85°	2538	3798	2538	3798



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.7	1.8
10°-20°	397.3	5.5
20°-30°	621.4	8.6
30°-40°	690.7	9.5
40°-50°	612.9	8.5
50°-60°	477.6	6.6
60°-70°	312.7	4.3
70°-80°	153.8	2.1
80°-90°	41.5	0.6
90°-100°	42.1	0.6
100°-110°	268.4	3.7
110°-120°	513.4	7.1
120°-130°	651.7	9.0
130°-140°	697.3	9.6
140°-150°	652.1	9.0
150°-160°	525.8	7.3
160°-170°	339.2	4.7
170°-180°	116.9	1.6
0°-30°	1150.3	15.9
0°-40°	1841.1	25.4
0°-60°	2931.5	40.5
0°-90°	3439.4	47.5
90°-120°	823.9	11.4
90°-150°	2825.0	39.0
90°-180°	3807.0	52.5
0°-180°	7246.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1359	1359	1359	1359	1359	
5°	1571	1358	1200	1358	1571	159
15°	2081	1299	893	1299	2081	592
25°	2244	1188	703	1188	2244	996
35°	1382	1032	588	1032	1382	866
45°	706	826	495	826	706	560
55°	422	593	369	593	422	384
65°	246	372	207	372	246	248
75°	114	183	98	183	114	125
85°	27	41	27	41	27	32
90°	28	3	28	3	28	13
95°	27	51	27	51	27	21
105°	262	277	262	277	262	229
115°	521	517	521	517	521	516
125°	733	727	733	727	733	653
135°	908	902	908	902	908	699
145°	1046	1040	1046	1040	1046	653
155°	1140	1140	1140	1140	1140	525
165°	1198	1203	1198	1203	1198	338
175°	1223	1231	1223	1231	1223	116
180°	1231	1231	1231	1231	1231	



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1433.7	1437.7	1433.7	1433.3	1428.9	1427.6	1425.8	1420.1	1409.6	1403.5	1404.8
5°	1570.7	1584.3	1576.7	1575.6	1563.5	1551.5	1543.8	1526.3	1507.7	1495.1	1484.6
7.5°	1729.0	1736.9	1732.1	1724.4	1704.9	1693.8	1676.1	1653.0	1619.6	1594.0	1570.7
10°	1836.8	1843.3	1841.2	1826.9	1812.7	1783.7	1767.2	1735.0	1692.7	1659.4	1628.1
12.5°	1942.8	1949.8	1930.5	1931.2	1904.2	1881.4	1855.3	1814.7	1765.9	1722.8	1683.8
15°	2081.1	2072.3	2072.3	2061.3	2031.2	1999.5	1972.6	1929.9	1868.5	1817.0	1762.8
17.5°	2189.3	2192.3	2187.8	2161.9	2138.3	2105.5	2056.3	2006.4	1949.5	1880.4	1825.0
20°	2254.1	2254.1	2249.2	2231.7	2201.0	2165.9	2112.8	2058.6	1986.3	1916.8	1854.3
22.5°	2280.4	2282.1	2276.3	2261.8	2234.3	2200.0	2154.8	2099.8	2025.3	1946.9	1869.6
25°	2244.3	2254.6	2255.7	2251.9	2243.7	2222.9	2184.0	2127.6	2060.8	1975.9	1892.6
27.5°	2060.5	2073.6	2085.1	2104.0	2129.2	2142.4	2144.1	2115.4	2057.1	1975.5	1891.7
30°	1877.3	1888.2	1923.9	1970.4	2006.5	2039.4	2067.9	2075.5	2042.7	1969.3	1881.1
32.5°	1674.0	1688.9	1724.5	1774.6	1834.8	1890.5	1954.4	1987.0	1986.2	1942.1	1860.5
35°	1382.3	1393.2	1426.1	1478.6	1550.9	1633.6	1735.0	1813.8	1867.4	1863.6	1813.8
37.5°	1114.8	1127.1	1160.3	1204.0	1274.1	1376.4	1474.5	1583.1	1682.4	1738.1	1721.4
40°	969.3	969.9	1002.2	1047.1	1112.8	1202.1	1308.8	1429.3	1539.9	1630.3	1647.8
42.5°	854.5	854.6	876.0	924.4	971.8	1055.7	1157.7	1277.3	1406.8	1511.2	1557.6
45°	706.5	711.4	728.9	758.0	795.2	866.3	947.9	1059.1	1204.3	1328.0	1405.3
47.5°	598.3	605.5	616.6	640.3	669.9	717.4	784.9	884.8	1002.8	1139.0	1248.9
50°	542.2	543.3	557.5	570.6	596.4	634.1	693.3	776.6	884.9	1015.9	1138.0
52.5°	494.0	493.8	502.3	519.0	539.9	569.3	617.1	692.8	789.0	906.3	1032.4
55°	421.7	424.5	431.0	444.1	460.0	480.9	518.6	575.6	651.2	751.4	865.9
57.5°	366.7	368.1	373.3	378.8	393.4	408.5	436.9	476.4	540.2	622.3	728.9
60°	330.7	331.3	333.0	341.2	352.7	366.9	386.1	419.5	473.2	548.2	632.6
62.5°	295.7	296.7	299.2	305.2	314.1	324.0	344.0	370.9	415.3	479.4	555.4
65°	246.4	247.0	250.8	253.0	260.2	268.9	283.7	301.7	332.4	386.1	443.6
67.5°	205.9	205.9	206.1	209.1	214.0	219.8	228.7	243.1	266.3	299.2	349.9
70°	179.6	179.6	180.7	182.4	185.1	190.0	195.0	205.9	222.9	249.7	288.6
72.5°	155.1	155.5	156.6	156.9	158.4	162.4	166.0	173.1	185.7	205.9	237.3
75°	113.9	115.6	118.3	120.5	123.2	122.7	126.5	130.9	134.8	146.8	164.9
77.5°	84.8	83.9	84.2	86.1	86.4	87.0	89.7	93.1	95.9	101.6	108.1
80°	64.6	64.6	66.2	66.8	66.2	66.8	69.6	71.2	72.3	74.5	80.5
82.5°	48.9	49.7	49.2	49.7	50.1	50.6	52.9	53.2	54.3	55.2	57.8
85°	27.4	28.0	28.4	27.4	27.4	27.4	28.4	29.0	30.1	29.5	30.7
87.5°	15.1	14.7	15.0	14.9	15.3	14.7	14.9	15.5	14.3	14.6	14.3
90°	27.6	27.2	26.8	26.4	26.0	25.2	23.9	22.7	21.5	20.3	18.6
92.5°	25.4	25.3	25.3	25.2	25.1	24.4	23.2	21.9	20.8	19.5	17.9
95°	26.7	26.5	26.3	26.1	25.9	25.2	23.9	22.7	21.5	20.3	20.0
97.5°	25.7	25.6	25.3	25.2	25.0	24.8	24.6	24.6	24.4	24.3	47.1
100°	25.7	25.6	25.3	25.2	25.0	26.6	30.1	33.5	37.0	40.5	68.8
102.5°	26.5	26.5	26.5	26.4	26.4	45.1	82.6	120.1	157.6	195.1	198.8
105°	262.4	269.7	277.0	284.4	291.8	294.5	292.7	290.9	289.1	287.2	286.1
107.5°	365.6	364.8	364.1	363.3	362.5	361.6	360.8	359.9	358.9	358.1	356.6
110°	410.5	410.0	409.3	408.7	408.1	407.6	407.2	406.8	406.3	405.9	404.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.4	454.7	453.9	453.1	452.3	452.0	452.1	452.2	452.3	452.3	451.8
115°	521.0	521.0	521.0	521.0	521.0	520.8	520.4	520.0	519.6	519.1	519.4
117.5°	587.6	587.7	587.8	587.9	588.0	588.0	588.1	588.2	588.3	588.4	588.0
120°	629.6	630.0	630.4	630.8	631.2	631.2	630.8	630.4	630.0	629.6	629.8
122.5°	670.8	671.2	671.7	672.1	672.5	672.6	672.3	672.1	671.8	671.6	671.3
125°	732.7	732.5	732.3	732.1	731.9	731.5	730.9	730.2	729.6	729.0	729.4
127.5°	787.0	787.2	787.3	787.5	787.7	787.8	787.9	788.1	788.1	788.3	787.3
130°	823.8	823.8	823.8	823.8	823.8	823.7	823.6	823.3	823.1	822.9	822.3
132.5°	857.7	857.9	858.0	858.2	858.3	858.3	858.2	857.9	857.7	857.5	856.7
135°	908.5	908.1	907.7	907.3	906.9	906.5	906.0	905.6	905.2	904.8	904.0
137.5°	952.0	952.0	952.2	952.4	952.4	952.3	951.8	951.4	950.9	950.5	949.6
140°	982.1	981.9	981.8	981.5	981.4	981.0	980.3	979.7	979.1	978.5	978.0
142.5°	1007.2	1007.2	1007.1	1007.1	1007.0	1006.8	1006.3	1005.9	1005.4	1005.0	1004.7
145°	1045.7	1045.3	1044.8	1044.4	1044.0	1043.7	1043.5	1043.3	1043.1	1042.9	1042.9
147.5°	1077.5	1077.3	1077.1	1076.9	1076.7	1076.5	1076.3	1076.2	1076.0	1075.9	1076.0
150°	1098.1	1098.0	1097.7	1097.5	1097.3	1097.2	1097.2	1097.2	1097.2	1097.2	1097.4
152.5°	1115.8	1115.9	1116.0	1116.2	1116.3	1116.2	1115.9	1115.6	1115.2	1114.9	1115.2
155°	1139.6	1140.2	1140.7	1141.4	1142.0	1141.9	1141.1	1140.3	1139.5	1138.6	1139.2
157.5°	1159.4	1160.5	1161.6	1162.6	1163.7	1163.7	1162.6	1161.6	1160.5	1159.4	1160.2
160°	1172.7	1173.9	1175.1	1176.4	1177.6	1177.6	1176.4	1175.1	1173.9	1172.7	1172.9
162.5°	1183.0	1184.4	1185.8	1187.2	1188.6	1188.7	1187.4	1186.2	1184.9	1183.8	1183.9
165°	1197.5	1199.4	1201.2	1203.1	1204.9	1205.0	1203.4	1201.7	1200.1	1198.5	1198.5
167.5°	1208.4	1210.5	1212.5	1214.6	1216.6	1216.7	1214.9	1213.1	1211.3	1209.5	1209.7
170°	1215.0	1217.1	1219.1	1221.1	1223.2	1223.4	1221.8	1220.1	1218.5	1216.9	1216.6
172.5°	1218.7	1220.9	1223.1	1225.3	1227.6	1227.8	1226.2	1224.6	1222.9	1221.3	1221.1
175°	1223.3	1225.7	1228.2	1230.7	1233.1	1233.4	1231.6	1229.8	1227.9	1226.1	1225.9
177.5°	1226.3	1228.2	1230.2	1232.2	1234.1	1234.5	1233.1	1231.8	1230.5	1229.2	1228.9
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1400.4	1394.3	1391.2	1384.2	1375.9	1371.5	1367.5	1361.8	1354.4	1346.6	1340.8
5°	1471.5	1458.3	1441.9	1422.2	1404.7	1387.7	1372.9	1358.1	1341.2	1323.7	1306.2
7.5°	1544.4	1518.6	1490.6	1458.3	1427.0	1398.4	1372.1	1346.9	1318.3	1292.8	1269.6
10°	1595.3	1560.2	1521.3	1480.3	1439.2	1403.6	1368.6	1336.8	1301.7	1270.5	1244.2
12.5°	1636.5	1595.3	1548.5	1497.4	1448.0	1404.9	1364.6	1323.2	1283.3	1249.5	1214.4
15°	1704.8	1648.4	1585.4	1524.1	1460.0	1401.4	1347.2	1299.0	1253.5	1205.9	1172.5
17.5°	1751.8	1684.9	1608.3	1534.6	1458.9	1389.8	1327.2	1269.9	1217.4	1168.8	1129.0
20°	1779.8	1705.9	1621.0	1537.2	1452.3	1378.4	1311.1	1247.5	1193.3	1140.7	1099.6
22.5°	1795.6	1713.8	1621.0	1533.3	1445.3	1365.2	1291.3	1225.2	1166.2	1113.6	1068.1
25°	1800.6	1713.0	1618.3	1517.5	1421.1	1336.3	1259.6	1187.8	1122.1	1069.5	1021.4
27.5°	1793.7	1690.4	1593.4	1490.0	1390.6	1301.1	1220.6	1145.3	1079.4	1023.0	973.6
30°	1783.1	1672.5	1568.4	1461.1	1360.3	1274.4	1189.5	1117.2	1048.7	990.1	940.3
32.5°	1760.3	1650.6	1538.7	1428.7	1326.6	1238.0	1157.5	1084.7	1017.6	957.7	904.8
35°	1715.2	1604.0	1482.5	1369.7	1269.4	1177.4	1101.8	1031.7	967.7	903.6	847.7
37.5°	1655.7	1542.1	1421.3	1297.7	1197.4	1110.5	1041.2	975.3	912.8	854.3	792.4
40°	1599.7	1496.1	1371.3	1248.6	1145.7	1061.8	997.8	938.1	875.1	817.1	755.2
42.5°	1531.8	1443.6	1317.4	1194.3	1092.7	1011.9	952.2	893.8	836.5	780.3	715.7
45°	1418.4	1351.5	1233.3	1115.0	1012.6	932.6	877.9	826.4	776.0	722.3	661.6
47.5°	1288.5	1243.3	1141.1	1020.0	925.3	853.3	800.4	758.4	715.7	662.1	608.8
50°	1198.3	1169.2	1070.6	960.0	869.7	803.4	749.2	709.7	674.1	622.7	575.0
52.5°	1101.8	1086.4	1003.1	897.4	810.1	745.1	698.8	663.3	627.2	584.6	540.0
55°	955.1	963.3	892.6	801.2	719.1	664.3	622.1	592.6	561.9	525.8	491.2
57.5°	805.0	835.0	787.6	707.3	630.3	579.7	548.0	523.1	497.3	467.4	437.9
60°	715.2	740.4	713.6	642.9	575.6	528.5	498.9	479.7	454.0	426.6	404.2
62.5°	627.6	654.5	638.7	581.6	519.0	478.6	452.5	434.6	415.4	391.6	368.2
65°	517.5	535.0	527.4	488.0	443.6	409.1	385.0	371.9	354.3	336.8	316.0
67.5°	396.4	430.2	425.7	404.8	366.5	339.5	323.8	312.1	296.2	283.1	269.0
70°	325.8	357.0	356.5	339.5	318.7	293.5	282.6	272.7	258.5	245.9	234.4
72.5°	266.7	295.3	299.5	286.5	272.3	253.3	242.7	235.9	222.1	213.5	204.1
75°	186.7	207.6	213.0	213.0	206.4	196.6	187.3	182.9	173.1	165.4	159.9
77.5°	122.5	135.6	144.2	146.1	147.1	143.8	136.2	133.1	125.5	122.8	117.6
80°	86.5	95.3	105.1	108.4	111.1	110.1	106.8	104.6	97.5	94.7	92.5
82.5°	59.8	64.6	72.7	79.9	79.2	82.1	79.2	77.5	72.1	71.1	68.9
85°	31.2	31.8	32.9	37.8	40.6	41.6	42.1	41.0	39.5	39.5	35.6
87.5°	13.9	13.2	13.7	13.3	13.3	14.6	15.4	15.4	14.6	13.7	12.8
90°	17.0	15.4	13.7	11.7	9.5	7.3	5.0	2.8	5.0	7.3	9.5
92.5°	16.2	14.6	13.0	12.1	12.0	11.9	11.7	11.6	11.7	11.9	12.0
95°	19.8	19.6	19.4	22.8	29.8	36.7	43.6	50.6	43.6	36.7	29.8
97.5°	69.9	92.8	115.6	124.8	120.5	116.2	111.9	107.5	111.9	116.2	120.5
100°	97.0	125.2	153.4	165.7	162.0	158.4	154.6	151.0	154.6	158.4	162.0
102.5°	202.5	206.2	209.8	210.3	207.6	204.9	202.2	199.6	202.2	204.9	207.6
105°	285.1	284.2	283.1	281.9	280.7	279.5	278.3	277.0	278.3	279.5	280.7
107.5°	355.3	353.9	352.5	351.5	350.9	350.3	349.7	349.0	349.7	350.3	350.9
110°	403.5	402.3	401.0	400.1	399.5	398.9	398.2	397.7	398.2	398.9	399.5



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	451.1	450.6	450.0	449.2	448.1	446.9	445.9	444.8	445.9	446.9	448.1
115°	519.6	519.8	520.0	519.8	519.1	518.6	517.9	517.3	517.9	518.6	519.1
117.5°	587.5	587.0	586.5	585.9	585.1	584.3	583.4	582.7	583.4	584.3	585.1
120°	630.0	630.3	630.4	630.1	629.3	628.5	627.6	626.9	627.6	628.5	629.3
122.5°	671.0	670.7	670.4	670.0	669.6	669.1	668.6	668.0	668.6	669.1	669.6
125°	729.8	730.2	730.6	730.5	729.6	728.8	728.0	727.1	728.0	728.8	729.6
127.5°	786.4	785.4	784.5	783.9	783.8	783.5	783.3	783.2	783.3	783.5	783.8
130°	821.7	821.1	820.5	820.1	819.8	819.7	819.4	819.2	819.4	819.7	819.8
132.5°	856.0	855.2	854.4	853.8	853.5	853.1	852.7	852.4	852.7	853.1	853.5
135°	903.2	902.4	901.6	901.3	901.4	901.7	901.9	902.1	901.9	901.7	901.4
137.5°	948.7	947.8	946.9	946.4	946.3	946.3	946.2	946.1	946.2	946.3	946.3
140°	977.6	977.2	976.8	976.4	976.0	975.6	975.2	974.8	975.2	975.6	976.0
142.5°	1004.5	1004.2	1004.0	1003.5	1002.7	1002.0	1001.3	1000.5	1001.3	1002.0	1002.7
145°	1042.9	1042.9	1042.9	1042.6	1042.0	1041.4	1040.8	1040.1	1040.8	1041.4	1042.0
147.5°	1076.3	1076.5	1076.7	1076.2	1075.1	1073.9	1072.8	1071.6	1072.8	1073.9	1075.1
150°	1097.6	1097.8	1098.0	1097.7	1096.9	1096.1	1095.3	1094.5	1095.3	1096.1	1096.9
152.5°	1115.6	1116.0	1116.3	1116.2	1115.6	1114.9	1114.3	1113.6	1114.3	1114.9	1115.6
155°	1139.9	1140.5	1141.1	1141.3	1141.1	1140.9	1140.7	1140.5	1140.7	1140.9	1141.1
157.5°	1160.9	1161.5	1162.2	1162.6	1162.8	1162.8	1163.0	1163.1	1163.0	1162.8	1162.8
160°	1173.1	1173.3	1173.5	1173.9	1174.6	1175.1	1175.8	1176.4	1175.8	1175.1	1174.6
162.5°	1184.2	1184.3	1184.6	1185.0	1185.8	1186.6	1187.4	1188.1	1187.4	1186.6	1185.8
165°	1198.5	1198.5	1198.5	1199.0	1200.0	1201.0	1202.1	1203.1	1202.1	1201.0	1200.0
167.5°	1209.7	1209.9	1210.0	1210.6	1211.6	1212.8	1213.8	1214.8	1213.8	1212.8	1211.6
170°	1216.5	1216.2	1216.1	1216.6	1217.8	1219.0	1220.3	1221.5	1220.3	1219.0	1217.8
172.5°	1220.9	1220.7	1220.4	1221.0	1222.2	1223.4	1224.6	1225.9	1224.6	1223.4	1222.2
175°	1225.7	1225.4	1225.3	1225.7	1227.0	1228.2	1229.5	1230.7	1229.5	1228.2	1227.0
177.5°	1228.5	1228.2	1227.9	1228.3	1229.5	1230.6	1231.8	1232.9	1231.8	1230.6	1229.5
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1334.7	1330.3	1324.6	1318.0	1310.2	1303.1	1300.1	1302.7	1304.0	1300.5	1300.1
5°	1294.1	1280.4	1269.4	1253.0	1239.8	1228.9	1221.2	1218.0	1219.0	1210.3	1208.1
7.5°	1248.4	1232.2	1214.3	1194.7	1176.5	1160.5	1152.0	1147.4	1138.1	1134.2	1127.5
10°	1219.0	1197.1	1179.6	1156.6	1135.8	1116.7	1107.3	1099.6	1090.4	1086.0	1076.7
12.5°	1188.8	1163.4	1144.1	1120.2	1099.0	1075.9	1067.0	1052.8	1038.2	1029.0	1017.1
15°	1146.2	1115.6	1092.0	1063.5	1038.3	1012.0	988.5	962.2	952.4	931.5	919.5
17.5°	1096.4	1065.2	1036.1	997.9	959.0	926.4	901.3	876.1	861.0	847.7	841.6
20°	1063.5	1035.1	994.5	950.1	906.9	870.8	850.5	834.1	817.6	808.3	801.8
22.5°	1032.4	996.0	949.0	901.1	857.9	829.6	812.4	795.5	782.1	773.2	764.5
25°	980.2	932.6	882.8	828.1	798.4	773.8	755.2	741.5	733.3	721.8	717.4
27.5°	926.7	869.0	814.0	777.2	746.4	723.9	707.7	697.4	687.0	679.6	673.9
30°	885.5	827.0	777.7	742.6	711.4	692.8	679.6	667.6	659.3	653.3	649.0
32.5°	844.8	786.2	744.8	707.1	682.5	664.3	650.3	641.3	634.9	627.0	624.4
35°	785.8	733.8	697.7	663.8	638.6	622.1	611.2	601.8	596.4	594.2	592.6
37.5°	729.2	686.7	647.8	620.0	597.5	584.6	571.6	567.0	563.3	559.4	561.1
40°	693.3	653.3	618.9	589.2	571.2	557.0	549.3	543.8	540.5	540.5	540.5
42.5°	662.2	623.1	589.5	563.0	544.9	532.8	524.3	519.7	518.6	518.2	520.8
45°	613.9	577.7	543.8	521.9	506.6	494.5	489.6	485.8	485.8	488.0	488.5
47.5°	566.0	532.2	504.9	480.4	466.4	458.8	454.6	452.6	452.8	455.0	457.5
50°	536.7	503.3	476.4	454.6	441.4	434.3	430.5	429.4	430.5	430.5	434.3
52.5°	504.7	474.8	448.4	430.0	415.1	408.4	406.3	404.8	405.4	407.3	408.8
55°	457.8	431.0	405.8	388.2	377.3	373.0	368.0	368.5	367.5	368.5	368.5
57.5°	410.8	386.7	363.3	349.4	339.8	333.4	328.0	329.5	328.0	327.7	326.9
60°	380.6	354.3	335.7	323.1	312.1	306.7	301.7	302.9	301.2	300.1	297.9
62.5°	347.8	325.8	308.1	296.0	287.2	280.8	275.9	274.8	271.0	267.3	262.4
65°	300.1	282.0	266.2	254.7	246.4	241.5	237.7	234.4	226.2	217.4	213.0
67.5°	253.8	240.7	225.9	216.2	209.5	203.0	195.7	190.1	182.4	177.7	174.9
70°	223.9	211.4	198.8	189.5	182.4	176.3	168.1	164.3	158.8	156.6	153.9
72.5°	195.5	183.8	172.1	163.7	156.1	151.4	144.9	141.1	138.6	137.8	135.1
75°	152.3	142.9	134.2	126.5	120.5	117.2	114.5	111.7	110.6	105.7	103.0
77.5°	111.1	105.0	99.4	94.0	89.7	87.5	82.2	79.1	77.2	74.9	74.4
80°	86.5	82.1	76.7	73.4	67.3	65.2	63.0	62.4	61.9	61.3	60.8
82.5°	65.0	60.7	55.2	53.2	51.6	50.3	49.0	48.4	47.8	48.2	48.1
85°	32.9	30.7	30.7	30.1	29.5	29.0	28.4	28.4	28.0	28.4	28.0
87.5°	13.3	13.2	13.5	13.1	13.8	14.1	13.9	14.2	14.9	14.3	14.4
90°	11.7	13.7	15.4	17.0	18.6	20.3	21.5	22.7	23.9	25.2	26.0
92.5°	12.1	13.0	14.6	16.2	17.9	19.5	20.8	21.9	23.2	24.4	25.1
95°	22.8	19.4	19.6	19.8	20.0	20.3	21.5	22.7	23.9	25.2	25.9
97.5°	124.8	115.6	92.8	69.9	47.1	24.3	24.4	24.6	24.6	24.8	25.0
100°	165.7	153.4	125.2	97.0	68.8	40.5	37.0	33.5	30.1	26.6	25.0
102.5°	210.3	209.8	206.2	202.5	198.8	195.1	157.6	120.1	82.6	45.1	26.4
105°	281.9	283.1	284.2	285.1	286.1	287.2	289.1	290.9	292.7	294.5	291.8
107.5°	351.5	352.5	353.9	355.3	356.6	358.1	358.9	359.9	360.8	361.6	362.5
110°	400.1	401.0	402.3	403.5	404.7	405.9	406.3	406.8	407.2	407.6	408.1



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	449.2	450.0	450.6	451.1	451.8	452.3	452.3	452.2	452.1	452.0	452.3
115°	519.8	520.0	519.8	519.6	519.4	519.1	519.6	520.0	520.4	520.8	521.0
117.5°	585.9	586.5	587.0	587.5	588.0	588.4	588.3	588.2	588.1	588.0	588.0
120°	630.1	630.4	630.3	630.0	629.8	629.6	630.0	630.4	630.8	631.2	631.2
122.5°	670.0	670.4	670.7	671.0	671.3	671.6	671.8	672.1	672.3	672.6	672.5
125°	730.5	730.6	730.2	729.8	729.4	729.0	729.6	730.2	730.9	731.5	731.9
127.5°	783.9	784.5	785.4	786.4	787.3	788.3	788.1	788.1	787.9	787.8	787.7
130°	820.1	820.5	821.1	821.7	822.3	822.9	823.1	823.3	823.6	823.7	823.8
132.5°	853.8	854.4	855.2	856.0	856.7	857.5	857.7	857.9	858.2	858.3	858.3
135°	901.3	901.6	902.4	903.2	904.0	904.8	905.2	905.6	906.0	906.5	906.9
137.5°	946.4	946.9	947.8	948.7	949.6	950.5	950.9	951.4	951.8	952.3	952.4
140°	976.4	976.8	977.2	977.6	978.0	978.5	979.1	979.7	980.3	981.0	981.4
142.5°	1003.5	1004.0	1004.2	1004.5	1004.7	1005.0	1005.4	1005.9	1006.3	1006.8	1007.0
145°	1042.6	1042.9	1042.9	1042.9	1042.9	1042.9	1043.1	1043.3	1043.5	1043.7	1044.0
147.5°	1076.2	1076.7	1076.5	1076.3	1076.0	1075.9	1076.0	1076.2	1076.3	1076.5	1076.7
150°	1097.7	1098.0	1097.8	1097.6	1097.4	1097.2	1097.2	1097.2	1097.2	1097.2	1097.3
152.5°	1116.2	1116.3	1116.0	1115.6	1115.2	1114.9	1115.2	1115.6	1115.9	1116.2	1116.3
155°	1141.3	1141.1	1140.5	1139.9	1139.2	1138.6	1139.5	1140.3	1141.1	1141.9	1142.0
157.5°	1162.6	1162.2	1161.5	1160.9	1160.2	1159.4	1160.5	1161.6	1162.6	1163.7	1163.7
160°	1173.9	1173.5	1173.3	1173.1	1172.9	1172.7	1173.9	1175.1	1176.4	1177.6	1177.6
162.5°	1185.0	1184.6	1184.3	1184.2	1183.9	1183.8	1184.9	1186.2	1187.4	1188.7	1188.6
165°	1199.0	1198.5	1198.5	1198.5	1198.5	1198.5	1200.1	1201.7	1203.4	1205.0	1204.9
167.5°	1210.6	1210.0	1209.9	1209.7	1209.7	1209.5	1211.3	1213.1	1214.9	1216.7	1216.6
170°	1216.6	1216.1	1216.2	1216.5	1216.6	1216.9	1218.5	1220.1	1221.8	1223.4	1223.2
172.5°	1221.0	1220.4	1220.7	1220.9	1221.1	1221.3	1222.9	1224.6	1226.2	1227.8	1227.6
175°	1225.7	1225.3	1225.4	1225.7	1225.9	1226.1	1227.9	1229.8	1231.6	1233.4	1233.1
177.5°	1228.3	1227.9	1228.2	1228.5	1228.9	1229.2	1230.5	1231.8	1233.1	1234.5	1234.1
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1297.4	1298.3	1295.3	1294.4	1295.3	1298.3	1297.4	1300.1	1300.5	1304.0	1302.7
5°	1203.7	1202.6	1199.8	1200.4	1199.8	1202.6	1203.7	1208.1	1210.3	1219.0	1218.0
7.5°	1123.6	1119.3	1120.5	1116.1	1120.5	1119.3	1123.6	1127.5	1134.2	1138.1	1147.4
10°	1074.4	1068.4	1063.5	1059.1	1063.5	1068.4	1074.4	1076.7	1086.0	1090.4	1099.6
12.5°	1007.4	1002.3	995.6	997.0	995.6	1002.3	1007.4	1017.1	1029.0	1038.2	1052.8
15°	912.4	904.1	891.0	892.6	891.0	904.1	912.4	919.5	931.5	952.4	962.2
17.5°	831.9	831.9	825.9	827.4	825.9	831.9	831.9	841.6	847.7	861.0	876.1
20°	790.3	786.4	787.0	785.3	787.0	786.4	790.3	801.8	808.3	817.6	834.1
22.5°	761.4	756.6	752.8	749.4	752.8	756.6	761.4	764.5	773.2	782.1	795.5
25°	712.5	709.2	704.3	703.1	704.3	709.2	712.5	717.4	721.8	733.3	741.5
27.5°	669.6	668.9	666.9	664.4	666.9	668.9	669.6	673.9	679.6	687.0	697.4
30°	644.6	643.5	642.4	640.7	642.4	643.5	644.6	649.0	653.3	659.3	667.6
32.5°	622.3	621.5	620.4	620.6	620.4	621.5	622.3	624.4	627.0	634.9	641.3
35°	590.3	589.8	588.7	588.2	588.7	589.8	590.3	592.6	594.2	596.4	601.8
37.5°	560.5	562.0	561.3	561.2	561.3	562.0	560.5	561.1	559.4	563.3	567.0
40°	540.0	540.5	541.6	541.1	541.6	540.5	540.0	540.5	540.5	540.5	543.8
42.5°	522.9	523.0	524.5	522.7	524.5	523.0	522.9	520.8	518.2	518.6	519.7
45°	492.3	495.6	495.0	495.0	495.0	495.6	492.3	488.5	488.0	485.8	485.8
47.5°	458.9	461.8	462.6	462.4	462.6	461.8	458.9	457.5	455.0	452.8	452.6
50°	437.0	435.9	437.6	437.0	437.6	435.9	437.0	434.3	430.5	430.5	429.4
52.5°	410.3	410.5	410.4	409.9	410.4	410.5	410.3	408.8	407.3	405.4	404.8
55°	369.1	369.6	368.5	369.1	368.5	369.6	369.1	368.5	368.5	367.5	368.5
57.5°	324.4	321.8	322.9	321.5	322.9	321.8	324.4	326.9	327.7	328.0	329.5
60°	292.5	288.0	286.9	284.8	286.9	288.0	292.5	297.9	300.1	301.2	302.9
62.5°	256.5	253.4	249.7	251.4	249.7	253.4	256.5	262.4	267.3	271.0	274.8
65°	208.7	206.4	204.8	207.0	204.8	206.4	208.7	213.0	217.4	226.2	234.4
67.5°	172.7	171.5	171.5	170.4	171.5	171.5	172.7	174.9	177.7	182.4	190.1
70°	153.9	152.3	152.3	151.1	152.3	152.3	153.9	153.9	156.6	158.8	164.3
72.5°	134.6	132.9	133.4	132.8	133.4	132.9	134.6	135.1	137.8	138.6	141.1
75°	99.7	97.0	97.0	97.5	97.0	97.0	99.7	103.0	105.7	110.6	111.7
77.5°	74.4	73.8	74.6	73.6	74.6	73.8	74.4	74.4	74.9	77.2	79.1
80°	60.8	60.2	59.7	61.3	59.7	60.2	60.8	60.8	61.3	61.9	62.4
82.5°	47.2	47.1	47.0	49.0	47.0	47.1	47.2	48.1	48.2	47.8	48.4
85°	28.4	27.4	28.4	27.4	28.4	27.4	28.4	28.0	28.4	28.0	28.4
87.5°	15.4	15.0	14.7	15.1	14.7	15.0	15.4	14.4	14.3	14.9	14.2
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.2	23.9	22.7
92.5°	25.2	25.3	25.3	25.4	25.3	25.3	25.2	25.1	24.4	23.2	21.9
95°	26.1	26.3	26.5	26.7	26.5	26.3	26.1	25.9	25.2	23.9	22.7
97.5°	25.2	25.3	25.6	25.7	25.6	25.3	25.2	25.0	24.8	24.6	24.6
100°	25.2	25.3	25.6	25.7	25.6	25.3	25.2	25.0	26.6	30.1	33.5
102.5°	26.4	26.5	26.5	26.5	26.5	26.5	26.4	26.4	45.1	82.6	120.1
105°	284.4	277.0	269.7	262.4	269.7	277.0	284.4	291.8	294.5	292.7	290.9
107.5°	363.3	364.1	364.8	365.6	364.8	364.1	363.3	362.5	361.6	360.8	359.9
110°	408.7	409.3	410.0	410.5	410.0	409.3	408.7	408.1	407.6	407.2	406.8



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	453.1	453.9	454.7	455.4	454.7	453.9	453.1	452.3	452.0	452.1	452.2
115°	521.0	521.0	521.0	521.0	521.0	521.0	521.0	521.0	520.8	520.4	520.0
117.5°	587.9	587.8	587.7	587.6	587.7	587.8	587.9	588.0	588.0	588.1	588.2
120°	630.8	630.4	630.0	629.6	630.0	630.4	630.8	631.2	631.2	630.8	630.4
122.5°	672.1	671.7	671.2	670.8	671.2	671.7	672.1	672.5	672.6	672.3	672.1
125°	732.1	732.3	732.5	732.7	732.5	732.3	732.1	731.9	731.5	730.9	730.2
127.5°	787.5	787.3	787.2	787.0	787.2	787.3	787.5	787.7	787.8	787.9	788.1
130°	823.8	823.8	823.8	823.8	823.8	823.8	823.8	823.8	823.7	823.6	823.3
132.5°	858.2	858.0	857.9	857.7	857.9	858.0	858.2	858.3	858.3	858.2	857.9
135°	907.3	907.7	908.1	908.5	908.1	907.7	907.3	906.9	906.5	906.0	905.6
137.5°	952.4	952.2	952.0	952.0	952.0	952.2	952.4	952.4	952.3	951.8	951.4
140°	981.5	981.8	981.9	982.1	981.9	981.8	981.5	981.4	981.0	980.3	979.7
142.5°	1007.1	1007.1	1007.2	1007.2	1007.2	1007.1	1007.1	1007.0	1006.8	1006.3	1005.9
145°	1044.4	1044.8	1045.3	1045.7	1045.3	1044.8	1044.4	1044.0	1043.7	1043.5	1043.3
147.5°	1076.9	1077.1	1077.3	1077.5	1077.3	1077.1	1076.9	1076.7	1076.5	1076.3	1076.2
150°	1097.5	1097.7	1098.0	1098.1	1098.0	1097.7	1097.5	1097.3	1097.2	1097.2	1097.2
152.5°	1116.2	1116.0	1115.9	1115.8	1115.9	1116.0	1116.2	1116.3	1116.2	1115.9	1115.6
155°	1141.4	1140.7	1140.2	1139.6	1140.2	1140.7	1141.4	1142.0	1141.9	1141.1	1140.3
157.5°	1162.6	1161.6	1160.5	1159.4	1160.5	1161.6	1162.6	1163.7	1163.7	1162.6	1161.6
160°	1176.4	1175.1	1173.9	1172.7	1173.9	1175.1	1176.4	1177.6	1177.6	1176.4	1175.1
162.5°	1187.2	1185.8	1184.4	1183.0	1184.4	1185.8	1187.2	1188.6	1188.7	1187.4	1186.2
165°	1203.1	1201.2	1199.4	1197.5	1199.4	1201.2	1203.1	1204.9	1205.0	1203.4	1201.7
167.5°	1214.6	1212.5	1210.5	1208.4	1210.5	1212.5	1214.6	1216.6	1216.7	1214.9	1213.1
170°	1221.1	1219.1	1217.1	1215.0	1217.1	1219.1	1221.1	1223.2	1223.4	1221.8	1220.1
172.5°	1225.3	1223.1	1220.9	1218.7	1220.9	1223.1	1225.3	1227.6	1227.8	1226.2	1224.6
175°	1230.7	1228.2	1225.7	1223.3	1225.7	1228.2	1230.7	1233.1	1233.4	1231.6	1229.8
177.5°	1232.2	1230.2	1228.2	1226.3	1228.2	1230.2	1232.2	1234.1	1234.5	1233.1	1231.8
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1300.1	1303.1	1310.2	1318.0	1324.6	1330.3	1334.7	1340.8	1346.6	1354.4	1361.8
5°	1221.2	1228.9	1239.8	1253.0	1269.4	1280.4	1294.1	1306.2	1323.7	1341.2	1358.1
7.5°	1152.0	1160.5	1176.5	1194.7	1214.3	1232.2	1248.4	1269.6	1292.8	1318.3	1346.9
10°	1107.3	1116.7	1135.8	1156.6	1179.6	1197.1	1219.0	1244.2	1270.5	1301.7	1336.8
12.5°	1067.0	1075.9	1099.0	1120.2	1144.1	1163.4	1188.8	1214.4	1249.5	1283.3	1323.2
15°	988.5	1012.0	1038.3	1063.5	1092.0	1115.6	1146.2	1172.5	1205.9	1253.5	1299.0
17.5°	901.3	926.4	959.0	997.9	1036.1	1065.2	1096.4	1129.0	1168.8	1217.4	1269.9
20°	850.5	870.8	906.9	950.1	994.5	1035.1	1063.5	1099.6	1140.7	1193.3	1247.5
22.5°	812.4	829.6	857.9	901.1	949.0	996.0	1032.4	1068.1	1113.6	1166.2	1225.2
25°	755.2	773.8	798.4	828.1	882.8	932.6	980.2	1021.4	1069.5	1122.1	1187.8
27.5°	707.7	723.9	746.4	777.2	814.0	869.0	926.7	973.6	1023.0	1079.4	1145.3
30°	679.6	692.8	711.4	742.6	777.7	827.0	885.5	940.3	990.1	1048.7	1117.2
32.5°	650.3	664.3	682.5	707.1	744.8	786.2	844.8	904.8	957.7	1017.6	1084.7
35°	611.2	622.1	638.6	663.8	697.7	733.8	785.8	847.7	903.6	967.7	1031.7
37.5°	571.6	584.6	597.5	620.0	647.8	686.7	729.2	792.4	854.3	912.8	975.3
40°	549.3	557.0	571.2	589.2	618.9	653.3	693.3	755.2	817.1	875.1	938.1
42.5°	524.3	532.8	544.9	563.0	589.5	623.1	662.2	715.7	780.3	836.5	893.8
45°	489.6	494.5	506.6	521.9	543.8	577.7	613.9	661.6	722.3	776.0	826.4
47.5°	454.6	458.8	466.4	480.4	504.9	532.2	566.0	608.8	662.1	715.7	758.4
50°	430.5	434.3	441.4	454.6	476.4	503.3	536.7	575.0	622.7	674.1	709.7
52.5°	406.3	408.4	415.1	430.0	448.4	474.8	504.7	540.0	584.6	627.2	663.3
55°	368.0	373.0	377.3	388.2	405.8	431.0	457.8	491.2	525.8	561.9	592.6
57.5°	328.0	333.4	339.8	349.4	363.3	386.7	410.8	437.9	467.4	497.3	523.1
60°	301.7	306.7	312.1	323.1	335.7	354.3	380.6	404.2	426.6	454.0	479.7
62.5°	275.9	280.8	287.2	296.0	308.1	325.8	347.8	368.2	391.6	415.4	434.6
65°	237.7	241.5	246.4	254.7	266.2	282.0	300.1	316.0	336.8	354.3	371.9
67.5°	195.7	203.0	209.5	216.2	225.9	240.7	253.8	269.0	283.1	296.2	312.1
70°	168.1	176.3	182.4	189.5	198.8	211.4	223.9	234.4	245.9	258.5	272.7
72.5°	144.9	151.4	156.1	163.7	172.1	183.8	195.5	204.1	213.5	222.1	235.9
75°	114.5	117.2	120.5	126.5	134.2	142.9	152.3	159.9	165.4	173.1	182.9
77.5°	82.2	87.5	89.7	94.0	99.4	105.0	111.1	117.6	122.8	125.5	133.1
80°	63.0	65.2	67.3	73.4	76.7	82.1	86.5	92.5	94.7	97.5	104.6
82.5°	49.0	50.3	51.6	53.2	55.2	60.7	65.0	68.9	71.1	72.1	77.5
85°	28.4	29.0	29.5	30.1	30.7	30.7	32.9	35.6	39.5	39.5	41.0
87.5°	13.9	14.1	13.8	13.1	13.5	13.2	13.3	12.8	13.7	14.6	15.4
90°	21.5	20.3	18.6	17.0	15.4	13.7	11.7	9.5	7.3	5.0	2.8
92.5°	20.8	19.5	17.9	16.2	14.6	13.0	12.1	12.0	11.9	11.7	11.6
95°	21.5	20.3	20.0	19.8	19.6	19.4	22.8	29.8	36.7	43.6	50.6
97.5°	24.4	24.3	47.1	69.9	92.8	115.6	124.8	120.5	116.2	111.9	107.5
100°	37.0	40.5	68.8	97.0	125.2	153.4	165.7	162.0	158.4	154.6	151.0
102.5°	157.6	195.1	198.8	202.5	206.2	209.8	210.3	207.6	204.9	202.2	199.6
105°	289.1	287.2	286.1	285.1	284.2	283.1	281.9	280.7	279.5	278.3	277.0
107.5°	358.9	358.1	356.6	355.3	353.9	352.5	351.5	350.9	350.3	349.7	349.0
110°	406.3	405.9	404.7	403.5	402.3	401.0	400.1	399.5	398.9	398.2	397.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.3	452.3	451.8	451.1	450.6	450.0	449.2	448.1	446.9	445.9	444.8
115°	519.6	519.1	519.4	519.6	519.8	520.0	519.8	519.1	518.6	517.9	517.3
117.5°	588.3	588.4	588.0	587.5	587.0	586.5	585.9	585.1	584.3	583.4	582.7
120°	630.0	629.6	629.8	630.0	630.3	630.4	630.1	629.3	628.5	627.6	626.9
122.5°	671.8	671.6	671.3	671.0	670.7	670.4	670.0	669.6	669.1	668.6	668.0
125°	729.6	729.0	729.4	729.8	730.2	730.6	730.5	729.6	728.8	728.0	727.1
127.5°	788.1	788.3	787.3	786.4	785.4	784.5	783.9	783.8	783.5	783.3	783.2
130°	823.1	822.9	822.3	821.7	821.1	820.5	820.1	819.8	819.7	819.4	819.2
132.5°	857.7	857.5	856.7	856.0	855.2	854.4	853.8	853.5	853.1	852.7	852.4
135°	905.2	904.8	904.0	903.2	902.4	901.6	901.3	901.4	901.7	901.9	902.1
137.5°	950.9	950.5	949.6	948.7	947.8	946.9	946.4	946.3	946.3	946.2	946.1
140°	979.1	978.5	978.0	977.6	977.2	976.8	976.4	976.0	975.6	975.2	974.8
142.5°	1005.4	1005.0	1004.7	1004.5	1004.2	1004.0	1003.5	1002.7	1002.0	1001.3	1000.5
145°	1043.1	1042.9	1042.9	1042.9	1042.9	1042.9	1042.6	1042.0	1041.4	1040.8	1040.1
147.5°	1076.0	1075.9	1076.0	1076.3	1076.5	1076.7	1076.2	1075.1	1073.9	1072.8	1071.6
150°	1097.2	1097.2	1097.4	1097.6	1097.8	1098.0	1097.7	1096.9	1096.1	1095.3	1094.5
152.5°	1115.2	1114.9	1115.2	1115.6	1116.0	1116.3	1116.2	1115.6	1114.9	1114.3	1113.6
155°	1139.5	1138.6	1139.2	1139.9	1140.5	1141.1	1141.3	1141.1	1140.9	1140.7	1140.5
157.5°	1160.5	1159.4	1160.2	1160.9	1161.5	1162.2	1162.6	1162.8	1162.8	1163.0	1163.1
160°	1173.9	1172.7	1172.9	1173.1	1173.3	1173.5	1173.9	1174.6	1175.1	1175.8	1176.4
162.5°	1184.9	1183.8	1183.9	1184.2	1184.3	1184.6	1185.0	1185.8	1186.6	1187.4	1188.1
165°	1200.1	1198.5	1198.5	1198.5	1198.5	1198.5	1199.0	1200.0	1201.0	1202.1	1203.1
167.5°	1211.3	1209.5	1209.7	1209.7	1209.9	1210.0	1210.6	1211.6	1212.8	1213.8	1214.8
170°	1218.5	1216.9	1216.6	1216.5	1216.2	1216.1	1216.6	1217.8	1219.0	1220.3	1221.5
172.5°	1222.9	1221.3	1221.1	1220.9	1220.7	1220.4	1221.0	1222.2	1223.4	1224.6	1225.9
175°	1227.9	1226.1	1225.9	1225.7	1225.4	1225.3	1225.7	1227.0	1228.2	1229.5	1230.7
177.5°	1230.5	1229.2	1228.9	1228.5	1228.2	1227.9	1228.3	1229.5	1230.6	1231.8	1232.9
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1367.5	1371.5	1375.9	1384.2	1391.2	1394.3	1400.4	1404.8	1403.5	1409.6	1420.1
5°	1372.9	1387.7	1404.7	1422.2	1441.9	1458.3	1471.5	1484.6	1495.1	1507.7	1526.3
7.5°	1372.1	1398.4	1427.0	1458.3	1490.6	1518.6	1544.4	1570.7	1594.0	1619.6	1653.0
10°	1368.6	1403.6	1439.2	1480.3	1521.3	1560.2	1595.3	1628.1	1659.4	1692.7	1735.0
12.5°	1364.6	1404.9	1448.0	1497.4	1548.5	1595.3	1636.5	1683.8	1722.8	1765.9	1814.7
15°	1347.2	1401.4	1460.0	1524.1	1585.4	1648.4	1704.8	1762.8	1817.0	1868.5	1929.9
17.5°	1327.2	1389.8	1458.9	1534.6	1608.3	1684.9	1751.8	1825.0	1880.4	1949.5	2006.4
20°	1311.1	1378.4	1452.3	1537.2	1621.0	1705.9	1779.8	1854.3	1916.8	1986.3	2058.6
22.5°	1291.3	1365.2	1445.3	1533.3	1621.0	1713.8	1795.6	1869.6	1946.9	2025.3	2099.8
25°	1259.6	1336.3	1421.1	1517.5	1618.3	1713.0	1800.6	1892.6	1975.9	2060.8	2127.6
27.5°	1220.6	1301.1	1390.6	1490.0	1593.4	1690.4	1793.7	1891.7	1975.5	2057.1	2115.4
30°	1189.5	1274.4	1360.3	1461.1	1568.4	1672.5	1783.1	1881.1	1969.3	2042.7	2075.5
32.5°	1157.5	1238.0	1326.6	1428.7	1538.7	1650.6	1760.3	1860.5	1942.1	1986.2	1987.0
35°	1101.8	1177.4	1269.4	1369.7	1482.5	1604.0	1715.2	1813.8	1863.6	1867.4	1813.8
37.5°	1041.2	1110.5	1197.4	1297.7	1421.3	1542.1	1655.7	1721.4	1738.1	1682.4	1583.1
40°	997.8	1061.8	1145.7	1248.6	1371.3	1496.1	1599.7	1647.8	1630.3	1539.9	1429.3
42.5°	952.2	1011.9	1092.7	1194.3	1317.4	1443.6	1531.8	1557.6	1511.2	1406.8	1277.3
45°	877.9	932.6	1012.6	1115.0	1233.3	1351.5	1418.4	1405.3	1328.0	1204.3	1059.1
47.5°	800.4	853.3	925.3	1020.0	1141.1	1243.3	1288.5	1248.9	1139.0	1002.8	884.8
50°	749.2	803.4	869.7	960.0	1070.6	1169.2	1198.3	1138.0	1015.9	884.9	776.6
52.5°	698.8	745.1	810.1	897.4	1003.1	1086.4	1101.8	1032.4	906.3	789.0	692.8
55°	622.1	664.3	719.1	801.2	892.6	963.3	955.1	865.9	751.4	651.2	575.6
57.5°	548.0	579.7	630.3	707.3	787.6	835.0	805.0	728.9	622.3	540.2	476.4
60°	498.9	528.5	575.6	642.9	713.6	740.4	715.2	632.6	548.2	473.2	419.5
62.5°	452.5	478.6	519.0	581.6	638.7	654.5	627.6	555.4	479.4	415.3	370.9
65°	385.0	409.1	443.6	488.0	527.4	535.0	517.5	443.6	386.1	332.4	301.7
67.5°	323.8	339.5	366.5	404.8	425.7	430.2	396.4	349.9	299.2	266.3	243.1
70°	282.6	293.5	318.7	339.5	356.5	357.0	325.8	288.6	249.7	222.9	205.9
72.5°	242.7	253.3	272.3	286.5	299.5	295.3	266.7	237.3	205.9	185.7	173.1
75°	187.3	196.6	206.4	213.0	213.0	207.6	186.7	164.9	146.8	134.8	130.9
77.5°	136.2	143.8	147.1	146.1	144.2	135.6	122.5	108.1	101.6	95.9	93.1
80°	106.8	110.1	111.1	108.4	105.1	95.3	86.5	80.5	74.5	72.3	71.2
82.5°	79.2	82.1	79.2	79.9	72.7	64.6	59.8	57.8	55.2	54.3	53.2
85°	42.1	41.6	40.6	37.8	32.9	31.8	31.2	30.7	29.5	30.1	29.0
87.5°	15.4	14.6	13.3	13.3	13.7	13.2	13.9	14.3	14.6	14.3	15.5
90°	5.0	7.3	9.5	11.7	13.7	15.4	17.0	18.6	20.3	21.5	22.7
92.5°	11.7	11.9	12.0	12.1	13.0	14.6	16.2	17.9	19.5	20.8	21.9
95°	43.6	36.7	29.8	22.8	19.4	19.6	19.8	20.0	20.3	21.5	22.7
97.5°	111.9	116.2	120.5	124.8	115.6	92.8	69.9	47.1	24.3	24.4	24.6
100°	154.6	158.4	162.0	165.7	153.4	125.2	97.0	68.8	40.5	37.0	33.5
102.5°	202.2	204.9	207.6	210.3	209.8	206.2	202.5	198.8	195.1	157.6	120.1
105°	278.3	279.5	280.7	281.9	283.1	284.2	285.1	286.1	287.2	289.1	290.9
107.5°	349.7	350.3	350.9	351.5	352.5	353.9	355.3	356.6	358.1	358.9	359.9
110°	398.2	398.9	399.5	400.1	401.0	402.3	403.5	404.7	405.9	406.3	406.8



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	445.9	446.9	448.1	449.2	450.0	450.6	451.1	451.8	452.3	452.3	452.2
115°	517.9	518.6	519.1	519.8	520.0	519.8	519.6	519.4	519.1	519.6	520.0
117.5°	583.4	584.3	585.1	585.9	586.5	587.0	587.5	588.0	588.4	588.3	588.2
120°	627.6	628.5	629.3	630.1	630.4	630.3	630.0	629.8	629.6	630.0	630.4
122.5°	668.6	669.1	669.6	670.0	670.4	670.7	671.0	671.3	671.6	671.8	672.1
125°	728.0	728.8	729.6	730.5	730.6	730.2	729.8	729.4	729.0	729.6	730.2
127.5°	783.3	783.5	783.8	783.9	784.5	785.4	786.4	787.3	788.3	788.1	788.1
130°	819.4	819.7	819.8	820.1	820.5	821.1	821.7	822.3	822.9	823.1	823.3
132.5°	852.7	853.1	853.5	853.8	854.4	855.2	856.0	856.7	857.5	857.7	857.9
135°	901.9	901.7	901.4	901.3	901.6	902.4	903.2	904.0	904.8	905.2	905.6
137.5°	946.2	946.3	946.3	946.4	946.9	947.8	948.7	949.6	950.5	950.9	951.4
140°	975.2	975.6	976.0	976.4	976.8	977.2	977.6	978.0	978.5	979.1	979.7
142.5°	1001.3	1002.0	1002.7	1003.5	1004.0	1004.2	1004.5	1004.7	1005.0	1005.4	1005.9
145°	1040.8	1041.4	1042.0	1042.6	1042.9	1042.9	1042.9	1042.9	1042.9	1043.1	1043.3
147.5°	1072.8	1073.9	1075.1	1076.2	1076.7	1076.5	1076.3	1076.0	1075.9	1076.0	1076.2
150°	1095.3	1096.1	1096.9	1097.7	1098.0	1097.8	1097.6	1097.4	1097.2	1097.2	1097.2
152.5°	1114.3	1114.9	1115.6	1116.2	1116.3	1116.0	1115.6	1115.2	1114.9	1115.2	1115.6
155°	1140.7	1140.9	1141.1	1141.3	1141.1	1140.5	1139.9	1139.2	1138.6	1139.5	1140.3
157.5°	1163.0	1162.8	1162.8	1162.6	1162.2	1161.5	1160.9	1160.2	1159.4	1160.5	1161.6
160°	1175.8	1175.1	1174.6	1173.9	1173.5	1173.3	1173.1	1172.9	1172.7	1173.9	1175.1
162.5°	1187.4	1186.6	1185.8	1185.0	1184.6	1184.3	1184.2	1183.9	1183.8	1184.9	1186.2
165°	1202.1	1201.0	1200.0	1199.0	1198.5	1198.5	1198.5	1198.5	1198.5	1200.1	1201.7
167.5°	1213.8	1212.8	1211.6	1210.6	1210.0	1209.9	1209.7	1209.7	1209.5	1211.3	1213.1
170°	1220.3	1219.0	1217.8	1216.6	1216.1	1216.2	1216.5	1216.6	1216.9	1218.5	1220.1
172.5°	1224.6	1223.4	1222.2	1221.0	1220.4	1220.7	1220.9	1221.1	1221.3	1222.9	1224.6
175°	1229.5	1228.2	1227.0	1225.7	1225.3	1225.4	1225.7	1225.9	1226.1	1227.9	1229.8
177.5°	1231.8	1230.6	1229.5	1228.3	1227.9	1228.2	1228.5	1228.9	1229.2	1230.5	1231.8
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2	1359.2
2.5°	1425.8	1427.6	1428.9	1433.3	1433.7	1437.7	1433.7
5°	1543.8	1551.5	1563.5	1575.6	1576.7	1584.3	1570.7
7.5°	1676.1	1693.8	1704.9	1724.4	1732.1	1736.9	1729.0
10°	1767.2	1783.7	1812.7	1826.9	1841.2	1843.3	1836.8
12.5°	1855.3	1881.4	1904.2	1931.2	1930.5	1949.8	1942.8
15°	1972.6	1999.5	2031.2	2061.3	2072.3	2072.3	2081.1
17.5°	2056.3	2105.5	2138.3	2161.9	2187.8	2192.3	2189.3
20°	2112.8	2165.9	2201.0	2231.7	2249.2	2254.1	2254.1
22.5°	2154.8	2200.0	2234.3	2261.8	2276.3	2282.1	2280.4
25°	2184.0	2222.9	2243.7	2251.9	2255.7	2254.6	2244.3
27.5°	2144.1	2142.4	2129.2	2104.0	2085.1	2073.6	2060.5
30°	2067.9	2039.4	2006.5	1970.4	1923.9	1888.2	1877.3
32.5°	1954.4	1890.5	1834.8	1774.6	1724.5	1688.9	1674.0
35°	1735.0	1633.6	1550.9	1478.6	1426.1	1393.2	1382.3
37.5°	1474.5	1376.4	1274.1	1204.0	1160.3	1127.1	1114.8
40°	1308.8	1202.1	1112.8	1047.1	1002.2	969.9	969.3
42.5°	1157.7	1055.7	971.8	924.4	876.0	854.6	854.5
45°	947.9	866.3	795.2	758.0	728.9	711.4	706.5
47.5°	784.9	717.4	669.9	640.3	616.6	605.5	598.3
50°	693.3	634.1	596.4	570.6	557.5	543.3	542.2
52.5°	617.1	569.3	539.9	519.0	502.3	493.8	494.0
55°	518.6	480.9	460.0	444.1	431.0	424.5	421.7
57.5°	436.9	408.5	393.4	378.8	373.3	368.1	366.7
60°	386.1	366.9	352.7	341.2	333.0	331.3	330.7
62.5°	344.0	324.0	314.1	305.2	299.2	296.7	295.7
65°	283.7	268.9	260.2	253.0	250.8	247.0	246.4
67.5°	228.7	219.8	214.0	209.1	206.1	205.9	205.9
70°	195.0	190.0	185.1	182.4	180.7	179.6	179.6
72.5°	166.0	162.4	158.4	156.9	156.6	155.5	155.1
75°	126.5	122.7	123.2	120.5	118.3	115.6	113.9
77.5°	89.7	87.0	86.4	86.1	84.2	83.9	84.8
80°	69.6	66.8	66.2	66.8	66.2	64.6	64.6
82.5°	52.9	50.6	50.1	49.7	49.2	49.7	48.9
85°	28.4	27.4	27.4	27.4	28.4	28.0	27.4
87.5°	14.9	14.7	15.3	14.9	15.0	14.7	15.1
90°	23.9	25.2	26.0	26.4	26.8	27.2	27.6
92.5°	23.2	24.4	25.1	25.2	25.3	25.3	25.4
95°	23.9	25.2	25.9	26.1	26.3	26.5	26.7
97.5°	24.6	24.8	25.0	25.2	25.3	25.6	25.7
100°	30.1	26.6	25.0	25.2	25.3	25.6	25.7
102.5°	82.6	45.1	26.4	26.4	26.5	26.5	26.5
105°	292.7	294.5	291.8	284.4	277.0	269.7	262.4
107.5°	360.8	361.6	362.5	363.3	364.1	364.8	365.6
110°	407.2	407.6	408.1	408.7	409.3	410.0	410.5



TEST NUMBER: P332979-927

CATALOG NUMBER: S124RDIP-S1020D1205U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	452.1	452.0	452.3	453.1	453.9	454.7	455.4
115°	520.4	520.8	521.0	521.0	521.0	521.0	521.0
117.5°	588.1	588.0	588.0	587.9	587.8	587.7	587.6
120°	630.8	631.2	631.2	630.8	630.4	630.0	629.6
122.5°	672.3	672.6	672.5	672.1	671.7	671.2	670.8
125°	730.9	731.5	731.9	732.1	732.3	732.5	732.7
127.5°	787.9	787.8	787.7	787.5	787.3	787.2	787.0
130°	823.6	823.7	823.8	823.8	823.8	823.8	823.8
132.5°	858.2	858.3	858.3	858.2	858.0	857.9	857.7
135°	906.0	906.5	906.9	907.3	907.7	908.1	908.5
137.5°	951.8	952.3	952.4	952.4	952.2	952.0	952.0
140°	980.3	981.0	981.4	981.5	981.8	981.9	982.1
142.5°	1006.3	1006.8	1007.0	1007.1	1007.1	1007.2	1007.2
145°	1043.5	1043.7	1044.0	1044.4	1044.8	1045.3	1045.7
147.5°	1076.3	1076.5	1076.7	1076.9	1077.1	1077.3	1077.5
150°	1097.2	1097.2	1097.3	1097.5	1097.7	1098.0	1098.1
152.5°	1115.9	1116.2	1116.3	1116.2	1116.0	1115.9	1115.8
155°	1141.1	1141.9	1142.0	1141.4	1140.7	1140.2	1139.6
157.5°	1162.6	1163.7	1163.7	1162.6	1161.6	1160.5	1159.4
160°	1176.4	1177.6	1177.6	1176.4	1175.1	1173.9	1172.7
162.5°	1187.4	1188.7	1188.6	1187.2	1185.8	1184.4	1183.0
165°	1203.4	1205.0	1204.9	1203.1	1201.2	1199.4	1197.5
167.5°	1214.9	1216.7	1216.6	1214.6	1212.5	1210.5	1208.4
170°	1221.8	1223.4	1223.2	1221.1	1219.1	1217.1	1215.0
172.5°	1226.2	1227.8	1227.6	1225.3	1223.1	1220.9	1218.7
175°	1231.6	1233.4	1233.1	1230.7	1228.2	1225.7	1223.3
177.5°	1233.1	1234.5	1234.1	1232.2	1230.2	1228.2	1226.3
180°	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7	1230.7

(END OF REPORT)