

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331918-940

Luminaire Tested: **S123DIP-S560D365U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331918-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D365U940-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3239.5 lumens  
Efficiency: N/A  
Efficacy: 117.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331918-940

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331918-940

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	33
5	70	58	50	44	66	55	48	42	49	43	38	43	39	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	32	28	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P331918-940

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.8	2.3
10°-20°	211.3	6.5
20°-30°	312.1	9.6
30°-40°	364.6	11.3
40°-50°	366.5	11.3
50°-60°	322.0	9.9
60°-70°	239.9	7.4
70°-80°	136.7	4.2
80°-90°	40.4	1.2
90°-100°	86.6	2.7
100°-110°	245.3	7.6
110°-120°	241.3	7.4
120°-130°	192.5	5.9
130°-140°	151.8	4.7
140°-150°	113.3	3.5
150°-160°	78.9	2.4
160°-170°	46.4	1.4
170°-180°	15.1	0.5
0°-30°	598.2	18.5
0°-40°	962.8	29.7
0°-60°	1651.3	51.0
0°-90°	2068.3	63.8
90°-120°	573.2	17.7
90°-150°	1030.7	31.8
90°-180°	1171.0	36.1
0°-180°	3239.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	1	4	8	9	9	3
95°	11	35	187	55	37	12
105°	37	54	253	443	401	39
115°	65	80	194	425	488	64
125°	90	106	181	328	384	80
135°	105	126	178	270	312	81
145°	120	138	176	221	244	75
155°	136	147	170	194	202	63
165°	149	153	163	173	176	42
175°	155	156	157	159	158	15
180°	156	156	156	156	156	



TEST NUMBER: P331918-940

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.4	14.1	13.8	13.6	13.5	13.3	13.4	13.5	13.6	13.6	13.4
90°	0.6	1.2	1.9	2.9	3.5	4.1	5.1	6.0	7.0	7.8	7.6
92.5°	3.9	5.8	8.5	10.9	13.6	18.2	26.5	40.0	53.3	48.4	36.6
95°	10.7	11.7	15.2	20.5	28.7	40.9	67.8	114.7	166.4	186.9	151.6
97.5°	18.3	18.5	21.3	25.9	34.1	47.3	72.9	125.8	212.0	289.6	309.8
100°	23.4	23.6	25.9	30.2	37.8	50.1	72.1	118.8	201.7	298.5	360.5
102.5°	28.6	29.2	31.1	35.3	42.1	53.4	73.2	112.7	186.5	282.0	363.0
105°	36.6	37.5	39.4	43.2	49.1	58.9	76.0	108.4	168.0	253.3	343.8
107.5°	45.0	45.9	47.8	51.5	57.1	66.2	81.1	108.1	156.1	228.0	310.1
110°	51.0	52.0	53.6	57.1	62.4	71.2	85.4	109.3	151.6	213.7	289.0



TEST NUMBER: P331918-940

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.6	57.5	59.1	62.6	67.9	76.5	89.7	111.9	149.0	204.0	270.5
115°	64.6	65.9	67.8	70.9	76.2	84.8	96.8	115.9	148.1	193.8	248.3
117.5°	72.6	74.0	75.6	78.6	84.5	92.4	104.2	121.4	148.6	187.7	234.9
120°	78.1	79.1	80.7	83.8	89.8	97.6	109.1	125.4	149.7	184.9	227.8
122.5°	82.9	83.9	85.4	88.9	94.6	103.0	114.0	129.2	151.4	183.2	222.0
125°	89.8	90.4	92.3	95.8	101.7	110.3	121.4	135.2	154.1	180.8	214.6
127.5°	95.1	95.9	98.4	101.8	108.4	117.0	127.6	140.1	157.1	179.8	208.0
130°	98.4	99.2	102.1	105.8	112.5	121.0	131.4	143.4	159.2	179.0	204.5
132.5°	100.9	102.0	105.1	109.7	116.3	124.6	134.6	146.4	160.7	178.7	201.3
135°	105.2	106.5	109.9	114.7	121.4	129.8	139.6	150.3	162.9	178.3	197.0
137.5°	109.4	110.8	114.1	119.1	125.7	133.6	143.0	153.2	164.4	177.6	193.2
140°	112.2	113.8	116.9	122.0	128.2	136.2	145.3	154.7	165.4	177.5	190.9
142.5°	115.2	116.5	119.9	124.5	130.8	138.1	147.0	156.2	166.2	176.9	189.0
145°	120.0	121.0	123.9	128.6	133.9	141.2	149.4	157.8	166.7	176.1	186.2
147.5°	125.0	125.6	128.3	132.4	137.6	143.7	151.2	158.9	166.7	175.0	183.6
150°	128.2	128.6	131.1	135.2	139.6	145.3	152.5	159.2	166.7	174.0	181.8
152.5°	131.5	131.6	134.1	137.7	141.6	147.0	153.3	159.6	165.9	172.7	179.8
155°	136.4	136.4	138.3	141.5	145.0	149.4	154.7	159.8	165.1	170.5	176.7
157.5°	140.4	140.6	142.1	144.9	147.8	151.2	155.5	160.1	164.1	168.5	173.3
160°	143.4	143.4	144.6	147.1	149.4	152.5	156.3	160.1	163.5	167.0	171.1
162.5°	145.6	145.6	146.7	148.6	150.6	153.3	156.6	159.8	162.6	165.5	168.8
165°	149.0	148.7	149.4	151.0	152.2	154.4	156.9	159.2	161.0	163.3	165.8
167.5°	151.6	151.2	151.6	152.8	153.6	155.1	156.9	158.6	159.5	161.0	162.8
170°	153.1	152.5	152.8	153.7	154.4	155.1	156.6	157.8	158.5	159.4	161.0
172.5°	154.2	153.7	153.8	154.5	154.9	155.2	156.6	157.7	157.7	158.2	159.3
175°	155.3	155.1	154.7	155.3	155.3	155.7	156.3	156.9	156.6	156.6	157.2
177.5°	156.0	155.7	155.4	155.7	155.7	155.7	156.0	156.4	156.0	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P331918-940

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	13.4	13.3	13.2	13.3	13.2	13.3	13.4	13.3
90°	7.8	8.2	8.5	9.1	8.8	9.1	9.5	9.1
92.5°	26.6	21.0	18.5	16.9	16.4	15.4	15.8	15.2
95°	113.4	76.9	60.2	48.9	42.9	40.0	37.8	36.6
97.5°	282.8	226.5	185.8	148.2	124.9	110.8	102.2	99.5
100°	371.5	346.0	309.2	264.4	232.6	209.6	197.2	197.6
102.5°	401.0	400.2	378.7	350.4	325.6	307.4	297.1	289.8
105°	409.7	441.1	447.1	439.0	424.5	412.5	402.4	400.8
107.5°	384.8	436.0	463.6	474.8	475.1	471.0	467.6	464.8
110°	361.1	419.1	458.8	480.9	489.7	492.2	491.6	491.0





TEST NUMBER: P331918-940

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	396.9	441.4	469.8	485.9	493.7	496.1	496.2
115°	306.6	361.4	407.8	442.1	465.7	479.6	485.9	487.5
117.5°	284.1	331.4	373.0	407.9	432.6	448.4	457.4	459.6
120°	272.2	314.8	352.6	384.4	409.3	427.0	434.5	436.4
122.5°	263.0	301.4	336.4	366.0	388.2	404.0	412.3	414.7
125°	250.5	284.9	315.1	340.4	360.5	374.3	382.3	384.4
127.5°	239.7	270.3	297.6	320.6	338.5	350.4	357.5	359.4
130°	232.8	261.3	286.8	308.2	324.9	336.3	342.9	345.4
132.5°	226.6	252.6	276.4	296.9	312.5	323.9	329.8	331.5
135°	218.0	240.4	260.9	278.8	294.4	303.8	309.4	311.7
137.5°	210.3	228.6	246.3	261.9	274.8	284.5	289.2	290.7
140°	205.8	221.9	236.9	250.5	262.5	271.3	276.3	276.1
142.5°	201.5	215.3	228.4	240.1	250.4	258.2	262.7	262.4
145°	196.4	206.7	216.8	226.0	233.8	240.4	243.0	243.6
147.5°	192.1	200.4	208.5	215.0	221.0	225.4	227.8	228.1
150°	189.0	196.4	203.0	208.9	213.7	217.1	219.0	219.0
152.5°	186.3	192.5	198.4	203.4	207.1	210.3	211.4	211.4
155°	182.2	187.2	191.9	195.6	198.5	201.1	201.7	202.0
157.5°	177.7	181.9	185.6	188.6	191.0	192.9	193.4	193.3
160°	175.2	178.7	181.8	184.0	186.2	188.2	188.2	187.8
162.5°	172.2	175.1	178.1	180.0	181.5	183.1	183.1	182.8
165°	168.3	170.1	172.4	174.0	175.2	176.5	176.1	176.1
167.5°	164.9	166.3	167.6	168.7	169.2	170.1	169.9	169.9
170°	162.6	163.5	164.8	165.4	165.8	166.4	166.0	166.0
172.5°	160.6	161.3	162.3	162.6	162.7	163.4	162.8	162.6
175°	157.8	158.2	158.8	158.8	158.8	159.2	158.8	158.5
177.5°	156.1	156.4	156.7	156.7	156.4	156.7	156.1	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7

(END OF REPORT)