

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331928-940

Luminaire Tested: **S123DIP-S560D805U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331928-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4991.7 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																												
1	96	92	88	85	88	84	81	78	70	68	65	56	55	53	44	43	42	36																												
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31																												
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26																												
4	74	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23																												
5	67	56	48	42	61	52	45	40	43	38	34	35	32	29	28	25	23	20																												
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	25	23	20	17																												
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16																												
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	21	18	16	14																												
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13																												
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7587	7587	7587	7587
5°	9048	7621	6753	7621
10°	11326	7582	6099	7582
15°	13891	7520	5678	7520
20°	16549	7425	5407	7425
25°	17570	7310	5346	7310
30°	15060	7225	5374	7225
35°	10474	7104	5430	7104
40°	7888	6962	5413	6962
45°	6550	6753	5345	6753
50°	5868	6325	5297	6325
55°	5485	5864	5230	5864
60°	5147	5382	5175	5382
65°	4834	4905	5010	4905
70°	4535	4365	4771	4365
75°	4059	3818	4375	3818
80°	3552	3137	3769	3137
85°	2791	2285	2532	2285



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	1.4
10°-20°	222.7	4.5
20°-30°	373.7	7.5
30°-40°	423.1	8.5
40°-50°	379.5	7.6
50°-60°	306.2	6.1
60°-70°	213.4	4.3
70°-80°	112.2	2.2
80°-90°	30.1	0.6
90°-100°	34.1	0.7
100°-110°	162.6	3.3
110°-120°	390.6	7.8
120°-130°	497.3	10.0
130°-140°	531.4	10.6
140°-150°	496.9	10.0
150°-160°	400.8	8.0
160°-170°	258.7	5.2
170°-180°	89.2	1.8
0°-30°	665.8	13.3
0°-40°	1088.9	21.8
0°-60°	1774.6	35.6
0°-90°	2130.2	42.7
90°-120°	587.3	11.8
90°-150°	2112.9	42.3
90°-180°	2862.0	57.3
0°-180°	4991.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	705	705	705	705	705	
5°	837	705	625	705	837	87
15°	1246	675	510	675	1246	360
25°	1479	616	450	616	1479	649
35°	797	541	413	541	797	518
45°	430	444	351	444	430	340
55°	292	312	279	312	292	262
65°	190	193	197	193	190	189
75°	98	92	105	92	98	105
85°	23	18	20	18	23	27
90°	21	1	21	1	21	11
95°	26	42	26	42	26	22
105°	31	208	31	208	31	70
115°	410	390	410	390	410	379
125°	560	549	560	549	560	501
135°	691	684	691	684	691	533
145°	797	789	797	789	797	497
155°	868	869	868	869	868	400
165°	915	917	915	917	915	258
175°	935	938	935	938	935	89
180°	938	938	938	938	938	



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	748.1	747.5	746.2	747.3	745.0	742.1	741.8	739.0	731.1	730.6	728.4
5°	837.4	834.6	834.4	834.0	829.2	822.7	810.4	809.4	793.0	784.8	774.9
7.5°	953.1	954.6	949.6	945.2	930.6	921.0	907.8	890.9	870.8	850.3	836.7
10°	1036.2	1047.4	1033.4	1023.9	1015.0	998.3	978.8	954.6	930.3	902.0	880.5
12.5°	1125.2	1130.8	1128.0	1118.9	1105.2	1079.7	1045.2	1018.5	996.1	949.0	929.9
15°	1246.5	1267.4	1254.1	1223.3	1224.1	1199.8	1154.7	1105.2	1078.9	1037.5	981.1
17.5°	1375.8	1378.4	1372.7	1347.1	1330.0	1296.7	1255.1	1207.6	1154.3	1104.4	1044.6
20°	1444.7	1442.6	1430.7	1417.3	1387.9	1362.0	1316.5	1263.6	1195.3	1146.1	1080.9
22.5°	1482.9	1479.4	1473.8	1462.7	1438.2	1410.3	1369.6	1311.7	1246.7	1178.9	1103.6
25°	1479.4	1483.9	1484.6	1481.5	1473.0	1456.3	1424.2	1378.0	1313.1	1226.1	1147.5
27.5°	1345.6	1351.8	1370.1	1386.3	1404.4	1422.8	1420.4	1397.5	1349.5	1274.3	1178.2
30°	1211.7	1198.0	1231.9	1274.5	1303.6	1354.8	1383.5	1385.2	1358.3	1293.7	1200.1
32.5°	1025.9	1041.0	1055.9	1108.4	1171.9	1229.4	1286.5	1332.5	1337.7	1294.8	1212.9
35°	797.1	815.9	843.2	870.6	938.9	997.6	1098.0	1185.4	1255.1	1264.3	1214.1
37.5°	642.3	651.7	668.9	696.2	740.9	810.7	888.3	998.8	1099.7	1174.8	1178.1
40°	561.4	564.2	583.6	604.5	640.7	698.0	768.1	865.8	986.7	1091.5	1135.2
42.5°	500.8	506.8	515.1	535.1	563.9	607.1	672.2	753.0	863.7	984.4	1069.9
45°	430.3	437.1	442.3	455.6	476.1	505.1	550.5	624.3	708.6	833.3	948.4
47.5°	383.7	384.2	388.1	398.1	412.1	433.9	466.0	513.4	590.8	691.9	810.1
50°	350.4	355.9	357.2	365.1	376.0	392.1	418.7	459.0	522.5	611.4	720.0
52.5°	326.9	328.5	332.3	338.0	347.6	360.1	383.2	414.7	464.6	540.3	640.2
55°	292.3	292.3	296.1	300.5	306.0	317.3	332.6	355.9	393.8	452.5	535.2
57.5°	260.4	262.1	264.7	266.1	270.7	278.2	291.1	308.7	337.0	382.2	447.9
60°	239.1	242.1	241.8	244.5	248.6	254.4	265.4	279.7	305.0	341.2	396.5
62.5°	220.5	220.3	220.3	223.5	227.6	233.1	240.2	252.6	274.1	306.2	353.3
65°	189.8	189.2	191.6	193.7	195.0	199.1	204.6	215.5	229.9	253.8	290.3
67.5°	162.7	160.7	162.0	162.7	165.1	168.3	173.3	180.1	191.5	210.7	238.3
70°	144.1	142.4	142.0	142.8	144.8	147.2	151.0	157.5	168.0	183.4	203.6
72.5°	125.0	123.9	123.8	125.3	126.3	127.8	130.5	136.4	144.8	156.3	175.1
75°	97.6	97.6	97.6	98.0	99.1	100.4	102.5	105.5	112.0	120.2	132.9
77.5°	73.2	73.1	72.8	72.7	74.2	74.8	75.3	78.1	81.8	87.3	96.5
80°	57.3	55.6	56.4	57.3	58.1	58.4	59.4	60.1	63.2	66.3	72.8
82.5°	42.6	41.2	41.3	42.9	43.1	43.3	44.4	45.4	46.5	49.3	52.8
85°	22.6	22.6	22.9	22.9	23.2	22.9	23.9	24.3	24.3	25.9	28.0
87.5°	12.4	11.8	11.9	12.2	11.9	12.0	12.2	12.3	12.5	12.7	12.5
90°	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0	17.4	16.8	14.7
92.5°	23.2	22.9	22.7	22.6	22.4	21.8	20.8	19.8	18.8	17.8	16.3
95°	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8	22.7	21.6	19.9
97.5°	28.7	28.5	28.4	28.3	28.1	27.4	26.1	25.0	23.7	22.5	33.6
100°	29.2	29.2	29.0	28.8	28.6	28.0	26.8	25.5	24.3	23.0	47.2
102.5°	29.9	29.5	29.2	29.0	28.7	30.5	34.3	38.2	42.0	45.8	72.2
105°	30.7	30.4	30.1	29.8	29.4	43.0	70.4	97.8	125.3	152.7	166.6
107.5°	96.3	117.0	137.7	158.4	179.0	199.4	219.5	239.6	259.8	279.8	277.6
110°	191.7	213.8	236.0	258.2	280.4	294.0	299.1	304.2	309.3	314.4	312.7



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.0	333.6	338.2	343.0	347.6	349.9	349.8	349.7	349.6	349.6	347.9
115°	409.9	409.3	408.7	408.0	407.4	406.4	404.8	403.2	401.7	400.2	398.8
117.5°	455.4	455.2	455.1	455.0	454.9	454.1	453.0	451.7	450.5	449.2	448.5
120°	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5	482.2	481.0	480.5
122.5°	517.3	517.2	517.0	516.9	516.7	516.3	515.4	514.5	513.7	512.8	512.2
125°	560.5	560.2	559.9	559.5	559.3	558.9	558.7	558.3	558.0	557.7	557.1
127.5°	602.1	602.4	602.7	603.0	603.2	603.2	602.7	602.2	601.7	601.2	600.5
130°	628.8	629.1	629.5	629.7	630.1	629.9	629.3	628.7	628.0	627.4	626.8
132.5°	653.4	653.8	654.2	654.7	655.1	655.0	654.3	653.7	653.2	652.6	652.0
135°	690.9	691.3	691.8	692.2	692.7	692.7	692.2	691.8	691.3	690.9	690.3
137.5°	726.1	726.5	726.7	727.1	727.4	727.2	726.4	725.7	725.0	724.2	723.8
140°	747.3	747.6	748.0	748.2	748.6	748.4	747.8	747.2	746.5	745.9	745.5
142.5°	766.9	767.3	767.7	768.1	768.6	768.6	768.0	767.6	767.0	766.6	766.1
145°	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0	795.8	795.4	795.1
147.5°	819.1	819.8	820.6	821.3	822.0	822.2	821.9	821.5	821.3	820.9	820.6
150°	835.9	836.3	836.8	837.2	837.8	837.8	837.5	837.1	836.9	836.6	836.2
152.5°	849.3	850.0	850.7	851.4	852.1	852.2	851.6	851.0	850.5	850.0	849.8
155°	867.9	868.9	869.8	870.8	871.6	871.7	870.9	870.2	869.4	868.6	868.4
157.5°	883.7	884.9	886.1	887.3	888.5	888.7	887.7	886.8	885.9	884.9	885.1
160°	893.8	894.8	895.9	897.0	898.0	898.1	897.2	896.3	895.4	894.4	894.6
162.5°	903.2	904.2	905.1	906.1	907.0	907.0	906.0	904.9	903.8	902.8	902.9
165°	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4	915.2	913.9	914.1
167.5°	922.8	924.1	925.3	926.6	927.8	927.8	926.6	925.3	924.1	922.8	922.8
170°	927.9	929.2	930.3	931.6	932.8	932.8	931.6	930.3	929.2	927.9	927.9
172.5°	930.7	932.0	933.4	934.8	936.1	936.2	935.0	933.7	932.5	931.2	931.1
175°	934.9	936.1	937.4	938.6	939.8	939.9	938.8	937.7	936.7	935.6	935.4
177.5°	936.1	937.4	938.6	939.9	941.1	941.2	940.2	939.2	938.3	937.2	937.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	726.7	724.6	722.4	718.5	715.2	710.6	709.3	707.7	702.8	698.3	695.1
5°	771.2	762.9	751.0	740.0	731.2	719.3	712.4	705.3	695.0	685.8	678.2
7.5°	817.6	801.5	782.9	762.9	744.1	726.0	711.5	698.6	684.2	670.6	660.0
10°	854.5	831.3	805.3	777.3	753.4	730.1	710.7	693.7	675.2	659.2	645.8
12.5°	896.5	862.1	826.3	792.3	764.0	731.8	708.3	686.5	665.7	646.3	631.3
15°	946.4	902.7	860.3	813.5	770.4	730.1	702.1	674.8	650.6	630.8	611.6
17.5°	991.7	942.2	886.4	829.5	777.6	729.8	690.5	659.7	629.4	605.1	586.0
20°	1017.4	961.0	897.9	838.7	781.4	728.1	685.1	648.2	615.5	589.8	568.3
22.5°	1039.6	973.6	908.2	845.1	781.1	723.7	675.0	637.0	601.5	576.4	553.6
25°	1062.5	983.6	918.0	843.9	772.5	713.1	658.4	615.5	579.9	550.5	527.0
27.5°	1082.2	982.9	905.1	825.4	759.0	699.5	641.1	594.9	557.2	525.3	501.4
30°	1095.3	984.3	891.7	812.8	745.9	684.4	627.7	581.3	541.6	509.2	486.7
32.5°	1103.5	983.5	879.4	795.3	725.1	670.7	613.2	565.2	524.4	492.6	470.8
35°	1108.2	977.4	858.3	759.2	691.6	638.6	590.5	540.6	497.9	468.2	443.6
37.5°	1098.7	964.8	833.7	724.3	650.3	598.2	557.7	515.2	474.4	441.7	420.4
40°	1083.6	956.6	814.5	699.8	621.9	571.7	537.3	495.5	455.2	424.2	404.4
42.5°	1055.0	940.0	793.5	672.4	592.4	542.2	510.4	475.6	437.5	408.3	388.5
45°	985.0	903.7	762.0	631.5	548.8	497.0	469.0	443.6	409.1	380.8	363.7
47.5°	887.8	849.1	716.3	588.3	503.4	453.4	424.3	403.9	378.7	355.9	339.5
50°	820.4	804.3	685.5	558.7	473.0	424.2	396.2	377.7	359.6	336.7	321.7
52.5°	742.4	752.3	649.3	528.2	442.1	394.1	367.7	353.1	336.7	317.9	304.8
55°	632.8	668.7	587.1	476.8	396.2	350.4	325.5	312.5	302.9	288.9	277.7
57.5°	530.2	575.8	519.7	423.8	351.0	311.6	287.7	273.5	267.3	260.0	251.2
60°	469.2	514.3	471.6	388.3	320.7	283.1	262.0	250.0	243.9	238.7	231.2
62.5°	414.9	460.5	424.6	352.2	290.9	256.1	237.6	226.0	221.1	218.5	212.0
65°	340.2	379.4	355.5	296.1	248.3	217.6	200.8	192.6	188.2	187.2	183.1
67.5°	276.9	306.7	289.4	245.6	207.9	181.4	167.2	160.2	156.9	156.5	153.4
70°	235.3	263.3	250.0	210.4	177.9	157.1	144.8	138.7	136.6	136.3	134.6
72.5°	203.0	222.6	212.0	179.0	153.9	135.0	125.9	119.5	117.2	117.7	116.5
75°	150.3	165.0	158.8	135.9	115.7	103.4	95.9	91.8	89.8	90.9	89.4
77.5°	108.2	117.4	111.9	96.0	83.6	74.7	69.2	66.7	64.8	64.7	64.1
80°	81.6	87.1	84.0	74.5	64.2	56.7	52.3	50.6	49.5	49.2	48.9
82.5°	58.1	62.8	59.1	52.6	45.7	41.1	38.6	36.4	35.6	35.8	35.5
85°	29.3	31.1	29.7	25.6	22.9	20.9	19.4	18.5	17.7	18.1	17.4
87.5°	12.7	12.5	11.3	9.8	9.0	7.8	7.6	6.7	6.4	6.8	6.8
90°	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7	2.2	3.8	5.4
92.5°	14.8	13.3	11.8	11.2	11.7	12.1	12.6	12.9	12.6	12.1	11.7
95°	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5	36.2	29.8	23.5
97.5°	44.8	55.9	67.1	74.1	77.0	79.8	82.7	85.4	82.7	79.8	77.0
100°	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8	120.9	124.0	127.1
102.5°	98.6	125.1	151.5	163.5	161.3	159.1	156.9	154.6	156.9	159.1	161.3
105°	180.6	194.5	208.5	214.5	212.9	211.2	209.5	207.8	209.5	211.2	212.9
107.5°	275.4	273.2	271.0	269.2	267.9	266.5	265.2	263.8	265.2	266.5	267.9
110°	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.1	302.4	303.6	304.9



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	346.2	344.5	342.7	341.3	340.2	339.1	338.0	336.9	338.0	339.1	340.2
115°	397.3	396.0	394.6	393.4	392.5	391.6	390.7	389.7	390.7	391.6	392.5
117.5°	447.8	447.1	446.4	445.4	444.3	443.2	442.0	440.9	442.0	443.2	444.3
120°	480.1	479.7	479.2	478.2	476.8	475.5	474.0	472.7	474.0	475.5	476.8
122.5°	511.7	511.0	510.4	509.6	508.5	507.3	506.1	505.0	506.1	507.3	508.5
125°	556.4	555.9	555.3	554.3	553.0	551.8	550.5	549.4	550.5	551.8	553.0
127.5°	599.8	599.0	598.2	597.3	596.0	594.8	593.5	592.3	593.5	594.8	596.0
130°	626.2	625.5	624.9	624.0	622.8	621.5	620.3	619.0	620.3	621.5	622.8
132.5°	651.5	651.0	650.5	649.7	648.5	647.2	646.0	644.7	646.0	647.2	648.5
135°	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9	684.8	685.7	686.7
137.5°	723.5	723.2	722.8	722.0	720.9	719.7	718.5	717.4	718.5	719.7	720.9
140°	745.0	744.6	744.0	743.4	742.4	741.5	740.6	739.7	740.6	741.5	742.4
142.5°	765.6	765.2	764.7	764.0	763.1	762.1	761.3	760.3	761.3	762.1	763.1
145°	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2	790.2	791.3	792.4
147.5°	820.3	820.0	819.7	819.2	818.5	817.8	817.1	816.4	817.1	817.8	818.5
150°	836.0	835.6	835.4	834.9	834.5	834.0	833.6	833.0	833.6	834.0	834.5
152.5°	849.5	849.4	849.2	849.0	848.8	848.6	848.4	848.1	848.4	848.6	848.8
155°	868.3	868.2	868.0	868.1	868.4	868.7	869.1	869.3	869.1	868.7	868.4
157.5°	885.3	885.4	885.6	885.6	885.6	885.7	885.7	885.7	885.7	885.7	885.6
160°	894.7	894.9	895.0	895.2	895.4	895.5	895.6	895.8	895.6	895.5	895.4
162.5°	903.1	903.2	903.4	903.7	904.1	904.5	904.9	905.3	904.9	904.5	904.1
165°	914.3	914.4	914.5	914.9	915.3	915.8	916.2	916.8	916.2	915.8	915.3
167.5°	922.8	922.8	922.8	923.2	923.8	924.4	925.1	925.7	925.1	924.4	923.8
170°	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7	930.1	929.4	928.8
172.5°	930.9	930.9	930.8	931.0	931.7	932.6	933.3	934.0	933.3	932.6	931.7
175°	935.2	935.0	935.0	935.2	936.0	936.8	937.5	938.3	937.5	936.8	936.0
177.5°	937.0	936.8	936.7	937.0	937.6	938.3	938.9	939.4	938.9	938.3	937.6
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	693.1	691.3	688.5	684.4	681.1	675.9	675.9	676.7	676.7	676.5	675.9
5°	672.1	667.0	660.8	653.7	646.1	638.6	637.3	634.5	632.5	631.2	629.5
7.5°	649.9	640.9	631.9	621.9	612.7	605.1	599.9	595.5	592.6	589.7	587.5
10°	634.9	623.6	613.1	602.4	590.8	581.6	575.8	571.7	568.6	565.9	564.5
12.5°	617.2	604.2	592.5	582.5	569.8	560.3	554.7	552.9	549.2	543.5	540.5
15°	591.2	579.3	565.3	549.8	543.7	532.1	525.6	522.5	520.5	516.0	514.7
17.5°	569.0	553.3	537.6	526.1	514.7	505.3	501.7	497.8	495.2	491.5	490.4
20°	551.3	537.3	522.9	510.6	498.6	488.4	485.3	482.6	479.8	478.1	476.8
22.5°	533.2	519.2	507.3	495.8	483.0	476.4	473.0	470.0	468.1	466.9	465.6
25°	507.8	495.5	482.2	472.0	461.7	457.3	455.2	453.5	452.2	450.5	450.1
27.5°	485.2	471.8	461.0	451.4	444.1	440.3	438.4	437.6	437.8	438.5	438.8
30°	468.2	455.9	447.0	438.8	432.0	428.6	428.3	428.3	429.6	430.0	430.7
32.5°	452.6	442.6	433.6	425.7	420.5	418.2	419.5	419.5	420.6	421.5	422.8
35°	430.0	421.1	414.3	407.4	403.0	404.0	404.7	405.4	407.1	409.1	410.5
37.5°	408.3	400.6	393.5	388.2	386.1	388.0	389.6	391.0	393.1	394.6	395.9
40°	392.7	386.9	380.1	375.3	376.0	377.0	378.4	380.1	381.8	382.8	384.2
42.5°	378.3	372.2	367.0	363.0	364.0	365.3	366.1	367.0	369.0	370.9	371.7
45°	356.2	351.4	346.6	344.3	344.9	345.6	346.3	347.3	349.0	350.4	350.7
47.5°	331.4	328.1	324.9	322.5	323.6	323.3	324.2	326.5	327.0	327.8	329.7
50°	315.6	312.5	308.7	308.1	308.1	308.1	308.4	311.1	311.1	312.5	313.9
52.5°	298.1	296.1	293.7	292.5	291.9	291.9	293.4	294.7	295.2	297.2	298.5
55°	272.2	270.1	268.1	267.1	266.4	267.1	269.8	270.5	272.2	273.2	274.2
57.5°	245.2	243.6	242.0	241.5	241.3	242.2	243.7	245.8	246.2	249.3	250.8
60°	227.5	225.1	223.7	223.7	223.0	226.0	225.4	228.8	229.5	231.6	234.0
62.5°	209.1	205.9	205.4	205.4	206.3	207.2	208.2	209.7	211.5	214.1	215.9
65°	179.7	177.9	180.3	179.9	179.3	181.4	181.4	183.1	185.1	187.5	191.3
67.5°	151.7	150.8	151.1	151.1	152.0	153.2	154.2	155.7	158.1	160.7	163.1
70°	132.9	133.8	132.2	133.6	134.6	134.9	135.5	137.6	140.4	142.0	144.8
72.5°	114.6	114.5	114.7	115.2	116.3	116.9	117.5	119.8	122.9	124.3	126.5
75°	88.1	87.7	88.8	88.8	90.5	91.2	91.8	92.9	95.6	97.6	99.4
77.5°	64.4	64.7	64.6	65.7	65.3	65.4	67.5	68.5	68.8	72.9	73.7
80°	48.5	49.2	49.5	49.8	50.2	49.5	51.9	53.0	53.0	55.3	57.1
82.5°	34.9	35.2	36.1	36.5	36.6	37.2	37.5	38.2	39.0	40.0	42.3
85°	17.4	18.5	18.8	18.5	18.8	18.1	19.1	19.4	19.8	19.8	19.8
87.5°	6.9	7.5	7.6	8.3	8.4	9.1	9.2	8.8	8.9	9.8	8.8
90°	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0	18.5	19.2	19.7
92.5°	11.2	11.8	13.3	14.8	16.3	17.8	18.8	19.8	20.8	21.8	22.4
95°	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8	24.9	25.9	26.5
97.5°	74.1	67.1	55.9	44.8	33.6	22.5	23.7	25.0	26.1	27.4	28.1
100°	130.2	119.7	95.5	71.3	47.2	23.0	24.3	25.5	26.8	28.0	28.6
102.5°	163.5	151.5	125.1	98.6	72.2	45.8	42.0	38.2	34.3	30.5	28.7
105°	214.5	208.5	194.5	180.6	166.6	152.7	125.3	97.8	70.4	43.0	29.4
107.5°	269.2	271.0	273.2	275.4	277.6	279.8	259.8	239.6	219.5	199.4	179.0
110°	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2	299.1	294.0	280.4



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	341.3	342.7	344.5	346.2	347.9	349.6	349.6	349.7	349.8	349.9	347.6
115°	393.4	394.6	396.0	397.3	398.8	400.2	401.7	403.2	404.8	406.4	407.4
117.5°	445.4	446.4	447.1	447.8	448.5	449.2	450.5	451.7	453.0	454.1	454.9
120°	478.2	479.2	479.7	480.1	480.5	481.0	482.2	483.5	484.7	486.0	486.6
122.5°	509.6	510.4	511.0	511.7	512.2	512.8	513.7	514.5	515.4	516.3	516.7
125°	554.3	555.3	555.9	556.4	557.1	557.7	558.0	558.3	558.7	558.9	559.3
127.5°	597.3	598.2	599.0	599.8	600.5	601.2	601.7	602.2	602.7	603.2	603.2
130°	624.0	624.9	625.5	626.2	626.8	627.4	628.0	628.7	629.3	629.9	630.1
132.5°	649.7	650.5	651.0	651.5	652.0	652.6	653.2	653.7	654.3	655.0	655.1
135°	687.6	688.4	689.0	689.6	690.3	690.9	691.3	691.8	692.2	692.7	692.7
137.5°	722.0	722.8	723.2	723.5	723.8	724.2	725.0	725.7	726.4	727.2	727.4
140°	743.4	744.0	744.6	745.0	745.5	745.9	746.5	747.2	747.8	748.4	748.6
142.5°	764.0	764.7	765.2	765.6	766.1	766.6	767.0	767.6	768.0	768.6	768.6
145°	793.5	794.2	794.5	794.8	795.1	795.4	795.8	796.0	796.4	796.7	796.8
147.5°	819.2	819.7	820.0	820.3	820.6	820.9	821.3	821.5	821.9	822.2	822.0
150°	834.9	835.4	835.6	836.0	836.2	836.6	836.9	837.1	837.5	837.8	837.8
152.5°	849.0	849.2	849.4	849.5	849.8	850.0	850.5	851.0	851.6	852.2	852.1
155°	868.1	868.0	868.2	868.3	868.4	868.6	869.4	870.2	870.9	871.7	871.6
157.5°	885.6	885.6	885.4	885.3	885.1	884.9	885.9	886.8	887.7	888.7	888.5
160°	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3	897.2	898.1	898.0
162.5°	903.7	903.4	903.2	903.1	902.9	902.8	903.8	904.9	906.0	907.0	907.0
165°	914.9	914.5	914.4	914.3	914.1	913.9	915.2	916.4	917.7	918.9	919.0
167.5°	923.2	922.8	922.8	922.8	922.8	922.8	924.1	925.3	926.6	927.8	927.8
170°	928.2	927.9	927.9	927.9	927.9	927.9	929.2	930.3	931.6	932.8	932.8
172.5°	931.0	930.8	930.9	930.9	931.1	931.2	932.5	933.7	935.0	936.2	936.1
175°	935.2	935.0	935.0	935.2	935.4	935.6	936.7	937.7	938.8	939.9	939.8
177.5°	937.0	936.7	936.8	937.0	937.1	937.2	938.3	939.2	940.2	941.2	941.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	674.0	673.8	675.6	674.3	675.6	673.8	674.0	675.9	676.5	676.7	676.7
5°	627.4	628.4	625.0	625.0	625.0	628.4	627.4	629.5	631.2	632.5	634.5
7.5°	585.9	584.3	584.5	582.6	584.5	584.3	585.9	587.5	589.7	592.6	595.5
10°	560.4	558.4	557.7	558.0	557.7	558.4	560.4	564.5	565.9	568.6	571.7
12.5°	539.4	539.0	534.5	534.6	534.5	539.0	539.4	540.5	543.5	549.2	552.9
15°	514.7	508.2	507.5	509.5	507.5	508.2	514.7	514.7	516.0	520.5	522.5
17.5°	489.9	486.4	486.7	485.6	486.7	486.4	489.9	490.4	491.5	495.2	497.8
20°	476.8	474.7	474.4	472.0	474.4	474.7	476.8	476.8	478.1	479.8	482.6
22.5°	464.8	464.0	464.2	461.6	464.2	464.0	464.8	465.6	466.9	468.1	470.0
25°	449.8	451.5	450.1	450.1	450.1	451.5	449.8	450.1	450.5	452.2	453.5
27.5°	439.7	439.6	438.9	438.9	438.9	439.6	439.7	438.8	438.5	437.8	437.6
30°	432.0	431.7	432.4	432.4	432.4	431.7	432.0	430.7	430.0	429.6	428.3
32.5°	424.4	424.8	425.0	425.3	425.0	424.8	424.4	422.8	421.5	420.6	419.5
35°	412.6	412.9	413.9	413.2	413.9	412.9	412.6	410.5	409.1	407.1	405.4
37.5°	396.5	398.1	397.8	398.3	397.8	398.1	396.5	395.9	394.6	393.1	391.0
40°	384.6	385.6	385.2	385.2	385.2	385.6	384.6	384.2	382.8	381.8	380.1
42.5°	372.3	373.0	372.1	371.6	372.1	373.0	372.3	371.7	370.9	369.0	367.0
45°	352.1	351.4	352.5	351.1	352.5	351.4	352.1	350.7	350.4	349.0	347.3
47.5°	329.6	330.3	330.6	331.5	330.6	330.3	329.6	329.7	327.8	327.0	326.5
50°	314.5	316.6	316.6	316.3	316.6	316.6	314.5	313.9	312.5	311.1	311.1
52.5°	299.8	300.8	302.1	302.0	302.1	300.8	299.8	298.5	297.2	295.2	294.7
55°	277.0	277.7	278.3	278.7	278.3	277.7	277.0	274.2	273.2	272.2	270.5
57.5°	253.3	253.1	254.7	255.2	254.7	253.1	253.3	250.8	249.3	246.2	245.8
60°	236.7	236.7	239.4	240.4	239.4	236.7	236.7	234.0	231.6	229.5	228.8
62.5°	218.9	220.0	222.7	221.3	222.7	220.0	218.9	215.9	214.1	211.5	209.7
65°	193.0	195.7	195.4	196.7	195.4	195.7	193.0	191.3	187.5	185.1	183.1
67.5°	165.9	167.6	170.0	170.2	170.0	167.6	165.9	163.1	160.7	158.1	155.7
70°	147.6	149.3	150.6	151.6	150.6	149.3	147.6	144.8	142.0	140.4	137.6
72.5°	129.7	130.6	133.9	132.5	133.9	130.6	129.7	126.5	124.3	122.9	119.8
75°	101.7	104.2	106.2	105.2	106.2	104.2	101.7	99.4	97.6	95.6	92.9
77.5°	75.3	77.7	78.6	77.8	78.6	77.7	75.3	73.7	72.9	68.8	68.5
80°	59.4	59.1	61.2	60.8	61.2	59.1	59.4	57.1	55.3	53.0	53.0
82.5°	43.6	43.2	44.2	44.4	44.2	43.2	43.6	42.3	40.0	39.0	38.2
85°	21.1	22.2	20.9	20.5	20.9	22.2	21.1	19.8	19.8	19.8	19.4
87.5°	8.9	9.0	8.7	8.6	8.7	9.0	8.9	8.8	9.8	8.9	8.8
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0
92.5°	22.6	22.7	22.9	23.2	22.9	22.7	22.6	22.4	21.8	20.8	19.8
95°	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8
97.5°	28.3	28.4	28.5	28.7	28.5	28.4	28.3	28.1	27.4	26.1	25.0
100°	28.8	29.0	29.2	29.2	29.2	29.0	28.8	28.6	28.0	26.8	25.5
102.5°	29.0	29.2	29.5	29.9	29.5	29.2	29.0	28.7	30.5	34.3	38.2
105°	29.8	30.1	30.4	30.7	30.4	30.1	29.8	29.4	43.0	70.4	97.8
107.5°	158.4	137.7	117.0	96.3	117.0	137.7	158.4	179.0	199.4	219.5	239.6
110°	258.2	236.0	213.8	191.7	213.8	236.0	258.2	280.4	294.0	299.1	304.2



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	343.0	338.2	333.6	329.0	333.6	338.2	343.0	347.6	349.9	349.8	349.7
115°	408.0	408.7	409.3	409.9	409.3	408.7	408.0	407.4	406.4	404.8	403.2
117.5°	455.0	455.1	455.2	455.4	455.2	455.1	455.0	454.9	454.1	453.0	451.7
120°	486.6	486.6	486.6	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5
122.5°	516.9	517.0	517.2	517.3	517.2	517.0	516.9	516.7	516.3	515.4	514.5
125°	559.5	559.9	560.2	560.5	560.2	559.9	559.5	559.3	558.9	558.7	558.3
127.5°	603.0	602.7	602.4	602.1	602.4	602.7	603.0	603.2	603.2	602.7	602.2
130°	629.7	629.5	629.1	628.8	629.1	629.5	629.7	630.1	629.9	629.3	628.7
132.5°	654.7	654.2	653.8	653.4	653.8	654.2	654.7	655.1	655.0	654.3	653.7
135°	692.2	691.8	691.3	690.9	691.3	691.8	692.2	692.7	692.7	692.2	691.8
137.5°	727.1	726.7	726.5	726.1	726.5	726.7	727.1	727.4	727.2	726.4	725.7
140°	748.2	748.0	747.6	747.3	747.6	748.0	748.2	748.6	748.4	747.8	747.2
142.5°	768.1	767.7	767.3	766.9	767.3	767.7	768.1	768.6	768.6	768.0	767.6
145°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0
147.5°	821.3	820.6	819.8	819.1	819.8	820.6	821.3	822.0	822.2	821.9	821.5
150°	837.2	836.8	836.3	835.9	836.3	836.8	837.2	837.8	837.8	837.5	837.1
152.5°	851.4	850.7	850.0	849.3	850.0	850.7	851.4	852.1	852.2	851.6	851.0
155°	870.8	869.8	868.9	867.9	868.9	869.8	870.8	871.6	871.7	870.9	870.2
157.5°	887.3	886.1	884.9	883.7	884.9	886.1	887.3	888.5	888.7	887.7	886.8
160°	897.0	895.9	894.8	893.8	894.8	895.9	897.0	898.0	898.1	897.2	896.3
162.5°	906.1	905.1	904.2	903.2	904.2	905.1	906.1	907.0	907.0	906.0	904.9
165°	917.9	916.8	915.7	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4
167.5°	926.6	925.3	924.1	922.8	924.1	925.3	926.6	927.8	927.8	926.6	925.3
170°	931.6	930.3	929.2	927.9	929.2	930.3	931.6	932.8	932.8	931.6	930.3
172.5°	934.8	933.4	932.0	930.7	932.0	933.4	934.8	936.1	936.2	935.0	933.7
175°	938.6	937.4	936.1	934.9	936.1	937.4	938.6	939.8	939.9	938.8	937.7
177.5°	939.9	938.6	937.4	936.1	937.4	938.6	939.9	941.1	941.2	940.2	939.2
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	675.9	675.9	681.1	684.4	688.5	691.3	693.1	695.1	698.3	702.8	707.7
5°	637.3	638.6	646.1	653.7	660.8	667.0	672.1	678.2	685.8	695.0	705.3
7.5°	599.9	605.1	612.7	621.9	631.9	640.9	649.9	660.0	670.6	684.2	698.6
10°	575.8	581.6	590.8	602.4	613.1	623.6	634.9	645.8	659.2	675.2	693.7
12.5°	554.7	560.3	569.8	582.5	592.5	604.2	617.2	631.3	646.3	665.7	686.5
15°	525.6	532.1	543.7	549.8	565.3	579.3	591.2	611.6	630.8	650.6	674.8
17.5°	501.7	505.3	514.7	526.1	537.6	553.3	569.0	586.0	605.1	629.4	659.7
20°	485.3	488.4	498.6	510.6	522.9	537.3	551.3	568.3	589.8	615.5	648.2
22.5°	473.0	476.4	483.0	495.8	507.3	519.2	533.2	553.6	576.4	601.5	637.0
25°	455.2	457.3	461.7	472.0	482.2	495.5	507.8	527.0	550.5	579.9	615.5
27.5°	438.4	440.3	444.1	451.4	461.0	471.8	485.2	501.4	525.3	557.2	594.9
30°	428.3	428.6	432.0	438.8	447.0	455.9	468.2	486.7	509.2	541.6	581.3
32.5°	419.5	418.2	420.5	425.7	433.6	442.6	452.6	470.8	492.6	524.4	565.2
35°	404.7	404.0	403.0	407.4	414.3	421.1	430.0	443.6	468.2	497.9	540.6
37.5°	389.6	388.0	386.1	388.2	393.5	400.6	408.3	420.4	441.7	474.4	515.2
40°	378.4	377.0	376.0	375.3	380.1	386.9	392.7	404.4	424.2	455.2	495.5
42.5°	366.1	365.3	364.0	363.0	367.0	372.2	378.3	388.5	408.3	437.5	475.6
45°	346.3	345.6	344.9	344.3	346.6	351.4	356.2	363.7	380.8	409.1	443.6
47.5°	324.2	323.3	323.6	322.5	324.9	328.1	331.4	339.5	355.9	378.7	403.9
50°	308.4	308.1	308.1	308.1	308.7	312.5	315.6	321.7	336.7	359.6	377.7
52.5°	293.4	291.9	291.9	292.5	293.7	296.1	298.1	304.8	317.9	336.7	353.1
55°	269.8	267.1	266.4	267.1	268.1	270.1	272.2	277.7	288.9	302.9	312.5
57.5°	243.7	242.2	241.3	241.5	242.0	243.6	245.2	251.2	260.0	267.3	273.5
60°	225.4	226.0	223.0	223.7	223.7	225.1	227.5	231.2	238.7	243.9	250.0
62.5°	208.2	207.2	206.3	205.4	205.4	205.9	209.1	212.0	218.5	221.1	226.0
65°	181.4	181.4	179.3	179.9	180.3	177.9	179.7	183.1	187.2	188.2	192.6
67.5°	154.2	153.2	152.0	151.1	151.1	150.8	151.7	153.4	156.5	156.9	160.2
70°	135.5	134.9	134.6	133.6	132.2	133.8	132.9	134.6	136.3	136.6	138.7
72.5°	117.5	116.9	116.3	115.2	114.7	114.5	114.6	116.5	117.7	117.2	119.5
75°	91.8	91.2	90.5	88.8	88.8	87.7	88.1	89.4	90.9	89.8	91.8
77.5°	67.5	65.4	65.3	65.7	64.6	64.7	64.4	64.1	64.7	64.8	66.7
80°	51.9	49.5	50.2	49.8	49.5	49.2	48.5	48.9	49.2	49.5	50.6
82.5°	37.5	37.2	36.6	36.5	36.1	35.2	34.9	35.5	35.8	35.6	36.4
85°	19.1	18.1	18.8	18.5	18.8	18.5	17.4	17.4	18.1	17.7	18.5
87.5°	9.2	9.1	8.4	8.3	7.6	7.5	6.9	6.8	6.8	6.4	6.7
90°	17.4	16.8	14.7	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7
92.5°	18.8	17.8	16.3	14.8	13.3	11.8	11.2	11.7	12.1	12.6	12.9
95°	22.7	21.6	19.9	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5
97.5°	23.7	22.5	33.6	44.8	55.9	67.1	74.1	77.0	79.8	82.7	85.4
100°	24.3	23.0	47.2	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8
102.5°	42.0	45.8	72.2	98.6	125.1	151.5	163.5	161.3	159.1	156.9	154.6
105°	125.3	152.7	166.6	180.6	194.5	208.5	214.5	212.9	211.2	209.5	207.8
107.5°	259.8	279.8	277.6	275.4	273.2	271.0	269.2	267.9	266.5	265.2	263.8
110°	309.3	314.4	312.7	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.1



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.6	349.6	347.9	346.2	344.5	342.7	341.3	340.2	339.1	338.0	336.9
115°	401.7	400.2	398.8	397.3	396.0	394.6	393.4	392.5	391.6	390.7	389.7
117.5°	450.5	449.2	448.5	447.8	447.1	446.4	445.4	444.3	443.2	442.0	440.9
120°	482.2	481.0	480.5	480.1	479.7	479.2	478.2	476.8	475.5	474.0	472.7
122.5°	513.7	512.8	512.2	511.7	511.0	510.4	509.6	508.5	507.3	506.1	505.0
125°	558.0	557.7	557.1	556.4	555.9	555.3	554.3	553.0	551.8	550.5	549.4
127.5°	601.7	601.2	600.5	599.8	599.0	598.2	597.3	596.0	594.8	593.5	592.3
130°	628.0	627.4	626.8	626.2	625.5	624.9	624.0	622.8	621.5	620.3	619.0
132.5°	653.2	652.6	652.0	651.5	651.0	650.5	649.7	648.5	647.2	646.0	644.7
135°	691.3	690.9	690.3	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9
137.5°	725.0	724.2	723.8	723.5	723.2	722.8	722.0	720.9	719.7	718.5	717.4
140°	746.5	745.9	745.5	745.0	744.6	744.0	743.4	742.4	741.5	740.6	739.7
142.5°	767.0	766.6	766.1	765.6	765.2	764.7	764.0	763.1	762.1	761.3	760.3
145°	795.8	795.4	795.1	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2
147.5°	821.3	820.9	820.6	820.3	820.0	819.7	819.2	818.5	817.8	817.1	816.4
150°	836.9	836.6	836.2	836.0	835.6	835.4	834.9	834.5	834.0	833.6	833.0
152.5°	850.5	850.0	849.8	849.5	849.4	849.2	849.0	848.8	848.6	848.4	848.1
155°	869.4	868.6	868.4	868.3	868.2	868.0	868.1	868.4	868.7	869.1	869.3
157.5°	885.9	884.9	885.1	885.3	885.4	885.6	885.6	885.6	885.7	885.7	885.7
160°	895.4	894.4	894.6	894.7	894.9	895.0	895.2	895.4	895.5	895.6	895.8
162.5°	903.8	902.8	902.9	903.1	903.2	903.4	903.7	904.1	904.5	904.9	905.3
165°	915.2	913.9	914.1	914.3	914.4	914.5	914.9	915.3	915.8	916.2	916.8
167.5°	924.1	922.8	922.8	922.8	922.8	922.8	923.2	923.8	924.4	925.1	925.7
170°	929.2	927.9	927.9	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7
172.5°	932.5	931.2	931.1	930.9	930.9	930.8	931.0	931.7	932.6	933.3	934.0
175°	936.7	935.6	935.4	935.2	935.0	935.0	935.2	936.0	936.8	937.5	938.3
177.5°	938.3	937.2	937.1	937.0	936.8	936.7	937.0	937.6	938.3	938.9	939.4
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	709.3	710.6	715.2	718.5	722.4	724.6	726.7	728.4	730.6	731.1	739.0
5°	712.4	719.3	731.2	740.0	751.0	762.9	771.2	774.9	784.8	793.0	809.4
7.5°	711.5	726.0	744.1	762.9	782.9	801.5	817.6	836.7	850.3	870.8	890.9
10°	710.7	730.1	753.4	777.3	805.3	831.3	854.5	880.5	902.0	930.3	954.6
12.5°	708.3	731.8	764.0	792.3	826.3	862.1	896.5	929.9	949.0	996.1	1018.5
15°	702.1	730.1	770.4	813.5	860.3	902.7	946.4	981.1	1037.5	1078.9	1105.2
17.5°	690.5	729.8	777.6	829.5	886.4	942.2	991.7	1044.6	1104.4	1154.3	1207.6
20°	685.1	728.1	781.4	838.7	897.9	961.0	1017.4	1080.9	1146.1	1195.3	1263.6
22.5°	675.0	723.7	781.1	845.1	908.2	973.6	1039.6	1103.6	1178.9	1246.7	1311.7
25°	658.4	713.1	772.5	843.9	918.0	983.6	1062.5	1147.5	1226.1	1313.1	1378.0
27.5°	641.1	699.5	759.0	825.4	905.1	982.9	1082.2	1178.2	1274.3	1349.5	1397.5
30°	627.7	684.4	745.9	812.8	891.7	984.3	1095.3	1200.1	1293.7	1358.3	1385.2
32.5°	613.2	670.7	725.1	795.3	879.4	983.5	1103.5	1212.9	1294.8	1337.7	1332.5
35°	590.5	638.6	691.6	759.2	858.3	977.4	1108.2	1214.1	1264.3	1255.1	1185.4
37.5°	557.7	598.2	650.3	724.3	833.7	964.8	1098.7	1178.1	1174.8	1099.7	998.8
40°	537.3	571.7	621.9	699.8	814.5	956.6	1083.6	1135.2	1091.5	986.7	865.8
42.5°	510.4	542.2	592.4	672.4	793.5	940.0	1055.0	1069.9	984.4	863.7	753.0
45°	469.0	497.0	548.8	631.5	762.0	903.7	985.0	948.4	833.3	708.6	624.3
47.5°	424.3	453.4	503.4	588.3	716.3	849.1	887.8	810.1	691.9	590.8	513.4
50°	396.2	424.2	473.0	558.7	685.5	804.3	820.4	720.0	611.4	522.5	459.0
52.5°	367.7	394.1	442.1	528.2	649.3	752.3	742.4	640.2	540.3	464.6	414.7
55°	325.5	350.4	396.2	476.8	587.1	668.7	632.8	535.2	452.5	393.8	355.9
57.5°	287.7	311.6	351.0	423.8	519.7	575.8	530.2	447.9	382.2	337.0	308.7
60°	262.0	283.1	320.7	388.3	471.6	514.3	469.2	396.5	341.2	305.0	279.7
62.5°	237.6	256.1	290.9	352.2	424.6	460.5	414.9	353.3	306.2	274.1	252.6
65°	200.8	217.6	248.3	296.1	355.5	379.4	340.2	290.3	253.8	229.9	215.5
67.5°	167.2	181.4	207.9	245.6	289.4	306.7	276.9	238.3	210.7	191.5	180.1
70°	144.8	157.1	177.9	210.4	250.0	263.3	235.3	203.6	183.4	168.0	157.5
72.5°	125.9	135.0	153.9	179.0	212.0	222.6	203.0	175.1	156.3	144.8	136.4
75°	95.9	103.4	115.7	135.9	158.8	165.0	150.3	132.9	120.2	112.0	105.5
77.5°	69.2	74.7	83.6	96.0	111.9	117.4	108.2	96.5	87.3	81.8	78.1
80°	52.3	56.7	64.2	74.5	84.0	87.1	81.6	72.8	66.3	63.2	60.1
82.5°	38.6	41.1	45.7	52.6	59.1	62.8	58.1	52.8	49.3	46.5	45.4
85°	19.4	20.9	22.9	25.6	29.7	31.1	29.3	28.0	25.9	24.3	24.3
87.5°	7.6	7.8	9.0	9.8	11.3	12.5	12.7	12.5	12.7	12.5	12.3
90°	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0
92.5°	12.6	12.1	11.7	11.2	11.8	13.3	14.8	16.3	17.8	18.8	19.8
95°	36.2	29.8	23.5	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8
97.5°	82.7	79.8	77.0	74.1	67.1	55.9	44.8	33.6	22.5	23.7	25.0
100°	120.9	124.0	127.1	130.2	119.7	95.5	71.3	47.2	23.0	24.3	25.5
102.5°	156.9	159.1	161.3	163.5	151.5	125.1	98.6	72.2	45.8	42.0	38.2
105°	209.5	211.2	212.9	214.5	208.5	194.5	180.6	166.6	152.7	125.3	97.8
107.5°	265.2	266.5	267.9	269.2	271.0	273.2	275.4	277.6	279.8	259.8	239.6
110°	302.4	303.6	304.9	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	338.0	339.1	340.2	341.3	342.7	344.5	346.2	347.9	349.6	349.6	349.7
115°	390.7	391.6	392.5	393.4	394.6	396.0	397.3	398.8	400.2	401.7	403.2
117.5°	442.0	443.2	444.3	445.4	446.4	447.1	447.8	448.5	449.2	450.5	451.7
120°	474.0	475.5	476.8	478.2	479.2	479.7	480.1	480.5	481.0	482.2	483.5
122.5°	506.1	507.3	508.5	509.6	510.4	511.0	511.7	512.2	512.8	513.7	514.5
125°	550.5	551.8	553.0	554.3	555.3	555.9	556.4	557.1	557.7	558.0	558.3
127.5°	593.5	594.8	596.0	597.3	598.2	599.0	599.8	600.5	601.2	601.7	602.2
130°	620.3	621.5	622.8	624.0	624.9	625.5	626.2	626.8	627.4	628.0	628.7
132.5°	646.0	647.2	648.5	649.7	650.5	651.0	651.5	652.0	652.6	653.2	653.7
135°	684.8	685.7	686.7	687.6	688.4	689.0	689.6	690.3	690.9	691.3	691.8
137.5°	718.5	719.7	720.9	722.0	722.8	723.2	723.5	723.8	724.2	725.0	725.7
140°	740.6	741.5	742.4	743.4	744.0	744.6	745.0	745.5	745.9	746.5	747.2
142.5°	761.3	762.1	763.1	764.0	764.7	765.2	765.6	766.1	766.6	767.0	767.6
145°	790.2	791.3	792.4	793.5	794.2	794.5	794.8	795.1	795.4	795.8	796.0
147.5°	817.1	817.8	818.5	819.2	819.7	820.0	820.3	820.6	820.9	821.3	821.5
150°	833.6	834.0	834.5	834.9	835.4	835.6	836.0	836.2	836.6	836.9	837.1
152.5°	848.4	848.6	848.8	849.0	849.2	849.4	849.5	849.8	850.0	850.5	851.0
155°	869.1	868.7	868.4	868.1	868.0	868.2	868.3	868.4	868.6	869.4	870.2
157.5°	885.7	885.7	885.6	885.6	885.6	885.4	885.3	885.1	884.9	885.9	886.8
160°	895.6	895.5	895.4	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3
162.5°	904.9	904.5	904.1	903.7	903.4	903.2	903.1	902.9	902.8	903.8	904.9
165°	916.2	915.8	915.3	914.9	914.5	914.4	914.3	914.1	913.9	915.2	916.4
167.5°	925.1	924.4	923.8	923.2	922.8	922.8	922.8	922.8	922.8	924.1	925.3
170°	930.1	929.4	928.8	928.2	927.9	927.9	927.9	927.9	927.9	929.2	930.3
172.5°	933.3	932.6	931.7	931.0	930.8	930.9	930.9	931.1	931.2	932.5	933.7
175°	937.5	936.8	936.0	935.2	935.0	935.0	935.2	935.4	935.6	936.7	937.7
177.5°	938.9	938.3	937.6	937.0	936.7	936.8	937.0	937.1	937.2	938.3	939.2
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	741.8	742.1	745.0	747.3	746.2	747.5	748.1
5°	810.4	822.7	829.2	834.0	834.4	834.6	837.4
7.5°	907.8	921.0	930.6	945.2	949.6	954.6	953.1
10°	978.8	998.3	1015.0	1023.9	1033.4	1047.4	1036.2
12.5°	1045.2	1079.7	1105.2	1118.9	1128.0	1130.8	1125.2
15°	1154.7	1199.8	1224.1	1223.3	1254.1	1267.4	1246.5
17.5°	1255.1	1296.7	1330.0	1347.1	1372.7	1378.4	1375.8
20°	1316.5	1362.0	1387.9	1417.3	1430.7	1442.6	1444.7
22.5°	1369.6	1410.3	1438.2	1462.7	1473.8	1479.4	1482.9
25°	1424.2	1456.3	1473.0	1481.5	1484.6	1483.9	1479.4
27.5°	1420.4	1422.8	1404.4	1386.3	1370.1	1351.8	1345.6
30°	1383.5	1354.8	1303.6	1274.5	1231.9	1198.0	1211.7
32.5°	1286.5	1229.4	1171.9	1108.4	1055.9	1041.0	1025.9
35°	1098.0	997.6	938.9	870.6	843.2	815.9	797.1
37.5°	888.3	810.7	740.9	696.2	668.9	651.7	642.3
40°	768.1	698.0	640.7	604.5	583.6	564.2	561.4
42.5°	672.2	607.1	563.9	535.1	515.1	506.8	500.8
45°	550.5	505.1	476.1	455.6	442.3	437.1	430.3
47.5°	466.0	433.9	412.1	398.1	388.1	384.2	383.7
50°	418.7	392.1	376.0	365.1	357.2	355.9	350.4
52.5°	383.2	360.1	347.6	338.0	332.3	328.5	326.9
55°	332.6	317.3	306.0	300.5	296.1	292.3	292.3
57.5°	291.1	278.2	270.7	266.1	264.7	262.1	260.4
60°	265.4	254.4	248.6	244.5	241.8	242.1	239.1
62.5°	240.2	233.1	227.6	223.5	220.3	220.3	220.5
65°	204.6	199.1	195.0	193.7	191.6	189.2	189.8
67.5°	173.3	168.3	165.1	162.7	162.0	160.7	162.7
70°	151.0	147.2	144.8	142.8	142.0	142.4	144.1
72.5°	130.5	127.8	126.3	125.3	123.8	123.9	125.0
75°	102.5	100.4	99.1	98.0	97.6	97.6	97.6
77.5°	75.3	74.8	74.2	72.7	72.8	73.1	73.2
80°	59.4	58.4	58.1	57.3	56.4	55.6	57.3
82.5°	44.4	43.3	43.1	42.9	41.3	41.2	42.6
85°	23.9	22.9	23.2	22.9	22.9	22.6	22.6
87.5°	12.2	12.0	11.9	12.2	11.9	11.8	12.4
90°	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	20.8	21.8	22.4	22.6	22.7	22.9	23.2
95°	24.9	25.9	26.5	26.5	26.5	26.5	26.5
97.5°	26.1	27.4	28.1	28.3	28.4	28.5	28.7
100°	26.8	28.0	28.6	28.8	29.0	29.2	29.2
102.5°	34.3	30.5	28.7	29.0	29.2	29.5	29.9
105°	70.4	43.0	29.4	29.8	30.1	30.4	30.7
107.5°	219.5	199.4	179.0	158.4	137.7	117.0	96.3
110°	299.1	294.0	280.4	258.2	236.0	213.8	191.7



TEST NUMBER: P331928-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.8	349.9	347.6	343.0	338.2	333.6	329.0
115°	404.8	406.4	407.4	408.0	408.7	409.3	409.9
117.5°	453.0	454.1	454.9	455.0	455.1	455.2	455.4
120°	484.7	486.0	486.6	486.6	486.6	486.6	486.6
122.5°	515.4	516.3	516.7	516.9	517.0	517.2	517.3
125°	558.7	558.9	559.3	559.5	559.9	560.2	560.5
127.5°	602.7	603.2	603.2	603.0	602.7	602.4	602.1
130°	629.3	629.9	630.1	629.7	629.5	629.1	628.8
132.5°	654.3	655.0	655.1	654.7	654.2	653.8	653.4
135°	692.2	692.7	692.7	692.2	691.8	691.3	690.9
137.5°	726.4	727.2	727.4	727.1	726.7	726.5	726.1
140°	747.8	748.4	748.6	748.2	748.0	747.6	747.3
142.5°	768.0	768.6	768.6	768.1	767.7	767.3	766.9
145°	796.4	796.7	796.8	796.8	796.8	796.8	796.8
147.5°	821.9	822.2	822.0	821.3	820.6	819.8	819.1
150°	837.5	837.8	837.8	837.2	836.8	836.3	835.9
152.5°	851.6	852.2	852.1	851.4	850.7	850.0	849.3
155°	870.9	871.7	871.6	870.8	869.8	868.9	867.9
157.5°	887.7	888.7	888.5	887.3	886.1	884.9	883.7
160°	897.2	898.1	898.0	897.0	895.9	894.8	893.8
162.5°	906.0	907.0	907.0	906.1	905.1	904.2	903.2
165°	917.7	918.9	919.0	917.9	916.8	915.7	914.6
167.5°	926.6	927.8	927.8	926.6	925.3	924.1	922.8
170°	931.6	932.8	932.8	931.6	930.3	929.2	927.9
172.5°	935.0	936.2	936.1	934.8	933.4	932.0	930.7
175°	938.8	939.9	939.8	938.6	937.4	936.1	934.9
177.5°	940.2	941.2	941.1	939.9	938.6	937.4	936.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3

(END OF REPORT)