

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332887-927

Luminaire Tested: **S124RDIP-S350D1035U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332887-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D1035U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3971.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332887-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332887-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21				
3	77	68	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	19	15				
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13				
6	60	48	40	35	53	44	37	32	35	30	26	26	23	21	19	17	15	12				
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	10				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9				
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	14	12	11	9				
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P332887-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.2
10°-20°	128.3	3.2
20°-30°	185.2	4.7
30°-40°	210.0	5.3
40°-50°	202.8	5.1
50°-60°	168.6	4.2
60°-70°	116.4	2.9
70°-80°	59.0	1.5
80°-90°	18.2	0.5
90°-100°	67.4	1.7
100°-110°	199.8	5.0
110°-120°	339.1	8.5
120°-130°	447.1	11.3
130°-140°	502.1	12.6
140°-150°	493.4	12.4
150°-160°	415.0	10.4
160°-170°	276.1	7.0
170°-180°	96.7	2.4
0°-30°	359.5	9.1
0°-40°	569.5	14.3
0°-60°	940.8	23.7
0°-90°	1134.5	28.6
90°-120°	606.3	15.3
90°-150°	2048.8	51.6
90°-180°	2837.0	71.4
0°-180°	3971.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	2	11	17	22	24	4
95°	48	54	60	62	62	53
105°	184	185	188	191	193	196
115°	345	345	343	342	342	340
125°	502	502	501	500	498	447
135°	648	652	652	651	648	501
145°	787	790	791	790	788	492
155°	901	901	901	903	901	415
165°	981	979	977	982	979	276
175°	1021	1017	1016	1021	1016	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332887-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.4	7.2	7.1	7.0	6.8	6.8	7.1	7.3	7.4	7.7	7.8
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	17.0	19.2	21.3	23.5	25.7	27.4	28.4	29.3	30.3	31.3	31.9
95°	47.5	49.0	50.6	52.2	53.8	55.1	56.4	57.7	58.9	60.1	60.6
97.5°	82.9	84.1	85.4	86.7	87.9	89.3	90.7	92.1	93.6	95.1	95.7
100°	110.7	111.4	112.1	112.8	113.5	114.6	116.2	117.8	119.4	121.0	121.4
102.5°	139.8	140.1	140.4	140.6	140.9	141.8	143.2	144.7	146.1	147.6	148.1
105°	184.3	184.4	184.6	184.7	185.0	185.4	186.1	186.8	187.5	188.2	188.7
107.5°	230.9	231.1	231.3	231.6	231.7	231.9	232.0	232.1	232.2	232.3	232.8
110°	262.5	262.8	263.2	263.6	264.0	264.0	263.8	263.6	263.5	263.3	262.9



TEST NUMBER: P332887-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.4	295.5	295.6	295.6	295.7	295.6	295.2	294.9	294.6	294.3	294.2
115°	344.8	344.8	344.8	344.8	344.8	344.6	344.2	343.9	343.5	343.2	343.0
117.5°	391.3	391.4	391.5	391.7	391.8	391.7	391.5	391.3	391.0	390.8	390.1
120°	422.2	422.9	423.7	424.4	425.1	425.2	424.6	424.1	423.6	423.0	422.2
122.5°	454.5	454.8	455.0	455.3	455.6	455.7	455.4	455.1	454.9	454.6	454.1
125°	502.1	502.1	502.1	502.1	502.1	502.0	501.8	501.7	501.5	501.3	501.0
127.5°	545.3	545.8	546.3	546.8	547.4	547.5	547.2	546.9	546.7	546.4	546.1
130°	575.6	576.2	576.7	577.2	577.7	578.0	578.0	578.0	578.0	578.0	577.7
132.5°	606.7	607.0	607.4	607.8	608.2	608.3	608.2	608.0	607.8	607.8	607.4
135°	647.6	648.6	649.7	650.8	651.8	652.4	652.4	652.4	652.4	652.4	652.0
137.5°	692.2	692.7	693.2	693.6	694.2	694.5	694.8	695.1	695.4	695.7	695.2
140°	721.9	722.2	722.6	722.9	723.3	723.5	723.5	723.5	723.5	723.5	723.3
142.5°	749.1	749.5	749.8	750.2	750.5	750.6	750.5	750.4	750.2	750.0	750.0
145°	786.7	787.4	788.1	788.9	789.6	790.0	790.2	790.4	790.5	790.7	790.5
147.5°	824.1	824.9	825.8	826.6	827.4	827.8	827.7	827.5	827.4	827.3	827.1
150°	846.8	847.6	848.3	849.0	849.7	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	868.4	868.8	869.2	869.7	870.1	870.3	870.4	870.6	870.8	870.8	871.3
155°	901.4	901.4	901.4	901.4	901.4	901.3	901.1	900.9	900.8	900.6	901.3
157.5°	929.2	928.9	928.6	928.3	928.0	927.8	927.7	927.7	927.7	927.6	928.2
160°	945.7	945.5	945.3	945.2	945.0	944.8	944.6	944.4	944.3	944.1	944.6
162.5°	960.8	960.4	960.0	959.5	959.0	958.7	958.5	958.4	958.2	958.0	958.9
165°	981.3	980.7	980.2	979.7	979.1	978.7	978.3	978.0	977.6	977.3	978.3
167.5°	997.0	996.2	995.5	994.7	994.0	993.6	993.6	993.7	993.7	993.8	994.8
170°	1005.8	1004.9	1004.0	1003.1	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7
172.5°	1012.1	1011.4	1010.7	1009.9	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1
175°	1020.8	1019.9	1019.1	1018.2	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3
177.5°	1023.7	1022.9	1022.2	1021.5	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332887-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	8.0	8.1	8.2	8.4	8.6	8.6	8.8	9.0
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	32.6	33.2	33.8	34.3	34.5	34.7	34.9	35.1
95°	61.2	61.7	62.2	62.5	62.5	62.5	62.5	62.5
97.5°	96.3	97.0	97.6	97.9	97.9	97.9	97.9	97.9
100°	121.7	122.0	122.4	122.6	122.6	122.6	122.6	122.6
102.5°	148.5	149.0	149.5	149.8	150.0	150.1	150.3	150.4
105°	189.3	189.8	190.3	190.8	191.3	191.9	192.4	192.9
107.5°	233.3	233.8	234.2	234.5	234.5	234.4	234.4	234.3
110°	262.6	262.2	261.9	262.0	262.5	263.0	263.6	264.1



TEST NUMBER: P332887-927

CATALOG NUMBER: S124RDIP-S350D1035U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	294.1	294.1	294.1	294.1	294.2	294.4	294.5
115°	342.8	342.6	342.5	342.3	342.1	341.9	341.7	341.6
117.5°	389.6	389.0	388.4	387.9	387.5	387.2	386.8	386.5
120°	421.3	420.4	419.5	419.2	419.6	419.9	420.3	420.6
122.5°	453.4	452.9	452.3	451.6	451.0	450.4	449.7	449.1
125°	500.6	500.3	499.9	499.6	499.2	498.8	498.5	498.1
127.5°	545.7	545.3	544.9	544.6	544.4	544.1	543.8	543.5
130°	577.3	576.9	576.6	576.1	575.4	574.6	573.9	573.2
132.5°	607.0	606.7	606.3	606.0	605.7	605.5	605.1	604.9
135°	651.6	651.3	650.9	650.5	650.0	649.4	648.9	648.4
137.5°	694.7	694.3	693.9	693.6	693.8	693.9	694.0	694.1
140°	723.2	722.9	722.8	722.6	722.5	722.2	722.1	721.9
142.5°	750.0	750.0	750.0	749.9	749.9	749.8	749.8	749.7
145°	790.4	790.2	790.0	789.6	789.1	788.6	788.1	787.5
147.5°	827.0	826.8	826.6	826.5	826.3	826.2	826.0	825.9
150°	850.0	850.0	850.0	849.9	849.8	849.5	849.4	849.2
152.5°	871.7	872.1	872.6	872.6	872.1	871.6	871.2	870.7
155°	902.1	902.7	903.4	903.4	902.7	902.1	901.3	900.6
157.5°	928.7	929.2	929.8	929.7	929.2	928.5	928.0	927.3
160°	945.2	945.7	946.2	946.0	945.2	944.3	943.4	942.5
162.5°	959.9	960.8	961.8	961.9	961.0	960.1	959.3	958.3
165°	979.5	980.5	981.5	981.7	981.0	980.3	979.6	978.9
167.5°	995.9	997.0	998.0	998.0	996.9	995.8	994.7	993.6
170°	1004.7	1005.8	1006.9	1006.7	1005.5	1004.2	1003.1	1001.8
172.5°	1011.3	1012.5	1013.8	1013.7	1012.5	1011.2	1010.0	1008.8
175°	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1
177.5°	1022.5	1023.4	1024.5	1024.4	1023.3	1022.1	1021.0	1019.9
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4

(END OF REPORT)