

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331934-940

Luminaire Tested: **S123DIP-S560D805U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331934-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D805U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4931.2 lumens  
Efficiency: N/A  
Efficacy: 128.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331934-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331934-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	19
6	61	49	41	36	56	46	38	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P331934-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.8	1.5
10°-20°	211.3	4.3
20°-30°	312.1	6.3
30°-40°	364.6	7.4
40°-50°	366.5	7.4
50°-60°	322.0	6.5
60°-70°	239.9	4.9
70°-80°	136.7	2.8
80°-90°	41.9	0.8
90°-100°	34.1	0.7
100°-110°	162.6	3.3
110°-120°	390.6	7.9
120°-130°	497.3	10.1
130°-140°	531.4	10.8
140°-150°	496.9	10.1
150°-160°	400.8	8.1
160°-170°	258.7	5.2
170°-180°	89.2	1.8
0°-30°	598.2	12.1
0°-40°	962.8	19.5
0°-60°	1651.3	33.5
0°-90°	2069.7	42.0
90°-120°	587.3	11.9
90°-150°	2112.9	42.8
90°-180°	2862.0	58.0
0°-180°	4931.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	1	8	17	19	21	4
95°	42	16	22	26	26	53
105°	208	212	153	36	31	220
115°	390	394	400	407	410	385
125°	549	555	558	559	560	490
135°	684	688	691	693	691	526
145°	789	794	795	797	797	494
155°	869	868	869	872	868	400
165°	917	915	914	919	915	259
175°	938	935	936	940	935	89
180°	938	938	938	938	938	



TEST NUMBER: P331934-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.4	14.3	14.3	14.2	14.1	14.3	14.5	14.8	15.1	15.3	15.3
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	12.9	12.6	12.1	11.7	11.2	11.8	13.3	14.8	16.3	17.8	18.8
95°	42.5	36.2	29.8	23.5	17.1	14.8	16.5	18.2	19.9	21.6	22.7
97.5°	85.4	82.7	79.8	77.0	74.1	67.1	55.9	44.8	33.6	22.5	23.7
100°	117.8	120.9	124.0	127.1	130.2	119.7	95.5	71.3	47.2	23.0	24.3
102.5°	154.6	156.9	159.1	161.3	163.5	151.5	125.1	98.6	72.2	45.8	42.0
105°	207.8	209.5	211.2	212.9	214.5	208.5	194.5	180.6	166.6	152.7	125.3
107.5°	263.8	265.2	266.5	267.9	269.2	271.0	273.2	275.4	277.6	279.8	259.8
110°	301.1	302.4	303.6	304.9	306.1	307.6	309.3	311.0	312.7	314.4	309.3



TEST NUMBER: P331934-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.9	338.0	339.1	340.2	341.3	342.7	344.5	346.2	347.9	349.6	349.6
115°	389.7	390.7	391.6	392.5	393.4	394.6	396.0	397.3	398.8	400.2	401.7
117.5°	440.9	442.0	443.2	444.3	445.4	446.4	447.1	447.8	448.5	449.2	450.5
120°	472.7	474.0	475.5	476.8	478.2	479.2	479.7	480.1	480.5	481.0	482.2
122.5°	505.0	506.1	507.3	508.5	509.6	510.4	511.0	511.7	512.2	512.8	513.7
125°	549.4	550.5	551.8	553.0	554.3	555.3	555.9	556.4	557.1	557.7	558.0
127.5°	592.3	593.5	594.8	596.0	597.3	598.2	599.0	599.8	600.5	601.2	601.7
130°	619.0	620.3	621.5	622.8	624.0	624.9	625.5	626.2	626.8	627.4	628.0
132.5°	644.7	646.0	647.2	648.5	649.7	650.5	651.0	651.5	652.0	652.6	653.2
135°	683.9	684.8	685.7	686.7	687.6	688.4	689.0	689.6	690.3	690.9	691.3
137.5°	717.4	718.5	719.7	720.9	722.0	722.8	723.2	723.5	723.8	724.2	725.0
140°	739.7	740.6	741.5	742.4	743.4	744.0	744.6	745.0	745.5	745.9	746.5
142.5°	760.3	761.3	762.1	763.1	764.0	764.7	765.2	765.6	766.1	766.6	767.0
145°	789.2	790.2	791.3	792.4	793.5	794.2	794.5	794.8	795.1	795.4	795.8
147.5°	816.4	817.1	817.8	818.5	819.2	819.7	820.0	820.3	820.6	820.9	821.3
150°	833.0	833.6	834.0	834.5	834.9	835.4	835.6	836.0	836.2	836.6	836.9
152.5°	848.1	848.4	848.6	848.8	849.0	849.2	849.4	849.5	849.8	850.0	850.5
155°	869.3	869.1	868.7	868.4	868.1	868.0	868.2	868.3	868.4	868.6	869.4
157.5°	885.7	885.7	885.7	885.6	885.6	885.6	885.4	885.3	885.1	884.9	885.9
160°	895.8	895.6	895.5	895.4	895.2	895.0	894.9	894.7	894.6	894.4	895.4
162.5°	905.3	904.9	904.5	904.1	903.7	903.4	903.2	903.1	902.9	902.8	903.8
165°	916.8	916.2	915.8	915.3	914.9	914.5	914.4	914.3	914.1	913.9	915.2
167.5°	925.7	925.1	924.4	923.8	923.2	922.8	922.8	922.8	922.8	922.8	924.1
170°	930.7	930.1	929.4	928.8	928.2	927.9	927.9	927.9	927.9	927.9	929.2
172.5°	934.0	933.3	932.6	931.7	931.0	930.8	930.9	930.9	931.1	931.2	932.5
175°	938.3	937.5	936.8	936.0	935.2	935.0	935.0	935.2	935.4	935.6	936.7
177.5°	939.4	938.9	938.3	937.6	937.0	936.7	936.8	937.0	937.1	937.2	938.3
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331934-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	15.3	15.3	15.3	15.4	15.5	15.5	15.6	15.7
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	19.8	20.8	21.8	22.4	22.6	22.7	22.9	23.2
95°	23.8	24.9	25.9	26.5	26.5	26.5	26.5	26.5
97.5°	25.0	26.1	27.4	28.1	28.3	28.4	28.5	28.7
100°	25.5	26.8	28.0	28.6	28.8	29.0	29.2	29.2
102.5°	38.2	34.3	30.5	28.7	29.0	29.2	29.5	29.9
105°	97.8	70.4	43.0	29.4	29.8	30.1	30.4	30.7
107.5°	239.6	219.5	199.4	179.0	158.4	137.7	117.0	96.3
110°	304.2	299.1	294.0	280.4	258.2	236.0	213.8	191.7





TEST NUMBER: P331934-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.7	349.8	349.9	347.6	343.0	338.2	333.6	329.0
115°	403.2	404.8	406.4	407.4	408.0	408.7	409.3	409.9
117.5°	451.7	453.0	454.1	454.9	455.0	455.1	455.2	455.4
120°	483.5	484.7	486.0	486.6	486.6	486.6	486.6	486.6
122.5°	514.5	515.4	516.3	516.7	516.9	517.0	517.2	517.3
125°	558.3	558.7	558.9	559.3	559.5	559.9	560.2	560.5
127.5°	602.2	602.7	603.2	603.2	603.0	602.7	602.4	602.1
130°	628.7	629.3	629.9	630.1	629.7	629.5	629.1	628.8
132.5°	653.7	654.3	655.0	655.1	654.7	654.2	653.8	653.4
135°	691.8	692.2	692.7	692.7	692.2	691.8	691.3	690.9
137.5°	725.7	726.4	727.2	727.4	727.1	726.7	726.5	726.1
140°	747.2	747.8	748.4	748.6	748.2	748.0	747.6	747.3
142.5°	767.6	768.0	768.6	768.6	768.1	767.7	767.3	766.9
145°	796.0	796.4	796.7	796.8	796.8	796.8	796.8	796.8
147.5°	821.5	821.9	822.2	822.0	821.3	820.6	819.8	819.1
150°	837.1	837.5	837.8	837.8	837.2	836.8	836.3	835.9
152.5°	851.0	851.6	852.2	852.1	851.4	850.7	850.0	849.3
155°	870.2	870.9	871.7	871.6	870.8	869.8	868.9	867.9
157.5°	886.8	887.7	888.7	888.5	887.3	886.1	884.9	883.7
160°	896.3	897.2	898.1	898.0	897.0	895.9	894.8	893.8
162.5°	904.9	906.0	907.0	907.0	906.1	905.1	904.2	903.2
165°	916.4	917.7	918.9	919.0	917.9	916.8	915.7	914.6
167.5°	925.3	926.6	927.8	927.8	926.6	925.3	924.1	922.8
170°	930.3	931.6	932.8	932.8	931.6	930.3	929.2	927.9
172.5°	933.7	935.0	936.2	936.1	934.8	933.4	932.0	930.7
175°	937.7	938.8	939.9	939.8	938.6	937.4	936.1	934.9
177.5°	939.2	940.2	941.2	941.1	939.9	938.6	937.4	936.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3

(END OF REPORT)