

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331988-940

Luminaire Tested: **S123DIP-S775D1025U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331988-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6482.3 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331988-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331988-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45	44	40	38	35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P331988-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	1.6
10°-20°	288.8	4.5
20°-30°	426.6	6.6
30°-40°	498.4	7.7
40°-50°	501.0	7.7
50°-60°	440.1	6.8
60°-70°	327.9	5.1
70°-80°	186.8	2.9
80°-90°	57.0	0.9
90°-100°	43.6	0.7
100°-110°	207.6	3.2
110°-120°	498.6	7.7
120°-130°	634.9	9.8
130°-140°	678.4	10.5
140°-150°	634.4	9.8
150°-160°	511.7	7.9
160°-170°	330.3	5.1
170°-180°	113.8	1.8
0°-30°	817.7	12.6
0°-40°	1316.1	20.3
0°-60°	2257.3	34.8
0°-90°	2828.9	43.6
90°-120°	749.8	11.6
90°-150°	2697.6	41.6
90°-180°	3653.0	56.4
0°-180°	6482.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	1	10	21	25	27	5
95°	54	20	28	34	34	67
105°	265	270	195	46	39	281
115°	498	503	511	520	523	491
125°	701	708	712	714	716	626
135°	873	878	882	884	882	672
145°	1008	1014	1016	1017	1017	630
155°	1110	1108	1109	1113	1108	511
165°	1170	1168	1167	1173	1168	331
175°	1198	1194	1194	1200	1194	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331988-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.6	19.5	19.4	19.3	19.2	19.4	19.6	20.0	20.3	20.7	20.7
90°	0.9	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1
92.5°	16.6	16.0	15.4	14.9	14.4	15.1	16.9	18.9	20.9	22.8	24.1
95°	54.3	46.2	38.1	30.0	21.8	18.9	21.0	23.3	25.4	27.6	29.0
97.5°	109.1	105.5	101.8	98.2	94.5	85.6	71.4	57.2	42.9	28.6	30.2
100°	150.4	154.4	158.4	162.3	166.2	152.8	121.9	91.0	60.2	29.3	30.9
102.5°	197.4	200.3	203.1	206.0	208.8	193.4	159.7	126.0	92.3	58.6	53.7
105°	265.2	267.4	269.6	271.8	273.9	266.1	248.3	230.5	212.8	194.9	159.9
107.5°	336.8	338.6	340.3	342.1	343.8	346.1	348.8	351.7	354.5	357.3	331.6
110°	384.5	386.1	387.6	389.2	390.8	392.7	394.8	397.1	399.2	401.4	394.8



TEST NUMBER: P331988-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.1	431.5	432.9	434.4	435.8	437.6	439.8	441.9	444.1	446.3	446.4
115°	497.6	498.7	499.9	501.1	502.3	503.8	505.5	507.3	509.1	510.9	512.9
117.5°	562.8	564.4	565.8	567.3	568.7	569.9	570.8	571.8	572.7	573.5	575.2
120°	603.4	605.2	607.0	608.8	610.6	611.8	612.3	613.0	613.6	614.1	615.7
122.5°	644.8	646.2	647.6	649.2	650.6	651.8	652.5	653.3	654.0	654.7	655.9
125°	701.3	702.9	704.5	706.1	707.7	708.9	709.7	710.4	711.2	712.0	712.5
127.5°	756.2	757.8	759.4	760.9	762.5	763.8	764.7	765.7	766.6	767.6	768.2
130°	790.4	791.9	793.5	795.1	796.7	797.9	798.7	799.5	800.2	801.0	801.8
132.5°	823.1	824.7	826.3	827.9	829.5	830.5	831.2	831.8	832.5	833.1	833.9
135°	873.2	874.3	875.5	876.7	877.9	878.9	879.7	880.5	881.3	882.1	882.6
137.5°	915.9	917.4	918.9	920.4	921.9	922.8	923.3	923.7	924.2	924.6	925.5
140°	944.3	945.6	946.7	947.9	949.1	950.0	950.6	951.2	951.8	952.3	953.1
142.5°	970.7	971.9	973.0	974.3	975.4	976.3	977.0	977.5	978.1	978.7	979.4
145°	1007.5	1009.0	1010.3	1011.7	1013.1	1014.0	1014.4	1014.8	1015.1	1015.6	1015.9
147.5°	1042.2	1043.2	1044.1	1045.0	1045.9	1046.5	1047.0	1047.3	1047.8	1048.1	1048.6
150°	1063.6	1064.3	1064.8	1065.4	1066.0	1066.5	1066.8	1067.3	1067.6	1068.1	1068.4
152.5°	1082.8	1083.2	1083.4	1083.7	1084.0	1084.2	1084.4	1084.7	1084.9	1085.1	1085.8
155°	1109.9	1109.5	1109.1	1108.8	1108.3	1108.2	1108.4	1108.6	1108.8	1109.0	1110.0
157.5°	1130.9	1130.9	1130.9	1130.8	1130.8	1130.6	1130.4	1130.2	1130.1	1129.8	1131.0
160°	1143.7	1143.5	1143.4	1143.2	1142.9	1142.7	1142.5	1142.4	1142.1	1141.9	1143.2
162.5°	1155.8	1155.3	1154.8	1154.3	1153.8	1153.4	1153.2	1153.0	1152.8	1152.6	1154.0
165°	1170.5	1169.8	1169.2	1168.7	1168.1	1167.7	1167.4	1167.2	1167.1	1166.9	1168.4
167.5°	1181.8	1181.1	1180.3	1179.5	1178.7	1178.2	1178.2	1178.2	1178.2	1178.2	1179.8
170°	1188.2	1187.4	1186.7	1185.9	1185.1	1184.6	1184.6	1184.6	1184.6	1184.6	1186.2
172.5°	1192.5	1191.6	1190.6	1189.6	1188.7	1188.3	1188.5	1188.7	1188.7	1188.9	1190.5
175°	1198.0	1197.0	1196.1	1195.1	1194.1	1193.6	1193.8	1194.1	1194.3	1194.4	1195.9
177.5°	1199.4	1198.6	1197.8	1197.0	1196.3	1196.0	1196.1	1196.3	1196.4	1196.6	1197.8
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P331988-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	20.7	20.7	20.7	20.7	20.8	20.9	21.0	21.0
90°	22.9	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	25.3	26.6	27.8	28.6	28.8	29.1	29.3	29.5
95°	30.3	31.7	33.2	33.8	33.8	33.8	33.8	33.8
97.5°	31.8	33.4	35.0	35.8	36.1	36.3	36.5	36.6
100°	32.5	34.2	35.7	36.6	36.8	37.0	37.2	37.4
102.5°	48.8	43.9	39.0	36.6	37.0	37.4	37.7	38.1
105°	124.9	89.9	54.9	37.5	38.0	38.3	38.8	39.1
107.5°	305.9	280.3	254.6	228.5	202.2	175.8	149.4	123.0
110°	388.3	381.8	375.3	357.9	329.6	301.3	273.0	244.8



TEST NUMBER: P331988-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	446.5	446.7	446.7	443.8	437.8	431.9	425.9	419.9
115°	514.9	516.8	518.8	520.2	520.9	521.7	522.5	523.3
117.5°	576.8	578.3	579.9	580.8	580.9	581.0	581.2	581.4
120°	617.3	618.8	620.5	621.3	621.3	621.3	621.3	621.3
122.5°	656.9	658.1	659.2	659.8	660.0	660.1	660.2	660.4
125°	712.8	713.2	713.6	714.0	714.4	714.8	715.2	715.6
127.5°	768.8	769.5	770.1	770.3	769.8	769.5	769.0	768.7
130°	802.6	803.4	804.2	804.4	804.1	803.6	803.3	802.8
132.5°	834.6	835.4	836.2	836.3	835.8	835.3	834.7	834.2
135°	883.2	883.9	884.4	884.4	883.9	883.2	882.6	882.1
137.5°	926.5	927.5	928.4	928.6	928.3	927.9	927.5	927.1
140°	954.0	954.8	955.6	955.7	955.3	954.9	954.6	954.1
142.5°	980.0	980.6	981.2	981.2	980.7	980.2	979.6	979.1
145°	1016.4	1016.7	1017.2	1017.4	1017.4	1017.4	1017.4	1017.4
147.5°	1048.9	1049.3	1049.7	1049.5	1048.6	1047.7	1046.7	1045.8
150°	1068.9	1069.3	1069.7	1069.5	1069.0	1068.4	1067.7	1067.2
152.5°	1086.5	1087.3	1088.0	1087.9	1087.0	1086.1	1085.2	1084.2
155°	1111.0	1112.0	1112.9	1112.9	1111.7	1110.5	1109.3	1108.1
157.5°	1132.2	1133.4	1134.6	1134.4	1132.8	1131.3	1129.8	1128.3
160°	1144.3	1145.5	1146.7	1146.6	1145.2	1143.8	1142.5	1141.0
162.5°	1155.3	1156.6	1158.0	1158.1	1156.8	1155.6	1154.4	1153.2
165°	1170.0	1171.6	1173.2	1173.3	1171.9	1170.5	1169.1	1167.8
167.5°	1181.4	1183.0	1184.5	1184.5	1183.0	1181.4	1179.8	1178.2
170°	1187.8	1189.5	1191.0	1191.0	1189.5	1187.8	1186.2	1184.6
172.5°	1192.1	1193.6	1195.2	1195.2	1193.5	1191.7	1190.0	1188.2
175°	1197.2	1198.6	1200.0	1199.9	1198.3	1196.8	1195.2	1193.6
177.5°	1199.1	1200.4	1201.7	1201.5	1199.9	1198.4	1196.8	1195.2
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0

(END OF REPORT)