

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331990-940

Luminaire Tested: **S123DIP-S775D1025U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331990-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6137.1 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331990-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331990-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46
1	97	93	89	85	89	85	82	79	71	69	66	58	57	55	46	45	44	39
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	41	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	29	33	28	25	26	23	21	18
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	19	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P331990-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	1.7
10°-20°	288.8	4.7
20°-30°	426.6	7.0
30°-40°	498.4	8.1
40°-50°	501.0	8.2
50°-60°	440.1	7.2
60°-70°	327.9	5.3
70°-80°	186.8	3.0
80°-90°	57.0	0.9
90°-100°	244.7	4.0
100°-110°	692.9	11.3
110°-120°	681.6	11.1
120°-130°	543.7	8.9
130°-140°	428.7	7.0
140°-150°	319.9	5.2
150°-160°	223.0	3.6
160°-170°	131.0	2.1
170°-180°	42.6	0.7
0°-30°	817.7	13.3
0°-40°	1316.1	21.4
0°-60°	2257.3	36.8
0°-90°	2829.0	46.1
90°-120°	1619.2	26.4
90°-150°	2911.5	47.4
90°-180°	3308.0	53.9
0°-180°	6137.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	2	11	22	25	26	5
95°	30	98	528	154	103	33
105°	103	153	716	1251	1132	110
115°	182	227	547	1200	1377	181
125°	254	300	511	926	1086	225
135°	297	355	504	762	880	230
145°	339	389	498	625	688	213
155°	385	416	482	547	570	177
165°	421	433	461	489	498	119
175°	439	439	442	449	448	42
180°	440	440	440	440	440	



TEST NUMBER: P331990-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.8	19.6	19.5	19.5	19.4	19.4	19.8	20.2	20.5	20.9	20.5
90°	1.8	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4
92.5°	11.1	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3
95°	30.2	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1
97.5°	51.6	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1
100°	65.9	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2
102.5°	80.8	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4
105°	103.3	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1
107.5°	127.1	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0
110°	144.2	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2



TEST NUMBER: P331990-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.9	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2
115°	182.4	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4
117.5°	205.1	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4
120°	220.7	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5
122.5°	234.3	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1
125°	253.7	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2
127.5°	268.5	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6
130°	277.7	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7
132.5°	284.8	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4
135°	297.3	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3
137.5°	309.1	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8
140°	316.9	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4
142.5°	325.4	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7
145°	339.1	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0
147.5°	353.0	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5
150°	362.3	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5
152.5°	371.5	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9
155°	385.4	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4
157.5°	396.5	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7
160°	405.0	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3
162.5°	411.4	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9
165°	421.0	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1
167.5°	428.3	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9
170°	432.6	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9
172.5°	435.4	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9
175°	438.8	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2
177.5°	440.4	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331990-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	20.5	20.6	20.6	20.9	20.7	20.9	21.0	20.9
90°	22.3	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	74.9	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	320.4	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	798.8	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	1049.5	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1132.7	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1157.1	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1087.0	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1020.0	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P331990-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	953.8	1121.1	1246.8	1327.0	1372.5	1394.5	1401.3	1401.7
115°	866.0	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	802.5	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	769.0	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	742.7	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	707.7	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	677.0	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	657.8	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	640.0	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	615.9	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	594.1	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	581.2	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	569.1	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	554.6	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	542.6	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	534.0	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	526.2	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	514.4	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	502.0	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	494.9	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	486.3	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	475.3	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	465.7	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	459.3	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	453.6	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	445.9	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.1	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)