

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332868-927

Luminaire Tested: **S124RDIP-S350D365U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332868-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D365U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2290.4 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332868-927

CATALOG NUMBER: S124RDIP-S350D365U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332868-927

CATALOG NUMBER: S124RDIP-S350D365U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	50	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	31
4	75	64	56	51	69	60	53	47	51	46	41	43	39	36	35	32	30	26
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	22	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P332868-927

CATALOG NUMBER: S124RDIP-S350D365U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.0	2.0
10°-20°	128.3	5.6
20°-30°	185.2	8.1
30°-40°	210.0	9.2
40°-50°	202.8	8.9
50°-60°	168.6	7.4
60°-70°	116.4	5.1
70°-80°	59.0	2.6
80°-90°	16.2	0.7
90°-100°	12.8	0.6
100°-110°	81.6	3.6
110°-120°	156.1	6.8
120°-130°	198.2	8.7
130°-140°	212.1	9.3
140°-150°	198.3	8.7
150°-160°	159.9	7.0
160°-170°	103.2	4.5
170°-180°	35.6	1.6
0°-30°	359.5	15.7
0°-40°	569.5	24.9
0°-60°	940.8	41.1
0°-90°	1132.5	49.4
90°-120°	250.6	10.9
90°-150°	859.2	37.5
90°-180°	1158.0	50.6
0°-180°	2290.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	1	4	6	8	8	2
95°	15	6	6	8	8	20
105°	84	86	87	89	80	88
115°	157	158	158	158	158	155
125°	221	222	222	222	223	197
135°	274	274	275	276	276	211
145°	316	317	317	317	318	198
155°	347	347	346	347	347	160
165°	366	365	364	366	364	103
175°	374	373	373	375	372	36
180°	374	374	374	374	374	



TEST NUMBER: P332868-927

CATALOG NUMBER: S124RDIP-S350D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.1	6.7	6.3	5.9	5.5	5.3	5.3	5.4	5.4	5.5	5.5
90°	0.9	1.5	2.2	2.9	3.6	4.2	4.7	5.1	5.6	6.2	6.5
92.5°	3.6	3.6	3.6	3.6	3.6	4.0	4.4	4.9	5.5	5.9	6.3
95°	15.4	13.3	11.2	9.0	7.0	5.9	5.9	6.0	6.1	6.2	6.5
97.5°	32.7	34.0	35.3	36.7	37.9	35.2	28.2	21.3	14.3	7.4	7.4
100°	45.9	47.1	48.2	49.3	50.4	46.7	38.1	29.5	20.9	12.4	11.2
102.5°	60.7	61.6	62.3	63.1	64.0	63.8	62.7	61.6	60.4	59.3	47.9
105°	84.3	84.6	85.0	85.4	85.8	86.1	86.4	86.7	87.1	87.4	87.9
107.5°	106.2	106.3	106.5	106.7	106.9	107.2	107.7	108.1	108.4	108.9	109.2
110°	121.0	121.1	121.3	121.5	121.7	122.0	122.3	122.7	123.1	123.5	123.6



TEST NUMBER: P332868-927

CATALOG NUMBER: S124RDIP-S350D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	135.3	135.6	135.9	136.3	136.7	136.9	137.0	137.2	137.4	137.6	137.5
115°	157.3	157.6	157.7	157.9	158.1	158.1	158.1	158.0	158.0	157.9	158.0
117.5°	177.2	177.4	177.7	178.0	178.2	178.4	178.6	178.7	178.8	179.0	179.0
120°	190.7	190.9	191.2	191.4	191.6	191.7	191.7	191.6	191.5	191.5	191.6
122.5°	203.2	203.4	203.5	203.7	203.8	203.9	204.0	204.1	204.1	204.3	204.3
125°	221.2	221.4	221.7	221.9	222.2	222.2	222.1	222.0	221.9	221.7	221.9
127.5°	238.2	238.3	238.3	238.4	238.4	238.6	238.9	239.2	239.5	239.8	239.7
130°	249.1	249.2	249.3	249.4	249.5	249.5	249.7	249.9	250.1	250.3	250.3
132.5°	259.3	259.4	259.4	259.6	259.7	259.8	260.1	260.3	260.5	260.8	260.9
135°	274.3	274.3	274.3	274.2	274.1	274.2	274.5	274.7	275.0	275.2	275.4
137.5°	287.7	287.8	287.8	287.8	287.9	288.0	288.3	288.5	288.8	289.1	289.2
140°	296.5	296.6	296.8	296.8	297.0	297.1	297.2	297.4	297.5	297.6	297.8
142.5°	304.4	304.5	304.8	305.0	305.2	305.4	305.5	305.5	305.6	305.7	305.8
145°	316.4	316.6	316.7	317.0	317.1	317.2	317.2	317.2	317.2	317.2	317.3
147.5°	325.9	326.3	326.6	327.0	327.3	327.5	327.4	327.3	327.3	327.3	327.3
150°	332.9	333.1	333.4	333.7	333.9	334.0	333.9	333.8	333.7	333.7	333.7
152.5°	338.7	338.9	339.1	339.3	339.5	339.5	339.5	339.3	339.2	339.1	339.2
155°	346.9	347.0	347.0	347.1	347.1	347.1	346.9	346.7	346.5	346.3	346.6
157.5°	353.8	353.7	353.7	353.6	353.6	353.5	353.3	353.1	352.8	352.7	353.0
160°	357.8	357.6	357.4	357.3	357.0	357.0	356.9	356.8	356.7	356.6	357.0
162.5°	361.4	361.2	360.9	360.7	360.4	360.3	360.2	360.1	360.1	360.0	360.4
165°	365.9	365.6	365.3	365.0	364.6	364.5	364.5	364.5	364.5	364.5	365.0
167.5°	369.5	369.2	368.8	368.5	368.2	368.0	368.0	368.0	367.9	367.9	368.4
170°	371.5	371.1	370.7	370.4	370.0	369.9	369.9	370.0	370.0	370.1	370.6
172.5°	372.9	372.5	372.1	371.8	371.4	371.2	371.3	371.4	371.4	371.5	371.9
175°	374.3	373.9	373.6	373.2	372.8	372.6	372.7	372.8	372.9	372.9	373.5
177.5°	375.0	374.6	374.3	373.9	373.6	373.4	373.6	373.7	373.8	373.8	374.3
180°	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3



TEST NUMBER: P332868-927

CATALOG NUMBER: S124RDIP-S350D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	5.5	5.5	5.5	5.5	5.6	5.7	5.8	5.9
90°	6.9	7.3	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	6.7	7.1	7.4	7.6	7.7	7.7	7.7	7.8
95°	6.9	7.3	7.7	7.8	7.9	8.0	8.1	8.1
97.5°	7.4	7.5	7.5	7.6	7.7	7.7	7.8	7.8
100°	10.2	9.1	8.1	7.6	7.7	7.7	7.8	7.8
102.5°	36.5	25.1	13.7	8.0	8.0	8.0	8.1	8.1
105°	88.5	89.0	89.6	88.7	86.5	84.3	82.0	79.8
107.5°	109.5	109.7	110.0	110.3	110.5	110.7	111.0	111.2
110°	123.7	123.8	124.0	124.1	124.3	124.5	124.7	124.8





TEST NUMBER: P332868-927

CATALOG NUMBER: S124RDIP-S350D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.5	137.5	137.4	137.6	137.8	138.1	138.3	138.6
115°	158.1	158.3	158.4	158.4	158.4	158.4	158.4	158.4
117.5°	178.9	178.9	178.9	178.8	178.8	178.8	178.8	178.7
120°	191.7	191.9	192.0	192.0	191.9	191.7	191.6	191.5
122.5°	204.4	204.5	204.5	204.5	204.4	204.3	204.1	204.1
125°	222.1	222.3	222.4	222.6	222.7	222.8	222.8	222.8
127.5°	239.7	239.6	239.6	239.6	239.6	239.5	239.4	239.4
130°	250.4	250.5	250.6	250.6	250.6	250.6	250.6	250.6
132.5°	260.9	261.0	261.1	261.1	261.0	260.9	260.9	260.9
135°	275.4	275.6	275.7	275.8	275.9	276.1	276.2	276.3
137.5°	289.4	289.5	289.6	289.7	289.6	289.6	289.5	289.5
140°	297.9	298.2	298.3	298.5	298.6	298.6	298.7	298.7
142.5°	305.9	306.1	306.2	306.3	306.3	306.3	306.3	306.3
145°	317.3	317.4	317.4	317.5	317.7	317.8	317.9	318.1
147.5°	327.3	327.4	327.4	327.5	327.6	327.6	327.6	327.7
150°	333.7	333.7	333.7	333.7	333.8	333.9	333.9	334.0
152.5°	339.3	339.4	339.5	339.5	339.5	339.5	339.5	339.4
155°	346.8	347.1	347.3	347.4	347.1	347.0	346.8	346.6
157.5°	353.3	353.6	353.9	353.9	353.6	353.3	353.0	352.7
160°	357.4	357.8	358.1	358.1	357.8	357.4	357.0	356.6
162.5°	360.8	361.2	361.6	361.5	361.1	360.7	360.2	359.8
165°	365.5	366.0	366.5	366.5	365.9	365.4	364.8	364.2
167.5°	369.0	369.6	370.0	370.0	369.4	368.8	368.1	367.6
170°	371.1	371.6	372.1	372.0	371.5	370.8	370.2	369.6
172.5°	372.5	373.0	373.4	373.4	372.7	372.0	371.4	370.7
175°	374.1	374.6	375.2	375.1	374.3	373.6	372.8	372.1
177.5°	374.7	375.1	375.5	375.3	374.8	374.1	373.6	373.0
180°	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3

(END OF REPORT)